

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331359

Luminaire Tested: **S122DIP-S675D925U835-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331359  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S675D925U835-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6546.5 lumens  
Efficiency: N/A  
Efficacy: 125.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45					45			
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39					39			
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33					33			
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33	28					28			
4	74	64	56	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25					25			
5	68	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22					22			
6	63	52	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22	19					19			
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17					17			
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16					16			
9	51	39	31	27	47	36	30	25	31	26	22	26	22	19	21	19	16	14					14			
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13					13			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21447	21447	21447	21447
5°	24044	21585	19128	21585
10°	27552	21408	16554	21408
15°	30479	21016	14626	21016
20°	30015	20594	13332	20594
25°	27064	20035	12513	20035
30°	22365	19140	11915	19140
35°	16301	18203	11491	18203
40°	13019	17098	11255	17098
45°	11376	15817	10933	15817
50°	10693	14579	10721	14579
55°	9858	13320	10432	13320
60°	9032	11983	9991	11983
65°	8229	10785	9555	10785
70°	7468	9616	8917	9616
75°	6625	8309	7898	8309
80°	5700	6881	6360	6881
85°	5113	5113	3779	5113



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.5	1.9
10°-20°	367.8	5.6
20°-30°	533.7	8.2
30°-40°	563.2	8.6
40°-50°	498.7	7.6
50°-60°	398.0	6.1
60°-70°	270.5	4.1
70°-80°	138.7	2.1
80°-90°	38.1	0.6
90°-100°	207.5	3.2
100°-110°	704.2	10.8
110°-120°	748.1	11.4
120°-130°	615.8	9.4
130°-140°	494.5	7.6
140°-150°	373.7	5.7
150°-160°	262.6	4.0
160°-170°	154.6	2.4
170°-180°	50.3	0.8
0°-30°	1028.0	15.7
0°-40°	1591.2	24.3
0°-60°	2487.8	38.0
0°-90°	2935.1	44.8
90°-120°	1659.8	25.4
90°-150°	3143.8	48.0
90°-180°	3611.0	55.2
0°-180°	6546.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1484	1332	1180	1332	1484	148
15°	1823	1257	875	1257	1823	503
25°	1519	1125	702	1125	1519	687
35°	827	924	583	924	827	538
45°	498	693	479	693	498	392
55°	350	473	371	473	350	314
65°	215	282	250	282	215	214
75°	106	133	127	133	106	113
85°	28	28	20	28	28	31
90°	33	1	33	1	33	19
95°	114	35	114	35	114	148
105°	1125	122	1125	122	1125	1088
115°	1480	215	1480	215	1480	1449
125°	1201	299	1201	299	1201	1085
135°	995	351	995	351	995	773
145°	794	401	794	401	794	505
155°	668	456	668	456	668	312
165°	586	497	586	497	586	168
175°	528	518	528	518	528	51
180°	519	519	519	519	519	



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1389.5	1389.9	1390.8	1384.2	1383.4	1383.4	1377.7	1372.8	1367.1	1359.3	1360.1
5°	1483.5	1489.1	1491.1	1485.0	1475.8	1474.8	1466.1	1451.8	1438.5	1427.8	1420.2
7.5°	1595.6	1597.8	1592.8	1584.7	1577.9	1565.7	1549.5	1533.7	1511.5	1491.2	1476.1
10°	1680.5	1683.6	1674.9	1663.2	1653.5	1639.2	1615.7	1591.7	1562.6	1534.5	1512.0
12.5°	1745.0	1752.6	1741.5	1739.9	1723.3	1703.7	1675.7	1663.6	1622.6	1583.5	1559.4
15°	1823.4	1822.9	1824.0	1814.3	1802.0	1798.9	1769.3	1737.2	1679.5	1656.5	1616.7
17.5°	1800.8	1808.5	1812.1	1812.0	1811.7	1809.8	1800.3	1780.0	1751.1	1713.8	1667.8
20°	1746.9	1757.1	1758.6	1770.4	1777.0	1785.7	1789.2	1783.6	1765.8	1734.6	1694.8
22.5°	1663.6	1666.4	1671.2	1689.5	1703.9	1725.6	1737.0	1755.9	1749.0	1733.8	1700.5
25°	1519.2	1514.1	1532.0	1541.1	1574.3	1609.0	1634.1	1661.6	1686.1	1700.9	1691.2
27.5°	1345.8	1338.2	1364.9	1389.3	1416.3	1453.9	1492.9	1538.9	1577.2	1625.1	1641.5
30°	1199.6	1204.2	1229.8	1255.8	1296.6	1349.7	1393.6	1444.2	1498.8	1552.4	1589.6
32.5°	1042.0	1059.7	1075.8	1115.7	1151.6	1210.9	1275.2	1338.4	1406.5	1467.4	1525.1
35°	827.0	847.4	869.9	899.0	949.5	1008.2	1071.0	1156.2	1249.2	1332.4	1400.8
37.5°	696.1	692.8	705.7	726.7	767.7	815.0	887.3	971.6	1080.9	1178.7	1275.2
40°	617.7	615.6	624.8	644.2	675.4	710.1	773.4	847.4	949.0	1068.4	1183.3
42.5°	563.8	565.0	570.1	583.8	605.1	633.7	681.1	744.1	837.1	949.6	1073.0
45°	498.2	501.8	507.4	514.1	526.3	549.8	576.3	621.3	694.8	788.7	910.2
47.5°	451.1	451.2	456.9	462.7	470.0	483.2	504.9	533.0	584.9	661.4	765.8
50°	425.7	422.2	426.3	430.8	438.5	447.7	462.0	488.5	523.2	585.0	672.3
52.5°	394.7	394.8	398.5	400.2	407.1	416.2	429.3	447.7	479.1	527.4	599.2
55°	350.2	352.7	354.8	357.8	364.0	370.6	380.8	393.1	417.6	453.8	506.9
57.5°	308.3	309.1	311.2	317.0	320.9	327.0	336.7	347.8	363.8	390.6	430.5
60°	279.7	279.7	283.8	286.4	291.5	297.6	305.3	316.0	330.3	352.2	384.4
62.5°	253.6	253.2	254.8	259.0	262.9	268.6	276.3	285.4	298.8	318.3	344.8
65°	215.4	214.4	217.5	218.5	222.6	228.2	234.3	244.0	254.7	269.0	292.5
67.5°	178.7	179.9	181.5	183.5	185.7	191.6	195.7	202.6	211.6	223.5	239.4
70°	158.2	158.2	158.2	159.8	162.8	165.9	170.0	175.6	184.3	194.5	208.8
72.5°	135.4	137.0	138.6	137.7	141.6	143.4	148.3	151.5	159.8	166.3	179.0
75°	106.2	106.2	106.2	108.7	110.3	111.8	114.9	117.9	122.0	130.2	136.8
77.5°	79.2	79.0	79.5	80.1	81.8	83.6	84.5	87.3	91.1	94.8	100.5
80°	61.3	62.3	62.8	63.8	63.8	64.8	65.3	68.9	71.5	74.0	77.6
82.5°	47.4	47.6	47.7	47.9	48.3	48.9	50.2	51.4	52.3	54.4	57.2
85°	27.6	27.1	27.1	28.1	27.6	27.6	28.6	29.6	29.6	30.1	31.6
87.5°	17.2	17.2	17.6	17.2	17.2	17.4	17.0	17.0	17.6	18.2	18.4
90°	32.9	32.9	32.9	32.9	32.9	31.9	29.9	31.9	32.9	33.9	32.9
92.5°	55.3	56.9	56.1	59.3	60.1	66.3	74.7	87.0	109.6	129.7	127.9
95°	113.8	112.8	115.8	123.8	136.7	158.7	200.6	261.5	342.3	391.2	346.3
97.5°	224.0	232.3	246.9	271.5	319.2	391.2	499.2	610.2	700.6	667.9	503.0
100°	357.3	375.3	404.2	447.1	530.0	650.7	787.4	911.2	932.2	788.4	542.9
102.5°	628.8	653.1	689.2	762.5	852.5	980.5	1080.5	1108.4	1018.4	792.4	527.8
105°	1124.8	1138.7	1181.7	1243.5	1305.4	1338.4	1325.4	1212.6	1005.0	739.5	498.0
107.5°	1436.8	1455.3	1463.9	1467.3	1459.5	1411.2	1307.4	1137.6	917.4	682.9	483.2
110°	1531.0	1532.0	1523.0	1504.0	1461.1	1379.3	1251.5	1072.9	862.3	655.7	480.1



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1529.4	1524.0	1507.0	1475.3	1415.6	1321.8	1185.3	1013.8	824.0	638.1	480.8
115°	1480.1	1471.1	1445.1	1399.2	1328.4	1225.6	1094.8	941.1	776.5	618.8	485.0
117.5°	1392.0	1384.5	1357.1	1308.6	1236.4	1139.9	1021.4	886.4	746.5	609.4	492.2
120°	1335.4	1325.4	1296.4	1249.5	1179.7	1088.8	983.1	859.3	730.6	603.8	497.0
122.5°	1276.3	1267.9	1242.1	1196.0	1133.4	1051.3	951.1	837.7	717.0	600.6	502.6
125°	1200.6	1192.6	1167.7	1129.8	1071.9	997.0	909.2	806.4	697.6	594.8	511.0
127.5°	1134.4	1128.0	1106.4	1070.9	1020.4	951.3	868.5	775.5	679.7	591.4	519.6
130°	1096.8	1088.8	1068.9	1035.0	986.1	920.2	841.3	755.5	667.7	589.8	526.0
132.5°	1057.7	1050.5	1032.2	998.2	950.1	888.2	815.8	736.3	658.1	589.0	532.3
135°	995.0	991.0	973.1	940.1	897.2	841.3	775.5	709.6	644.7	587.8	539.9
137.5°	933.6	927.6	911.8	883.5	844.3	795.6	743.3	688.2	635.3	587.6	546.7
140°	891.2	885.3	870.3	844.3	812.4	768.5	722.6	674.7	629.8	586.8	549.9
142.5°	848.9	847.7	834.4	810.8	780.5	743.7	704.2	663.5	624.2	586.8	552.3
145°	794.4	791.4	781.5	764.5	740.5	711.6	680.7	647.7	616.8	584.8	554.9
147.5°	748.7	746.9	740.1	726.6	706.8	685.6	661.5	635.5	609.2	581.3	555.7
150°	721.6	720.6	714.6	702.6	687.6	669.7	648.7	626.8	602.8	578.9	554.9
152.5°	698.4	698.2	693.8	683.4	671.7	656.1	638.3	618.0	597.2	574.9	553.3
155°	667.7	669.7	665.7	658.7	647.7	636.7	621.8	605.8	586.8	567.9	550.9
157.5°	641.5	641.5	639.7	633.9	626.2	617.6	605.0	591.6	577.1	560.7	546.3
160°	624.8	624.8	623.8	618.8	611.8	604.8	593.8	582.8	569.9	555.9	543.9
162.5°	608.8	609.6	608.6	605.2	598.2	592.8	583.4	574.1	563.5	551.9	541.5
165°	585.8	586.8	586.8	582.8	578.9	574.9	567.9	560.9	552.9	543.9	536.9
167.5°	564.7	565.9	566.1	563.9	562.1	558.5	553.7	548.3	542.5	536.9	532.3
170°	551.9	553.9	554.9	551.9	550.9	548.9	544.9	541.9	536.9	532.9	530.0
172.5°	541.5	542.7	543.7	542.3	541.3	540.1	536.9	534.7	531.4	528.2	526.8
175°	528.0	530.0	531.0	530.0	530.0	529.0	528.0	527.0	524.0	523.0	522.0
177.5°	519.8	521.4	522.2	522.2	522.2	522.2	521.4	521.4	519.8	519.0	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1363.0	1359.7	1357.7	1350.3	1343.8	1337.3	1335.2	1336.0	1327.1	1318.5	1314.8
5°	1416.1	1405.9	1396.2	1382.4	1366.1	1348.2	1339.0	1331.8	1314.0	1294.6	1283.4
7.5°	1463.7	1449.1	1430.4	1404.4	1380.7	1352.6	1334.7	1318.9	1292.7	1265.4	1248.6
10°	1492.7	1472.7	1448.7	1417.1	1388.0	1353.8	1329.8	1305.8	1275.2	1242.5	1222.1
12.5°	1517.6	1490.7	1467.1	1426.5	1392.1	1349.3	1320.8	1287.0	1254.8	1216.0	1196.0
15°	1576.9	1527.4	1482.4	1436.5	1394.1	1334.4	1302.8	1257.3	1214.9	1167.0	1144.0
17.5°	1622.7	1567.1	1496.3	1437.9	1388.5	1322.4	1275.9	1221.5	1171.4	1116.5	1085.3
20°	1648.9	1585.0	1509.0	1439.6	1380.3	1304.8	1254.3	1198.6	1139.9	1078.1	1044.4
22.5°	1664.4	1597.3	1522.1	1433.4	1364.0	1290.5	1226.9	1165.9	1106.4	1039.8	1004.4
25°	1669.3	1608.0	1528.4	1428.3	1343.6	1260.4	1183.8	1124.6	1052.6	990.3	938.8
27.5°	1645.0	1601.1	1524.5	1418.7	1320.0	1222.7	1137.4	1070.3	994.3	926.7	874.9
30°	1615.2	1589.6	1515.1	1408.9	1301.2	1196.6	1102.6	1026.6	951.0	882.6	829.5
32.5°	1569.0	1563.5	1498.0	1395.0	1281.2	1163.5	1066.3	989.4	905.7	838.5	787.9
35°	1478.4	1502.9	1461.5	1364.0	1243.5	1116.4	1011.3	923.5	836.7	772.4	724.9
37.5°	1356.9	1417.7	1406.9	1318.6	1192.7	1065.2	949.1	857.3	774.6	709.7	663.1
40°	1273.1	1350.7	1362.0	1283.9	1156.8	1025.6	902.5	811.2	730.5	671.3	624.3
42.5°	1183.3	1274.0	1304.8	1242.2	1117.5	983.9	860.9	766.2	686.4	628.8	587.2
45°	1032.7	1152.7	1208.3	1172.6	1052.1	915.3	788.7	692.7	620.2	566.1	534.0
47.5°	891.9	1023.0	1097.8	1085.2	979.3	843.8	718.7	626.6	556.0	512.8	484.0
50°	792.3	927.0	1017.4	1021.5	927.0	792.8	667.2	580.4	515.6	475.3	451.8
52.5°	705.7	834.3	932.9	954.5	868.6	739.7	621.1	534.7	477.6	440.5	419.5
55°	592.7	701.4	810.6	850.5	781.5	659.0	549.3	473.2	419.6	394.1	375.7
57.5°	492.7	583.4	684.3	728.3	685.8	580.9	478.0	412.0	368.5	346.1	332.0
60°	440.0	511.5	601.3	653.9	617.2	523.8	433.9	371.1	335.4	315.5	302.2
62.5°	391.0	454.3	530.3	578.4	558.4	470.3	389.8	334.4	303.5	284.8	275.3
65°	322.6	372.7	431.4	475.8	462.5	395.6	329.8	282.3	257.8	243.0	235.3
67.5°	265.7	301.8	342.5	381.4	370.7	323.3	270.5	233.5	215.2	202.5	197.9
70°	229.7	257.3	293.5	324.7	316.0	277.2	235.3	203.7	187.9	177.1	172.5
72.5°	195.4	218.1	245.7	271.2	265.3	233.1	198.2	174.3	162.1	152.2	148.4
75°	147.5	164.9	181.7	198.6	197.0	172.0	151.6	133.2	123.5	115.9	114.3
77.5°	108.9	118.6	130.1	140.1	137.3	123.0	107.0	96.5	89.3	84.2	83.4
80°	83.2	88.8	97.0	104.1	100.6	94.4	81.7	74.0	68.9	63.8	61.8
82.5°	60.3	66.0	70.9	74.7	72.0	66.3	58.4	53.2	50.1	46.7	45.8
85°	31.6	34.7	36.8	37.8	36.8	33.2	29.6	27.6	25.0	23.5	23.0
87.5°	17.6	16.2	15.2	15.5	13.8	13.4	11.0	9.2	9.4	9.8	9.3
90°	26.9	20.0	15.0	12.0	10.0	8.0	4.0	1.0	4.0	8.0	10.0
92.5°	99.6	67.9	45.3	35.9	29.1	24.8	17.6	12.2	17.6	24.8	29.1
95°	230.5	143.7	97.8	73.9	57.9	48.9	38.9	34.9	38.9	48.9	57.9
97.5°	310.6	189.6	131.9	104.8	86.4	72.9	62.3	56.9	62.3	72.9	86.4
100°	327.4	205.6	152.7	124.8	104.8	88.8	79.8	76.8	79.8	88.8	104.8
102.5°	328.2	220.0	171.1	143.1	122.4	106.4	97.4	95.2	97.4	106.4	122.4
105°	333.3	244.5	197.6	169.7	147.7	132.7	125.8	121.8	125.8	132.7	147.7
107.5°	347.1	269.7	224.2	196.0	174.3	160.5	153.7	150.5	153.7	160.5	174.3
110°	358.3	286.4	242.5	213.6	192.6	179.6	173.7	169.7	173.7	179.6	192.6





TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	370.3	302.4	260.1	230.3	210.2	198.0	191.2	187.2	191.2	198.0	210.2
115°	388.2	327.4	284.4	257.5	237.5	225.6	219.6	214.6	219.6	225.6	237.5
117.5°	407.4	350.3	310.6	282.6	263.5	252.9	246.9	242.9	246.9	252.9	263.5
120°	420.2	366.3	327.4	299.4	279.4	270.5	264.5	260.5	264.5	270.5	279.4
122.5°	431.3	381.4	344.9	316.2	296.2	286.4	280.4	277.3	280.4	286.4	296.2
125°	449.1	404.2	368.3	340.3	320.4	308.4	302.4	299.4	302.4	308.4	320.4
127.5°	465.7	425.4	390.4	361.7	342.5	329.3	321.0	317.0	321.0	329.3	342.5
130°	476.1	438.1	403.2	375.3	355.3	341.3	331.3	327.4	331.3	341.3	355.3
132.5°	486.4	449.3	416.0	388.0	367.3	352.5	341.7	336.9	341.7	352.5	367.3
135°	500.0	465.1	433.1	405.2	382.2	367.3	355.3	351.3	355.3	367.3	382.2
137.5°	510.4	477.9	446.3	420.4	397.6	381.6	369.7	364.9	369.7	381.6	397.6
140°	516.0	485.0	455.1	429.2	407.2	391.2	379.3	375.3	379.3	391.2	407.2
142.5°	520.8	490.6	461.5	437.1	416.0	400.0	388.8	385.6	388.8	400.0	416.0
145°	527.0	499.0	472.1	450.1	430.2	415.2	405.2	401.2	405.2	415.2	430.2
147.5°	530.4	505.8	480.5	460.9	444.3	430.5	421.0	418.0	421.0	430.5	444.3
150°	531.9	509.0	486.0	468.1	453.1	440.1	432.1	429.2	432.1	440.1	453.1
152.5°	532.7	512.2	491.6	475.3	461.1	449.7	441.7	440.3	441.7	449.7	461.1
155°	533.9	517.0	500.0	485.0	474.1	463.1	457.1	456.1	457.1	463.1	474.1
157.5°	533.9	520.4	506.0	493.4	484.6	475.1	470.3	469.3	470.3	475.1	484.6
160°	533.9	522.0	510.0	499.0	491.0	483.0	479.1	478.1	479.1	483.0	491.0
162.5°	533.1	522.8	512.4	503.8	496.6	490.2	486.2	486.8	486.2	490.2	496.6
165°	531.0	524.0	515.0	509.0	504.0	498.0	496.0	497.0	496.0	498.0	504.0
167.5°	529.6	523.8	517.2	513.4	509.8	506.0	504.2	505.4	504.2	506.0	509.8
170°	528.0	523.0	518.0	515.0	513.0	510.0	509.0	511.0	509.0	510.0	513.0
172.5°	525.6	522.2	518.8	516.6	515.4	512.4	513.0	514.2	513.0	512.4	515.4
175°	523.0	521.0	519.0	518.0	518.0	516.0	517.0	518.0	517.0	516.0	518.0
177.5°	521.4	519.8	519.0	519.0	519.0	517.4	518.2	519.8	518.2	517.4	519.0
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1310.7	1308.3	1299.7	1295.2	1287.8	1280.9	1276.4	1278.5	1280.1	1279.3	1278.0
5°	1273.1	1263.4	1248.6	1235.9	1226.7	1209.8	1202.7	1199.1	1196.1	1192.5	1188.9
7.5°	1228.4	1213.1	1191.9	1173.7	1156.5	1135.6	1123.7	1116.5	1109.2	1101.1	1094.0
10°	1196.6	1175.1	1152.7	1127.1	1106.7	1087.8	1071.0	1059.8	1049.6	1039.9	1032.7
12.5°	1163.1	1138.4	1110.6	1075.7	1053.2	1026.2	1023.6	1003.8	987.9	981.9	973.5
15°	1109.8	1075.1	1039.9	998.5	980.6	956.1	940.8	925.5	911.7	902.0	899.5
17.5°	1049.2	1004.3	969.3	939.6	910.3	885.2	871.1	858.8	847.5	834.5	832.8
20°	1003.1	964.3	926.0	900.0	869.9	844.3	827.0	814.7	805.0	797.4	790.7
22.5°	959.4	916.9	881.9	853.4	823.7	803.1	789.4	777.6	769.5	761.0	754.8
25°	889.3	856.1	817.8	785.6	761.1	747.9	736.6	726.4	721.3	715.7	708.6
27.5°	827.9	791.0	755.2	730.3	708.8	697.0	689.0	682.1	677.3	674.0	670.0
30°	784.6	747.3	719.3	694.8	676.9	665.2	660.1	656.0	650.4	648.3	646.3
32.5°	743.0	709.4	685.4	664.1	647.1	639.4	634.7	631.1	626.7	624.6	620.5
35°	684.0	656.0	632.5	620.7	607.0	600.3	596.8	591.6	587.6	585.5	585.0
37.5°	628.6	604.2	588.8	573.7	567.9	563.8	558.9	555.4	554.2	553.9	553.4
40°	592.7	572.8	559.0	546.7	544.2	538.0	534.0	530.9	530.9	531.4	530.9
42.5°	560.0	542.1	530.0	519.4	516.4	512.7	508.6	508.4	509.3	511.0	509.3
45°	510.5	497.7	489.0	483.9	478.3	474.7	474.2	475.8	476.3	476.8	478.3
47.5°	464.9	456.5	448.6	443.0	440.5	439.9	439.3	442.0	444.4	445.3	447.7
50°	438.0	428.3	421.7	418.1	416.0	415.0	416.0	419.1	421.1	423.7	425.2
52.5°	407.8	400.9	396.3	393.6	392.8	393.4	393.6	397.1	400.3	401.2	402.0
55°	366.0	360.9	359.9	355.3	357.3	356.8	359.4	361.4	364.5	367.5	368.1
57.5°	324.4	320.3	317.5	317.9	318.5	320.8	322.9	326.5	329.8	333.0	333.3
60°	296.6	294.5	293.0	293.0	294.0	297.1	299.7	303.2	305.3	307.3	308.8
62.5°	271.3	269.2	267.7	268.5	271.2	273.0	276.0	277.9	279.9	282.0	282.7
65°	231.2	230.2	231.8	232.8	233.3	235.8	239.4	240.9	243.0	244.0	247.6
67.5°	194.4	194.6	194.4	195.8	198.8	199.4	202.8	206.3	206.7	208.7	211.0
70°	169.5	170.5	171.5	172.5	175.1	176.1	178.7	180.2	182.2	183.8	185.3
72.5°	146.6	146.8	147.8	147.6	149.8	152.0	154.2	155.7	157.7	159.7	161.2
75°	112.8	112.8	113.8	114.3	116.9	119.5	118.9	120.0	122.0	124.0	125.1
77.5°	82.4	81.3	82.4	82.9	83.7	85.9	86.3	87.7	90.0	89.3	90.5
80°	62.8	61.3	62.8	63.3	63.3	65.9	65.9	66.9	68.4	66.9	68.4
82.5°	44.8	44.1	45.2	45.3	46.1	46.2	47.1	47.3	48.8	48.1	48.8
85°	22.5	22.0	22.5	22.0	22.5	23.0	23.0	22.5	22.5	23.5	22.0
87.5°	9.3	9.5	10.1	11.5	12.3	12.1	11.5	11.3	10.9	10.5	10.7
90°	12.0	15.0	20.0	26.9	32.9	33.9	32.9	31.9	29.9	31.9	32.9
92.5°	35.9	45.3	67.9	99.6	127.9	129.7	109.6	87.0	74.7	66.3	60.1
95°	73.9	97.8	143.7	230.5	346.3	391.2	342.3	261.5	200.6	158.7	136.7
97.5°	104.8	131.9	189.6	310.6	503.0	667.9	700.6	610.2	499.2	391.2	319.2
100°	124.8	152.7	205.6	327.4	542.9	788.4	932.2	911.2	787.4	650.7	530.0
102.5°	143.1	171.1	220.0	328.2	527.8	792.4	1018.4	1108.4	1080.5	980.5	852.5
105°	169.7	197.6	244.5	333.3	498.0	739.5	1005.0	1212.6	1325.4	1338.4	1305.4
107.5°	196.0	224.2	269.7	347.1	483.2	682.9	917.4	1137.6	1307.4	1411.2	1459.5
110°	213.6	242.5	286.4	358.3	480.1	655.7	862.3	1072.9	1251.5	1379.3	1461.1



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	230.3	260.1	302.4	370.3	480.8	638.1	824.0	1013.8	1185.3	1321.8	1415.6
115°	257.5	284.4	327.4	388.2	485.0	618.8	776.5	941.1	1094.8	1225.6	1328.4
117.5°	282.6	310.6	350.3	407.4	492.2	609.4	746.5	886.4	1021.4	1139.9	1236.4
120°	299.4	327.4	366.3	420.2	497.0	603.8	730.6	859.3	983.1	1088.8	1179.7
122.5°	316.2	344.9	381.4	431.3	502.6	600.6	717.0	837.7	951.1	1051.3	1133.4
125°	340.3	368.3	404.2	449.1	511.0	594.8	697.6	806.4	909.2	997.0	1071.9
127.5°	361.7	390.4	425.4	465.7	519.6	591.4	679.7	775.5	868.5	951.3	1020.4
130°	375.3	403.2	438.1	476.1	526.0	589.8	667.7	755.5	841.3	920.2	986.1
132.5°	388.0	416.0	449.3	486.4	532.3	589.0	658.1	736.3	815.8	888.2	950.1
135°	405.2	433.1	465.1	500.0	539.9	587.8	644.7	709.6	775.5	841.3	897.2
137.5°	420.4	446.3	477.9	510.4	546.7	587.6	635.3	688.2	743.3	795.6	844.3
140°	429.2	455.1	485.0	516.0	549.9	586.8	629.8	674.7	722.6	768.5	812.4
142.5°	437.1	461.5	490.6	520.8	552.3	586.8	624.2	663.5	704.2	743.7	780.5
145°	450.1	472.1	499.0	527.0	554.9	584.8	616.8	647.7	680.7	711.6	740.5
147.5°	460.9	480.5	505.8	530.4	555.7	581.3	609.2	635.5	661.5	685.6	706.8
150°	468.1	486.0	509.0	531.9	554.9	578.9	602.8	626.8	648.7	669.7	687.6
152.5°	475.3	491.6	512.2	532.7	553.3	574.9	597.2	618.0	638.3	656.1	671.7
155°	485.0	500.0	517.0	533.9	550.9	567.9	586.8	605.8	621.8	636.7	647.7
157.5°	493.4	506.0	520.4	533.9	546.3	560.7	577.1	591.6	605.0	617.6	626.2
160°	499.0	510.0	522.0	533.9	543.9	555.9	569.9	582.8	593.8	604.8	611.8
162.5°	503.8	512.4	522.8	533.1	541.5	551.9	563.5	574.1	583.4	592.8	598.2
165°	509.0	515.0	524.0	531.0	536.9	543.9	552.9	560.9	567.9	574.9	578.9
167.5°	513.4	517.2	523.8	529.6	532.3	536.9	542.5	548.3	553.7	558.5	562.1
170°	515.0	518.0	523.0	528.0	530.0	532.9	536.9	541.9	544.9	548.9	550.9
172.5°	516.6	518.8	522.2	525.6	526.8	528.2	531.4	534.7	536.9	540.1	541.3
175°	518.0	519.0	521.0	523.0	522.0	523.0	524.0	527.0	528.0	529.0	530.0
177.5°	519.0	519.0	519.8	521.4	519.8	519.0	519.8	521.4	521.4	522.2	522.2
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1274.0	1273.1	1273.1	1269.5	1273.1	1273.1	1274.0	1278.0	1279.3	1280.1	1278.5
5°	1181.8	1180.2	1177.7	1180.2	1177.7	1180.2	1181.8	1188.9	1192.5	1196.1	1199.1
7.5°	1090.6	1084.5	1083.6	1077.5	1083.6	1084.5	1090.6	1094.0	1101.1	1109.2	1116.5
10°	1024.0	1019.9	1019.4	1009.7	1019.4	1019.9	1024.0	1032.7	1039.9	1049.6	1059.8
12.5°	973.4	963.6	965.5	959.9	965.5	963.6	973.4	973.5	981.9	987.9	1003.8
15°	885.7	885.7	883.6	875.0	883.6	885.7	885.7	899.5	902.0	911.7	925.5
17.5°	822.7	821.7	816.8	819.2	816.8	821.7	822.7	832.8	834.5	847.5	858.8
20°	785.1	782.1	775.9	775.9	775.9	782.1	785.1	790.7	797.4	805.0	814.7
22.5°	749.6	749.4	742.9	744.9	742.9	749.4	749.6	754.8	761.0	769.5	777.6
25°	708.0	704.0	700.9	702.4	700.9	704.0	708.0	708.6	715.7	721.3	726.4
27.5°	668.6	666.4	666.2	662.0	666.2	666.4	668.6	670.0	674.0	677.3	682.1
30°	645.8	640.7	641.7	639.1	641.7	640.7	645.8	646.3	648.3	650.4	656.0
32.5°	619.6	617.8	616.8	614.6	616.8	617.8	619.6	620.5	624.6	626.7	631.1
35°	584.0	584.5	582.0	583.0	582.0	584.5	584.0	585.0	585.5	587.6	591.6
37.5°	552.9	554.5	553.3	553.6	553.3	554.5	552.9	553.4	553.9	554.2	555.4
40°	532.4	532.4	532.4	534.0	532.4	532.4	532.4	530.9	531.4	530.9	530.9
42.5°	512.8	512.0	511.2	511.1	511.2	512.0	512.8	509.3	511.0	509.3	508.4
45°	479.3	480.9	481.4	478.8	481.4	480.9	479.3	478.3	476.8	476.3	475.8
47.5°	449.0	449.2	449.0	451.3	449.0	449.2	449.0	447.7	445.3	444.4	442.0
50°	427.8	426.8	427.8	426.8	427.8	426.8	427.8	425.2	423.7	421.1	419.1
52.5°	405.3	405.5	404.9	404.7	404.9	405.5	405.3	402.0	401.2	400.3	397.1
55°	370.1	371.1	370.6	370.6	370.6	371.1	370.1	368.1	367.5	364.5	361.4
57.5°	333.7	334.6	335.3	333.0	335.3	334.6	333.7	333.3	333.0	329.8	326.5
60°	308.3	310.9	310.4	309.4	310.4	310.9	308.3	308.8	307.3	305.3	303.2
62.5°	285.1	286.0	285.9	285.7	285.9	286.0	285.1	282.7	282.0	279.9	277.9
65°	249.1	250.1	248.6	250.1	248.6	250.1	249.1	247.6	244.0	243.0	240.9
67.5°	210.4	210.7	211.9	212.6	211.9	210.7	210.4	211.0	208.7	206.7	206.3
70°	186.3	185.8	187.3	188.9	187.3	185.8	186.3	185.3	183.8	182.2	180.2
72.5°	161.0	162.1	161.6	162.7	161.6	162.1	161.0	161.2	159.7	157.7	155.7
75°	124.0	125.6	125.1	126.6	125.1	125.6	124.0	125.1	124.0	122.0	120.0
77.5°	89.6	89.8	89.6	90.5	89.6	89.8	89.6	90.5	89.3	90.0	87.7
80°	68.4	67.4	66.4	68.4	66.4	67.4	68.4	68.4	66.9	68.4	66.9
82.5°	47.6	48.2	47.2	47.2	47.2	48.2	47.6	48.8	48.1	48.8	47.3
85°	22.0	21.4	20.4	20.4	20.4	21.4	22.0	22.0	23.5	22.5	22.5
87.5°	10.7	10.3	10.3	9.9	10.3	10.3	10.7	10.7	10.5	10.9	11.3
90°	32.9	32.9	32.9	32.9	32.9	32.9	32.9	32.9	31.9	29.9	31.9
92.5°	59.3	56.1	56.9	55.3	56.9	56.1	59.3	60.1	66.3	74.7	87.0
95°	123.8	115.8	112.8	113.8	112.8	115.8	123.8	136.7	158.7	200.6	261.5
97.5°	271.5	246.9	232.3	224.0	232.3	246.9	271.5	319.2	391.2	499.2	610.2
100°	447.1	404.2	375.3	357.3	375.3	404.2	447.1	530.0	650.7	787.4	911.2
102.5°	762.5	689.2	653.1	628.8	653.1	689.2	762.5	852.5	980.5	1080.5	1108.4
105°	1243.5	1181.7	1138.7	1124.8	1138.7	1181.7	1243.5	1305.4	1338.4	1325.4	1212.6
107.5°	1467.3	1463.9	1455.3	1436.8	1455.3	1463.9	1467.3	1459.5	1411.2	1307.4	1137.6
110°	1504.0	1523.0	1532.0	1531.0	1532.0	1523.0	1504.0	1461.1	1379.3	1251.5	1072.9



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1475.3	1507.0	1524.0	1529.4	1524.0	1507.0	1475.3	1415.6	1321.8	1185.3	1013.8
115°	1399.2	1445.1	1471.1	1480.1	1471.1	1445.1	1399.2	1328.4	1225.6	1094.8	941.1
117.5°	1308.6	1357.1	1384.5	1392.0	1384.5	1357.1	1308.6	1236.4	1139.9	1021.4	886.4
120°	1249.5	1296.4	1325.4	1335.4	1325.4	1296.4	1249.5	1179.7	1088.8	983.1	859.3
122.5°	1196.0	1242.1	1267.9	1276.3	1267.9	1242.1	1196.0	1133.4	1051.3	951.1	837.7
125°	1129.8	1167.7	1192.6	1200.6	1192.6	1167.7	1129.8	1071.9	997.0	909.2	806.4
127.5°	1070.9	1106.4	1128.0	1134.4	1128.0	1106.4	1070.9	1020.4	951.3	868.5	775.5
130°	1035.0	1068.9	1088.8	1096.8	1088.8	1068.9	1035.0	986.1	920.2	841.3	755.5
132.5°	998.2	1032.2	1050.5	1057.7	1050.5	1032.2	998.2	950.1	888.2	815.8	736.3
135°	940.1	973.1	991.0	995.0	991.0	973.1	940.1	897.2	841.3	775.5	709.6
137.5°	883.5	911.8	927.6	933.6	927.6	911.8	883.5	844.3	795.6	743.3	688.2
140°	844.3	870.3	885.3	891.2	885.3	870.3	844.3	812.4	768.5	722.6	674.7
142.5°	810.8	834.4	847.7	848.9	847.7	834.4	810.8	780.5	743.7	704.2	663.5
145°	764.5	781.5	791.4	794.4	791.4	781.5	764.5	740.5	711.6	680.7	647.7
147.5°	726.6	740.1	746.9	748.7	746.9	740.1	726.6	706.8	685.6	661.5	635.5
150°	702.6	714.6	720.6	721.6	720.6	714.6	702.6	687.6	669.7	648.7	626.8
152.5°	683.4	693.8	698.2	698.4	698.2	693.8	683.4	671.7	656.1	638.3	618.0
155°	658.7	665.7	669.7	667.7	669.7	665.7	658.7	647.7	636.7	621.8	605.8
157.5°	633.9	639.7	641.5	641.5	641.5	639.7	633.9	626.2	617.6	605.0	591.6
160°	618.8	623.8	624.8	624.8	624.8	623.8	618.8	611.8	604.8	593.8	582.8
162.5°	605.2	608.6	609.6	608.8	609.6	608.6	605.2	598.2	592.8	583.4	574.1
165°	582.8	586.8	586.8	585.8	586.8	586.8	582.8	578.9	574.9	567.9	560.9
167.5°	563.9	566.1	565.9	564.7	565.9	566.1	563.9	562.1	558.5	553.7	548.3
170°	551.9	554.9	553.9	551.9	553.9	554.9	551.9	550.9	548.9	544.9	541.9
172.5°	542.3	543.7	542.7	541.5	542.7	543.7	542.3	541.3	540.1	536.9	534.7
175°	530.0	531.0	530.0	528.0	530.0	531.0	530.0	530.0	529.0	528.0	527.0
177.5°	522.2	522.2	521.4	519.8	521.4	522.2	522.2	522.2	522.2	521.4	521.4
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1276.4	1280.9	1287.8	1295.2	1299.7	1308.3	1310.7	1314.8	1318.5	1327.1	1336.0
5°	1202.7	1209.8	1226.7	1235.9	1248.6	1263.4	1273.1	1283.4	1294.6	1314.0	1331.8
7.5°	1123.7	1135.6	1156.5	1173.7	1191.9	1213.1	1228.4	1248.6	1265.4	1292.7	1318.9
10°	1071.0	1087.8	1106.7	1127.1	1152.7	1175.1	1196.6	1222.1	1242.5	1275.2	1305.8
12.5°	1023.6	1026.2	1053.2	1075.7	1110.6	1138.4	1163.1	1196.0	1216.0	1254.8	1287.0
15°	940.8	956.1	980.6	998.5	1039.9	1075.1	1109.8	1144.0	1167.0	1214.9	1257.3
17.5°	871.1	885.2	910.3	939.6	969.3	1004.3	1049.2	1085.3	1116.5	1171.4	1221.5
20°	827.0	844.3	869.9	900.0	926.0	964.3	1003.1	1044.4	1078.1	1139.9	1198.6
22.5°	789.4	803.1	823.7	853.4	881.9	916.9	959.4	1004.4	1039.8	1106.4	1165.9
25°	736.6	747.9	761.1	785.6	817.8	856.1	889.3	938.8	990.3	1052.6	1124.6
27.5°	689.0	697.0	708.8	730.3	755.2	791.0	827.9	874.9	926.7	994.3	1070.3
30°	660.1	665.2	676.9	694.8	719.3	747.3	784.6	829.5	882.6	951.0	1026.6
32.5°	634.7	639.4	647.1	664.1	685.4	709.4	743.0	787.9	838.5	905.7	989.4
35°	596.8	600.3	607.0	620.7	632.5	656.0	684.0	724.9	772.4	836.7	923.5
37.5°	558.9	563.8	567.9	573.7	588.8	604.2	628.6	663.1	709.7	774.6	857.3
40°	534.0	538.0	544.2	546.7	559.0	572.8	592.7	624.3	671.3	730.5	811.2
42.5°	508.6	512.7	516.4	519.4	530.0	542.1	560.0	587.2	628.8	686.4	766.2
45°	474.2	474.7	478.3	483.9	489.0	497.7	510.5	534.0	566.1	620.2	692.7
47.5°	439.3	439.9	440.5	443.0	448.6	456.5	464.9	484.0	512.8	556.0	626.6
50°	416.0	415.0	416.0	418.1	421.7	428.3	438.0	451.8	475.3	515.6	580.4
52.5°	393.6	393.4	392.8	393.6	396.3	400.9	407.8	419.5	440.5	477.6	534.7
55°	359.4	356.8	357.3	355.3	359.9	360.9	366.0	375.7	394.1	419.6	473.2
57.5°	322.9	320.8	318.5	317.9	317.5	320.3	324.4	332.0	346.1	368.5	412.0
60°	299.7	297.1	294.0	293.0	293.0	294.5	296.6	302.2	315.5	335.4	371.1
62.5°	276.0	273.0	271.2	268.5	267.7	269.2	271.3	275.3	284.8	303.5	334.4
65°	239.4	235.8	233.3	232.8	231.8	230.2	231.2	235.3	243.0	257.8	282.3
67.5°	202.8	199.4	198.8	195.8	194.4	194.6	194.4	197.9	202.5	215.2	233.5
70°	178.7	176.1	175.1	172.5	171.5	170.5	169.5	172.5	177.1	187.9	203.7
72.5°	154.2	152.0	149.8	147.6	147.8	146.8	146.6	148.4	152.2	162.1	174.3
75°	118.9	119.5	116.9	114.3	113.8	112.8	112.8	114.3	115.9	123.5	133.2
77.5°	86.3	85.9	83.7	82.9	82.4	81.3	82.4	83.4	84.2	89.3	96.5
80°	65.9	65.9	63.3	63.3	62.8	61.3	62.8	61.8	63.8	68.9	74.0
82.5°	47.1	46.2	46.1	45.3	45.2	44.1	44.8	45.8	46.7	50.1	53.2
85°	23.0	23.0	22.5	22.0	22.5	22.0	22.5	23.0	23.5	25.0	27.6
87.5°	11.5	12.1	12.3	11.5	10.1	9.5	9.3	9.3	9.8	9.4	9.2
90°	32.9	33.9	32.9	26.9	20.0	15.0	12.0	10.0	8.0	4.0	1.0
92.5°	109.6	129.7	127.9	99.6	67.9	45.3	35.9	29.1	24.8	17.6	12.2
95°	342.3	391.2	346.3	230.5	143.7	97.8	73.9	57.9	48.9	38.9	34.9
97.5°	700.6	667.9	503.0	310.6	189.6	131.9	104.8	86.4	72.9	62.3	56.9
100°	932.2	788.4	542.9	327.4	205.6	152.7	124.8	104.8	88.8	79.8	76.8
102.5°	1018.4	792.4	527.8	328.2	220.0	171.1	143.1	122.4	106.4	97.4	95.2
105°	1005.0	739.5	498.0	333.3	244.5	197.6	169.7	147.7	132.7	125.8	121.8
107.5°	917.4	682.9	483.2	347.1	269.7	224.2	196.0	174.3	160.5	153.7	150.5
110°	862.3	655.7	480.1	358.3	286.4	242.5	213.6	192.6	179.6	173.7	169.7



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	824.0	638.1	480.8	370.3	302.4	260.1	230.3	210.2	198.0	191.2	187.2
115°	776.5	618.8	485.0	388.2	327.4	284.4	257.5	237.5	225.6	219.6	214.6
117.5°	746.5	609.4	492.2	407.4	350.3	310.6	282.6	263.5	252.9	246.9	242.9
120°	730.6	603.8	497.0	420.2	366.3	327.4	299.4	279.4	270.5	264.5	260.5
122.5°	717.0	600.6	502.6	431.3	381.4	344.9	316.2	296.2	286.4	280.4	277.3
125°	697.6	594.8	511.0	449.1	404.2	368.3	340.3	320.4	308.4	302.4	299.4
127.5°	679.7	591.4	519.6	465.7	425.4	390.4	361.7	342.5	329.3	321.0	317.0
130°	667.7	589.8	526.0	476.1	438.1	403.2	375.3	355.3	341.3	331.3	327.4
132.5°	658.1	589.0	532.3	486.4	449.3	416.0	388.0	367.3	352.5	341.7	336.9
135°	644.7	587.8	539.9	500.0	465.1	433.1	405.2	382.2	367.3	355.3	351.3
137.5°	635.3	587.6	546.7	510.4	477.9	446.3	420.4	397.6	381.6	369.7	364.9
140°	629.8	586.8	549.9	516.0	485.0	455.1	429.2	407.2	391.2	379.3	375.3
142.5°	624.2	586.8	552.3	520.8	490.6	461.5	437.1	416.0	400.0	388.8	385.6
145°	616.8	584.8	554.9	527.0	499.0	472.1	450.1	430.2	415.2	405.2	401.2
147.5°	609.2	581.3	555.7	530.4	505.8	480.5	460.9	444.3	430.5	421.0	418.0
150°	602.8	578.9	554.9	531.9	509.0	486.0	468.1	453.1	440.1	432.1	429.2
152.5°	597.2	574.9	553.3	532.7	512.2	491.6	475.3	461.1	449.7	441.7	440.3
155°	586.8	567.9	550.9	533.9	517.0	500.0	485.0	474.1	463.1	457.1	456.1
157.5°	577.1	560.7	546.3	533.9	520.4	506.0	493.4	484.6	475.1	470.3	469.3
160°	569.9	555.9	543.9	533.9	522.0	510.0	499.0	491.0	483.0	479.1	478.1
162.5°	563.5	551.9	541.5	533.1	522.8	512.4	503.8	496.6	490.2	486.2	486.8
165°	552.9	543.9	536.9	531.0	524.0	515.0	509.0	504.0	498.0	496.0	497.0
167.5°	542.5	536.9	532.3	529.6	523.8	517.2	513.4	509.8	506.0	504.2	505.4
170°	536.9	532.9	530.0	528.0	523.0	518.0	515.0	513.0	510.0	509.0	511.0
172.5°	531.4	528.2	526.8	525.6	522.2	518.8	516.6	515.4	512.4	513.0	514.2
175°	524.0	523.0	522.0	523.0	521.0	519.0	518.0	518.0	516.0	517.0	518.0
177.5°	519.8	519.0	519.8	521.4	519.8	519.0	519.0	519.0	517.4	518.2	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1335.2	1337.3	1343.8	1350.3	1357.7	1359.7	1363.0	1360.1	1359.3	1367.1	1372.8
5°	1339.0	1348.2	1366.1	1382.4	1396.2	1405.9	1416.1	1420.2	1427.8	1438.5	1451.8
7.5°	1334.7	1352.6	1380.7	1404.4	1430.4	1449.1	1463.7	1476.1	1491.2	1511.5	1533.7
10°	1329.8	1353.8	1388.0	1417.1	1448.7	1472.7	1492.7	1512.0	1534.5	1562.6	1591.7
12.5°	1320.8	1349.3	1392.1	1426.5	1467.1	1490.7	1517.6	1559.4	1583.5	1622.6	1663.6
15°	1302.8	1334.4	1394.1	1436.5	1482.4	1527.4	1576.9	1616.7	1656.5	1679.5	1737.2
17.5°	1275.9	1322.4	1388.5	1437.9	1496.3	1567.1	1622.7	1667.8	1713.8	1751.1	1780.0
20°	1254.3	1304.8	1380.3	1439.6	1509.0	1585.0	1648.9	1694.8	1734.6	1765.8	1783.6
22.5°	1226.9	1290.5	1364.0	1433.4	1522.1	1597.3	1664.4	1700.5	1733.8	1749.0	1755.9
25°	1183.8	1260.4	1343.6	1428.3	1528.4	1608.0	1669.3	1691.2	1700.9	1686.1	1661.6
27.5°	1137.4	1222.7	1320.0	1418.7	1524.5	1601.1	1645.0	1641.5	1625.1	1577.2	1538.9
30°	1102.6	1196.6	1301.2	1408.9	1515.1	1589.6	1615.2	1589.6	1552.4	1498.8	1444.2
32.5°	1066.3	1163.5	1281.2	1395.0	1498.0	1563.5	1569.0	1525.1	1467.4	1406.5	1338.4
35°	1011.3	1116.4	1243.5	1364.0	1461.5	1502.9	1478.4	1400.8	1332.4	1249.2	1156.2
37.5°	949.1	1065.2	1192.7	1318.6	1406.9	1417.7	1356.9	1275.2	1178.7	1080.9	971.6
40°	902.5	1025.6	1156.8	1283.9	1362.0	1350.7	1273.1	1183.3	1068.4	949.0	847.4
42.5°	860.9	983.9	1117.5	1242.2	1304.8	1274.0	1183.3	1073.0	949.6	837.1	744.1
45°	788.7	915.3	1052.1	1172.6	1208.3	1152.7	1032.7	910.2	788.7	694.8	621.3
47.5°	718.7	843.8	979.3	1085.2	1097.8	1023.0	891.9	765.8	661.4	584.9	533.0
50°	667.2	792.8	927.0	1021.5	1017.4	927.0	792.3	672.3	585.0	523.2	488.5
52.5°	621.1	739.7	868.6	954.5	932.9	834.3	705.7	599.2	527.4	479.1	447.7
55°	549.3	659.0	781.5	850.5	810.6	701.4	592.7	506.9	453.8	417.6	393.1
57.5°	478.0	580.9	685.8	728.3	684.3	583.4	492.7	430.5	390.6	363.8	347.8
60°	433.9	523.8	617.2	653.9	601.3	511.5	440.0	384.4	352.2	330.3	316.0
62.5°	389.8	470.3	558.4	578.4	530.3	454.3	391.0	344.8	318.3	298.8	285.4
65°	329.8	395.6	462.5	475.8	431.4	372.7	322.6	292.5	269.0	254.7	244.0
67.5°	270.5	323.3	370.7	381.4	342.5	301.8	265.7	239.4	223.5	211.6	202.6
70°	235.3	277.2	316.0	324.7	293.5	257.3	229.7	208.8	194.5	184.3	175.6
72.5°	198.2	233.1	265.3	271.2	245.7	218.1	195.4	179.0	166.3	159.8	151.5
75°	151.6	172.0	197.0	198.6	181.7	164.9	147.5	136.8	130.2	122.0	117.9
77.5°	107.0	123.0	137.3	140.1	130.1	118.6	108.9	100.5	94.8	91.1	87.3
80°	81.7	94.4	100.6	104.1	97.0	88.8	83.2	77.6	74.0	71.5	68.9
82.5°	58.4	66.3	72.0	74.7	70.9	66.0	60.3	57.2	54.4	52.3	51.4
85°	29.6	33.2	36.8	37.8	36.8	34.7	31.6	31.6	30.1	29.6	29.6
87.5°	11.0	13.4	13.8	15.5	15.2	16.2	17.6	18.4	18.2	17.6	17.0
90°	4.0	8.0	10.0	12.0	15.0	20.0	26.9	32.9	33.9	32.9	31.9
92.5°	17.6	24.8	29.1	35.9	45.3	67.9	99.6	127.9	129.7	109.6	87.0
95°	38.9	48.9	57.9	73.9	97.8	143.7	230.5	346.3	391.2	342.3	261.5
97.5°	62.3	72.9	86.4	104.8	131.9	189.6	310.6	503.0	667.9	700.6	610.2
100°	79.8	88.8	104.8	124.8	152.7	205.6	327.4	542.9	788.4	932.2	911.2
102.5°	97.4	106.4	122.4	143.1	171.1	220.0	328.2	527.8	792.4	1018.4	1108.4
105°	125.8	132.7	147.7	169.7	197.6	244.5	333.3	498.0	739.5	1005.0	1212.6
107.5°	153.7	160.5	174.3	196.0	224.2	269.7	347.1	483.2	682.9	917.4	1137.6
110°	173.7	179.6	192.6	213.6	242.5	286.4	358.3	480.1	655.7	862.3	1072.9





TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	191.2	198.0	210.2	230.3	260.1	302.4	370.3	480.8	638.1	824.0	1013.8
115°	219.6	225.6	237.5	257.5	284.4	327.4	388.2	485.0	618.8	776.5	941.1
117.5°	246.9	252.9	263.5	282.6	310.6	350.3	407.4	492.2	609.4	746.5	886.4
120°	264.5	270.5	279.4	299.4	327.4	366.3	420.2	497.0	603.8	730.6	859.3
122.5°	280.4	286.4	296.2	316.2	344.9	381.4	431.3	502.6	600.6	717.0	837.7
125°	302.4	308.4	320.4	340.3	368.3	404.2	449.1	511.0	594.8	697.6	806.4
127.5°	321.0	329.3	342.5	361.7	390.4	425.4	465.7	519.6	591.4	679.7	775.5
130°	331.3	341.3	355.3	375.3	403.2	438.1	476.1	526.0	589.8	667.7	755.5
132.5°	341.7	352.5	367.3	388.0	416.0	449.3	486.4	532.3	589.0	658.1	736.3
135°	355.3	367.3	382.2	405.2	433.1	465.1	500.0	539.9	587.8	644.7	709.6
137.5°	369.7	381.6	397.6	420.4	446.3	477.9	510.4	546.7	587.6	635.3	688.2
140°	379.3	391.2	407.2	429.2	455.1	485.0	516.0	549.9	586.8	629.8	674.7
142.5°	388.8	400.0	416.0	437.1	461.5	490.6	520.8	552.3	586.8	624.2	663.5
145°	405.2	415.2	430.2	450.1	472.1	499.0	527.0	554.9	584.8	616.8	647.7
147.5°	421.0	430.5	444.3	460.9	480.5	505.8	530.4	555.7	581.3	609.2	635.5
150°	432.1	440.1	453.1	468.1	486.0	509.0	531.9	554.9	578.9	602.8	626.8
152.5°	441.7	449.7	461.1	475.3	491.6	512.2	532.7	553.3	574.9	597.2	618.0
155°	457.1	463.1	474.1	485.0	500.0	517.0	533.9	550.9	567.9	586.8	605.8
157.5°	470.3	475.1	484.6	493.4	506.0	520.4	533.9	546.3	560.7	577.1	591.6
160°	479.1	483.0	491.0	499.0	510.0	522.0	533.9	543.9	555.9	569.9	582.8
162.5°	486.2	490.2	496.6	503.8	512.4	522.8	533.1	541.5	551.9	563.5	574.1
165°	496.0	498.0	504.0	509.0	515.0	524.0	531.0	536.9	543.9	552.9	560.9
167.5°	504.2	506.0	509.8	513.4	517.2	523.8	529.6	532.3	536.9	542.5	548.3
170°	509.0	510.0	513.0	515.0	518.0	523.0	528.0	530.0	532.9	536.9	541.9
172.5°	513.0	512.4	515.4	516.6	518.8	522.2	525.6	526.8	528.2	531.4	534.7
175°	517.0	516.0	518.0	518.0	519.0	521.0	523.0	522.0	523.0	524.0	527.0
177.5°	518.2	517.4	519.0	519.0	519.0	519.8	521.4	519.8	519.0	519.8	521.4
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0	519.0



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1377.7	1383.4	1383.4	1384.2	1390.8	1389.9	1389.5
5°	1466.1	1474.8	1475.8	1485.0	1491.1	1489.1	1483.5
7.5°	1549.5	1565.7	1577.9	1584.7	1592.8	1597.8	1595.6
10°	1615.7	1639.2	1653.5	1663.2	1674.9	1683.6	1680.5
12.5°	1675.7	1703.7	1723.3	1739.9	1741.5	1752.6	1745.0
15°	1769.3	1798.9	1802.0	1814.3	1824.0	1822.9	1823.4
17.5°	1800.3	1809.8	1811.7	1812.0	1812.1	1808.5	1800.8
20°	1789.2	1785.7	1777.0	1770.4	1758.6	1757.1	1746.9
22.5°	1737.0	1725.6	1703.9	1689.5	1671.2	1666.4	1663.6
25°	1634.1	1609.0	1574.3	1541.1	1532.0	1514.1	1519.2
27.5°	1492.9	1453.9	1416.3	1389.3	1364.9	1338.2	1345.8
30°	1393.6	1349.7	1296.6	1255.8	1229.8	1204.2	1199.6
32.5°	1275.2	1210.9	1151.6	1115.7	1075.8	1059.7	1042.0
35°	1071.0	1008.2	949.5	899.0	869.9	847.4	827.0
37.5°	887.3	815.0	767.7	726.7	705.7	692.8	696.1
40°	773.4	710.1	675.4	644.2	624.8	615.6	617.7
42.5°	681.1	633.7	605.1	583.8	570.1	565.0	563.8
45°	576.3	549.8	526.3	514.1	507.4	501.8	498.2
47.5°	504.9	483.2	470.0	462.7	456.9	451.2	451.1
50°	462.0	447.7	438.5	430.8	426.3	422.2	425.7
52.5°	429.3	416.2	407.1	400.2	398.5	394.8	394.7
55°	380.8	370.6	364.0	357.8	354.8	352.7	350.2
57.5°	336.7	327.0	320.9	317.0	311.2	309.1	308.3
60°	305.3	297.6	291.5	286.4	283.8	279.7	279.7
62.5°	276.3	268.6	262.9	259.0	254.8	253.2	253.6
65°	234.3	228.2	222.6	218.5	217.5	214.4	215.4
67.5°	195.7	191.6	185.7	183.5	181.5	179.9	178.7
70°	170.0	165.9	162.8	159.8	158.2	158.2	158.2
72.5°	148.3	143.4	141.6	137.7	138.6	137.0	135.4
75°	114.9	111.8	110.3	108.7	106.2	106.2	106.2
77.5°	84.5	83.6	81.8	80.1	79.5	79.0	79.2
80°	65.3	64.8	63.8	63.8	62.8	62.3	61.3
82.5°	50.2	48.9	48.3	47.9	47.7	47.6	47.4
85°	28.6	27.6	27.6	28.1	27.1	27.1	27.6
87.5°	17.0	17.4	17.2	17.2	17.6	17.2	17.2
90°	29.9	31.9	32.9	32.9	32.9	32.9	32.9
92.5°	74.7	66.3	60.1	59.3	56.1	56.9	55.3
95°	200.6	158.7	136.7	123.8	115.8	112.8	113.8
97.5°	499.2	391.2	319.2	271.5	246.9	232.3	224.0
100°	787.4	650.7	530.0	447.1	404.2	375.3	357.3
102.5°	1080.5	980.5	852.5	762.5	689.2	653.1	628.8
105°	1325.4	1338.4	1305.4	1243.5	1181.7	1138.7	1124.8
107.5°	1307.4	1411.2	1459.5	1467.3	1463.9	1455.3	1436.8
110°	1251.5	1379.3	1461.1	1504.0	1523.0	1532.0	1531.0



TEST NUMBER: P331359

CATALOG NUMBER: S122DIP-S675D925U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1185.3	1321.8	1415.6	1475.3	1507.0	1524.0	1529.4
115°	1094.8	1225.6	1328.4	1399.2	1445.1	1471.1	1480.1
117.5°	1021.4	1139.9	1236.4	1308.6	1357.1	1384.5	1392.0
120°	983.1	1088.8	1179.7	1249.5	1296.4	1325.4	1335.4
122.5°	951.1	1051.3	1133.4	1196.0	1242.1	1267.9	1276.3
125°	909.2	997.0	1071.9	1129.8	1167.7	1192.6	1200.6
127.5°	868.5	951.3	1020.4	1070.9	1106.4	1128.0	1134.4
130°	841.3	920.2	986.1	1035.0	1068.9	1088.8	1096.8
132.5°	815.8	888.2	950.1	998.2	1032.2	1050.5	1057.7
135°	775.5	841.3	897.2	940.1	973.1	991.0	995.0
137.5°	743.3	795.6	844.3	883.5	911.8	927.6	933.6
140°	722.6	768.5	812.4	844.3	870.3	885.3	891.2
142.5°	704.2	743.7	780.5	810.8	834.4	847.7	848.9
145°	680.7	711.6	740.5	764.5	781.5	791.4	794.4
147.5°	661.5	685.6	706.8	726.6	740.1	746.9	748.7
150°	648.7	669.7	687.6	702.6	714.6	720.6	721.6
152.5°	638.3	656.1	671.7	683.4	693.8	698.2	698.4
155°	621.8	636.7	647.7	658.7	665.7	669.7	667.7
157.5°	605.0	617.6	626.2	633.9	639.7	641.5	641.5
160°	593.8	604.8	611.8	618.8	623.8	624.8	624.8
162.5°	583.4	592.8	598.2	605.2	608.6	609.6	608.8
165°	567.9	574.9	578.9	582.8	586.8	586.8	585.8
167.5°	553.7	558.5	562.1	563.9	566.1	565.9	564.7
170°	544.9	548.9	550.9	551.9	554.9	553.9	551.9
172.5°	536.9	540.1	541.3	542.3	543.7	542.7	541.5
175°	528.0	529.0	530.0	530.0	531.0	530.0	528.0
177.5°	521.4	522.2	522.2	522.2	522.2	521.4	519.8
180°	519.0	519.0	519.0	519.0	519.0	519.0	519.0

(END OF REPORT)