

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931506

Luminaire Tested: DFN2DS-TR4F0-070DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931506
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-070DS927-RLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4712.4 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931506

CATALOG NUMBER: DFN2DS-TR4F0-070DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931506

CATALOG NUMBER: DFN2DS-TR4F0-070DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1820	1820	1820
5°	1827	1797	1807
10°	1813	1768	1753
15°	1792	1716	1666
20°	1764	1641	1558
25°	1734	1556	1454
30°	1693	1468	1320
35°	1653	1374	1203
40°	1613	1275	1067
45°	1566	1165	944
50°	1517	1053	823
55°	1467	933	707
60°	1410	807	587
65°	1345	678	534
70°	1267	559	491
75°	1171	509	459
80°	1034	455	418
85°	812	359	359

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1566 cd/sqm

TEST NUMBER: P931506

CATALOG NUMBER: DFN2DS-TR4F0-070DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.7	4.6
10°-20°	589.5	12.5
20°-30°	827.7	17.6
30°-40°	902.2	19.1
40°-50°	829.2	17.6
50°-60°	651.2	13.8
60°-70°	423.9	9.0
70°-80°	218.2	4.6
80°-90°	55.7	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1631.9	34.6
0°-40°	2534.1	53.8
0°-60°	4014.6	85.2
0°-90°	4712.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4712.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2291	2291	2291	2291	2291	
5°	2291	2281	2254	2273	2266	217
15°	2179	2156	2086	2047	2026	614
25°	1978	1912	1775	1690	1659	910
35°	1704	1599	1416	1286	1240	1067
45°	1394	1254	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	715	547	361	290	284	709
75°	382	236	166	151	149	403
85°	89	46	39	39	39	107
90°	0	0	0	0	0	

TEST NUMBER: P931506

CATALOG NUMBER: DFN2DS-TR4F0-070DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.3	2291.3	2291.3	2291.3	2291.3
2.5°	2301.6	2291.3	2268.4	2289.4	2285.2
5°	2291.3	2281.0	2254.0	2272.6	2266.5
7.5°	2272.6	2260.3	2231.3	2239.4	2229.1
10°	2247.8	2233.3	2191.9	2185.5	2173.2
12.5°	2216.7	2198.0	2142.0	2129.6	2106.7
15°	2179.3	2156.5	2086.0	2046.7	2026.0
17.5°	2135.8	2102.6	2015.5	1969.9	1936.7
20°	2086.0	2044.5	1940.9	1889.2	1843.4
22.5°	2032.2	1984.4	1864.1	1793.6	1762.7
25°	1978.3	1911.8	1775.0	1690.0	1658.8
27.5°	1914.0	1843.4	1692.0	1594.6	1546.9
30°	1845.6	1766.6	1600.7	1495.1	1439.1
32.5°	1779.1	1683.7	1513.8	1389.3	1337.4
35°	1704.5	1598.7	1416.4	1285.7	1240.0
37.5°	1632.0	1517.8	1325.1	1181.8	1130.2
40°	1555.2	1430.9	1229.6	1082.4	1028.5
42.5°	1476.4	1343.8	1134.3	980.7	929.1
45°	1393.5	1254.4	1036.9	889.5	839.8
47.5°	1314.7	1167.6	943.6	796.2	750.7
50°	1227.6	1080.4	852.3	709.1	665.8
52.5°	1142.5	986.9	765.2	628.3	588.9
55°	1059.5	897.8	673.8	549.6	510.2
57.5°	974.6	808.7	593.1	476.9	443.8
60°	887.5	721.6	508.0	402.4	369.2
62.5°	802.5	636.7	435.4	336.0	319.4
65°	715.4	547.4	360.8	290.4	284.0
67.5°	632.5	464.4	290.4	254.9	248.8
70°	545.4	383.6	240.5	219.8	211.4
72.5°	462.4	308.9	201.1	184.6	180.4
75°	381.5	236.3	165.8	151.4	149.4
77.5°	300.7	167.8	130.7	122.3	118.2
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.5	80.9	68.4	64.2	64.2
85°	89.1	45.5	39.4	39.4	39.4
87.5°	33.2	16.5	16.5	14.5	14.5
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931506

CATALOG NUMBER: DFN2DS-TR4F0-070DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.32	14.84	13.68	15.15	15.47	9.28	10.80	9.64	11.11	11.43
	3H	15.08	16.45	15.46	16.77	17.14	10.54	11.91	10.92	12.23	12.60
	4H	15.75	17.03	16.15	17.38	17.76	11.04	12.32	11.44	12.67	13.05
	6H	16.24	17.42	16.65	17.79	18.18	11.42	12.61	11.84	12.97	13.37
	8H	16.40	17.53	16.83	17.92	18.32	11.55	12.68	11.97	13.06	13.47
	12H	16.50	17.58	16.94	17.96	18.39	11.63	12.71	12.06	13.09	13.52
4H	2H	13.42	14.70	13.82	15.05	15.43	9.97	11.25	10.37	11.60	11.98
	3H	15.35	16.42	15.76	16.82	17.22	11.41	12.48	11.83	12.88	13.28
	4H	16.10	17.06	16.54	17.47	17.91	12.01	12.97	12.45	13.39	13.82
	6H	16.69	17.53	17.15	17.97	18.43	12.50	13.33	12.96	13.78	14.24
	8H	16.91	17.69	17.37	18.13	18.60	12.66	13.44	13.13	13.89	14.35
	12H	17.06	17.76	17.54	18.23	18.71	12.78	13.48	13.26	13.95	14.43
8H	4H	16.13	16.90	16.59	17.35	17.82	12.37	13.15	12.83	13.59	14.06
	6H	16.76	17.41	17.26	17.90	18.38	12.95	13.60	13.45	14.09	14.57
	8H	17.01	17.59	17.53	18.10	18.59	13.18	13.75	13.69	14.26	14.75
	12H	17.22	17.73	17.73	18.22	18.78	13.35	13.86	13.86	14.36	14.92
12H	4H	16.11	16.81	16.59	17.28	17.75	12.41	13.11	12.89	13.58	14.06
	6H	16.74	17.32	17.26	17.83	18.32	13.02	13.60	13.53	14.11	14.59
	8H	17.03	17.54	17.54	18.03	18.60	13.29	13.80	13.80	14.29	14.86

END OF REPORT