

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931523

Luminaire Tested: DFN2DS-TR4F0-080DS927-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931523
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-080DS927-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6272.6 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 81.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931523

CATALOG NUMBER: DFN2DS-TR4F0-080DS927-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931523

CATALOG NUMBER: DFN2DS-TR4F0-080DS927-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1959	1959	1959
5°	1966	1938	1949
10°	1955	1918	1928
15°	1930	1893	1891
20°	1896	1856	1854
25°	1862	1810	1810
30°	1818	1768	1753
35°	1777	1717	1692
40°	1726	1667	1635
45°	1675	1617	1577
50°	1620	1565	1509
55°	1563	1504	1448
60°	1499	1431	1379
65°	1431	1359	1297
70°	1344	1272	1212
75°	1222	1171	1142
80°	1085	1052	997
85°	885	844	757

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1675 cd/sqm

TEST NUMBER: P931523

CATALOG NUMBER: DFN2DS-TR4F0-080DS927-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.0	3.7
10°-20°	652.9	10.4
20°-30°	959.5	15.3
30°-40°	1114.4	17.8
40°-50°	1113.0	17.7
50°-60°	970.5	15.5
60°-70°	717.4	11.4
70°-80°	405.9	6.5
80°-90°	107.1	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1844.4	29.4
0°-40°	2958.8	47.2
0°-60°	5042.2	80.4
0°-90°	6272.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6272.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2465	2465	2465	2465	2465	
5°	2465	2456	2430	2449	2444	234
15°	2347	2333	2302	2312	2300	661
25°	2124	2105	2065	2070	2065	977
35°	1832	1809	1771	1757	1745	1144
45°	1491	1475	1439	1413	1404	1151
55°	1128	1114	1086	1057	1046	1009
65°	761	747	723	702	690	752
75°	398	394	382	368	372	425
85°	97	95	93	85	83	114
90°	0	0	0	0	0	

TEST NUMBER: P931523

CATALOG NUMBER: DFN2DS-TR4F0-080DS927-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2465.3	2465.3	2465.3	2465.3	2465.3
2.5°	2479.7	2467.9	2441.7	2465.3	2460.8
5°	2465.3	2456.1	2429.9	2448.8	2444.3
7.5°	2448.8	2434.7	2408.6	2427.6	2422.9
10°	2422.9	2406.3	2377.8	2396.7	2389.7
12.5°	2387.2	2373.1	2344.6	2356.4	2351.7
15°	2346.9	2332.8	2301.9	2311.5	2299.7
17.5°	2297.1	2283.0	2252.1	2263.9	2252.1
20°	2242.5	2228.5	2195.3	2202.3	2193.0
22.5°	2188.2	2166.8	2135.9	2135.9	2131.1
25°	2124.1	2105.2	2065.0	2069.5	2065.0
27.5°	2052.9	2036.3	2005.6	1998.5	1986.7
30°	1982.0	1962.8	1927.4	1920.4	1910.8
32.5°	1906.0	1891.9	1853.9	1839.6	1830.1
35°	1832.5	1808.9	1770.9	1756.6	1744.8
37.5°	1749.5	1728.1	1690.2	1673.6	1661.8
40°	1664.3	1645.1	1607.2	1586.1	1576.5
42.5°	1581.3	1562.1	1524.4	1500.5	1486.5
45°	1491.3	1474.6	1438.9	1413.0	1403.5
47.5°	1403.5	1386.9	1348.9	1322.7	1308.6
50°	1310.9	1299.1	1265.9	1232.7	1220.9
52.5°	1220.9	1204.2	1173.6	1147.4	1130.8
55°	1128.5	1114.2	1085.8	1057.4	1045.5
57.5°	1036.0	1024.2	993.2	964.8	955.2
60°	943.4	934.2	900.9	874.8	867.7
62.5°	853.4	836.8	813.1	789.5	780.0
65°	761.1	746.8	723.1	701.7	689.9
67.5°	666.2	654.2	633.0	616.5	606.9
70°	578.5	568.9	547.6	531.0	521.6
72.5°	488.4	478.9	467.0	450.5	443.4
75°	398.1	393.6	381.6	367.5	372.2
77.5°	317.7	308.1	303.3	296.3	289.2
80°	237.2	234.7	229.9	222.9	218.0
82.5°	161.3	161.3	159.0	149.4	149.4
85°	97.1	94.8	92.6	85.3	83.0
87.5°	42.8	38.0	33.2	26.1	23.7
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931523

CATALOG NUMBER: DFN2DS-TR4F0-080DS927-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.62	15.23	13.98	15.54	15.86	13.17	14.78	13.54	15.10	15.41
	3H	15.37	16.82	15.75	17.15	17.51	14.88	16.33	15.25	16.66	17.02
	4H	16.01	17.38	16.41	17.73	18.11	15.52	16.89	15.92	17.24	17.61
	6H	16.48	17.75	16.89	18.12	18.51	15.98	17.25	16.39	17.62	18.01
	8H	16.63	17.84	17.05	18.23	18.63	16.12	17.33	16.55	17.72	18.12
	12H	16.72	17.88	17.15	18.26	18.69	16.20	17.36	16.63	17.75	18.18
4H	2H	14.18	15.55	14.58	15.90	16.27	13.83	15.19	14.22	15.54	15.92
	3H	16.15	17.30	16.56	17.70	18.10	15.75	16.89	16.16	17.29	17.69
	4H	16.93	17.97	17.36	18.38	18.82	16.51	17.54	16.94	17.96	18.39
	6H	17.53	18.43	17.98	18.87	19.33	17.09	18.00	17.55	18.44	18.90
	8H	17.72	18.56	18.18	19.01	19.47	17.28	18.12	17.74	18.57	19.03
	12H	17.85	18.61	18.33	19.08	19.55	17.40	18.16	17.88	18.63	19.10
8H	4H	17.20	18.05	17.66	18.49	18.96	16.83	17.68	17.29	18.12	18.58
	6H	17.92	18.62	18.41	19.11	19.58	17.54	18.24	18.03	18.73	19.20
	8H	18.18	18.81	18.69	19.31	19.80	17.79	18.42	18.30	18.92	19.41
	12H	18.38	18.93	18.88	19.43	19.99	17.96	18.52	18.47	19.01	19.57
12H	4H	17.23	17.99	17.71	18.47	18.93	16.86	17.62	17.35	18.10	18.57
	6H	17.96	18.60	18.47	19.10	19.59	17.59	18.23	18.10	18.73	19.22
	8H	18.28	18.84	18.78	19.33	19.89	17.90	18.46	18.41	18.95	19.51

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7