

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331383

Luminaire Tested: **S122DIP-S865D330U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331383
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S865D330U835-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4791.2 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331383

CATALOG NUMBER: S122DIP-S865D330U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331383

CATALOG NUMBER: S122DIP-S865D330U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	113	113	113	113	107	107	107	107	96	96	96	87	87	87	78	78	78	73				
1	103	99	94	91	98	94	90	87	85	82	79	76	74	72	69	67	66	62				
2	94	86	80	74	89	82	76	71	74	70	66	67	63	60	60	58	55	52				
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	54	50	47	44				
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	41	38				
5	72	60	52	45	68	57	50	44	52	46	41	48	42	38	43	39	35	33				
6	67	54	46	39	63	52	44	38	47	41	36	43	38	34	39	35	31	29				
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25				
8	57	45	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25	23				
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	23	21				
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	28	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22281	22281	22281
5°	22366	22044	22174
10°	22233	21820	21930
15°	21959	21538	21514
20°	21569	21113	21089
25°	21180	20591	20591
30°	20681	20113	19939
35°	20217	19537	19249
40°	19633	18963	18598
45°	19057	18393	17938
50°	18432	17799	17166
55°	17779	17106	16473
60°	17053	16281	15684
65°	16275	15461	14751
70°	15286	14469	13780
75°	13905	13325	12994
80°	12338	11967	11353
85°	10078	9596	8596



TEST NUMBER: P331383

CATALOG NUMBER: S122DIP-S865D330U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.8	2.7
10°-20°	365.1	7.6
20°-30°	536.7	11.2
30°-40°	623.4	13.0
40°-50°	622.7	13.0
50°-60°	543.1	11.3
60°-70°	401.6	8.4
70°-80°	227.4	4.7
80°-90°	62.8	1.3
90°-100°	73.5	1.5
100°-110°	249.3	5.2
110°-120°	264.8	5.5
120°-130°	218.0	4.6
130°-140°	175.1	3.7
140°-150°	132.3	2.8
150°-160°	93.0	1.9
160°-170°	54.7	1.1
170°-180°	17.8	0.4
0°-30°	1031.6	21.5
0°-40°	1655.0	34.5
0°-60°	2820.8	58.9
0°-90°	3512.6	73.3
90°-120°	587.6	12.3
90°-150°	1113.0	23.2
90°-180°	1279.0	26.7
0°-180°	4791.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1380	1380	1380	1380	1380	
5°	1380	1374	1360	1370	1368	131
15°	1314	1305	1288	1293	1287	370
25°	1189	1178	1156	1158	1156	547
35°	1026	1012	991	983	977	640
45°	835	825	806	791	786	644
55°	632	623	608	592	585	565
65°	426	418	405	393	386	421
75°	223	220	214	206	208	238
85°	54	53	52	48	46	62
90°	0	5	12	12	12	3
95°	12	30	138	52	40	13
105°	43	65	262	468	398	46
115°	76	96	219	452	524	75
125°	106	125	211	366	425	94
135°	124	148	208	308	352	96
145°	142	163	207	257	281	89
155°	162	174	201	227	236	74
165°	176	181	193	204	207	50
175°	183	184	185	187	187	17
180°	184	184	184	184	184	



TEST NUMBER: P331383

CATALOG NUMBER: S122DIP-S865D330U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0
2.5°	1386.4	1385.2	1384.0	1382.9	1381.7	1379.8	1377.2	1374.6	1372.0	1369.4	1371.8
5°	1380.0	1378.8	1377.7	1376.5	1375.3	1373.1	1369.9	1366.6	1363.4	1360.1	1362.5
7.5°	1367.8	1366.0	1364.2	1362.3	1360.5	1357.9	1354.6	1351.3	1348.0	1344.7	1347.1
10°	1356.1	1354.1	1352.0	1349.9	1347.9	1345.1	1341.5	1338.0	1334.5	1330.9	1333.3
12.5°	1340.2	1338.4	1336.6	1334.7	1332.9	1330.2	1326.7	1323.1	1319.6	1316.1	1317.7
15°	1313.7	1311.9	1310.1	1308.4	1306.6	1303.8	1300.0	1296.1	1292.3	1288.5	1289.6
17.5°	1279.7	1277.9	1276.2	1274.4	1272.6	1269.8	1265.9	1262.0	1258.1	1254.2	1255.6
20°	1255.3	1253.5	1251.8	1250.0	1248.2	1245.3	1241.1	1237.0	1232.9	1228.8	1229.6
22.5°	1230.9	1228.4	1225.9	1223.4	1221.0	1217.8	1213.9	1210.0	1206.1	1202.2	1202.4
25°	1188.9	1186.6	1184.2	1181.9	1179.5	1175.8	1170.8	1165.8	1160.8	1155.8	1156.4
27.5°	1141.2	1139.1	1136.9	1134.8	1132.7	1129.6	1125.7	1121.7	1117.8	1113.8	1113.0
30°	1109.3	1107.0	1104.6	1102.3	1099.9	1096.5	1092.1	1087.7	1083.2	1078.8	1077.9
32.5°	1075.4	1073.5	1071.6	1069.7	1067.8	1064.5	1059.9	1055.2	1050.6	1045.9	1044.3
35°	1025.7	1022.8	1019.8	1016.9	1013.9	1010.1	1005.4	1000.7	995.9	991.2	989.5
37.5°	969.7	967.1	964.5	961.9	959.4	955.7	951.0	946.3	941.5	936.8	934.6
40°	931.5	929.2	926.8	924.4	922.1	918.5	913.8	909.1	904.4	899.7	897.0
42.5°	894.4	892.0	889.6	887.3	884.9	881.4	876.7	872.0	867.2	862.5	859.6
45°	834.6	832.6	830.5	828.5	826.4	823.1	818.7	814.3	809.9	805.5	802.2
47.5°	775.2	773.3	771.3	769.4	767.4	764.1	759.5	754.9	750.3	745.7	742.3
50°	733.8	732.3	730.9	729.4	727.9	725.1	721.0	716.8	712.7	708.6	704.5
52.5°	693.5	691.5	689.6	687.6	685.7	682.8	678.9	675.0	671.1	667.2	663.8
55°	631.6	629.9	628.1	626.3	624.5	621.9	618.4	614.8	611.3	607.7	604.2
57.5°	569.5	568.1	566.7	565.3	563.9	561.2	557.3	553.4	549.5	545.6	542.2
60°	528.1	526.9	525.8	524.6	523.4	520.8	516.6	512.5	508.4	504.2	501.0
62.5°	487.8	485.9	484.0	482.1	480.2	477.7	474.5	471.3	468.1	465.0	462.0
65°	426.0	424.2	422.4	420.6	418.9	416.5	413.6	410.6	407.7	404.7	402.1
67.5°	363.1	361.6	360.2	358.8	357.4	355.4	352.7	350.0	347.4	344.7	342.7
70°	323.8	322.6	321.4	320.2	319.1	317.1	314.5	311.8	309.2	306.5	304.5
72.5°	283.4	282.3	281.1	279.9	278.7	277.3	275.6	273.9	272.1	270.4	268.4
75°	222.9	222.3	221.7	221.2	220.6	219.5	218.1	216.6	215.1	213.6	211.9
77.5°	168.8	167.8	166.8	165.8	164.8	164.0	163.4	162.8	162.2	161.6	160.7
80°	132.7	132.4	132.1	131.8	131.5	131.1	130.5	129.9	129.3	128.7	127.8
82.5°	98.7	98.7	98.6	98.5	98.5	98.3	97.9	97.6	97.2	96.9	95.7
85°	54.4	54.1	53.8	53.5	53.2	52.9	52.6	52.3	52.0	51.8	50.9
87.5°	19.2	18.9	18.7	18.4	18.1	17.8	17.7	17.7	17.7	17.3	16.5
90°	0.4	1.4	2.8	3.5	4.2	5.3	7.1	9.5	11.7	12.0	11.7
92.5°	4.3	6.2	8.8	10.3	12.7	16.0	24.0	35.3	45.3	45.9	38.8
95°	12.4	13.8	17.3	20.5	26.1	34.6	50.9	81.6	122.6	138.5	121.2
97.5°	20.1	22.0	25.8	30.6	37.1	46.7	67.1	110.0	178.1	236.4	248.0
100°	27.2	28.3	31.4	37.1	44.2	54.1	72.8	115.9	192.2	279.1	330.0
102.5°	33.7	34.5	37.7	43.3	50.7	60.6	77.9	116.2	186.8	280.5	360.5
105°	43.1	44.5	47.0	52.3	60.1	70.0	86.6	118.0	176.3	261.8	355.8
107.5°	53.3	54.4	56.8	61.7	69.4	79.4	95.5	122.9	171.1	241.7	324.8
110°	60.1	61.5	63.6	68.2	75.6	85.9	101.4	126.8	170.0	232.1	305.3



TEST NUMBER: P331383

CATALOG NUMBER: S122DIP-S865D330U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	66.3	67.7	70.1	74.4	81.5	92.1	107.1	131.1	170.2	225.9	291.7
115°	76.0	77.7	79.9	84.1	91.2	100.7	115.9	137.4	171.7	219.1	274.9
117.5°	86.0	87.4	89.5	93.3	100.1	110.0	124.0	144.2	174.3	215.7	264.3
120°	92.2	93.6	95.8	98.9	106.0	115.9	129.7	148.8	176.0	213.8	258.6
122.5°	98.2	99.3	101.4	104.9	111.9	122.1	135.0	152.7	177.9	212.6	253.8
125°	106.0	107.1	109.2	113.4	120.5	130.4	143.1	159.0	180.9	210.6	247.0
127.5°	112.2	113.6	116.6	121.3	128.0	138.2	150.6	164.9	183.9	209.4	240.6
130°	115.9	117.3	120.8	125.8	132.9	142.7	155.1	168.5	186.2	208.8	236.4
132.5°	119.3	121.0	124.8	130.0	137.4	147.3	159.1	172.2	188.5	208.5	233.0
135°	124.4	125.8	130.0	135.3	143.5	153.3	164.7	177.0	191.2	208.1	228.2
137.5°	129.2	130.9	135.1	140.8	148.8	158.0	169.2	180.7	193.6	208.0	224.9
140°	132.9	134.3	138.5	144.2	151.9	161.1	171.7	182.7	194.7	207.8	222.9
142.5°	136.5	137.7	141.6	147.3	154.8	163.4	173.7	184.4	195.5	207.8	221.0
145°	142.0	143.5	147.0	152.3	159.4	167.1	176.7	186.6	196.4	207.0	218.4
147.5°	148.0	149.0	152.4	157.3	163.2	170.1	179.1	187.8	196.7	205.8	215.7
150°	151.9	153.0	155.8	160.4	165.7	172.1	180.2	188.3	196.4	204.9	213.4
152.5°	155.9	156.4	159.2	163.2	168.3	174.0	181.3	188.6	195.9	203.5	211.4
155°	161.5	161.8	163.9	167.8	171.7	177.0	183.0	189.0	195.0	201.0	207.8
157.5°	166.1	166.5	168.2	171.6	174.7	179.1	184.2	189.0	193.4	198.5	204.3
160°	169.2	169.6	171.0	173.8	176.7	180.6	184.8	189.0	192.6	196.8	201.7
162.5°	172.4	172.1	173.6	175.8	178.4	181.4	185.1	188.7	191.7	195.4	199.5
165°	176.0	175.6	176.3	178.4	180.2	182.3	185.5	188.0	190.1	192.6	195.7
167.5°	178.9	178.5	179.1	180.5	181.8	183.1	185.4	187.5	188.5	190.1	192.1
170°	180.9	180.2	180.6	181.6	182.3	183.4	185.1	186.9	187.6	188.7	190.1
172.5°	182.0	181.6	181.4	182.5	182.9	183.7	184.9	186.1	186.5	187.0	188.1
175°	183.4	183.0	182.7	183.4	183.4	183.7	184.4	185.1	184.8	185.1	185.5
177.5°	184.0	183.4	183.2	183.7	183.7	183.7	184.0	184.6	184.0	183.7	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331383

CATALOG NUMBER: S122DIP-S865D330U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0
2.5°	1374.1	1376.5	1378.8	1379.8	1379.3	1378.8	1378.4	1377.9
5°	1364.8	1367.2	1369.6	1370.4	1369.9	1369.3	1368.7	1368.1
7.5°	1349.4	1351.8	1354.2	1355.0	1354.4	1353.7	1353.1	1352.4
10°	1335.6	1338.0	1340.4	1341.1	1340.2	1339.3	1338.4	1337.6
12.5°	1319.4	1321.0	1322.7	1323.2	1322.5	1321.9	1321.2	1320.6
15°	1290.8	1292.0	1293.2	1293.0	1291.6	1290.1	1288.6	1287.1
17.5°	1256.9	1258.3	1259.7	1259.6	1258.2	1256.8	1255.4	1254.0
20°	1230.5	1231.4	1232.3	1232.1	1231.0	1229.8	1228.6	1227.4
22.5°	1202.6	1202.7	1202.9	1202.7	1201.9	1201.2	1200.5	1199.8
25°	1157.0	1157.5	1158.1	1158.1	1157.5	1157.0	1156.4	1155.8
27.5°	1112.1	1111.2	1110.3	1109.2	1107.7	1106.3	1104.9	1103.5
30°	1077.0	1076.2	1075.3	1074.2	1073.1	1071.9	1070.7	1069.5
32.5°	1042.7	1041.1	1039.5	1038.1	1037.0	1035.8	1034.6	1033.4
35°	987.7	985.9	984.2	982.5	981.1	979.6	978.1	976.6
37.5°	932.5	930.3	928.1	926.3	924.9	923.5	922.1	920.6
40°	894.4	891.7	889.1	887.1	886.0	884.8	883.6	882.4
42.5°	856.7	853.8	851.0	848.7	847.0	845.4	843.7	842.1
45°	799.0	795.7	792.5	790.3	789.1	787.9	786.7	785.6
47.5°	738.9	735.5	732.1	729.5	727.8	726.1	724.4	722.7
50°	700.3	696.2	692.1	689.3	687.8	686.3	684.9	683.4
52.5°	660.3	656.9	653.5	650.8	648.9	646.9	645.0	643.0
55°	600.7	597.1	593.6	591.1	589.6	588.1	586.7	585.2
57.5°	538.7	535.2	531.7	529.4	528.3	527.2	526.1	524.9
60°	497.8	494.5	491.3	489.2	488.3	487.4	486.5	485.7
62.5°	458.9	455.9	452.9	450.9	449.7	448.6	447.5	446.4
65°	399.4	396.8	394.1	392.0	390.6	389.1	387.6	386.1
67.5°	340.6	338.5	336.5	334.9	333.7	332.5	331.3	330.1
70°	302.4	300.3	298.3	296.6	295.5	294.3	293.1	291.9
72.5°	266.3	264.2	262.2	260.7	259.7	258.8	257.8	256.9
75°	210.1	208.3	206.6	206.0	206.6	207.2	207.7	208.3
77.5°	159.9	159.0	158.1	157.2	156.4	155.6	154.8	153.9
80°	126.9	126.1	125.2	124.4	123.8	123.3	122.7	122.1
82.5°	94.6	93.5	92.4	91.8	91.6	91.5	91.4	91.3
85°	50.0	49.1	48.2	47.6	47.3	47.0	46.7	46.4
87.5°	15.7	14.9	14.3	13.9	13.7	13.4	13.2	12.9
90°	11.3	10.6	11.3	11.7	11.7	11.7	11.7	11.7
92.5°	30.8	26.4	23.5	21.3	21.0	19.9	20.1	19.6
95°	92.6	71.0	56.2	48.4	43.8	41.0	39.9	40.3
97.5°	216.0	176.7	138.5	113.0	96.1	87.4	82.3	79.3
100°	322.6	278.8	230.4	187.6	158.3	143.1	132.9	126.5
102.5°	392.4	382.5	347.1	301.8	269.9	244.0	231.2	222.6
105°	429.3	469.2	473.8	462.2	440.2	418.3	403.1	398.2
107.5°	402.7	462.9	499.6	516.7	519.5	518.3	515.2	508.7
110°	379.8	443.1	488.3	517.3	532.5	539.2	542.4	542.0



TEST NUMBER: P331383

CATALOG NUMBER: S122DIP-S865D330U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	358.9	419.6	467.9	501.2	522.3	533.5	539.5	541.4
115°	333.2	387.6	433.9	470.3	495.4	511.6	520.8	524.0
117.5°	313.8	361.6	403.6	437.7	463.3	480.5	490.1	492.8
120°	304.2	348.0	385.5	417.6	442.4	459.0	469.2	472.8
122.5°	296.6	336.7	372.2	401.2	423.4	439.8	448.9	451.8
125°	285.5	321.9	353.0	379.5	400.0	413.4	422.2	425.1
127.5°	274.5	307.5	336.8	361.2	379.1	391.7	399.3	401.6
130°	267.5	297.9	325.8	349.1	366.4	378.4	385.5	388.3
132.5°	260.7	288.8	314.5	336.4	353.4	365.4	371.9	374.5
135°	251.2	274.5	297.9	317.6	332.8	344.5	350.9	352.3
137.5°	243.7	263.2	281.7	298.9	312.8	322.8	328.4	330.5
140°	238.8	255.8	272.1	287.6	298.9	308.1	313.4	315.5
142.5°	234.9	249.3	263.3	276.3	287.0	295.4	300.1	300.5
145°	229.3	241.0	251.9	262.2	270.6	276.7	280.2	281.2
147.5°	225.0	234.2	242.7	250.2	257.2	262.0	264.4	265.1
150°	221.9	229.7	237.1	243.4	248.7	253.0	255.1	255.5
152.5°	218.8	226.0	232.3	237.8	242.0	245.6	247.2	247.3
155°	214.5	220.1	225.4	229.3	233.2	235.7	237.1	236.4
157.5°	209.5	214.2	218.6	221.7	224.4	226.5	227.1	227.1
160°	206.3	210.2	214.1	216.6	219.1	220.8	221.2	221.2
162.5°	203.2	206.6	209.9	211.8	214.3	215.5	215.8	215.5
165°	198.6	201.0	203.5	204.9	206.3	207.8	207.8	207.4
167.5°	194.1	196.0	197.7	199.0	199.6	200.4	200.3	199.9
170°	191.9	192.9	194.3	195.0	195.4	196.4	196.1	195.4
172.5°	189.3	190.1	191.2	191.6	192.0	192.5	192.1	191.7
175°	186.6	186.9	187.3	187.6	187.6	188.0	187.6	186.9
177.5°	184.6	184.6	184.9	184.9	184.9	184.9	184.6	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7

(END OF REPORT)