

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331385

Luminaire Tested: **S122DIP-S865D530U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331385
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S865D530U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5701.3 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67																				
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	62	58																				
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49																				
3	86	77	69	64	81	73	66	61	65	60	56	58	54	51	51	48	46	42																				
4	79	68	60	54	74	65	58	52	58	53	48	52	48	44	46	43	40	37																				
5	73	61	53	47	68	58	51	46	52	47	42	47	42	39	42	38	35	33																				
6	67	55	47	41	63	53	45	40	48	42	37	43	38	34	39	35	32	29																				
7	62	50	42	37	59	48	41	36	43	37	33	39	34	31	35	31	28	26																				
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	23																				
9	54	42	35	30	51	40	33	29	37	31	27	33	29	25	30	26	23	21																				
10	51	39	32	27	48	37	31	26	34	28	24	31	26	23	28	24	21	19																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27876	27876	27876	27876
5°	31253	28058	24864	28058
10°	35813	27829	21518	27829
15°	39619	27318	19010	27318
20°	39015	26770	17330	26770
25°	35179	26042	16265	26042
30°	29071	24878	15489	24878
35°	21187	23660	14937	23660
40°	16923	22223	14629	22223
45°	14787	20559	14212	20559
50°	13901	18952	13933	18952
55°	12814	17315	13560	17315
60°	11741	15578	12984	15578
65°	10697	14017	12420	14017
70°	9711	12500	11589	12500
75°	8609	10805	10268	10805
80°	7401	8945	8266	8945
85°	6632	6632	4909	6632



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.4	2.9
10°-20°	478.0	8.4
20°-30°	693.8	12.2
30°-40°	732.1	12.8
40°-50°	648.2	11.4
50°-60°	517.3	9.1
60°-70°	351.6	6.2
70°-80°	180.3	3.2
80°-90°	46.2	0.8
90°-100°	42.8	0.8
100°-110°	133.0	2.3
110°-120°	227.3	4.0
120°-130°	298.9	5.2
130°-140°	335.5	5.9
140°-150°	329.0	5.8
150°-160°	275.9	4.8
160°-170°	183.0	3.2
170°-180°	64.0	1.1
0°-30°	1336.2	23.4
0°-40°	2068.3	36.3
0°-60°	3233.8	56.7
0°-90°	3811.8	66.9
90°-120°	403.1	7.1
90°-150°	1366.6	24.0
90°-180°	1889.0	33.1
0°-180°	5701.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1726	1726	1726	1726	1726	
5°	1928	1731	1534	1731	1928	193
15°	2370	1634	1137	1634	2370	654
25°	1975	1462	913	1462	1975	893
35°	1075	1200	758	1200	1075	699
45°	648	900	622	900	648	509
55°	455	615	482	615	455	408
65°	280	367	325	367	280	278
75°	138	173	165	173	138	147
85°	36	36	26	36	36	40
90°	19	1	19	1	19	10
95°	35	30	35	30	35	39
105°	127	123	127	123	127	133
115°	228	228	228	228	228	225
125°	333	332	333	332	333	297
135°	434	429	434	429	434	334
145°	527	521	527	521	527	329
155°	600	596	600	596	600	276
165°	649	648	649	648	649	183
175°	672	675	672	675	672	64
180°	676	676	676	676	676	



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1806.2	1806.7	1807.8	1799.3	1798.2	1798.2	1790.8	1784.4	1777.0	1766.9	1768.0
5°	1928.3	1935.6	1938.2	1930.3	1918.3	1917.0	1905.7	1887.1	1869.9	1855.9	1846.0
7.5°	2074.0	2076.9	2070.4	2059.9	2051.0	2035.1	2014.1	1993.6	1964.8	1938.4	1918.7
10°	2184.4	2188.4	2177.1	2161.8	2149.2	2130.6	2100.1	2068.9	2031.1	1994.6	1965.4
12.5°	2268.3	2278.1	2263.6	2261.6	2240.0	2214.5	2178.2	2162.4	2109.2	2058.3	2027.0
15°	2370.2	2369.5	2370.9	2358.2	2342.3	2338.3	2299.9	2258.1	2183.1	2153.2	2101.5
17.5°	2340.7	2350.8	2355.5	2355.3	2354.9	2352.4	2340.1	2313.7	2276.1	2227.7	2167.9
20°	2270.7	2283.9	2285.9	2301.2	2309.8	2321.1	2325.7	2318.4	2295.2	2254.7	2203.0
22.5°	2162.4	2166.1	2172.3	2196.1	2214.8	2243.1	2257.8	2282.3	2273.4	2253.7	2210.4
25°	1974.7	1968.1	1991.3	2003.2	2046.4	2091.5	2124.0	2159.8	2191.7	2210.9	2198.3
27.5°	1749.4	1739.4	1774.2	1805.9	1840.9	1889.8	1940.5	2000.3	2050.1	2112.3	2133.7
30°	1559.3	1565.3	1598.5	1632.3	1685.4	1754.4	1811.5	1877.2	1948.2	2017.8	2066.3
32.5°	1354.4	1377.4	1398.4	1450.2	1497.0	1573.9	1657.5	1739.7	1828.2	1907.4	1982.4
35°	1074.9	1101.5	1130.7	1168.5	1234.2	1310.5	1392.1	1502.9	1623.7	1731.9	1820.8
37.5°	904.8	900.6	917.3	944.6	997.8	1059.4	1153.4	1262.9	1405.0	1532.1	1657.5
40°	802.9	800.2	812.2	837.4	877.9	923.0	1005.3	1101.5	1233.5	1388.8	1538.1
42.5°	732.8	734.4	741.0	758.8	786.6	823.7	885.3	967.2	1088.1	1234.3	1394.8
45°	647.6	652.3	659.6	668.2	684.1	714.6	749.1	807.5	903.1	1025.2	1183.1
47.5°	586.3	586.4	593.9	601.4	610.9	628.1	656.2	692.9	760.3	859.7	995.5
50°	553.4	548.8	554.1	560.0	570.0	581.9	600.5	635.0	680.1	760.4	873.9
52.5°	513.1	513.2	518.0	520.2	529.1	541.1	558.0	581.9	622.8	685.6	778.9
55°	455.2	458.5	461.2	465.1	473.1	481.7	495.0	510.9	542.8	589.9	658.9
57.5°	400.8	401.8	404.5	412.1	417.1	425.1	437.7	452.1	472.8	507.7	559.6
60°	363.6	363.6	368.9	372.2	378.9	386.8	396.8	410.7	429.3	457.8	499.7
62.5°	329.7	329.1	331.2	336.7	341.7	349.2	359.1	370.9	388.4	413.8	448.2
65°	280.0	278.7	282.7	284.0	289.3	296.6	304.6	317.2	331.1	349.7	380.2
67.5°	232.2	233.8	236.0	238.5	241.4	249.1	254.4	263.3	275.1	290.5	311.2
70°	205.7	205.7	205.7	207.7	211.7	215.7	221.0	228.3	239.5	252.8	271.4
72.5°	176.0	178.1	180.2	179.0	184.1	186.5	192.8	196.9	207.7	216.2	232.6
75°	138.0	138.0	138.0	141.3	143.3	145.3	149.3	153.3	158.6	169.2	177.8
77.5°	103.0	102.7	103.4	104.2	106.3	108.7	109.9	113.5	118.4	123.3	130.6
80°	79.6	81.0	81.6	82.9	82.9	84.3	84.9	89.6	92.9	96.2	100.9
82.5°	61.6	61.8	62.0	62.2	62.8	63.6	65.3	66.8	67.9	70.7	74.3
85°	35.8	35.2	35.2	36.5	35.8	35.8	37.2	38.5	38.5	39.1	41.1
87.5°	17.7	17.7	18.2	17.6	17.6	18.1	18.2	17.7	18.3	18.9	18.8
90°	19.4	19.3	19.1	19.0	18.9	18.9	19.2	19.5	19.7	20.0	17.2
92.5°	18.5	18.5	18.4	18.4	18.4	18.3	18.3	18.2	18.2	18.1	17.5
95°	35.4	35.6	35.9	36.1	36.4	36.5	36.5	36.5	36.5	36.5	36.2
97.5°	61.2	61.3	61.3	61.3	61.3	61.4	61.4	61.4	61.4	61.4	60.9
100°	78.1	78.3	78.4	78.5	78.6	78.7	78.7	78.7	78.7	78.7	78.3
102.5°	97.3	97.4	97.5	97.7	97.8	97.8	97.7	97.6	97.5	97.4	96.9
105°	126.6	126.6	126.6	126.6	126.6	126.5	126.2	126.0	125.7	125.5	125.2
107.5°	154.2	154.8	155.4	155.9	156.5	156.8	156.7	156.6	156.5	156.4	156.4
110°	175.6	176.0	176.4	176.8	177.2	177.3	177.3	177.3	177.3	177.3	177.3



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	196.2	196.4	196.7	197.0	197.3	197.6	197.9	198.2	198.5	198.8	198.9
115°	228.1	228.5	228.9	229.2	229.6	229.9	230.0	230.1	230.3	230.4	230.6
117.5°	258.5	258.9	259.3	259.7	260.1	260.4	260.7	261.0	261.3	261.6	262.3
120°	280.0	280.4	280.8	281.1	281.5	281.7	281.7	281.7	281.7	281.7	282.7
122.5°	301.0	301.3	301.5	301.8	302.1	302.4	302.7	303.0	303.3	303.6	304.3
125°	333.0	333.1	333.3	333.4	333.5	333.8	334.2	334.5	334.9	335.3	335.7
127.5°	362.2	362.6	363.0	363.4	363.8	364.3	364.7	365.2	365.6	366.1	366.6
130°	383.2	383.7	384.2	384.7	385.2	385.6	385.9	386.1	386.4	386.6	386.9
132.5°	403.3	403.7	404.1	404.5	404.9	405.4	405.9	406.5	407.1	407.6	407.6
135°	434.5	434.9	435.3	435.7	436.0	436.3	436.4	436.6	436.7	436.8	436.6
137.5°	462.8	463.3	463.8	464.3	464.8	465.1	465.2	465.3	465.4	465.5	465.2
140°	482.4	482.9	483.4	483.9	484.5	484.7	484.7	484.7	484.7	484.7	484.1
142.5°	500.2	500.7	501.2	501.7	502.2	502.4	502.3	502.2	502.1	502.0	501.6
145°	526.9	527.4	527.9	528.4	528.9	529.1	529.0	528.9	528.7	528.6	527.9
147.5°	550.7	551.2	551.7	552.2	552.7	552.8	552.5	552.2	551.9	551.7	551.1
150°	566.3	566.6	567.0	567.4	567.8	567.8	567.4	567.0	566.6	566.3	565.7
152.5°	580.9	581.3	581.8	582.3	582.8	582.8	582.3	581.8	581.3	580.9	580.2
155°	600.5	600.8	601.2	601.6	602.0	601.9	601.2	600.6	600.0	599.3	598.9
157.5°	617.3	618.0	618.6	619.2	619.8	619.7	618.8	617.9	617.1	616.2	616.0
160°	627.8	628.3	628.9	629.4	629.9	629.7	629.0	628.2	627.5	626.7	626.6
162.5°	637.0	637.6	638.2	638.8	639.4	639.3	638.4	637.5	636.7	635.8	635.7
165°	648.9	649.6	650.2	650.8	651.5	651.3	650.5	649.6	648.7	647.8	647.8
167.5°	658.7	659.4	660.1	660.7	661.4	661.3	660.4	659.5	658.6	657.7	657.7
170°	663.8	664.5	665.3	666.0	666.8	666.7	665.9	665.0	664.1	663.2	663.3
172.5°	667.9	668.6	669.4	670.2	670.9	670.8	670.0	669.1	668.2	667.3	667.4
175°	672.3	673.1	673.8	674.6	675.4	675.3	674.4	673.5	672.6	671.7	672.0
177.5°	674.4	675.0	675.6	676.2	676.8	676.8	676.2	675.6	675.0	674.4	674.6
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1771.7	1767.4	1764.8	1755.2	1746.7	1738.2	1735.6	1736.6	1725.0	1713.8	1709.0
5°	1840.7	1827.4	1814.8	1796.9	1775.7	1752.4	1740.5	1731.2	1708.0	1682.8	1668.2
7.5°	1902.5	1883.5	1859.3	1825.6	1794.6	1758.1	1734.9	1714.3	1680.4	1644.8	1623.0
10°	1940.2	1914.3	1883.1	1842.0	1804.2	1759.7	1728.5	1697.4	1657.5	1615.1	1588.5
12.5°	1972.6	1937.7	1907.0	1854.2	1809.5	1753.9	1716.9	1672.9	1631.0	1580.6	1554.6
15°	2049.7	1985.3	1926.9	1867.2	1812.1	1734.5	1693.4	1634.3	1579.2	1516.9	1487.0
17.5°	2109.3	2037.0	1945.0	1869.1	1804.8	1718.9	1658.5	1587.7	1522.6	1451.3	1410.7
20°	2143.3	2060.3	1961.4	1871.2	1794.2	1696.0	1630.3	1558.0	1481.7	1401.4	1357.6
22.5°	2163.4	2076.2	1978.4	1863.2	1773.0	1677.4	1594.8	1515.5	1438.2	1351.5	1305.6
25°	2169.8	2090.2	1986.7	1856.6	1746.5	1638.3	1538.8	1461.8	1368.2	1287.3	1220.3
27.5°	2138.2	2081.1	1981.6	1844.1	1715.8	1589.3	1478.4	1391.2	1292.5	1204.6	1137.2
30°	2099.5	2066.3	1969.4	1831.4	1691.4	1555.4	1433.3	1334.4	1236.2	1147.3	1078.3
32.5°	2039.5	2032.3	1947.1	1813.3	1665.4	1512.4	1386.0	1286.1	1177.3	1089.9	1024.1
35°	1921.6	1953.5	1899.7	1773.0	1616.4	1451.2	1314.5	1200.4	1087.6	1003.9	942.2
37.5°	1763.7	1842.8	1828.7	1713.9	1550.3	1384.6	1233.7	1114.4	1006.9	922.5	861.9
40°	1654.9	1755.7	1770.3	1668.8	1503.6	1333.1	1173.2	1054.4	949.5	872.6	811.5
42.5°	1538.1	1655.9	1696.0	1614.7	1452.6	1278.9	1119.0	996.0	892.2	817.4	763.2
45°	1342.4	1498.3	1570.6	1524.2	1367.6	1189.7	1025.2	900.4	806.2	735.9	694.1
47.5°	1159.3	1329.7	1427.0	1410.6	1272.9	1096.8	934.1	814.4	722.7	666.6	629.2
50°	1029.8	1205.0	1322.4	1327.8	1205.0	1030.5	867.3	754.5	670.2	617.8	587.2
52.5°	917.3	1084.5	1212.6	1240.7	1129.1	961.5	807.3	695.0	620.8	572.6	545.3
55°	770.4	911.7	1053.7	1105.5	1015.9	856.6	714.0	615.1	545.4	512.3	488.4
57.5°	640.5	758.3	889.4	946.6	891.4	755.1	621.3	535.5	478.9	449.9	431.6
60°	572.0	664.9	781.7	850.0	802.2	680.8	564.0	482.4	436.0	410.1	392.8
62.5°	508.3	590.6	689.3	751.8	725.8	611.3	506.7	434.6	394.5	370.3	357.8
65°	419.4	484.4	560.7	618.4	601.2	514.2	428.7	366.9	335.1	315.8	305.9
67.5°	345.3	392.3	445.2	495.8	481.9	420.3	351.5	303.5	279.8	263.2	257.2
70°	298.6	334.4	381.5	422.0	410.7	360.3	305.9	264.8	244.2	230.3	224.3
72.5°	254.0	283.5	319.4	352.5	344.9	303.0	257.6	226.5	210.7	197.9	193.0
75°	191.8	214.3	236.2	258.1	256.1	223.6	197.1	173.2	160.6	150.6	148.6
77.5°	141.6	154.2	169.1	182.1	178.5	159.9	139.1	125.4	116.1	109.5	108.4
80°	108.2	115.5	126.1	135.4	130.7	122.8	106.2	96.2	89.6	82.9	80.3
82.5°	78.4	85.7	92.1	97.1	93.6	86.1	75.9	69.1	65.2	60.6	59.6
85°	41.1	45.1	47.8	49.1	47.8	43.1	38.5	35.8	32.5	30.5	29.9
87.5°	18.8	18.2	17.7	18.3	16.4	16.1	13.7	11.8	11.6	11.3	10.6
90°	14.4	11.6	8.8	6.7	5.1	3.6	2.1	0.6	2.1	3.6	5.1
92.5°	16.8	16.2	15.5	14.6	13.5	12.4	11.3	10.2	11.3	12.4	13.5
95°	36.0	35.7	35.5	34.7	33.5	32.2	30.9	29.7	30.9	32.2	33.5
97.5°	60.4	59.9	59.4	58.6	57.5	56.4	55.3	54.2	55.3	56.4	57.5
100°	77.9	77.6	77.2	76.5	75.5	74.4	73.4	72.4	73.4	74.4	75.5
102.5°	96.4	96.0	95.5	94.8	94.0	93.2	92.4	91.6	92.4	93.2	94.0
105°	124.9	124.7	124.4	124.1	123.7	123.4	123.0	122.6	123.0	123.4	123.7
107.5°	156.4	156.4	156.4	156.1	155.5	155.0	154.4	153.9	154.4	155.0	155.5
110°	177.3	177.3	177.3	177.0	176.2	175.4	174.7	173.9	174.7	175.4	176.2



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	199.0	199.1	199.2	198.9	198.1	197.3	196.6	195.8	196.6	197.3	198.1
115°	230.9	231.1	231.4	231.1	230.4	229.6	228.9	228.1	228.9	229.6	230.4
117.5°	263.0	263.8	264.5	264.3	263.3	262.3	261.3	260.3	261.3	262.3	263.3
120°	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7	282.7	283.7	284.7
122.5°	305.0	305.7	306.4	306.2	305.0	303.8	302.5	301.3	302.5	303.8	305.0
125°	336.1	336.4	336.8	336.4	335.3	334.2	333.0	331.9	333.0	334.2	335.3
127.5°	367.0	367.5	367.9	367.4	366.0	364.5	363.1	361.6	363.1	364.5	366.0
130°	387.1	387.4	387.6	386.9	385.3	383.6	382.0	380.4	382.0	383.6	385.3
132.5°	407.5	407.5	407.4	406.7	405.4	404.0	402.7	401.3	402.7	404.0	405.4
135°	436.3	436.0	435.8	435.0	433.6	432.2	430.8	429.4	430.8	432.2	433.6
137.5°	464.9	464.6	464.2	463.5	462.4	461.2	460.1	458.9	460.1	461.2	462.4
140°	483.4	482.8	482.2	481.3	480.1	479.0	477.9	476.7	477.9	479.0	480.1
142.5°	501.2	500.8	500.3	499.5	498.4	497.3	496.1	495.0	496.1	497.3	498.4
145°	527.1	526.3	525.6	524.8	523.9	523.0	522.1	521.2	522.1	523.0	523.9
147.5°	550.6	550.1	549.6	548.8	547.8	546.7	545.6	544.6	545.6	546.7	547.8
150°	565.2	564.7	564.2	563.6	562.8	562.1	561.3	560.6	561.3	562.1	562.8
152.5°	579.6	579.0	578.4	577.7	577.0	576.2	575.5	574.7	575.5	576.2	577.0
155°	598.6	598.2	597.8	597.4	597.0	596.7	596.3	595.9	596.3	596.7	597.0
157.5°	615.8	615.5	615.3	615.1	614.8	614.5	614.3	614.0	614.3	614.5	614.8
160°	626.4	626.3	626.2	626.0	625.7	625.5	625.2	625.0	625.2	625.5	625.7
162.5°	635.6	635.4	635.3	635.2	635.2	635.1	635.1	635.0	635.1	635.1	635.2
165°	647.8	647.8	647.8	647.9	648.0	648.1	648.2	648.4	648.2	648.1	648.0
167.5°	657.8	657.8	657.8	658.0	658.4	658.8	659.2	659.5	659.2	658.8	658.4
170°	663.4	663.6	663.7	664.0	664.3	664.7	665.1	665.5	665.1	664.7	664.3
172.5°	667.6	667.7	667.8	668.1	668.4	668.8	669.2	669.6	669.2	668.8	668.4
175°	672.3	672.5	672.8	673.1	673.5	673.8	674.2	674.6	674.2	673.8	673.5
177.5°	674.8	675.0	675.2	675.4	675.7	676.0	676.3	676.7	676.3	676.0	675.7
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1703.7	1700.5	1689.4	1683.6	1674.0	1665.0	1659.1	1661.8	1663.9	1662.8	1661.3
5°	1654.9	1642.3	1623.0	1606.4	1594.5	1572.6	1563.3	1558.7	1554.7	1550.0	1545.4
7.5°	1596.8	1576.9	1549.2	1525.6	1503.3	1476.1	1460.6	1451.3	1441.8	1431.3	1422.0
10°	1555.4	1527.5	1498.3	1465.1	1438.6	1414.0	1392.1	1377.5	1364.3	1351.6	1342.4
12.5°	1511.8	1479.7	1443.6	1398.2	1369.0	1333.9	1330.5	1304.8	1284.1	1276.3	1265.4
15°	1442.6	1397.4	1351.6	1297.9	1274.7	1242.8	1222.9	1203.0	1185.1	1172.5	1169.2
17.5°	1363.9	1305.5	1259.9	1221.3	1183.2	1150.6	1132.3	1116.4	1101.6	1084.8	1082.5
20°	1303.9	1253.4	1203.7	1169.8	1130.7	1097.5	1074.9	1059.0	1046.4	1036.5	1027.8
22.5°	1247.1	1191.9	1146.3	1109.3	1070.7	1043.9	1026.1	1010.7	1000.2	989.2	981.1
25°	1155.9	1112.8	1063.0	1021.2	989.3	972.1	957.5	944.2	937.6	930.3	921.0
27.5°	1076.1	1028.2	981.7	949.3	921.3	906.0	895.7	886.6	880.4	876.1	870.8
30°	1019.9	971.4	934.9	903.1	879.9	864.6	858.0	852.7	845.4	842.7	840.1
32.5°	965.7	922.1	890.9	863.3	841.1	831.2	825.1	820.3	814.6	811.9	806.6
35°	889.2	852.7	822.1	806.9	789.0	780.3	775.7	769.1	763.7	761.1	760.4
37.5°	817.1	785.4	765.3	745.7	738.1	732.8	726.5	721.9	720.3	719.9	719.3
40°	770.4	744.5	726.6	710.7	707.3	699.4	694.1	690.1	690.1	690.8	690.1
42.5°	727.9	704.7	688.9	675.1	671.2	666.5	661.2	660.9	662.0	664.2	662.0
45°	663.5	647.0	635.7	629.0	621.7	617.1	616.4	618.4	619.1	619.8	621.7
47.5°	604.4	593.3	583.1	575.8	572.6	571.8	571.0	574.5	577.7	578.9	581.9
50°	569.3	556.7	548.1	543.4	540.8	539.5	540.8	544.8	547.4	550.7	552.7
52.5°	530.0	521.1	515.2	511.6	510.5	511.3	511.6	516.1	520.4	521.5	522.5
55°	475.8	469.1	467.8	461.8	464.5	463.8	467.1	469.8	473.8	477.8	478.4
57.5°	421.6	416.3	412.7	413.3	414.1	417.0	419.8	424.4	428.7	432.9	433.3
60°	385.5	382.9	380.9	380.9	382.2	386.2	389.5	394.1	396.8	399.5	401.4
62.5°	352.6	350.0	348.0	349.0	352.5	354.9	358.7	361.2	363.9	366.5	367.5
65°	300.6	299.3	301.3	302.6	303.2	306.6	311.2	313.2	315.8	317.2	321.8
67.5°	252.7	252.9	252.7	254.5	258.4	259.2	263.6	268.2	268.7	271.3	274.3
70°	220.3	221.6	223.0	224.3	227.6	228.9	232.2	234.2	236.9	238.9	240.9
72.5°	190.6	190.8	192.2	191.9	194.7	197.6	200.4	202.4	205.0	207.6	209.5
75°	146.6	146.6	148.0	148.6	152.0	155.3	154.6	155.9	158.6	161.2	162.6
77.5°	107.1	105.6	107.1	107.8	108.8	111.6	112.1	114.0	117.0	116.1	117.6
80°	81.6	79.6	81.6	82.3	82.3	85.6	85.6	86.9	88.9	86.9	88.9
82.5°	58.3	57.3	58.8	58.9	60.0	60.1	61.2	61.4	63.4	62.5	63.4
85°	29.2	28.5	29.2	28.5	29.2	29.9	29.9	29.2	29.2	30.5	28.5
87.5°	10.4	10.3	10.3	10.8	10.9	10.9	10.3	10.3	10.2	9.1	9.1
90°	6.7	8.8	11.6	14.4	17.2	20.0	19.7	19.5	19.2	18.9	18.9
92.5°	14.6	15.5	16.2	16.8	17.5	18.1	18.2	18.2	18.3	18.3	18.4
95°	34.7	35.5	35.7	36.0	36.2	36.5	36.5	36.5	36.5	36.5	36.4
97.5°	58.6	59.4	59.9	60.4	60.9	61.4	61.4	61.4	61.4	61.4	61.3
100°	76.5	77.2	77.6	77.9	78.3	78.7	78.7	78.7	78.7	78.7	78.6
102.5°	94.8	95.5	96.0	96.4	96.9	97.4	97.5	97.6	97.7	97.8	97.8
105°	124.1	124.4	124.7	124.9	125.2	125.5	125.7	126.0	126.2	126.5	126.6
107.5°	156.1	156.4	156.4	156.4	156.4	156.4	156.5	156.6	156.7	156.8	156.5
110°	177.0	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.2



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	198.9	199.2	199.1	199.0	198.9	198.8	198.5	198.2	197.9	197.6	197.3
115°	231.1	231.4	231.1	230.9	230.6	230.4	230.3	230.1	230.0	229.9	229.6
117.5°	264.3	264.5	263.8	263.0	262.3	261.6	261.3	261.0	260.7	260.4	260.1
120°	285.8	285.8	284.7	283.7	282.7	281.7	281.7	281.7	281.7	281.7	281.5
122.5°	306.2	306.4	305.7	305.0	304.3	303.6	303.3	303.0	302.7	302.4	302.1
125°	336.4	336.8	336.4	336.1	335.7	335.3	334.9	334.5	334.2	333.8	333.5
127.5°	367.4	367.9	367.5	367.0	366.6	366.1	365.6	365.2	364.7	364.3	363.8
130°	386.9	387.6	387.4	387.1	386.9	386.6	386.4	386.1	385.9	385.6	385.2
132.5°	406.7	407.4	407.5	407.5	407.6	407.6	407.1	406.5	405.9	405.4	404.9
135°	435.0	435.8	436.0	436.3	436.6	436.8	436.7	436.6	436.4	436.3	436.0
137.5°	463.5	464.2	464.6	464.9	465.2	465.5	465.4	465.3	465.2	465.1	464.8
140°	481.3	482.2	482.8	483.4	484.1	484.7	484.7	484.7	484.7	484.7	484.5
142.5°	499.5	500.3	500.8	501.2	501.6	502.0	502.1	502.2	502.3	502.4	502.2
145°	524.8	525.6	526.3	527.1	527.9	528.6	528.7	528.9	529.0	529.1	528.9
147.5°	548.8	549.6	550.1	550.6	551.1	551.7	551.9	552.2	552.5	552.8	552.7
150°	563.6	564.2	564.7	565.2	565.7	566.3	566.6	567.0	567.4	567.8	567.8
152.5°	577.7	578.4	579.0	579.6	580.2	580.9	581.3	581.8	582.3	582.8	582.8
155°	597.4	597.8	598.2	598.6	598.9	599.3	600.0	600.6	601.2	601.9	602.0
157.5°	615.1	615.3	615.5	615.8	616.0	616.2	617.1	617.9	618.8	619.7	619.8
160°	626.0	626.2	626.3	626.4	626.6	626.7	627.5	628.2	629.0	629.7	629.9
162.5°	635.2	635.3	635.4	635.6	635.7	635.8	636.7	637.5	638.4	639.3	639.4
165°	647.9	647.8	647.8	647.8	647.8	647.8	648.7	649.6	650.5	651.3	651.5
167.5°	658.0	657.8	657.8	657.8	657.7	657.7	658.6	659.5	660.4	661.3	661.4
170°	664.0	663.7	663.6	663.4	663.3	663.2	664.1	665.0	665.9	666.7	666.8
172.5°	668.1	667.8	667.7	667.6	667.4	667.3	668.2	669.1	670.0	670.8	670.9
175°	673.1	672.8	672.5	672.3	672.0	671.7	672.6	673.5	674.4	675.3	675.4
177.5°	675.4	675.2	675.0	674.8	674.6	674.4	675.0	675.6	676.2	676.8	676.8
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1655.9	1654.9	1654.9	1650.1	1654.9	1654.9	1655.9	1661.3	1662.8	1663.9	1661.8
5°	1536.1	1534.1	1530.8	1534.1	1530.8	1534.1	1536.1	1545.4	1550.0	1554.7	1558.7
7.5°	1417.6	1409.6	1408.4	1400.6	1408.4	1409.6	1417.6	1422.0	1431.3	1441.8	1451.3
10°	1331.1	1325.8	1325.1	1312.5	1325.1	1325.8	1331.1	1342.4	1351.6	1364.3	1377.5
12.5°	1265.3	1252.5	1255.0	1247.7	1255.0	1252.5	1265.3	1265.4	1276.3	1284.1	1304.8
15°	1151.3	1151.3	1148.6	1137.3	1148.6	1151.3	1151.3	1169.2	1172.5	1185.1	1203.0
17.5°	1069.4	1068.0	1061.7	1064.9	1061.7	1068.0	1069.4	1082.5	1084.8	1101.6	1116.4
20°	1020.5	1016.6	1008.6	1008.6	1008.6	1016.6	1020.5	1027.8	1036.5	1046.4	1059.0
22.5°	974.4	974.1	965.6	968.2	965.6	974.1	974.4	981.1	989.2	1000.2	1010.7
25°	920.3	915.0	911.1	913.0	911.1	915.0	920.3	921.0	930.3	937.6	944.2
27.5°	869.1	866.2	865.9	860.5	865.9	866.2	869.1	870.8	876.1	880.4	886.6
30°	839.4	832.8	834.1	830.8	834.1	832.8	839.4	840.1	842.7	845.4	852.7
32.5°	805.4	803.0	801.7	798.9	801.7	803.0	805.4	806.6	811.9	814.6	820.3
35°	759.1	759.8	756.4	757.8	756.4	759.8	759.1	760.4	761.1	763.7	769.1
37.5°	718.6	720.7	719.2	719.6	719.2	720.7	718.6	719.3	719.9	720.3	721.9
40°	692.1	692.1	692.1	694.1	692.1	692.1	692.1	690.1	690.8	690.1	690.1
42.5°	666.6	665.5	664.5	664.3	664.5	665.5	666.6	662.0	664.2	662.0	660.9
45°	623.1	625.1	625.7	622.4	625.7	625.1	623.1	621.7	619.8	619.1	618.4
47.5°	583.7	583.9	583.7	586.6	583.7	583.9	583.7	581.9	578.9	577.7	574.5
50°	556.1	554.7	556.1	554.7	556.1	554.7	556.1	552.7	550.7	547.4	544.8
52.5°	526.9	527.1	526.3	526.1	526.3	527.1	526.9	522.5	521.5	520.4	516.1
55°	481.1	482.4	481.7	481.7	481.7	482.4	481.1	478.4	477.8	473.8	469.8
57.5°	433.7	434.9	435.8	432.9	435.8	434.9	433.7	433.3	432.9	428.7	424.4
60°	400.8	404.1	403.4	402.1	403.4	404.1	400.8	401.4	399.5	396.8	394.1
62.5°	370.5	371.7	371.6	371.3	371.6	371.7	370.5	367.5	366.5	363.9	361.2
65°	323.8	325.1	323.1	325.1	323.1	325.1	323.8	321.8	317.2	315.8	313.2
67.5°	273.5	273.9	275.4	276.3	275.4	273.9	273.5	274.3	271.3	268.7	268.2
70°	242.2	241.5	243.5	245.5	243.5	241.5	242.2	240.9	238.9	236.9	234.2
72.5°	209.3	210.7	210.1	211.5	210.1	210.7	209.3	209.5	207.6	205.0	202.4
75°	161.2	163.2	162.6	164.6	162.6	163.2	161.2	162.6	161.2	158.6	155.9
77.5°	116.5	116.8	116.5	117.6	116.5	116.8	116.5	117.6	116.1	117.0	114.0
80°	88.9	87.6	86.3	88.9	86.3	87.6	88.9	88.9	86.9	88.9	86.9
82.5°	61.8	62.6	61.3	61.3	61.3	62.6	61.8	63.4	62.5	63.4	61.4
85°	28.5	27.9	26.5	26.5	26.5	27.9	28.5	28.5	30.5	29.2	29.2
87.5°	9.1	8.6	8.6	8.1	8.6	8.6	9.1	9.1	9.1	10.2	10.3
90°	19.0	19.1	19.3	19.4	19.3	19.1	19.0	18.9	18.9	19.2	19.5
92.5°	18.4	18.4	18.5	18.5	18.5	18.4	18.4	18.4	18.3	18.3	18.2
95°	36.1	35.9	35.6	35.4	35.6	35.9	36.1	36.4	36.5	36.5	36.5
97.5°	61.3	61.3	61.3	61.2	61.3	61.3	61.3	61.3	61.4	61.4	61.4
100°	78.5	78.4	78.3	78.1	78.3	78.4	78.5	78.6	78.7	78.7	78.7
102.5°	97.7	97.5	97.4	97.3	97.4	97.5	97.7	97.8	97.8	97.7	97.6
105°	126.6	126.6	126.6	126.6	126.6	126.6	126.6	126.6	126.5	126.2	126.0
107.5°	155.9	155.4	154.8	154.2	154.8	155.4	155.9	156.5	156.8	156.7	156.6
110°	176.8	176.4	176.0	175.6	176.0	176.4	176.8	177.2	177.3	177.3	177.3



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	197.0	196.7	196.4	196.2	196.4	196.7	197.0	197.3	197.6	197.9	198.2
115°	229.2	228.9	228.5	228.1	228.5	228.9	229.2	229.6	229.9	230.0	230.1
117.5°	259.7	259.3	258.9	258.5	258.9	259.3	259.7	260.1	260.4	260.7	261.0
120°	281.1	280.8	280.4	280.0	280.4	280.8	281.1	281.5	281.7	281.7	281.7
122.5°	301.8	301.5	301.3	301.0	301.3	301.5	301.8	302.1	302.4	302.7	303.0
125°	333.4	333.3	333.1	333.0	333.1	333.3	333.4	333.5	333.8	334.2	334.5
127.5°	363.4	363.0	362.6	362.2	362.6	363.0	363.4	363.8	364.3	364.7	365.2
130°	384.7	384.2	383.7	383.2	383.7	384.2	384.7	385.2	385.6	385.9	386.1
132.5°	404.5	404.1	403.7	403.3	403.7	404.1	404.5	404.9	405.4	405.9	406.5
135°	435.7	435.3	434.9	434.5	434.9	435.3	435.7	436.0	436.3	436.4	436.6
137.5°	464.3	463.8	463.3	462.8	463.3	463.8	464.3	464.8	465.1	465.2	465.3
140°	483.9	483.4	482.9	482.4	482.9	483.4	483.9	484.5	484.7	484.7	484.7
142.5°	501.7	501.2	500.7	500.2	500.7	501.2	501.7	502.2	502.4	502.3	502.2
145°	528.4	527.9	527.4	526.9	527.4	527.9	528.4	528.9	529.1	529.0	528.9
147.5°	552.2	551.7	551.2	550.7	551.2	551.7	552.2	552.7	552.8	552.5	552.2
150°	567.4	567.0	566.6	566.3	566.6	567.0	567.4	567.8	567.8	567.4	567.0
152.5°	582.3	581.8	581.3	580.9	581.3	581.8	582.3	582.8	582.8	582.3	581.8
155°	601.6	601.2	600.8	600.5	600.8	601.2	601.6	602.0	601.9	601.2	600.6
157.5°	619.2	618.6	618.0	617.3	618.0	618.6	619.2	619.8	619.7	618.8	617.9
160°	629.4	628.9	628.3	627.8	628.3	628.9	629.4	629.9	629.7	629.0	628.2
162.5°	638.8	638.2	637.6	637.0	637.6	638.2	638.8	639.4	639.3	638.4	637.5
165°	650.8	650.2	649.6	648.9	649.6	650.2	650.8	651.5	651.3	650.5	649.6
167.5°	660.7	660.1	659.4	658.7	659.4	660.1	660.7	661.4	661.3	660.4	659.5
170°	666.0	665.3	664.5	663.8	664.5	665.3	666.0	666.8	666.7	665.9	665.0
172.5°	670.2	669.4	668.6	667.9	668.6	669.4	670.2	670.9	670.8	670.0	669.1
175°	674.6	673.8	673.1	672.3	673.1	673.8	674.6	675.4	675.3	674.4	673.5
177.5°	676.2	675.6	675.0	674.4	675.0	675.6	676.2	676.8	676.8	676.2	675.6
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1659.1	1665.0	1674.0	1683.6	1689.4	1700.5	1703.7	1709.0	1713.8	1725.0	1736.6
5°	1563.3	1572.6	1594.5	1606.4	1623.0	1642.3	1654.9	1668.2	1682.8	1708.0	1731.2
7.5°	1460.6	1476.1	1503.3	1525.6	1549.2	1576.9	1596.8	1623.0	1644.8	1680.4	1714.3
10°	1392.1	1414.0	1438.6	1465.1	1498.3	1527.5	1555.4	1588.5	1615.1	1657.5	1697.4
12.5°	1330.5	1333.9	1369.0	1398.2	1443.6	1479.7	1511.8	1554.6	1580.6	1631.0	1672.9
15°	1222.9	1242.8	1274.7	1297.9	1351.6	1397.4	1442.6	1487.0	1516.9	1579.2	1634.3
17.5°	1132.3	1150.6	1183.2	1221.3	1259.9	1305.5	1363.9	1410.7	1451.3	1522.6	1587.7
20°	1074.9	1097.5	1130.7	1169.8	1203.7	1253.4	1303.9	1357.6	1401.4	1481.7	1558.0
22.5°	1026.1	1043.9	1070.7	1109.3	1146.3	1191.9	1247.1	1305.6	1351.5	1438.2	1515.5
25°	957.5	972.1	989.3	1021.2	1063.0	1112.8	1155.9	1220.3	1287.3	1368.2	1461.8
27.5°	895.7	906.0	921.3	949.3	981.7	1028.2	1076.1	1137.2	1204.6	1292.5	1391.2
30°	858.0	864.6	879.9	903.1	934.9	971.4	1019.9	1078.3	1147.3	1236.2	1334.4
32.5°	825.1	831.2	841.1	863.3	890.9	922.1	965.7	1024.1	1089.9	1177.3	1286.1
35°	775.7	780.3	789.0	806.9	822.1	852.7	889.2	942.2	1003.9	1087.6	1200.4
37.5°	726.5	732.8	738.1	745.7	765.3	785.4	817.1	861.9	922.5	1006.9	1114.4
40°	694.1	699.4	707.3	710.7	726.6	744.5	770.4	811.5	872.6	949.5	1054.4
42.5°	661.2	666.5	671.2	675.1	688.9	704.7	727.9	763.2	817.4	892.2	996.0
45°	616.4	617.1	621.7	629.0	635.7	647.0	663.5	694.1	735.9	806.2	900.4
47.5°	571.0	571.8	572.6	575.8	583.1	593.3	604.4	629.2	666.6	722.7	814.4
50°	540.8	539.5	540.8	543.4	548.1	556.7	569.3	587.2	617.8	670.2	754.5
52.5°	511.6	511.3	510.5	511.6	515.2	521.1	530.0	545.3	572.6	620.8	695.0
55°	467.1	463.8	464.5	461.8	467.8	469.1	475.8	488.4	512.3	545.4	615.1
57.5°	419.8	417.0	414.1	413.3	412.7	416.3	421.6	431.6	449.9	478.9	535.5
60°	389.5	386.2	382.2	380.9	380.9	382.9	385.5	392.8	410.1	436.0	482.4
62.5°	358.7	354.9	352.5	349.0	348.0	350.0	352.6	357.8	370.3	394.5	434.6
65°	311.2	306.6	303.2	302.6	301.3	299.3	300.6	305.9	315.8	335.1	366.9
67.5°	263.6	259.2	258.4	254.5	252.7	252.9	252.7	257.2	263.2	279.8	303.5
70°	232.2	228.9	227.6	224.3	223.0	221.6	220.3	224.3	230.3	244.2	264.8
72.5°	200.4	197.6	194.7	191.9	192.2	190.8	190.6	193.0	197.9	210.7	226.5
75°	154.6	155.3	152.0	148.6	148.0	146.6	146.6	148.6	150.6	160.6	173.2
77.5°	112.1	111.6	108.8	107.8	107.1	105.6	107.1	108.4	109.5	116.1	125.4
80°	85.6	85.6	82.3	82.3	81.6	79.6	81.6	80.3	82.9	89.6	96.2
82.5°	61.2	60.1	60.0	58.9	58.8	57.3	58.3	59.6	60.6	65.2	69.1
85°	29.9	29.9	29.2	28.5	29.2	28.5	29.2	29.9	30.5	32.5	35.8
87.5°	10.3	10.9	10.9	10.8	10.3	10.3	10.4	10.6	11.3	11.6	11.8
90°	19.7	20.0	17.2	14.4	11.6	8.8	6.7	5.1	3.6	2.1	0.6
92.5°	18.2	18.1	17.5	16.8	16.2	15.5	14.6	13.5	12.4	11.3	10.2
95°	36.5	36.5	36.2	36.0	35.7	35.5	34.7	33.5	32.2	30.9	29.7
97.5°	61.4	61.4	60.9	60.4	59.9	59.4	58.6	57.5	56.4	55.3	54.2
100°	78.7	78.7	78.3	77.9	77.6	77.2	76.5	75.5	74.4	73.4	72.4
102.5°	97.5	97.4	96.9	96.4	96.0	95.5	94.8	94.0	93.2	92.4	91.6
105°	125.7	125.5	125.2	124.9	124.7	124.4	124.1	123.7	123.4	123.0	122.6
107.5°	156.5	156.4	156.4	156.4	156.4	156.4	156.1	155.5	155.0	154.4	153.9
110°	177.3	177.3	177.3	177.3	177.3	177.3	177.0	176.2	175.4	174.7	173.9



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	198.5	198.8	198.9	199.0	199.1	199.2	198.9	198.1	197.3	196.6	195.8
115°	230.3	230.4	230.6	230.9	231.1	231.4	231.1	230.4	229.6	228.9	228.1
117.5°	261.3	261.6	262.3	263.0	263.8	264.5	264.3	263.3	262.3	261.3	260.3
120°	281.7	281.7	282.7	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7
122.5°	303.3	303.6	304.3	305.0	305.7	306.4	306.2	305.0	303.8	302.5	301.3
125°	334.9	335.3	335.7	336.1	336.4	336.8	336.4	335.3	334.2	333.0	331.9
127.5°	365.6	366.1	366.6	367.0	367.5	367.9	367.4	366.0	364.5	363.1	361.6
130°	386.4	386.6	386.9	387.1	387.4	387.6	386.9	385.3	383.6	382.0	380.4
132.5°	407.1	407.6	407.6	407.5	407.5	407.4	406.7	405.4	404.0	402.7	401.3
135°	436.7	436.8	436.6	436.3	436.0	435.8	435.0	433.6	432.2	430.8	429.4
137.5°	465.4	465.5	465.2	464.9	464.6	464.2	463.5	462.4	461.2	460.1	458.9
140°	484.7	484.7	484.1	483.4	482.8	482.2	481.3	480.1	479.0	477.9	476.7
142.5°	502.1	502.0	501.6	501.2	500.8	500.3	499.5	498.4	497.3	496.1	495.0
145°	528.7	528.6	527.9	527.1	526.3	525.6	524.8	523.9	523.0	522.1	521.2
147.5°	551.9	551.7	551.1	550.6	550.1	549.6	548.8	547.8	546.7	545.6	544.6
150°	566.6	566.3	565.7	565.2	564.7	564.2	563.6	562.8	562.1	561.3	560.6
152.5°	581.3	580.9	580.2	579.6	579.0	578.4	577.7	577.0	576.2	575.5	574.7
155°	600.0	599.3	598.9	598.6	598.2	597.8	597.4	597.0	596.7	596.3	595.9
157.5°	617.1	616.2	616.0	615.8	615.5	615.3	615.1	614.8	614.5	614.3	614.0
160°	627.5	626.7	626.6	626.4	626.3	626.2	626.0	625.7	625.5	625.2	625.0
162.5°	636.7	635.8	635.7	635.6	635.4	635.3	635.2	635.2	635.1	635.1	635.0
165°	648.7	647.8	647.8	647.8	647.8	647.8	647.9	648.0	648.1	648.2	648.4
167.5°	658.6	657.7	657.7	657.8	657.8	657.8	658.0	658.4	658.8	659.2	659.5
170°	664.1	663.2	663.3	663.4	663.6	663.7	664.0	664.3	664.7	665.1	665.5
172.5°	668.2	667.3	667.4	667.6	667.7	667.8	668.1	668.4	668.8	669.2	669.6
175°	672.6	671.7	672.0	672.3	672.5	672.8	673.1	673.5	673.8	674.2	674.6
177.5°	675.0	674.4	674.6	674.8	675.0	675.2	675.4	675.7	676.0	676.3	676.7
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1735.6	1738.2	1746.7	1755.2	1764.8	1767.4	1771.7	1768.0	1766.9	1777.0	1784.4
5°	1740.5	1752.4	1775.7	1796.9	1814.8	1827.4	1840.7	1846.0	1855.9	1869.9	1887.1
7.5°	1734.9	1758.1	1794.6	1825.6	1859.3	1883.5	1902.5	1918.7	1938.4	1964.8	1993.6
10°	1728.5	1759.7	1804.2	1842.0	1883.1	1914.3	1940.2	1965.4	1994.6	2031.1	2068.9
12.5°	1716.9	1753.9	1809.5	1854.2	1907.0	1937.7	1972.6	2027.0	2058.3	2109.2	2162.4
15°	1693.4	1734.5	1812.1	1867.2	1926.9	1985.3	2049.7	2101.5	2153.2	2183.1	2258.1
17.5°	1658.5	1718.9	1804.8	1869.1	1945.0	2037.0	2109.3	2167.9	2227.7	2276.1	2313.7
20°	1630.3	1696.0	1794.2	1871.2	1961.4	2060.3	2143.3	2203.0	2254.7	2295.2	2318.4
22.5°	1594.8	1677.4	1773.0	1863.2	1978.4	2076.2	2163.4	2210.4	2253.7	2273.4	2282.3
25°	1538.8	1638.3	1746.5	1856.6	1986.7	2090.2	2169.8	2198.3	2210.9	2191.7	2159.8
27.5°	1478.4	1589.3	1715.8	1844.1	1981.6	2081.1	2138.2	2133.7	2112.3	2050.1	2000.3
30°	1433.3	1555.4	1691.4	1831.4	1969.4	2066.3	2099.5	2066.3	2017.8	1948.2	1877.2
32.5°	1386.0	1512.4	1665.4	1813.3	1947.1	2032.3	2039.5	1982.4	1907.4	1828.2	1739.7
35°	1314.5	1451.2	1616.4	1773.0	1899.7	1953.5	1921.6	1820.8	1731.9	1623.7	1502.9
37.5°	1233.7	1384.6	1550.3	1713.9	1828.7	1842.8	1763.7	1657.5	1532.1	1405.0	1262.9
40°	1173.2	1333.1	1503.6	1668.8	1770.3	1755.7	1654.9	1538.1	1388.8	1233.5	1101.5
42.5°	1119.0	1278.9	1452.6	1614.7	1696.0	1655.9	1538.1	1394.8	1234.3	1088.1	967.2
45°	1025.2	1189.7	1367.6	1524.2	1570.6	1498.3	1342.4	1183.1	1025.2	903.1	807.5
47.5°	934.1	1096.8	1272.9	1410.6	1427.0	1329.7	1159.3	995.5	859.7	760.3	692.9
50°	867.3	1030.5	1205.0	1327.8	1322.4	1205.0	1029.8	873.9	760.4	680.1	635.0
52.5°	807.3	961.5	1129.1	1240.7	1212.6	1084.5	917.3	778.9	685.6	622.8	581.9
55°	714.0	856.6	1015.9	1105.5	1053.7	911.7	770.4	658.9	589.9	542.8	510.9
57.5°	621.3	755.1	891.4	946.6	889.4	758.3	640.5	559.6	507.7	472.8	452.1
60°	564.0	680.8	802.2	850.0	781.7	664.9	572.0	499.7	457.8	429.3	410.7
62.5°	506.7	611.3	725.8	751.8	689.3	590.6	508.3	448.2	413.8	388.4	370.9
65°	428.7	514.2	601.2	618.4	560.7	484.4	419.4	380.2	349.7	331.1	317.2
67.5°	351.5	420.3	481.9	495.8	445.2	392.3	345.3	311.2	290.5	275.1	263.3
70°	305.9	360.3	410.7	422.0	381.5	334.4	298.6	271.4	252.8	239.5	228.3
72.5°	257.6	303.0	344.9	352.5	319.4	283.5	254.0	232.6	216.2	207.7	196.9
75°	197.1	223.6	256.1	258.1	236.2	214.3	191.8	177.8	169.2	158.6	153.3
77.5°	139.1	159.9	178.5	182.1	169.1	154.2	141.6	130.6	123.3	118.4	113.5
80°	106.2	122.8	130.7	135.4	126.1	115.5	108.2	100.9	96.2	92.9	89.6
82.5°	75.9	86.1	93.6	97.1	92.1	85.7	78.4	74.3	70.7	67.9	66.8
85°	38.5	43.1	47.8	49.1	47.8	45.1	41.1	41.1	39.1	38.5	38.5
87.5°	13.7	16.1	16.4	18.3	17.7	18.2	18.8	18.8	18.9	18.3	17.7
90°	2.1	3.6	5.1	6.7	8.8	11.6	14.4	17.2	20.0	19.7	19.5
92.5°	11.3	12.4	13.5	14.6	15.5	16.2	16.8	17.5	18.1	18.2	18.2
95°	30.9	32.2	33.5	34.7	35.5	35.7	36.0	36.2	36.5	36.5	36.5
97.5°	55.3	56.4	57.5	58.6	59.4	59.9	60.4	60.9	61.4	61.4	61.4
100°	73.4	74.4	75.5	76.5	77.2	77.6	77.9	78.3	78.7	78.7	78.7
102.5°	92.4	93.2	94.0	94.8	95.5	96.0	96.4	96.9	97.4	97.5	97.6
105°	123.0	123.4	123.7	124.1	124.4	124.7	124.9	125.2	125.5	125.7	126.0
107.5°	154.4	155.0	155.5	156.1	156.4	156.4	156.4	156.4	156.4	156.5	156.6
110°	174.7	175.4	176.2	177.0	177.3	177.3	177.3	177.3	177.3	177.3	177.3



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	196.6	197.3	198.1	198.9	199.2	199.1	199.0	198.9	198.8	198.5	198.2
115°	228.9	229.6	230.4	231.1	231.4	231.1	230.9	230.6	230.4	230.3	230.1
117.5°	261.3	262.3	263.3	264.3	264.5	263.8	263.0	262.3	261.6	261.3	261.0
120°	282.7	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7	281.7	281.7
122.5°	302.5	303.8	305.0	306.2	306.4	305.7	305.0	304.3	303.6	303.3	303.0
125°	333.0	334.2	335.3	336.4	336.8	336.4	336.1	335.7	335.3	334.9	334.5
127.5°	363.1	364.5	366.0	367.4	367.9	367.5	367.0	366.6	366.1	365.6	365.2
130°	382.0	383.6	385.3	386.9	387.6	387.4	387.1	386.9	386.6	386.4	386.1
132.5°	402.7	404.0	405.4	406.7	407.4	407.5	407.5	407.6	407.6	407.1	406.5
135°	430.8	432.2	433.6	435.0	435.8	436.0	436.3	436.6	436.8	436.7	436.6
137.5°	460.1	461.2	462.4	463.5	464.2	464.6	464.9	465.2	465.5	465.4	465.3
140°	477.9	479.0	480.1	481.3	482.2	482.8	483.4	484.1	484.7	484.7	484.7
142.5°	496.1	497.3	498.4	499.5	500.3	500.8	501.2	501.6	502.0	502.1	502.2
145°	522.1	523.0	523.9	524.8	525.6	526.3	527.1	527.9	528.6	528.7	528.9
147.5°	545.6	546.7	547.8	548.8	549.6	550.1	550.6	551.1	551.7	551.9	552.2
150°	561.3	562.1	562.8	563.6	564.2	564.7	565.2	565.7	566.3	566.6	567.0
152.5°	575.5	576.2	577.0	577.7	578.4	579.0	579.6	580.2	580.9	581.3	581.8
155°	596.3	596.7	597.0	597.4	597.8	598.2	598.6	598.9	599.3	600.0	600.6
157.5°	614.3	614.5	614.8	615.1	615.3	615.5	615.8	616.0	616.2	617.1	617.9
160°	625.2	625.5	625.7	626.0	626.2	626.3	626.4	626.6	626.7	627.5	628.2
162.5°	635.1	635.1	635.2	635.2	635.3	635.4	635.6	635.7	635.8	636.7	637.5
165°	648.2	648.1	648.0	647.9	647.8	647.8	647.8	647.8	647.8	648.7	649.6
167.5°	659.2	658.8	658.4	658.0	657.8	657.8	657.8	657.7	657.7	658.6	659.5
170°	665.1	664.7	664.3	664.0	663.7	663.6	663.4	663.3	663.2	664.1	665.0
172.5°	669.2	668.8	668.4	668.1	667.8	667.7	667.6	667.4	667.3	668.2	669.1
175°	674.2	673.8	673.5	673.1	672.8	672.5	672.3	672.0	671.7	672.6	673.5
177.5°	676.3	676.0	675.7	675.4	675.2	675.0	674.8	674.6	674.4	675.0	675.6
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1790.8	1798.2	1798.2	1799.3	1807.8	1806.7	1806.2
5°	1905.7	1917.0	1918.3	1930.3	1938.2	1935.6	1928.3
7.5°	2014.1	2035.1	2051.0	2059.9	2070.4	2076.9	2074.0
10°	2100.1	2130.6	2149.2	2161.8	2177.1	2188.4	2184.4
12.5°	2178.2	2214.5	2240.0	2261.6	2263.6	2278.1	2268.3
15°	2299.9	2338.3	2342.3	2358.2	2370.9	2369.5	2370.2
17.5°	2340.1	2352.4	2354.9	2355.3	2355.5	2350.8	2340.7
20°	2325.7	2321.1	2309.8	2301.2	2285.9	2283.9	2270.7
22.5°	2257.8	2243.1	2214.8	2196.1	2172.3	2166.1	2162.4
25°	2124.0	2091.5	2046.4	2003.2	1991.3	1968.1	1974.7
27.5°	1940.5	1889.8	1840.9	1805.9	1774.2	1739.4	1749.4
30°	1811.5	1754.4	1685.4	1632.3	1598.5	1565.3	1559.3
32.5°	1657.5	1573.9	1497.0	1450.2	1398.4	1377.4	1354.4
35°	1392.1	1310.5	1234.2	1168.5	1130.7	1101.5	1074.9
37.5°	1153.4	1059.4	997.8	944.6	917.3	900.6	904.8
40°	1005.3	923.0	877.9	837.4	812.2	800.2	802.9
42.5°	885.3	823.7	786.6	758.8	741.0	734.4	732.8
45°	749.1	714.6	684.1	668.2	659.6	652.3	647.6
47.5°	656.2	628.1	610.9	601.4	593.9	586.4	586.3
50°	600.5	581.9	570.0	560.0	554.1	548.8	553.4
52.5°	558.0	541.1	529.1	520.2	518.0	513.2	513.1
55°	495.0	481.7	473.1	465.1	461.2	458.5	455.2
57.5°	437.7	425.1	417.1	412.1	404.5	401.8	400.8
60°	396.8	386.8	378.9	372.2	368.9	363.6	363.6
62.5°	359.1	349.2	341.7	336.7	331.2	329.1	329.7
65°	304.6	296.6	289.3	284.0	282.7	278.7	280.0
67.5°	254.4	249.1	241.4	238.5	236.0	233.8	232.2
70°	221.0	215.7	211.7	207.7	205.7	205.7	205.7
72.5°	192.8	186.5	184.1	179.0	180.2	178.1	176.0
75°	149.3	145.3	143.3	141.3	138.0	138.0	138.0
77.5°	109.9	108.7	106.3	104.2	103.4	102.7	103.0
80°	84.9	84.3	82.9	82.9	81.6	81.0	79.6
82.5°	65.3	63.6	62.8	62.2	62.0	61.8	61.6
85°	37.2	35.8	35.8	36.5	35.2	35.2	35.8
87.5°	18.2	18.1	17.6	17.6	18.2	17.7	17.7
90°	19.2	18.9	18.9	19.0	19.1	19.3	19.4
92.5°	18.3	18.3	18.4	18.4	18.4	18.5	18.5
95°	36.5	36.5	36.4	36.1	35.9	35.6	35.4
97.5°	61.4	61.4	61.3	61.3	61.3	61.3	61.2
100°	78.7	78.7	78.6	78.5	78.4	78.3	78.1
102.5°	97.7	97.8	97.8	97.7	97.5	97.4	97.3
105°	126.2	126.5	126.6	126.6	126.6	126.6	126.6
107.5°	156.7	156.8	156.5	155.9	155.4	154.8	154.2
110°	177.3	177.3	177.2	176.8	176.4	176.0	175.6



TEST NUMBER: P331385

CATALOG NUMBER: S122DIP-S865D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	197.9	197.6	197.3	197.0	196.7	196.4	196.2
115°	230.0	229.9	229.6	229.2	228.9	228.5	228.1
117.5°	260.7	260.4	260.1	259.7	259.3	258.9	258.5
120°	281.7	281.7	281.5	281.1	280.8	280.4	280.0
122.5°	302.7	302.4	302.1	301.8	301.5	301.3	301.0
125°	334.2	333.8	333.5	333.4	333.3	333.1	333.0
127.5°	364.7	364.3	363.8	363.4	363.0	362.6	362.2
130°	385.9	385.6	385.2	384.7	384.2	383.7	383.2
132.5°	405.9	405.4	404.9	404.5	404.1	403.7	403.3
135°	436.4	436.3	436.0	435.7	435.3	434.9	434.5
137.5°	465.2	465.1	464.8	464.3	463.8	463.3	462.8
140°	484.7	484.7	484.5	483.9	483.4	482.9	482.4
142.5°	502.3	502.4	502.2	501.7	501.2	500.7	500.2
145°	529.0	529.1	528.9	528.4	527.9	527.4	526.9
147.5°	552.5	552.8	552.7	552.2	551.7	551.2	550.7
150°	567.4	567.8	567.8	567.4	567.0	566.6	566.3
152.5°	582.3	582.8	582.8	582.3	581.8	581.3	580.9
155°	601.2	601.9	602.0	601.6	601.2	600.8	600.5
157.5°	618.8	619.7	619.8	619.2	618.6	618.0	617.3
160°	629.0	629.7	629.9	629.4	628.9	628.3	627.8
162.5°	638.4	639.3	639.4	638.8	638.2	637.6	637.0
165°	650.5	651.3	651.5	650.8	650.2	649.6	648.9
167.5°	660.4	661.3	661.4	660.7	660.1	659.4	658.7
170°	665.9	666.7	666.8	666.0	665.3	664.5	663.8
172.5°	670.0	670.8	670.9	670.2	669.4	668.6	667.9
175°	674.4	675.3	675.4	674.6	673.8	673.1	672.3
177.5°	676.2	676.8	676.8	676.2	675.6	675.0	674.4
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7

(END OF REPORT)