

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931596

Luminaire Tested: DFN2DS-TR4F0-120DS927-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931596
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-120DS927-RLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8078.4 lumens
Efficiency: N/A
Efficacy: 61.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 131.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931596

CATALOG NUMBER: DFN2DS-TR4F0-120DS927-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931596

CATALOG NUMBER: DFN2DS-TR4F0-120DS927-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3121	3121	3121
5°	3132	3081	3098
10°	3108	3031	3005
15°	3073	2941	2857
20°	3023	2813	2672
25°	2973	2667	2493
30°	2902	2517	2263
35°	2834	2355	2061
40°	2765	2186	1829
45°	2684	1997	1617
50°	2601	1806	1411
55°	2516	1600	1211
60°	2417	1384	1006
65°	2306	1163	915
70°	2172	957	842
75°	2007	873	786
80°	1772	780	716
85°	1393	615	615

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2684 cd/sqm

TEST NUMBER: P931596

CATALOG NUMBER: DFN2DS-TR4F0-120DS927-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	368.1	4.6
10°-20°	1010.6	12.5
20°-30°	1418.9	17.6
30°-40°	1546.6	19.1
40°-50°	1421.5	17.6
50°-60°	1116.4	13.8
60°-70°	726.7	9.0
70°-80°	374.1	4.6
80°-90°	95.5	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2797.6	34.6
0°-40°	4344.2	53.8
0°-60°	6882.2	85.2
0°-90°	8078.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8078.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3928	3928	3928	3928	3928	
5°	3928	3910	3864	3896	3885	372
15°	3736	3697	3576	3509	3473	1053
25°	3391	3277	3043	2897	2844	1560
35°	2922	2741	2428	2204	2126	1829
45°	2389	2150	1778	1525	1440	1845
55°	1816	1539	1155	942	875	1623
65°	1226	938	619	498	487	1216
75°	654	405	284	260	256	692
85°	153	78	68	68	68	183
90°	0	0	0	0	0	

TEST NUMBER: P931596

CATALOG NUMBER: DFN2DS-TR4F0-120DS927-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3928.0	3928.0	3928.0	3928.0	3928.0
2.5°	3945.7	3928.0	3888.8	3924.6	3917.4
5°	3928.0	3910.3	3863.9	3895.9	3885.4
7.5°	3895.9	3874.8	3825.0	3839.0	3821.2
10°	3853.3	3828.4	3757.5	3746.6	3725.5
12.5°	3800.1	3768.1	3671.9	3650.8	3611.6
15°	3736.0	3696.8	3576.1	3508.6	3473.2
17.5°	3661.3	3604.4	3455.0	3377.0	3320.1
20°	3576.1	3504.8	3327.2	3238.6	3160.1
22.5°	3483.7	3401.9	3195.6	3074.9	3021.7
25°	3391.3	3277.4	3042.8	2897.2	2843.7
27.5°	3281.2	3160.1	2900.6	2733.6	2651.7
30°	3163.9	3028.5	2744.1	2563.1	2466.9
32.5°	3050.0	2886.3	2595.1	2381.7	2292.7
35°	2922.2	2740.7	2428.0	2204.1	2125.6
37.5°	2797.7	2602.0	2271.5	2026.0	1937.4
40°	2666.0	2453.0	2107.9	1855.6	1763.2
42.5°	2531.0	2303.6	1944.6	1681.3	1592.7
45°	2388.8	2150.5	1777.5	1524.8	1439.5
47.5°	2253.8	2001.5	1617.6	1364.9	1286.8
50°	2104.5	1852.2	1461.1	1215.6	1141.3
52.5°	1958.5	1691.9	1311.7	1077.1	1009.6
55°	1816.4	1539.2	1155.2	942.1	874.6
57.5°	1670.7	1386.4	1016.8	817.7	760.7
60°	1521.4	1237.0	870.8	689.8	632.9
62.5°	1375.9	1091.5	746.4	575.9	547.6
65°	1226.5	938.4	618.6	497.9	486.9
67.5°	1084.3	796.1	497.9	437.1	426.6
70°	935.0	657.8	412.2	376.8	362.4
72.5°	792.8	529.5	344.7	316.4	309.3
75°	654.0	405.0	284.4	259.5	256.1
77.5°	515.6	287.7	224.1	209.7	202.5
80°	387.4	206.3	170.4	156.5	156.5
82.5°	270.1	138.8	117.3	110.1	110.1
85°	152.8	78.1	67.5	67.5	67.5
87.5°	56.9	28.3	28.3	24.9	24.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931596

CATALOG NUMBER: DFN2DS-TR4F0-120DS927-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.19	16.71	15.55	17.02	17.34	11.15	12.67	11.51	12.98	13.30
	3H	16.95	18.32	17.33	18.65	19.01	12.41	13.78	12.79	14.11	14.47
	4H	17.62	18.90	18.02	19.25	19.63	12.92	14.20	13.32	14.55	14.92
	6H	18.11	19.29	18.52	19.66	20.05	13.30	14.48	13.71	14.85	15.24
	8H	18.27	19.40	18.70	19.79	20.19	13.42	14.55	13.85	14.94	15.34
	12H	18.38	19.46	18.81	19.84	20.27	13.50	14.58	13.93	14.96	15.39
4H	2H	15.29	16.57	15.69	16.92	17.30	11.85	13.13	12.24	13.47	13.85
	3H	17.23	18.29	17.64	18.69	19.09	13.29	14.35	13.70	14.75	15.15
	4H	17.98	18.93	18.41	19.35	19.79	13.89	14.84	14.32	15.26	15.70
	6H	18.57	19.40	19.02	19.84	20.30	14.38	15.21	14.83	15.65	16.11
	8H	18.78	19.56	19.24	20.00	20.47	14.54	15.31	15.00	15.76	16.23
	12H	18.94	19.63	19.42	20.11	20.58	14.65	15.35	15.14	15.83	16.30
8H	4H	18.00	18.78	18.46	19.22	19.69	14.24	15.02	14.70	15.46	15.93
	6H	18.64	19.28	19.13	19.77	20.25	14.83	15.47	15.32	15.96	16.44
	8H	18.89	19.46	19.40	19.97	20.46	15.05	15.63	15.56	16.13	16.62
	12H	19.09	19.60	19.60	20.09	20.66	15.23	15.74	15.74	16.23	16.79
12H	4H	17.98	18.68	18.47	19.16	19.63	14.28	14.98	14.77	15.46	15.93
	6H	18.62	19.20	19.13	19.71	20.19	14.89	15.47	15.40	15.98	16.47
	8H	18.90	19.41	19.41	19.90	20.47	15.16	15.67	15.67	16.17	16.73