

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331746

Luminaire Tested: **S122RDIP-S1005D530U835-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331746  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S1005D530U835-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5549.3 lumens  
Efficiency: N/A  
Efficacy: 100.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331746

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331746

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	59	54
2	93	85	80	74	87	80	75	71	71	67	64	62	59	57	54	52	50	46
3	85	76	69	63	79	71	65	60	63	58	54	56	52	49	49	46	43	40
4	78	67	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	35
5	72	61	52	47	67	57	50	45	51	45	41	45	41	37	40	36	33	31
6	67	55	47	41	62	52	44	39	46	40	36	41	36	33	36	33	30	27
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	33	30	27	24
8	57	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24	22
9	54	42	34	29	50	39	33	28	36	30	26	32	27	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	27341	27341	27341
5°	27446	27000	27149
10°	27237	26558	26332
15°	26924	25770	25028
20°	26490	24646	23409
25°	26045	23370	21841
30°	25430	22057	19829
35°	24829	20631	18065
40°	24226	19155	16021
45°	23516	17497	14173
50°	22790	15822	12356
55°	22044	14021	10612
60°	21180	12126	8809
65°	20199	10189	8023
70°	19029	8393	7378
75°	17592	7648	6881
80°	15528	6843	6267
85°	12208	5391	5391



TEST NUMBER: P331746

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.5	2.9
10°-20°	435.2	7.8
20°-30°	611.2	11.0
30°-40°	666.5	12.0
40°-50°	612.8	11.0
50°-60°	481.3	8.7
60°-70°	313.8	5.7
70°-80°	161.8	2.9
80°-90°	44.6	0.8
90°-100°	118.6	2.1
100°-110°	402.4	7.3
110°-120°	427.5	7.7
120°-130°	351.9	6.3
130°-140°	282.6	5.1
140°-150°	213.5	3.8
150°-160°	150.1	2.7
160°-170°	88.3	1.6
170°-180°	28.8	0.5
0°-30°	1204.9	21.7
0°-40°	1871.4	33.7
0°-60°	2965.4	53.4
0°-90°	3485.7	62.8
90°-120°	948.4	17.1
90°-150°	1796.4	32.4
90°-180°	2064.0	37.2
0°-180°	5549.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1693	1693	1693	1693	1693	
5°	1693	1685	1666	1679	1675	160
15°	1611	1592	1542	1513	1497	454
25°	1462	1410	1312	1251	1226	672
35°	1260	1178	1047	954	916	788
45°	1030	924	766	661	621	795
55°	783	661	498	410	377	700
65°	529	404	267	217	210	524
75°	282	178	123	112	110	298
85°	66	35	29	29	29	78
90°	1	8	19	18	19	4
95°	20	49	224	84	65	21
105°	70	105	423	755	643	74
115°	123	155	354	730	846	122
125°	171	202	340	591	686	152
135°	201	240	336	497	569	155
145°	229	263	334	415	454	144
155°	261	281	324	367	382	120
165°	284	293	311	330	335	80
175°	296	296	299	303	302	28
180°	296	296	296	296	296	



TEST NUMBER: P331746

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1699.6	1698.2	1696.8	1695.5	1694.1	1691.9	1688.9	1686.0	1683.0	1680.0	1682.7
5°	1693.4	1691.7	1690.0	1688.3	1686.6	1683.6	1679.1	1674.7	1670.3	1665.9	1668.9
7.5°	1676.0	1673.9	1671.8	1669.6	1667.5	1663.9	1658.7	1653.5	1648.4	1643.2	1644.1
10°	1661.3	1658.9	1656.5	1654.1	1651.7	1647.1	1640.3	1633.5	1626.7	1619.9	1618.9
12.5°	1642.9	1639.9	1637.0	1634.1	1631.2	1625.3	1616.6	1607.9	1599.2	1590.5	1588.6
15°	1610.7	1606.9	1603.2	1599.4	1595.7	1588.0	1576.5	1564.9	1553.3	1541.7	1535.3
17.5°	1571.1	1565.4	1559.7	1554.0	1548.3	1538.0	1523.1	1508.3	1493.4	1478.6	1470.9
20°	1541.7	1534.9	1528.1	1521.3	1514.5	1502.6	1485.5	1468.5	1451.5	1434.4	1425.9
22.5°	1509.8	1502.2	1494.6	1487.0	1479.3	1465.9	1446.7	1427.5	1408.3	1389.1	1378.1
25°	1462.0	1451.1	1440.2	1429.3	1418.4	1401.8	1379.3	1356.8	1334.3	1311.8	1297.9
27.5°	1404.4	1392.6	1380.7	1368.9	1357.0	1338.4	1313.1	1287.7	1262.4	1237.1	1220.8
30°	1364.0	1351.0	1338.1	1325.1	1312.2	1292.1	1264.8	1237.6	1210.4	1183.1	1165.7
32.5°	1324.7	1309.6	1294.5	1279.4	1264.2	1242.8	1215.0	1187.2	1159.4	1131.6	1111.8
35°	1259.7	1242.4	1225.0	1207.6	1190.3	1166.6	1136.6	1106.7	1076.7	1046.7	1025.3
37.5°	1194.8	1175.7	1156.6	1137.5	1118.5	1093.0	1061.0	1029.1	997.1	965.2	941.6
40°	1149.4	1129.0	1108.5	1088.1	1067.7	1040.9	1007.9	974.9	941.8	908.8	884.6
42.5°	1102.8	1081.3	1059.8	1038.2	1016.7	988.9	954.8	920.6	886.5	852.4	827.4
45°	1029.9	1007.0	984.2	961.4	938.6	909.3	873.5	837.8	802.0	766.3	742.1
47.5°	958.7	934.6	910.4	886.2	862.0	831.5	794.6	757.6	720.7	683.8	659.8
50°	907.3	883.1	858.9	834.7	810.5	779.7	742.3	704.8	667.3	629.9	606.4
52.5°	857.0	831.7	806.5	781.2	755.9	725.0	688.3	651.7	615.0	578.4	555.7
55°	783.1	756.6	730.0	703.4	676.9	645.2	608.4	571.6	534.9	498.1	477.6
57.5°	707.4	680.2	652.9	625.7	598.4	567.1	531.8	496.4	461.1	425.7	407.0
60°	655.9	628.7	601.4	574.2	546.9	515.8	480.7	445.6	410.5	375.5	358.1
62.5°	605.7	578.4	551.2	523.9	496.7	466.3	432.9	399.4	366.0	332.6	316.0
65°	528.7	501.1	473.6	446.0	418.4	389.3	358.6	328.0	297.3	266.7	255.1
67.5°	454.5	427.2	399.8	372.4	345.0	317.5	290.0	262.4	234.8	207.2	201.9
70°	403.1	376.5	349.9	323.4	296.8	271.8	248.3	224.8	201.3	177.8	174.4
72.5°	354.0	328.5	303.1	277.6	252.1	229.9	211.1	192.2	173.3	154.5	151.6
75°	282.0	258.1	234.3	210.5	186.6	168.9	157.3	145.8	134.2	122.6	120.2
77.5°	211.2	190.3	169.4	148.5	127.5	114.3	108.7	103.1	97.5	92.0	90.6
80°	167.0	149.7	132.3	114.9	97.6	87.2	83.8	80.4	77.0	73.6	72.2
82.5°	126.6	113.0	99.5	85.9	72.4	64.4	62.1	59.8	57.5	55.2	54.4
85°	65.9	58.7	51.6	44.4	37.3	33.2	32.2	31.2	30.1	29.1	29.1
87.5°	19.7	17.9	16.2	14.2	12.3	11.5	12.1	12.9	13.6	13.7	13.3
90°	0.6	2.3	4.6	5.7	6.8	8.6	11.4	15.4	18.8	19.4	18.8
92.5°	7.0	10.0	14.1	16.7	20.5	25.9	38.8	56.9	73.1	74.1	62.6
95°	20.0	22.2	27.9	33.1	42.2	55.9	82.1	131.7	197.9	223.6	195.6
97.5°	32.5	35.6	41.6	49.4	59.9	75.4	108.4	177.5	287.4	381.6	400.3
100°	43.9	45.6	50.8	59.9	71.3	87.3	117.5	187.1	310.2	450.5	532.6
102.5°	54.4	55.7	60.8	69.9	81.8	97.7	125.7	187.5	301.6	452.8	581.9
105°	69.6	71.9	75.8	84.4	96.9	112.9	139.7	190.5	284.6	422.6	574.3
107.5°	86.0	87.8	91.7	99.6	112.0	128.1	154.1	198.3	276.1	390.2	524.2
110°	96.9	99.2	102.7	110.1	122.0	138.6	163.7	204.7	274.3	374.7	492.7



TEST NUMBER: P331746

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	107.0	109.3	113.1	120.1	131.6	148.6	172.8	211.6	274.8	364.6	470.8
115°	122.6	125.5	128.9	135.7	147.1	162.5	187.1	221.8	277.2	353.6	443.7
117.5°	138.8	141.1	144.5	150.6	161.5	177.5	200.2	232.8	281.3	348.2	426.6
120°	148.8	151.1	154.5	159.7	171.1	187.1	209.3	240.1	284.0	345.0	417.5
122.5°	158.4	160.3	163.7	169.3	180.7	197.1	218.0	246.5	287.2	343.2	409.7
125°	171.1	172.8	176.2	183.1	194.5	210.4	231.0	256.6	292.0	339.9	398.6
127.5°	181.1	183.4	188.2	195.7	206.7	223.1	243.1	266.1	296.9	338.0	388.4
130°	187.1	189.3	195.0	203.0	214.4	230.4	250.4	272.0	300.5	337.0	381.5
132.5°	192.5	195.3	201.4	209.9	221.7	237.7	256.7	278.0	304.2	336.6	376.0
135°	200.7	203.0	209.9	218.4	231.5	247.5	265.8	285.7	308.5	335.9	368.4
137.5°	208.5	211.2	218.1	227.2	240.2	255.0	273.1	291.6	312.4	335.8	363.0
140°	214.4	216.7	223.6	232.7	245.2	260.1	277.2	294.8	314.2	335.3	359.9
142.5°	220.4	222.2	228.6	237.7	249.8	263.7	280.4	297.6	315.6	335.3	356.7
145°	229.3	231.5	237.2	245.8	257.2	269.7	285.1	301.1	317.1	334.2	352.4
147.5°	238.8	240.5	246.0	253.9	263.4	274.5	289.0	303.1	317.5	332.1	348.1
150°	245.2	246.9	251.5	258.9	267.5	277.7	290.8	304.0	317.1	330.8	344.5
152.5°	251.6	252.4	257.0	263.5	271.6	280.9	292.7	304.4	316.2	328.5	341.3
155°	260.6	261.2	264.6	270.9	277.2	285.7	295.4	305.1	314.8	324.5	335.3
157.5°	268.1	268.7	271.5	276.9	282.0	289.1	297.3	305.1	312.2	320.4	329.7
160°	273.2	273.7	276.0	280.6	285.1	291.4	298.3	305.1	310.8	317.7	325.6
162.5°	278.2	277.8	280.1	283.8	287.9	292.8	298.7	304.6	309.4	315.4	322.0
165°	284.0	283.4	284.6	288.0	290.8	294.3	299.4	303.4	306.8	310.8	315.9
167.5°	288.8	288.1	289.1	291.3	293.4	295.5	299.3	302.6	304.2	306.8	310.0
170°	292.0	290.8	291.4	293.1	294.3	296.0	298.8	301.7	302.8	304.5	306.8
172.5°	293.8	293.1	292.8	294.5	295.2	296.4	298.4	300.3	301.0	301.8	303.6
175°	296.0	295.4	294.8	296.0	296.0	296.5	297.7	298.8	298.3	298.8	299.4
177.5°	297.0	296.1	295.6	296.5	296.5	296.5	297.0	297.9	297.0	296.5	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331746

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1685.4	1688.1	1690.9	1691.9	1691.4	1690.9	1690.3	1689.8
5°	1672.0	1675.1	1678.1	1679.1	1678.1	1677.1	1676.1	1675.1
7.5°	1644.9	1645.8	1646.7	1646.3	1644.5	1642.7	1641.0	1639.2
10°	1617.8	1616.8	1615.8	1614.3	1612.2	1610.2	1608.1	1606.1
12.5°	1586.8	1584.9	1583.1	1580.5	1577.1	1573.7	1570.3	1566.9
15°	1528.8	1522.3	1515.8	1510.9	1507.5	1504.1	1500.7	1497.3
17.5°	1463.2	1455.5	1447.8	1441.0	1435.2	1429.3	1423.4	1417.6
20°	1417.4	1408.9	1400.4	1392.4	1384.9	1377.4	1369.9	1362.4
22.5°	1367.2	1356.2	1345.2	1336.9	1331.4	1325.8	1320.2	1314.6
25°	1283.9	1270.0	1256.0	1246.5	1241.3	1236.2	1231.1	1226.0
27.5°	1204.5	1188.2	1171.9	1159.7	1151.6	1143.5	1135.4	1127.3
30°	1148.4	1131.0	1113.6	1100.4	1091.2	1082.0	1072.8	1063.6
32.5°	1092.0	1072.2	1052.3	1038.1	1029.5	1020.8	1012.1	1003.5
35°	1003.8	982.4	960.9	946.4	938.9	931.4	923.9	916.5
37.5°	917.9	894.3	870.6	854.5	846.0	837.4	828.8	820.2
40°	860.4	836.2	812.1	795.6	786.7	777.8	769.0	760.1
42.5°	802.4	777.4	752.4	735.6	727.0	718.4	709.9	701.3
45°	717.9	693.7	669.5	653.4	645.2	637.0	628.8	620.7
47.5°	635.7	611.7	587.6	571.9	564.5	557.1	549.6	542.2
50°	582.9	559.4	535.9	520.5	513.4	506.2	499.1	491.9
52.5°	533.0	510.3	487.7	473.0	466.4	459.8	453.2	446.6
55°	457.2	436.8	416.3	402.9	396.4	389.9	383.5	377.0
57.5°	388.3	369.5	350.8	338.7	333.3	327.8	322.4	316.9
60°	340.7	323.4	306.0	294.6	289.1	283.7	278.2	272.8
62.5°	299.5	282.9	266.4	256.4	253.2	249.9	246.6	243.4
65°	243.5	231.9	220.3	214.0	213.0	212.0	211.0	210.0
67.5°	196.6	191.3	185.9	182.7	181.7	180.6	179.5	178.4
70°	171.0	167.6	164.2	161.8	160.4	159.0	157.7	156.3
72.5°	148.8	145.9	143.0	141.2	140.4	139.6	138.7	137.9
75°	117.8	115.5	113.1	111.7	111.4	111.0	110.7	110.3
77.5°	89.2	87.9	86.5	85.5	85.0	84.5	83.9	83.4
80°	70.8	69.5	68.1	67.4	67.4	67.4	67.4	67.4
82.5°	53.5	52.7	51.9	51.5	51.5	51.5	51.5	51.5
85°	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
87.5°	12.9	12.4	12.4	12.3	12.3	12.3	12.3	12.3
90°	18.2	17.1	18.2	18.8	18.8	18.8	18.8	18.8
92.5°	49.7	42.7	37.9	34.3	33.9	32.1	32.5	31.6
95°	149.4	114.6	90.7	78.1	70.7	66.2	64.4	65.0
97.5°	348.7	285.3	223.6	182.4	155.1	141.1	132.8	128.0
100°	520.7	450.0	371.8	302.8	255.5	231.0	214.4	204.2
102.5°	633.4	617.4	560.3	487.1	435.7	393.8	373.2	359.3
105°	692.9	757.3	764.8	745.9	710.6	675.2	650.7	642.7
107.5°	650.0	747.1	806.4	834.0	838.4	836.5	831.6	821.0
110°	613.1	715.1	788.1	834.9	859.4	870.3	875.4	874.8





TEST NUMBER: P331746

CATALOG NUMBER: S122RDIP-S1005D530U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	579.3	677.3	755.3	808.9	843.0	861.1	870.8	873.9
115°	537.8	625.6	700.3	759.1	799.5	825.8	840.6	845.7
117.5°	506.5	583.6	651.4	706.5	747.8	775.5	791.1	795.4
120°	491.0	561.7	622.2	674.1	714.0	740.8	757.3	763.0
122.5°	478.7	543.5	600.7	647.6	683.4	709.8	724.5	729.3
125°	460.8	519.5	569.7	612.5	645.6	667.2	681.5	686.1
127.5°	443.1	496.3	543.6	583.1	611.9	632.2	644.5	648.2
130°	431.7	480.8	525.8	563.4	591.4	610.8	622.2	626.7
132.5°	420.8	466.2	507.6	542.9	570.4	589.8	600.3	604.4
135°	405.5	443.1	480.8	512.7	537.2	556.0	566.3	568.6
137.5°	393.3	424.8	454.6	482.5	504.8	521.0	530.0	533.4
140°	385.5	412.9	439.1	464.2	482.5	497.3	505.8	509.3
142.5°	379.1	402.4	425.0	446.0	463.3	476.8	484.4	485.1
145°	370.1	388.9	406.6	423.2	436.8	446.5	452.2	453.9
147.5°	363.2	378.0	391.8	403.9	415.2	422.9	426.8	427.8
150°	358.1	370.7	382.7	392.9	401.5	408.3	411.7	412.3
152.5°	353.1	364.8	374.9	383.8	390.5	396.5	399.0	399.1
155°	346.2	355.3	363.8	370.1	376.4	380.4	382.7	381.5
157.5°	338.1	345.7	352.9	357.8	362.2	365.6	366.6	366.6
160°	333.0	339.3	345.6	349.6	353.6	356.4	357.0	357.0
162.5°	328.0	333.4	338.8	341.8	345.8	347.8	348.3	347.9
165°	320.5	324.5	328.5	330.8	333.0	335.3	335.3	334.8
167.5°	313.3	316.4	319.1	321.2	322.2	323.5	323.4	322.7
170°	309.7	311.4	313.7	314.8	315.4	317.1	316.5	315.4
172.5°	305.6	306.8	308.6	309.3	309.9	310.7	310.1	309.4
175°	301.1	301.7	302.3	302.8	302.8	303.4	302.8	301.7
177.5°	297.9	297.9	298.4	298.4	298.4	298.4	297.9	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5

(END OF REPORT)