

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931471

Luminaire Tested: DFN2DS-TR4F0-050DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931471
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-050DS930-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4034.2 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 48.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931471

CATALOG NUMBER: DFN2DS-TR4F0-050DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931471

CATALOG NUMBER: DFN2DS-TR4F0-050DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1260	1260	1260
5°	1264	1246	1254
10°	1257	1234	1240
15°	1241	1218	1216
20°	1219	1194	1192
25°	1197	1164	1164
30°	1169	1137	1127
35°	1143	1105	1088
40°	1110	1072	1051
45°	1078	1040	1014
50°	1042	1006	970
55°	1005	967	931
60°	964	921	887
65°	920	874	834
70°	864	818	779
75°	786	753	735
80°	698	676	642
85°	569	542	487

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1078 cd/sqm

TEST NUMBER: P931471

CATALOG NUMBER: DFN2DS-TR4F0-050DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.2	3.7
10°-20°	419.9	10.4
20°-30°	617.1	15.3
30°-40°	716.7	17.8
40°-50°	715.8	17.7
50°-60°	624.2	15.5
60°-70°	461.4	11.4
70°-80°	261.0	6.5
80°-90°	68.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1186.2	29.4
0°-40°	1902.9	47.2
0°-60°	3242.9	80.4
0°-90°	4034.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4034.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1586	1586	1586	1586	1586	
5°	1586	1580	1563	1575	1572	151
15°	1509	1500	1480	1487	1479	425
25°	1366	1354	1328	1331	1328	629
35°	1179	1163	1139	1130	1122	736
45°	959	948	925	909	903	740
55°	726	717	698	680	672	649
65°	490	480	465	451	444	484
75°	256	253	245	236	239	273
85°	62	61	60	55	53	73
90°	0	0	0	0	0	

TEST NUMBER: P931471

CATALOG NUMBER: DFN2DS-TR4F0-050DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1585.6	1585.6	1585.6	1585.6	1585.6
2.5°	1594.8	1587.2	1570.4	1585.6	1582.7
5°	1585.6	1579.6	1562.8	1574.9	1572.1
7.5°	1574.9	1565.9	1549.1	1561.4	1558.3
10°	1558.3	1547.6	1529.3	1541.4	1536.9
12.5°	1535.3	1526.3	1508.0	1515.6	1512.5
15°	1509.4	1500.3	1480.4	1486.6	1479.0
17.5°	1477.4	1468.3	1448.4	1456.0	1448.4
20°	1442.3	1433.3	1411.9	1416.4	1410.4
22.5°	1407.3	1393.6	1373.7	1373.7	1370.6
25°	1366.1	1354.0	1328.0	1331.0	1328.0
27.5°	1320.3	1309.6	1289.9	1285.3	1277.8
30°	1274.7	1262.4	1239.6	1235.1	1228.9
32.5°	1225.8	1216.8	1192.3	1183.1	1177.0
35°	1178.6	1163.4	1139.0	1129.8	1122.2
37.5°	1125.2	1111.5	1087.0	1076.4	1068.8
40°	1070.4	1058.1	1033.7	1020.1	1013.9
42.5°	1017.0	1004.7	980.4	965.0	956.0
45°	959.1	948.4	925.4	908.8	902.6
47.5°	902.6	891.9	867.6	850.7	841.7
50°	843.1	835.5	814.2	792.8	785.2
52.5°	785.2	774.5	754.8	738.0	727.3
55°	725.8	716.6	698.3	680.0	672.5
57.5°	666.3	658.7	638.8	620.5	614.3
60°	606.8	600.8	579.5	562.6	558.1
62.5°	548.9	538.2	523.0	507.7	501.6
65°	489.5	480.3	465.0	451.3	443.7
67.5°	428.5	420.8	407.2	396.5	390.3
70°	372.0	365.9	352.2	341.5	335.5
72.5°	314.2	308.0	300.4	289.7	285.2
75°	256.1	253.1	245.4	236.4	239.4
77.5°	204.3	198.1	195.1	190.5	186.1
80°	152.6	150.9	147.8	143.4	140.3
82.5°	103.7	103.7	102.2	96.1	96.1
85°	62.4	61.0	59.5	54.8	53.4
87.5°	27.5	24.4	21.4	16.8	15.2
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931471

CATALOG NUMBER: DFN2DS-TR4F0-050DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.08	13.70	12.45	14.01	14.32	11.64	13.25	12.00	13.56	13.88
	3H	13.83	15.29	14.21	15.62	15.98	13.34	14.80	13.72	15.12	15.48
	4H	14.48	15.85	14.88	16.20	16.57	13.99	15.36	14.38	15.70	16.08
	6H	14.95	16.22	15.36	16.58	16.97	14.45	15.72	14.86	16.08	16.47
	8H	15.09	16.30	15.52	16.69	17.09	14.59	15.80	15.02	16.19	16.59
	12H	15.18	16.34	15.61	16.73	17.15	14.67	15.83	15.10	16.21	16.64
4H	2H	12.64	14.01	13.04	14.36	14.74	12.29	13.66	12.69	14.01	14.38
	3H	14.62	15.77	15.03	16.16	16.56	14.21	15.36	14.62	15.76	16.16
	4H	15.40	16.43	15.83	16.85	17.28	14.97	16.01	15.40	16.42	16.86
	6H	15.99	16.90	16.45	17.34	17.79	15.56	16.47	16.02	16.91	17.36
	8H	16.18	17.03	16.64	17.47	17.94	15.74	16.59	16.21	17.03	17.50
	12H	16.31	17.07	16.79	17.55	18.02	15.86	16.62	16.34	17.10	17.57
8H	4H	15.67	16.52	16.13	16.96	17.42	15.30	16.14	15.76	16.58	17.05
	6H	16.38	17.09	16.88	17.58	18.05	16.00	16.71	16.50	17.19	17.67
	8H	16.64	17.27	17.15	17.78	18.27	16.25	16.88	16.76	17.39	17.88
	12H	16.84	17.40	17.35	17.89	18.45	16.43	16.99	16.94	17.48	18.04
12H	4H	15.70	16.46	16.18	16.93	17.40	15.33	16.09	15.81	16.57	17.04
	6H	16.43	17.06	16.94	17.57	18.05	16.06	16.69	16.57	17.20	17.69
	8H	16.74	17.30	17.25	17.79	18.35	16.37	16.92	16.87	17.41	17.98

END OF REPORT