

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331642

Luminaire Tested: **S122RDIP-S290D1080U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331642  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S290D1080U835-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5341.4 lumens  
Efficiency: N/A  
Efficacy: 126.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331642

CATALOG NUMBER: S122RDIP-S290D1080U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331642

CATALOG NUMBER: S122RDIP-S290D1080U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19
1	91	87	83	80	80	77	74	71	58	56	54	41	40	39	25	24	24	17
2	83	76	70	66	73	67	63	59	51	48	45	36	34	33	22	21	20	14
3	76	67	60	55	67	59	54	49	45	41	38	32	30	28	20	19	18	12
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	16	15	11
5	64	53	45	39	56	47	40	36	36	31	28	26	23	21	16	15	13	9
6	58	47	40	34	51	42	36	31	32	28	24	23	20	18	15	13	12	8
7	54	42	35	30	47	38	31	27	29	25	21	21	18	16	13	12	10	7
8	50	38	31	26	44	34	28	24	26	22	19	19	16	14	12	11	9	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	11	10	9	6
10	43	32	25	21	38	28	23	19	22	18	15	16	13	11	10	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8105	8105	8105
5°	8136	8003	8047
10°	8073	7873	7806
15°	7980	7639	7418
20°	7852	7306	6940
25°	7721	6928	6474
30°	7538	6538	5878
35°	7360	6116	5355
40°	7181	5678	4749
45°	6971	5186	4201
50°	6754	4690	3662
55°	6533	4155	3147
60°	6278	3594	2612
65°	5987	3018	2376
70°	5641	2488	2186
75°	5215	2264	2040
80°	4603	2027	1860
85°	3612	1593	1593



TEST NUMBER: P331642

CATALOG NUMBER: S122RDIP-S290D1080U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.0	0.9
10°-20°	129.0	2.4
20°-30°	181.2	3.4
30°-40°	197.6	3.7
40°-50°	181.6	3.4
50°-60°	142.7	2.7
60°-70°	93.0	1.7
70°-80°	48.0	0.9
80°-90°	16.1	0.3
90°-100°	49.0	0.9
100°-110°	179.7	3.4
110°-120°	480.4	9.0
120°-130°	793.0	14.8
130°-140°	843.3	15.8
140°-150°	783.8	14.7
150°-160°	630.2	11.8
160°-170°	406.1	7.6
170°-180°	139.8	2.6
0°-30°	357.2	6.7
0°-40°	554.7	10.4
0°-60°	879.0	16.5
0°-90°	1036.0	19.4
90°-120°	709.1	13.3
90°-150°	3129.2	58.6
90°-180°	4305.0	80.6
0°-180°	5341.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	502	500	494	498	496	48
15°	477	472	457	449	444	134
25°	433	418	389	371	363	199
35°	373	349	310	283	272	234
45°	305	274	227	196	184	236
55°	232	196	148	121	112	207
65°	157	120	79	64	62	155
75°	84	53	36	33	33	88
85°	20	10	9	9	9	23
90°	1	13	21	26	29	4
95°	69	36	42	46	46	85
105°	323	337	65	76	81	345
115°	611	630	656	187	87	602
125°	864	878	898	906	909	770
135°	1069	1086	1096	1106	1104	826
145°	1241	1241	1258	1264	1260	776
155°	1366	1358	1369	1375	1367	629
165°	1439	1434	1436	1443	1436	406
175°	1472	1465	1467	1473	1464	140
180°	1469	1469	1469	1469	1469	



TEST NUMBER: P331642

CATALOG NUMBER: S122RDIP-S290D1080U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	503.8	503.4	503.0	502.6	502.2	501.5	500.6	499.8	498.9	498.0	498.8
5°	502.0	501.5	501.0	500.5	500.0	499.0	497.7	496.4	495.1	493.8	494.7
7.5°	496.8	496.2	495.5	494.9	494.3	493.2	491.7	490.1	488.6	487.1	487.3
10°	492.4	491.7	491.0	490.3	489.6	488.2	486.2	484.2	482.2	480.2	479.9
12.5°	487.0	486.1	485.2	484.4	483.5	481.8	479.2	476.6	474.0	471.4	470.9
15°	477.4	476.3	475.2	474.1	473.0	470.7	467.3	463.9	460.4	457.0	455.1
17.5°	465.7	464.0	462.3	460.6	458.9	455.9	451.5	447.1	442.7	438.3	436.0
20°	457.0	455.0	453.0	450.9	448.9	445.4	440.3	435.3	430.3	425.2	422.7
22.5°	447.6	445.3	443.0	440.8	438.5	434.5	428.8	423.1	417.5	411.8	408.5
25°	433.4	430.1	426.9	423.7	420.5	415.5	408.8	402.2	395.5	388.9	384.7
27.5°	416.3	412.8	409.3	405.8	402.2	396.7	389.2	381.7	374.2	366.7	361.9
30°	404.3	400.5	396.6	392.8	389.0	383.0	374.9	366.9	358.8	350.7	345.6
32.5°	392.7	388.2	383.7	379.2	374.7	368.4	360.2	351.9	343.7	335.4	329.6
35°	373.4	368.3	363.1	358.0	352.8	345.8	336.9	328.0	319.2	310.3	303.9
37.5°	354.2	348.5	342.8	337.2	331.5	324.0	314.5	305.0	295.6	286.1	279.1
40°	340.7	334.7	328.6	322.5	316.5	308.6	298.8	289.0	279.2	269.4	262.2
42.5°	326.9	320.5	314.1	307.8	301.4	293.1	283.0	272.9	262.8	252.7	245.3
45°	305.3	298.5	291.7	285.0	278.2	269.5	258.9	248.3	237.7	227.1	220.0
47.5°	284.2	277.0	269.9	262.7	255.5	246.5	235.5	224.6	213.6	202.7	195.6
50°	268.9	261.8	254.6	247.4	240.3	231.1	220.0	208.9	197.8	186.7	179.7
52.5°	254.0	246.5	239.1	231.6	224.1	214.9	204.0	193.2	182.3	171.4	164.7
55°	232.1	224.3	216.4	208.5	200.6	191.3	180.3	169.4	158.5	147.6	141.6
57.5°	209.7	201.6	193.5	185.5	177.4	168.1	157.6	147.2	136.7	126.2	120.6
60°	194.4	186.4	178.3	170.2	162.1	152.9	142.5	132.1	121.7	111.3	106.1
62.5°	179.5	171.5	163.4	155.3	147.2	138.2	128.3	118.4	108.5	98.6	93.7
65°	156.7	148.5	140.4	132.2	124.0	115.4	106.3	97.2	88.1	79.0	75.6
67.5°	134.7	126.6	118.5	110.4	102.3	94.1	85.9	77.8	69.6	61.4	59.8
70°	119.5	111.6	103.7	95.9	88.0	80.6	73.6	66.6	59.7	52.7	51.7
72.5°	104.9	97.4	89.8	82.3	74.7	68.2	62.6	57.0	51.4	45.8	44.9
75°	83.6	76.5	69.5	62.4	55.3	50.1	46.6	43.2	39.8	36.3	35.6
77.5°	62.6	56.4	50.2	44.0	37.8	33.9	32.2	30.6	28.9	27.3	26.9
80°	49.5	44.4	39.2	34.1	28.9	25.8	24.8	23.8	22.8	21.8	21.4
82.5°	37.5	33.5	29.5	25.5	21.5	19.1	18.4	17.7	17.0	16.4	16.1
85°	19.5	17.4	15.3	13.2	11.1	9.8	9.5	9.2	8.9	8.6	8.6
87.5°	6.0	5.9	5.8	5.6	5.5	5.6	6.0	6.4	6.8	7.2	7.3
90°	1.1	3.7	6.3	8.9	11.5	13.7	15.6	17.5	19.4	21.3	22.4
92.5°	21.5	21.2	21.0	20.8	20.5	20.9	21.8	22.8	23.7	24.7	25.3
95°	69.1	61.3	53.5	45.7	37.9	34.8	36.5	38.2	39.8	41.5	42.6
97.5°	137.1	115.2	93.2	71.2	49.3	40.2	44.0	47.8	51.7	55.5	56.4
100°	188.2	155.8	123.4	91.1	58.7	44.5	48.5	52.6	56.6	60.6	62.5
102.5°	244.3	237.4	230.6	223.7	216.9	196.7	163.1	129.5	95.9	62.3	64.8
105°	323.2	330.3	337.3	344.4	351.5	322.8	258.3	193.8	129.3	64.8	67.4
107.5°	413.1	418.8	424.5	430.2	436.0	400.2	322.8	245.5	168.1	90.8	88.1
110°	470.9	475.9	480.9	485.8	490.8	459.1	390.8	322.6	254.3	186.0	162.4



TEST NUMBER: P331642

CATALOG NUMBER: S122RDIP-S290D1080U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	525.4	529.8	534.1	538.5	542.9	536.7	519.8	503.0	486.1	469.2	383.1
115°	611.3	615.3	619.3	623.3	627.3	632.3	638.2	644.1	650.0	655.9	546.5
117.5°	688.0	692.5	697.0	701.5	706.0	710.2	714.3	718.4	722.4	726.5	700.0
120°	744.1	747.7	751.2	754.8	758.3	762.2	766.5	770.7	775.0	779.2	782.0
122.5°	791.8	795.5	799.2	803.0	806.7	810.9	815.5	820.1	824.8	829.4	831.1
125°	864.3	867.3	870.4	873.5	876.5	880.3	884.8	889.3	893.8	898.3	899.9
127.5°	930.0	933.4	936.8	940.2	943.6	946.9	950.3	953.6	957.0	960.4	962.8
130°	971.6	975.4	979.2	983.0	986.7	989.9	992.5	995.1	997.7	1000.3	1002.9
132.5°	1014.1	1017.4	1020.6	1023.8	1027.0	1029.9	1032.5	1035.1	1037.7	1040.3	1042.5
135°	1069.4	1073.2	1077.0	1080.8	1084.5	1087.5	1089.6	1091.7	1093.9	1096.0	1098.4
137.5°	1125.3	1128.0	1130.6	1133.3	1135.9	1138.4	1140.9	1143.3	1145.7	1148.1	1150.4
140°	1161.9	1163.8	1165.7	1167.6	1169.5	1171.7	1174.3	1176.9	1179.5	1182.1	1184.2
142.5°	1192.5	1194.2	1195.9	1197.6	1199.3	1201.7	1204.6	1207.6	1210.6	1213.6	1215.5
145°	1240.6	1240.3	1240.1	1239.9	1239.6	1241.5	1245.5	1249.5	1253.6	1257.6	1259.2
147.5°	1282.5	1281.6	1280.7	1279.8	1278.9	1280.4	1284.4	1288.3	1292.3	1296.3	1297.5
150°	1309.7	1308.0	1306.4	1304.7	1303.1	1304.1	1307.9	1311.7	1315.5	1319.2	1320.7
152.5°	1332.6	1330.8	1328.9	1327.1	1325.3	1326.1	1329.7	1333.3	1336.9	1340.5	1341.9
155°	1366.0	1363.9	1361.8	1359.6	1357.5	1357.9	1360.7	1363.5	1366.4	1369.2	1370.6
157.5°	1392.2	1390.4	1388.6	1386.8	1385.0	1385.1	1387.1	1389.0	1391.0	1393.0	1394.6
160°	1407.5	1406.1	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1408.9
162.5°	1421.1	1419.7	1418.2	1416.8	1415.4	1415.3	1416.5	1417.8	1419.0	1420.2	1421.8
165°	1439.4	1437.9	1436.5	1435.1	1433.7	1433.3	1434.0	1434.8	1435.5	1436.2	1437.8
167.5°	1453.0	1451.6	1450.1	1448.7	1447.3	1446.9	1447.6	1448.2	1448.9	1449.6	1451.2
170°	1460.6	1459.2	1457.8	1456.4	1455.0	1454.5	1455.0	1455.4	1455.9	1456.4	1458.0
172.5°	1465.7	1464.3	1462.9	1461.5	1460.1	1459.6	1460.1	1460.5	1461.0	1461.5	1463.1
175°	1472.3	1470.7	1469.0	1467.4	1465.7	1465.1	1465.6	1466.1	1466.5	1467.0	1468.7
177.5°	1473.4	1472.1	1470.7	1469.4	1468.1	1467.5	1467.7	1467.9	1468.1	1468.3	1469.6
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331642

CATALOG NUMBER: S122RDIP-S290D1080U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	499.6	500.4	501.2	501.5	501.4	501.2	501.0	500.9
5°	495.6	496.5	497.4	497.7	497.4	497.1	496.8	496.5
7.5°	487.6	487.9	488.1	488.0	487.5	486.9	486.4	485.9
10°	479.6	479.3	479.0	478.5	477.9	477.3	476.7	476.1
12.5°	470.4	469.8	469.3	468.5	467.5	466.5	465.5	464.5
15°	453.2	451.2	449.3	447.9	446.9	445.8	444.8	443.8
17.5°	433.7	431.4	429.2	427.2	425.4	423.7	421.9	420.2
20°	420.2	417.6	415.1	412.7	410.5	408.3	406.1	403.9
22.5°	405.3	402.0	398.8	396.3	394.6	393.0	391.3	389.7
25°	380.6	376.4	372.3	369.5	368.0	366.4	364.9	363.4
27.5°	357.0	352.2	347.4	343.8	341.4	339.0	336.6	334.2
30°	340.4	335.3	330.1	326.2	323.4	320.7	318.0	315.3
32.5°	323.7	317.8	311.9	307.7	305.2	302.6	300.0	297.5
35°	297.6	291.2	284.8	280.5	278.3	276.1	273.9	271.7
37.5°	272.1	265.1	258.1	253.3	250.8	248.2	245.7	243.1
40°	255.1	247.9	240.7	235.8	233.2	230.6	227.9	225.3
42.5°	237.8	230.4	223.0	218.1	215.5	213.0	210.4	207.9
45°	212.8	205.6	198.5	193.7	191.3	188.8	186.4	184.0
47.5°	188.4	181.3	174.2	169.5	167.3	165.1	162.9	160.7
50°	172.8	165.8	158.8	154.3	152.2	150.1	147.9	145.8
52.5°	158.0	151.3	144.6	140.2	138.3	136.3	134.3	132.4
55°	135.5	129.5	123.4	119.4	117.5	115.6	113.7	111.8
57.5°	115.1	109.5	104.0	100.4	98.8	97.2	95.6	93.9
60°	101.0	95.9	90.7	87.3	85.7	84.1	82.5	80.9
62.5°	88.8	83.9	79.0	76.0	75.0	74.1	73.1	72.1
65°	72.2	68.7	65.3	63.4	63.1	62.8	62.5	62.2
67.5°	58.3	56.7	55.1	54.2	53.8	53.5	53.2	52.9
70°	50.7	49.7	48.7	48.0	47.5	47.1	46.7	46.3
72.5°	44.1	43.2	42.4	41.9	41.6	41.4	41.1	40.9
75°	34.9	34.2	33.5	33.1	33.0	32.9	32.8	32.7
77.5°	26.4	26.0	25.6	25.4	25.2	25.0	24.9	24.7
80°	21.0	20.6	20.2	20.0	20.0	20.0	20.0	20.0
82.5°	15.9	15.6	15.4	15.3	15.3	15.3	15.3	15.3
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
87.5°	7.5	7.6	7.8	7.9	8.0	8.1	8.2	8.3
90°	23.6	24.8	26.0	26.8	27.3	27.8	28.2	28.7
92.5°	25.9	26.5	27.1	27.6	27.9	28.1	28.4	28.7
95°	43.8	45.0	46.2	46.7	46.4	46.2	45.9	45.7
97.5°	57.4	58.3	59.3	59.9	60.2	60.5	60.7	61.0
100°	64.4	66.3	68.2	69.3	69.8	70.3	70.8	71.2
102.5°	67.2	69.7	72.1	73.7	74.3	75.0	75.7	76.3
105°	70.0	72.6	75.2	77.0	78.0	78.9	79.8	80.8
107.5°	85.5	82.8	80.2	79.4	80.3	81.2	82.2	83.1
110°	138.8	115.2	91.5	80.2	81.1	82.1	83.0	84.0





TEST NUMBER: P331642

CATALOG NUMBER: S122RDIP-S290D1080U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	296.9	210.7	124.5	81.8	82.6	83.3	84.1	84.8
115°	437.1	327.8	218.4	155.2	138.2	121.2	104.2	87.2
117.5°	673.6	647.1	620.7	579.5	523.6	467.7	411.8	355.9
120°	784.9	787.7	790.6	776.0	744.1	712.2	680.3	648.5
122.5°	832.8	834.5	836.2	833.9	827.8	821.6	815.4	809.2
125°	901.6	903.2	904.9	906.1	906.8	907.5	908.2	908.9
127.5°	965.2	967.6	970.0	971.3	971.4	971.6	971.7	971.8
130°	1005.5	1008.1	1010.7	1011.9	1011.7	1011.4	1011.2	1011.0
132.5°	1044.7	1047.0	1049.2	1050.2	1049.9	1049.7	1049.5	1049.2
135°	1100.7	1103.1	1105.4	1106.4	1105.9	1105.4	1105.0	1104.5
137.5°	1152.7	1155.0	1157.3	1158.1	1157.3	1156.5	1155.7	1154.9
140°	1186.4	1188.5	1190.6	1191.1	1189.9	1188.7	1187.5	1186.4
142.5°	1217.4	1219.4	1221.3	1221.7	1220.5	1219.3	1218.2	1217.0
145°	1260.9	1262.5	1264.2	1264.4	1263.3	1262.1	1260.9	1259.7
147.5°	1298.7	1300.0	1301.2	1301.3	1300.3	1299.3	1298.3	1297.3
150°	1322.1	1323.5	1324.9	1325.0	1323.8	1322.7	1321.5	1320.3
152.5°	1343.3	1344.8	1346.2	1346.1	1344.5	1343.0	1341.4	1339.9
155°	1372.0	1373.5	1374.9	1374.6	1372.7	1370.9	1369.0	1367.1
157.5°	1396.2	1397.8	1399.4	1399.3	1397.5	1395.6	1393.8	1391.9
160°	1410.3	1411.7	1413.1	1413.0	1411.4	1409.7	1408.1	1406.4
162.5°	1423.4	1425.0	1426.7	1426.4	1424.4	1422.4	1420.3	1418.3
165°	1439.5	1441.1	1442.8	1442.8	1441.1	1439.5	1437.8	1436.2
167.5°	1452.9	1454.5	1456.2	1455.9	1453.8	1451.7	1449.6	1447.4
170°	1459.7	1461.3	1463.0	1462.7	1460.6	1458.5	1456.4	1454.2
172.5°	1464.8	1466.4	1468.1	1467.9	1465.7	1463.6	1461.5	1459.3
175°	1470.3	1472.0	1473.6	1473.3	1470.9	1468.5	1466.2	1463.8
177.5°	1470.9	1472.2	1473.6	1473.4	1471.7	1470.0	1468.3	1466.6
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1

(END OF REPORT)