

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931490

Luminaire Tested: DFN2DS-TR4F0-060DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931490
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-060DS930-RLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4156.5 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 59.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931490

CATALOG NUMBER: DFN2DS-TR4F0-060DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931490

CATALOG NUMBER: DFN2DS-TR4F0-060DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1606	1606	1606
5°	1612	1585	1594
10°	1599	1560	1546
15°	1581	1513	1470
20°	1555	1447	1375
25°	1530	1372	1283
30°	1493	1295	1164
35°	1458	1212	1061
40°	1423	1125	941
45°	1381	1028	832
50°	1338	929	726
55°	1294	823	623
60°	1244	712	517
65°	1186	598	471
70°	1117	493	433
75°	1033	449	405
80°	912	401	368
85°	716	316	316

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1381 cd/sqm

TEST NUMBER: P931490

CATALOG NUMBER: DFN2DS-TR4F0-060DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.4	4.6
10°-20°	520.0	12.5
20°-30°	730.0	17.6
30°-40°	795.8	19.1
40°-50°	731.4	17.6
50°-60°	574.4	13.8
60°-70°	373.9	9.0
70°-80°	192.5	4.6
80°-90°	49.1	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1439.4	34.6
0°-40°	2235.2	53.8
0°-60°	3541.0	85.2
0°-90°	4156.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4156.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2021	2021	2021	2021	2021	
5°	2021	2012	1988	2005	1999	192
15°	1922	1902	1840	1805	1787	542
25°	1745	1686	1566	1491	1463	802
35°	1504	1410	1249	1134	1094	941
45°	1229	1106	915	784	741	949
55°	935	792	594	485	450	835
65°	631	483	318	256	250	626
75°	336	208	146	134	132	356
85°	79	40	35	35	35	94
90°	0	0	0	0	0	

TEST NUMBER: P931490

CATALOG NUMBER: DFN2DS-TR4F0-060DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2021.0	2021.0	2021.0	2021.0	2021.0
2.5°	2030.2	2021.0	2000.8	2019.2	2015.6
5°	2021.0	2011.9	1988.0	2004.6	1999.1
7.5°	2004.6	1993.7	1968.1	1975.2	1966.1
10°	1982.6	1969.8	1933.3	1927.7	1916.8
12.5°	1955.3	1938.7	1889.3	1878.4	1858.2
15°	1922.3	1902.0	1839.9	1805.2	1787.0
17.5°	1883.9	1854.5	1777.7	1737.5	1708.2
20°	1839.9	1803.3	1711.9	1666.3	1625.9
22.5°	1792.4	1750.3	1644.2	1582.1	1554.7
25°	1744.9	1686.3	1565.6	1490.7	1463.2
27.5°	1688.3	1625.9	1492.4	1406.4	1364.4
30°	1627.9	1558.2	1411.9	1318.8	1269.3
32.5°	1569.3	1485.1	1335.3	1225.4	1179.6
35°	1503.5	1410.2	1249.3	1134.0	1093.6
37.5°	1439.5	1338.7	1168.8	1042.5	996.8
40°	1371.7	1262.1	1084.5	954.7	907.2
42.5°	1302.3	1185.3	1000.5	865.0	819.5
45°	1229.1	1106.4	914.6	784.5	740.7
47.5°	1159.7	1029.8	832.3	702.3	662.1
50°	1082.8	953.0	751.8	625.4	587.2
52.5°	1007.7	870.5	674.9	554.2	519.5
55°	934.6	791.9	594.4	484.8	450.0
57.5°	859.7	713.3	523.1	420.7	391.4
60°	782.8	636.5	448.1	354.9	325.6
62.5°	707.9	561.6	384.0	296.3	281.7
65°	631.1	482.8	318.3	256.2	250.5
67.5°	557.9	409.6	256.2	224.9	219.5
70°	481.0	338.4	212.1	193.9	186.5
72.5°	407.9	272.5	177.3	162.8	159.1
75°	336.5	208.4	146.3	133.5	131.8
77.5°	265.3	148.1	115.2	107.9	104.2
80°	199.3	106.1	87.7	80.5	80.5
82.5°	139.0	71.4	60.3	56.6	56.6
85°	78.6	40.2	34.7	34.7	34.7
87.5°	29.3	14.6	14.6	12.8	12.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931490

CATALOG NUMBER: DFN2DS-TR4F0-060DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.88	14.40	13.24	14.71	15.03	8.84	10.36	9.21	10.68	10.99
	3H	14.64	16.01	15.02	16.34	16.70	10.11	11.47	10.48	11.80	12.16
	4H	15.31	16.59	15.71	16.94	17.32	10.61	11.89	11.01	12.24	12.62
	6H	15.80	16.98	16.21	17.35	17.74	10.99	12.17	11.40	12.54	12.93
	8H	15.97	17.09	16.39	17.48	17.88	11.11	12.24	11.54	12.63	13.03
	12H	16.07	17.15	16.50	17.53	17.96	11.19	12.27	11.62	12.65	13.08
4H	2H	12.98	14.26	13.38	14.61	14.99	9.54	10.82	9.94	11.17	11.54
	3H	14.92	15.98	15.33	16.38	16.78	10.98	12.04	11.39	12.44	12.84
	4H	15.67	16.62	16.10	17.04	17.48	11.58	12.54	12.01	12.95	13.39
	6H	16.26	17.09	16.72	17.53	17.99	12.07	12.90	12.52	13.34	13.80
	8H	16.47	17.25	16.94	17.69	18.16	12.23	13.01	12.69	13.45	13.92
	12H	16.63	17.32	17.11	17.80	18.27	12.35	13.04	12.83	13.52	13.99
8H	4H	15.69	16.47	16.15	16.91	17.38	11.93	12.71	12.40	13.15	13.62
	6H	16.33	16.97	16.82	17.46	17.94	12.52	13.16	13.02	13.65	14.13
	8H	16.58	17.16	17.09	17.66	18.15	12.74	13.32	13.25	13.83	14.31
	12H	16.78	17.29	17.29	17.78	18.35	12.92	13.43	13.43	13.92	14.48
12H	4H	15.67	16.37	16.16	16.85	17.32	11.98	12.67	12.46	13.15	13.62
	6H	16.31	16.89	16.82	17.40	17.88	12.58	13.16	13.10	13.67	14.16
	8H	16.59	17.10	17.10	17.60	18.16	12.85	13.36	13.36	13.86	14.42