

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931508

Luminaire Tested: DFN2DS-TR4F0-070DS930-RLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333882)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-070DS930-RLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4849.2 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931508

CATALOG NUMBER: DFN2DS-TR4F0-070DS930-RLL

Luminous Intensity Polar Plot



TEST NUMBER: P931508

CATALOG NUMBER: DFN2DS-TR4F0-070DS930-RLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	98	107	103	100	97	99	96	94		95	93	91		92
2	101	94	87	82	98	92	86	81	88	83	79		85	81	78		82
3	93	83	76	70	90	82	75	69	79	73	68		76	71	67		74
4	86	75	66	60	83	73	66	60	71	64	59		69	63	58		66
5	79	67	59	53	77	66	58	52	64	57	52		62	56	51		60
6	74	61	53	47	72	60	52	46	58	51	46		57	50	46		55
7	68	56	47	42	67	55	47	42	53	46	41		52	46	41		51
8	64	51	43	38	62	51	43	37	49	42	37		48	42	37		47
9	60	47	39	34	59	47	39	34	46	39	34		44	38	34		44
10	56	44	36	31	55	43	36	31	42	36	31		41	35	31		41

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1873	1873	1873
5°	1880	1850	1860
10°	1866	1819	1804
15°	1844	1765	1715
20°	1815	1688	1604
25°	1784	1601	1496
30°	1742	1511	1358
35°	1701	1414	1237
40°	1660	1312	1098
45°	1611	1199	971
50°	1561	1084	847
55°	1510	960	727
60°	1451	831	604
65°	1384	698	549
70°	1304	575	505
75°	1205	524	472
80°	1064	468	430
85°	836	369	369

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1611 cd/sqm

TEST NUMBER: P931508

CATALOG NUMBER: DFN2DS-TR4F0-070DS930-RLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.0	4.6
10°-20°	606.6	12.5
20°-30°	851.7	17.6
30°-40°	928.4	19.1
40°-50°	853.3	17.6
50°-60°	670.1	13.8
60°-70°	436.2	9.0
70°-80°	224.5	4.6
80°-90°	57.3	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1679.3	34.6
0°-40°	2607.7	53.8
0°-60°	4131.2	85.2
0°-90°	4849.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4849.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2358	2358	2358	2358	2358	
5°	2358	2347	2319	2339	2332	224
15°	2243	2219	2147	2106	2085	632
25°	2036	1967	1826	1739	1707	936
35°	1754	1645	1458	1323	1276	1098
45°	1434	1291	1067	915	864	1107
55°	1090	924	693	566	525	974
65°	736	563	371	299	292	730
75°	393	243	171	156	154	415
85°	92	47	40	40	40	110
90°	0	0	0	0	0	

TEST NUMBER: P931508

CATALOG NUMBER: DFN2DS-TR4F0-070DS930-RLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2357.9	2357.9	2357.9	2357.9	2357.9
2.5°	2368.5	2357.9	2334.3	2355.8	2351.5
5°	2357.9	2347.2	2319.4	2338.6	2332.3
7.5°	2338.6	2325.9	2296.1	2304.4	2293.8
10°	2313.1	2298.1	2255.5	2249.0	2236.3
12.5°	2281.1	2261.9	2204.2	2191.5	2167.9
15°	2242.6	2219.1	2146.6	2106.1	2084.9
17.5°	2197.8	2163.7	2074.0	2027.1	1992.9
20°	2146.6	2103.8	1997.2	1944.0	1896.9
22.5°	2091.2	2042.1	1918.2	1845.7	1813.9
25°	2035.7	1967.3	1826.5	1739.1	1707.0
27.5°	1969.6	1896.9	1741.2	1640.9	1591.8
30°	1899.2	1817.9	1647.2	1538.6	1480.9
32.5°	1830.8	1732.6	1557.8	1429.7	1376.2
35°	1754.0	1645.2	1457.5	1323.1	1276.0
37.5°	1679.4	1561.9	1363.6	1216.1	1163.0
40°	1600.3	1472.5	1265.3	1113.9	1058.4
42.5°	1519.3	1382.8	1167.2	1009.2	956.1
45°	1434.0	1290.9	1067.0	915.3	864.1
47.5°	1352.9	1201.5	971.0	819.3	772.5
50°	1263.2	1111.8	877.0	729.7	685.1
52.5°	1175.6	1015.6	787.4	646.5	606.0
55°	1090.3	923.9	693.4	565.5	525.0
57.5°	1002.9	832.2	610.4	490.8	456.6
60°	913.3	742.5	522.7	414.1	379.9
62.5°	825.8	655.2	448.0	345.7	328.7
65°	736.2	563.2	371.3	298.9	292.3
67.5°	650.9	477.9	298.9	262.3	256.1
70°	561.2	394.8	247.4	226.2	217.5
72.5°	475.9	317.8	206.9	190.0	185.7
75°	392.6	243.1	170.7	155.7	153.7
77.5°	309.5	172.7	134.5	125.8	121.6
80°	232.5	123.8	102.4	94.0	94.0
82.5°	162.1	83.3	70.4	66.1	66.1
85°	91.7	46.9	40.5	40.5	40.5
87.5°	34.1	17.0	17.0	14.9	14.9
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931508

CATALOG NUMBER: DFN2DS-TR4F0-070DS930-RLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.42	14.94	13.78	15.25	15.56	9.38	10.90	9.74	11.21	11.53
	3H	15.18	16.55	15.56	16.87	17.24	10.64	12.01	11.02	12.33	12.70
	4H	15.85	17.13	16.25	17.48	17.85	11.14	12.42	11.54	12.77	13.15
	6H	16.34	17.52	16.75	17.89	18.28	11.52	12.71	11.94	13.07	13.46
	8H	16.50	17.63	16.93	18.02	18.42	11.65	12.77	12.07	13.16	13.57
	12H	16.60	17.68	17.03	18.06	18.49	11.73	12.81	12.16	13.19	13.62
4H	2H	13.52	14.80	13.92	15.15	15.53	10.07	11.35	10.47	11.70	12.08
	3H	15.45	16.52	15.86	16.92	17.32	11.51	12.58	11.92	12.98	13.38
	4H	16.20	17.16	16.63	17.57	18.01	12.11	13.07	12.55	13.49	13.92
	6H	16.79	17.63	17.25	18.07	18.53	12.60	13.43	13.06	13.88	14.34
	8H	17.01	17.79	17.47	18.23	18.70	12.76	13.54	13.23	13.99	14.45
	12H	17.16	17.86	17.64	18.33	18.81	12.88	13.58	13.36	14.05	14.53
8H	4H	16.23	17.00	16.69	17.45	17.91	12.47	13.24	12.93	13.69	14.16
	6H	16.86	17.51	17.36	18.00	18.47	13.05	13.70	13.55	14.19	14.67
	8H	17.11	17.69	17.63	18.20	18.69	13.28	13.85	13.79	14.36	14.85
	12H	17.32	17.83	17.83	18.32	18.88	13.45	13.96	13.96	14.46	15.02
12H	4H	16.21	16.91	16.69	17.38	17.85	12.51	13.21	12.99	13.68	14.15
	6H	16.84	17.42	17.36	17.93	18.42	13.12	13.70	13.63	14.20	14.69
	8H	17.13	17.64	17.64	18.13	18.70	13.39	13.90	13.90	14.39	14.96

END OF REPORT