

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931525

Luminaire Tested: DFN2DS-TR4F0-080DS930-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931525
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-080DS930-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6454.8 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 81.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931525

CATALOG NUMBER: DFN2DS-TR4F0-080DS930-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931525

CATALOG NUMBER: DFN2DS-TR4F0-080DS930-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2015	2015	2015
5°	2023	1994	2006
10°	2011	1974	1984
15°	1986	1948	1946
20°	1951	1910	1908
25°	1916	1863	1863
30°	1871	1819	1804
35°	1829	1767	1741
40°	1776	1715	1682
45°	1724	1664	1623
50°	1667	1610	1553
55°	1608	1548	1490
60°	1542	1473	1419
65°	1472	1399	1334
70°	1383	1309	1247
75°	1258	1205	1176
80°	1117	1082	1027
85°	911	869	778

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1724 cd/sqm

TEST NUMBER: P931525

CATALOG NUMBER: DFN2DS-TR4F0-080DS930-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.8	3.7
10°-20°	671.8	10.4
20°-30°	987.3	15.3
30°-40°	1146.7	17.8
40°-50°	1145.3	17.7
50°-60°	998.7	15.5
60°-70°	738.2	11.4
70°-80°	417.7	6.5
80°-90°	110.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1898.0	29.4
0°-40°	3044.7	47.2
0°-60°	5188.6	80.4
0°-90°	6454.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6454.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2537	2537	2537	2537	2537	
5°	2537	2527	2500	2520	2515	241
15°	2415	2401	2369	2379	2366	680
25°	2186	2166	2125	2130	2125	1006
35°	1886	1862	1822	1808	1795	1178
45°	1535	1517	1481	1454	1444	1184
55°	1161	1146	1117	1088	1076	1038
65°	783	768	744	722	710	774
75°	410	405	393	378	383	437
85°	100	98	95	88	85	117
90°	0	0	0	0	0	

TEST NUMBER: P931525

CATALOG NUMBER: DFN2DS-TR4F0-080DS930-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2536.9	2536.9	2536.9	2536.9	2536.9
2.5°	2551.7	2539.5	2512.6	2536.9	2532.3
5°	2536.9	2527.4	2500.5	2519.9	2515.3
7.5°	2519.9	2505.4	2478.5	2498.1	2493.2
10°	2493.2	2476.1	2446.9	2466.3	2459.1
12.5°	2456.5	2442.0	2412.7	2424.9	2420.0
15°	2415.1	2400.6	2368.7	2378.6	2366.4
17.5°	2363.8	2349.3	2317.5	2329.7	2317.5
20°	2307.7	2293.2	2259.0	2266.3	2256.7
22.5°	2251.8	2229.8	2197.9	2197.9	2193.0
25°	2185.7	2166.4	2124.9	2129.6	2124.9
27.5°	2112.5	2095.4	2063.8	2056.6	2044.4
30°	2039.5	2019.8	1983.4	1976.1	1966.3
32.5°	1961.4	1946.9	1907.8	1893.0	1883.2
35°	1885.7	1861.5	1822.3	1807.6	1795.4
37.5°	1800.3	1778.3	1739.3	1722.2	1710.0
40°	1712.6	1692.9	1653.9	1632.1	1622.3
42.5°	1627.2	1607.5	1568.7	1544.1	1529.7
45°	1534.6	1517.4	1480.7	1454.0	1444.3
47.5°	1444.3	1427.1	1388.0	1361.1	1346.6
50°	1349.0	1336.8	1302.6	1268.5	1256.3
52.5°	1256.3	1239.2	1207.7	1180.8	1163.7
55°	1161.3	1146.5	1117.4	1088.1	1075.9
57.5°	1066.1	1054.0	1022.1	992.8	983.0
60°	970.8	961.3	927.1	900.2	892.9
62.5°	878.2	861.1	836.8	812.5	802.6
65°	783.2	768.5	744.1	722.1	709.9
67.5°	685.6	673.2	651.4	634.4	624.5
70°	595.3	585.4	563.5	546.4	536.8
72.5°	502.6	492.8	480.6	463.6	456.3
75°	409.7	405.1	392.7	378.2	383.0
77.5°	326.9	317.0	312.1	304.9	297.6
80°	244.1	241.5	236.6	229.3	224.4
82.5°	165.9	165.9	163.6	153.7	153.7
85°	99.9	97.6	95.3	87.8	85.4
87.5°	44.0	39.1	34.1	26.9	24.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931525

CATALOG NUMBER: DFN2DS-TR4F0-080DS930-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.72	15.33	14.08	15.64	15.96	13.27	14.88	13.64	15.20	15.51
	3H	15.47	16.92	15.84	17.25	17.61	14.98	16.43	15.35	16.76	17.12
	4H	16.11	17.48	16.51	17.83	18.21	15.62	16.99	16.02	17.34	17.71
	6H	16.58	17.85	16.99	18.22	18.61	16.08	17.35	16.49	17.71	18.11
	8H	16.73	17.94	17.15	18.33	18.73	16.22	17.43	16.65	17.82	18.22
	12H	16.82	17.98	17.25	18.36	18.79	16.30	17.46	16.73	17.85	18.27
4H	2H	14.28	15.65	14.68	16.00	16.37	13.92	15.29	14.32	15.64	16.02
	3H	16.25	17.40	16.66	17.80	18.20	15.85	16.99	16.26	17.39	17.79
	4H	17.03	18.07	17.46	18.48	18.92	16.61	17.64	17.04	18.06	18.49
	6H	17.63	18.53	18.08	18.97	19.43	17.19	18.10	17.65	18.54	19.00
	8H	17.82	18.66	18.28	19.10	19.57	17.38	18.22	17.84	18.67	19.13
	12H	17.95	18.71	18.43	19.18	19.65	17.50	18.26	17.98	18.73	19.20
8H	4H	17.30	18.15	17.76	18.59	19.06	16.93	17.78	17.39	18.22	18.68
	6H	18.02	18.72	18.51	19.21	19.68	17.64	18.34	18.13	18.83	19.30
	8H	18.28	18.91	18.79	19.41	19.90	17.88	18.52	18.39	19.02	19.51
	12H	18.48	19.03	18.98	19.52	20.09	18.06	18.62	18.57	19.11	19.67
12H	4H	17.33	18.09	17.81	18.56	19.03	16.96	17.72	17.44	18.20	18.67
	6H	18.06	18.69	18.57	19.20	19.69	17.69	18.33	18.20	18.83	19.32
	8H	18.38	18.93	18.88	19.43	19.99	18.00	18.56	18.51	19.05	19.61

END OF REPORT