

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331733

Luminaire Tested: **S122RDIP-S865D1080U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331733  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S865D1080U835-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6870.1 lumens  
Efficiency: N/A  
Efficacy: 105.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331733

CATALOG NUMBER: S122RDIP-S865D1080U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331733

CATALOG NUMBER: S122RDIP-S865D1080U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44																				
1	97	93	89	86	89	85	82	79	71	68	66	57	56	55	45	44	43	38																				
2	88	81	76	71	81	75	70	66	62	59	56	51	48	46	40	39	37	32																				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	40	36	34	32	28																				
4	74	64	56	50	68	59	52	47	49	45	41	41	37	34	33	30	28	24																				
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	30	27	25	21																				
6	63	51	44	38	58	47	41	36	40	35	31	33	29	26	27	24	22	19																				
7	58	46	39	33	53	43	36	31	37	31	27	30	26	24	25	22	20	17																				
8	54	42	35	30	50	39	33	28	33	28	24	28	24	21	23	20	18	15																				
9	50	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16	14																				
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15	13																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	23675	23675	23675
5°	23765	23378	23506
10°	23582	22996	22799
15°	23311	22313	21670
20°	22936	21340	20270
25°	22552	20236	18912
30°	22018	19099	17169
35°	21498	17864	15640
40°	20976	16585	13873
45°	20361	15150	12271
50°	19733	13700	10698
55°	19088	12141	9188
60°	18338	10498	7627
65°	17490	8821	6946
70°	16475	7265	6387
75°	15234	6625	5958
80°	13445	5923	5430
85°	10578	4668	4668



TEST NUMBER: P331733

CATALOG NUMBER: S122RDIP-S865D1080U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.2	2.0
10°-20°	376.8	5.5
20°-30°	529.2	7.7
30°-40°	577.1	8.4
40°-50°	530.6	7.7
50°-60°	416.7	6.1
60°-70°	271.7	4.0
70°-80°	140.1	2.0
80°-90°	41.8	0.6
90°-100°	87.2	1.3
100°-110°	270.9	3.9
110°-120°	463.1	6.7
120°-130°	608.9	8.9
130°-140°	683.5	9.9
140°-150°	670.1	9.8
150°-160°	562.1	8.2
160°-170°	372.8	5.4
170°-180°	130.3	1.9
0°-30°	1043.3	15.2
0°-40°	1620.3	23.6
0°-60°	2567.6	37.4
0°-90°	3021.2	44.0
90°-120°	821.2	12.0
90°-150°	2783.7	40.5
90°-180°	3849.0	56.0
0°-180°	6870.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1466	1466	1466	1466	1466	
5°	1466	1459	1442	1453	1450	139
15°	1395	1378	1335	1310	1296	393
25°	1266	1221	1136	1083	1062	582
35°	1091	1020	906	826	794	682
45°	892	800	664	573	537	688
55°	678	572	431	355	326	606
65°	458	350	231	188	182	454
75°	244	154	106	97	96	258
85°	57	31	25	25	25	67
90°	1	16	41	39	40	6
95°	60	72	74	74	72	69
105°	250	253	256	258	258	264
115°	465	471	469	468	465	459
125°	676	686	683	680	678	604
135°	875	887	890	888	885	675
145°	1062	1070	1077	1078	1073	663
155°	1214	1217	1221	1226	1223	558
165°	1321	1320	1320	1327	1322	372
175°	1374	1371	1368	1376	1370	130
180°	1376	1376	1376	1376	1376	



TEST NUMBER: P331733

CATALOG NUMBER: S122RDIP-S865D1080U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3
2.5°	1471.6	1470.4	1469.2	1468.0	1466.9	1465.0	1462.4	1459.8	1457.2	1454.6	1457.0
5°	1466.3	1464.8	1463.3	1461.8	1460.4	1457.7	1453.9	1450.1	1446.2	1442.4	1445.0
7.5°	1451.1	1449.3	1447.5	1445.7	1443.8	1440.7	1436.2	1431.7	1427.2	1422.7	1423.5
10°	1438.4	1436.3	1434.3	1432.2	1430.1	1426.2	1420.3	1414.4	1408.5	1402.6	1401.7
12.5°	1422.5	1419.9	1417.4	1414.9	1412.3	1407.3	1399.7	1392.2	1384.6	1377.1	1375.5
15°	1394.6	1391.4	1388.1	1384.9	1381.6	1375.0	1365.0	1355.0	1344.9	1334.9	1329.3
17.5°	1360.4	1355.4	1350.5	1345.5	1340.6	1331.7	1318.8	1305.9	1293.1	1280.2	1273.6
20°	1334.9	1329.0	1323.1	1317.2	1311.3	1301.0	1286.2	1271.5	1256.8	1242.0	1234.6
22.5°	1307.3	1300.7	1294.1	1287.5	1280.9	1269.3	1252.6	1236.0	1219.4	1202.7	1193.2
25°	1265.9	1256.5	1247.0	1237.6	1228.2	1213.7	1194.2	1174.8	1155.3	1135.9	1123.8
27.5°	1216.0	1205.7	1195.5	1185.2	1175.0	1158.9	1136.9	1115.0	1093.0	1071.1	1057.0
30°	1181.0	1169.8	1158.6	1147.4	1136.2	1118.8	1095.2	1071.6	1048.0	1024.4	1009.4
32.5°	1147.0	1133.9	1120.8	1107.7	1094.6	1076.1	1052.0	1027.9	1003.9	979.8	962.7
35°	1090.7	1075.7	1060.7	1045.6	1030.6	1010.1	984.1	958.2	932.3	906.3	887.7
37.5°	1034.5	1018.0	1001.5	984.9	968.4	946.3	918.7	891.0	863.4	835.7	815.2
40°	995.2	977.5	959.8	942.1	924.4	901.3	872.7	844.1	815.5	786.9	765.9
42.5°	954.9	936.2	917.6	899.0	880.3	856.2	826.7	797.1	767.6	738.0	716.4
45°	891.7	871.9	852.2	832.4	812.7	787.3	756.4	725.4	694.4	663.5	642.5
47.5°	830.1	809.2	788.3	767.3	746.4	719.9	688.0	656.0	624.0	592.1	571.3
50°	785.6	764.6	743.7	722.7	701.8	675.1	642.7	610.2	577.8	545.4	525.0
52.5°	742.0	720.1	698.3	676.4	654.5	627.7	596.0	564.2	532.5	500.8	481.1
55°	678.1	655.1	632.1	609.1	586.1	558.6	526.8	494.9	463.1	431.3	413.6
57.5°	612.5	588.9	565.3	541.7	518.2	491.1	460.4	429.8	399.2	368.6	352.4
60°	567.9	544.3	520.8	497.2	473.6	446.6	416.2	385.8	355.5	325.1	310.1
62.5°	524.4	500.8	477.2	453.6	430.0	403.8	374.8	345.9	316.9	287.9	273.6
65°	457.8	433.9	410.0	386.1	362.3	337.0	310.5	284.0	257.4	230.9	220.9
67.5°	393.6	369.9	346.2	322.4	298.7	274.9	251.1	227.2	203.3	179.4	174.8
70°	349.0	326.0	303.0	280.0	257.0	235.3	215.0	194.6	174.3	153.9	151.0
72.5°	306.5	284.5	262.4	240.4	218.3	199.1	182.8	166.4	150.1	133.8	131.3
75°	244.2	223.5	202.9	182.2	161.6	146.3	136.2	126.2	116.2	106.2	104.1
77.5°	182.9	164.7	146.6	128.5	110.4	99.0	94.1	89.3	84.5	79.6	78.4
80°	144.6	129.6	114.6	99.5	84.5	75.5	72.5	69.6	66.6	63.7	62.5
82.5°	109.6	97.9	86.1	74.4	62.7	55.8	53.8	51.8	49.8	47.8	47.1
85°	57.1	50.9	44.7	38.5	32.3	28.8	27.9	27.0	26.1	25.2	25.2
87.5°	17.2	15.9	14.7	13.4	12.1	12.1	13.2	14.4	15.5	16.6	16.3
90°	1.2	4.3	7.4	10.5	13.6	17.9	23.6	29.3	35.0	40.7	40.1
92.5°	20.7	22.9	25.2	27.5	29.8	31.6	32.9	34.3	35.6	36.9	37.0
95°	60.4	63.0	65.6	68.1	70.7	72.3	72.8	73.3	73.8	74.3	74.3
97.5°	110.4	112.6	114.9	117.2	119.4	121.1	122.0	123.0	124.0	125.0	125.0
100°	147.5	149.6	151.7	153.7	155.8	157.2	158.0	158.7	159.5	160.3	160.3
102.5°	186.6	188.2	189.9	191.5	193.2	194.5	195.5	196.4	197.4	198.4	198.6
105°	249.7	250.5	251.3	252.1	252.8	253.5	254.0	254.5	255.0	255.5	256.1
107.5°	313.4	314.5	315.7	316.8	317.9	318.5	318.5	318.5	318.5	318.5	318.7
110°	354.3	355.8	357.4	358.9	360.5	361.3	361.3	361.3	361.3	361.3	361.3



TEST NUMBER: P331733

CATALOG NUMBER: S122RDIP-S865D1080U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	398.9	400.4	402.0	403.5	405.1	405.8	405.5	405.3	405.1	404.9	404.3
115°	464.6	466.2	467.7	469.3	470.8	471.3	470.8	470.3	469.8	469.3	469.0
117.5°	530.1	532.2	534.3	536.3	538.4	538.7	537.3	535.8	534.4	532.9	532.3
120°	573.8	575.9	578.0	580.0	582.1	582.1	580.0	578.0	575.9	573.8	573.8
122.5°	613.8	616.3	618.7	621.2	623.7	624.2	622.8	621.3	619.9	618.4	617.8
125°	676.0	678.4	680.7	683.0	685.3	686.1	685.3	684.6	683.8	683.0	682.2
127.5°	736.7	739.6	742.6	745.5	748.4	749.5	748.5	747.6	746.7	745.7	744.8
130°	774.8	778.1	781.5	784.8	788.2	789.6	789.1	788.6	788.1	787.6	787.0
132.5°	817.5	820.3	823.0	825.7	828.5	829.9	830.0	830.1	830.2	830.3	829.2
135°	874.7	877.5	880.4	883.2	886.0	887.7	888.2	888.7	889.3	889.8	889.5
137.5°	934.8	937.2	939.5	941.8	944.1	945.6	946.3	947.0	947.6	948.3	948.1
140°	971.1	973.4	975.7	978.1	980.4	982.2	983.5	984.8	986.1	987.3	987.3
142.5°	1008.3	1010.6	1012.9	1015.2	1017.5	1019.1	1020.0	1020.9	1021.8	1022.7	1022.9
145°	1061.7	1063.5	1065.3	1067.1	1068.9	1070.6	1072.1	1073.7	1075.2	1076.8	1077.0
147.5°	1109.3	1111.5	1113.6	1115.8	1118.0	1119.6	1120.6	1121.7	1122.7	1123.7	1124.3
150°	1141.8	1143.4	1144.9	1146.5	1148.0	1149.3	1150.4	1151.4	1152.4	1153.5	1154.2
152.5°	1170.6	1172.2	1173.7	1175.3	1176.8	1178.2	1179.5	1180.7	1182.0	1183.2	1184.2
155°	1213.9	1214.6	1215.4	1216.2	1217.0	1217.7	1218.5	1219.3	1220.1	1220.8	1222.1
157.5°	1250.8	1251.3	1251.8	1252.3	1252.9	1253.3	1253.8	1254.3	1254.7	1255.2	1257.0
160°	1273.1	1273.6	1274.1	1274.6	1275.2	1275.5	1275.8	1276.1	1276.3	1276.6	1278.1
162.5°	1293.5	1293.6	1293.7	1293.8	1294.0	1294.1	1294.4	1294.6	1294.9	1295.2	1296.9
165°	1320.7	1320.5	1320.2	1319.9	1319.7	1319.6	1319.6	1319.6	1319.6	1319.6	1321.4
167.5°	1343.5	1342.7	1341.9	1341.2	1340.4	1340.0	1339.9	1339.9	1339.8	1339.8	1341.6
170°	1355.6	1354.8	1354.0	1353.2	1352.5	1352.0	1351.7	1351.4	1351.2	1350.9	1352.7
172.5°	1363.9	1363.2	1362.4	1361.6	1360.8	1360.3	1360.1	1359.8	1359.5	1359.3	1361.1
175°	1374.2	1373.4	1372.6	1371.8	1371.1	1370.4	1369.9	1369.4	1368.9	1368.3	1370.2
177.5°	1378.3	1377.7	1377.1	1376.5	1375.9	1375.3	1374.9	1374.5	1374.1	1373.7	1374.9
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5



TEST NUMBER: P331733

CATALOG NUMBER: S122RDIP-S865D1080U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3	1466.3
2.5°	1459.3	1461.7	1464.0	1465.0	1464.5	1464.0	1463.6	1463.1
5°	1447.7	1450.3	1453.0	1453.9	1453.0	1452.1	1451.2	1450.3
7.5°	1424.3	1425.0	1425.8	1425.4	1423.9	1422.4	1420.8	1419.3
10°	1400.8	1399.9	1399.0	1397.7	1395.9	1394.2	1392.4	1390.6
12.5°	1373.9	1372.3	1370.7	1368.5	1365.5	1362.6	1359.6	1356.7
15°	1323.7	1318.1	1312.5	1308.2	1305.3	1302.3	1299.4	1296.4
17.5°	1266.9	1260.2	1253.6	1247.7	1242.6	1237.6	1232.5	1227.4
20°	1227.3	1219.9	1212.5	1205.6	1199.1	1192.6	1186.1	1179.7
22.5°	1183.8	1174.3	1164.8	1157.6	1152.8	1147.9	1143.1	1138.3
25°	1111.7	1099.6	1087.5	1079.2	1074.8	1070.4	1066.0	1061.6
27.5°	1042.9	1028.8	1014.7	1004.2	997.2	990.1	983.1	976.1
30°	994.3	979.3	964.2	952.7	944.8	936.8	928.9	920.9
32.5°	945.5	928.3	911.2	898.8	891.4	883.9	876.4	868.9
35°	869.1	850.6	832.0	819.5	813.0	806.5	800.0	793.5
37.5°	794.8	774.3	753.9	739.9	732.5	725.0	717.6	710.2
40°	745.0	724.1	703.1	688.8	681.2	673.5	665.8	658.2
42.5°	694.8	673.1	651.5	636.9	629.5	622.1	614.6	607.2
45°	621.6	600.7	579.7	565.7	558.6	551.6	544.5	537.4
47.5°	550.4	529.6	508.8	495.2	488.8	482.3	475.9	469.5
50°	504.7	484.3	464.0	450.7	444.5	438.3	432.1	425.9
52.5°	461.5	441.9	422.2	409.6	403.8	398.1	392.4	386.7
55°	395.9	378.2	360.5	348.8	343.2	337.6	332.0	326.4
57.5°	336.2	320.0	303.8	293.3	288.6	283.8	279.1	274.4
60°	295.0	280.0	264.9	255.1	250.3	245.6	240.9	236.2
62.5°	259.3	245.0	230.6	222.0	219.2	216.4	213.5	210.7
65°	210.8	200.8	190.8	185.3	184.4	183.6	182.7	181.8
67.5°	170.2	165.6	161.0	158.2	157.3	156.3	155.4	154.5
70°	148.0	145.1	142.1	140.1	138.9	137.7	136.5	135.3
72.5°	128.8	126.3	123.8	122.3	121.5	120.8	120.1	119.4
75°	102.0	100.0	97.9	96.7	96.4	96.1	95.8	95.5
77.5°	77.3	76.1	74.9	74.1	73.6	73.1	72.7	72.2
80°	61.3	60.2	59.0	58.4	58.4	58.4	58.4	58.4
82.5°	46.4	45.6	44.9	44.6	44.6	44.6	44.6	44.6
85°	25.2	25.2	25.2	25.2	25.2	25.2	25.2	25.2
87.5°	15.9	15.6	15.3	15.1	15.2	15.2	15.3	15.3
90°	39.6	39.1	38.6	38.5	38.7	39.0	39.2	39.5
92.5°	37.1	37.2	37.4	37.4	37.5	37.5	37.6	37.6
95°	74.3	74.3	74.3	74.1	73.6	73.1	72.5	72.0
97.5°	125.0	125.0	125.0	125.0	124.9	124.9	124.8	124.8
100°	160.3	160.3	160.3	160.2	159.9	159.7	159.4	159.1
102.5°	198.8	199.0	199.2	199.2	198.9	198.7	198.4	198.2
105°	256.6	257.1	257.6	257.9	257.9	257.9	257.9	257.9
107.5°	318.9	319.1	319.3	318.8	317.7	316.5	315.3	314.1
110°	361.3	361.3	361.3	360.9	360.1	359.3	358.5	357.8





TEST NUMBER: P331733

CATALOG NUMBER: S122RDIP-S865D1080U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	403.7	403.1	402.5	401.9	401.3	400.7	400.2	399.6
115°	468.8	468.5	468.2	467.7	467.0	466.2	465.4	464.6
117.5°	531.7	531.1	530.5	529.8	529.0	528.2	527.4	526.7
120°	573.8	573.8	573.8	573.4	572.7	571.9	571.1	570.3
122.5°	617.2	616.6	615.9	615.4	614.8	614.2	613.7	613.1
125°	681.5	680.7	679.9	679.4	679.1	678.9	678.6	678.4
127.5°	743.9	742.9	742.0	741.1	740.3	739.5	738.7	737.8
130°	786.5	786.0	785.5	784.7	783.7	782.6	781.6	780.6
132.5°	828.0	826.9	825.8	824.8	824.0	823.1	822.3	821.5
135°	889.3	889.0	888.7	888.2	887.4	886.7	885.9	885.1
137.5°	947.9	947.7	947.5	946.9	945.8	944.8	943.8	942.7
140°	987.3	987.3	987.3	986.8	985.8	984.8	983.7	982.7
142.5°	1023.1	1023.3	1023.5	1023.1	1022.0	1021.0	1020.0	1018.9
145°	1077.3	1077.6	1077.8	1077.4	1076.4	1075.4	1074.3	1073.3
147.5°	1124.9	1125.4	1126.0	1125.8	1124.8	1123.8	1122.8	1121.9
150°	1155.0	1155.8	1156.6	1156.6	1155.8	1155.0	1154.2	1153.5
152.5°	1185.2	1186.1	1187.1	1187.1	1186.1	1185.2	1184.2	1183.2
155°	1223.4	1224.7	1226.0	1226.2	1225.5	1224.7	1223.9	1223.1
157.5°	1258.7	1260.5	1262.2	1262.5	1261.2	1260.0	1258.8	1257.5
160°	1279.7	1281.2	1282.8	1283.0	1282.0	1281.0	1279.9	1278.9
162.5°	1298.7	1300.4	1302.2	1302.4	1301.2	1300.0	1298.7	1297.5
165°	1323.2	1325.0	1326.8	1327.0	1325.8	1324.5	1323.2	1321.9
167.5°	1343.4	1345.2	1347.0	1347.2	1345.9	1344.5	1343.2	1341.9
170°	1354.5	1356.3	1358.1	1358.3	1356.7	1355.2	1353.6	1352.1
172.5°	1362.9	1364.7	1366.5	1366.6	1365.1	1363.5	1362.0	1360.4
175°	1372.0	1373.8	1375.6	1375.7	1374.2	1372.6	1371.1	1369.5
177.5°	1376.2	1377.4	1378.6	1378.6	1377.4	1376.2	1374.9	1373.7
180°	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5	1376.5

(END OF REPORT)