

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331718

Luminaire Tested: **S122RDIP-S865D725U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331718  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S865D725U835-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5893.8 lumens  
Efficiency: N/A  
Efficacy: 108.3 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56				56
1	100	96	92	89	93	89	86	84	77	75	73	66	65	63	56	55	54				49	
2	92	85	79	74	85	79	74	70	69	65	62	59	56	54	50	48	47				42	
3	84	75	69	63	78	71	65	60	62	57	53	53	50	47	45	43	41				37	
4	78	68	60	54	72	63	57	52	55	50	46	48	44	41	41	38	36				33	
5	72	61	53	47	67	57	50	45	50	45	41	44	40	36	38	35	32				29	
6	67	55	47	42	62	52	45	40	46	40	36	40	36	32	35	31	29				26	
7	62	50	42	37	58	47	40	35	42	36	32	37	32	29	32	29	26				24	
8	58	46	38	33	54	43	37	32	38	33	29	34	30	26	30	26	24				22	
9	54	42	35	30	50	40	33	29	36	30	26	31	27	24	28	24	22				20	
10	51	39	32	27	47	37	30	26	33	28	24	29	25	22	26	22	20				18	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	30832	30832	30832	30832
5°	34434	31024	27509	31024
10°	38203	30808	23845	30808
15°	40082	30355	18788	30355
20°	34749	29687	16258	29687
25°	22789	28771	14516	28771
30°	15340	27660	13136	27660
35°	12423	26260	11848	26260
40°	11049	24738	10964	24738
45°	9999	22952	9787	22952
50°	9100	21182	9065	21182
55°	8555	19220	8442	19220
60°	7156	17418	7072	17418
65°	6032	15817	6842	15817
70°	5575	14124	6453	14124
75°	5215	12296	5958	12296
80°	4816	10116	5309	10116
85°	4428	7984	4668	7984



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	181.0	3.1
10°-20°	504.4	8.6
20°-30°	650.0	11.0
30°-40°	617.7	10.5
40°-50°	529.1	9.0
50°-60°	402.9	6.8
60°-70°	254.7	4.3
70°-80°	127.2	2.2
80°-90°	36.8	0.6
90°-100°	58.7	1.0
100°-110°	182.3	3.1
110°-120°	311.6	5.3
120°-130°	409.8	7.0
130°-140°	459.9	7.8
140°-150°	450.9	7.7
150°-160°	378.2	6.4
160°-170°	250.9	4.3
170°-180°	87.7	1.5
0°-30°	1335.4	22.7
0°-40°	1953.1	33.1
0°-60°	2885.1	49.0
0°-90°	3303.9	56.1
90°-120°	552.6	9.4
90°-150°	1873.2	31.8
90°-180°	2590.0	43.9
0°-180°	5893.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1910	1910	1910	1910	1910	
5°	2125	1914	1697	1914	2125	210
15°	2398	1816	1124	1816	2398	647
25°	1279	1615	815	1615	1279	607
35°	630	1332	601	1332	630	403
45°	438	1005	429	1005	438	339
55°	304	683	300	683	304	267
65°	158	414	179	414	158	161
75°	84	197	96	197	84	89
85°	24	43	25	43	24	26
90°	27	1	27	1	27	13
95°	48	41	48	41	48	54
105°	174	168	174	168	174	182
115°	313	313	313	313	313	309
125°	456	455	456	455	456	407
135°	596	589	596	589	596	458
145°	722	714	722	714	722	451
155°	823	817	823	817	823	379
165°	890	889	890	889	890	251
175°	922	925	922	925	922	88
180°	926	926	926	926	926	



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1987.1	1988.7	1990.3	1986.5	1986.5	1983.4	1976.5	1971.2	1956.3	1954.2	1954.2
5°	2124.6	2123.2	2125.9	2117.3	2105.3	2102.7	2090.1	2073.5	2056.2	2037.0	2033.0
7.5°	2261.2	2259.2	2253.9	2252.5	2243.3	2223.3	2203.0	2181.4	2152.7	2124.7	2110.6
10°	2330.2	2352.1	2338.9	2315.6	2320.3	2289.1	2272.5	2244.0	2220.1	2178.3	2169.0
12.5°	2398.2	2406.8	2402.6	2389.4	2383.5	2361.8	2339.4	2314.6	2270.5	2233.0	2200.3
15°	2397.9	2410.5	2413.8	2409.9	2413.2	2411.9	2399.9	2379.3	2340.9	2299.7	2263.9
17.5°	2220.9	2229.7	2251.4	2266.1	2284.7	2324.0	2343.4	2350.9	2345.2	2321.7	2296.5
20°	2022.4	2007.8	2068.8	2100.0	2126.5	2192.9	2250.0	2271.9	2307.0	2306.4	2299.7
22.5°	1741.0	1744.5	1802.4	1839.4	1916.9	1983.2	2048.3	2130.7	2198.7	2243.7	2270.0
25°	1279.2	1304.5	1362.2	1412.6	1498.9	1622.3	1734.4	1864.5	1987.2	2084.1	2176.3
27.5°	960.8	962.6	1008.4	1055.0	1106.2	1207.3	1348.5	1503.8	1678.8	1823.2	1989.3
30°	822.8	818.8	838.0	866.5	910.3	988.6	1094.8	1247.4	1421.9	1639.5	1833.3
32.5°	725.1	725.3	739.8	760.9	797.3	850.1	922.8	1046.8	1211.7	1425.6	1652.8
35°	630.3	629.7	640.3	655.5	670.8	704.6	754.4	819.4	932.9	1132.6	1364.8
37.5°	562.4	565.3	570.5	580.0	596.9	615.7	645.6	689.3	770.1	888.2	1083.4
40°	524.2	525.5	532.8	540.8	550.7	565.3	589.9	625.0	684.1	778.3	920.9
42.5°	489.1	490.5	495.6	503.1	510.9	525.5	545.8	576.2	624.1	697.6	815.3
45°	437.9	437.9	442.6	445.9	454.5	467.8	484.4	509.6	542.7	597.2	675.5
47.5°	389.9	390.0	393.1	398.8	404.2	414.6	430.9	451.5	475.6	517.7	584.6
50°	362.3	362.9	364.9	369.6	372.9	382.2	394.8	412.7	437.9	470.4	526.2
52.5°	340.0	339.6	342.1	344.1	346.4	353.0	362.4	378.2	400.8	429.0	475.2
55°	303.9	301.2	305.2	308.5	310.5	313.2	318.5	328.4	347.7	371.6	406.1
57.5°	258.8	257.7	260.5	263.5	269.8	276.9	281.5	287.8	297.8	314.9	349.1
60°	221.6	221.6	227.6	229.6	236.9	246.2	255.5	260.8	270.7	282.0	307.2
62.5°	188.7	189.2	192.0	194.0	198.1	209.5	222.5	234.2	243.6	254.4	271.1
65°	157.9	159.2	159.2	160.6	163.2	165.9	171.2	180.5	197.1	212.3	224.9
67.5°	134.0	134.4	134.8	136.2	136.8	139.7	141.9	146.0	149.8	164.3	179.9
70°	118.1	120.1	119.4	120.8	121.4	122.7	125.4	127.4	133.4	136.7	146.0
72.5°	103.2	104.7	104.6	105.4	107.1	107.4	109.5	111.5	115.3	118.1	123.1
75°	83.6	82.9	83.6	84.9	85.6	86.3	86.3	88.9	90.9	93.6	96.9
77.5°	64.5	65.2	65.0	65.2	65.3	66.5	66.4	67.5	69.5	70.9	72.5
80°	51.8	52.4	51.8	52.4	53.1	53.7	53.1	53.7	55.7	57.1	57.1
82.5°	40.1	40.2	40.6	40.7	40.9	41.0	41.9	42.1	43.5	43.3	43.8
85°	23.9	23.2	23.2	23.2	23.9	24.5	23.9	23.9	24.5	24.5	24.5
87.5°	13.8	14.3	14.3	14.2	14.2	14.2	14.3	14.9	14.4	15.0	13.7
90°	26.6	26.4	26.2	26.1	25.9	26.0	26.3	26.7	27.0	27.4	23.5
92.5°	25.3	25.3	25.3	25.2	25.2	25.1	25.1	25.0	24.9	24.9	24.0
95°	48.5	48.8	49.2	49.5	49.9	50.0	50.0	50.0	50.0	50.0	49.7
97.5°	83.9	84.0	84.0	84.1	84.1	84.1	84.1	84.1	84.1	84.1	83.4
100°	107.1	107.3	107.4	107.6	107.8	107.9	107.9	107.9	107.9	107.9	107.3
102.5°	133.3	133.5	133.7	133.9	134.0	134.1	133.9	133.8	133.6	133.5	132.8
105°	173.5	173.5	173.5	173.5	173.5	173.4	173.0	172.7	172.3	172.0	171.6
107.5°	211.4	212.2	213.0	213.8	214.6	214.9	214.7	214.6	214.5	214.3	214.3
110°	240.7	241.3	241.8	242.3	242.8	243.1	243.1	243.1	243.1	243.1	243.1



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	268.9	269.3	269.6	270.0	270.4	270.8	271.2	271.6	272.1	272.5	272.6
115°	312.7	313.2	313.7	314.2	314.7	315.1	315.3	315.4	315.6	315.8	316.1
117.5°	354.4	354.9	355.4	356.0	356.5	356.9	357.4	357.8	358.2	358.6	359.6
120°	383.8	384.3	384.8	385.3	385.9	386.1	386.1	386.1	386.1	386.1	387.5
122.5°	412.6	412.9	413.3	413.7	414.1	414.5	414.9	415.3	415.7	416.1	417.1
125°	456.5	456.7	456.8	457.0	457.2	457.5	458.0	458.6	459.1	459.6	460.1
127.5°	496.5	497.1	497.6	498.2	498.7	499.3	499.9	500.6	501.2	501.8	502.4
130°	525.3	526.0	526.7	527.3	528.0	528.6	528.9	529.3	529.6	530.0	530.3
132.5°	552.8	553.3	553.9	554.4	555.0	555.7	556.4	557.2	558.0	558.7	558.6
135°	595.6	596.1	596.7	597.2	597.7	598.0	598.2	598.4	598.6	598.7	598.4
137.5°	634.4	635.1	635.8	636.5	637.2	637.6	637.7	637.9	638.0	638.1	637.7
140°	661.3	662.0	662.7	663.4	664.0	664.4	664.4	664.4	664.4	664.4	663.5
142.5°	685.7	686.4	687.0	687.7	688.4	688.7	688.6	688.4	688.3	688.2	687.6
145°	722.2	722.9	723.6	724.3	725.0	725.3	725.1	724.9	724.8	724.6	723.5
147.5°	754.9	755.6	756.2	756.9	757.6	757.7	757.3	756.9	756.5	756.2	755.5
150°	776.2	776.7	777.2	777.7	778.3	778.3	777.7	777.2	776.7	776.2	775.5
152.5°	796.2	796.8	797.5	798.2	798.8	798.8	798.2	797.5	796.8	796.2	795.3
155°	823.1	823.6	824.1	824.6	825.2	825.0	824.1	823.2	822.4	821.5	821.0
157.5°	846.2	847.0	847.9	848.7	849.5	849.4	848.2	847.0	845.8	844.6	844.3
160°	860.6	861.3	862.0	862.7	863.4	863.2	862.2	861.1	860.1	859.0	858.9
162.5°	873.1	873.9	874.8	875.6	876.4	876.3	875.1	873.9	872.7	871.5	871.4
165°	889.5	890.4	891.2	892.1	893.0	892.8	891.6	890.4	889.2	887.9	887.9
167.5°	903.0	903.9	904.8	905.7	906.6	906.4	905.2	904.0	902.8	901.5	901.6
170°	909.8	910.9	911.9	913.0	914.0	913.9	912.7	911.5	910.3	909.0	909.2
172.5°	915.5	916.5	917.5	918.6	919.6	919.5	918.3	917.1	915.9	914.7	914.9
175°	921.6	922.6	923.6	924.7	925.7	925.6	924.4	923.2	922.0	920.8	921.1
177.5°	924.4	925.2	926.0	926.9	927.7	927.7	926.9	926.0	925.2	924.4	924.6
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1955.2	1951.0	1947.3	1937.7	1932.9	1922.3	1920.7	1920.2	1906.4	1893.1	1889.4
5°	2022.4	2011.8	1995.8	1977.3	1958.0	1938.1	1924.8	1914.2	1887.7	1862.5	1847.9
7.5°	2090.1	2067.2	2039.8	2004.6	1975.3	1942.4	1917.9	1896.0	1858.4	1822.3	1798.0
10°	2140.5	2103.3	2066.8	2018.4	1980.6	1943.4	1908.9	1879.1	1836.6	1788.8	1755.0
12.5°	2171.8	2130.9	2080.6	2033.3	1984.3	1937.0	1890.9	1852.5	1802.6	1753.3	1713.0
15°	2214.1	2170.3	2109.3	2041.6	1978.6	1916.9	1863.8	1816.0	1751.0	1691.9	1642.8
17.5°	2248.8	2188.5	2123.0	2044.7	1971.7	1893.3	1824.9	1763.9	1691.5	1620.3	1562.4
20°	2259.9	2200.2	2124.6	2046.3	1960.0	1867.8	1794.1	1727.8	1650.1	1572.5	1506.2
22.5°	2253.0	2206.6	2122.4	2028.7	1940.4	1843.9	1760.7	1683.7	1597.6	1518.4	1441.4
25°	2206.2	2190.2	2110.6	2008.4	1907.6	1795.5	1699.2	1615.0	1516.8	1431.9	1348.2
27.5°	2097.0	2131.3	2082.0	1973.1	1861.0	1740.8	1632.6	1536.7	1434.8	1339.2	1255.9
30°	1991.9	2070.8	2049.6	1948.7	1823.3	1705.2	1583.8	1483.6	1374.8	1276.6	1194.3
32.5°	1848.0	1978.4	1999.2	1914.8	1785.1	1655.3	1528.1	1428.4	1314.8	1211.3	1131.1
35°	1619.0	1814.0	1903.6	1849.9	1719.8	1579.8	1448.4	1332.3	1218.2	1116.0	1036.4
37.5°	1345.7	1611.4	1760.7	1764.5	1645.1	1499.5	1356.5	1241.2	1124.4	1024.1	937.9
40°	1168.4	1456.4	1650.8	1693.9	1593.1	1435.8	1291.2	1173.7	1059.6	961.4	862.6
42.5°	1009.2	1296.1	1535.1	1610.1	1529.9	1373.7	1228.6	1105.8	994.9	902.0	801.0
45°	816.1	1066.9	1330.3	1464.4	1419.9	1275.3	1122.0	1005.2	901.0	820.8	723.9
47.5°	688.5	865.2	1120.1	1301.4	1300.6	1168.6	1017.8	906.0	809.3	734.1	655.7
50°	615.7	769.7	985.3	1191.0	1208.2	1097.4	954.1	843.3	753.1	674.1	611.1
52.5°	550.4	677.3	871.2	1068.4	1117.5	1021.5	882.5	780.2	692.6	620.0	566.0
55°	465.1	563.3	710.6	895.1	969.4	901.7	778.3	682.8	611.8	550.7	504.3
57.5°	393.5	467.1	585.3	733.8	820.4	777.8	676.0	598.4	537.6	482.4	445.7
60°	348.3	408.7	508.9	633.0	728.5	698.7	611.8	539.4	487.7	439.9	405.4
62.5°	305.9	357.8	443.6	544.3	631.9	619.6	548.6	487.9	442.6	399.0	369.8
65°	246.2	284.0	351.0	430.0	500.3	506.3	455.2	414.0	373.6	339.1	313.2
67.5°	196.0	220.7	267.9	334.4	387.1	405.9	374.7	343.3	311.2	284.5	262.1
70°	165.2	185.1	219.6	273.4	321.8	341.7	323.8	299.2	271.4	249.5	230.2
72.5°	133.9	153.3	178.7	218.2	259.7	281.2	275.0	257.3	234.7	216.6	198.4
75°	100.9	106.8	124.1	150.6	183.1	201.7	206.4	197.1	179.1	165.2	154.6
77.5°	74.6	78.2	86.4	100.3	121.6	138.1	144.9	143.8	131.5	123.4	113.5
80°	59.7	61.7	65.7	71.7	87.6	104.2	108.8	108.8	100.2	96.9	86.9
82.5°	45.4	46.8	49.2	52.5	60.0	74.4	79.6	80.7	75.2	70.9	63.0
85°	25.9	25.2	26.5	28.5	29.9	33.8	41.8	43.1	41.8	36.5	34.5
87.5°	13.0	12.7	12.0	10.8	11.0	11.1	13.3	15.5	13.8	12.7	12.0
90°	19.7	15.9	12.1	9.1	7.0	5.0	2.9	0.8	2.9	5.0	7.0
92.5°	23.0	22.1	21.2	20.0	18.5	17.0	15.4	13.9	15.4	17.0	18.5
95°	49.3	49.0	48.6	47.6	45.9	44.1	42.4	40.6	42.4	44.1	45.9
97.5°	82.8	82.1	81.5	80.4	78.8	77.3	75.8	74.3	75.8	77.3	78.8
100°	106.8	106.3	105.8	104.8	103.4	102.0	100.7	99.3	100.7	102.0	103.4
102.5°	132.2	131.5	130.9	130.0	128.9	127.8	126.6	125.5	126.6	127.8	128.9
105°	171.3	170.9	170.6	170.1	169.6	169.1	168.6	168.1	168.6	169.1	169.6
107.5°	214.3	214.3	214.3	213.9	213.2	212.4	211.7	210.9	211.7	212.4	213.2
110°	243.1	243.1	243.1	242.6	241.5	240.5	239.4	238.4	239.4	240.5	241.5





TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	272.8	272.9	273.0	272.6	271.5	270.5	269.5	268.4	269.5	270.5	271.5
115°	316.5	316.8	317.2	316.8	315.8	314.7	313.7	312.7	313.7	314.7	315.8
117.5°	360.6	361.5	362.5	362.3	360.9	359.5	358.1	356.7	358.1	359.5	360.9
120°	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1	387.5	388.9	390.3
122.5°	418.1	419.1	420.0	419.7	418.0	416.4	414.7	413.0	414.7	416.4	418.0
125°	460.6	461.2	461.7	461.2	459.6	458.0	456.5	454.9	456.5	458.0	459.6
127.5°	503.1	503.7	504.3	503.6	501.7	499.7	497.7	495.7	497.7	499.7	501.7
130°	530.6	531.0	531.3	530.4	528.1	525.9	523.6	521.4	523.6	525.9	528.1
132.5°	558.6	558.5	558.4	557.5	555.6	553.8	552.0	550.1	552.0	553.8	555.6
135°	598.0	597.7	597.3	596.2	594.3	592.4	590.5	588.6	590.5	592.4	594.3
137.5°	637.2	636.8	636.3	635.3	633.8	632.2	630.6	629.1	630.6	632.2	633.8
140°	662.7	661.8	660.9	659.7	658.1	656.6	655.0	653.5	655.0	656.6	658.1
142.5°	687.0	686.4	685.8	684.7	683.2	681.6	680.0	678.5	680.0	681.6	683.2
145°	722.5	721.5	720.4	719.3	718.1	716.9	715.6	714.4	715.6	716.9	718.1
147.5°	754.8	754.1	753.4	752.3	750.8	749.4	747.9	746.5	747.9	749.4	750.8
150°	774.8	774.1	773.4	772.5	771.5	770.4	769.4	768.4	769.4	770.4	771.5
152.5°	794.5	793.7	792.8	791.9	790.9	789.8	788.8	787.7	788.8	789.8	790.9
155°	820.5	819.9	819.4	818.9	818.4	817.9	817.3	816.8	817.3	817.9	818.4
157.5°	844.0	843.7	843.4	843.1	842.7	842.4	842.0	841.7	842.0	842.4	842.7
160°	858.7	858.5	858.3	858.1	857.7	857.4	857.0	856.7	857.0	857.4	857.7
162.5°	871.2	871.0	870.8	870.7	870.6	870.6	870.5	870.4	870.5	870.6	870.6
165°	887.9	887.9	887.9	888.0	888.2	888.4	888.6	888.7	888.6	888.4	888.2
167.5°	901.6	901.7	901.7	902.0	902.5	903.0	903.5	904.0	903.5	903.0	902.5
170°	909.4	909.6	909.7	910.1	910.6	911.1	911.7	912.2	911.7	911.1	910.6
172.5°	915.0	915.2	915.4	915.7	916.2	916.8	917.3	917.8	917.3	916.8	916.2
175°	921.5	921.8	922.2	922.6	923.1	923.6	924.2	924.7	924.2	923.6	923.1
177.5°	924.9	925.2	925.5	925.8	926.2	926.7	927.1	927.5	927.1	926.7	926.2
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1882.5	1878.8	1871.9	1861.3	1854.9	1843.8	1836.3	1840.6	1841.6	1840.6	1839.5
5°	1831.9	1818.0	1798.8	1780.2	1762.9	1744.4	1733.7	1729.1	1719.8	1714.5	1711.9
7.5°	1770.8	1746.8	1719.5	1687.2	1659.7	1630.9	1616.2	1608.9	1589.9	1579.5	1570.5
10°	1725.1	1687.3	1660.1	1617.6	1591.8	1553.9	1528.1	1528.7	1502.8	1488.2	1477.6
12.5°	1674.7	1633.2	1587.9	1549.7	1513.7	1483.3	1452.2	1439.5	1412.1	1398.0	1369.3
15°	1591.1	1542.7	1494.9	1443.1	1406.6	1359.5	1314.4	1259.3	1214.9	1176.4	1165.8
17.5°	1499.8	1439.8	1391.9	1331.1	1268.6	1189.4	1137.1	1105.1	1078.3	1058.0	1042.9
20°	1437.2	1376.1	1325.0	1233.5	1149.2	1095.5	1057.0	1032.4	1004.6	982.7	970.7
22.5°	1371.3	1307.6	1238.0	1135.8	1070.1	1027.0	992.7	964.5	945.6	928.5	917.6
25°	1277.9	1208.2	1093.5	1023.1	970.0	924.9	901.0	883.8	863.9	840.7	830.0
27.5°	1179.2	1068.4	986.0	933.7	883.0	853.7	832.2	806.4	788.6	778.2	767.1
30°	1105.4	994.6	930.2	873.2	837.3	804.8	779.6	765.0	747.8	729.9	722.6
32.5°	1023.1	934.6	872.9	825.4	789.0	761.3	741.4	717.8	705.3	694.3	679.0
35°	920.9	853.9	797.5	759.1	724.6	702.0	678.8	664.8	642.3	633.0	627.0
37.5°	834.4	776.3	734.2	693.6	666.3	641.3	627.1	605.0	595.2	582.3	569.7
40°	785.6	728.5	688.1	654.9	624.4	605.8	587.9	570.0	555.4	549.4	534.1
42.5°	735.7	689.3	648.8	612.4	592.0	572.3	549.7	536.5	521.4	511.7	502.3
45°	666.8	625.7	591.2	561.3	538.8	518.2	503.6	481.7	473.1	453.8	445.9
47.5°	606.3	568.1	535.2	506.8	484.8	471.4	450.0	432.9	419.1	407.3	397.0
50°	563.3	531.5	499.6	474.4	454.5	435.3	413.4	404.7	383.5	377.5	371.6
52.5°	524.0	493.8	464.6	439.9	420.0	401.3	382.0	370.8	356.4	350.5	346.1
55°	469.1	439.9	412.0	390.1	370.2	351.0	339.1	325.1	318.5	313.8	308.5
57.5°	413.9	387.6	366.3	344.1	324.1	308.8	295.0	286.6	279.7	273.6	267.3
60°	378.9	353.6	334.4	313.8	293.3	280.7	270.0	260.1	252.1	242.8	240.2
62.5°	341.7	319.7	302.0	282.0	264.1	252.5	242.4	233.0	223.5	209.9	206.2
65°	290.6	273.4	254.8	238.2	222.3	211.0	196.4	185.8	181.8	180.5	179.8
67.5°	244.4	228.1	212.2	195.2	180.7	170.3	162.8	161.2	158.4	157.6	155.8
70°	213.6	198.4	182.5	166.5	152.6	150.6	148.0	145.3	142.0	140.7	139.3
72.5°	186.0	170.3	154.3	141.6	135.6	133.1	130.4	127.8	125.5	124.2	123.4
75°	142.7	128.1	117.4	112.8	109.5	107.5	103.5	101.5	100.2	98.2	97.5
77.5°	102.7	94.5	89.6	86.7	83.2	81.1	78.8	76.8	75.4	75.0	73.9
80°	78.3	74.3	71.0	67.0	65.7	63.0	62.4	60.4	61.0	59.1	59.1
82.5°	60.8	55.7	52.9	51.1	49.8	47.6	47.0	46.0	46.2	44.7	44.7
85°	31.2	29.9	28.5	27.2	27.2	25.2	25.9	25.2	25.2	23.9	23.2
87.5°	11.9	12.0	11.7	12.4	13.2	13.4	13.4	12.8	12.7	12.6	12.1
90°	9.1	12.1	15.9	19.7	23.5	27.4	27.0	26.7	26.3	26.0	25.9
92.5°	20.0	21.2	22.1	23.0	24.0	24.9	24.9	25.0	25.1	25.1	25.2
95°	47.6	48.6	49.0	49.3	49.7	50.0	50.0	50.0	50.0	50.0	49.9
97.5°	80.4	81.5	82.1	82.8	83.4	84.1	84.1	84.1	84.1	84.1	84.1
100°	104.8	105.8	106.3	106.8	107.3	107.9	107.9	107.9	107.9	107.9	107.8
102.5°	130.0	130.9	131.5	132.2	132.8	133.5	133.6	133.8	133.9	134.1	134.0
105°	170.1	170.6	170.9	171.3	171.6	172.0	172.3	172.7	173.0	173.4	173.5
107.5°	213.9	214.3	214.3	214.3	214.3	214.3	214.5	214.6	214.7	214.9	214.6
110°	242.6	243.1	243.1	243.1	243.1	243.1	243.1	243.1	243.1	243.1	242.8



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	272.6	273.0	272.9	272.8	272.6	272.5	272.1	271.6	271.2	270.8	270.4
115°	316.8	317.2	316.8	316.5	316.1	315.8	315.6	315.4	315.3	315.1	314.7
117.5°	362.3	362.5	361.5	360.6	359.6	358.6	358.2	357.8	357.4	356.9	356.5
120°	391.7	391.7	390.3	388.9	387.5	386.1	386.1	386.1	386.1	386.1	385.9
122.5°	419.7	420.0	419.1	418.1	417.1	416.1	415.7	415.3	414.9	414.5	414.1
125°	461.2	461.7	461.2	460.6	460.1	459.6	459.1	458.6	458.0	457.5	457.2
127.5°	503.6	504.3	503.7	503.1	502.4	501.8	501.2	500.6	499.9	499.3	498.7
130°	530.4	531.3	531.0	530.6	530.3	530.0	529.6	529.3	528.9	528.6	528.0
132.5°	557.5	558.4	558.5	558.6	558.6	558.7	558.0	557.2	556.4	555.7	555.0
135°	596.2	597.3	597.7	598.0	598.4	598.7	598.6	598.4	598.2	598.0	597.7
137.5°	635.3	636.3	636.8	637.2	637.7	638.1	638.0	637.9	637.7	637.6	637.2
140°	659.7	660.9	661.8	662.7	663.5	664.4	664.4	664.4	664.4	664.4	664.0
142.5°	684.7	685.8	686.4	687.0	687.6	688.2	688.3	688.4	688.6	688.7	688.4
145°	719.3	720.4	721.5	722.5	723.5	724.6	724.8	724.9	725.1	725.3	725.0
147.5°	752.3	753.4	754.1	754.8	755.5	756.2	756.5	756.9	757.3	757.7	757.6
150°	772.5	773.4	774.1	774.8	775.5	776.2	776.7	777.2	777.7	778.3	778.3
152.5°	791.9	792.8	793.7	794.5	795.3	796.2	796.8	797.5	798.2	798.8	798.8
155°	818.9	819.4	819.9	820.5	821.0	821.5	822.4	823.2	824.1	825.0	825.2
157.5°	843.1	843.4	843.7	844.0	844.3	844.6	845.8	847.0	848.2	849.4	849.5
160°	858.1	858.3	858.5	858.7	858.9	859.0	860.1	861.1	862.2	863.2	863.4
162.5°	870.7	870.8	871.0	871.2	871.4	871.5	872.7	873.9	875.1	876.3	876.4
165°	888.0	887.9	887.9	887.9	887.9	887.9	889.2	890.4	891.6	892.8	893.0
167.5°	902.0	901.7	901.7	901.6	901.6	901.5	902.8	904.0	905.2	906.4	906.6
170°	910.1	909.7	909.6	909.4	909.2	909.0	910.3	911.5	912.7	913.9	914.0
172.5°	915.7	915.4	915.2	915.0	914.9	914.7	915.9	917.1	918.3	919.5	919.6
175°	922.6	922.2	921.8	921.5	921.1	920.8	922.0	923.2	924.4	925.6	925.7
177.5°	925.8	925.5	925.2	924.9	924.6	924.4	925.2	926.0	926.9	927.7	927.7
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1833.7	1834.7	1833.1	1834.2	1833.1	1834.7	1833.7	1839.5	1840.6	1841.6	1840.6
5°	1708.5	1700.6	1699.2	1697.3	1699.2	1700.6	1708.5	1711.9	1714.5	1719.8	1729.1
7.5°	1559.1	1557.9	1554.6	1550.0	1554.6	1557.9	1559.1	1570.5	1579.5	1589.9	1608.9
10°	1463.0	1459.7	1459.1	1454.4	1459.1	1459.7	1463.0	1477.6	1488.2	1502.8	1528.7
12.5°	1350.5	1329.1	1326.9	1315.3	1326.9	1329.1	1350.5	1369.3	1398.0	1412.1	1439.5
15°	1149.9	1145.9	1132.6	1124.0	1132.6	1145.9	1149.9	1165.8	1176.4	1214.9	1259.3
17.5°	1035.2	1022.2	1018.1	1016.2	1018.1	1022.2	1035.2	1042.9	1058.0	1078.3	1105.1
20°	961.4	949.5	947.5	946.2	947.5	949.5	961.4	970.7	982.7	1004.6	1032.4
22.5°	910.5	898.0	892.8	888.8	892.8	898.0	910.5	917.6	928.5	945.6	964.5
25°	823.4	818.8	816.1	814.8	816.1	818.8	823.4	830.0	840.7	863.9	883.8
27.5°	755.3	745.1	743.1	739.7	743.1	745.1	755.3	767.1	778.2	788.6	806.4
30°	716.6	713.3	708.6	704.6	708.6	713.3	716.6	722.6	729.9	747.8	765.0
32.5°	670.9	668.2	664.0	662.2	664.0	668.2	670.9	679.0	694.3	705.3	717.8
35°	620.4	611.1	607.1	601.1	607.1	611.1	620.4	627.0	633.0	642.3	664.8
37.5°	566.9	562.0	556.4	558.4	556.4	562.0	566.9	569.7	582.3	595.2	605.0
40°	525.5	522.2	520.9	520.2	520.9	522.2	525.5	534.1	549.4	555.4	570.0
42.5°	492.6	483.4	480.0	479.8	480.0	483.4	492.6	502.3	511.7	521.4	536.5
45°	442.6	433.9	428.0	428.6	428.0	433.9	442.6	445.9	453.8	473.1	481.7
47.5°	391.3	391.1	387.4	388.6	387.4	391.1	391.3	397.0	407.3	419.1	432.9
50°	366.9	362.9	360.3	360.9	360.3	362.9	366.9	371.6	377.5	383.5	404.7
52.5°	343.6	340.1	338.0	340.8	338.0	340.1	343.6	346.1	350.5	356.4	370.8
55°	305.2	301.2	300.6	299.9	300.6	301.2	305.2	308.5	313.8	318.5	325.1
57.5°	262.4	259.7	255.7	254.0	255.7	259.7	262.4	267.3	273.6	279.7	286.6
60°	231.6	226.3	219.6	219.0	219.6	226.3	231.6	240.2	242.8	252.1	260.1
62.5°	203.4	202.4	201.0	200.9	201.0	202.4	203.4	206.2	209.9	223.5	233.0
65°	178.5	177.8	178.5	179.1	178.5	177.8	178.5	179.8	180.5	181.8	185.8
67.5°	155.5	154.3	153.1	153.7	153.1	154.3	155.5	155.8	157.6	158.4	161.2
70°	138.0	137.3	136.7	136.7	136.7	137.3	138.0	139.3	140.7	142.0	145.3
72.5°	121.0	120.9	120.2	119.7	120.2	120.9	121.0	123.4	124.2	125.5	127.8
75°	96.9	95.5	95.5	95.5	95.5	95.5	96.9	97.5	98.2	100.2	101.5
77.5°	73.8	73.1	72.5	71.9	72.5	73.1	73.8	73.9	75.0	75.4	76.8
80°	58.4	57.7	57.1	57.1	57.1	57.7	58.4	59.1	59.1	61.0	60.4
82.5°	44.6	43.9	43.8	43.3	43.8	43.9	44.6	44.7	44.7	46.2	46.0
85°	23.9	24.5	23.9	25.2	23.9	24.5	23.9	23.2	23.9	25.2	25.2
87.5°	12.1	11.6	12.2	11.7	12.2	11.6	12.1	12.1	12.6	12.7	12.8
90°	26.1	26.2	26.4	26.6	26.4	26.2	26.1	25.9	26.0	26.3	26.7
92.5°	25.2	25.3	25.3	25.3	25.3	25.3	25.2	25.2	25.1	25.1	25.0
95°	49.5	49.2	48.8	48.5	48.8	49.2	49.5	49.9	50.0	50.0	50.0
97.5°	84.1	84.0	84.0	83.9	84.0	84.0	84.1	84.1	84.1	84.1	84.1
100°	107.6	107.4	107.3	107.1	107.3	107.4	107.6	107.8	107.9	107.9	107.9
102.5°	133.9	133.7	133.5	133.3	133.5	133.7	133.9	134.0	134.1	133.9	133.8
105°	173.5	173.5	173.5	173.5	173.5	173.5	173.5	173.5	173.4	173.0	172.7
107.5°	213.8	213.0	212.2	211.4	212.2	213.0	213.8	214.6	214.9	214.7	214.6
110°	242.3	241.8	241.3	240.7	241.3	241.8	242.3	242.8	243.1	243.1	243.1



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	270.0	269.6	269.3	268.9	269.3	269.6	270.0	270.4	270.8	271.2	271.6
115°	314.2	313.7	313.2	312.7	313.2	313.7	314.2	314.7	315.1	315.3	315.4
117.5°	356.0	355.4	354.9	354.4	354.9	355.4	356.0	356.5	356.9	357.4	357.8
120°	385.3	384.8	384.3	383.8	384.3	384.8	385.3	385.9	386.1	386.1	386.1
122.5°	413.7	413.3	412.9	412.6	412.9	413.3	413.7	414.1	414.5	414.9	415.3
125°	457.0	456.8	456.7	456.5	456.7	456.8	457.0	457.2	457.5	458.0	458.6
127.5°	498.2	497.6	497.1	496.5	497.1	497.6	498.2	498.7	499.3	499.9	500.6
130°	527.3	526.7	526.0	525.3	526.0	526.7	527.3	528.0	528.6	528.9	529.3
132.5°	554.4	553.9	553.3	552.8	553.3	553.9	554.4	555.0	555.7	556.4	557.2
135°	597.2	596.7	596.1	595.6	596.1	596.7	597.2	597.7	598.0	598.2	598.4
137.5°	636.5	635.8	635.1	634.4	635.1	635.8	636.5	637.2	637.6	637.7	637.9
140°	663.4	662.7	662.0	661.3	662.0	662.7	663.4	664.0	664.4	664.4	664.4
142.5°	687.7	687.0	686.4	685.7	686.4	687.0	687.7	688.4	688.7	688.6	688.4
145°	724.3	723.6	722.9	722.2	722.9	723.6	724.3	725.0	725.3	725.1	724.9
147.5°	756.9	756.2	755.6	754.9	755.6	756.2	756.9	757.6	757.7	757.3	756.9
150°	777.7	777.2	776.7	776.2	776.7	777.2	777.7	778.3	778.3	777.7	777.2
152.5°	798.2	797.5	796.8	796.2	796.8	797.5	798.2	798.8	798.8	798.2	797.5
155°	824.6	824.1	823.6	823.1	823.6	824.1	824.6	825.2	825.0	824.1	823.2
157.5°	848.7	847.9	847.0	846.2	847.0	847.9	848.7	849.5	849.4	848.2	847.0
160°	862.7	862.0	861.3	860.6	861.3	862.0	862.7	863.4	863.2	862.2	861.1
162.5°	875.6	874.8	873.9	873.1	873.9	874.8	875.6	876.4	876.3	875.1	873.9
165°	892.1	891.2	890.4	889.5	890.4	891.2	892.1	893.0	892.8	891.6	890.4
167.5°	905.7	904.8	903.9	903.0	903.9	904.8	905.7	906.6	906.4	905.2	904.0
170°	913.0	911.9	910.9	909.8	910.9	911.9	913.0	914.0	913.9	912.7	911.5
172.5°	918.6	917.5	916.5	915.5	916.5	917.5	918.6	919.6	919.5	918.3	917.1
175°	924.7	923.6	922.6	921.6	922.6	923.6	924.7	925.7	925.6	924.4	923.2
177.5°	926.9	926.0	925.2	924.4	925.2	926.0	926.9	927.7	927.7	926.9	926.0
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1836.3	1843.8	1854.9	1861.3	1871.9	1878.8	1882.5	1889.4	1893.1	1906.4	1920.2
5°	1733.7	1744.4	1762.9	1780.2	1798.8	1818.0	1831.9	1847.9	1862.5	1887.7	1914.2
7.5°	1616.2	1630.9	1659.7	1687.2	1719.5	1746.8	1770.8	1798.0	1822.3	1858.4	1896.0
10°	1528.1	1553.9	1591.8	1617.6	1660.1	1687.3	1725.1	1755.0	1788.8	1836.6	1879.1
12.5°	1452.2	1483.3	1513.7	1549.7	1587.9	1633.2	1674.7	1713.0	1753.3	1802.6	1852.5
15°	1314.4	1359.5	1406.6	1443.1	1494.9	1542.7	1591.1	1642.8	1691.9	1751.0	1816.0
17.5°	1137.1	1189.4	1268.6	1331.1	1391.9	1439.8	1499.8	1562.4	1620.3	1691.5	1763.9
20°	1057.0	1095.5	1149.2	1233.5	1325.0	1376.1	1437.2	1506.2	1572.5	1650.1	1727.8
22.5°	992.7	1027.0	1070.1	1135.8	1238.0	1307.6	1371.3	1441.4	1518.4	1597.6	1683.7
25°	901.0	924.9	970.0	1023.1	1093.5	1208.2	1277.9	1348.2	1431.9	1516.8	1615.0
27.5°	832.2	853.7	883.0	933.7	986.0	1068.4	1179.2	1255.9	1339.2	1434.8	1536.7
30°	779.6	804.8	837.3	873.2	930.2	994.6	1105.4	1194.3	1276.6	1374.8	1483.6
32.5°	741.4	761.3	789.0	825.4	872.9	934.6	1023.1	1131.1	1211.3	1314.8	1428.4
35°	678.8	702.0	724.6	759.1	797.5	853.9	920.9	1036.4	1116.0	1218.2	1332.3
37.5°	627.1	641.3	666.3	693.6	734.2	776.3	834.4	937.9	1024.1	1124.4	1241.2
40°	587.9	605.8	624.4	654.9	688.1	728.5	785.6	862.6	961.4	1059.6	1173.7
42.5°	549.7	572.3	592.0	612.4	648.8	689.3	735.7	801.0	902.0	994.9	1105.8
45°	503.6	518.2	538.8	561.3	591.2	625.7	666.8	723.9	820.8	901.0	1005.2
47.5°	450.0	471.4	484.8	506.8	535.2	568.1	606.3	655.7	734.1	809.3	906.0
50°	413.4	435.3	454.5	474.4	499.6	531.5	563.3	611.1	674.1	753.1	843.3
52.5°	382.0	401.3	420.0	439.9	464.6	493.8	524.0	566.0	620.0	692.6	780.2
55°	339.1	351.0	370.2	390.1	412.0	439.9	469.1	504.3	550.7	611.8	682.8
57.5°	295.0	308.8	324.1	344.1	366.3	387.6	413.9	445.7	482.4	537.6	598.4
60°	270.0	280.7	293.3	313.8	334.4	353.6	378.9	405.4	439.9	487.7	539.4
62.5°	242.4	252.5	264.1	282.0	302.0	319.7	341.7	369.8	399.0	442.6	487.9
65°	196.4	211.0	222.3	238.2	254.8	273.4	290.6	313.2	339.1	373.6	414.0
67.5°	162.8	170.3	180.7	195.2	212.2	228.1	244.4	262.1	284.5	311.2	343.3
70°	148.0	150.6	152.6	166.5	182.5	198.4	213.6	230.2	249.5	271.4	299.2
72.5°	130.4	133.1	135.6	141.6	154.3	170.3	186.0	198.4	216.6	234.7	257.3
75°	103.5	107.5	109.5	112.8	117.4	128.1	142.7	154.6	165.2	179.1	197.1
77.5°	78.8	81.1	83.2	86.7	89.6	94.5	102.7	113.5	123.4	131.5	143.8
80°	62.4	63.0	65.7	67.0	71.0	74.3	78.3	86.9	96.9	100.2	108.8
82.5°	47.0	47.6	49.8	51.1	52.9	55.7	60.8	63.0	70.9	75.2	80.7
85°	25.9	25.2	27.2	27.2	28.5	29.9	31.2	34.5	36.5	41.8	43.1
87.5°	13.4	13.4	13.2	12.4	11.7	12.0	11.9	12.0	12.7	13.8	15.5
90°	27.0	27.4	23.5	19.7	15.9	12.1	9.1	7.0	5.0	2.9	0.8
92.5°	24.9	24.9	24.0	23.0	22.1	21.2	20.0	18.5	17.0	15.4	13.9
95°	50.0	50.0	49.7	49.3	49.0	48.6	47.6	45.9	44.1	42.4	40.6
97.5°	84.1	84.1	83.4	82.8	82.1	81.5	80.4	78.8	77.3	75.8	74.3
100°	107.9	107.9	107.3	106.8	106.3	105.8	104.8	103.4	102.0	100.7	99.3
102.5°	133.6	133.5	132.8	132.2	131.5	130.9	130.0	128.9	127.8	126.6	125.5
105°	172.3	172.0	171.6	171.3	170.9	170.6	170.1	169.6	169.1	168.6	168.1
107.5°	214.5	214.3	214.3	214.3	214.3	214.3	213.9	213.2	212.4	211.7	210.9
110°	243.1	243.1	243.1	243.1	243.1	243.1	242.6	241.5	240.5	239.4	238.4



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	272.1	272.5	272.6	272.8	272.9	273.0	272.6	271.5	270.5	269.5	268.4
115°	315.6	315.8	316.1	316.5	316.8	317.2	316.8	315.8	314.7	313.7	312.7
117.5°	358.2	358.6	359.6	360.6	361.5	362.5	362.3	360.9	359.5	358.1	356.7
120°	386.1	386.1	387.5	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1
122.5°	415.7	416.1	417.1	418.1	419.1	420.0	419.7	418.0	416.4	414.7	413.0
125°	459.1	459.6	460.1	460.6	461.2	461.7	461.2	459.6	458.0	456.5	454.9
127.5°	501.2	501.8	502.4	503.1	503.7	504.3	503.6	501.7	499.7	497.7	495.7
130°	529.6	530.0	530.3	530.6	531.0	531.3	530.4	528.1	525.9	523.6	521.4
132.5°	558.0	558.7	558.6	558.6	558.5	558.4	557.5	555.6	553.8	552.0	550.1
135°	598.6	598.7	598.4	598.0	597.7	597.3	596.2	594.3	592.4	590.5	588.6
137.5°	638.0	638.1	637.7	637.2	636.8	636.3	635.3	633.8	632.2	630.6	629.1
140°	664.4	664.4	663.5	662.7	661.8	660.9	659.7	658.1	656.6	655.0	653.5
142.5°	688.3	688.2	687.6	687.0	686.4	685.8	684.7	683.2	681.6	680.0	678.5
145°	724.8	724.6	723.5	722.5	721.5	720.4	719.3	718.1	716.9	715.6	714.4
147.5°	756.5	756.2	755.5	754.8	754.1	753.4	752.3	750.8	749.4	747.9	746.5
150°	776.7	776.2	775.5	774.8	774.1	773.4	772.5	771.5	770.4	769.4	768.4
152.5°	796.8	796.2	795.3	794.5	793.7	792.8	791.9	790.9	789.8	788.8	787.7
155°	822.4	821.5	821.0	820.5	819.9	819.4	818.9	818.4	817.9	817.3	816.8
157.5°	845.8	844.6	844.3	844.0	843.7	843.4	843.1	842.7	842.4	842.0	841.7
160°	860.1	859.0	858.9	858.7	858.5	858.3	858.1	857.7	857.4	857.0	856.7
162.5°	872.7	871.5	871.4	871.2	871.0	870.8	870.7	870.6	870.6	870.5	870.4
165°	889.2	887.9	887.9	887.9	887.9	887.9	888.0	888.2	888.4	888.6	888.7
167.5°	902.8	901.5	901.6	901.6	901.7	901.7	902.0	902.5	903.0	903.5	904.0
170°	910.3	909.0	909.2	909.4	909.6	909.7	910.1	910.6	911.1	911.7	912.2
172.5°	915.9	914.7	914.9	915.0	915.2	915.4	915.7	916.2	916.8	917.3	917.8
175°	922.0	920.8	921.1	921.5	921.8	922.2	922.6	923.1	923.6	924.2	924.7
177.5°	925.2	924.4	924.6	924.9	925.2	925.5	925.8	926.2	926.7	927.1	927.5
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1920.7	1922.3	1932.9	1937.7	1947.3	1951.0	1955.2	1954.2	1954.2	1956.3	1971.2
5°	1924.8	1938.1	1958.0	1977.3	1995.8	2011.8	2022.4	2033.0	2037.0	2056.2	2073.5
7.5°	1917.9	1942.4	1975.3	2004.6	2039.8	2067.2	2090.1	2110.6	2124.7	2152.7	2181.4
10°	1908.9	1943.4	1980.6	2018.4	2066.8	2103.3	2140.5	2169.0	2178.3	2220.1	2244.0
12.5°	1890.9	1937.0	1984.3	2033.3	2080.6	2130.9	2171.8	2200.3	2233.0	2270.5	2314.6
15°	1863.8	1916.9	1978.6	2041.6	2109.3	2170.3	2214.1	2263.9	2299.7	2340.9	2379.3
17.5°	1824.9	1893.3	1971.7	2044.7	2123.0	2188.5	2248.8	2296.5	2321.7	2345.2	2350.9
20°	1794.1	1867.8	1960.0	2046.3	2124.6	2200.2	2259.9	2299.7	2306.4	2307.0	2271.9
22.5°	1760.7	1843.9	1940.4	2028.7	2122.4	2206.6	2253.0	2270.0	2243.7	2198.7	2130.7
25°	1699.2	1795.5	1907.6	2008.4	2110.6	2190.2	2206.2	2176.3	2084.1	1987.2	1864.5
27.5°	1632.6	1740.8	1861.0	1973.1	2082.0	2131.3	2097.0	1989.3	1823.2	1678.8	1503.8
30°	1583.8	1705.2	1823.3	1948.7	2049.6	2070.8	1991.9	1833.3	1639.5	1421.9	1247.4
32.5°	1528.1	1655.3	1785.1	1914.8	1999.2	1978.4	1848.0	1652.8	1425.6	1211.7	1046.8
35°	1448.4	1579.8	1719.8	1849.9	1903.6	1814.0	1619.0	1364.8	1132.6	932.9	819.4
37.5°	1356.5	1499.5	1645.1	1764.5	1760.7	1611.4	1345.7	1083.4	888.2	770.1	689.3
40°	1291.2	1435.8	1593.1	1693.9	1650.8	1456.4	1168.4	920.9	778.3	684.1	625.0
42.5°	1228.6	1373.7	1529.9	1610.1	1535.1	1296.1	1009.2	815.3	697.6	624.1	576.2
45°	1122.0	1275.3	1419.9	1464.4	1330.3	1066.9	816.1	675.5	597.2	542.7	509.6
47.5°	1017.8	1168.6	1300.6	1301.4	1120.1	865.2	688.5	584.6	517.7	475.6	451.5
50°	954.1	1097.4	1208.2	1191.0	985.3	769.7	615.7	526.2	470.4	437.9	412.7
52.5°	882.5	1021.5	1117.5	1068.4	871.2	677.3	550.4	475.2	429.0	400.8	378.2
55°	778.3	901.7	969.4	895.1	710.6	563.3	465.1	406.1	371.6	347.7	328.4
57.5°	676.0	777.8	820.4	733.8	585.3	467.1	393.5	349.1	314.9	297.8	287.8
60°	611.8	698.7	728.5	633.0	508.9	408.7	348.3	307.2	282.0	270.7	260.8
62.5°	548.6	619.6	631.9	544.3	443.6	357.8	305.9	271.1	254.4	243.6	234.2
65°	455.2	506.3	500.3	430.0	351.0	284.0	246.2	224.9	212.3	197.1	180.5
67.5°	374.7	405.9	387.1	334.4	267.9	220.7	196.0	179.9	164.3	149.8	146.0
70°	323.8	341.7	321.8	273.4	219.6	185.1	165.2	146.0	136.7	133.4	127.4
72.5°	275.0	281.2	259.7	218.2	178.7	153.3	133.9	123.1	118.1	115.3	111.5
75°	206.4	201.7	183.1	150.6	124.1	106.8	100.9	96.9	93.6	90.9	88.9
77.5°	144.9	138.1	121.6	100.3	86.4	78.2	74.6	72.5	70.9	69.5	67.5
80°	108.8	104.2	87.6	71.7	65.7	61.7	59.7	57.1	57.1	55.7	53.7
82.5°	79.6	74.4	60.0	52.5	49.2	46.8	45.4	43.8	43.3	43.5	42.1
85°	41.8	33.8	29.9	28.5	26.5	25.2	25.9	24.5	24.5	24.5	23.9
87.5°	13.3	11.1	11.0	10.8	12.0	12.7	13.0	13.7	15.0	14.4	14.9
90°	2.9	5.0	7.0	9.1	12.1	15.9	19.7	23.5	27.4	27.0	26.7
92.5°	15.4	17.0	18.5	20.0	21.2	22.1	23.0	24.0	24.9	24.9	25.0
95°	42.4	44.1	45.9	47.6	48.6	49.0	49.3	49.7	50.0	50.0	50.0
97.5°	75.8	77.3	78.8	80.4	81.5	82.1	82.8	83.4	84.1	84.1	84.1
100°	100.7	102.0	103.4	104.8	105.8	106.3	106.8	107.3	107.9	107.9	107.9
102.5°	126.6	127.8	128.9	130.0	130.9	131.5	132.2	132.8	133.5	133.6	133.8
105°	168.6	169.1	169.6	170.1	170.6	170.9	171.3	171.6	172.0	172.3	172.7
107.5°	211.7	212.4	213.2	213.9	214.3	214.3	214.3	214.3	214.3	214.5	214.6
110°	239.4	240.5	241.5	242.6	243.1	243.1	243.1	243.1	243.1	243.1	243.1





TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	269.5	270.5	271.5	272.6	273.0	272.9	272.8	272.6	272.5	272.1	271.6
115°	313.7	314.7	315.8	316.8	317.2	316.8	316.5	316.1	315.8	315.6	315.4
117.5°	358.1	359.5	360.9	362.3	362.5	361.5	360.6	359.6	358.6	358.2	357.8
120°	387.5	388.9	390.3	391.7	391.7	390.3	388.9	387.5	386.1	386.1	386.1
122.5°	414.7	416.4	418.0	419.7	420.0	419.1	418.1	417.1	416.1	415.7	415.3
125°	456.5	458.0	459.6	461.2	461.7	461.2	460.6	460.1	459.6	459.1	458.6
127.5°	497.7	499.7	501.7	503.6	504.3	503.7	503.1	502.4	501.8	501.2	500.6
130°	523.6	525.9	528.1	530.4	531.3	531.0	530.6	530.3	530.0	529.6	529.3
132.5°	552.0	553.8	555.6	557.5	558.4	558.5	558.6	558.6	558.7	558.0	557.2
135°	590.5	592.4	594.3	596.2	597.3	597.7	598.0	598.4	598.7	598.6	598.4
137.5°	630.6	632.2	633.8	635.3	636.3	636.8	637.2	637.7	638.1	638.0	637.9
140°	655.0	656.6	658.1	659.7	660.9	661.8	662.7	663.5	664.4	664.4	664.4
142.5°	680.0	681.6	683.2	684.7	685.8	686.4	687.0	687.6	688.2	688.3	688.4
145°	715.6	716.9	718.1	719.3	720.4	721.5	722.5	723.5	724.6	724.8	724.9
147.5°	747.9	749.4	750.8	752.3	753.4	754.1	754.8	755.5	756.2	756.5	756.9
150°	769.4	770.4	771.5	772.5	773.4	774.1	774.8	775.5	776.2	776.7	777.2
152.5°	788.8	789.8	790.9	791.9	792.8	793.7	794.5	795.3	796.2	796.8	797.5
155°	817.3	817.9	818.4	818.9	819.4	819.9	820.5	821.0	821.5	822.4	823.2
157.5°	842.0	842.4	842.7	843.1	843.4	843.7	844.0	844.3	844.6	845.8	847.0
160°	857.0	857.4	857.7	858.1	858.3	858.5	858.7	858.9	859.0	860.1	861.1
162.5°	870.5	870.6	870.6	870.7	870.8	871.0	871.2	871.4	871.5	872.7	873.9
165°	888.6	888.4	888.2	888.0	887.9	887.9	887.9	887.9	887.9	889.2	890.4
167.5°	903.5	903.0	902.5	902.0	901.7	901.7	901.6	901.6	901.5	902.8	904.0
170°	911.7	911.1	910.6	910.1	909.7	909.6	909.4	909.2	909.0	910.3	911.5
172.5°	917.3	916.8	916.2	915.7	915.4	915.2	915.0	914.9	914.7	915.9	917.1
175°	924.2	923.6	923.1	922.6	922.2	921.8	921.5	921.1	920.8	922.0	923.2
177.5°	927.1	926.7	926.2	925.8	925.5	925.2	924.9	924.6	924.4	925.2	926.0
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2	926.2



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6	1909.6
2.5°	1976.5	1983.4	1986.5	1986.5	1990.3	1988.7	1987.1
5°	2090.1	2102.7	2105.3	2117.3	2125.9	2123.2	2124.6
7.5°	2203.0	2223.3	2243.3	2252.5	2253.9	2259.2	2261.2
10°	2272.5	2289.1	2320.3	2315.6	2338.9	2352.1	2330.2
12.5°	2339.4	2361.8	2383.5	2389.4	2402.6	2406.8	2398.2
15°	2399.9	2411.9	2413.2	2409.9	2413.8	2410.5	2397.9
17.5°	2343.4	2324.0	2284.7	2266.1	2251.4	2229.7	2220.9
20°	2250.0	2192.9	2126.5	2100.0	2068.8	2007.8	2022.4
22.5°	2048.3	1983.2	1916.9	1839.4	1802.4	1744.5	1741.0
25°	1734.4	1622.3	1498.9	1412.6	1362.2	1304.5	1279.2
27.5°	1348.5	1207.3	1106.2	1055.0	1008.4	962.6	960.8
30°	1094.8	988.6	910.3	866.5	838.0	818.8	822.8
32.5°	922.8	850.1	797.3	760.9	739.8	725.3	725.1
35°	754.4	704.6	670.8	655.5	640.3	629.7	630.3
37.5°	645.6	615.7	596.9	580.0	570.5	565.3	562.4
40°	589.9	565.3	550.7	540.8	532.8	525.5	524.2
42.5°	545.8	525.5	510.9	503.1	495.6	490.5	489.1
45°	484.4	467.8	454.5	445.9	442.6	437.9	437.9
47.5°	430.9	414.6	404.2	398.8	393.1	390.0	389.9
50°	394.8	382.2	372.9	369.6	364.9	362.9	362.3
52.5°	362.4	353.0	346.4	344.1	342.1	339.6	340.0
55°	318.5	313.2	310.5	308.5	305.2	301.2	303.9
57.5°	281.5	276.9	269.8	263.5	260.5	257.7	258.8
60°	255.5	246.2	236.9	229.6	227.6	221.6	221.6
62.5°	222.5	209.5	198.1	194.0	192.0	189.2	188.7
65°	171.2	165.9	163.2	160.6	159.2	159.2	157.9
67.5°	141.9	139.7	136.8	136.2	134.8	134.4	134.0
70°	125.4	122.7	121.4	120.8	119.4	120.1	118.1
72.5°	109.5	107.4	107.1	105.4	104.6	104.7	103.2
75°	86.3	86.3	85.6	84.9	83.6	82.9	83.6
77.5°	66.4	66.5	65.3	65.2	65.0	65.2	64.5
80°	53.1	53.7	53.1	52.4	51.8	52.4	51.8
82.5°	41.9	41.0	40.9	40.7	40.6	40.2	40.1
85°	23.9	24.5	23.9	23.2	23.2	23.2	23.9
87.5°	14.3	14.2	14.2	14.2	14.3	14.3	13.8
90°	26.3	26.0	25.9	26.1	26.2	26.4	26.6
92.5°	25.1	25.1	25.2	25.2	25.3	25.3	25.3
95°	50.0	50.0	49.9	49.5	49.2	48.8	48.5
97.5°	84.1	84.1	84.1	84.1	84.0	84.0	83.9
100°	107.9	107.9	107.8	107.6	107.4	107.3	107.1
102.5°	133.9	134.1	134.0	133.9	133.7	133.5	133.3
105°	173.0	173.4	173.5	173.5	173.5	173.5	173.5
107.5°	214.7	214.9	214.6	213.8	213.0	212.2	211.4
110°	243.1	243.1	242.8	242.3	241.8	241.3	240.7



TEST NUMBER: P331718

CATALOG NUMBER: S122RDIP-S865D725U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	271.2	270.8	270.4	270.0	269.6	269.3	268.9
115°	315.3	315.1	314.7	314.2	313.7	313.2	312.7
117.5°	357.4	356.9	356.5	356.0	355.4	354.9	354.4
120°	386.1	386.1	385.9	385.3	384.8	384.3	383.8
122.5°	414.9	414.5	414.1	413.7	413.3	412.9	412.6
125°	458.0	457.5	457.2	457.0	456.8	456.7	456.5
127.5°	499.9	499.3	498.7	498.2	497.6	497.1	496.5
130°	528.9	528.6	528.0	527.3	526.7	526.0	525.3
132.5°	556.4	555.7	555.0	554.4	553.9	553.3	552.8
135°	598.2	598.0	597.7	597.2	596.7	596.1	595.6
137.5°	637.7	637.6	637.2	636.5	635.8	635.1	634.4
140°	664.4	664.4	664.0	663.4	662.7	662.0	661.3
142.5°	688.6	688.7	688.4	687.7	687.0	686.4	685.7
145°	725.1	725.3	725.0	724.3	723.6	722.9	722.2
147.5°	757.3	757.7	757.6	756.9	756.2	755.6	754.9
150°	777.7	778.3	778.3	777.7	777.2	776.7	776.2
152.5°	798.2	798.8	798.8	798.2	797.5	796.8	796.2
155°	824.1	825.0	825.2	824.6	824.1	823.6	823.1
157.5°	848.2	849.4	849.5	848.7	847.9	847.0	846.2
160°	862.2	863.2	863.4	862.7	862.0	861.3	860.6
162.5°	875.1	876.3	876.4	875.6	874.8	873.9	873.1
165°	891.6	892.8	893.0	892.1	891.2	890.4	889.5
167.5°	905.2	906.4	906.6	905.7	904.8	903.9	903.0
170°	912.7	913.9	914.0	913.0	911.9	910.9	909.8
172.5°	918.3	919.5	919.6	918.6	917.5	916.5	915.5
175°	924.4	925.6	925.7	924.7	923.6	922.6	921.6
177.5°	926.9	927.7	927.7	926.9	926.0	925.2	924.4
180°	926.2	926.2	926.2	926.2	926.2	926.2	926.2

(END OF REPORT)