

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931455

Luminaire Tested: DFN2DS-TR4F0-040DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-040DS935-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3405.6 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 38.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931455

CATALOG NUMBER: DFN2DS-TR4F0-040DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931455

CATALOG NUMBER: DFN2DS-TR4F0-040DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1063	1063	1063
5°	1067	1052	1058
10°	1061	1041	1047
15°	1048	1028	1027
20°	1029	1008	1007
25°	1011	983	983
30°	987	960	952
35°	965	932	919
40°	937	905	888
45°	910	878	856
50°	880	849	819
55°	849	816	786
60°	814	777	749
65°	777	738	704
70°	730	691	658
75°	664	636	620
80°	589	571	542
85°	480	458	411

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 910 cd/sqm

TEST NUMBER: P931455

CATALOG NUMBER: DFN2DS-TR4F0-040DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.0	3.7
10°-20°	354.5	10.4
20°-30°	520.9	15.3
30°-40°	605.0	17.8
40°-50°	604.3	17.7
50°-60°	526.9	15.5
60°-70°	389.5	11.4
70°-80°	220.4	6.5
80°-90°	58.2	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1001.4	29.4
0°-40°	1606.4	47.2
0°-60°	2737.6	80.4
0°-90°	3405.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3405.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1338	1338	1338	1338	1338	
5°	1338	1333	1319	1330	1327	127
15°	1274	1266	1250	1255	1248	359
25°	1153	1143	1121	1124	1121	531
35°	995	982	962	954	947	621
45°	810	801	781	767	762	625
55°	613	605	590	574	568	548
65°	413	405	393	381	375	409
75°	216	214	207	200	202	231
85°	53	52	50	46	45	62
90°	0	0	0	0	0	

TEST NUMBER: P931455

CATALOG NUMBER: DFN2DS-TR4F0-040DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1338.5	1338.5	1338.5	1338.5	1338.5
2.5°	1346.3	1339.9	1325.7	1338.5	1336.1
5°	1338.5	1333.4	1319.2	1329.5	1327.1
7.5°	1329.5	1321.8	1307.6	1318.0	1315.5
10°	1315.5	1306.4	1291.0	1301.3	1297.4
12.5°	1296.0	1288.4	1273.0	1279.4	1276.8
15°	1274.2	1266.5	1249.8	1254.9	1248.5
17.5°	1247.2	1239.5	1222.7	1229.1	1222.7
20°	1217.5	1209.8	1191.9	1195.7	1190.7
22.5°	1188.0	1176.4	1159.6	1159.6	1157.0
25°	1153.2	1142.9	1121.1	1123.6	1121.1
27.5°	1114.6	1105.5	1088.9	1085.1	1078.7
30°	1076.0	1065.7	1046.4	1042.6	1037.4
32.5°	1034.8	1027.2	1006.5	998.8	993.6
35°	994.9	982.1	961.5	953.7	947.3
37.5°	949.9	938.3	917.6	908.7	902.2
40°	903.6	893.2	872.6	861.1	856.0
42.5°	858.5	848.1	827.7	814.7	807.0
45°	809.6	800.7	781.2	767.2	762.0
47.5°	762.0	752.9	732.4	718.2	710.5
50°	711.7	705.3	687.3	669.3	662.8
52.5°	662.8	653.9	637.2	623.0	614.0
55°	612.8	604.9	589.5	574.0	567.7
57.5°	562.4	556.1	539.2	523.8	518.7
60°	512.2	507.1	489.2	475.0	471.1
62.5°	463.4	454.3	441.5	428.6	423.5
65°	413.2	405.4	392.6	381.0	374.6
67.5°	361.7	355.2	343.7	334.7	329.6
70°	314.1	308.9	297.3	288.3	283.2
72.5°	265.2	260.0	253.6	244.6	240.7
75°	216.2	213.7	207.2	199.5	202.1
77.5°	172.4	167.3	164.7	160.8	157.0
80°	128.7	127.4	124.8	121.0	118.4
82.5°	87.5	87.5	86.3	81.1	81.1
85°	52.7	51.5	50.2	46.3	45.1
87.5°	23.2	20.6	18.1	14.2	12.8
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931455

CATALOG NUMBER: DFN2DS-TR4F0-040DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.50	13.11	11.86	13.42	13.74	11.05	12.66	11.42	12.98	13.29
	3H	13.25	14.70	13.62	15.03	15.39	12.76	14.21	13.13	14.54	14.90
	4H	13.89	15.26	14.29	15.61	15.99	13.40	14.77	13.80	15.11	15.49
	6H	14.36	15.63	14.77	15.99	16.39	13.86	15.13	14.27	15.49	15.88
	8H	14.50	15.72	14.93	16.10	16.50	14.00	15.21	14.43	15.60	16.00
	12H	14.59	15.75	15.02	16.14	16.57	14.08	15.24	14.51	15.62	16.05
4H	2H	12.06	13.43	12.46	13.77	14.15	11.70	13.07	12.10	13.42	13.80
	3H	14.03	15.18	14.44	15.58	15.98	13.63	14.77	14.03	15.17	15.57
	4H	14.81	15.84	15.24	16.26	16.69	14.38	15.42	14.82	15.83	16.27
	6H	15.40	16.31	15.86	16.75	17.21	14.97	15.88	15.43	16.32	16.77
	8H	15.59	16.44	16.05	16.88	17.35	15.16	16.00	15.62	16.44	16.91
	12H	15.73	16.49	16.21	16.96	17.43	15.27	16.03	15.75	16.51	16.98
8H	4H	15.08	15.93	15.54	16.37	16.84	14.71	15.55	15.17	16.00	16.46
	6H	15.80	16.50	16.29	16.99	17.46	15.41	16.12	15.91	16.61	17.08
	8H	16.05	16.69	16.56	17.19	17.68	15.66	16.29	16.17	16.80	17.29
	12H	16.25	16.81	16.76	17.30	17.86	15.84	16.40	16.35	16.89	17.45
12H	4H	15.11	15.87	15.59	16.34	16.81	14.74	15.50	15.22	15.98	16.45
	6H	15.84	16.47	16.35	16.98	17.47	15.47	16.10	15.98	16.61	17.10
	8H	16.15	16.71	16.66	17.20	17.76	15.78	16.33	16.28	16.83	17.39