

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931473

Luminaire Tested: DFN2DS-TR4F0-050DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931473
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-050DS935-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4257.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 48.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931473

CATALOG NUMBER: DFN2DS-TR4F0-050DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931473

CATALOG NUMBER: DFN2DS-TR4F0-050DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1329	1329	1329
5°	1334	1315	1323
10°	1326	1302	1308
15°	1310	1285	1284
20°	1287	1260	1258
25°	1264	1228	1228
30°	1234	1200	1190
35°	1206	1166	1148
40°	1171	1131	1110
45°	1137	1097	1070
50°	1100	1062	1024
55°	1061	1021	983
60°	1017	972	936
65°	971	922	880
70°	912	863	822
75°	829	795	776
80°	737	714	677
85°	601	572	513

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1137 cd/sqm

TEST NUMBER: P931473

CATALOG NUMBER: DFN2DS-TR4F0-050DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	3.7
10°-20°	443.1	10.4
20°-30°	651.1	15.3
30°-40°	756.3	17.8
40°-50°	755.3	17.7
50°-60°	658.6	15.5
60°-70°	486.9	11.4
70°-80°	275.5	6.5
80°-90°	72.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1251.7	29.4
0°-40°	2008.0	47.2
0°-60°	3421.9	80.4
0°-90°	4257.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4257.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1673	1673	1673	1673	1673	
5°	1673	1667	1649	1662	1659	159
15°	1593	1583	1562	1569	1561	449
25°	1442	1429	1401	1404	1401	663
35°	1244	1228	1202	1192	1184	777
45°	1012	1001	976	959	952	781
55°	766	756	737	718	710	685
65°	516	507	491	476	468	511
75°	270	267	259	249	253	288
85°	66	64	63	58	56	77
90°	0	0	0	0	0	

TEST NUMBER: P931473

CATALOG NUMBER: DFN2DS-TR4F0-050DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1673.1	1673.1	1673.1	1673.1	1673.1
2.5°	1682.8	1674.8	1657.1	1673.1	1670.1
5°	1673.1	1666.9	1649.0	1661.9	1658.9
7.5°	1661.9	1652.3	1634.6	1647.6	1644.3
10°	1644.3	1633.1	1613.8	1626.5	1621.8
12.5°	1620.1	1610.5	1591.3	1599.3	1596.0
15°	1592.7	1583.2	1562.2	1568.7	1560.6
17.5°	1558.9	1549.4	1528.4	1536.4	1528.4
20°	1521.9	1512.4	1489.9	1494.6	1488.3
22.5°	1485.0	1470.5	1449.5	1449.5	1446.3
25°	1441.5	1428.7	1401.4	1404.5	1401.4
27.5°	1393.2	1381.9	1361.1	1356.3	1348.3
30°	1345.0	1332.1	1308.1	1303.2	1296.8
32.5°	1293.5	1284.0	1258.2	1248.5	1242.0
35°	1243.6	1227.6	1201.8	1192.1	1184.1
37.5°	1187.3	1172.9	1147.1	1135.8	1127.8
40°	1129.5	1116.5	1090.7	1076.4	1069.9
42.5°	1073.2	1060.2	1034.6	1018.3	1008.8
45°	1012.0	1000.8	976.5	959.0	952.4
47.5°	952.4	941.2	915.5	897.7	888.1
50°	889.7	881.7	859.1	836.6	828.5
52.5°	828.5	817.3	796.4	778.7	767.5
55°	765.9	756.2	736.8	717.6	709.6
57.5°	703.0	695.1	674.1	654.8	648.3
60°	640.3	634.0	611.5	593.7	588.9
62.5°	579.2	567.9	551.9	535.8	529.3
65°	516.5	506.8	490.7	476.3	468.2
67.5°	452.2	444.0	429.7	418.4	411.9
70°	392.6	386.1	371.6	360.3	354.1
72.5°	331.5	325.0	317.0	305.7	300.9
75°	270.2	267.1	258.9	249.4	252.7
77.5°	215.6	209.1	205.9	201.1	196.3
80°	161.0	159.3	156.0	151.3	148.0
82.5°	109.4	109.4	107.8	101.4	101.4
85°	65.9	64.3	62.8	57.9	56.3
87.5°	29.0	25.8	22.5	17.7	16.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931473

CATALOG NUMBER: DFN2DS-TR4F0-050DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.27	13.88	12.64	14.20	14.51	11.83	13.44	12.19	13.75	14.07
	3H	14.02	15.48	14.40	15.80	16.16	13.53	14.99	13.91	15.31	15.67
	4H	14.67	16.04	15.07	16.38	16.76	14.17	15.54	14.57	15.89	16.27
	6H	15.14	16.41	15.55	16.77	17.16	14.64	15.90	15.05	16.27	16.66
	8H	15.28	16.49	15.70	16.88	17.28	14.78	15.99	15.20	16.38	16.78
	12H	15.37	16.53	15.80	16.91	17.34	14.86	16.02	15.29	16.40	16.83
4H	2H	12.83	14.20	13.23	14.55	14.92	12.48	13.85	12.88	14.20	14.57
	3H	14.81	15.95	15.22	16.35	16.75	14.40	15.55	14.81	15.94	16.34
	4H	15.58	16.62	16.01	17.03	17.47	15.16	16.20	15.59	16.61	17.05
	6H	16.18	17.08	16.63	17.53	17.98	15.75	16.65	16.20	17.09	17.55
	8H	16.37	17.22	16.83	17.66	18.12	15.93	16.78	16.39	17.22	17.69
	12H	16.50	17.26	16.98	17.74	18.21	16.05	16.81	16.53	17.29	17.75
8H	4H	15.86	16.70	16.32	17.15	17.61	15.48	16.33	15.94	16.77	17.24
	6H	16.57	17.27	17.06	17.76	18.24	16.19	16.89	16.68	17.38	17.86
	8H	16.83	17.46	17.34	17.97	18.45	16.44	17.07	16.95	17.58	18.06
	12H	17.03	17.59	17.54	18.08	18.64	16.62	17.18	17.12	17.67	18.23
12H	4H	15.88	16.64	16.36	17.12	17.59	15.52	16.28	16.00	16.75	17.22
	6H	16.62	17.25	17.13	17.76	18.24	16.25	16.88	16.76	17.39	17.87
	8H	16.93	17.49	17.44	17.98	18.54	16.55	17.11	17.06	17.60	18.16