

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931509

Luminaire Tested: DFN2DS-TR4F0-070DS935-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931509
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-070DS935-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5959.8 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931509

CATALOG NUMBER: DFN2DS-TR4F0-070DS935-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931509

CATALOG NUMBER: DFN2DS-TR4F0-070DS935-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1861	1861	1861
5°	1868	1841	1852
10°	1857	1822	1832
15°	1834	1799	1797
20°	1801	1763	1762
25°	1769	1720	1720
30°	1727	1680	1665
35°	1689	1632	1608
40°	1640	1584	1553
45°	1592	1536	1498
50°	1539	1486	1434
55°	1485	1429	1376
60°	1424	1360	1310
65°	1359	1292	1232
70°	1277	1208	1151
75°	1161	1113	1086
80°	1031	999	948
85°	841	802	719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1592 cd/sqm

TEST NUMBER: P931509

CATALOG NUMBER: DFN2DS-TR4F0-070DS935-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.5	3.7
10°-20°	620.3	10.4
20°-30°	911.6	15.3
30°-40°	1058.8	17.8
40°-50°	1057.5	17.7
50°-60°	922.1	15.5
60°-70°	681.6	11.4
70°-80°	385.7	6.5
80°-90°	101.8	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1752.4	29.4
0°-40°	2811.2	47.2
0°-60°	4790.7	80.4
0°-90°	5959.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5959.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2342	2342	2342	2342	2342	
5°	2342	2334	2309	2327	2322	222
15°	2230	2216	2187	2196	2185	628
25°	2018	2000	1962	1966	1962	929
35°	1741	1719	1683	1669	1658	1087
45°	1417	1401	1367	1342	1333	1093
55°	1072	1059	1032	1005	993	959
65°	723	710	687	667	656	715
75°	378	374	362	349	354	404
85°	92	90	88	81	79	108
90°	0	0	0	0	0	

TEST NUMBER: P931509

CATALOG NUMBER: DFN2DS-TR4F0-070DS935-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2342.4	2342.4	2342.4	2342.4	2342.4
2.5°	2356.1	2344.8	2319.9	2342.4	2338.1
5°	2342.4	2333.6	2308.8	2326.6	2322.3
7.5°	2326.6	2313.2	2288.4	2306.6	2302.0
10°	2302.0	2286.2	2259.2	2277.2	2270.5
12.5°	2268.1	2254.7	2227.7	2238.9	2234.4
15°	2229.9	2216.5	2187.1	2196.2	2184.9
17.5°	2182.5	2169.2	2139.8	2151.0	2139.8
20°	2130.6	2117.3	2085.8	2092.5	2083.6
22.5°	2079.0	2058.8	2029.3	2029.3	2024.8
25°	2018.2	2000.2	1962.0	1966.3	1962.0
27.5°	1950.5	1934.7	1905.6	1898.9	1887.6
30°	1883.1	1864.9	1831.3	1824.6	1815.5
32.5°	1810.9	1797.6	1761.5	1747.9	1738.7
35°	1741.2	1718.7	1682.6	1669.0	1657.7
37.5°	1662.3	1642.0	1605.9	1590.1	1578.9
40°	1581.3	1563.1	1527.0	1507.0	1497.9
42.5°	1502.4	1484.3	1448.4	1425.7	1412.3
45°	1416.8	1401.1	1367.1	1342.5	1333.4
47.5°	1333.4	1317.7	1281.6	1256.7	1243.4
50°	1245.5	1234.3	1202.7	1171.2	1160.0
52.5°	1160.0	1144.2	1115.1	1090.2	1074.4
55°	1072.2	1058.7	1031.7	1004.7	993.4
57.5°	984.4	973.1	943.7	916.7	907.6
60°	896.4	887.5	856.0	831.2	824.5
62.5°	810.8	795.1	772.6	750.2	741.1
65°	723.2	709.5	687.1	666.8	655.5
67.5°	633.0	621.6	601.5	585.7	576.6
70°	549.6	540.6	520.2	504.5	495.6
72.5°	464.1	455.0	443.8	428.0	421.3
75°	378.3	374.0	362.5	349.2	353.7
77.5°	301.9	292.7	288.2	281.5	274.9
80°	225.3	223.0	218.4	211.7	207.2
82.5°	153.2	153.2	151.0	142.0	142.0
85°	92.3	90.1	88.0	81.0	78.9
87.5°	40.6	36.1	31.6	24.9	22.4
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931509

CATALOG NUMBER: DFN2DS-TR4F0-070DS935-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.44	15.05	13.81	15.37	15.68	13.00	14.61	13.36	14.92	15.23
	3H	15.19	16.64	15.57	16.97	17.33	14.70	16.15	15.08	16.48	16.84
	4H	15.84	17.21	16.24	17.55	17.93	15.34	16.71	15.74	17.06	17.43
	6H	16.31	17.57	16.72	17.94	18.33	15.80	17.07	16.22	17.44	17.83
	8H	16.45	17.66	16.87	18.05	18.45	15.95	17.16	16.37	17.55	17.95
	12H	16.54	17.70	16.97	18.08	18.51	16.03	17.19	16.46	17.57	18.00
4H	2H	14.00	15.37	14.40	15.72	16.09	13.65	15.02	14.05	15.36	15.74
	3H	15.98	17.12	16.39	17.52	17.92	15.57	16.72	15.98	17.11	17.51
	4H	16.75	17.79	17.18	18.20	18.64	16.33	17.36	16.76	17.78	18.21
	6H	17.35	18.25	17.80	18.69	19.15	16.92	17.82	17.37	18.26	18.72
	8H	17.54	18.38	18.00	18.83	19.29	17.10	17.95	17.56	18.39	18.85
	12H	17.67	18.43	18.15	18.91	19.38	17.22	17.98	17.70	18.45	18.92
8H	4H	17.03	17.87	17.49	18.31	18.78	16.65	17.50	17.11	17.94	18.41
	6H	17.74	18.44	18.23	18.93	19.41	17.36	18.06	17.85	18.55	19.03
	8H	18.00	18.63	18.51	19.14	19.62	17.61	18.24	18.12	18.75	19.23
	12H	18.20	18.76	18.71	19.25	19.81	17.79	18.34	18.29	18.83	19.40
12H	4H	17.05	17.81	17.53	18.29	18.76	16.69	17.45	17.17	17.92	18.39
	6H	17.79	18.42	18.30	18.92	19.41	17.42	18.05	17.93	18.56	19.04
	8H	18.10	18.66	18.61	19.15	19.71	17.72	18.28	18.23	18.77	19.33

END OF REPORT