

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331464-935

Luminaire Tested: **S122DIP-S1005D1080U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331464-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S1005D1080U935-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7115.2 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331464-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331464-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		55	55	55	49
1	98	93	89	86	90	86	83	80	73	70	68		60	59	57		49	48	47	41
2	89	81	75	70	82	75	70	65	64	60	56		53	50	48		43	41	39	35
3	81	72	64	58	74	66	60	55	56	51	47		47	43	40		38	36	33	29
4	74	63	55	49	68	59	52	46	50	45	40		42	38	35		34	31	29	25
5	68	56	48	42	62	52	45	40	45	39	35		37	33	30		31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	30		34	30	26		28	25	22	19
7	58	46	38	32	53	43	35	30	36	31	27		31	26	23		25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24		28	24	21		23	20	18	15
9	50	38	30	25	46	35	29	24	30	25	21		26	22	19		22	18	16	14
10	47	35	28	23	43	32	26	22	28	23	19		24	20	17		20	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22157	22157	22157
5°	22242	21921	22049
10°	22109	21697	21807
15°	21835	21417	21396
20°	21448	20993	20972
25°	21063	20475	20475
30°	20566	19999	19827
35°	20103	19429	19141
40°	19524	18858	18493
45°	18952	18287	17838
50°	18329	17698	17071
55°	17681	17011	16380
60°	16956	16191	15594
65°	16180	15373	14670
70°	15196	14389	13704
75°	13830	13250	12926
80°	12273	11901	11288
85°	10022	9541	8540



TEST NUMBER: P331464-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	1.8
10°-20°	363.1	5.1
20°-30°	533.7	7.5
30°-40°	619.9	8.7
40°-50°	619.3	8.7
50°-60°	540.0	7.6
60°-70°	399.3	5.6
70°-80°	226.2	3.2
80°-90°	65.5	0.9
90°-100°	208.0	2.9
100°-110°	705.7	9.9
110°-120°	749.7	10.5
120°-130°	617.2	8.7
130°-140°	495.6	7.0
140°-150°	374.5	5.3
150°-160°	263.2	3.7
160°-170°	154.9	2.2
170°-180°	50.4	0.7
0°-30°	1025.8	14.4
0°-40°	1645.7	23.1
0°-60°	2805.0	39.4
0°-90°	3496.0	49.1
90°-120°	1663.4	23.4
90°-150°	3150.7	44.3
90°-180°	3619.0	50.9
0°-180°	7115.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1372	1366	1352	1362	1360	130
15°	1306	1298	1281	1286	1280	368
25°	1182	1171	1149	1152	1149	544
35°	1020	1006	986	978	971	637
45°	830	820	801	787	781	640
55°	628	620	604	589	582	561
65°	424	415	402	391	384	419
75°	222	219	212	205	207	237
85°	54	53	52	48	46	62
90°	1	14	34	32	33	5
95°	35	86	392	148	114	37
105°	122	184	741	1325	1127	130
115°	215	272	620	1280	1483	213
125°	300	355	596	1037	1203	266
135°	352	420	589	871	997	272
145°	402	462	586	728	796	252
155°	457	494	569	644	669	210
165°	498	513	545	578	587	140
175°	519	520	524	531	529	49
180°	520	520	520	520	520	



TEST NUMBER: P331464-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1378.6	1377.4	1376.3	1375.1	1373.9	1372.1	1369.5	1366.9	1364.3	1361.8	1364.1
5°	1372.3	1371.1	1369.9	1368.7	1367.6	1365.4	1362.2	1358.9	1355.7	1352.5	1354.9
7.5°	1360.1	1358.3	1356.5	1354.7	1352.9	1350.3	1347.0	1343.8	1340.5	1337.2	1339.5
10°	1348.5	1346.5	1344.5	1342.4	1340.3	1337.6	1334.0	1330.5	1327.0	1323.4	1325.9
12.5°	1332.7	1330.8	1329.0	1327.2	1325.4	1322.8	1319.2	1315.7	1312.3	1308.7	1310.4
15°	1306.3	1304.6	1302.8	1301.1	1299.2	1296.5	1292.7	1288.8	1285.0	1281.3	1282.5
17.5°	1272.6	1270.7	1269.0	1267.2	1265.5	1262.7	1258.8	1254.9	1251.0	1247.2	1248.5
20°	1248.3	1246.5	1244.7	1242.9	1241.2	1238.3	1234.2	1230.1	1226.0	1221.8	1222.7
22.5°	1224.0	1221.5	1219.1	1216.6	1214.1	1211.0	1207.1	1203.2	1199.4	1195.5	1195.7
25°	1182.3	1179.9	1177.6	1175.3	1172.9	1169.2	1164.2	1159.3	1154.3	1149.3	1149.9
27.5°	1134.8	1132.6	1130.6	1128.4	1126.4	1123.3	1119.4	1115.4	1111.6	1107.6	1106.7
30°	1103.1	1100.8	1098.4	1096.1	1093.7	1090.4	1086.0	1081.6	1077.2	1072.7	1071.9
32.5°	1069.4	1067.5	1065.6	1063.7	1061.8	1058.6	1054.0	1049.3	1044.7	1040.0	1038.5
35°	1019.9	1017.0	1014.1	1011.2	1008.2	1004.4	999.7	995.1	990.4	985.7	984.0
37.5°	964.3	961.7	959.2	956.6	954.0	950.4	945.6	941.0	936.3	931.6	929.4
40°	926.3	923.9	921.6	919.3	916.9	913.4	908.7	904.0	899.3	894.7	892.0
42.5°	889.3	887.0	884.7	882.4	879.9	876.4	871.8	867.0	862.4	857.6	854.8
45°	830.0	827.9	825.9	823.8	821.7	818.6	814.2	809.8	805.4	800.9	797.7
47.5°	770.9	769.0	767.0	765.1	763.1	759.8	755.3	750.7	746.1	741.6	738.1
50°	729.7	728.2	726.8	725.3	723.8	721.0	717.0	712.8	708.7	704.6	700.5
52.5°	689.6	687.7	685.7	683.8	681.8	678.9	675.0	671.1	667.4	663.5	660.0
55°	628.1	626.3	624.6	622.8	621.0	618.4	614.9	611.4	607.9	604.3	600.8
57.5°	566.4	564.9	563.5	562.1	560.7	558.1	554.2	550.4	546.5	542.6	539.2
60°	525.1	524.0	522.8	521.7	520.5	517.8	513.8	509.6	505.5	501.4	498.2
62.5°	485.1	483.2	481.3	479.4	477.5	475.0	471.8	468.7	465.5	462.4	459.3
65°	423.5	421.8	420.1	418.3	416.6	414.1	411.2	408.3	405.4	402.4	399.8
67.5°	361.0	359.6	358.2	356.8	355.4	353.4	350.7	348.1	345.4	342.9	340.8
70°	321.9	320.8	319.6	318.5	317.3	315.4	312.7	310.0	307.5	304.8	302.7
72.5°	281.8	280.7	279.5	278.4	277.2	275.7	274.1	272.3	270.6	268.9	266.8
75°	221.7	221.1	220.5	219.9	219.3	218.3	216.8	215.3	213.9	212.4	210.7
77.5°	167.8	166.9	165.8	164.9	163.8	163.1	162.5	161.9	161.3	160.7	159.8
80°	132.0	131.6	131.4	131.0	130.8	130.4	129.8	129.2	128.5	128.0	127.1
82.5°	98.2	98.2	98.1	98.0	97.9	97.7	97.4	97.0	96.7	96.3	95.2
85°	54.1	53.8	53.6	53.2	53.0	52.6	52.3	52.0	51.7	51.5	50.5
87.5°	19.2	19.4	19.6	19.6	19.5	19.6	20.1	21.1	21.9	21.6	20.7
90°	1.0	4.0	8.0	10.0	12.0	15.0	20.0	27.0	33.0	34.0	33.0
92.5°	12.2	17.6	24.8	29.2	36.0	45.4	68.0	99.8	128.2	130.0	109.9
95°	35.0	39.0	49.0	58.0	74.0	98.0	144.0	231.0	347.1	392.1	343.1
97.5°	57.0	62.4	73.0	86.6	105.0	132.2	190.0	311.3	504.1	669.3	702.1
100°	77.0	80.0	89.0	105.0	125.0	153.0	206.0	328.0	544.1	790.1	934.2
102.5°	95.4	97.6	106.6	122.6	143.4	171.4	220.4	328.9	528.9	794.2	1020.6
105°	122.0	126.1	133.0	148.0	170.0	198.0	245.0	334.1	499.1	741.1	1007.2
107.5°	150.8	154.0	160.8	174.6	196.5	224.6	270.3	347.8	484.3	684.3	919.4
110°	170.0	174.0	180.0	193.0	214.0	243.1	287.1	359.0	481.1	657.1	864.2



TEST NUMBER: P331464-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	187.6	191.7	198.5	210.6	230.8	260.6	303.1	371.1	481.9	639.6	825.8
115°	215.1	220.1	226.0	238.1	258.0	285.1	328.0	389.1	486.1	620.1	778.2
117.5°	243.5	247.5	253.5	264.1	283.3	311.3	351.0	408.3	493.3	610.7	748.1
120°	261.1	265.0	271.0	280.1	300.1	328.0	367.0	421.1	498.1	605.1	732.1
122.5°	277.8	281.0	287.1	296.9	316.8	345.7	382.3	432.3	503.7	601.9	718.5
125°	300.1	303.1	309.1	321.1	341.0	369.1	405.1	450.1	512.1	596.2	699.1
127.5°	317.6	321.7	330.1	343.3	362.5	391.2	426.3	466.7	520.7	592.7	681.1
130°	328.0	332.1	342.1	356.1	376.1	404.1	439.1	477.1	527.1	591.1	669.2
132.5°	337.7	342.5	353.3	368.1	388.9	416.9	450.3	487.5	533.5	590.3	659.5
135°	352.1	356.1	368.1	383.1	406.0	434.1	466.1	501.1	541.1	589.1	646.1
137.5°	365.7	370.5	382.5	398.5	421.3	447.3	478.9	511.5	547.9	588.9	636.7
140°	376.1	380.0	392.1	408.1	430.1	456.1	486.1	517.1	551.1	588.1	631.1
142.5°	386.5	389.7	400.9	416.9	438.1	462.5	491.7	521.9	553.5	588.1	625.5
145°	402.1	406.0	416.1	431.1	451.1	473.1	500.1	528.1	556.1	586.1	618.1
147.5°	418.9	421.9	431.4	445.3	461.9	481.5	506.9	531.5	556.9	582.6	610.5
150°	430.1	433.1	441.1	454.1	469.1	487.1	510.1	533.1	556.1	580.1	604.1
152.5°	441.3	442.7	450.6	462.1	476.3	492.7	513.3	533.9	554.5	576.1	598.5
155°	457.1	458.1	464.1	475.1	486.1	501.1	518.1	535.1	552.1	569.1	588.1
157.5°	470.3	471.3	476.1	485.7	494.5	507.1	521.5	535.1	547.5	561.9	578.3
160°	479.1	480.1	484.1	492.1	500.1	511.1	523.1	535.1	545.1	557.2	571.1
162.5°	487.9	487.3	491.3	497.7	504.9	513.5	523.9	534.3	542.7	553.1	564.7
165°	498.1	497.1	499.1	505.1	510.1	516.1	525.1	532.1	538.1	545.1	554.1
167.5°	506.5	505.3	507.1	510.9	514.5	518.3	524.9	530.7	533.5	538.1	543.7
170°	512.1	510.1	511.1	514.1	516.1	519.1	524.1	529.1	531.1	534.1	538.1
172.5°	515.3	514.1	513.5	516.5	517.7	519.9	523.3	526.7	527.9	529.3	532.5
175°	519.1	518.1	517.1	519.1	519.1	520.1	522.1	524.1	523.1	524.1	525.1
177.5°	520.9	519.3	518.5	520.1	520.1	520.1	520.9	522.5	520.9	520.1	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331464-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3	1372.3
2.5°	1366.4	1368.7	1371.1	1372.1	1371.6	1371.1	1370.6	1370.2
5°	1357.2	1359.5	1361.8	1362.8	1362.2	1361.6	1361.0	1360.4
7.5°	1341.9	1344.2	1346.6	1347.5	1346.8	1346.2	1345.5	1344.9
10°	1328.2	1330.5	1332.8	1333.6	1332.7	1331.8	1330.9	1330.1
12.5°	1312.0	1313.6	1315.3	1315.8	1315.1	1314.5	1313.8	1313.2
15°	1283.6	1284.8	1285.9	1285.8	1284.4	1282.9	1281.4	1280.0
17.5°	1249.9	1251.3	1252.6	1252.6	1251.1	1249.7	1248.4	1246.9
20°	1223.7	1224.5	1225.4	1225.2	1224.1	1222.9	1221.8	1220.6
22.5°	1195.8	1196.0	1196.2	1195.9	1195.2	1194.6	1193.8	1193.1
25°	1150.5	1151.1	1151.7	1151.7	1151.1	1150.5	1149.9	1149.3
27.5°	1105.9	1104.9	1104.1	1102.9	1101.6	1100.1	1098.7	1097.3
30°	1071.0	1070.1	1069.3	1068.2	1067.0	1065.8	1064.7	1063.5
32.5°	1036.9	1035.3	1033.7	1032.3	1031.1	1030.0	1028.8	1027.6
35°	982.1	980.4	978.6	977.1	975.6	974.1	972.6	971.1
37.5°	927.2	925.1	922.9	921.1	919.7	918.3	916.9	915.5
40°	889.3	886.7	884.1	882.2	881.0	879.9	878.7	877.4
42.5°	852.0	849.0	846.2	844.0	842.3	840.7	839.0	837.3
45°	794.5	791.3	788.1	785.8	784.6	783.5	782.3	781.2
47.5°	734.8	731.3	728.0	725.4	723.7	722.0	720.3	718.6
50°	696.4	692.3	688.2	685.4	684.0	682.5	681.1	679.6
52.5°	656.7	653.2	649.9	647.2	645.2	643.3	641.4	639.5
55°	597.3	593.7	590.3	587.8	586.3	584.9	583.4	581.9
57.5°	535.6	532.2	528.7	526.4	525.4	524.3	523.1	522.0
60°	495.0	491.7	488.5	486.5	485.6	484.7	483.8	482.9
62.5°	456.4	453.4	450.4	448.3	447.2	446.1	445.0	443.8
65°	397.2	394.5	391.9	389.9	388.4	386.9	385.5	384.0
67.5°	338.7	336.7	334.6	332.9	331.8	330.6	329.5	328.3
70°	300.7	298.7	296.6	295.0	293.8	292.7	291.4	290.3
72.5°	264.8	262.8	260.7	259.2	258.3	257.4	256.4	255.5
75°	209.0	207.2	205.4	204.8	205.4	206.0	206.6	207.2
77.5°	158.9	158.1	157.2	156.4	155.5	154.7	153.9	153.1
80°	126.2	125.4	124.5	123.7	123.1	122.6	122.0	121.4
82.5°	94.1	93.0	91.9	91.3	91.1	91.0	90.9	90.7
85°	49.7	48.8	48.0	47.4	47.1	46.8	46.5	46.1
87.5°	19.8	18.7	18.3	18.1	17.8	17.7	17.4	17.1
90°	32.0	30.0	32.0	33.0	33.0	33.0	33.0	33.0
92.5°	87.2	74.8	66.4	60.2	59.4	56.2	57.0	55.4
95°	262.1	201.0	159.0	137.0	124.0	116.1	113.0	114.0
97.5°	611.5	500.3	392.1	319.9	272.1	247.5	232.8	224.5
100°	913.2	789.2	652.1	531.1	448.1	405.1	376.1	358.1
102.5°	1110.9	1082.8	982.6	854.4	764.1	690.8	654.5	630.2
105°	1215.2	1328.3	1341.3	1308.3	1246.2	1184.2	1141.3	1127.2
107.5°	1140.1	1310.3	1414.3	1462.7	1470.5	1467.1	1458.4	1439.9
110°	1075.2	1254.2	1382.2	1464.3	1507.3	1526.3	1535.3	1534.3



TEST NUMBER: P331464-935

CATALOG NUMBER: S122DIP-S1005D1080U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1016.0	1187.8	1324.6	1418.7	1478.5	1510.3	1527.3	1532.7
115°	943.2	1097.3	1228.2	1331.3	1402.3	1448.3	1474.3	1483.3
117.5°	888.4	1023.6	1142.5	1239.1	1311.5	1360.0	1387.5	1395.1
120°	861.2	985.2	1091.2	1182.2	1252.2	1299.2	1328.3	1338.3
122.5°	839.6	953.2	1053.6	1135.8	1198.6	1244.8	1270.7	1279.0
125°	808.1	911.2	999.2	1074.2	1132.2	1170.3	1195.2	1203.2
127.5°	777.1	870.4	953.4	1022.6	1073.2	1108.8	1130.4	1136.9
130°	757.2	843.2	922.2	988.2	1037.2	1071.3	1091.2	1099.2
132.5°	738.0	817.6	890.2	952.2	1000.4	1034.4	1052.8	1060.0
135°	711.1	777.1	843.2	899.1	942.2	975.2	993.2	997.2
137.5°	689.7	744.9	797.4	846.2	885.4	913.8	929.6	935.6
140°	676.1	724.2	770.2	814.2	846.2	872.2	887.2	893.2
142.5°	665.0	705.8	745.4	782.1	812.5	836.2	849.5	850.8
145°	649.1	682.2	713.2	742.2	766.1	783.2	793.2	796.2
147.5°	637.0	663.0	687.2	708.3	728.1	741.8	748.6	750.4
150°	628.1	650.1	671.1	689.1	704.1	716.2	722.1	723.2
152.5°	619.3	639.7	657.5	673.1	684.9	695.3	699.7	699.9
155°	607.1	623.1	638.1	649.1	660.1	667.1	671.1	669.2
157.5°	592.9	606.3	618.9	627.5	635.3	641.1	642.9	642.9
160°	584.1	595.1	606.1	613.1	620.1	625.1	626.1	626.1
162.5°	575.3	584.7	594.1	599.5	606.5	609.9	610.9	610.1
165°	562.1	569.1	576.1	580.1	584.1	588.1	588.1	587.1
167.5°	549.5	554.9	559.7	563.4	565.1	567.3	567.1	565.9
170°	543.1	546.1	550.1	552.1	553.1	556.1	555.1	553.1
172.5°	535.9	538.1	541.3	542.5	543.5	544.9	543.9	542.7
175°	528.1	529.1	530.1	531.1	531.1	532.1	531.1	529.1
177.5°	522.5	522.5	523.3	523.3	523.3	523.3	522.5	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1

(END OF REPORT)