

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931457

Luminaire Tested: DFN2DS-TR4F0-040DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931457
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-040DS940-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3532.3 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 38.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931457

CATALOG NUMBER: DFN2DS-TR4F0-040DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931457

CATALOG NUMBER: DFN2DS-TR4F0-040DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1103	1103	1103
5°	1107	1091	1098
10°	1101	1080	1086
15°	1087	1066	1065
20°	1068	1045	1044
25°	1048	1019	1019
30°	1024	996	987
35°	1001	967	953
40°	972	939	921
45°	943	910	888
50°	912	881	850
55°	880	847	816
60°	844	806	776
65°	806	765	730
70°	757	716	682
75°	688	660	643
80°	611	592	562
85°	499	475	426

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 943 cd/sqm

TEST NUMBER: P931457

CATALOG NUMBER: DFN2DS-TR4F0-040DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.7	3.7
10°-20°	367.6	10.4
20°-30°	540.3	15.3
30°-40°	627.5	17.8
40°-50°	626.8	17.7
50°-60°	546.5	15.5
60°-70°	404.0	11.4
70°-80°	228.6	6.5
80°-90°	60.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1038.6	29.4
0°-40°	1666.2	47.2
0°-60°	2839.4	80.4
0°-90°	3532.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3532.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1388	1383	1368	1379	1376	132
15°	1322	1314	1296	1302	1295	372
25°	1196	1186	1163	1165	1163	550
35°	1032	1019	997	989	982	644
45°	840	830	810	796	790	648
55°	636	627	612	595	589	568
65°	429	420	407	395	389	424
75°	224	222	215	207	210	239
85°	55	53	52	48	47	64
90°	0	0	0	0	0	

TEST NUMBER: P931457

CATALOG NUMBER: DFN2DS-TR4F0-040DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.3	1388.3	1388.3	1388.3	1388.3
2.5°	1396.4	1389.7	1375.0	1388.3	1385.8
5°	1388.3	1383.0	1368.3	1378.9	1376.4
7.5°	1378.9	1371.0	1356.3	1367.1	1364.4
10°	1364.4	1355.0	1339.1	1349.7	1345.7
12.5°	1344.2	1336.3	1320.3	1327.0	1324.3
15°	1321.6	1313.6	1296.3	1301.6	1295.0
17.5°	1293.6	1285.6	1268.2	1274.8	1268.2
20°	1262.8	1254.9	1236.2	1240.1	1235.0
22.5°	1232.2	1220.2	1202.8	1202.8	1200.1
25°	1196.1	1185.5	1162.8	1165.4	1162.8
27.5°	1156.0	1146.7	1129.5	1125.4	1118.8
30°	1116.1	1105.4	1085.4	1081.4	1076.0
32.5°	1073.3	1065.4	1044.0	1036.0	1030.5
35°	1032.0	1018.7	997.3	989.2	982.5
37.5°	985.2	973.2	951.8	942.5	935.8
40°	937.2	926.4	905.0	893.2	887.8
42.5°	890.5	879.7	858.5	845.0	837.1
45°	839.7	830.5	810.3	795.8	790.3
47.5°	790.3	780.9	759.6	744.9	737.0
50°	738.2	731.5	712.9	694.2	687.5
52.5°	687.5	678.2	660.9	646.2	636.8
55°	635.6	627.4	611.5	595.4	588.8
57.5°	583.4	576.8	559.3	543.3	538.0
60°	531.3	526.0	507.4	492.7	488.6
62.5°	480.6	471.2	458.0	444.6	439.2
65°	428.6	420.5	407.2	395.2	388.6
67.5°	375.2	368.4	356.5	347.2	341.8
70°	325.8	320.4	308.4	299.0	293.7
72.5°	275.1	269.7	263.1	253.7	249.7
75°	224.2	221.7	214.9	206.9	209.6
77.5°	178.8	173.5	170.8	166.8	162.9
80°	133.5	132.1	129.4	125.5	122.8
82.5°	90.8	90.8	89.6	84.1	84.1
85°	54.7	53.4	52.1	48.0	46.7
87.5°	24.1	21.4	18.7	14.7	13.3
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931457

CATALOG NUMBER: DFN2DS-TR4F0-040DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.62	13.23	11.99	13.55	13.86	11.18	12.79	11.54	13.10	13.42
	3H	13.37	14.83	13.75	15.15	15.51	12.88	14.34	13.26	14.66	15.02
	4H	14.02	15.39	14.42	15.74	16.11	13.52	14.89	13.92	15.24	15.62
	6H	14.49	15.76	14.90	16.12	16.51	13.99	15.26	14.40	15.62	16.01
	8H	14.63	15.84	15.06	16.23	16.63	14.13	15.34	14.55	15.73	16.13
	12H	14.72	15.88	15.15	16.26	16.69	14.21	15.37	14.64	15.75	16.18
4H	2H	12.18	13.55	12.58	13.90	14.28	11.83	13.20	12.23	13.55	13.92
	3H	14.16	15.31	14.57	15.70	16.10	13.75	14.90	14.16	15.30	15.70
	4H	14.94	15.97	15.37	16.38	16.82	14.51	15.55	14.94	15.96	16.40
	6H	15.53	16.44	15.99	16.88	17.33	15.10	16.00	15.55	16.44	16.90
	8H	15.72	16.57	16.18	17.01	17.48	15.28	16.13	15.74	16.57	17.04
	12H	15.85	16.61	16.33	17.09	17.56	15.40	16.16	15.88	16.64	17.11
8H	4H	15.21	16.06	15.67	16.50	16.96	14.83	15.68	15.29	16.12	16.59
	6H	15.92	16.63	16.42	17.11	17.59	15.54	16.24	16.03	16.73	17.21
	8H	16.18	16.81	16.69	17.32	17.81	15.79	16.42	16.30	16.93	17.41
	12H	16.38	16.94	16.89	17.43	17.99	15.97	16.53	16.48	17.02	17.58
12H	4H	15.23	15.99	15.71	16.47	16.94	14.87	15.63	15.35	16.11	16.57
	6H	15.97	16.60	16.48	17.11	17.59	15.60	16.23	16.11	16.74	17.22
	8H	16.28	16.84	16.79	17.33	17.89	15.90	16.46	16.41	16.95	17.51

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

7 of 7