

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331248-935

Luminaire Tested: **S122DIP-S290D330U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331248-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D330U935-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2137.1 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331248-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331248-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	55	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6567	6567	6567
5°	6592	6498	6536
10°	6555	6432	6465
15°	6472	6349	6342
20°	6357	6223	6216
25°	6242	6070	6070
30°	6096	5929	5876
35°	5960	5757	5673
40°	5788	5590	5482
45°	5617	5421	5286
50°	5433	5247	5061
55°	5239	5044	4856
60°	5028	4799	4624
65°	4795	4558	4348
70°	4504	4263	4060
75°	4099	3924	3830
80°	3636	3533	3347
85°	2964	2816	2538



TEST NUMBER: P331248-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	1.8
10°-20°	107.6	5.0
20°-30°	158.2	7.4
30°-40°	183.8	8.6
40°-50°	183.6	8.6
50°-60°	160.1	7.5
60°-70°	118.4	5.5
70°-80°	67.0	3.1
80°-90°	19.5	0.9
90°-100°	63.3	3.0
100°-110°	214.7	10.0
110°-120°	228.0	10.7
120°-130°	187.7	8.8
130°-140°	150.7	7.1
140°-150°	113.9	5.3
150°-160°	80.1	3.7
160°-170°	47.1	2.2
170°-180°	15.3	0.7
0°-30°	304.1	14.2
0°-40°	487.8	22.8
0°-60°	831.5	38.9
0°-90°	1036.3	48.5
90°-120°	505.9	23.7
90°-150°	958.3	44.8
90°-180°	1101.0	51.5
0°-180°	2137.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	407	407	407	407	407	
5°	407	405	401	404	403	39
15°	387	385	380	381	379	109
25°	350	347	341	341	341	161
35°	302	298	292	290	288	189
45°	246	243	237	233	232	190
55°	186	184	179	175	172	166
65°	126	123	119	116	114	124
75°	66	65	63	61	61	70
85°	16	16	15	14	14	18
90°	0	4	10	10	10	1
95°	11	26	119	45	35	11
105°	37	56	225	403	343	39
115°	65	83	189	389	451	65
125°	91	108	181	315	366	81
135°	107	128	179	265	303	83
145°	122	141	178	221	242	77
155°	139	150	173	196	204	64
165°	152	156	166	176	179	43
175°	158	158	159	161	161	15
180°	158	158	158	158	158	



TEST NUMBER: P331248-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	408.6	408.3	407.9	407.6	407.3	406.7	406.0	405.2	404.4	403.6	404.3
5°	406.7	406.4	406.0	405.7	405.4	404.8	403.8	402.9	401.8	400.9	401.6
7.5°	403.2	402.6	402.1	401.6	401.1	400.3	399.3	398.3	397.4	396.4	397.1
10°	399.8	399.2	398.6	398.0	397.3	396.5	395.5	394.4	393.4	392.3	393.0
12.5°	395.0	394.5	394.0	393.4	392.9	392.1	391.1	390.0	389.0	388.0	388.4
15°	387.2	386.7	386.2	385.6	385.1	384.4	383.1	382.0	380.9	379.8	380.1
17.5°	377.2	376.7	376.2	375.7	375.1	374.3	373.2	372.0	370.8	369.7	370.1
20°	370.0	369.5	368.9	368.4	367.9	367.0	365.8	364.6	363.4	362.2	362.5
22.5°	362.8	362.1	361.4	360.6	359.9	359.0	357.8	356.6	355.5	354.4	354.4
25°	350.4	349.7	349.0	348.4	347.7	346.6	345.1	343.6	342.2	340.7	340.9
27.5°	336.4	335.8	335.1	334.5	333.9	332.9	331.8	330.6	329.5	328.3	328.0
30°	327.0	326.3	325.6	324.9	324.2	323.2	321.9	320.6	319.3	318.0	317.7
32.5°	316.9	316.4	315.9	315.3	314.8	313.7	312.4	311.1	309.7	308.3	307.8
35°	302.4	301.4	300.6	299.7	298.9	297.7	296.4	295.0	293.6	292.1	291.6
37.5°	285.9	285.1	284.3	283.5	282.8	281.7	280.3	279.0	277.5	276.1	275.5
40°	274.6	273.9	273.2	272.5	271.8	270.8	269.3	267.9	266.6	265.2	264.4
42.5°	263.6	262.9	262.3	261.6	260.9	259.8	258.4	257.0	255.6	254.3	253.4
45°	246.0	245.4	244.8	244.2	243.6	242.6	241.3	240.0	238.8	237.4	236.4
47.5°	228.5	227.9	227.4	226.8	226.2	225.2	223.9	222.6	221.2	219.8	218.8
50°	216.3	215.9	215.4	215.0	214.6	213.7	212.5	211.3	210.1	208.9	207.7
52.5°	204.4	203.8	203.3	202.7	202.1	201.2	200.1	199.0	197.8	196.7	195.6
55°	186.1	185.6	185.1	184.6	184.1	183.3	182.3	181.2	180.2	179.2	178.1
57.5°	167.9	167.5	167.0	166.6	166.2	165.4	164.3	163.2	162.0	160.8	159.8
60°	155.7	155.3	155.0	154.6	154.3	153.5	152.3	151.1	149.8	148.6	147.7
62.5°	143.8	143.2	142.7	142.2	141.5	140.8	139.8	139.0	138.0	137.1	136.1
65°	125.5	125.0	124.5	124.0	123.5	122.8	121.9	121.1	120.2	119.3	118.5
67.5°	107.0	106.6	106.2	105.7	105.4	104.8	103.9	103.1	102.4	101.6	101.0
70°	95.4	95.1	94.7	94.4	94.0	93.5	92.7	92.0	91.1	90.3	89.7
72.5°	83.5	83.2	82.8	82.5	82.1	81.7	81.2	80.8	80.2	79.7	79.1
75°	65.7	65.5	65.3	65.2	65.0	64.7	64.3	63.8	63.4	62.9	62.4
77.5°	49.8	49.4	49.2	48.9	48.6	48.3	48.1	48.0	47.8	47.6	47.4
80°	39.1	39.0	38.9	38.8	38.7	38.7	38.5	38.3	38.1	38.0	37.7
82.5°	29.1	29.1	29.1	29.0	29.0	28.9	28.8	28.8	28.7	28.6	28.2
85°	16.0	15.9	15.8	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.0
87.5°	5.7	5.8	5.9	5.9	5.8	5.9	6.0	6.3	6.5	6.5	6.2
90°	0.3	1.2	2.4	3.0	3.6	4.6	6.1	8.2	10.1	10.3	10.1
92.5°	3.7	5.3	7.6	8.9	10.9	13.8	20.7	30.4	39.0	39.5	33.4
95°	10.7	11.9	14.9	17.7	22.5	29.8	43.8	70.3	105.6	119.2	104.4
97.5°	17.3	18.9	22.2	26.3	31.9	40.2	57.8	94.7	153.3	203.5	213.5
100°	23.4	24.4	27.0	31.9	38.1	46.6	62.7	99.8	165.5	240.3	284.1
102.5°	29.0	29.7	32.5	37.3	43.7	52.2	67.1	100.0	160.8	241.5	310.4
105°	37.1	38.3	40.5	45.0	51.7	60.3	74.6	101.6	151.8	225.4	306.3
107.5°	45.9	46.8	48.9	53.1	59.8	68.4	82.2	105.8	147.3	208.1	279.7
110°	51.7	53.0	54.8	58.7	65.1	74.0	87.3	109.2	146.4	199.8	262.9



TEST NUMBER: P331248-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.1	58.3	60.4	64.1	70.2	79.3	92.2	112.9	146.5	194.5	251.2
115°	65.4	66.9	68.8	72.4	78.5	86.7	99.8	118.3	147.8	188.6	236.7
117.5°	74.0	75.3	77.1	80.3	86.2	94.7	106.8	124.2	150.1	185.7	227.6
120°	79.4	80.6	82.5	85.2	91.3	99.8	111.7	128.1	151.5	184.1	222.7
122.5°	84.6	85.5	87.3	90.3	96.3	105.1	116.2	131.5	153.2	183.0	218.5
125°	91.3	92.2	94.0	97.6	103.8	112.3	123.2	136.9	155.8	181.3	212.7
127.5°	96.6	97.8	100.4	104.4	110.2	119.0	129.7	142.0	158.3	180.3	207.2
130°	99.8	101.0	104.0	108.3	114.4	122.9	133.5	145.1	160.3	179.8	203.5
132.5°	102.7	104.2	107.5	111.9	118.3	126.8	137.0	148.3	162.3	179.5	200.6
135°	107.1	108.3	111.9	116.5	123.6	132.0	141.8	152.4	164.6	179.2	196.5
137.5°	111.2	112.7	116.3	121.2	128.1	136.0	145.7	155.6	166.7	179.1	193.6
140°	114.4	115.6	119.2	124.2	130.8	138.7	147.8	157.3	167.6	178.9	191.9
142.5°	117.5	118.6	121.9	126.8	133.3	140.7	149.6	158.8	168.3	178.9	190.3
145°	122.3	123.6	126.6	131.1	137.2	143.9	152.1	160.7	169.1	178.2	188.0
147.5°	127.4	128.3	131.2	135.4	140.5	146.5	154.2	161.7	169.4	177.2	185.7
150°	130.8	131.7	134.1	138.1	142.7	148.2	155.2	162.1	169.1	176.4	183.7
152.5°	134.2	134.7	137.1	140.5	144.9	149.8	156.1	162.4	168.7	175.2	182.0
155°	139.1	139.3	141.1	144.5	147.8	152.4	157.6	162.7	167.9	173.1	178.9
157.5°	143.0	143.4	144.8	147.7	150.4	154.2	158.6	162.7	166.5	170.9	175.9
160°	145.7	146.0	147.2	149.6	152.1	155.5	159.1	162.7	165.8	169.4	173.7
162.5°	148.4	148.2	149.5	151.4	153.6	156.2	159.4	162.5	165.1	168.2	171.8
165°	151.5	151.2	151.8	153.6	155.2	157.0	159.7	161.9	163.7	165.8	168.5
167.5°	154.0	153.7	154.2	155.4	156.5	157.6	159.6	161.4	162.3	163.7	165.4
170°	155.8	155.2	155.5	156.4	157.0	157.9	159.4	160.9	161.5	162.5	163.7
172.5°	156.7	156.4	156.2	157.1	157.5	158.2	159.2	160.2	160.6	161.0	162.0
175°	157.9	157.6	157.3	157.9	157.9	158.2	158.8	159.4	159.1	159.4	159.7
177.5°	158.4	157.9	157.7	158.2	158.2	158.2	158.4	158.9	158.4	158.2	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331248-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	405.0	405.7	406.4	406.7	406.6	406.4	406.3	406.1
5°	402.3	403.0	403.7	404.0	403.8	403.6	403.5	403.3
7.5°	397.8	398.5	399.2	399.4	399.2	399.0	398.8	398.6
10°	393.7	394.4	395.1	395.3	395.0	394.8	394.5	394.3
12.5°	388.9	389.3	389.9	390.0	389.9	389.6	389.4	389.3
15°	380.5	380.8	381.2	381.2	380.7	380.3	379.9	379.4
17.5°	370.5	370.9	371.3	371.3	370.8	370.5	370.1	369.6
20°	362.7	363.0	363.3	363.2	362.8	362.5	362.1	361.8
22.5°	354.5	354.6	354.6	354.5	354.3	354.0	353.9	353.7
25°	341.0	341.2	341.4	341.4	341.2	341.0	340.9	340.7
27.5°	327.8	327.5	327.3	326.9	326.5	326.1	325.7	325.3
30°	317.5	317.2	316.9	316.7	316.3	316.0	315.6	315.2
32.5°	307.4	306.9	306.4	306.0	305.7	305.3	305.0	304.6
35°	291.1	290.6	290.1	289.6	289.2	288.8	288.3	287.8
37.5°	274.8	274.2	273.5	273.0	272.6	272.2	271.8	271.4
40°	263.6	262.9	262.1	261.5	261.1	260.8	260.5	260.1
42.5°	252.5	251.7	250.8	250.1	249.7	249.2	248.7	248.2
45°	235.5	234.5	233.6	232.9	232.6	232.2	231.9	231.5
47.5°	217.8	216.8	215.8	215.0	214.6	214.0	213.5	213.0
50°	206.5	205.2	204.0	203.2	202.8	202.3	201.9	201.5
52.5°	194.7	193.6	192.6	191.8	191.2	190.7	190.1	189.5
55°	177.0	176.0	175.0	174.3	173.8	173.3	172.9	172.5
57.5°	158.8	157.7	156.7	156.0	155.8	155.4	155.1	154.7
60°	146.7	145.8	144.8	144.2	144.0	143.7	143.4	143.2
62.5°	135.3	134.4	133.5	132.9	132.6	132.2	131.9	131.6
65°	117.7	116.9	116.1	115.5	115.1	114.7	114.3	113.8
67.5°	100.4	99.8	99.2	98.7	98.3	98.0	97.6	97.3
70°	89.1	88.5	87.9	87.5	87.1	86.7	86.4	86.0
72.5°	78.5	77.9	77.3	76.8	76.5	76.3	76.0	75.7
75°	61.9	61.4	60.9	60.7	60.9	61.0	61.2	61.4
77.5°	47.1	46.8	46.6	46.3	46.1	45.9	45.6	45.4
80°	37.5	37.2	36.9	36.7	36.5	36.3	36.2	36.0
82.5°	27.9	27.6	27.2	27.0	27.0	26.9	26.9	26.9
85°	14.7	14.5	14.2	14.0	13.9	13.9	13.8	13.7
87.5°	5.9	5.6	5.5	5.4	5.3	5.3	5.2	5.2
90°	9.7	9.1	9.7	10.1	10.1	10.1	10.1	10.1
92.5°	26.5	22.7	20.2	18.3	18.1	17.1	17.3	16.9
95°	79.7	61.1	48.4	41.7	37.7	35.3	34.4	34.7
97.5°	186.0	152.1	119.2	97.3	82.7	75.3	70.9	68.3
100°	277.8	240.0	198.4	161.5	136.3	123.2	114.4	108.9
102.5°	337.9	329.3	298.9	259.8	232.4	210.1	199.1	191.7
105°	369.6	404.0	407.9	398.0	379.0	360.2	347.1	342.9
107.5°	346.7	398.6	430.2	444.9	447.3	446.3	443.6	438.0
110°	327.0	381.5	420.4	445.4	458.5	464.3	467.0	466.7



TEST NUMBER: P331248-935

CATALOG NUMBER: S122DIP-S290D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	309.0	361.3	402.9	431.5	449.7	459.3	464.5	466.1
115°	286.9	333.7	373.6	404.9	426.5	440.5	448.4	451.2
117.5°	270.2	311.3	347.5	376.9	398.9	413.7	422.0	424.3
120°	261.9	299.6	331.9	359.6	380.9	395.2	404.0	407.1
122.5°	255.4	289.9	320.5	345.4	364.5	378.7	386.5	389.0
125°	245.8	277.2	303.9	326.7	344.4	355.9	363.5	366.0
127.5°	236.3	264.8	290.0	311.0	326.4	337.3	343.8	345.8
130°	230.3	256.5	280.5	300.6	315.5	325.8	331.9	334.3
132.5°	224.5	248.7	270.8	289.6	304.3	314.6	320.2	322.4
135°	216.3	236.3	256.5	273.5	286.5	296.6	302.1	303.3
137.5°	209.8	226.6	242.5	257.4	269.3	277.9	282.8	284.6
140°	205.6	220.2	234.3	247.6	257.4	265.3	269.8	271.6
142.5°	202.2	214.6	226.7	237.9	247.1	254.3	258.4	258.7
145°	197.4	207.5	216.9	225.8	233.0	238.2	241.3	242.1
147.5°	193.7	201.6	209.0	215.4	221.4	225.6	227.6	228.3
150°	191.1	197.8	204.1	209.6	214.1	217.8	219.6	220.0
152.5°	188.4	194.6	200.0	204.7	208.4	211.5	212.8	212.9
155°	184.7	189.5	194.1	197.4	200.8	202.9	204.1	203.5
157.5°	180.4	184.4	188.2	190.9	193.2	195.0	195.5	195.5
160°	177.6	181.0	184.3	186.5	188.6	190.1	190.5	190.5
162.5°	175.0	177.9	180.7	182.4	184.5	185.5	185.8	185.5
165°	171.0	173.1	175.2	176.4	177.6	178.9	178.9	178.6
167.5°	167.1	168.8	170.2	171.3	171.9	172.5	172.5	172.1
170°	165.2	166.1	167.3	167.9	168.2	169.1	168.8	168.2
172.5°	163.0	163.7	164.6	165.0	165.3	165.7	165.4	165.1
175°	160.7	160.9	161.3	161.5	161.5	161.9	161.5	160.9
177.5°	158.9	158.9	159.2	159.2	159.2	159.2	158.9	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2

(END OF REPORT)