

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331275-935

Luminaire Tested: **S122DIP-S290D925U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331275-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S290D925U935-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4148.3 lumens  
Efficiency: N/A  
Efficacy: 111.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331275-935

CATALOG NUMBER: S122DIP-S290D925U935-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331275-935

CATALOG NUMBER: S122DIP-S290D925U935-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33	25
1	92	88	84	81	82	78	75	73	61	59	57	44	43	42	29	29	28	21
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	23	18
3	76	67	60	55	68	60	54	50	47	43	39	34	32	29	23	21	20	15
4	70	60	52	46	62	53	47	42	41	37	33	31	28	25	20	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	39	34	52	42	36	31	33	28	25	25	21	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6567	6567	6567
5°	6592	6498	6536
10°	6555	6432	6465
15°	6472	6349	6342
20°	6357	6223	6216
25°	6242	6070	6070
30°	6096	5929	5876
35°	5960	5757	5673
40°	5788	5590	5482
45°	5617	5421	5286
50°	5433	5247	5061
55°	5239	5044	4856
60°	5028	4799	4624
65°	4795	4558	4348
70°	4504	4263	4060
75°	4099	3924	3830
80°	3636	3533	3347
85°	2964	2816	2538



TEST NUMBER: P331275-935

CATALOG NUMBER: S122DIP-S290D925U935-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.3	0.9
10°-20°	107.6	2.6
20°-30°	158.2	3.8
30°-40°	183.8	4.4
40°-50°	183.6	4.4
50°-60°	160.1	3.9
60°-70°	118.4	2.9
70°-80°	67.0	1.6
80°-90°	22.0	0.5
90°-100°	178.7	4.3
100°-110°	606.3	14.6
110°-120°	644.1	15.5
120°-130°	530.2	12.8
130°-140°	425.8	10.3
140°-150°	321.8	7.8
150°-160°	226.1	5.5
160°-170°	133.1	3.2
170°-180°	43.3	1.0
0°-30°	304.1	7.3
0°-40°	487.8	11.8
0°-60°	831.5	20.0
0°-90°	1038.9	25.0
90°-120°	1429.1	34.4
90°-150°	2706.8	65.3
90°-180°	3109.0	74.9
0°-180°	4148.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	407	407	407	407	407	
5°	407	405	401	404	403	39
15°	387	385	380	381	379	109
25°	350	347	341	341	341	161
35°	302	298	292	290	288	189
45°	246	243	237	233	232	190
55°	186	184	179	175	172	166
65°	126	123	119	116	114	124
75°	66	65	63	61	61	70
85°	16	16	15	14	14	18
90°	1	12	29	28	28	2
95°	30	74	337	127	98	32
105°	105	158	637	1138	968	111
115°	185	233	533	1100	1274	183
125°	258	305	512	891	1034	229
135°	302	361	506	748	857	234
145°	345	397	504	625	684	217
155°	393	424	489	553	575	181
165°	428	441	468	497	504	121
175°	446	446	450	456	455	42
180°	447	447	447	447	447	



TEST NUMBER: P331275-935

CATALOG NUMBER: S122DIP-S290D925U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	408.6	408.3	407.9	407.6	407.3	406.7	406.0	405.2	404.4	403.6	404.3
5°	406.7	406.4	406.0	405.7	405.4	404.8	403.8	402.9	401.8	400.9	401.6
7.5°	403.2	402.6	402.1	401.6	401.1	400.3	399.3	398.3	397.4	396.4	397.1
10°	399.8	399.2	398.6	398.0	397.3	396.5	395.5	394.4	393.4	392.3	393.0
12.5°	395.0	394.5	394.0	393.4	392.9	392.1	391.1	390.0	389.0	388.0	388.4
15°	387.2	386.7	386.2	385.6	385.1	384.4	383.1	382.0	380.9	379.8	380.1
17.5°	377.2	376.7	376.2	375.7	375.1	374.3	373.2	372.0	370.8	369.7	370.1
20°	370.0	369.5	368.9	368.4	367.9	367.0	365.8	364.6	363.4	362.2	362.5
22.5°	362.8	362.1	361.4	360.6	359.9	359.0	357.8	356.6	355.5	354.4	354.4
25°	350.4	349.7	349.0	348.4	347.7	346.6	345.1	343.6	342.2	340.7	340.9
27.5°	336.4	335.8	335.1	334.5	333.9	332.9	331.8	330.6	329.5	328.3	328.0
30°	327.0	326.3	325.6	324.9	324.2	323.2	321.9	320.6	319.3	318.0	317.7
32.5°	316.9	316.4	315.9	315.3	314.8	313.7	312.4	311.1	309.7	308.3	307.8
35°	302.4	301.4	300.6	299.7	298.9	297.7	296.4	295.0	293.6	292.1	291.6
37.5°	285.9	285.1	284.3	283.5	282.8	281.7	280.3	279.0	277.5	276.1	275.5
40°	274.6	273.9	273.2	272.5	271.8	270.8	269.3	267.9	266.6	265.2	264.4
42.5°	263.6	262.9	262.3	261.6	260.9	259.8	258.4	257.0	255.6	254.3	253.4
45°	246.0	245.4	244.8	244.2	243.6	242.6	241.3	240.0	238.8	237.4	236.4
47.5°	228.5	227.9	227.4	226.8	226.2	225.2	223.9	222.6	221.2	219.8	218.8
50°	216.3	215.9	215.4	215.0	214.6	213.7	212.5	211.3	210.1	208.9	207.7
52.5°	204.4	203.8	203.3	202.7	202.1	201.2	200.1	199.0	197.8	196.7	195.6
55°	186.1	185.6	185.1	184.6	184.1	183.3	182.3	181.2	180.2	179.2	178.1
57.5°	167.9	167.5	167.0	166.6	166.2	165.4	164.3	163.2	162.0	160.8	159.8
60°	155.7	155.3	155.0	154.6	154.3	153.5	152.3	151.1	149.8	148.6	147.7
62.5°	143.8	143.2	142.7	142.2	141.5	140.8	139.8	139.0	138.0	137.1	136.1
65°	125.5	125.0	124.5	124.0	123.5	122.8	121.9	121.1	120.2	119.3	118.5
67.5°	107.0	106.6	106.2	105.7	105.4	104.8	103.9	103.1	102.4	101.6	101.0
70°	95.4	95.1	94.7	94.4	94.0	93.5	92.7	92.0	91.1	90.3	89.7
72.5°	83.5	83.2	82.8	82.5	82.1	81.7	81.2	80.8	80.2	79.7	79.1
75°	65.7	65.5	65.3	65.2	65.0	64.7	64.3	63.8	63.4	62.9	62.4
77.5°	49.8	49.4	49.2	48.9	48.6	48.3	48.1	48.0	47.8	47.6	47.4
80°	39.1	39.0	38.9	38.8	38.7	38.7	38.5	38.3	38.1	38.0	37.7
82.5°	29.1	29.1	29.1	29.0	29.0	28.9	28.8	28.8	28.7	28.6	28.2
85°	16.0	15.9	15.8	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.0
87.5°	5.8	6.2	6.7	7.0	7.1	7.5	8.3	9.3	10.2	10.2	9.8
90°	0.9	3.4	6.9	8.6	10.3	12.9	17.2	23.2	28.3	29.2	28.3
92.5°	10.5	15.2	21.4	25.1	30.9	39.0	58.5	85.8	110.1	111.7	94.4
95°	30.0	33.5	42.1	49.9	63.6	84.2	123.7	198.5	298.2	336.8	294.7
97.5°	49.0	53.6	62.8	74.4	90.2	113.6	163.2	267.4	433.1	575.1	603.2
100°	66.1	68.7	76.5	90.2	107.5	131.5	177.0	281.9	467.4	678.8	802.6
102.5°	82.0	83.9	91.6	105.4	123.2	147.3	189.4	282.6	454.4	682.3	876.8
105°	104.9	108.3	114.3	127.2	146.1	170.1	210.5	287.0	428.8	636.7	865.3
107.5°	129.6	132.3	138.2	150.1	168.8	193.0	232.2	298.9	416.0	588.0	789.9
110°	146.1	149.6	154.6	165.8	183.9	208.8	246.6	308.5	413.4	564.6	742.4



TEST NUMBER: P331275-935

CATALOG NUMBER: S122DIP-S290D925U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	161.2	164.6	170.5	181.0	198.3	223.9	260.4	318.8	414.0	549.4	709.5
115°	184.8	189.1	194.2	204.5	221.7	244.9	281.9	334.2	417.6	532.8	668.6
117.5°	209.1	212.6	217.7	226.9	243.3	267.4	301.6	350.8	423.8	524.7	642.7
120°	224.3	227.7	232.9	240.6	257.8	281.9	315.4	361.8	427.9	519.9	629.0
122.5°	238.8	241.4	246.6	255.0	272.2	297.0	328.4	371.3	432.7	517.1	617.3
125°	257.8	260.4	265.5	275.9	293.0	317.1	348.0	386.7	440.0	512.1	600.6
127.5°	272.9	276.4	283.5	294.9	311.4	336.1	366.3	401.0	447.4	509.2	585.2
130°	281.9	285.2	293.9	305.9	323.1	347.2	377.2	409.9	452.9	507.8	574.9
132.5°	290.1	294.2	303.5	316.2	334.1	358.2	386.8	418.8	458.3	507.1	566.6
135°	302.5	305.9	316.2	329.1	348.9	372.9	400.5	430.5	464.9	506.1	555.1
137.5°	314.2	318.3	328.6	342.3	362.0	384.3	411.5	439.5	470.7	505.9	547.0
140°	323.1	326.6	336.8	350.6	369.5	391.8	417.6	444.3	473.5	505.2	542.3
142.5°	332.0	334.8	344.4	358.2	376.3	397.4	422.4	448.4	475.5	505.2	537.4
145°	345.4	348.9	357.5	370.4	387.5	406.5	429.6	453.7	477.8	503.5	531.1
147.5°	359.9	362.5	370.7	382.5	396.8	413.7	435.5	456.7	478.5	500.5	524.5
150°	369.5	372.0	378.9	390.1	403.0	418.4	438.2	458.0	477.8	498.4	519.0
152.5°	379.1	380.3	387.2	397.0	409.2	423.3	441.0	458.7	476.4	495.0	514.2
155°	392.7	393.6	398.7	408.2	417.6	430.5	445.1	459.7	474.3	489.0	505.2
157.5°	404.1	404.9	409.1	417.2	424.8	435.7	448.1	459.7	470.4	482.8	496.9
160°	411.6	412.5	415.9	422.8	429.6	439.1	449.4	459.7	468.3	478.6	490.7
162.5°	419.1	418.6	422.1	427.6	433.8	441.2	450.1	459.0	466.2	475.2	485.2
165°	427.9	427.1	428.8	433.9	438.2	443.4	451.2	457.2	462.3	468.3	476.0
167.5°	435.1	434.1	435.7	438.9	442.0	445.3	451.0	456.0	458.3	462.3	467.1
170°	440.0	438.2	439.1	441.7	443.4	446.0	450.3	454.6	456.3	458.8	462.3
172.5°	442.7	441.7	441.2	443.8	444.8	446.7	449.6	452.5	453.6	454.8	457.5
175°	446.0	445.1	444.3	446.0	446.0	446.9	448.6	450.3	449.4	450.3	451.2
177.5°	447.5	446.2	445.5	446.9	446.9	446.9	447.5	448.9	447.5	446.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9



TEST NUMBER: P331275-935

CATALOG NUMBER: S122DIP-S290D925U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	405.0	405.7	406.4	406.7	406.6	406.4	406.3	406.1
5°	402.3	403.0	403.7	404.0	403.8	403.6	403.5	403.3
7.5°	397.8	398.5	399.2	399.4	399.2	399.0	398.8	398.6
10°	393.7	394.4	395.1	395.3	395.0	394.8	394.5	394.3
12.5°	388.9	389.3	389.9	390.0	389.9	389.6	389.4	389.3
15°	380.5	380.8	381.2	381.2	380.7	380.3	379.9	379.4
17.5°	370.5	370.9	371.3	371.3	370.8	370.5	370.1	369.6
20°	362.7	363.0	363.3	363.2	362.8	362.5	362.1	361.8
22.5°	354.5	354.6	354.6	354.5	354.3	354.0	353.9	353.7
25°	341.0	341.2	341.4	341.4	341.2	341.0	340.9	340.7
27.5°	327.8	327.5	327.3	326.9	326.5	326.1	325.7	325.3
30°	317.5	317.2	316.9	316.7	316.3	316.0	315.6	315.2
32.5°	307.4	306.9	306.4	306.0	305.7	305.3	305.0	304.6
35°	291.1	290.6	290.1	289.6	289.2	288.8	288.3	287.8
37.5°	274.8	274.2	273.5	273.0	272.6	272.2	271.8	271.4
40°	263.6	262.9	262.1	261.5	261.1	260.8	260.5	260.1
42.5°	252.5	251.7	250.8	250.1	249.7	249.2	248.7	248.2
45°	235.5	234.5	233.6	232.9	232.6	232.2	231.9	231.5
47.5°	217.8	216.8	215.8	215.0	214.6	214.0	213.5	213.0
50°	206.5	205.2	204.0	203.2	202.8	202.3	201.9	201.5
52.5°	194.7	193.6	192.6	191.8	191.2	190.7	190.1	189.5
55°	177.0	176.0	175.0	174.3	173.8	173.3	172.9	172.5
57.5°	158.8	157.7	156.7	156.0	155.8	155.4	155.1	154.7
60°	146.7	145.8	144.8	144.2	144.0	143.7	143.4	143.2
62.5°	135.3	134.4	133.5	132.9	132.6	132.2	131.9	131.6
65°	117.7	116.9	116.1	115.5	115.1	114.7	114.3	113.8
67.5°	100.4	99.8	99.2	98.7	98.3	98.0	97.6	97.3
70°	89.1	88.5	87.9	87.5	87.1	86.7	86.4	86.0
72.5°	78.5	77.9	77.3	76.8	76.5	76.3	76.0	75.7
75°	61.9	61.4	60.9	60.7	60.9	61.0	61.2	61.4
77.5°	47.1	46.8	46.6	46.3	46.1	45.9	45.6	45.4
80°	37.5	37.2	36.9	36.7	36.5	36.3	36.2	36.0
82.5°	27.9	27.6	27.2	27.0	27.0	26.9	26.9	26.9
85°	14.7	14.5	14.2	14.0	13.9	13.9	13.8	13.7
87.5°	9.5	8.9	9.0	9.0	9.0	9.0	8.9	8.8
90°	27.5	25.7	27.5	28.3	28.3	28.3	28.3	28.3
92.5°	74.9	64.3	57.1	51.7	51.1	48.3	49.0	47.6
95°	225.2	172.7	136.6	117.7	106.6	99.7	97.1	98.0
97.5°	525.4	429.8	336.8	274.8	233.8	212.6	200.0	192.9
100°	784.5	678.0	560.3	456.3	385.0	348.0	323.1	307.6
102.5°	954.3	930.3	844.2	734.0	656.5	593.4	562.3	541.4
105°	1044.0	1141.2	1152.4	1123.9	1070.7	1017.4	980.4	968.5
107.5°	979.5	1125.7	1215.0	1256.6	1263.3	1260.4	1253.0	1237.1
110°	923.8	1077.5	1187.6	1258.0	1294.9	1311.3	1319.1	1318.2





TEST NUMBER: P331275-935

CATALOG NUMBER: S122DIP-S290D925U935-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	872.9	1020.5	1138.1	1218.8	1270.2	1297.5	1312.2	1316.8
115°	810.3	942.6	1055.2	1143.8	1204.7	1244.2	1266.6	1274.4
117.5°	763.2	879.4	981.5	1064.5	1126.7	1168.5	1192.1	1198.5
120°	739.9	846.4	937.5	1015.7	1075.8	1116.2	1141.2	1149.8
122.5°	721.3	818.9	905.2	975.9	1029.8	1069.4	1091.7	1098.9
125°	694.3	782.8	858.4	922.9	972.8	1005.4	1026.8	1033.7
127.5°	667.7	747.8	819.1	878.6	922.0	952.6	971.2	976.7
130°	650.5	724.4	792.3	849.0	891.1	920.3	937.5	944.3
132.5°	634.0	702.4	764.7	818.0	859.5	888.7	904.5	910.7
135°	611.0	667.7	724.4	772.5	809.4	837.8	853.3	856.7
137.5°	592.5	640.0	685.0	726.9	760.7	785.1	798.7	803.8
140°	580.9	622.2	661.7	699.5	726.9	749.3	762.2	767.3
142.5°	571.3	606.3	640.3	672.0	698.1	718.4	729.9	730.9
145°	557.7	586.1	612.7	637.6	658.2	672.9	681.4	684.0
147.5°	547.2	569.6	590.3	608.6	625.6	637.2	643.1	644.6
150°	539.7	558.5	576.6	592.0	604.9	615.3	620.4	621.3
152.5°	532.1	549.6	564.9	578.3	588.4	597.4	601.2	601.3
155°	521.6	535.4	548.2	557.7	567.1	573.2	576.6	574.9
157.5°	509.4	520.9	531.8	539.2	545.8	550.8	552.3	552.3
160°	501.8	511.3	520.7	526.8	532.8	537.1	538.0	538.0
162.5°	494.3	502.3	510.4	515.1	521.1	524.0	524.9	524.2
165°	482.9	489.0	495.0	498.4	501.8	505.2	505.2	504.4
167.5°	472.1	476.7	480.9	484.0	485.5	487.4	487.2	486.2
170°	466.6	469.2	472.6	474.3	475.2	477.8	476.9	475.2
172.5°	460.4	462.3	465.0	466.1	466.9	468.1	467.3	466.2
175°	453.7	454.6	455.5	456.3	456.3	457.2	456.3	454.6
177.5°	448.9	448.9	449.6	449.6	449.6	449.6	448.9	447.5
180°	446.9	446.9	446.9	446.9	446.9	446.9	446.9	446.9

(END OF REPORT)