

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931547

Luminaire Tested: DFN2DS-TR4F0-090DS940-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-090DS940-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7947.7 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 93.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931547

CATALOG NUMBER: DFN2DS-TR4F0-090DS940-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931547

CATALOG NUMBER: DFN2DS-TR4F0-090DS940-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90	88	86	84
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63	58	54	51
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57	51	47	45
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52	46	41	39
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47	41	37	35
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44	38	33	31
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40	34	30	28
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37	32	27	26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2482	2482	2482
5°	2491	2455	2470
10°	2476	2430	2442
15°	2446	2399	2396
20°	2402	2351	2349
25°	2359	2293	2293
30°	2304	2240	2221
35°	2252	2176	2144
40°	2187	2112	2072
45°	2123	2048	1998
50°	2053	1982	1912
55°	1981	1905	1835
60°	1899	1814	1747
65°	1813	1722	1643
70°	1703	1612	1535
75°	1549	1484	1448
80°	1375	1332	1264
85°	1121	1069	959

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2123 cd/sqm

TEST NUMBER: P931547

CATALOG NUMBER: DFN2DS-TR4F0-090DS940-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	294.0	3.7
10°-20°	827.2	10.4
20°-30°	1215.7	15.3
30°-40°	1412.0	17.8
40°-50°	1410.2	17.7
50°-60°	1229.7	15.5
60°-70°	909.0	11.4
70°-80°	514.3	6.5
80°-90°	135.7	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2336.9	29.4
0°-40°	3748.9	47.2
0°-60°	6388.7	80.4
0°-90°	7947.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7947.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3124	3124	3124	3124	3124	
5°	3124	3112	3079	3103	3097	297
15°	2974	2956	2917	2929	2914	837
25°	2691	2667	2616	2622	2616	1238
35°	2322	2292	2244	2226	2211	1450
45°	1889	1868	1823	1790	1778	1458
55°	1430	1412	1376	1340	1325	1278
65°	964	946	916	889	874	953
75°	504	499	484	466	472	539
85°	123	120	117	108	105	145
90°	0	0	0	0	0	

TEST NUMBER: P931547

CATALOG NUMBER: DFN2DS-TR4F0-090DS940-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3123.7	3123.7	3123.7	3123.7	3123.7
2.5°	3141.9	3126.9	3093.8	3123.7	3118.0
5°	3123.7	3111.9	3078.8	3102.7	3096.9
7.5°	3102.7	3084.9	3051.7	3076.0	3069.9
10°	3069.9	3048.9	3012.8	3036.7	3027.8
12.5°	3024.6	3006.8	2970.8	2985.7	2979.7
15°	2973.7	2955.8	2916.6	2928.7	2913.7
17.5°	2910.5	2892.7	2853.5	2868.5	2853.5
20°	2841.4	2823.5	2781.4	2790.4	2778.6
22.5°	2772.5	2745.5	2706.2	2706.2	2700.2
25°	2691.3	2667.3	2616.4	2622.1	2616.4
27.5°	2601.1	2580.0	2541.2	2532.3	2517.3
30°	2511.2	2487.0	2442.0	2433.1	2421.1
32.5°	2415.0	2397.2	2349.0	2330.9	2318.8
35°	2322.0	2292.0	2243.8	2225.7	2210.7
37.5°	2216.8	2189.7	2141.5	2120.6	2105.6
40°	2108.7	2084.5	2036.3	2009.6	1997.5
42.5°	2003.5	1979.3	1931.5	1901.3	1883.5
45°	1889.4	1868.5	1823.2	1790.3	1778.3
47.5°	1778.3	1757.2	1709.1	1676.0	1658.1
50°	1661.0	1646.0	1603.9	1561.9	1546.9
52.5°	1546.9	1525.9	1487.0	1453.9	1432.8
55°	1430.0	1411.8	1375.7	1339.8	1324.8
57.5°	1312.7	1297.7	1258.5	1222.5	1210.4
60°	1195.4	1183.6	1141.5	1108.4	1099.5
62.5°	1081.3	1060.2	1030.3	1000.4	988.2
65°	964.3	946.1	916.2	889.1	874.2
67.5°	844.2	828.9	802.1	781.1	769.0
70°	733.0	720.8	693.8	672.7	661.0
72.5°	618.9	606.7	591.8	570.8	561.9
75°	504.5	498.7	483.5	465.6	471.7
77.5°	402.5	390.4	384.4	375.4	366.5
80°	300.5	297.3	291.2	282.3	276.3
82.5°	204.3	204.3	201.4	189.3	189.3
85°	123.0	120.2	117.3	108.0	105.2
87.5°	54.1	48.1	42.1	33.2	30.0
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931547

CATALOG NUMBER: DFN2DS-TR4F0-090DS940-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.44	16.05	14.81	16.37	16.68	14.00	15.61	14.36	15.92	16.24
	3H	16.19	17.65	16.57	17.97	18.33	15.70	17.15	16.08	17.48	17.84
	4H	16.84	18.21	17.24	18.55	18.93	16.34	17.71	16.74	18.06	18.44
	6H	17.31	18.57	17.72	18.94	19.33	16.80	18.07	17.22	18.44	18.83
	8H	17.45	18.66	17.87	19.05	19.45	16.95	18.16	17.37	18.55	18.95
	12H	17.54	18.70	17.97	19.08	19.51	17.03	18.19	17.46	18.57	19.00
4H	2H	15.00	16.37	15.40	16.72	17.09	14.65	16.02	15.05	16.36	16.74
	3H	16.98	18.12	17.39	18.52	18.92	16.57	17.72	16.98	18.11	18.51
	4H	17.75	18.79	18.18	19.20	19.64	17.33	18.36	17.76	18.78	19.21
	6H	18.35	19.25	18.80	19.69	20.15	17.92	18.82	18.37	19.26	19.72
	8H	18.54	19.38	19.00	19.83	20.29	18.10	18.95	18.56	19.39	19.85
	12H	18.67	19.43	19.15	19.91	20.38	18.22	18.98	18.70	19.45	19.92
8H	4H	18.03	18.87	18.49	19.31	19.78	17.65	18.50	18.11	18.94	19.41
	6H	18.74	19.44	19.23	19.93	20.41	18.36	19.06	18.85	19.55	20.03
	8H	19.00	19.63	19.51	20.14	20.62	18.61	19.24	19.12	19.75	20.23
	12H	19.20	19.76	19.71	20.25	20.81	18.79	19.34	19.29	19.83	20.40
12H	4H	18.05	18.81	18.53	19.29	19.76	17.69	18.45	18.17	18.92	19.39
	6H	18.79	19.42	19.29	19.92	20.41	18.42	19.05	18.93	19.56	20.04
	8H	19.10	19.66	19.61	20.15	20.71	18.72	19.28	19.23	19.77	20.33

END OF REPORT