

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331369-935

Luminaire Tested: **S122DIP-S675D1080U935-4F0-1E-UDD-D**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331369-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D1080U935-4F0-1E-UDD-D
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6023.8 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331369-935

CATALOG NUMBER: S122DIP-S675D1080U935-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P331369-935

CATALOG NUMBER: S122DIP-S675D1080U935-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34
1	93	89	84	81	84	80	76	73	64	61	59	49	47	46	35	34	33	27
2	84	77	70	65	76	69	64	59	55	51	48	42	40	37	30	29	27	22
3	77	67	60	54	69	61	54	49	48	44	40	37	34	31	26	24	23	18
4	70	59	51	45	63	53	46	41	43	38	34	33	29	26	23	21	19	15
5	64	52	44	38	57	47	40	35	38	33	29	29	25	22	21	18	16	13
6	59	47	39	33	53	42	35	30	34	29	25	26	22	19	19	16	14	11
7	54	42	34	28	49	38	31	26	31	25	22	24	20	17	17	15	13	10
8	50	38	30	25	45	34	28	23	28	23	19	22	18	15	16	13	11	9
9	47	35	27	22	42	31	25	20	25	20	17	20	16	13	15	12	10	8
10	43	32	24	20	39	29	22	18	23	18	15	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9792	9792	9792
5°	9839	9426	9390
10°	9778	9148	9044
15°	9643	8853	8681
20°	9473	8536	8331
25°	9305	8231	8014
30°	9067	7919	7694
35°	8828	7615	7468
40°	8576	7358	7243
45°	8334	7127	7051
50°	8078	6920	6861
55°	7810	6696	6668
60°	7480	6465	6465
65°	7135	6192	6222
70°	6751	5899	5960
75°	6257	5612	5720
80°	5488	5319	5476
85°	4743	5064	5286



TEST NUMBER: P331369-935

CATALOG NUMBER: S122DIP-S675D1080U935-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	1.0
10°-20°	164.8	2.7
20°-30°	249.7	4.1
30°-40°	304.2	5.0
40°-50°	327.2	5.4
50°-60°	317.8	5.3
60°-70°	277.5	4.6
70°-80°	213.6	3.5
80°-90°	146.5	2.4
90°-100°	141.0	2.3
100°-110°	226.9	3.8
110°-120°	461.2	7.7
120°-130°	709.3	11.8
130°-140°	737.3	12.2
140°-150°	676.8	11.2
150°-160°	542.6	9.0
160°-170°	349.7	5.8
170°-180°	120.4	2.0
0°-30°	472.0	7.8
0°-40°	776.1	12.9
0°-60°	1421.1	23.6
0°-90°	2058.7	34.2
90°-120°	829.1	13.8
90°-150°	2952.5	49.0
90°-180°	3965.0	65.8
0°-180°	6023.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	606	606	606	606	606	
5°	608	605	600	605	605	58
15°	580	582	582	589	589	163
25°	527	534	541	552	555	242
35°	454	469	486	505	512	284
45°	373	397	427	453	463	288
55°	286	318	363	394	406	255
65°	195	239	290	325	338	194
75°	108	158	214	250	263	114
85°	32	86	142	178	192	34
90°	10	71	134	173	186	9
95°	67	80	137	173	184	78
105°	283	321	131	171	186	302
115°	530	557	617	239	164	521
125°	746	760	803	832	844	665
135°	922	936	953	980	986	712
145°	1068	1068	1083	1094	1094	668
155°	1176	1169	1179	1184	1177	542
165°	1239	1234	1237	1242	1237	350
175°	1268	1262	1263	1269	1260	121
180°	1265	1265	1265	1265	1265	



TEST NUMBER: P331369-935

CATALOG NUMBER: S122DIP-S675D1080U935-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	606.5	606.5	606.5	606.5	606.5	606.5	606.5	606.5	606.5	606.5	606.5
2.5°	610.0	609.5	609.1	608.6	608.1	607.3	606.2	605.1	604.1	603.0	603.7
5°	608.2	607.6	607.1	606.5	605.9	605.0	603.8	602.7	601.5	600.3	601.5
7.5°	602.8	602.4	602.0	601.6	601.2	600.5	599.7	598.7	597.9	597.0	598.4
10°	598.6	598.1	597.8	597.4	597.0	596.5	595.9	595.4	594.8	594.2	595.7
12.5°	591.5	591.6	591.7	591.8	591.9	591.7	591.2	590.8	590.4	590.0	591.5
15°	580.1	580.5	580.9	581.3	581.7	581.9	581.9	581.9	581.9	581.9	583.6
17.5°	565.3	566.2	567.0	567.8	568.6	569.4	570.0	570.6	571.2	571.9	573.7
20°	555.5	556.5	557.4	558.4	559.4	560.3	561.0	561.9	562.7	563.4	565.6
22.5°	544.9	546.0	547.3	548.4	549.5	550.6	551.7	552.8	553.9	555.0	557.2
25°	527.4	528.7	530.1	531.5	532.9	534.4	536.1	538.0	539.7	541.4	543.8
27.5°	506.3	508.5	510.7	513.0	515.2	517.4	519.4	521.5	523.6	525.6	528.6
30°	492.2	494.7	497.3	499.8	502.4	504.9	507.5	510.0	512.6	515.1	518.1
32.5°	476.7	479.6	482.4	485.3	488.2	491.1	494.1	497.1	500.1	503.1	506.7
35°	454.4	457.7	461.1	464.3	467.7	471.2	474.9	478.6	482.3	486.0	490.3
37.5°	430.2	434.0	437.8	441.6	445.5	449.8	454.6	459.4	464.2	469.0	473.8
40°	414.0	418.3	422.6	426.9	431.2	435.9	441.3	446.5	451.8	457.0	462.1
42.5°	398.6	402.8	407.1	411.4	415.7	420.9	427.0	433.0	439.0	445.1	450.6
45°	372.6	378.0	383.2	388.5	393.7	399.8	406.7	413.5	420.3	427.1	433.3
47.5°	347.2	352.9	358.7	364.4	370.1	377.0	385.0	393.0	401.1	409.1	415.4
50°	329.6	335.7	341.7	347.8	353.8	361.3	370.1	378.8	387.6	396.4	403.0
52.5°	312.7	319.1	325.5	331.8	338.2	346.0	355.2	364.5	373.8	383.1	389.9
55°	285.7	292.7	299.7	306.8	313.7	322.4	332.5	342.7	352.8	363.0	370.1
57.5°	258.9	266.9	274.8	282.8	290.7	299.8	310.1	320.5	330.9	341.2	348.8
60°	240.0	248.3	256.8	265.2	273.5	283.4	294.5	305.6	316.7	327.9	335.3
62.5°	223.1	231.8	240.5	249.2	258.0	267.9	279.0	290.1	301.3	312.4	320.3
65°	195.1	204.7	214.3	223.9	233.4	243.9	255.5	267.0	278.5	290.1	298.1
67.5°	169.4	179.4	189.5	199.5	209.5	220.3	232.1	243.9	255.7	267.5	275.6
70°	151.2	161.4	171.5	181.7	191.8	202.9	215.1	227.1	239.3	251.4	259.8
72.5°	134.3	144.7	155.2	165.7	176.2	187.5	199.8	212.1	224.4	236.6	244.9
75°	108.1	119.1	130.0	140.9	151.9	163.6	176.1	188.6	201.0	213.6	222.0
77.5°	82.8	94.3	105.7	117.1	128.5	140.7	153.3	166.1	178.7	191.4	199.8
80°	66.0	77.8	89.7	101.7	113.6	125.9	138.6	151.3	163.9	176.7	184.9
82.5°	51.8	63.6	75.3	87.1	98.9	111.2	124.1	136.9	149.7	162.6	170.8
85°	31.7	43.7	55.9	67.9	80.1	92.4	104.9	117.4	129.9	142.4	150.6
87.5°	17.4	29.5	41.6	53.6	65.8	78.3	91.0	103.8	116.7	129.5	137.7
90°	9.7	23.2	36.9	50.4	64.0	77.8	92.0	106.1	120.2	134.3	143.2
92.5°	26.6	36.9	47.3	57.6	67.9	79.6	92.4	105.2	118.0	131.0	139.1
95°	66.6	69.0	71.5	74.0	76.4	84.2	97.4	110.5	123.6	136.8	145.3
97.5°	124.2	113.5	102.7	92.0	81.2	83.1	97.6	112.2	126.7	141.3	149.3
100°	168.2	147.5	126.9	106.2	85.6	82.5	96.9	111.2	125.7	140.1	149.0
102.5°	215.8	216.5	217.2	217.9	218.6	209.8	191.5	173.2	154.9	136.6	145.8
105°	282.7	294.4	306.2	318.0	329.7	312.9	267.5	222.1	176.8	131.4	140.5
107.5°	359.9	369.4	378.8	388.2	397.7	374.0	317.1	260.3	203.5	146.5	150.8
110°	409.0	417.2	425.3	433.5	441.7	421.2	372.0	322.8	273.5	224.4	210.3



TEST NUMBER: P331369-935

CATALOG NUMBER: S122DIP-S675D1080U935-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	455.8	462.9	469.9	477.1	484.1	484.9	479.5	474.1	468.6	463.2	395.3
115°	529.8	535.4	541.1	546.6	552.2	562.0	575.8	589.7	603.6	617.4	529.2
117.5°	595.0	600.3	605.5	610.8	616.1	624.6	636.2	647.8	659.4	671.1	654.0
120°	643.3	647.1	651.0	654.8	658.7	666.3	677.8	689.2	700.8	712.2	720.1
122.5°	684.3	687.9	691.4	694.9	698.4	705.8	717.2	728.5	739.9	751.2	757.9
125°	745.9	748.6	751.1	753.8	756.5	762.8	772.9	783.1	793.2	803.3	810.0
127.5°	802.5	805.2	807.9	810.6	813.4	818.7	826.6	834.6	842.5	850.4	857.3
130°	838.4	841.4	844.5	847.5	850.6	855.2	861.6	868.0	874.3	880.6	887.5
132.5°	874.9	877.5	880.1	882.6	885.2	889.2	894.6	900.0	905.4	910.9	917.2
135°	921.6	924.9	928.2	931.4	934.7	938.1	941.9	945.7	949.5	953.3	959.5
137.5°	969.8	972.1	974.3	976.5	978.8	981.4	984.3	987.2	990.2	993.1	998.7
140°	1001.3	1002.7	1004.2	1005.6	1007.0	1009.0	1011.7	1014.3	1016.9	1019.5	1024.5
142.5°	1027.6	1028.9	1030.2	1031.5	1032.7	1034.7	1037.3	1039.9	1042.6	1045.3	1049.4
145°	1068.2	1067.9	1067.7	1067.6	1067.3	1068.9	1072.4	1075.8	1079.3	1082.8	1085.4
147.5°	1104.2	1103.5	1102.7	1101.9	1101.1	1102.4	1105.9	1109.2	1112.7	1116.1	1117.3
150°	1127.7	1126.2	1124.8	1123.3	1122.0	1122.8	1126.1	1129.4	1132.6	1135.8	1137.1
152.5°	1147.4	1145.8	1144.2	1142.6	1141.1	1141.8	1144.9	1148.0	1151.1	1154.2	1155.4
155°	1176.1	1174.3	1172.5	1170.6	1168.8	1169.2	1171.6	1174.0	1176.5	1178.9	1180.1
157.5°	1198.7	1197.1	1195.6	1194.0	1192.5	1192.6	1194.3	1195.9	1197.7	1199.4	1200.8
160°	1211.9	1210.7	1209.4	1208.2	1206.9	1206.9	1208.2	1209.4	1210.7	1211.9	1213.1
162.5°	1223.6	1222.4	1221.1	1219.9	1218.7	1218.6	1219.6	1220.7	1221.8	1222.8	1224.2
165°	1239.3	1238.0	1236.8	1235.6	1234.4	1234.1	1234.7	1235.4	1236.0	1236.6	1237.9
167.5°	1251.0	1249.8	1248.5	1247.3	1246.1	1245.8	1246.4	1246.9	1247.5	1248.1	1249.5
170°	1257.6	1256.4	1255.2	1254.0	1252.8	1252.3	1252.8	1253.1	1253.5	1254.0	1255.3
172.5°	1262.0	1260.8	1259.6	1258.4	1257.1	1256.7	1257.1	1257.5	1257.9	1258.4	1259.7
175°	1267.7	1266.3	1264.8	1263.4	1262.0	1261.5	1261.9	1262.3	1262.7	1263.1	1264.6
177.5°	1268.6	1267.5	1266.3	1265.2	1264.0	1263.5	1263.7	1263.9	1264.0	1264.2	1265.3
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9



TEST NUMBER: P331369-935

CATALOG NUMBER: S122DIP-S675D1080U935-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	606.5	606.5	606.5	606.5	606.5	606.5	606.5	606.5
2.5°	604.5	605.3	606.1	606.3	606.0	605.7	605.4	605.1
5°	602.7	603.8	605.0	605.5	605.3	605.1	604.9	604.7
7.5°	599.8	601.2	602.6	603.2	603.0	602.8	602.6	602.4
10°	597.3	598.8	600.5	601.1	600.9	600.7	600.5	600.3
12.5°	593.1	594.6	596.2	596.8	596.7	596.5	596.3	596.1
15°	585.4	587.1	588.9	589.7	589.5	589.3	589.1	588.9
17.5°	575.5	577.4	579.2	580.1	580.1	580.1	580.1	580.1
20°	567.7	569.9	572.0	573.1	573.1	573.1	573.1	573.1
22.5°	559.3	561.5	563.5	564.8	565.1	565.4	565.8	566.0
25°	546.1	548.5	550.8	552.2	552.8	553.5	554.1	554.7
27.5°	531.6	534.5	537.5	539.2	539.6	540.0	540.4	540.9
30°	521.3	524.4	527.5	529.4	530.0	530.6	531.2	531.8
32.5°	510.3	513.9	517.5	519.8	520.9	521.9	523.0	524.0
35°	494.6	498.9	503.3	506.1	507.5	508.9	510.1	511.5
37.5°	478.5	483.3	488.1	491.2	492.7	494.0	495.5	497.0
40°	467.2	472.3	477.3	480.8	482.5	484.3	486.0	487.8
42.5°	456.2	461.8	467.3	471.0	472.7	474.5	476.2	477.9
45°	439.3	445.3	451.4	455.4	457.4	459.3	461.2	463.2
47.5°	421.7	428.1	434.4	438.6	440.7	442.9	445.1	447.2
50°	409.7	416.3	423.0	427.4	429.6	431.7	433.8	435.9
52.5°	396.7	403.5	410.3	414.8	417.1	419.4	421.7	424.0
55°	377.0	384.1	391.2	395.9	398.5	401.0	403.6	406.0
57.5°	356.4	363.9	371.5	376.6	379.2	381.8	384.4	386.9
60°	342.7	350.1	357.6	362.7	365.3	368.1	370.8	373.6
62.5°	328.1	336.0	344.0	349.2	351.7	354.3	356.9	359.5
65°	306.1	314.1	322.1	327.4	329.9	332.4	335.0	337.5
67.5°	283.7	291.8	299.9	305.3	307.9	310.6	313.2	315.9
70°	268.2	276.6	285.0	290.3	292.7	295.1	297.4	299.7
72.5°	253.1	261.3	269.6	275.1	277.9	280.8	283.5	286.4
75°	230.4	238.8	247.2	252.6	255.2	257.7	260.3	262.8
77.5°	208.2	216.5	224.9	230.4	233.2	235.9	238.6	241.3
80°	193.0	201.3	209.5	215.0	217.7	220.4	223.2	225.9
82.5°	179.0	187.2	195.4	200.8	203.4	206.0	208.5	211.1
85°	158.8	167.0	175.2	180.6	183.4	186.1	188.9	191.6
87.5°	145.9	154.0	162.2	167.6	170.1	172.7	175.3	177.9
90°	152.0	160.8	169.6	175.5	178.2	180.9	183.7	186.4
92.5°	147.3	155.5	163.7	169.0	171.7	174.3	176.8	179.4
95°	153.7	162.1	170.6	175.8	178.0	180.1	182.3	184.4
97.5°	157.4	165.4	173.5	178.7	181.3	183.8	186.4	189.0
100°	157.7	166.6	175.5	181.2	183.7	186.3	188.8	191.4
102.5°	155.0	164.2	173.3	179.3	182.0	184.8	187.4	190.2
105°	149.6	158.7	167.7	173.7	176.7	179.7	182.6	185.5
107.5°	155.2	159.4	163.7	167.3	170.3	173.2	176.2	179.2
110°	196.1	182.1	168.0	162.4	165.4	168.3	171.3	174.3



TEST NUMBER: P331369-935

CATALOG NUMBER: S122DIP-S675D1080U935-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	327.4	259.4	191.5	158.9	161.7	164.5	167.3	170.0
115°	440.8	352.5	264.2	213.8	201.3	188.8	176.3	163.8
117.5°	637.1	620.0	603.0	571.4	525.4	479.2	433.1	386.9
120°	728.1	736.0	743.8	735.1	709.8	684.5	659.2	634.0
122.5°	764.7	771.5	778.3	780.0	776.4	772.9	769.5	765.9
125°	816.7	823.4	830.1	834.7	837.0	839.4	841.7	844.1
127.5°	864.3	871.2	878.1	882.4	884.3	886.1	888.0	889.8
130°	894.5	901.4	908.4	912.5	913.8	915.2	916.5	917.9
132.5°	923.7	930.1	936.6	940.5	941.8	943.2	944.6	945.9
135°	965.6	971.7	977.8	981.5	982.7	983.9	985.0	986.1
137.5°	1004.3	1009.9	1015.5	1018.6	1019.2	1019.8	1020.5	1021.1
140°	1029.5	1034.4	1039.4	1041.9	1042.1	1042.2	1042.4	1042.6
142.5°	1053.6	1057.7	1061.9	1064.0	1064.0	1064.0	1064.0	1064.0
145°	1088.0	1090.5	1093.1	1094.4	1094.4	1094.3	1094.3	1094.2
147.5°	1118.5	1119.7	1120.9	1121.4	1120.9	1120.6	1120.2	1119.8
150°	1138.3	1139.5	1140.7	1140.8	1139.8	1138.8	1137.8	1136.8
152.5°	1156.6	1157.9	1159.1	1159.0	1157.6	1156.3	1154.9	1153.7
155°	1181.3	1182.6	1183.8	1183.5	1181.9	1180.3	1178.7	1177.1
157.5°	1202.1	1203.5	1204.9	1204.8	1203.2	1201.6	1200.1	1198.4
160°	1214.3	1215.5	1216.7	1216.6	1215.2	1213.8	1212.4	1210.9
162.5°	1225.5	1226.9	1228.4	1228.1	1226.4	1224.7	1222.9	1221.2
165°	1239.4	1240.8	1242.3	1242.3	1240.8	1239.4	1237.9	1236.6
167.5°	1250.9	1252.3	1253.8	1253.5	1251.7	1249.9	1248.1	1246.2
170°	1256.8	1258.2	1259.6	1259.4	1257.6	1255.8	1254.0	1252.1
172.5°	1261.2	1262.6	1264.0	1263.9	1262.0	1260.2	1258.4	1256.5
175°	1265.9	1267.4	1268.8	1268.5	1266.4	1264.4	1262.4	1260.3
177.5°	1266.4	1267.6	1268.8	1268.6	1267.1	1265.7	1264.2	1262.7
180°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9

(END OF REPORT)