

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P931459

Luminaire Tested: DFN2DS-TR4F0-040DS950-FLL

Issue Date: 11/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P931459
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P333812)
Test Lab: INNOVATION CENTER
Issue Date: 11/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DS-TR4F0-040DS950-FLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3742.2 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular (W 3.96' x L: 3.43' x H: 0')
CIE Type: Direct

Input Watts (W): 38.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P931459

CATALOG NUMBER: DFN2DS-TR4F0-040DS950-FLL

Luminous Intensity Polar Plot



TEST NUMBER: P931459

CATALOG NUMBER: DFN2DS-TR4F0-040DS950-FLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	85	79	97	89	83	78	86	81	76		83	78	74		80
3	91	80	72	66	88	79	71	65	76	69	64		73	68	63		71
4	83	71	63	56	81	70	62	56	68	61	55		65	59	54		63
5	77	64	55	49	75	63	55	48	61	53	48		59	52	47		57
6	71	58	49	43	69	57	48	42	55	48	42		53	47	42		52
7	66	52	44	38	64	52	43	38	50	43	37		49	42	37		47
8	61	48	40	34	60	47	39	34	46	39	33		45	38	33		44
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	53	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1168	1168	1168
5°	1173	1156	1163
10°	1166	1144	1150
15°	1152	1129	1128
20°	1131	1107	1106
25°	1111	1080	1080
30°	1085	1055	1046
35°	1060	1025	1009
40°	1030	994	975
45°	999	964	941
50°	967	933	900
55°	933	897	864
60°	894	854	823
65°	854	811	774
70°	802	759	723
75°	729	699	682
80°	647	627	595
85°	528	503	451

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 999 cd/sqm

TEST NUMBER: P931459

CATALOG NUMBER: DFN2DS-TR4F0-040DS950-FLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.4	3.7
10°-20°	389.5	10.4
20°-30°	572.4	15.3
30°-40°	664.8	17.8
40°-50°	664.0	17.7
50°-60°	579.0	15.5
60°-70°	428.0	11.4
70°-80°	242.2	6.5
80°-90°	63.9	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1100.3	29.4
0°-40°	1765.2	47.2
0°-60°	3008.1	80.4
0°-90°	3742.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3742.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1471	1471	1471	1471	1471	
5°	1471	1465	1450	1461	1458	140
15°	1400	1392	1373	1379	1372	394
25°	1267	1256	1232	1235	1232	583
35°	1093	1079	1056	1048	1041	683
45°	890	880	858	843	837	687
55°	673	665	648	631	624	602
65°	454	446	431	419	412	449
75°	238	235	228	219	222	254
85°	58	57	55	51	50	68
90°	0	0	0	0	0	

TEST NUMBER: P931459

CATALOG NUMBER: DFN2DS-TR4F0-040DS950-FLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1470.8	1470.8	1470.8	1470.8	1470.8
2.5°	1479.4	1472.3	1456.7	1470.8	1468.2
5°	1470.8	1465.2	1449.6	1460.9	1458.2
7.5°	1460.9	1452.5	1436.9	1448.3	1445.5
10°	1445.5	1435.5	1418.6	1429.9	1425.6
12.5°	1424.1	1415.7	1398.8	1405.9	1402.9
15°	1400.1	1391.7	1373.3	1378.9	1372.0
17.5°	1370.4	1362.0	1343.6	1350.6	1343.6
20°	1337.8	1329.4	1309.7	1313.8	1308.4
22.5°	1305.4	1292.7	1274.2	1274.2	1271.4
25°	1267.2	1255.9	1231.9	1234.6	1231.9
27.5°	1224.7	1214.8	1196.6	1192.3	1185.3
30°	1182.4	1171.0	1149.9	1145.6	1140.0
32.5°	1137.1	1128.7	1106.0	1097.5	1091.8
35°	1093.3	1079.2	1056.5	1048.0	1040.9
37.5°	1043.8	1031.0	1008.3	998.5	991.4
40°	992.9	981.5	958.8	946.2	940.6
42.5°	943.4	932.0	909.5	895.2	886.8
45°	889.6	879.8	858.4	843.0	837.3
47.5°	837.3	827.3	804.8	789.2	780.8
50°	782.1	775.0	755.2	735.4	728.3
52.5°	728.3	718.5	700.2	684.6	674.6
55°	673.3	664.7	647.8	630.8	623.8
57.5°	618.0	611.0	592.5	575.6	569.9
60°	562.8	557.3	537.5	521.9	517.7
62.5°	509.2	499.2	485.2	471.0	465.3
65°	454.1	445.5	431.4	418.6	411.6
67.5°	397.5	390.3	377.7	367.8	362.1
70°	345.1	339.4	326.7	316.8	311.2
72.5°	291.4	285.7	278.7	268.8	264.5
75°	237.6	234.8	227.7	219.2	222.1
77.5°	189.5	183.8	181.0	176.7	172.6
80°	141.5	140.0	137.1	133.0	130.1
82.5°	96.2	96.2	94.9	89.1	89.1
85°	57.9	56.6	55.2	50.8	49.5
87.5°	25.5	22.7	19.8	15.6	14.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P931459

CATALOG NUMBER: DFN2DS-TR4F0-040DS950-FLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.82	13.43	12.19	13.75	14.06	11.38	12.99	11.74	13.30	13.62
	3H	13.57	15.03	13.95	15.35	15.72	13.08	14.54	13.46	14.86	15.22
	4H	14.22	15.59	14.62	15.94	16.31	13.73	15.09	14.12	15.44	15.82
	6H	14.69	15.96	15.10	16.32	16.71	14.19	15.46	14.60	15.82	16.21
	8H	14.83	16.04	15.26	16.43	16.83	14.33	15.54	14.75	15.93	16.33
	12H	14.92	16.08	15.35	16.46	16.89	14.41	15.57	14.84	15.95	16.38
4H	2H	12.38	13.75	12.78	14.10	14.48	12.03	13.40	12.43	13.75	14.12
	3H	14.36	15.51	14.77	15.90	16.30	13.95	15.10	14.36	15.50	15.90
	4H	15.14	16.17	15.57	16.58	17.02	14.71	15.75	15.14	16.16	16.60
	6H	15.73	16.64	16.19	17.08	17.53	15.30	16.20	15.75	16.65	17.10
	8H	15.92	16.77	16.38	17.21	17.68	15.48	16.33	15.94	16.77	17.24
	12H	16.05	16.81	16.53	17.29	17.76	15.60	16.36	16.08	16.84	17.31
8H	4H	15.41	16.26	15.87	16.70	17.16	15.03	15.88	15.50	16.32	16.79
	6H	16.12	16.83	16.62	17.31	17.79	15.74	16.44	16.24	16.93	17.41
	8H	16.38	17.01	16.89	17.52	18.01	15.99	16.62	16.50	17.13	17.61
	12H	16.58	17.14	17.09	17.63	18.19	16.17	16.73	16.68	17.22	17.78
12H	4H	15.43	16.19	15.92	16.67	17.14	15.07	15.83	15.55	16.31	16.78
	6H	16.17	16.80	16.68	17.31	17.79	15.80	16.43	16.31	16.94	17.42
	8H	16.48	17.04	16.99	17.53	18.09	16.10	16.66	16.61	17.15	17.71