

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331340-935

Luminaire Tested: **S122DIP-S675D530U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331340-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S675D530U935-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4152.3 lumens  
Efficiency: N/A  
Efficacy: 103.0 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	66	66	66	66	66	66	66	66	61																	
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	59	58	57	57	57	57	57	57	57	57	57	57	57	57	52																	
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	49	49	49	49	49	49	49	49	49	49	49	45																	
3	85	75	68	62	79	71	65	59	62	58	53	55	51	48	47	45	42	42	42	42	42	42	42	42	42	42	42	42	39																	
4	78	67	59	53	73	63	56	51	56	50	46	49	45	41	43	40	37	37	37	37	37	37	37	37	37	37	37	37	34																	
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33	33	33	33	33	33	33	33	33	33	33	33	30																	
6	66	54	46	41	62	51	44	39	46	40	36	40	36	32	35	32	29	29	29	29	29	29	29	29	29	29	29	29	26																	
7	61	49	41	36	57	47	40	34	42	36	32	37	32	29	33	29	26	26	26	26	26	26	26	26	26	26	26	26	24																	
8	57	45	37	32	54	43	36	31	38	32	28	34	29	26	30	26	24	24	24	24	24	24	24	24	24	24	24	24	21																	
9	53	41	34	29	50	39	32	28	35	30	26	31	27	23	28	24	21	21	21	21	21	21	21	21	21	21	21	21	19																	
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	20	20	20	20	20	20	20	20	20	20	20	18																	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	18466	18466	18466	18466
5°	20702	18585	16470	18585
10°	23722	18433	14254	18433
15°	26242	18094	12593	18094
20°	25844	17732	11478	17732
25°	23302	17250	10774	17250
30°	19257	16479	10260	16479
35°	14034	15672	9895	15672
40°	11209	14720	9691	14720
45°	9796	13618	9412	13618
50°	9206	12552	9231	12552
55°	8487	11468	8982	11468
60°	7776	10317	8603	10317
65°	7087	9287	8225	9287
70°	6430	8280	7676	8280
75°	5702	7155	6800	7155
80°	4909	5923	5477	5923
85°	4409	4409	3260	4409



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.9	2.6
10°-20°	316.6	7.6
20°-30°	459.5	11.1
30°-40°	484.9	11.7
40°-50°	429.4	10.3
50°-60°	342.6	8.3
60°-70°	232.9	5.6
70°-80°	119.4	2.9
80°-90°	31.1	0.7
90°-100°	36.9	0.9
100°-110°	114.5	2.8
110°-120°	195.7	4.7
120°-130°	257.4	6.2
130°-140°	288.9	7.0
140°-150°	283.3	6.8
150°-160°	237.6	5.7
160°-170°	157.6	3.8
170°-180°	55.1	1.3
0°-30°	885.1	21.3
0°-40°	1370.0	33.0
0°-60°	2142.0	51.6
0°-90°	2525.4	60.8
90°-120°	347.1	8.4
90°-150°	1176.6	28.3
90°-180°	1627.0	39.2
0°-180°	4152.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1144	1144	1144	1144	1144	
5°	1277	1147	1016	1147	1277	128
15°	1570	1082	753	1082	1570	433
25°	1308	968	605	968	1308	591
35°	712	795	502	795	712	463
45°	429	596	412	596	429	337
55°	302	407	319	407	302	270
65°	186	243	215	243	186	184
75°	91	115	109	115	91	98
85°	24	24	18	24	24	26
90°	17	0	17	0	17	8
95°	30	26	30	26	30	34
105°	109	106	109	106	109	115
115°	196	196	196	196	196	194
125°	287	286	287	286	287	256
135°	374	370	374	370	374	288
145°	454	449	454	449	454	283
155°	517	513	517	513	517	238
165°	559	558	559	558	559	158
175°	579	581	579	581	579	55
180°	582	582	582	582	582	



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1196.4	1196.7	1197.5	1191.8	1191.1	1191.1	1186.2	1182.0	1177.1	1170.4	1171.0
5°	1277.3	1282.1	1283.8	1278.6	1270.7	1269.8	1262.3	1250.0	1238.5	1229.3	1222.8
7.5°	1373.8	1375.7	1371.4	1364.4	1358.6	1348.1	1334.1	1320.5	1301.4	1283.9	1270.9
10°	1446.9	1449.6	1442.1	1432.0	1423.7	1411.4	1391.1	1370.5	1345.4	1321.2	1301.8
12.5°	1502.4	1509.0	1499.4	1498.1	1483.8	1466.9	1442.8	1432.4	1397.1	1363.4	1342.6
15°	1569.9	1569.5	1570.5	1562.1	1551.5	1548.9	1523.4	1495.7	1446.0	1426.2	1392.0
17.5°	1550.5	1557.1	1560.2	1560.1	1559.9	1558.2	1550.1	1532.6	1507.7	1475.6	1436.0
20°	1504.1	1512.9	1514.2	1524.3	1530.0	1537.5	1540.5	1535.7	1520.4	1493.5	1459.2
22.5°	1432.4	1434.8	1438.9	1454.7	1467.1	1485.7	1495.6	1511.8	1505.9	1492.8	1464.1
25°	1308.0	1303.6	1319.1	1326.9	1355.5	1385.3	1407.0	1430.6	1451.7	1464.5	1456.1
27.5°	1158.7	1152.2	1175.2	1196.2	1219.4	1251.8	1285.4	1325.0	1358.0	1399.2	1413.3
30°	1032.9	1036.8	1058.9	1081.2	1116.4	1162.1	1199.9	1243.5	1290.5	1336.6	1368.6
32.5°	897.2	912.4	926.3	960.6	991.5	1042.6	1097.9	1152.4	1211.0	1263.4	1313.1
35°	712.0	729.6	749.0	774.0	817.5	868.1	922.1	995.5	1075.6	1147.2	1206.1
37.5°	599.3	596.5	607.6	625.7	661.0	701.7	764.0	836.5	930.7	1014.9	1097.9
40°	531.8	530.0	538.0	554.7	581.5	611.4	665.9	729.6	817.1	919.9	1018.8
42.5°	485.4	486.5	490.9	502.7	521.0	545.6	586.4	640.7	720.7	817.6	923.9
45°	429.0	432.0	436.9	442.6	453.1	473.4	496.2	534.9	598.2	679.1	783.7
47.5°	388.4	388.5	393.4	398.4	404.7	416.0	434.7	458.9	503.6	569.5	659.4
50°	366.5	363.5	367.0	370.9	377.5	385.5	397.8	420.6	450.5	503.7	578.9
52.5°	339.8	339.9	343.1	344.6	350.5	358.3	369.6	385.5	412.5	454.1	515.9
55°	301.5	303.7	305.5	308.1	313.4	319.1	327.9	338.5	359.6	390.7	436.4
57.5°	265.4	266.1	267.9	272.9	276.3	281.5	289.9	299.5	313.2	336.3	370.7
60°	240.8	240.8	244.4	246.6	251.0	256.2	262.9	272.1	284.4	303.2	331.0
62.5°	218.3	218.0	219.4	223.0	226.4	231.3	237.9	245.7	257.3	274.1	296.9
65°	185.5	184.6	187.3	188.1	191.7	196.5	201.7	210.1	219.3	231.6	251.8
67.5°	153.9	154.9	156.3	158.0	159.9	165.0	168.5	174.4	182.2	192.4	206.1
70°	136.2	136.2	136.2	137.6	140.2	142.8	146.4	151.2	158.7	167.5	179.8
72.5°	116.6	118.0	119.3	118.6	121.9	123.5	127.7	130.4	137.6	143.2	154.1
75°	91.4	91.4	91.4	93.6	95.0	96.3	98.9	101.5	105.0	112.1	117.8
77.5°	68.2	68.0	68.4	69.0	70.4	72.0	72.8	75.2	78.4	81.6	86.5
80°	52.8	53.6	54.1	54.9	54.9	55.8	56.2	59.3	61.6	63.7	66.8
82.5°	40.8	41.0	41.1	41.2	41.6	42.1	43.2	44.3	45.0	46.8	49.2
85°	23.8	23.3	23.3	24.2	23.8	23.8	24.6	25.5	25.5	25.9	27.2
87.5°	12.5	12.5	12.8	12.4	12.4	12.7	12.8	12.5	12.9	13.3	13.2
90°	16.7	16.6	16.4	16.4	16.3	16.3	16.5	16.8	17.0	17.2	14.8
92.5°	15.9	15.9	15.8	15.8	15.8	15.8	15.8	15.7	15.7	15.6	15.1
95°	30.5	30.7	30.9	31.1	31.3	31.4	31.4	31.4	31.4	31.4	31.2
97.5°	52.7	52.8	52.8	52.8	52.8	52.9	52.9	52.9	52.9	52.9	52.4
100°	67.2	67.4	67.5	67.6	67.7	67.8	67.8	67.8	67.8	67.8	67.4
102.5°	83.8	83.9	83.9	84.1	84.2	84.2	84.1	84.0	83.9	83.9	83.4
105°	109.0	109.0	109.0	109.0	109.0	108.9	108.7	108.5	108.2	108.1	107.8
107.5°	132.8	133.3	133.8	134.2	134.7	135.0	134.9	134.8	134.7	134.7	134.7
110°	151.2	151.5	151.9	152.2	152.6	152.7	152.7	152.7	152.7	152.7	152.7



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	168.9	169.1	169.4	169.6	169.9	170.1	170.4	170.7	170.9	171.2	171.3
115°	196.4	196.7	197.1	197.3	197.7	197.9	198.0	198.1	198.3	198.4	198.5
117.5°	222.6	222.9	223.3	223.6	223.9	224.2	224.5	224.7	225.0	225.2	225.8
120°	241.1	241.4	241.8	242.0	242.4	242.5	242.5	242.5	242.5	242.5	243.4
122.5°	259.2	259.4	259.6	259.8	260.1	260.4	260.6	260.9	261.1	261.4	262.0
125°	286.7	286.8	287.0	287.1	287.1	287.4	287.7	288.0	288.3	288.7	289.0
127.5°	311.9	312.2	312.5	312.9	313.2	313.7	314.0	314.4	314.8	315.2	315.6
130°	329.9	330.4	330.8	331.2	331.7	332.0	332.3	332.4	332.7	332.9	333.1
132.5°	347.2	347.6	347.9	348.3	348.6	349.0	349.5	350.0	350.5	350.9	350.9
135°	374.1	374.4	374.8	375.1	375.4	375.7	375.7	375.9	376.0	376.1	375.9
137.5°	398.5	398.9	399.3	399.8	400.2	400.5	400.5	400.6	400.7	400.8	400.5
140°	415.3	415.8	416.2	416.6	417.2	417.3	417.3	417.3	417.3	417.3	416.8
142.5°	430.7	431.1	431.5	432.0	432.4	432.6	432.5	432.4	432.3	432.2	431.9
145°	453.7	454.1	454.5	455.0	455.4	455.6	455.5	455.4	455.2	455.1	454.5
147.5°	474.2	474.6	475.0	475.4	475.9	476.0	475.7	475.4	475.2	475.0	474.5
150°	487.6	487.8	488.2	488.5	488.9	488.9	488.5	488.2	487.8	487.6	487.1
152.5°	500.2	500.5	500.9	501.4	501.8	501.8	501.4	500.9	500.5	500.2	499.6
155°	517.0	517.3	517.6	518.0	518.3	518.2	517.6	517.1	516.6	516.0	515.7
157.5°	531.5	532.1	532.6	533.1	533.6	533.6	532.8	532.0	531.3	530.5	530.4
160°	540.5	541.0	541.5	541.9	542.3	542.2	541.6	540.9	540.3	539.6	539.5
162.5°	548.5	549.0	549.5	550.0	550.5	550.4	549.7	548.9	548.2	547.4	547.3
165°	558.7	559.3	559.8	560.3	560.9	560.8	560.1	559.3	558.5	557.8	557.8
167.5°	567.1	567.7	568.3	568.9	569.5	569.4	568.6	567.8	567.1	566.3	566.3
170°	571.5	572.1	572.8	573.4	574.1	574.0	573.3	572.6	571.8	571.0	571.1
172.5°	575.1	575.7	576.4	577.0	577.6	577.6	576.9	576.1	575.3	574.5	574.6
175°	578.9	579.5	580.1	580.8	581.5	581.4	580.7	579.9	579.1	578.3	578.6
177.5°	580.7	581.2	581.7	582.2	582.7	582.7	582.2	581.7	581.2	580.7	580.8
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1173.5	1170.7	1169.0	1162.6	1157.0	1151.4	1149.6	1150.3	1142.6	1135.2	1132.0
5°	1219.3	1210.5	1202.1	1190.2	1176.2	1160.8	1152.9	1146.7	1131.4	1114.7	1105.0
7.5°	1260.2	1247.7	1231.6	1209.2	1188.8	1164.6	1149.2	1135.6	1113.0	1089.5	1075.0
10°	1285.2	1268.0	1247.3	1220.1	1195.1	1165.6	1145.0	1124.3	1097.9	1069.8	1052.2
12.5°	1306.7	1283.5	1263.2	1228.2	1198.6	1161.7	1137.2	1108.1	1080.4	1047.0	1029.8
15°	1357.7	1315.1	1276.3	1236.8	1200.3	1148.9	1121.7	1082.5	1046.0	1004.8	985.0
17.5°	1397.1	1349.3	1288.3	1238.0	1195.5	1138.6	1098.5	1051.7	1008.6	961.3	934.4
20°	1419.7	1364.7	1299.2	1239.5	1188.4	1123.4	1080.0	1032.0	981.5	928.2	899.2
22.5°	1433.0	1375.3	1310.5	1234.2	1174.4	1111.1	1056.4	1003.8	952.6	895.3	864.8
25°	1437.3	1384.5	1316.0	1229.8	1156.8	1085.2	1019.3	968.3	906.3	852.6	808.3
27.5°	1416.3	1378.5	1312.6	1221.5	1136.5	1052.7	979.3	921.5	856.1	797.9	753.3
30°	1390.7	1368.6	1304.5	1213.1	1120.3	1030.3	949.3	883.9	818.8	759.9	714.2
32.5°	1350.9	1346.2	1289.8	1201.1	1103.1	1001.8	918.1	851.9	779.8	721.9	678.4
35°	1272.9	1294.0	1258.4	1174.4	1070.7	961.2	870.7	795.1	720.4	665.0	624.1
37.5°	1168.3	1220.6	1211.3	1135.3	1026.9	917.1	817.2	738.1	666.9	611.1	570.9
40°	1096.1	1163.0	1172.7	1105.4	996.0	883.0	777.1	698.4	629.0	578.0	537.5
42.5°	1018.8	1096.9	1123.4	1069.5	962.2	847.1	741.2	659.7	591.0	541.4	505.6
45°	889.2	992.5	1040.3	1009.6	905.9	788.1	679.1	596.4	534.0	487.4	459.8
47.5°	767.9	880.8	945.2	934.4	843.2	726.5	618.8	539.5	478.7	441.5	416.7
50°	682.2	798.1	876.0	879.5	798.1	682.6	574.5	499.7	443.9	409.2	389.0
52.5°	607.6	718.3	803.2	821.8	747.9	636.9	534.8	460.4	411.2	379.3	361.2
55°	510.3	603.9	697.9	732.3	672.9	567.4	472.9	407.4	361.3	339.3	323.5
57.5°	424.2	502.3	589.2	627.1	590.5	500.2	411.6	354.7	317.3	298.0	285.9
60°	378.8	440.4	517.7	563.0	531.4	451.0	373.6	319.5	288.8	271.6	260.2
62.5°	336.7	391.2	456.6	498.0	480.8	404.9	335.6	287.9	261.3	245.2	237.0
65°	277.8	320.9	371.4	409.7	398.2	340.6	284.0	243.1	222.0	209.2	202.6
67.5°	228.8	259.8	294.9	328.4	319.2	278.4	232.9	201.0	185.3	174.4	170.4
70°	197.8	221.5	252.7	279.6	272.1	238.7	202.6	175.4	161.8	152.5	148.5
72.5°	168.2	187.8	211.5	233.5	228.4	200.7	170.7	150.1	139.6	131.0	127.8
75°	127.0	142.0	156.4	171.0	169.6	148.1	130.5	114.7	106.3	99.8	98.4
77.5°	93.8	102.1	112.0	120.6	118.2	105.9	92.1	83.1	76.9	72.5	71.8
80°	71.6	76.5	83.5	89.6	86.6	81.3	70.3	63.7	59.3	54.9	53.2
82.5°	51.9	56.8	61.0	64.3	62.0	57.1	50.3	45.8	43.1	40.2	39.4
85°	27.2	29.9	31.7	32.5	31.7	28.6	25.5	23.8	21.5	20.2	19.8
87.5°	13.0	12.6	12.1	12.4	11.1	10.8	9.1	7.8	7.7	7.7	7.2
90°	12.4	10.0	7.6	5.8	4.4	3.1	1.8	0.5	1.8	3.1	4.4
92.5°	14.5	13.9	13.3	12.6	11.6	10.7	9.7	8.8	9.7	10.7	11.6
95°	31.0	30.7	30.6	29.9	28.8	27.7	26.6	25.6	26.6	27.7	28.8
97.5°	52.0	51.6	51.1	50.5	49.5	48.6	47.6	46.7	47.6	48.6	49.5
100°	67.1	66.8	66.5	65.9	65.0	64.1	63.2	62.3	63.2	64.1	65.0
102.5°	83.0	82.7	82.2	81.6	80.9	80.2	79.6	78.9	79.6	80.2	80.9
105°	107.5	107.4	107.1	106.9	106.5	106.2	105.9	105.6	105.9	106.2	106.5
107.5°	134.7	134.7	134.7	134.4	133.9	133.5	132.9	132.5	132.9	133.5	133.9
110°	152.7	152.7	152.7	152.4	151.7	151.0	150.4	149.7	150.4	151.0	151.7





TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	171.3	171.4	171.5	171.3	170.6	169.9	169.3	168.6	169.3	169.9	170.6
115°	198.8	199.0	199.2	199.0	198.4	197.7	197.1	196.4	197.1	197.7	198.4
117.5°	226.4	227.1	227.7	227.6	226.7	225.8	225.0	224.1	225.0	225.8	226.7
120°	244.3	245.1	246.1	246.1	245.1	244.3	243.4	242.5	243.4	244.3	245.1
122.5°	262.6	263.2	263.8	263.6	262.6	261.6	260.5	259.4	260.5	261.6	262.6
125°	289.4	289.6	290.0	289.6	288.7	287.7	286.7	285.8	286.7	287.7	288.7
127.5°	316.0	316.4	316.8	316.3	315.1	313.8	312.6	311.3	312.6	313.8	315.1
130°	333.3	333.6	333.7	333.1	331.7	330.3	328.9	327.5	328.9	330.3	331.7
132.5°	350.9	350.9	350.8	350.2	349.0	347.8	346.7	345.5	346.7	347.8	349.0
135°	375.7	375.4	375.2	374.5	373.3	372.1	370.9	369.7	370.9	372.1	373.3
137.5°	400.3	400.0	399.7	399.1	398.1	397.1	396.1	395.1	396.1	397.1	398.1
140°	416.2	415.7	415.2	414.4	413.4	412.4	411.5	410.4	411.5	412.4	413.4
142.5°	431.5	431.2	430.8	430.1	429.1	428.2	427.1	426.2	427.1	428.2	429.1
145°	453.8	453.1	452.5	451.9	451.1	450.3	449.5	448.8	449.5	450.3	451.1
147.5°	474.1	473.6	473.2	472.5	471.7	470.7	469.8	468.9	469.8	470.7	471.7
150°	486.6	486.2	485.8	485.3	484.6	484.0	483.3	482.7	483.3	484.0	484.6
152.5°	499.0	498.5	498.0	497.4	496.8	496.1	495.5	494.8	495.5	496.1	496.8
155°	515.4	515.1	514.7	514.4	514.0	513.8	513.4	513.1	513.4	513.8	514.0
157.5°	530.2	529.9	529.8	529.6	529.3	529.1	528.9	528.7	528.9	529.1	529.3
160°	539.3	539.2	539.2	539.0	538.7	538.6	538.3	538.1	538.3	538.6	538.7
162.5°	547.3	547.1	547.0	546.9	546.9	546.8	546.8	546.7	546.8	546.8	546.9
165°	557.8	557.8	557.8	557.8	557.9	558.0	558.1	558.3	558.1	558.0	557.9
167.5°	566.4	566.4	566.4	566.5	566.9	567.2	567.6	567.8	567.6	567.2	566.9
170°	571.2	571.4	571.4	571.7	572.0	572.3	572.7	573.0	572.7	572.3	572.0
172.5°	574.8	574.9	575.0	575.2	575.5	575.8	576.2	576.5	576.2	575.8	575.5
175°	578.9	579.0	579.3	579.5	579.9	580.1	580.5	580.8	580.5	580.1	579.9
177.5°	581.0	581.2	581.3	581.5	581.8	582.0	582.3	582.6	582.3	582.0	581.8
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1128.5	1126.4	1119.0	1115.2	1108.8	1102.9	1099.0	1100.8	1102.2	1101.5	1100.4
5°	1096.1	1087.8	1075.0	1064.1	1056.2	1041.6	1035.5	1032.4	1029.8	1026.7	1023.6
7.5°	1057.7	1044.5	1026.2	1010.6	995.7	977.8	967.5	961.3	955.0	948.0	941.9
10°	1030.3	1011.8	992.5	970.4	952.9	936.6	922.1	912.5	903.7	895.4	889.2
12.5°	1001.4	980.2	956.2	926.2	906.8	883.6	881.3	864.3	850.6	845.4	838.2
15°	955.5	925.7	895.4	859.7	844.3	823.2	810.0	796.9	785.0	776.6	774.5
17.5°	903.4	864.7	834.6	809.0	783.8	762.2	750.0	739.4	729.7	718.5	717.0
20°	863.7	830.3	797.3	774.9	749.0	726.9	712.0	701.5	693.1	686.6	680.8
22.5°	826.0	789.5	759.3	734.8	709.2	691.5	679.7	669.5	662.5	655.2	649.9
25°	765.7	737.1	704.1	676.4	655.3	643.9	634.2	625.4	621.0	616.2	610.1
27.5°	712.8	681.1	650.2	628.8	610.3	600.1	593.2	587.3	583.2	580.3	576.9
30°	675.5	643.4	619.3	598.2	582.8	572.7	568.3	564.8	560.0	558.2	556.5
32.5°	639.7	610.8	590.1	571.8	557.2	550.5	546.5	543.4	539.6	537.8	534.3
35°	588.9	564.8	544.6	534.4	522.6	516.9	513.8	509.4	505.9	504.1	503.7
37.5°	541.2	520.2	507.0	494.0	489.0	485.4	481.2	478.2	477.2	476.9	476.5
40°	510.3	493.2	481.3	470.7	468.6	463.2	459.8	457.1	457.1	457.5	457.1
42.5°	482.2	466.7	456.3	447.2	444.6	441.4	437.9	437.7	438.5	440.0	438.5
45°	439.5	428.5	421.0	416.6	411.8	408.7	408.3	409.7	410.1	410.5	411.8
47.5°	400.3	393.0	386.2	381.4	379.3	378.8	378.2	380.6	382.6	383.4	385.5
50°	377.1	368.8	363.1	360.0	358.2	357.3	358.2	360.8	362.6	364.8	366.1
52.5°	351.1	345.2	341.2	338.9	338.2	338.7	338.9	341.9	344.7	345.4	346.1
55°	315.1	310.7	309.9	305.9	307.6	307.2	309.4	311.2	313.8	316.4	316.9
57.5°	279.3	275.8	273.4	273.7	274.2	276.2	278.0	281.1	284.0	286.7	287.0
60°	255.4	253.6	252.3	252.3	253.1	255.8	258.0	261.1	262.9	264.6	265.9
62.5°	233.6	231.8	230.5	231.2	233.5	235.1	237.6	239.3	241.0	242.8	243.4
65°	199.1	198.2	199.6	200.4	200.9	203.0	206.1	207.4	209.2	210.1	213.2
67.5°	167.4	167.6	167.4	168.6	171.2	171.7	174.6	177.6	178.0	179.7	181.7
70°	145.9	146.8	147.7	148.5	150.8	151.6	153.9	155.2	156.9	158.3	159.5
72.5°	126.2	126.4	127.3	127.1	129.0	130.9	132.8	134.1	135.8	137.5	138.8
75°	97.1	97.1	98.0	98.4	100.7	102.9	102.4	103.3	105.0	106.8	107.7
77.5°	70.9	70.0	70.9	71.4	72.1	74.0	74.3	75.5	77.5	76.9	77.9
80°	54.1	52.8	54.1	54.5	54.5	56.7	56.7	57.6	58.9	57.6	58.9
82.5°	38.6	38.0	38.9	39.0	39.7	39.8	40.6	40.7	42.0	41.4	42.0
85°	19.4	18.9	19.4	18.9	19.4	19.8	19.8	19.4	19.4	20.2	18.9
87.5°	7.1	7.1	7.2	7.7	7.9	8.0	7.6	7.6	7.5	6.8	6.8
90°	5.8	7.6	10.0	12.4	14.8	17.2	17.0	16.8	16.5	16.3	16.3
92.5°	12.6	13.3	13.9	14.5	15.1	15.6	15.7	15.7	15.8	15.8	15.8
95°	29.9	30.6	30.7	31.0	31.2	31.4	31.4	31.4	31.4	31.4	31.3
97.5°	50.5	51.1	51.6	52.0	52.4	52.9	52.9	52.9	52.9	52.9	52.8
100°	65.9	66.5	66.8	67.1	67.4	67.8	67.8	67.8	67.8	67.8	67.7
102.5°	81.6	82.2	82.7	83.0	83.4	83.9	83.9	84.0	84.1	84.2	84.2
105°	106.9	107.1	107.4	107.5	107.8	108.1	108.2	108.5	108.7	108.9	109.0
107.5°	134.4	134.7	134.7	134.7	134.7	134.7	134.7	134.8	134.9	135.0	134.7
110°	152.4	152.7	152.7	152.7	152.7	152.7	152.7	152.7	152.7	152.7	152.6



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	171.3	171.5	171.4	171.3	171.3	171.2	170.9	170.7	170.4	170.1	169.9
115°	199.0	199.2	199.0	198.8	198.5	198.4	198.3	198.1	198.0	197.9	197.7
117.5°	227.6	227.7	227.1	226.4	225.8	225.2	225.0	224.7	224.5	224.2	223.9
120°	246.1	246.1	245.1	244.3	243.4	242.5	242.5	242.5	242.5	242.5	242.4
122.5°	263.6	263.8	263.2	262.6	262.0	261.4	261.1	260.9	260.6	260.4	260.1
125°	289.6	290.0	289.6	289.4	289.0	288.7	288.3	288.0	287.7	287.4	287.1
127.5°	316.3	316.8	316.4	316.0	315.6	315.2	314.8	314.4	314.0	313.7	313.2
130°	333.1	333.7	333.6	333.3	333.1	332.9	332.7	332.4	332.3	332.0	331.7
132.5°	350.2	350.8	350.9	350.9	350.9	350.9	350.5	350.0	349.5	349.0	348.6
135°	374.5	375.2	375.4	375.7	375.9	376.1	376.0	375.9	375.7	375.7	375.4
137.5°	399.1	399.7	400.0	400.3	400.5	400.8	400.7	400.6	400.5	400.5	400.2
140°	414.4	415.2	415.7	416.2	416.8	417.3	417.3	417.3	417.3	417.3	417.2
142.5°	430.1	430.8	431.2	431.5	431.9	432.2	432.3	432.4	432.5	432.6	432.4
145°	451.9	452.5	453.1	453.8	454.5	455.1	455.2	455.4	455.5	455.6	455.4
147.5°	472.5	473.2	473.6	474.1	474.5	475.0	475.2	475.4	475.7	476.0	475.9
150°	485.3	485.8	486.2	486.6	487.1	487.6	487.8	488.2	488.5	488.9	488.9
152.5°	497.4	498.0	498.5	499.0	499.6	500.2	500.5	500.9	501.4	501.8	501.8
155°	514.4	514.7	515.1	515.4	515.7	516.0	516.6	517.1	517.6	518.2	518.3
157.5°	529.6	529.8	529.9	530.2	530.4	530.5	531.3	532.0	532.8	533.6	533.6
160°	539.0	539.2	539.2	539.3	539.5	539.6	540.3	540.9	541.6	542.2	542.3
162.5°	546.9	547.0	547.1	547.3	547.3	547.4	548.2	548.9	549.7	550.4	550.5
165°	557.8	557.8	557.8	557.8	557.8	557.8	558.5	559.3	560.1	560.8	560.9
167.5°	566.5	566.4	566.4	566.4	566.3	566.3	567.1	567.8	568.6	569.4	569.5
170°	571.7	571.4	571.4	571.2	571.1	571.0	571.8	572.6	573.3	574.0	574.1
172.5°	575.2	575.0	574.9	574.8	574.6	574.5	575.3	576.1	576.9	577.6	577.6
175°	579.5	579.3	579.0	578.9	578.6	578.3	579.1	579.9	580.7	581.4	581.5
177.5°	581.5	581.3	581.2	581.0	580.8	580.7	581.2	581.7	582.2	582.7	582.7
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1096.9	1096.1	1096.1	1093.0	1096.1	1096.1	1096.9	1100.4	1101.5	1102.2	1100.8
5°	1017.5	1016.2	1014.0	1016.2	1014.0	1016.2	1017.5	1023.6	1026.7	1029.8	1032.4
7.5°	939.0	933.8	933.0	927.7	933.0	933.8	939.0	941.9	948.0	955.0	961.3
10°	881.7	878.1	877.7	869.4	877.7	878.1	881.7	889.2	895.4	903.7	912.5
12.5°	838.1	829.7	831.3	826.5	831.3	829.7	838.1	838.2	845.4	850.6	864.3
15°	762.6	762.6	760.8	753.4	760.8	762.6	762.6	774.5	776.6	785.0	796.9
17.5°	708.3	707.5	703.3	705.3	703.3	707.5	708.3	717.0	718.5	729.7	739.4
20°	676.0	673.4	668.0	668.0	668.0	673.4	676.0	680.8	686.6	693.1	701.5
22.5°	645.4	645.2	639.6	641.4	639.6	645.2	645.4	649.9	655.2	662.5	669.5
25°	609.6	606.1	603.5	604.8	603.5	606.1	609.6	610.1	616.2	621.0	625.4
27.5°	575.7	573.8	573.6	570.0	573.6	573.8	575.7	576.9	580.3	583.2	587.3
30°	556.0	551.6	552.5	550.3	552.5	551.6	556.0	556.5	558.2	560.0	564.8
32.5°	533.5	531.9	531.1	529.2	531.1	531.9	533.5	534.3	537.8	539.6	543.4
35°	502.8	503.3	501.1	502.0	501.1	503.3	502.8	503.7	504.1	505.9	509.4
37.5°	476.0	477.4	476.4	476.6	476.4	477.4	476.0	476.5	476.9	477.2	478.2
40°	458.4	458.4	458.4	459.8	458.4	458.4	458.4	457.1	457.5	457.1	457.1
42.5°	441.5	440.8	440.1	440.1	440.1	440.8	441.5	438.5	440.0	438.5	437.7
45°	412.7	414.1	414.5	412.2	414.5	414.1	412.7	411.8	410.5	410.1	409.7
47.5°	386.6	386.8	386.6	388.6	386.6	386.8	386.6	385.5	383.4	382.6	380.6
50°	368.3	367.5	368.3	367.5	368.3	367.5	368.3	366.1	364.8	362.6	360.8
52.5°	349.0	349.1	348.6	348.4	348.6	349.1	349.0	346.1	345.4	344.7	341.9
55°	318.7	319.5	319.1	319.1	319.1	319.5	318.7	316.9	316.4	313.8	311.2
57.5°	287.3	288.1	288.7	286.7	288.7	288.1	287.3	287.0	286.7	284.0	281.1
60°	265.4	267.7	267.3	266.4	267.3	267.7	265.4	265.9	264.6	262.9	261.1
62.5°	245.5	246.2	246.2	246.0	246.2	246.2	245.5	243.4	242.8	241.0	239.3
65°	214.5	215.3	214.0	215.3	214.0	215.3	214.5	213.2	210.1	209.2	207.4
67.5°	181.2	181.4	182.4	183.0	182.4	181.4	181.2	181.7	179.7	178.0	177.6
70°	160.4	160.0	161.3	162.6	161.3	160.0	160.4	159.5	158.3	156.9	155.2
72.5°	138.6	139.6	139.1	140.1	139.1	139.6	138.6	138.8	137.5	135.8	134.1
75°	106.8	108.1	107.7	109.0	107.7	108.1	106.8	107.7	106.8	105.0	103.3
77.5°	77.1	77.3	77.1	77.9	77.1	77.3	77.1	77.9	76.9	77.5	75.5
80°	58.9	58.0	57.2	58.9	57.2	58.0	58.9	58.9	57.6	58.9	57.6
82.5°	41.0	41.5	40.6	40.6	40.6	41.5	41.0	42.0	41.4	42.0	40.7
85°	18.9	18.4	17.6	17.6	17.6	18.4	18.9	18.9	20.2	19.4	19.4
87.5°	6.8	6.5	6.5	6.1	6.5	6.5	6.8	6.8	6.8	7.5	7.6
90°	16.4	16.4	16.6	16.7	16.6	16.4	16.4	16.3	16.3	16.5	16.8
92.5°	15.8	15.8	15.9	15.9	15.9	15.8	15.8	15.8	15.8	15.8	15.7
95°	31.1	30.9	30.7	30.5	30.7	30.9	31.1	31.3	31.4	31.4	31.4
97.5°	52.8	52.8	52.8	52.7	52.8	52.8	52.8	52.8	52.9	52.9	52.9
100°	67.6	67.5	67.4	67.2	67.4	67.5	67.6	67.7	67.8	67.8	67.8
102.5°	84.1	83.9	83.9	83.8	83.9	83.9	84.1	84.2	84.2	84.1	84.0
105°	109.0	109.0	109.0	109.0	109.0	109.0	109.0	109.0	108.9	108.7	108.5
107.5°	134.2	133.8	133.3	132.8	133.3	133.8	134.2	134.7	135.0	134.9	134.8
110°	152.2	151.9	151.5	151.2	151.5	151.9	152.2	152.6	152.7	152.7	152.7



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	169.6	169.4	169.1	168.9	169.1	169.4	169.6	169.9	170.1	170.4	170.7
115°	197.3	197.1	196.7	196.4	196.7	197.1	197.3	197.7	197.9	198.0	198.1
117.5°	223.6	223.3	222.9	222.6	222.9	223.3	223.6	223.9	224.2	224.5	224.7
120°	242.0	241.8	241.4	241.1	241.4	241.8	242.0	242.4	242.5	242.5	242.5
122.5°	259.8	259.6	259.4	259.2	259.4	259.6	259.8	260.1	260.4	260.6	260.9
125°	287.1	287.0	286.8	286.7	286.8	287.0	287.1	287.1	287.4	287.7	288.0
127.5°	312.9	312.5	312.2	311.9	312.2	312.5	312.9	313.2	313.7	314.0	314.4
130°	331.2	330.8	330.4	329.9	330.4	330.8	331.2	331.7	332.0	332.3	332.4
132.5°	348.3	347.9	347.6	347.2	347.6	347.9	348.3	348.6	349.0	349.5	350.0
135°	375.1	374.8	374.4	374.1	374.4	374.8	375.1	375.4	375.7	375.7	375.9
137.5°	399.8	399.3	398.9	398.5	398.9	399.3	399.8	400.2	400.5	400.5	400.6
140°	416.6	416.2	415.8	415.3	415.8	416.2	416.6	417.2	417.3	417.3	417.3
142.5°	432.0	431.5	431.1	430.7	431.1	431.5	432.0	432.4	432.6	432.5	432.4
145°	455.0	454.5	454.1	453.7	454.1	454.5	455.0	455.4	455.6	455.5	455.4
147.5°	475.4	475.0	474.6	474.2	474.6	475.0	475.4	475.9	476.0	475.7	475.4
150°	488.5	488.2	487.8	487.6	487.8	488.2	488.5	488.9	488.9	488.5	488.2
152.5°	501.4	500.9	500.5	500.2	500.5	500.9	501.4	501.8	501.8	501.4	500.9
155°	518.0	517.6	517.3	517.0	517.3	517.6	518.0	518.3	518.2	517.6	517.1
157.5°	533.1	532.6	532.1	531.5	532.1	532.6	533.1	533.6	533.6	532.8	532.0
160°	541.9	541.5	541.0	540.5	541.0	541.5	541.9	542.3	542.2	541.6	540.9
162.5°	550.0	549.5	549.0	548.5	549.0	549.5	550.0	550.5	550.4	549.7	548.9
165°	560.3	559.8	559.3	558.7	559.3	559.8	560.3	560.9	560.8	560.1	559.3
167.5°	568.9	568.3	567.7	567.1	567.7	568.3	568.9	569.5	569.4	568.6	567.8
170°	573.4	572.8	572.1	571.5	572.1	572.8	573.4	574.1	574.0	573.3	572.6
172.5°	577.0	576.4	575.7	575.1	575.7	576.4	577.0	577.6	577.6	576.9	576.1
175°	580.8	580.1	579.5	578.9	579.5	580.1	580.8	581.5	581.4	580.7	579.9
177.5°	582.2	581.7	581.2	580.7	581.2	581.7	582.2	582.7	582.7	582.2	581.7
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1099.0	1102.9	1108.8	1115.2	1119.0	1126.4	1128.5	1132.0	1135.2	1142.6	1150.3
5°	1035.5	1041.6	1056.2	1064.1	1075.0	1087.8	1096.1	1105.0	1114.7	1131.4	1146.7
7.5°	967.5	977.8	995.7	1010.6	1026.2	1044.5	1057.7	1075.0	1089.5	1113.0	1135.6
10°	922.1	936.6	952.9	970.4	992.5	1011.8	1030.3	1052.2	1069.8	1097.9	1124.3
12.5°	881.3	883.6	906.8	926.2	956.2	980.2	1001.4	1029.8	1047.0	1080.4	1108.1
15°	810.0	823.2	844.3	859.7	895.4	925.7	955.5	985.0	1004.8	1046.0	1082.5
17.5°	750.0	762.2	783.8	809.0	834.6	864.7	903.4	934.4	961.3	1008.6	1051.7
20°	712.0	726.9	749.0	774.9	797.3	830.3	863.7	899.2	928.2	981.5	1032.0
22.5°	679.7	691.5	709.2	734.8	759.3	789.5	826.0	864.8	895.3	952.6	1003.8
25°	634.2	643.9	655.3	676.4	704.1	737.1	765.7	808.3	852.6	906.3	968.3
27.5°	593.2	600.1	610.3	628.8	650.2	681.1	712.8	753.3	797.9	856.1	921.5
30°	568.3	572.7	582.8	598.2	619.3	643.4	675.5	714.2	759.9	818.8	883.9
32.5°	546.5	550.5	557.2	571.8	590.1	610.8	639.7	678.4	721.9	779.8	851.9
35°	513.8	516.9	522.6	534.4	544.6	564.8	588.9	624.1	665.0	720.4	795.1
37.5°	481.2	485.4	489.0	494.0	507.0	520.2	541.2	570.9	611.1	666.9	738.1
40°	459.8	463.2	468.6	470.7	481.3	493.2	510.3	537.5	578.0	629.0	698.4
42.5°	437.9	441.4	444.6	447.2	456.3	466.7	482.2	505.6	541.4	591.0	659.7
45°	408.3	408.7	411.8	416.6	421.0	428.5	439.5	459.8	487.4	534.0	596.4
47.5°	378.2	378.8	379.3	381.4	386.2	393.0	400.3	416.7	441.5	478.7	539.5
50°	358.2	357.3	358.2	360.0	363.1	368.8	377.1	389.0	409.2	443.9	499.7
52.5°	338.9	338.7	338.2	338.9	341.2	345.2	351.1	361.2	379.3	411.2	460.4
55°	309.4	307.2	307.6	305.9	309.9	310.7	315.1	323.5	339.3	361.3	407.4
57.5°	278.0	276.2	274.2	273.7	273.4	275.8	279.3	285.9	298.0	317.3	354.7
60°	258.0	255.8	253.1	252.3	252.3	253.6	255.4	260.2	271.6	288.8	319.5
62.5°	237.6	235.1	233.5	231.2	230.5	231.8	233.6	237.0	245.2	261.3	287.9
65°	206.1	203.0	200.9	200.4	199.6	198.2	199.1	202.6	209.2	222.0	243.1
67.5°	174.6	171.7	171.2	168.6	167.4	167.6	167.4	170.4	174.4	185.3	201.0
70°	153.9	151.6	150.8	148.5	147.7	146.8	145.9	148.5	152.5	161.8	175.4
72.5°	132.8	130.9	129.0	127.1	127.3	126.4	126.2	127.8	131.0	139.6	150.1
75°	102.4	102.9	100.7	98.4	98.0	97.1	97.1	98.4	99.8	106.3	114.7
77.5°	74.3	74.0	72.1	71.4	70.9	70.0	70.9	71.8	72.5	76.9	83.1
80°	56.7	56.7	54.5	54.5	54.1	52.8	54.1	53.2	54.9	59.3	63.7
82.5°	40.6	39.8	39.7	39.0	38.9	38.0	38.6	39.4	40.2	43.1	45.8
85°	19.8	19.8	19.4	18.9	19.4	18.9	19.4	19.8	20.2	21.5	23.8
87.5°	7.6	8.0	7.9	7.7	7.2	7.1	7.1	7.2	7.7	7.7	7.8
90°	17.0	17.2	14.8	12.4	10.0	7.6	5.8	4.4	3.1	1.8	0.5
92.5°	15.7	15.6	15.1	14.5	13.9	13.3	12.6	11.6	10.7	9.7	8.8
95°	31.4	31.4	31.2	31.0	30.7	30.6	29.9	28.8	27.7	26.6	25.6
97.5°	52.9	52.9	52.4	52.0	51.6	51.1	50.5	49.5	48.6	47.6	46.7
100°	67.8	67.8	67.4	67.1	66.8	66.5	65.9	65.0	64.1	63.2	62.3
102.5°	83.9	83.9	83.4	83.0	82.7	82.2	81.6	80.9	80.2	79.6	78.9
105°	108.2	108.1	107.8	107.5	107.4	107.1	106.9	106.5	106.2	105.9	105.6
107.5°	134.7	134.7	134.7	134.7	134.7	134.7	134.4	133.9	133.5	132.9	132.5
110°	152.7	152.7	152.7	152.7	152.7	152.7	152.4	151.7	151.0	150.4	149.7



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	170.9	171.2	171.3	171.3	171.4	171.5	171.3	170.6	169.9	169.3	168.6
115°	198.3	198.4	198.5	198.8	199.0	199.2	199.0	198.4	197.7	197.1	196.4
117.5°	225.0	225.2	225.8	226.4	227.1	227.7	227.6	226.7	225.8	225.0	224.1
120°	242.5	242.5	243.4	244.3	245.1	246.1	246.1	245.1	244.3	243.4	242.5
122.5°	261.1	261.4	262.0	262.6	263.2	263.8	263.6	262.6	261.6	260.5	259.4
125°	288.3	288.7	289.0	289.4	289.6	290.0	289.6	288.7	287.7	286.7	285.8
127.5°	314.8	315.2	315.6	316.0	316.4	316.8	316.3	315.1	313.8	312.6	311.3
130°	332.7	332.9	333.1	333.3	333.6	333.7	333.1	331.7	330.3	328.9	327.5
132.5°	350.5	350.9	350.9	350.9	350.9	350.8	350.2	349.0	347.8	346.7	345.5
135°	376.0	376.1	375.9	375.7	375.4	375.2	374.5	373.3	372.1	370.9	369.7
137.5°	400.7	400.8	400.5	400.3	400.0	399.7	399.1	398.1	397.1	396.1	395.1
140°	417.3	417.3	416.8	416.2	415.7	415.2	414.4	413.4	412.4	411.5	410.4
142.5°	432.3	432.2	431.9	431.5	431.2	430.8	430.1	429.1	428.2	427.1	426.2
145°	455.2	455.1	454.5	453.8	453.1	452.5	451.9	451.1	450.3	449.5	448.8
147.5°	475.2	475.0	474.5	474.1	473.6	473.2	472.5	471.7	470.7	469.8	468.9
150°	487.8	487.6	487.1	486.6	486.2	485.8	485.3	484.6	484.0	483.3	482.7
152.5°	500.5	500.2	499.6	499.0	498.5	498.0	497.4	496.8	496.1	495.5	494.8
155°	516.6	516.0	515.7	515.4	515.1	514.7	514.4	514.0	513.8	513.4	513.1
157.5°	531.3	530.5	530.4	530.2	529.9	529.8	529.6	529.3	529.1	528.9	528.7
160°	540.3	539.6	539.5	539.3	539.2	539.2	539.0	538.7	538.6	538.3	538.1
162.5°	548.2	547.4	547.3	547.3	547.1	547.0	546.9	546.9	546.8	546.8	546.7
165°	558.5	557.8	557.8	557.8	557.8	557.8	557.8	557.9	558.0	558.1	558.3
167.5°	567.1	566.3	566.3	566.4	566.4	566.4	566.5	566.9	567.2	567.6	567.8
170°	571.8	571.0	571.1	571.2	571.4	571.4	571.7	572.0	572.3	572.7	573.0
172.5°	575.3	574.5	574.6	574.8	574.9	575.0	575.2	575.5	575.8	576.2	576.5
175°	579.1	578.3	578.6	578.9	579.0	579.3	579.5	579.9	580.1	580.5	580.8
177.5°	581.2	580.7	580.8	581.0	581.2	581.3	581.5	581.8	582.0	582.3	582.6
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1149.6	1151.4	1157.0	1162.6	1169.0	1170.7	1173.5	1171.0	1170.4	1177.1	1182.0
5°	1152.9	1160.8	1176.2	1190.2	1202.1	1210.5	1219.3	1222.8	1229.3	1238.5	1250.0
7.5°	1149.2	1164.6	1188.8	1209.2	1231.6	1247.7	1260.2	1270.9	1283.9	1301.4	1320.5
10°	1145.0	1165.6	1195.1	1220.1	1247.3	1268.0	1285.2	1301.8	1321.2	1345.4	1370.5
12.5°	1137.2	1161.7	1198.6	1228.2	1263.2	1283.5	1306.7	1342.6	1363.4	1397.1	1432.4
15°	1121.7	1148.9	1200.3	1236.8	1276.3	1315.1	1357.7	1392.0	1426.2	1446.0	1495.7
17.5°	1098.5	1138.6	1195.5	1238.0	1288.3	1349.3	1397.1	1436.0	1475.6	1507.7	1532.6
20°	1080.0	1123.4	1188.4	1239.5	1299.2	1364.7	1419.7	1459.2	1493.5	1520.4	1535.7
22.5°	1056.4	1111.1	1174.4	1234.2	1310.5	1375.3	1433.0	1464.1	1492.8	1505.9	1511.8
25°	1019.3	1085.2	1156.8	1229.8	1316.0	1384.5	1437.3	1456.1	1464.5	1451.7	1430.6
27.5°	979.3	1052.7	1136.5	1221.5	1312.6	1378.5	1416.3	1413.3	1399.2	1358.0	1325.0
30°	949.3	1030.3	1120.3	1213.1	1304.5	1368.6	1390.7	1368.6	1336.6	1290.5	1243.5
32.5°	918.1	1001.8	1103.1	1201.1	1289.8	1346.2	1350.9	1313.1	1263.4	1211.0	1152.4
35°	870.7	961.2	1070.7	1174.4	1258.4	1294.0	1272.9	1206.1	1147.2	1075.6	995.5
37.5°	817.2	917.1	1026.9	1135.3	1211.3	1220.6	1168.3	1097.9	1014.9	930.7	836.5
40°	777.1	883.0	996.0	1105.4	1172.7	1163.0	1096.1	1018.8	919.9	817.1	729.6
42.5°	741.2	847.1	962.2	1069.5	1123.4	1096.9	1018.8	923.9	817.6	720.7	640.7
45°	679.1	788.1	905.9	1009.6	1040.3	992.5	889.2	783.7	679.1	598.2	534.9
47.5°	618.8	726.5	843.2	934.4	945.2	880.8	767.9	659.4	569.5	503.6	458.9
50°	574.5	682.6	798.1	879.5	876.0	798.1	682.2	578.9	503.7	450.5	420.6
52.5°	534.8	636.9	747.9	821.8	803.2	718.3	607.6	515.9	454.1	412.5	385.5
55°	472.9	567.4	672.9	732.3	697.9	603.9	510.3	436.4	390.7	359.6	338.5
57.5°	411.6	500.2	590.5	627.1	589.2	502.3	424.2	370.7	336.3	313.2	299.5
60°	373.6	451.0	531.4	563.0	517.7	440.4	378.8	331.0	303.2	284.4	272.1
62.5°	335.6	404.9	480.8	498.0	456.6	391.2	336.7	296.9	274.1	257.3	245.7
65°	284.0	340.6	398.2	409.7	371.4	320.9	277.8	251.8	231.6	219.3	210.1
67.5°	232.9	278.4	319.2	328.4	294.9	259.8	228.8	206.1	192.4	182.2	174.4
70°	202.6	238.7	272.1	279.6	252.7	221.5	197.8	179.8	167.5	158.7	151.2
72.5°	170.7	200.7	228.4	233.5	211.5	187.8	168.2	154.1	143.2	137.6	130.4
75°	130.5	148.1	169.6	171.0	156.4	142.0	127.0	117.8	112.1	105.0	101.5
77.5°	92.1	105.9	118.2	120.6	112.0	102.1	93.8	86.5	81.6	78.4	75.2
80°	70.3	81.3	86.6	89.6	83.5	76.5	71.6	66.8	63.7	61.6	59.3
82.5°	50.3	57.1	62.0	64.3	61.0	56.8	51.9	49.2	46.8	45.0	44.3
85°	25.5	28.6	31.7	32.5	31.7	29.9	27.2	27.2	25.9	25.5	25.5
87.5°	9.1	10.8	11.1	12.4	12.1	12.6	13.0	13.2	13.3	12.9	12.5
90°	1.8	3.1	4.4	5.8	7.6	10.0	12.4	14.8	17.2	17.0	16.8
92.5°	9.7	10.7	11.6	12.6	13.3	13.9	14.5	15.1	15.6	15.7	15.7
95°	26.6	27.7	28.8	29.9	30.6	30.7	31.0	31.2	31.4	31.4	31.4
97.5°	47.6	48.6	49.5	50.5	51.1	51.6	52.0	52.4	52.9	52.9	52.9
100°	63.2	64.1	65.0	65.9	66.5	66.8	67.1	67.4	67.8	67.8	67.8
102.5°	79.6	80.2	80.9	81.6	82.2	82.7	83.0	83.4	83.9	83.9	84.0
105°	105.9	106.2	106.5	106.9	107.1	107.4	107.5	107.8	108.1	108.2	108.5
107.5°	132.9	133.5	133.9	134.4	134.7	134.7	134.7	134.7	134.7	134.7	134.8
110°	150.4	151.0	151.7	152.4	152.7	152.7	152.7	152.7	152.7	152.7	152.7





TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	169.3	169.9	170.6	171.3	171.5	171.4	171.3	171.3	171.2	170.9	170.7
115°	197.1	197.7	198.4	199.0	199.2	199.0	198.8	198.5	198.4	198.3	198.1
117.5°	225.0	225.8	226.7	227.6	227.7	227.1	226.4	225.8	225.2	225.0	224.7
120°	243.4	244.3	245.1	246.1	246.1	245.1	244.3	243.4	242.5	242.5	242.5
122.5°	260.5	261.6	262.6	263.6	263.8	263.2	262.6	262.0	261.4	261.1	260.9
125°	286.7	287.7	288.7	289.6	290.0	289.6	289.4	289.0	288.7	288.3	288.0
127.5°	312.6	313.8	315.1	316.3	316.8	316.4	316.0	315.6	315.2	314.8	314.4
130°	328.9	330.3	331.7	333.1	333.7	333.6	333.3	333.1	332.9	332.7	332.4
132.5°	346.7	347.8	349.0	350.2	350.8	350.9	350.9	350.9	350.9	350.5	350.0
135°	370.9	372.1	373.3	374.5	375.2	375.4	375.7	375.9	376.1	376.0	375.9
137.5°	396.1	397.1	398.1	399.1	399.7	400.0	400.3	400.5	400.8	400.7	400.6
140°	411.5	412.4	413.4	414.4	415.2	415.7	416.2	416.8	417.3	417.3	417.3
142.5°	427.1	428.2	429.1	430.1	430.8	431.2	431.5	431.9	432.2	432.3	432.4
145°	449.5	450.3	451.1	451.9	452.5	453.1	453.8	454.5	455.1	455.2	455.4
147.5°	469.8	470.7	471.7	472.5	473.2	473.6	474.1	474.5	475.0	475.2	475.4
150°	483.3	484.0	484.6	485.3	485.8	486.2	486.6	487.1	487.6	487.8	488.2
152.5°	495.5	496.1	496.8	497.4	498.0	498.5	499.0	499.6	500.2	500.5	500.9
155°	513.4	513.8	514.0	514.4	514.7	515.1	515.4	515.7	516.0	516.6	517.1
157.5°	528.9	529.1	529.3	529.6	529.8	529.9	530.2	530.4	530.5	531.3	532.0
160°	538.3	538.6	538.7	539.0	539.2	539.2	539.3	539.5	539.6	540.3	540.9
162.5°	546.8	546.8	546.9	546.9	547.0	547.1	547.3	547.3	547.4	548.2	548.9
165°	558.1	558.0	557.9	557.8	557.8	557.8	557.8	557.8	557.8	558.5	559.3
167.5°	567.6	567.2	566.9	566.5	566.4	566.4	566.4	566.3	566.3	567.1	567.8
170°	572.7	572.3	572.0	571.7	571.4	571.4	571.2	571.1	571.0	571.8	572.6
172.5°	576.2	575.8	575.5	575.2	575.0	574.9	574.8	574.6	574.5	575.3	576.1
175°	580.5	580.1	579.9	579.5	579.3	579.0	578.9	578.6	578.3	579.1	579.9
177.5°	582.3	582.0	581.8	581.5	581.3	581.2	581.0	580.8	580.7	581.2	581.7
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8	581.8



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1186.2	1191.1	1191.1	1191.8	1197.5	1196.7	1196.4
5°	1262.3	1269.8	1270.7	1278.6	1283.8	1282.1	1277.3
7.5°	1334.1	1348.1	1358.6	1364.4	1371.4	1375.7	1373.8
10°	1391.1	1411.4	1423.7	1432.0	1442.1	1449.6	1446.9
12.5°	1442.8	1466.9	1483.8	1498.1	1499.4	1509.0	1502.4
15°	1523.4	1548.9	1551.5	1562.1	1570.5	1569.5	1569.9
17.5°	1550.1	1558.2	1559.9	1560.1	1560.2	1557.1	1550.5
20°	1540.5	1537.5	1530.0	1524.3	1514.2	1512.9	1504.1
22.5°	1495.6	1485.7	1467.1	1454.7	1438.9	1434.8	1432.4
25°	1407.0	1385.3	1355.5	1326.9	1319.1	1303.6	1308.0
27.5°	1285.4	1251.8	1219.4	1196.2	1175.2	1152.2	1158.7
30°	1199.9	1162.1	1116.4	1081.2	1058.9	1036.8	1032.9
32.5°	1097.9	1042.6	991.5	960.6	926.3	912.4	897.2
35°	922.1	868.1	817.5	774.0	749.0	729.6	712.0
37.5°	764.0	701.7	661.0	625.7	607.6	596.5	599.3
40°	665.9	611.4	581.5	554.7	538.0	530.0	531.8
42.5°	586.4	545.6	521.0	502.7	490.9	486.5	485.4
45°	496.2	473.4	453.1	442.6	436.9	432.0	429.0
47.5°	434.7	416.0	404.7	398.4	393.4	388.5	388.4
50°	397.8	385.5	377.5	370.9	367.0	363.5	366.5
52.5°	369.6	358.3	350.5	344.6	343.1	339.9	339.8
55°	327.9	319.1	313.4	308.1	305.5	303.7	301.5
57.5°	289.9	281.5	276.3	272.9	267.9	266.1	265.4
60°	262.9	256.2	251.0	246.6	244.4	240.8	240.8
62.5°	237.9	231.3	226.4	223.0	219.4	218.0	218.3
65°	201.7	196.5	191.7	188.1	187.3	184.6	185.5
67.5°	168.5	165.0	159.9	158.0	156.3	154.9	153.9
70°	146.4	142.8	140.2	137.6	136.2	136.2	136.2
72.5°	127.7	123.5	121.9	118.6	119.3	118.0	116.6
75°	98.9	96.3	95.0	93.6	91.4	91.4	91.4
77.5°	72.8	72.0	70.4	69.0	68.4	68.0	68.2
80°	56.2	55.8	54.9	54.9	54.1	53.6	52.8
82.5°	43.2	42.1	41.6	41.2	41.1	41.0	40.8
85°	24.6	23.8	23.8	24.2	23.3	23.3	23.8
87.5°	12.8	12.7	12.4	12.4	12.8	12.5	12.5
90°	16.5	16.3	16.3	16.4	16.4	16.6	16.7
92.5°	15.8	15.8	15.8	15.8	15.8	15.9	15.9
95°	31.4	31.4	31.3	31.1	30.9	30.7	30.5
97.5°	52.9	52.9	52.8	52.8	52.8	52.8	52.7
100°	67.8	67.8	67.7	67.6	67.5	67.4	67.2
102.5°	84.1	84.2	84.2	84.1	83.9	83.9	83.8
105°	108.7	108.9	109.0	109.0	109.0	109.0	109.0
107.5°	134.9	135.0	134.7	134.2	133.8	133.3	132.8
110°	152.7	152.7	152.6	152.2	151.9	151.5	151.2



TEST NUMBER: P331340-935

CATALOG NUMBER: S122DIP-S675D530U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	170.4	170.1	169.9	169.6	169.4	169.1	168.9
115°	198.0	197.9	197.7	197.3	197.1	196.7	196.4
117.5°	224.5	224.2	223.9	223.6	223.3	222.9	222.6
120°	242.5	242.5	242.4	242.0	241.8	241.4	241.1
122.5°	260.6	260.4	260.1	259.8	259.6	259.4	259.2
125°	287.7	287.4	287.1	287.1	287.0	286.8	286.7
127.5°	314.0	313.7	313.2	312.9	312.5	312.2	311.9
130°	332.3	332.0	331.7	331.2	330.8	330.4	329.9
132.5°	349.5	349.0	348.6	348.3	347.9	347.6	347.2
135°	375.7	375.7	375.4	375.1	374.8	374.4	374.1
137.5°	400.5	400.5	400.2	399.8	399.3	398.9	398.5
140°	417.3	417.3	417.2	416.6	416.2	415.8	415.3
142.5°	432.5	432.6	432.4	432.0	431.5	431.1	430.7
145°	455.5	455.6	455.4	455.0	454.5	454.1	453.7
147.5°	475.7	476.0	475.9	475.4	475.0	474.6	474.2
150°	488.5	488.9	488.9	488.5	488.2	487.8	487.6
152.5°	501.4	501.8	501.8	501.4	500.9	500.5	500.2
155°	517.6	518.2	518.3	518.0	517.6	517.3	517.0
157.5°	532.8	533.6	533.6	533.1	532.6	532.1	531.5
160°	541.6	542.2	542.3	541.9	541.5	541.0	540.5
162.5°	549.7	550.4	550.5	550.0	549.5	549.0	548.5
165°	560.1	560.8	560.9	560.3	559.8	559.3	558.7
167.5°	568.6	569.4	569.5	568.9	568.3	567.7	567.1
170°	573.3	574.0	574.1	573.4	572.8	572.1	571.5
172.5°	576.9	577.6	577.6	577.0	576.4	575.7	575.1
175°	580.7	581.4	581.5	580.8	580.1	579.5	578.9
177.5°	582.2	582.7	582.7	582.2	581.7	581.2	580.7
180°	581.8	581.8	581.8	581.8	581.8	581.8	581.8

(END OF REPORT)