

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331383-935

Luminaire Tested: **S122DIP-S865D330U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331383-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S865D330U935-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4125.2 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331383-935

CATALOG NUMBER: S122DIP-S865D330U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331383-935

CATALOG NUMBER: S122DIP-S865D330U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	87	87	87	78	78	78	73
1	103	99	94	91	98	94	90	87	85	82	79	76	74	72	69	67	66	62
2	94	86	80	74	89	82	76	71	74	70	66	67	63	60	60	58	55	52
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	54	50	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	41	38
5	72	60	52	45	68	57	50	44	52	46	41	48	42	38	43	39	35	33
6	67	54	46	39	63	52	44	38	47	41	36	43	38	34	39	35	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	45	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	23	21
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19184	19184	19184
5°	19258	18979	19091
10°	19143	18787	18882
15°	18907	18544	18524
20°	18570	18179	18158
25°	18235	17728	17728
30°	17807	17316	17167
35°	17406	16821	16575
40°	16904	16326	16012
45°	16408	15835	15445
50°	15870	15325	14780
55°	15308	14728	14184
60°	14683	14018	13504
65°	14013	13310	12699
70°	13161	12458	11863
75°	11971	11472	11185
80°	10628	10302	9772
85°	8670	8262	7410



TEST NUMBER: P331383-935

CATALOG NUMBER: S122DIP-S865D330U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.7	2.7
10°-20°	314.4	7.6
20°-30°	462.1	11.2
30°-40°	536.8	13.0
40°-50°	536.2	13.0
50°-60°	467.6	11.3
60°-70°	345.7	8.4
70°-80°	195.8	4.7
80°-90°	54.1	1.3
90°-100°	63.3	1.5
100°-110°	214.7	5.2
110°-120°	228.0	5.5
120°-130°	187.7	4.6
130°-140°	150.7	3.7
140°-150°	113.9	2.8
150°-160°	80.1	1.9
160°-170°	47.1	1.1
170°-180°	15.3	0.4
0°-30°	888.2	21.5
0°-40°	1425.0	34.5
0°-60°	2428.7	58.9
0°-90°	3024.4	73.3
90°-120°	505.9	12.3
90°-150°	958.3	23.2
90°-180°	1101.0	26.7
0°-180°	4125.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1188	1188	1188	1188	1188	
5°	1188	1183	1171	1180	1178	113
15°	1131	1124	1109	1113	1108	318
25°	1024	1014	995	997	995	471
35°	883	871	853	847	841	551
45°	719	710	694	681	676	554
55°	544	537	523	510	504	486
65°	367	360	348	338	332	363
75°	192	189	184	178	179	205
85°	47	46	45	41	40	54
90°	0	4	10	10	10	3
95°	11	26	119	45	35	11
105°	37	56	225	403	343	39
115°	65	83	189	389	451	65
125°	91	108	181	315	366	81
135°	107	128	179	265	303	83
145°	122	141	178	221	242	77
155°	139	150	173	196	204	64
165°	152	156	166	176	179	43
175°	158	158	159	161	161	15
180°	158	158	158	158	158	



TEST NUMBER: P331383-935

CATALOG NUMBER: S122DIP-S865D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1193.7	1192.7	1191.6	1190.7	1189.6	1188.0	1185.8	1183.5	1181.3	1179.1	1181.1
5°	1188.2	1187.1	1186.2	1185.2	1184.1	1182.2	1179.5	1176.6	1173.9	1171.0	1173.1
7.5°	1177.7	1176.1	1174.6	1172.9	1171.4	1169.2	1166.3	1163.5	1160.6	1157.8	1159.9
10°	1167.6	1165.9	1164.1	1162.3	1160.5	1158.1	1155.0	1152.0	1149.0	1145.9	1148.0
12.5°	1153.9	1152.4	1150.8	1149.2	1147.6	1145.3	1142.3	1139.2	1136.2	1133.2	1134.5
15°	1131.1	1129.5	1128.0	1126.5	1125.0	1122.6	1119.3	1115.9	1112.7	1109.4	1110.3
17.5°	1101.8	1100.3	1098.8	1097.3	1095.7	1093.3	1089.9	1086.6	1083.2	1079.9	1081.1
20°	1080.8	1079.3	1077.8	1076.2	1074.7	1072.2	1068.6	1065.1	1061.5	1058.0	1058.7
22.5°	1059.8	1057.7	1055.5	1053.3	1051.3	1048.5	1045.2	1041.8	1038.5	1035.1	1035.3
25°	1023.6	1021.7	1019.6	1017.6	1015.5	1012.4	1008.1	1003.8	999.4	995.1	995.7
27.5°	982.6	980.8	978.9	977.1	975.3	972.6	969.2	965.8	962.4	959.0	958.3
30°	955.1	953.1	951.1	949.1	947.0	944.1	940.3	936.5	932.6	928.8	928.1
32.5°	925.9	924.3	922.6	921.0	919.4	916.5	912.6	908.5	904.6	900.5	899.1
35°	883.1	880.6	878.0	875.6	873.0	869.7	865.6	861.6	857.5	853.4	852.0
37.5°	834.9	832.7	830.4	828.2	826.0	822.9	818.8	814.8	810.6	806.6	804.7
40°	802.0	800.0	798.0	795.9	793.9	790.8	786.8	782.7	778.7	774.6	772.3
42.5°	770.1	768.0	765.9	764.0	761.9	758.9	754.8	750.8	746.7	742.6	740.1
45°	718.6	716.9	715.1	713.3	711.5	708.7	704.9	701.1	697.3	693.5	690.7
47.5°	667.4	665.8	664.1	662.5	660.7	657.9	653.9	650.0	646.0	642.0	639.1
50°	631.8	630.5	629.3	628.0	626.7	624.3	620.8	617.2	613.6	610.1	606.6
52.5°	597.1	595.4	593.7	592.0	590.4	587.9	584.5	581.2	577.8	574.5	571.5
55°	543.8	542.3	540.8	539.2	537.7	535.5	532.4	529.3	526.3	523.2	520.2
57.5°	490.3	489.1	487.9	486.7	485.5	483.2	479.8	476.5	473.1	469.8	466.8
60°	454.7	453.7	452.7	451.7	450.6	448.4	444.8	441.3	437.7	434.1	431.4
62.5°	420.0	418.4	416.7	415.1	413.5	411.3	408.5	405.8	403.0	400.4	397.8
65°	366.8	365.2	363.7	362.1	360.7	358.6	356.1	353.5	351.0	348.4	346.2
67.5°	312.6	311.3	310.1	308.9	307.7	306.0	303.7	301.4	299.1	296.8	295.1
70°	278.8	277.8	276.7	275.7	274.7	273.0	270.8	268.5	266.2	263.9	262.2
72.5°	244.0	243.1	242.0	241.0	240.0	238.8	237.3	235.8	234.3	232.8	231.1
75°	191.9	191.4	190.9	190.5	189.9	189.0	187.8	186.5	185.2	183.9	182.4
77.5°	145.3	144.5	143.6	142.8	141.9	141.2	140.7	140.2	139.7	139.1	138.4
80°	114.3	114.0	113.7	113.5	113.2	112.9	112.4	111.8	111.3	110.8	110.0
82.5°	85.0	85.0	84.9	84.8	84.8	84.6	84.3	84.0	83.7	83.4	82.4
85°	46.8	46.6	46.3	46.1	45.8	45.5	45.3	45.0	44.8	44.6	43.8
87.5°	16.5	16.3	16.1	15.8	15.6	15.3	15.2	15.2	15.2	14.9	14.2
90°	0.3	1.2	2.4	3.0	3.6	4.6	6.1	8.2	10.1	10.3	10.1
92.5°	3.7	5.3	7.6	8.9	10.9	13.8	20.7	30.4	39.0	39.5	33.4
95°	10.7	11.9	14.9	17.7	22.5	29.8	43.8	70.3	105.6	119.2	104.4
97.5°	17.3	18.9	22.2	26.3	31.9	40.2	57.8	94.7	153.3	203.5	213.5
100°	23.4	24.4	27.0	31.9	38.1	46.6	62.7	99.8	165.5	240.3	284.1
102.5°	29.0	29.7	32.5	37.3	43.7	52.2	67.1	100.0	160.8	241.5	310.4
105°	37.1	38.3	40.5	45.0	51.7	60.3	74.6	101.6	151.8	225.4	306.3
107.5°	45.9	46.8	48.9	53.1	59.8	68.4	82.2	105.8	147.3	208.1	279.7
110°	51.7	53.0	54.8	58.7	65.1	74.0	87.3	109.2	146.4	199.8	262.9



TEST NUMBER: P331383-935

CATALOG NUMBER: S122DIP-S865D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.1	58.3	60.4	64.1	70.2	79.3	92.2	112.9	146.5	194.5	251.2
115°	65.4	66.9	68.8	72.4	78.5	86.7	99.8	118.3	147.8	188.6	236.7
117.5°	74.0	75.3	77.1	80.3	86.2	94.7	106.8	124.2	150.1	185.7	227.6
120°	79.4	80.6	82.5	85.2	91.3	99.8	111.7	128.1	151.5	184.1	222.7
122.5°	84.6	85.5	87.3	90.3	96.3	105.1	116.2	131.5	153.2	183.0	218.5
125°	91.3	92.2	94.0	97.6	103.8	112.3	123.2	136.9	155.8	181.3	212.7
127.5°	96.6	97.8	100.4	104.4	110.2	119.0	129.7	142.0	158.3	180.3	207.2
130°	99.8	101.0	104.0	108.3	114.4	122.9	133.5	145.1	160.3	179.8	203.5
132.5°	102.7	104.2	107.5	111.9	118.3	126.8	137.0	148.3	162.3	179.5	200.6
135°	107.1	108.3	111.9	116.5	123.6	132.0	141.8	152.4	164.6	179.2	196.5
137.5°	111.2	112.7	116.3	121.2	128.1	136.0	145.7	155.6	166.7	179.1	193.6
140°	114.4	115.6	119.2	124.2	130.8	138.7	147.8	157.3	167.6	178.9	191.9
142.5°	117.5	118.6	121.9	126.8	133.3	140.7	149.6	158.8	168.3	178.9	190.3
145°	122.3	123.6	126.6	131.1	137.2	143.9	152.1	160.7	169.1	178.2	188.0
147.5°	127.4	128.3	131.2	135.4	140.5	146.5	154.2	161.7	169.4	177.2	185.7
150°	130.8	131.7	134.1	138.1	142.7	148.2	155.2	162.1	169.1	176.4	183.7
152.5°	134.2	134.7	137.1	140.5	144.9	149.8	156.1	162.4	168.7	175.2	182.0
155°	139.1	139.3	141.1	144.5	147.8	152.4	157.6	162.7	167.9	173.1	178.9
157.5°	143.0	143.4	144.8	147.7	150.4	154.2	158.6	162.7	166.5	170.9	175.9
160°	145.7	146.0	147.2	149.6	152.1	155.5	159.1	162.7	165.8	169.4	173.7
162.5°	148.4	148.2	149.5	151.4	153.6	156.2	159.4	162.5	165.1	168.2	171.8
165°	151.5	151.2	151.8	153.6	155.2	157.0	159.7	161.9	163.7	165.8	168.5
167.5°	154.0	153.7	154.2	155.4	156.5	157.6	159.6	161.4	162.3	163.7	165.4
170°	155.8	155.2	155.5	156.4	157.0	157.9	159.4	160.9	161.5	162.5	163.7
172.5°	156.7	156.4	156.2	157.1	157.5	158.2	159.2	160.2	160.6	161.0	162.0
175°	157.9	157.6	157.3	157.9	157.9	158.2	158.8	159.4	159.1	159.4	159.7
177.5°	158.4	157.9	157.7	158.2	158.2	158.2	158.4	158.9	158.4	158.2	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2



TEST NUMBER: P331383-935

CATALOG NUMBER: S122DIP-S865D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1183.1	1185.2	1187.1	1188.0	1187.6	1187.1	1186.8	1186.4
5°	1175.1	1177.2	1179.2	1179.9	1179.5	1179.0	1178.5	1177.9
7.5°	1161.8	1163.9	1166.0	1166.7	1166.1	1165.5	1165.0	1164.4
10°	1150.0	1152.0	1154.1	1154.7	1153.9	1153.1	1152.4	1151.7
12.5°	1136.0	1137.4	1138.8	1139.3	1138.7	1138.2	1137.6	1137.0
15°	1111.4	1112.4	1113.4	1113.3	1112.1	1110.8	1109.5	1108.2
17.5°	1082.2	1083.4	1084.6	1084.5	1083.3	1082.1	1080.9	1079.7
20°	1059.5	1060.2	1061.0	1060.8	1059.9	1058.9	1057.8	1056.8
22.5°	1035.4	1035.5	1035.7	1035.5	1034.8	1034.2	1033.6	1033.0
25°	996.2	996.6	997.1	997.1	996.6	996.2	995.7	995.1
27.5°	957.5	956.7	956.0	955.0	953.7	952.5	951.3	950.1
30°	927.3	926.6	925.8	924.9	923.9	922.9	921.9	920.8
32.5°	897.8	896.4	895.0	893.8	892.9	891.8	890.8	889.8
35°	850.4	848.9	847.4	845.9	844.7	843.4	842.1	840.9
37.5°	802.9	801.0	799.1	797.5	796.3	795.1	793.9	792.6
40°	770.1	767.8	765.5	763.8	762.8	761.8	760.8	759.7
42.5°	737.6	735.1	732.7	730.7	729.3	727.9	726.4	725.0
45°	687.9	685.1	682.3	680.4	679.4	678.4	677.3	676.4
47.5°	636.2	633.3	630.3	628.1	626.6	625.2	623.7	622.2
50°	603.0	599.4	595.9	593.5	592.2	590.9	589.7	588.4
52.5°	568.5	565.6	562.7	560.3	558.7	557.0	555.3	553.6
55°	517.2	514.1	511.1	508.9	507.6	506.4	505.1	503.9
57.5°	463.8	460.8	457.8	455.8	454.9	453.9	453.0	451.9
60°	428.6	425.8	423.0	421.2	420.4	419.7	418.9	418.2
62.5°	395.1	392.5	389.9	388.2	387.2	386.2	385.3	384.4
65°	343.9	341.6	339.3	337.5	336.3	335.0	333.7	332.4
67.5°	293.3	291.4	289.7	288.3	287.3	286.3	285.2	284.2
70°	260.4	258.6	256.8	255.4	254.4	253.4	252.4	251.3
72.5°	229.3	227.5	225.8	224.5	223.6	222.8	222.0	221.2
75°	180.9	179.3	177.9	177.4	177.9	178.4	178.8	179.3
77.5°	137.7	136.9	136.1	135.3	134.7	134.0	133.3	132.5
80°	109.3	108.6	107.8	107.1	106.6	106.2	105.6	105.1
82.5°	81.5	80.5	79.6	79.0	78.9	78.8	78.7	78.6
85°	43.0	42.3	41.5	41.0	40.7	40.5	40.2	40.0
87.5°	13.5	12.8	12.3	12.0	11.8	11.5	11.4	11.1
90°	9.7	9.1	9.7	10.1	10.1	10.1	10.1	10.1
92.5°	26.5	22.7	20.2	18.3	18.1	17.1	17.3	16.9
95°	79.7	61.1	48.4	41.7	37.7	35.3	34.4	34.7
97.5°	186.0	152.1	119.2	97.3	82.7	75.3	70.9	68.3
100°	277.8	240.0	198.4	161.5	136.3	123.2	114.4	108.9
102.5°	337.9	329.3	298.9	259.8	232.4	210.1	199.1	191.7
105°	369.6	404.0	407.9	398.0	379.0	360.2	347.1	342.9
107.5°	346.7	398.6	430.2	444.9	447.3	446.3	443.6	438.0
110°	327.0	381.5	420.4	445.4	458.5	464.3	467.0	466.7



TEST NUMBER: P331383-935

CATALOG NUMBER: S122DIP-S865D330U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	309.0	361.3	402.9	431.5	449.7	459.3	464.5	466.1
115°	286.9	333.7	373.6	404.9	426.5	440.5	448.4	451.2
117.5°	270.2	311.3	347.5	376.9	398.9	413.7	422.0	424.3
120°	261.9	299.6	331.9	359.6	380.9	395.2	404.0	407.1
122.5°	255.4	289.9	320.5	345.4	364.5	378.7	386.5	389.0
125°	245.8	277.2	303.9	326.7	344.4	355.9	363.5	366.0
127.5°	236.3	264.8	290.0	311.0	326.4	337.3	343.8	345.8
130°	230.3	256.5	280.5	300.6	315.5	325.8	331.9	334.3
132.5°	224.5	248.7	270.8	289.6	304.3	314.6	320.2	322.4
135°	216.3	236.3	256.5	273.5	286.5	296.6	302.1	303.3
137.5°	209.8	226.6	242.5	257.4	269.3	277.9	282.8	284.6
140°	205.6	220.2	234.3	247.6	257.4	265.3	269.8	271.6
142.5°	202.2	214.6	226.7	237.9	247.1	254.3	258.4	258.7
145°	197.4	207.5	216.9	225.8	233.0	238.2	241.3	242.1
147.5°	193.7	201.6	209.0	215.4	221.4	225.6	227.6	228.3
150°	191.1	197.8	204.1	209.6	214.1	217.8	219.6	220.0
152.5°	188.4	194.6	200.0	204.7	208.4	211.5	212.8	212.9
155°	184.7	189.5	194.1	197.4	200.8	202.9	204.1	203.5
157.5°	180.4	184.4	188.2	190.9	193.2	195.0	195.5	195.5
160°	177.6	181.0	184.3	186.5	188.6	190.1	190.5	190.5
162.5°	175.0	177.9	180.7	182.4	184.5	185.5	185.8	185.5
165°	171.0	173.1	175.2	176.4	177.6	178.9	178.9	178.6
167.5°	167.1	168.8	170.2	171.3	171.9	172.5	172.5	172.1
170°	165.2	166.1	167.3	167.9	168.2	169.1	168.8	168.2
172.5°	163.0	163.7	164.6	165.0	165.3	165.7	165.4	165.1
175°	160.7	160.9	161.3	161.5	161.5	161.9	161.5	160.9
177.5°	158.9	158.9	159.2	159.2	159.2	159.2	158.9	158.4
180°	158.2	158.2	158.2	158.2	158.2	158.2	158.2	158.2

(END OF REPORT)