

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331390-935

Luminaire Tested: **S122DIP-S865D530U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331390-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S865D530U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4844.3 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331390-935

CATALOG NUMBER: S122DIP-S865D530U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331390-935

CATALOG NUMBER: S122DIP-S865D530U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	53	50	48
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41
4	77	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19184	19184	19184
5°	19258	18979	19091
10°	19143	18787	18882
15°	18907	18544	18524
20°	18570	18179	18158
25°	18235	17728	17728
30°	17807	17316	17167
35°	17406	16821	16575
40°	16904	16326	16012
45°	16408	15835	15445
50°	15870	15325	14780
55°	15308	14728	14184
60°	14683	14018	13504
65°	14013	13310	12699
70°	13161	12458	11863
75°	11971	11472	11185
80°	10628	10302	9772
85°	8670	8262	7410



TEST NUMBER: P331390-935

CATALOG NUMBER: S122DIP-S865D530U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.7	2.3
10°-20°	314.4	6.5
20°-30°	462.1	9.5
30°-40°	536.8	11.1
40°-50°	536.2	11.1
50°-60°	467.6	9.7
60°-70°	345.7	7.1
70°-80°	195.8	4.0
80°-90°	54.2	1.1
90°-100°	20.7	0.4
100°-110°	76.0	1.6
110°-120°	203.0	4.2
120°-130°	335.2	6.9
130°-140°	356.5	7.4
140°-150°	331.3	6.8
150°-160°	266.4	5.5
160°-170°	171.7	3.5
170°-180°	59.1	1.2
0°-30°	888.2	18.3
0°-40°	1425.0	29.4
0°-60°	2428.7	50.1
0°-90°	3024.5	62.4
90°-120°	299.7	6.2
90°-150°	1322.7	27.3
90°-180°	1820.0	37.6
0°-180°	4844.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1188	1188	1188	1188	1188	
5°	1188	1183	1171	1180	1178	113
15°	1131	1124	1109	1113	1108	318
25°	1024	1014	995	997	995	471
35°	883	871	853	847	841	551
45°	719	710	694	681	676	554
55°	544	537	523	510	504	486
65°	367	360	348	338	332	363
75°	192	189	184	178	179	205
85°	47	46	45	41	40	54
90°	0	5	9	11	12	4
95°	29	15	18	20	19	36
105°	137	143	27	32	34	146
115°	258	266	277	79	37	254
125°	365	371	380	383	384	326
135°	452	459	463	468	467	349
145°	524	524	532	534	532	328
155°	577	574	579	581	578	266
165°	608	606	607	610	607	172
175°	622	619	620	623	619	59
180°	621	621	621	621	621	



TEST NUMBER: P331390-935

CATALOG NUMBER: S122DIP-S865D530U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1193.7	1192.7	1191.6	1190.7	1189.6	1188.0	1185.8	1183.5	1181.3	1179.1	1181.1
5°	1188.2	1187.1	1186.2	1185.2	1184.1	1182.2	1179.5	1176.6	1173.9	1171.0	1173.1
7.5°	1177.7	1176.1	1174.6	1172.9	1171.4	1169.2	1166.3	1163.5	1160.6	1157.8	1159.9
10°	1167.6	1165.9	1164.1	1162.3	1160.5	1158.1	1155.0	1152.0	1149.0	1145.9	1148.0
12.5°	1153.9	1152.4	1150.8	1149.2	1147.6	1145.3	1142.3	1139.2	1136.2	1133.2	1134.5
15°	1131.1	1129.5	1128.0	1126.5	1125.0	1122.6	1119.3	1115.9	1112.7	1109.4	1110.3
17.5°	1101.8	1100.3	1098.8	1097.3	1095.7	1093.3	1089.9	1086.6	1083.2	1079.9	1081.1
20°	1080.8	1079.3	1077.8	1076.2	1074.7	1072.2	1068.6	1065.1	1061.5	1058.0	1058.7
22.5°	1059.8	1057.7	1055.5	1053.3	1051.3	1048.5	1045.2	1041.8	1038.5	1035.1	1035.3
25°	1023.6	1021.7	1019.6	1017.6	1015.5	1012.4	1008.1	1003.8	999.4	995.1	995.7
27.5°	982.6	980.8	978.9	977.1	975.3	972.6	969.2	965.8	962.4	959.0	958.3
30°	955.1	953.1	951.1	949.1	947.0	944.1	940.3	936.5	932.6	928.8	928.1
32.5°	925.9	924.3	922.6	921.0	919.4	916.5	912.6	908.5	904.6	900.5	899.1
35°	883.1	880.6	878.0	875.6	873.0	869.7	865.6	861.6	857.5	853.4	852.0
37.5°	834.9	832.7	830.4	828.2	826.0	822.9	818.8	814.8	810.6	806.6	804.7
40°	802.0	800.0	798.0	795.9	793.9	790.8	786.8	782.7	778.7	774.6	772.3
42.5°	770.1	768.0	765.9	764.0	761.9	758.9	754.8	750.8	746.7	742.6	740.1
45°	718.6	716.9	715.1	713.3	711.5	708.7	704.9	701.1	697.3	693.5	690.7
47.5°	667.4	665.8	664.1	662.5	660.7	657.9	653.9	650.0	646.0	642.0	639.1
50°	631.8	630.5	629.3	628.0	626.7	624.3	620.8	617.2	613.6	610.1	606.6
52.5°	597.1	595.4	593.7	592.0	590.4	587.9	584.5	581.2	577.8	574.5	571.5
55°	543.8	542.3	540.8	539.2	537.7	535.5	532.4	529.3	526.3	523.2	520.2
57.5°	490.3	489.1	487.9	486.7	485.5	483.2	479.8	476.5	473.1	469.8	466.8
60°	454.7	453.7	452.7	451.7	450.6	448.4	444.8	441.3	437.7	434.1	431.4
62.5°	420.0	418.4	416.7	415.1	413.5	411.3	408.5	405.8	403.0	400.4	397.8
65°	366.8	365.2	363.7	362.1	360.7	358.6	356.1	353.5	351.0	348.4	346.2
67.5°	312.6	311.3	310.1	308.9	307.7	306.0	303.7	301.4	299.1	296.8	295.1
70°	278.8	277.8	276.7	275.7	274.7	273.0	270.8	268.5	266.2	263.9	262.2
72.5°	244.0	243.1	242.0	241.0	240.0	238.8	237.3	235.8	234.3	232.8	231.1
75°	191.9	191.4	190.9	190.5	189.9	189.0	187.8	186.5	185.2	183.9	182.4
77.5°	145.3	144.5	143.6	142.8	141.9	141.2	140.7	140.2	139.7	139.1	138.4
80°	114.3	114.0	113.7	113.5	113.2	112.9	112.4	111.8	111.3	110.8	110.0
82.5°	85.0	85.0	84.9	84.8	84.8	84.6	84.3	84.0	83.7	83.4	82.4
85°	46.8	46.6	46.3	46.1	45.8	45.5	45.3	45.0	44.8	44.6	43.8
87.5°	16.5	16.4	16.2	16.0	15.8	15.6	15.3	15.1	14.8	14.6	14.1
90°	0.4	1.5	2.7	3.7	4.8	5.8	6.6	7.4	8.2	9.0	9.5
92.5°	9.0	9.0	8.9	8.8	8.7	8.9	9.2	9.6	10.0	10.4	10.7
95°	29.2	25.9	22.6	19.3	16.0	14.7	15.4	16.1	16.8	17.6	18.0
97.5°	57.9	48.6	39.4	30.1	20.8	17.0	18.6	20.2	21.9	23.4	23.8
100°	79.6	65.9	52.2	38.5	24.8	18.9	20.5	22.2	23.9	25.6	26.4
102.5°	103.2	100.4	97.5	94.5	91.7	83.1	69.0	54.8	40.6	26.3	27.4
105°	136.6	139.6	142.6	145.6	148.6	136.5	109.2	82.0	54.7	27.4	28.5
107.5°	174.6	177.0	179.4	181.8	184.3	169.1	136.5	103.8	71.0	38.4	37.3
110°	199.1	201.1	203.3	205.3	207.4	194.1	165.2	136.4	107.5	78.6	68.6



TEST NUMBER: P331390-935

CATALOG NUMBER: S122DIP-S865D530U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	222.1	223.9	225.8	227.6	229.5	226.9	219.7	212.6	205.4	198.4	161.9
115°	258.4	260.0	261.7	263.5	265.2	267.3	269.8	272.2	274.7	277.2	231.0
117.5°	290.8	292.7	294.6	296.5	298.4	300.2	302.0	303.7	305.4	307.0	295.9
120°	314.5	316.0	317.5	319.0	320.6	322.2	324.0	325.8	327.5	329.3	330.5
122.5°	334.7	336.2	337.9	339.4	341.0	342.8	344.7	346.6	348.6	350.6	351.3
125°	365.3	366.6	367.9	369.2	370.5	372.1	374.0	375.9	377.8	379.7	380.4
127.5°	393.0	394.5	396.0	397.4	398.8	400.3	401.7	403.1	404.5	406.0	406.9
130°	410.7	412.2	413.9	415.5	417.1	418.4	419.6	420.6	421.7	422.8	424.0
132.5°	428.7	430.0	431.4	432.7	434.1	435.3	436.4	437.6	438.6	439.7	440.7
135°	452.0	453.7	455.2	456.8	458.4	459.7	460.5	461.5	462.4	463.2	464.3
137.5°	475.7	476.7	477.9	479.0	480.1	481.2	482.2	483.3	484.2	485.3	486.3
140°	491.1	491.9	492.8	493.5	494.3	495.2	496.4	497.5	498.5	499.6	500.6
142.5°	504.0	504.8	505.5	506.2	507.0	507.9	509.2	510.4	511.7	513.0	513.8
145°	524.3	524.3	524.2	524.1	524.0	524.8	526.5	528.1	529.9	531.6	532.3
147.5°	542.1	541.7	541.3	541.0	540.5	541.2	542.9	544.6	546.2	547.9	548.5
150°	553.5	552.8	552.2	551.5	550.8	551.2	552.8	554.4	556.0	557.6	558.2
152.5°	563.3	562.5	561.7	560.9	560.2	560.5	562.1	563.6	565.1	566.6	567.2
155°	577.4	576.5	575.6	574.7	573.8	573.9	575.1	576.4	577.6	578.8	579.4
157.5°	588.4	587.7	586.9	586.2	585.4	585.5	586.3	587.1	588.0	588.8	589.4
160°	595.0	594.3	593.7	593.1	592.5	592.5	593.1	593.7	594.3	595.0	595.6
162.5°	600.6	600.0	599.4	598.8	598.3	598.2	598.7	599.3	599.8	600.3	601.0
165°	608.4	607.8	607.2	606.6	606.0	605.9	606.1	606.4	606.7	607.0	607.8
167.5°	614.2	613.5	612.9	612.3	611.7	611.6	611.8	612.2	612.4	612.7	613.4
170°	617.3	616.8	616.2	615.6	615.0	614.8	615.0	615.2	615.4	615.6	616.3
172.5°	619.6	619.0	618.4	617.8	617.2	616.9	617.2	617.3	617.5	617.8	618.5
175°	622.3	621.6	621.0	620.3	619.5	619.3	619.5	619.7	619.8	620.1	620.8
177.5°	622.8	622.2	621.6	621.1	620.5	620.3	620.4	620.4	620.5	620.6	621.2
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0



TEST NUMBER: P331390-935

CATALOG NUMBER: S122DIP-S865D530U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2	1188.2
2.5°	1183.1	1185.2	1187.1	1188.0	1187.6	1187.1	1186.8	1186.4
5°	1175.1	1177.2	1179.2	1179.9	1179.5	1179.0	1178.5	1177.9
7.5°	1161.8	1163.9	1166.0	1166.7	1166.1	1165.5	1165.0	1164.4
10°	1150.0	1152.0	1154.1	1154.7	1153.9	1153.1	1152.4	1151.7
12.5°	1136.0	1137.4	1138.8	1139.3	1138.7	1138.2	1137.6	1137.0
15°	1111.4	1112.4	1113.4	1113.3	1112.1	1110.8	1109.5	1108.2
17.5°	1082.2	1083.4	1084.6	1084.5	1083.3	1082.1	1080.9	1079.7
20°	1059.5	1060.2	1061.0	1060.8	1059.9	1058.9	1057.8	1056.8
22.5°	1035.4	1035.5	1035.7	1035.5	1034.8	1034.2	1033.6	1033.0
25°	996.2	996.6	997.1	997.1	996.6	996.2	995.7	995.1
27.5°	957.5	956.7	956.0	955.0	953.7	952.5	951.3	950.1
30°	927.3	926.6	925.8	924.9	923.9	922.9	921.9	920.8
32.5°	897.8	896.4	895.0	893.8	892.9	891.8	890.8	889.8
35°	850.4	848.9	847.4	845.9	844.7	843.4	842.1	840.9
37.5°	802.9	801.0	799.1	797.5	796.3	795.1	793.9	792.6
40°	770.1	767.8	765.5	763.8	762.8	761.8	760.8	759.7
42.5°	737.6	735.1	732.7	730.7	729.3	727.9	726.4	725.0
45°	687.9	685.1	682.3	680.4	679.4	678.4	677.3	676.4
47.5°	636.2	633.3	630.3	628.1	626.6	625.2	623.7	622.2
50°	603.0	599.4	595.9	593.5	592.2	590.9	589.7	588.4
52.5°	568.5	565.6	562.7	560.3	558.7	557.0	555.3	553.6
55°	517.2	514.1	511.1	508.9	507.6	506.4	505.1	503.9
57.5°	463.8	460.8	457.8	455.8	454.9	453.9	453.0	451.9
60°	428.6	425.8	423.0	421.2	420.4	419.7	418.9	418.2
62.5°	395.1	392.5	389.9	388.2	387.2	386.2	385.3	384.4
65°	343.9	341.6	339.3	337.5	336.3	335.0	333.7	332.4
67.5°	293.3	291.4	289.7	288.3	287.3	286.3	285.2	284.2
70°	260.4	258.6	256.8	255.4	254.4	253.4	252.4	251.3
72.5°	229.3	227.5	225.8	224.5	223.6	222.8	222.0	221.2
75°	180.9	179.3	177.9	177.4	177.9	178.4	178.8	179.3
77.5°	137.7	136.9	136.1	135.3	134.7	134.0	133.3	132.5
80°	109.3	108.6	107.8	107.1	106.6	106.2	105.6	105.1
82.5°	81.5	80.5	79.6	79.0	78.9	78.8	78.7	78.6
85°	43.0	42.3	41.5	41.0	40.7	40.5	40.2	40.0
87.5°	13.6	13.1	12.6	12.2	12.1	11.9	11.7	11.5
90°	10.0	10.5	11.0	11.4	11.5	11.7	12.0	12.1
92.5°	10.9	11.2	11.5	11.6	11.8	11.9	12.1	12.1
95°	18.5	19.0	19.5	19.7	19.6	19.5	19.5	19.3
97.5°	24.3	24.6	25.1	25.3	25.4	25.6	25.7	25.8
100°	27.2	28.0	28.8	29.3	29.5	29.7	29.9	30.1
102.5°	28.4	29.4	30.5	31.2	31.4	31.7	31.9	32.3
105°	29.6	30.7	31.8	32.5	33.0	33.3	33.8	34.2
107.5°	36.2	35.0	33.9	33.6	33.9	34.4	34.7	35.1
110°	58.6	48.6	38.7	33.9	34.3	34.7	35.1	35.5



TEST NUMBER: P331390-935

CATALOG NUMBER: S122DIP-S865D530U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	125.4	89.0	52.6	34.6	34.9	35.2	35.6	35.8
115°	184.8	138.5	92.3	65.6	58.4	51.2	44.0	36.9
117.5°	284.7	273.5	262.3	245.0	221.3	197.7	174.1	150.4
120°	331.7	332.9	334.2	328.0	314.5	301.1	287.6	274.1
122.5°	352.0	352.8	353.4	352.5	349.9	347.2	344.7	342.0
125°	381.1	381.8	382.5	383.0	383.3	383.6	383.9	384.2
127.5°	407.9	409.0	410.0	410.5	410.6	410.7	410.7	410.8
130°	425.0	426.1	427.2	427.7	427.6	427.5	427.4	427.3
132.5°	441.6	442.6	443.5	443.8	443.8	443.7	443.6	443.5
135°	465.3	466.2	467.3	467.7	467.4	467.3	467.1	466.8
137.5°	487.2	488.2	489.2	489.5	489.1	488.8	488.5	488.2
140°	501.4	502.3	503.3	503.4	502.9	502.5	502.0	501.4
142.5°	514.6	515.4	516.3	516.4	515.9	515.4	514.9	514.4
145°	533.0	533.6	534.3	534.4	534.0	533.5	533.0	532.4
147.5°	549.0	549.5	550.0	550.0	549.7	549.2	548.8	548.4
150°	558.8	559.4	560.0	560.1	559.6	559.0	558.5	558.1
152.5°	567.8	568.4	569.0	568.9	568.3	567.7	567.0	566.4
155°	580.0	580.6	581.2	581.0	580.2	579.5	578.7	577.8
157.5°	590.1	590.8	591.5	591.5	590.6	589.9	589.1	588.3
160°	596.1	596.7	597.3	597.3	596.6	595.9	595.1	594.4
162.5°	601.7	602.4	603.0	603.0	602.1	601.2	600.4	599.5
165°	608.5	609.2	609.8	609.8	609.2	608.5	607.8	607.0
167.5°	614.1	614.8	615.5	615.4	614.5	613.6	612.7	611.8
170°	617.0	617.7	618.4	618.3	617.3	616.5	615.6	614.7
172.5°	619.1	619.8	620.5	620.4	619.6	618.6	617.8	616.8
175°	621.5	622.2	622.8	622.8	621.7	620.7	619.7	618.7
177.5°	621.7	622.3	622.8	622.8	622.1	621.3	620.6	619.9
180°	621.0	621.0	621.0	621.0	621.0	621.0	621.0	621.0

(END OF REPORT)