

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331747-935

Luminaire Tested: **S122RDIP-S1005D725U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331747-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S1005D725U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5778.2 lumens  
Efficiency: N/A  
Efficacy: 95.2 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57																												
1	100	96	93	89	93	90	87	84	78	75	73	67	65	64	56	55	54	50																												
2	92	85	79	74	86	80	75	70	69	65	62	60	57	55	51	49	47	43																												
3	85	76	69	63	79	71	65	60	62	57	54	54	50	47	46	43	41	38																												
4	78	68	60	54	72	64	57	52	56	51	47	49	45	41	42	39	37	33																												
5	72	61	53	47	67	57	50	45	50	45	41	44	40	37	38	35	33	30																												
6	67	55	47	42	62	52	45	40	46	40	36	40	36	33	35	32	29	27																												
7	62	50	43	37	58	47	41	36	42	37	33	37	33	29	32	29	26	24																												
8	58	46	38	33	54	43	37	32	39	33	29	34	30	27	30	27	24	22																												
9	54	42	35	30	51	40	33	29	36	30	27	32	27	24	28	25	22	20																												
10	51	39	32	27	47	37	31	26	33	28	24	30	25	22	26	23	20	18																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	30658	30658	30658	30658
5°	34240	30851	27353	30851
10°	37990	30634	23710	30634
15°	39858	30186	18683	30186
20°	34553	29520	16167	29520
25°	22661	28609	14434	28609
30°	15252	27505	13064	27505
35°	12354	26112	11783	26112
40°	10985	24601	10903	24601
45°	9944	22825	9732	22825
50°	9048	21064	9018	21064
55°	8507	19111	8397	19111
60°	7114	17321	7030	17321
65°	5998	15729	6804	15729
70°	5542	14049	6420	14049
75°	5190	12227	5926	12227
80°	4788	10060	5272	10060
85°	4409	7947	4650	7947



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.0	3.1
10°-20°	501.6	8.7
20°-30°	646.3	11.2
30°-40°	614.2	10.6
40°-50°	526.2	9.1
50°-60°	400.7	6.9
60°-70°	253.3	4.4
70°-80°	126.5	2.2
80°-90°	35.0	0.6
90°-100°	28.4	0.5
100°-110°	104.1	1.8
110°-120°	278.3	4.8
120°-130°	459.4	8.0
130°-140°	488.6	8.5
140°-150°	454.1	7.9
150°-160°	365.1	6.3
160°-170°	235.3	4.1
170°-180°	81.0	1.4
0°-30°	1327.9	23.0
0°-40°	1942.1	33.6
0°-60°	2869.0	49.7
0°-90°	3283.8	56.8
90°-120°	410.8	7.1
90°-150°	1813.0	31.4
90°-180°	2494.0	43.2
0°-180°	5778.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2113	1904	1688	1904	2113	209
15°	2384	1806	1118	1806	2384	643
25°	1272	1606	810	1606	1272	604
35°	627	1325	598	1325	627	401
45°	436	1000	426	1000	436	337
55°	302	679	298	679	302	265
65°	157	412	178	412	157	160
75°	83	196	95	196	83	88
85°	24	43	25	43	24	26
90°	17	1	17	1	17	8
95°	26	40	26	40	26	25
105°	47	187	47	187	47	49
115°	50	354	50	354	50	126
125°	527	501	527	501	527	456
135°	640	620	640	620	640	493
145°	730	719	730	719	730	456
155°	792	791	792	791	792	365
165°	832	834	832	834	832	235
175°	848	853	848	853	848	81
180°	851	851	851	851	851	



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1975.9	1977.5	1979.1	1975.4	1975.4	1972.2	1965.4	1960.1	1945.3	1943.2	1943.2
5°	2112.6	2111.3	2113.9	2105.4	2093.5	2090.9	2078.4	2061.8	2044.7	2025.6	2021.6
7.5°	2248.6	2246.6	2241.3	2239.9	2230.8	2210.8	2190.6	2169.1	2140.6	2112.8	2098.8
10°	2317.2	2339.0	2325.7	2302.7	2307.3	2276.3	2259.8	2231.5	2207.7	2166.1	2156.9
12.5°	2384.7	2393.3	2389.1	2376.0	2370.1	2348.5	2326.2	2301.6	2257.8	2220.4	2188.0
15°	2384.5	2397.0	2400.3	2396.3	2399.7	2398.3	2386.4	2366.0	2327.7	2286.8	2251.2
17.5°	2208.5	2217.2	2238.8	2253.4	2271.9	2311.0	2330.2	2337.8	2332.1	2308.8	2283.6
20°	2011.0	1996.5	2057.2	2088.3	2114.6	2180.6	2237.3	2259.1	2294.0	2293.4	2286.8
22.5°	1731.3	1734.7	1792.3	1829.1	1906.2	1972.1	2036.8	2118.7	2186.4	2231.1	2257.3
25°	1272.0	1297.2	1354.5	1404.7	1490.5	1613.2	1724.7	1854.0	1976.1	2072.4	2164.1
27.5°	955.4	957.3	1002.7	1049.0	1100.0	1200.6	1340.9	1495.4	1669.4	1813.0	1978.1
30°	818.1	814.2	833.3	861.7	905.3	983.1	1088.6	1240.4	1413.9	1630.3	1823.0
32.5°	721.0	721.3	735.6	756.6	792.8	845.3	917.7	1040.9	1204.9	1417.6	1643.6
35°	626.8	626.1	636.7	651.9	667.0	700.7	750.2	814.9	927.6	1126.3	1357.2
37.5°	559.2	562.1	567.3	576.8	593.6	612.3	642.0	685.4	765.8	883.2	1077.3
40°	521.2	522.5	529.8	537.7	547.6	562.1	586.5	621.6	680.3	774.0	915.8
42.5°	486.4	487.8	492.8	500.2	508.1	522.5	542.8	573.0	620.6	693.7	810.7
45°	435.5	435.5	440.1	443.4	451.9	465.1	481.6	506.7	539.7	593.8	671.7
47.5°	387.7	387.8	390.9	396.6	401.9	412.2	428.4	448.9	472.9	514.8	581.3
50°	360.2	360.9	362.9	367.5	370.8	380.0	392.6	410.4	435.5	467.8	523.2
52.5°	338.1	337.7	340.2	342.2	344.4	351.0	360.4	376.1	398.5	426.6	472.5
55°	302.2	299.5	303.5	306.8	308.8	311.4	316.7	326.6	345.7	369.5	403.8
57.5°	257.4	256.2	259.1	262.1	268.3	275.4	279.9	286.2	296.1	313.1	347.2
60°	220.3	220.3	226.3	228.3	235.6	244.8	254.0	259.3	269.2	280.4	305.5
62.5°	187.6	188.2	191.0	193.0	197.0	208.4	221.3	232.9	242.3	253.0	269.6
65°	157.0	158.3	158.3	159.6	162.3	165.0	170.2	179.4	196.0	211.1	223.7
67.5°	133.3	133.7	134.1	135.3	136.0	139.0	141.0	145.2	149.0	163.3	178.9
70°	117.4	119.4	118.7	120.1	120.7	122.1	124.7	126.7	132.6	136.0	145.2
72.5°	102.6	104.1	104.0	104.8	106.5	106.8	108.8	110.8	114.7	117.4	122.4
75°	83.2	82.5	83.2	84.5	85.2	85.8	85.8	88.4	90.4	93.0	96.3
77.5°	64.1	64.8	64.7	64.8	64.9	66.1	66.0	67.2	69.1	70.4	72.1
80°	51.5	52.1	51.5	52.1	52.8	53.5	52.8	53.5	55.4	56.7	56.7
82.5°	39.9	40.0	40.4	40.6	40.6	40.8	41.7	41.8	43.3	43.0	43.6
85°	23.8	23.1	23.1	23.1	23.8	24.5	23.8	23.8	24.5	24.5	24.5
87.5°	11.8	12.2	12.2	12.1	12.1	12.0	11.9	12.2	11.5	12.0	11.2
90°	16.6	16.4	16.1	15.8	15.5	15.1	14.4	13.7	13.0	12.3	11.2
92.5°	16.6	16.4	16.3	16.1	16.0	15.7	15.3	15.0	14.6	14.3	13.8
95°	26.5	26.6	26.8	26.9	27.0	26.8	26.1	25.4	24.7	24.0	23.1
97.5°	35.4	35.2	35.0	34.9	34.7	34.4	33.8	33.2	32.7	32.1	30.0
100°	41.2	41.0	40.7	40.5	40.2	39.5	38.4	37.3	36.2	35.1	32.8
102.5°	44.3	43.8	43.5	43.0	42.7	41.8	40.4	38.9	37.5	36.1	55.5
105°	46.8	46.2	45.7	45.2	44.6	43.6	42.1	40.6	39.1	37.5	74.9
107.5°	48.1	47.6	47.1	46.5	46.0	46.5	48.0	49.5	51.1	52.6	97.4
110°	48.6	48.1	47.5	47.0	46.5	53.0	66.7	80.4	94.1	107.8	147.3



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	49.2	48.7	48.3	47.9	47.4	72.2	122.1	172.0	222.0	271.8	281.6
115°	50.5	60.4	70.2	80.1	89.9	126.6	189.9	253.3	316.7	380.0	376.6
117.5°	206.2	238.6	271.0	303.3	335.7	359.6	374.9	390.3	405.6	420.9	418.5
120°	375.7	394.2	412.7	431.1	449.6	458.1	456.4	454.8	453.1	451.4	449.0
122.5°	468.8	472.4	476.0	479.6	483.2	484.5	483.5	482.5	481.5	480.5	477.9
125°	526.6	526.2	525.8	525.4	525.0	524.3	523.3	522.4	521.4	520.5	517.8
127.5°	563.1	563.0	562.9	562.8	562.7	562.0	560.6	559.2	557.8	556.4	554.5
130°	585.7	585.8	586.0	586.2	586.3	585.6	584.1	582.6	581.1	579.5	578.1
132.5°	607.9	608.0	608.2	608.3	608.5	607.9	606.6	605.3	604.0	602.7	601.2
135°	639.9	640.2	640.5	640.8	641.0	640.5	639.1	637.7	636.4	635.0	633.8
137.5°	669.1	669.6	670.0	670.5	671.0	670.5	669.2	667.9	666.5	665.2	663.7
140°	687.3	688.0	688.7	689.4	690.1	689.8	688.5	687.3	686.1	684.9	683.4
142.5°	705.1	705.8	706.5	707.1	707.8	707.6	706.5	705.3	704.2	703.1	701.4
145°	729.9	730.6	731.2	731.9	732.5	732.5	731.5	730.6	729.6	728.6	726.3
147.5°	751.7	752.3	752.8	753.4	754.0	753.9	753.2	752.4	751.7	751.1	748.7
150°	764.9	765.6	766.3	767.0	767.7	767.6	766.8	765.9	765.2	764.3	762.2
152.5°	776.3	777.2	778.1	779.0	779.9	780.0	779.1	778.3	777.5	776.6	774.6
155°	792.0	793.2	794.3	795.3	796.4	796.6	795.7	795.0	794.1	793.2	791.6
157.5°	806.5	807.5	808.6	809.7	810.7	810.8	809.9	808.9	808.0	807.1	805.9
160°	814.9	815.8	816.7	817.7	818.6	818.7	817.9	817.1	816.3	815.5	814.6
162.5°	821.7	822.9	824.1	825.3	826.5	826.6	825.6	824.7	823.8	822.9	822.2
165°	832.1	833.0	834.0	835.0	835.9	835.9	835.0	834.0	833.0	832.1	831.6
167.5°	838.6	839.8	841.1	842.3	843.5	843.7	842.7	841.8	840.8	839.8	839.5
170°	842.6	843.8	845.0	846.3	847.5	847.7	846.6	845.7	844.7	843.8	843.5
172.5°	845.5	846.7	848.0	849.2	850.4	850.6	849.6	848.7	847.7	846.7	846.4
175°	848.1	849.5	850.8	852.2	853.6	853.8	852.8	851.9	850.9	850.0	849.6
177.5°	849.7	850.7	851.7	852.6	853.7	853.8	853.0	852.2	851.4	850.7	850.6
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1944.3	1940.0	1936.4	1926.8	1922.1	1911.5	1910.0	1909.4	1895.7	1882.5	1878.8
5°	2011.0	2000.4	1984.7	1966.2	1947.1	1927.3	1914.1	1903.5	1877.1	1852.0	1837.5
7.5°	2078.4	2055.6	2028.3	1993.4	1964.2	1931.5	1907.2	1885.4	1848.0	1812.1	1787.9
10°	2128.5	2091.5	2055.2	2007.1	1969.5	1932.5	1898.2	1868.5	1826.3	1778.8	1745.2
12.5°	2159.6	2119.0	2069.0	2021.9	1973.2	1926.2	1880.3	1842.1	1792.5	1743.4	1703.5
15°	2201.7	2158.2	2097.5	2030.2	1967.5	1906.2	1853.4	1805.9	1741.2	1682.5	1633.7
17.5°	2236.2	2176.3	2111.1	2033.3	1960.7	1882.7	1814.7	1754.0	1682.0	1611.2	1553.7
20°	2247.2	2187.9	2112.6	2034.8	1949.0	1857.3	1784.1	1718.1	1640.9	1563.7	1497.7
22.5°	2240.4	2194.2	2110.6	2017.4	1929.5	1833.6	1750.8	1674.3	1588.6	1509.8	1433.3
25°	2193.8	2178.0	2098.8	1997.2	1896.9	1785.4	1689.7	1605.9	1508.3	1423.8	1340.7
27.5°	2085.2	2119.4	2070.3	1962.0	1850.5	1731.0	1623.5	1528.1	1426.8	1331.7	1248.9
30°	1980.7	2059.2	2038.1	1937.8	1813.1	1695.7	1574.9	1475.3	1367.1	1269.5	1187.7
32.5°	1837.6	1967.4	1988.0	1904.0	1775.1	1646.1	1519.5	1420.4	1307.4	1204.5	1124.8
35°	1609.9	1803.9	1892.9	1839.5	1710.2	1571.0	1440.3	1324.8	1211.3	1109.7	1030.6
37.5°	1338.2	1602.4	1750.8	1754.6	1635.9	1491.2	1348.8	1234.2	1118.1	1018.3	932.7
40°	1161.9	1448.2	1641.6	1684.5	1584.2	1427.8	1283.9	1167.2	1053.7	956.1	857.7
42.5°	1003.6	1288.8	1526.5	1601.0	1521.4	1366.1	1221.7	1099.6	989.3	896.9	796.5
45°	811.6	1060.9	1322.8	1456.1	1412.0	1268.1	1115.7	999.6	896.0	816.1	719.8
47.5°	684.6	860.4	1113.9	1294.1	1293.3	1162.0	1012.1	900.9	804.8	730.0	652.0
50°	612.3	765.3	979.8	1184.3	1201.4	1091.3	948.7	838.6	748.9	670.4	607.7
52.5°	547.3	673.5	866.3	1062.4	1111.2	1015.8	877.5	775.8	688.7	616.5	562.8
55°	462.5	560.2	706.6	890.0	964.0	896.6	774.0	678.9	608.3	547.6	501.4
57.5°	391.2	464.5	582.0	729.7	815.8	773.4	672.2	595.0	534.6	479.7	443.2
60°	346.4	406.4	506.1	629.5	724.4	694.7	608.3	536.4	484.9	437.5	403.1
62.5°	304.2	355.8	441.2	541.3	628.4	616.1	545.5	485.2	440.1	396.8	367.7
65°	244.8	282.4	349.0	427.6	497.5	503.4	452.6	411.7	371.4	337.2	311.4
67.5°	194.9	219.5	266.4	332.5	385.0	403.6	372.6	341.4	309.4	282.9	260.6
70°	164.3	184.1	218.3	271.8	320.0	339.8	322.0	297.6	269.8	248.1	228.9
72.5°	133.1	152.4	177.7	217.0	258.2	279.7	273.5	255.9	233.4	215.3	197.3
75°	100.3	106.2	123.4	149.8	182.1	200.6	205.2	196.0	178.1	164.3	153.7
77.5°	74.1	77.7	85.9	99.8	120.9	137.3	144.1	143.0	130.8	122.7	112.8
80°	59.4	61.4	65.3	71.3	87.1	103.6	108.2	108.2	99.6	96.3	86.4
82.5°	45.1	46.6	49.0	52.3	59.7	74.0	79.2	80.2	74.8	70.4	62.7
85°	25.7	25.1	26.4	28.4	29.7	33.7	41.6	42.9	41.6	36.2	34.3
87.5°	11.0	11.3	11.1	10.3	10.5	10.8	13.1	15.4	13.6	12.3	11.6
90°	10.2	9.0	7.9	6.6	5.2	3.6	2.2	0.6	2.2	3.6	5.2
92.5°	13.2	12.7	12.1	11.9	12.1	12.1	12.3	12.4	12.3	12.1	12.1
95°	22.1	21.2	20.1	22.0	26.5	31.0	35.6	40.0	35.6	31.0	26.5
97.5°	27.7	25.5	23.2	28.5	41.2	54.0	66.7	79.5	66.7	54.0	41.2
100°	30.5	28.2	25.8	34.0	52.8	71.5	90.2	109.0	90.2	71.5	52.8
102.5°	75.0	94.5	113.9	125.6	129.7	133.6	137.6	141.5	137.6	133.6	129.7
105°	112.3	149.6	187.0	203.6	199.6	195.4	191.3	187.3	191.3	195.4	199.6
107.5°	142.2	187.0	231.9	252.6	249.3	246.0	242.6	239.4	242.6	246.0	249.3
110°	186.9	226.4	266.0	284.3	281.5	278.6	275.7	272.9	275.7	278.6	281.5





TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	291.4	301.2	310.9	314.5	312.0	309.4	306.9	304.4	306.9	309.4	312.0
115°	373.2	369.7	366.4	363.4	361.1	358.8	356.5	354.1	356.5	358.8	361.1
117.5°	416.2	413.9	411.5	409.0	406.4	403.8	401.2	398.6	401.2	403.8	406.4
120°	446.5	444.1	441.6	439.4	437.3	435.2	433.2	431.1	433.2	435.2	437.3
122.5°	475.2	472.5	469.8	467.4	465.2	463.0	460.9	458.7	460.9	463.0	465.2
125°	515.2	512.6	510.1	507.8	506.1	504.3	502.5	500.8	502.5	504.3	506.1
127.5°	552.5	550.6	548.6	546.6	544.7	542.8	540.8	538.8	540.8	542.8	544.7
130°	576.5	575.1	573.5	571.7	569.5	567.3	565.2	562.9	565.2	567.3	569.5
132.5°	599.7	598.2	596.7	595.0	593.1	591.3	589.4	587.5	589.4	591.3	593.1
135°	632.5	631.3	630.1	628.4	626.2	624.0	621.8	619.6	621.8	624.0	626.2
137.5°	662.4	661.0	659.6	658.1	656.6	655.0	653.5	652.0	653.5	655.0	656.6
140°	681.9	680.4	678.9	677.5	676.5	675.4	674.2	673.2	674.2	675.4	676.5
142.5°	699.6	697.9	696.2	694.8	693.9	692.9	691.9	691.0	691.9	692.9	693.9
145°	723.9	721.6	719.3	718.2	718.3	718.5	718.6	718.8	718.6	718.5	718.3
147.5°	746.4	744.2	741.8	741.0	741.5	742.0	742.5	743.0	742.5	742.0	741.5
150°	759.9	757.8	755.6	754.9	756.0	756.9	757.9	758.8	757.9	756.9	756.0
152.5°	772.5	770.4	768.4	767.8	768.9	770.0	771.0	772.1	771.0	770.0	768.9
155°	790.0	788.3	786.7	786.5	787.7	788.9	790.2	791.4	790.2	788.9	787.7
157.5°	804.8	803.7	802.5	802.5	803.5	804.5	805.6	806.6	805.6	804.5	803.5
160°	813.8	813.0	812.2	812.2	813.0	813.8	814.6	815.5	814.6	813.8	813.0
162.5°	821.4	820.7	820.0	820.0	820.9	821.7	822.5	823.4	822.5	821.7	820.9
165°	831.3	830.9	830.4	830.6	831.5	832.3	833.1	834.0	833.1	832.3	831.5
167.5°	839.0	838.7	838.3	838.5	839.4	840.2	841.0	841.8	841.0	840.2	839.4
170°	843.3	843.0	842.7	843.0	843.8	844.6	845.4	846.3	845.4	844.6	843.8
172.5°	846.2	845.9	845.7	845.9	846.7	847.6	848.3	849.2	848.3	847.6	846.7
175°	849.4	849.1	848.9	849.2	850.2	851.1	852.0	853.0	852.0	851.1	850.2
177.5°	850.5	850.3	850.2	850.6	851.4	852.1	852.9	853.7	852.9	852.1	851.4
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1872.0	1868.3	1861.4	1850.8	1844.5	1833.4	1826.0	1830.2	1831.3	1830.2	1829.2
5°	1821.7	1807.8	1788.7	1770.2	1753.1	1734.6	1724.1	1719.4	1710.2	1704.9	1702.3
7.5°	1760.8	1737.0	1709.9	1677.7	1650.4	1621.8	1607.1	1599.8	1581.0	1570.7	1561.7
10°	1715.5	1677.8	1650.8	1608.6	1582.9	1545.2	1519.5	1520.2	1494.4	1479.9	1469.4
12.5°	1665.3	1624.0	1579.0	1541.0	1505.3	1475.1	1444.0	1431.5	1404.2	1390.2	1361.7
15°	1582.2	1534.0	1486.5	1435.0	1398.8	1351.9	1307.1	1252.3	1208.1	1169.8	1159.3
17.5°	1491.4	1431.8	1384.1	1323.7	1261.5	1182.8	1130.8	1099.0	1072.3	1052.1	1037.1
20°	1429.1	1368.4	1317.6	1226.6	1142.7	1089.3	1051.0	1026.7	998.9	977.1	965.3
22.5°	1363.7	1300.3	1231.1	1129.5	1064.1	1021.2	987.1	959.1	940.3	923.3	912.5
25°	1270.7	1201.4	1087.4	1017.4	964.6	919.7	896.0	878.8	859.0	835.9	825.4
27.5°	1172.6	1062.4	980.4	928.4	878.0	848.9	827.5	801.9	784.2	773.8	762.8
30°	1099.2	989.0	925.1	868.3	832.7	800.3	775.2	760.8	743.6	725.7	718.5
32.5°	1017.4	929.4	868.1	820.8	784.6	757.1	737.3	713.8	701.4	690.4	675.2
35°	915.8	849.1	793.1	754.8	720.5	698.1	674.9	661.1	638.7	629.5	623.5
37.5°	829.7	772.0	730.1	689.7	662.5	637.7	623.6	601.6	591.9	579.0	566.5
40°	781.2	724.4	684.2	651.2	620.9	602.4	584.5	566.8	552.2	546.3	531.2
42.5°	731.6	685.4	645.1	609.0	588.7	569.1	546.6	533.5	518.5	508.9	499.5
45°	663.1	622.2	587.9	558.2	535.7	515.3	500.8	479.0	470.5	451.3	443.4
47.5°	603.0	564.9	532.2	503.9	482.1	468.7	447.5	430.4	416.7	405.0	394.9
50°	560.2	528.5	496.8	471.7	451.9	432.8	411.0	402.4	381.3	375.4	369.5
52.5°	521.1	491.0	462.0	437.5	417.7	399.1	379.9	368.7	354.5	348.5	344.1
55°	466.5	437.5	409.7	388.0	368.2	349.0	337.2	323.3	316.7	312.1	306.8
57.5°	411.6	385.5	364.2	342.2	322.3	307.0	293.3	285.0	278.2	272.1	265.8
60°	376.8	351.6	332.5	312.1	291.6	279.1	268.5	258.6	250.7	241.5	238.8
62.5°	339.8	317.9	300.3	280.4	262.6	251.2	241.1	231.7	222.2	208.8	205.1
65°	289.0	271.8	253.4	236.9	221.0	209.8	195.3	184.8	180.8	179.4	178.8
67.5°	243.1	226.9	211.0	194.1	179.7	169.3	162.0	160.3	157.6	156.8	154.9
70°	212.5	197.3	181.4	165.6	151.8	149.8	147.1	144.5	141.2	139.9	138.5
72.5°	185.0	169.3	153.4	140.8	134.8	132.3	129.8	127.1	124.8	123.6	122.7
75°	141.9	127.3	116.8	112.2	108.8	106.9	102.9	100.9	99.6	97.6	96.9
77.5°	102.1	93.9	89.1	86.2	82.7	80.6	78.4	76.4	75.0	74.6	73.5
80°	77.8	73.9	70.6	66.6	65.3	62.7	62.0	60.0	60.7	58.7	58.7
82.5°	60.4	55.4	52.7	50.8	49.5	47.4	46.8	45.8	45.9	44.4	44.4
85°	31.0	29.7	28.4	27.0	27.0	25.1	25.7	25.1	25.1	23.8	23.1
87.5°	11.4	11.1	10.2	10.5	10.7	10.4	10.5	10.2	10.2	10.4	10.0
90°	6.6	7.9	9.0	10.2	11.2	12.3	13.0	13.7	14.4	15.1	15.5
92.5°	11.9	12.1	12.7	13.2	13.8	14.3	14.6	15.0	15.3	15.7	16.0
95°	22.0	20.1	21.2	22.1	23.1	24.0	24.7	25.4	26.1	26.8	27.0
97.5°	28.5	23.2	25.5	27.7	30.0	32.1	32.7	33.2	33.8	34.4	34.7
100°	34.0	25.8	28.2	30.5	32.8	35.1	36.2	37.3	38.4	39.5	40.2
102.5°	125.6	113.9	94.5	75.0	55.5	36.1	37.5	38.9	40.4	41.8	42.7
105°	203.6	187.0	149.6	112.3	74.9	37.5	39.1	40.6	42.1	43.6	44.6
107.5°	252.6	231.9	187.0	142.2	97.4	52.6	51.1	49.5	48.0	46.5	46.0
110°	284.3	266.0	226.4	186.9	147.3	107.8	94.1	80.4	66.7	53.0	46.5



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	314.5	310.9	301.2	291.4	281.6	271.8	222.0	172.0	122.1	72.2	47.4
115°	363.4	366.4	369.7	373.2	376.6	380.0	316.7	253.3	189.9	126.6	89.9
117.5°	409.0	411.5	413.9	416.2	418.5	420.9	405.6	390.3	374.9	359.6	335.7
120°	439.4	441.6	444.1	446.5	449.0	451.4	453.1	454.8	456.4	458.1	449.6
122.5°	467.4	469.8	472.5	475.2	477.9	480.5	481.5	482.5	483.5	484.5	483.2
125°	507.8	510.1	512.6	515.2	517.8	520.5	521.4	522.4	523.3	524.3	525.0
127.5°	546.6	548.6	550.6	552.5	554.5	556.4	557.8	559.2	560.6	562.0	562.7
130°	571.7	573.5	575.1	576.5	578.1	579.5	581.1	582.6	584.1	585.6	586.3
132.5°	595.0	596.7	598.2	599.7	601.2	602.7	604.0	605.3	606.6	607.9	608.5
135°	628.4	630.1	631.3	632.5	633.8	635.0	636.4	637.7	639.1	640.5	641.0
137.5°	658.1	659.6	661.0	662.4	663.7	665.2	666.5	667.9	669.2	670.5	671.0
140°	677.5	678.9	680.4	681.9	683.4	684.9	686.1	687.3	688.5	689.8	690.1
142.5°	694.8	696.2	697.9	699.6	701.4	703.1	704.2	705.3	706.5	707.6	707.8
145°	718.2	719.3	721.6	723.9	726.3	728.6	729.6	730.6	731.5	732.5	732.5
147.5°	741.0	741.8	744.2	746.4	748.7	751.1	751.7	752.4	753.2	753.9	754.0
150°	754.9	755.6	757.8	759.9	762.2	764.3	765.2	765.9	766.8	767.6	767.7
152.5°	767.8	768.4	770.4	772.5	774.6	776.6	777.5	778.3	779.1	780.0	779.9
155°	786.5	786.7	788.3	790.0	791.6	793.2	794.1	795.0	795.7	796.6	796.4
157.5°	802.5	802.5	803.7	804.8	805.9	807.1	808.0	808.9	809.9	810.8	810.7
160°	812.2	812.2	813.0	813.8	814.6	815.5	816.3	817.1	817.9	818.7	818.6
162.5°	820.0	820.0	820.7	821.4	822.2	822.9	823.8	824.7	825.6	826.6	826.5
165°	830.6	830.4	830.9	831.3	831.6	832.1	833.0	834.0	835.0	835.9	835.9
167.5°	838.5	838.3	838.7	839.0	839.5	839.8	840.8	841.8	842.7	843.7	843.5
170°	843.0	842.7	843.0	843.3	843.5	843.8	844.7	845.7	846.6	847.7	847.5
172.5°	845.9	845.7	845.9	846.2	846.4	846.7	847.7	848.7	849.6	850.6	850.4
175°	849.2	848.9	849.1	849.4	849.6	850.0	850.9	851.9	852.8	853.8	853.6
177.5°	850.6	850.2	850.3	850.5	850.6	850.7	851.4	852.2	853.0	853.8	853.7
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1823.4	1824.5	1822.9	1823.9	1822.9	1824.5	1823.4	1829.2	1830.2	1831.3	1830.2
5°	1698.9	1691.0	1689.7	1687.7	1689.7	1691.0	1698.9	1702.3	1704.9	1710.2	1719.4
7.5°	1550.4	1549.2	1545.9	1541.3	1545.9	1549.2	1550.4	1561.7	1570.7	1581.0	1599.8
10°	1454.8	1451.6	1450.9	1446.2	1450.9	1451.6	1454.8	1469.4	1479.9	1494.4	1520.2
12.5°	1342.9	1321.7	1319.5	1307.9	1319.5	1321.7	1342.9	1361.7	1390.2	1404.2	1431.5
15°	1143.4	1139.4	1126.3	1117.7	1126.3	1139.4	1143.4	1159.3	1169.8	1208.1	1252.3
17.5°	1029.4	1016.5	1012.4	1010.6	1012.4	1016.5	1029.4	1037.1	1052.1	1072.3	1099.0
20°	956.1	944.2	942.2	940.9	942.2	944.2	956.1	965.3	977.1	998.9	1026.7
22.5°	905.3	892.9	887.8	883.8	887.8	892.9	905.3	912.5	923.3	940.3	959.1
25°	818.8	814.2	811.6	810.2	811.6	814.2	818.8	825.4	835.9	859.0	878.8
27.5°	751.1	741.0	739.0	735.6	739.0	741.0	751.1	762.8	773.8	784.2	801.9
30°	712.6	709.3	704.6	700.7	704.6	709.3	712.6	718.5	725.7	743.6	760.8
32.5°	667.2	664.4	660.3	658.5	660.3	664.4	667.2	675.2	690.4	701.4	713.8
35°	616.9	607.7	603.7	597.8	603.7	607.7	616.9	623.5	629.5	638.7	661.1
37.5°	563.7	558.9	553.3	555.3	553.3	558.9	563.7	566.5	579.0	591.9	601.6
40°	522.5	519.3	518.0	517.3	518.0	519.3	522.5	531.2	546.3	552.2	566.8
42.5°	489.8	480.7	477.3	477.2	477.3	480.7	489.8	499.5	508.9	518.5	533.5
45°	440.1	431.5	425.6	426.2	425.6	431.5	440.1	443.4	451.3	470.5	479.0
47.5°	389.2	388.9	385.2	386.3	385.2	388.9	389.2	394.9	405.0	416.7	430.4
50°	364.9	360.9	358.3	359.0	358.3	360.9	364.9	369.5	375.4	381.3	402.4
52.5°	341.6	338.2	336.1	338.9	336.1	338.2	341.6	344.1	348.5	354.5	368.7
55°	303.5	299.5	298.9	298.3	298.9	299.5	303.5	306.8	312.1	316.7	323.3
57.5°	260.9	258.2	254.3	252.5	254.3	258.2	260.9	265.8	272.1	278.2	285.0
60°	230.2	225.0	218.3	217.7	218.3	225.0	230.2	238.8	241.5	250.7	258.6
62.5°	202.2	201.2	199.9	199.8	199.9	201.2	202.2	205.1	208.8	222.2	231.7
65°	177.5	176.8	177.5	178.1	177.5	176.8	177.5	178.8	179.4	180.8	184.8
67.5°	154.6	153.4	152.3	152.8	152.3	153.4	154.6	154.9	156.8	157.6	160.3
70°	137.2	136.6	136.0	136.0	136.0	136.6	137.2	138.5	139.9	141.2	144.5
72.5°	120.4	120.2	119.6	119.0	119.6	120.2	120.4	122.7	123.6	124.8	127.1
75°	96.3	95.0	95.0	95.0	95.0	95.0	96.3	96.9	97.6	99.6	100.9
77.5°	73.4	72.7	72.1	71.5	72.1	72.7	73.4	73.5	74.6	75.0	76.4
80°	58.0	57.4	56.7	56.7	56.7	57.4	58.0	58.7	58.7	60.7	60.0
82.5°	44.3	43.7	43.6	43.0	43.6	43.7	44.3	44.4	44.4	45.9	45.8
85°	23.8	24.5	23.8	25.1	23.8	24.5	23.8	23.1	23.8	25.1	25.1
87.5°	10.0	9.6	10.2	9.6	10.2	9.6	10.0	10.0	10.4	10.2	10.2
90°	15.8	16.1	16.4	16.6	16.4	16.1	15.8	15.5	15.1	14.4	13.7
92.5°	16.1	16.3	16.4	16.6	16.4	16.3	16.1	16.0	15.7	15.3	15.0
95°	26.9	26.8	26.6	26.5	26.6	26.8	26.9	27.0	26.8	26.1	25.4
97.5°	34.9	35.0	35.2	35.4	35.2	35.0	34.9	34.7	34.4	33.8	33.2
100°	40.5	40.7	41.0	41.2	41.0	40.7	40.5	40.2	39.5	38.4	37.3
102.5°	43.0	43.5	43.8	44.3	43.8	43.5	43.0	42.7	41.8	40.4	38.9
105°	45.2	45.7	46.2	46.8	46.2	45.7	45.2	44.6	43.6	42.1	40.6
107.5°	46.5	47.1	47.6	48.1	47.6	47.1	46.5	46.0	46.5	48.0	49.5
110°	47.0	47.5	48.1	48.6	48.1	47.5	47.0	46.5	53.0	66.7	80.4



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	47.9	48.3	48.7	49.2	48.7	48.3	47.9	47.4	72.2	122.1	172.0
115°	80.1	70.2	60.4	50.5	60.4	70.2	80.1	89.9	126.6	189.9	253.3
117.5°	303.3	271.0	238.6	206.2	238.6	271.0	303.3	335.7	359.6	374.9	390.3
120°	431.1	412.7	394.2	375.7	394.2	412.7	431.1	449.6	458.1	456.4	454.8
122.5°	479.6	476.0	472.4	468.8	472.4	476.0	479.6	483.2	484.5	483.5	482.5
125°	525.4	525.8	526.2	526.6	526.2	525.8	525.4	525.0	524.3	523.3	522.4
127.5°	562.8	562.9	563.0	563.1	563.0	562.9	562.8	562.7	562.0	560.6	559.2
130°	586.2	586.0	585.8	585.7	585.8	586.0	586.2	586.3	585.6	584.1	582.6
132.5°	608.3	608.2	608.0	607.9	608.0	608.2	608.3	608.5	607.9	606.6	605.3
135°	640.8	640.5	640.2	639.9	640.2	640.5	640.8	641.0	640.5	639.1	637.7
137.5°	670.5	670.0	669.6	669.1	669.6	670.0	670.5	671.0	670.5	669.2	667.9
140°	689.4	688.7	688.0	687.3	688.0	688.7	689.4	690.1	689.8	688.5	687.3
142.5°	707.1	706.5	705.8	705.1	705.8	706.5	707.1	707.8	707.6	706.5	705.3
145°	731.9	731.2	730.6	729.9	730.6	731.2	731.9	732.5	732.5	731.5	730.6
147.5°	753.4	752.8	752.3	751.7	752.3	752.8	753.4	754.0	753.9	753.2	752.4
150°	767.0	766.3	765.6	764.9	765.6	766.3	767.0	767.7	767.6	766.8	765.9
152.5°	779.0	778.1	777.2	776.3	777.2	778.1	779.0	779.9	780.0	779.1	778.3
155°	795.3	794.3	793.2	792.0	793.2	794.3	795.3	796.4	796.6	795.7	795.0
157.5°	809.7	808.6	807.5	806.5	807.5	808.6	809.7	810.7	810.8	809.9	808.9
160°	817.7	816.7	815.8	814.9	815.8	816.7	817.7	818.6	818.7	817.9	817.1
162.5°	825.3	824.1	822.9	821.7	822.9	824.1	825.3	826.5	826.6	825.6	824.7
165°	835.0	834.0	833.0	832.1	833.0	834.0	835.0	835.9	835.9	835.0	834.0
167.5°	842.3	841.1	839.8	838.6	839.8	841.1	842.3	843.5	843.7	842.7	841.8
170°	846.3	845.0	843.8	842.6	843.8	845.0	846.3	847.5	847.7	846.6	845.7
172.5°	849.2	848.0	846.7	845.5	846.7	848.0	849.2	850.4	850.6	849.6	848.7
175°	852.2	850.8	849.5	848.1	849.5	850.8	852.2	853.6	853.8	852.8	851.9
177.5°	852.6	851.7	850.7	849.7	850.7	851.7	852.6	853.7	853.8	853.0	852.2
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1826.0	1833.4	1844.5	1850.8	1861.4	1868.3	1872.0	1878.8	1882.5	1895.7	1909.4
5°	1724.1	1734.6	1753.1	1770.2	1788.7	1807.8	1821.7	1837.5	1852.0	1877.1	1903.5
7.5°	1607.1	1621.8	1650.4	1677.7	1709.9	1737.0	1760.8	1787.9	1812.1	1848.0	1885.4
10°	1519.5	1545.2	1582.9	1608.6	1650.8	1677.8	1715.5	1745.2	1778.8	1826.3	1868.5
12.5°	1444.0	1475.1	1505.3	1541.0	1579.0	1624.0	1665.3	1703.5	1743.4	1792.5	1842.1
15°	1307.1	1351.9	1398.8	1435.0	1486.5	1534.0	1582.2	1633.7	1682.5	1741.2	1805.9
17.5°	1130.8	1182.8	1261.5	1323.7	1384.1	1431.8	1491.4	1553.7	1611.2	1682.0	1754.0
20°	1051.0	1089.3	1142.7	1226.6	1317.6	1368.4	1429.1	1497.7	1563.7	1640.9	1718.1
22.5°	987.1	1021.2	1064.1	1129.5	1231.1	1300.3	1363.7	1433.3	1509.8	1588.6	1674.3
25°	896.0	919.7	964.6	1017.4	1087.4	1201.4	1270.7	1340.7	1423.8	1508.3	1605.9
27.5°	827.5	848.9	878.0	928.4	980.4	1062.4	1172.6	1248.9	1331.7	1426.8	1528.1
30°	775.2	800.3	832.7	868.3	925.1	989.0	1099.2	1187.7	1269.5	1367.1	1475.3
32.5°	737.3	757.1	784.6	820.8	868.1	929.4	1017.4	1124.8	1204.5	1307.4	1420.4
35°	674.9	698.1	720.5	754.8	793.1	849.1	915.8	1030.6	1109.7	1211.3	1324.8
37.5°	623.6	637.7	662.5	689.7	730.1	772.0	829.7	932.7	1018.3	1118.1	1234.2
40°	584.5	602.4	620.9	651.2	684.2	724.4	781.2	857.7	956.1	1053.7	1167.2
42.5°	546.6	569.1	588.7	609.0	645.1	685.4	731.6	796.5	896.9	989.3	1099.6
45°	500.8	515.3	535.7	558.2	587.9	622.2	663.1	719.8	816.1	896.0	999.6
47.5°	447.5	468.7	482.1	503.9	532.2	564.9	603.0	652.0	730.0	804.8	900.9
50°	411.0	432.8	451.9	471.7	496.8	528.5	560.2	607.7	670.4	748.9	838.6
52.5°	379.9	399.1	417.7	437.5	462.0	491.0	521.1	562.8	616.5	688.7	775.8
55°	337.2	349.0	368.2	388.0	409.7	437.5	466.5	501.4	547.6	608.3	678.9
57.5°	293.3	307.0	322.3	342.2	364.2	385.5	411.6	443.2	479.7	534.6	595.0
60°	268.5	279.1	291.6	312.1	332.5	351.6	376.8	403.1	437.5	484.9	536.4
62.5°	241.1	251.2	262.6	280.4	300.3	317.9	339.8	367.7	396.8	440.1	485.2
65°	195.3	209.8	221.0	236.9	253.4	271.8	289.0	311.4	337.2	371.4	411.7
67.5°	162.0	169.3	179.7	194.1	211.0	226.9	243.1	260.6	282.9	309.4	341.4
70°	147.1	149.8	151.8	165.6	181.4	197.3	212.5	228.9	248.1	269.8	297.6
72.5°	129.8	132.3	134.8	140.8	153.4	169.3	185.0	197.3	215.3	233.4	255.9
75°	102.9	106.9	108.8	112.2	116.8	127.3	141.9	153.7	164.3	178.1	196.0
77.5°	78.4	80.6	82.7	86.2	89.1	93.9	102.1	112.8	122.7	130.8	143.0
80°	62.0	62.7	65.3	66.6	70.6	73.9	77.8	86.4	96.3	99.6	108.2
82.5°	46.8	47.4	49.5	50.8	52.7	55.4	60.4	62.7	70.4	74.8	80.2
85°	25.7	25.1	27.0	27.0	28.4	29.7	31.0	34.3	36.2	41.6	42.9
87.5°	10.5	10.4	10.7	10.5	10.2	11.1	11.4	11.6	12.3	13.6	15.4
90°	13.0	12.3	11.2	10.2	9.0	7.9	6.6	5.2	3.6	2.2	0.6
92.5°	14.6	14.3	13.8	13.2	12.7	12.1	11.9	12.1	12.1	12.3	12.4
95°	24.7	24.0	23.1	22.1	21.2	20.1	22.0	26.5	31.0	35.6	40.0
97.5°	32.7	32.1	30.0	27.7	25.5	23.2	28.5	41.2	54.0	66.7	79.5
100°	36.2	35.1	32.8	30.5	28.2	25.8	34.0	52.8	71.5	90.2	109.0
102.5°	37.5	36.1	55.5	75.0	94.5	113.9	125.6	129.7	133.6	137.6	141.5
105°	39.1	37.5	74.9	112.3	149.6	187.0	203.6	199.6	195.4	191.3	187.3
107.5°	51.1	52.6	97.4	142.2	187.0	231.9	252.6	249.3	246.0	242.6	239.4
110°	94.1	107.8	147.3	186.9	226.4	266.0	284.3	281.5	278.6	275.7	272.9



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	222.0	271.8	281.6	291.4	301.2	310.9	314.5	312.0	309.4	306.9	304.4
115°	316.7	380.0	376.6	373.2	369.7	366.4	363.4	361.1	358.8	356.5	354.1
117.5°	405.6	420.9	418.5	416.2	413.9	411.5	409.0	406.4	403.8	401.2	398.6
120°	453.1	451.4	449.0	446.5	444.1	441.6	439.4	437.3	435.2	433.2	431.1
122.5°	481.5	480.5	477.9	475.2	472.5	469.8	467.4	465.2	463.0	460.9	458.7
125°	521.4	520.5	517.8	515.2	512.6	510.1	507.8	506.1	504.3	502.5	500.8
127.5°	557.8	556.4	554.5	552.5	550.6	548.6	546.6	544.7	542.8	540.8	538.8
130°	581.1	579.5	578.1	576.5	575.1	573.5	571.7	569.5	567.3	565.2	562.9
132.5°	604.0	602.7	601.2	599.7	598.2	596.7	595.0	593.1	591.3	589.4	587.5
135°	636.4	635.0	633.8	632.5	631.3	630.1	628.4	626.2	624.0	621.8	619.6
137.5°	666.5	665.2	663.7	662.4	661.0	659.6	658.1	656.6	655.0	653.5	652.0
140°	686.1	684.9	683.4	681.9	680.4	678.9	677.5	676.5	675.4	674.2	673.2
142.5°	704.2	703.1	701.4	699.6	697.9	696.2	694.8	693.9	692.9	691.9	691.0
145°	729.6	728.6	726.3	723.9	721.6	719.3	718.2	718.3	718.5	718.6	718.8
147.5°	751.7	751.1	748.7	746.4	744.2	741.8	741.0	741.5	742.0	742.5	743.0
150°	765.2	764.3	762.2	759.9	757.8	755.6	754.9	756.0	756.9	757.9	758.8
152.5°	777.5	776.6	774.6	772.5	770.4	768.4	767.8	768.9	770.0	771.0	772.1
155°	794.1	793.2	791.6	790.0	788.3	786.7	786.5	787.7	788.9	790.2	791.4
157.5°	808.0	807.1	805.9	804.8	803.7	802.5	802.5	803.5	804.5	805.6	806.6
160°	816.3	815.5	814.6	813.8	813.0	812.2	812.2	813.0	813.8	814.6	815.5
162.5°	823.8	822.9	822.2	821.4	820.7	820.0	820.0	820.9	821.7	822.5	823.4
165°	833.0	832.1	831.6	831.3	830.9	830.4	830.6	831.5	832.3	833.1	834.0
167.5°	840.8	839.8	839.5	839.0	838.7	838.3	838.5	839.4	840.2	841.0	841.8
170°	844.7	843.8	843.5	843.3	843.0	842.7	843.0	843.8	844.6	845.4	846.3
172.5°	847.7	846.7	846.4	846.2	845.9	845.7	845.9	846.7	847.6	848.3	849.2
175°	850.9	850.0	849.6	849.4	849.1	848.9	849.2	850.2	851.1	852.0	853.0
177.5°	851.4	850.7	850.6	850.5	850.3	850.2	850.6	851.4	852.1	852.9	853.7
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1910.0	1911.5	1922.1	1926.8	1936.4	1940.0	1944.3	1943.2	1943.2	1945.3	1960.1
5°	1914.1	1927.3	1947.1	1966.2	1984.7	2000.4	2011.0	2021.6	2025.6	2044.7	2061.8
7.5°	1907.2	1931.5	1964.2	1993.4	2028.3	2055.6	2078.4	2098.8	2112.8	2140.6	2169.1
10°	1898.2	1932.5	1969.5	2007.1	2055.2	2091.5	2128.5	2156.9	2166.1	2207.7	2231.5
12.5°	1880.3	1926.2	1973.2	2021.9	2069.0	2119.0	2159.6	2188.0	2220.4	2257.8	2301.6
15°	1853.4	1906.2	1967.5	2030.2	2097.5	2158.2	2201.7	2251.2	2286.8	2327.7	2366.0
17.5°	1814.7	1882.7	1960.7	2033.3	2111.1	2176.3	2236.2	2283.6	2308.8	2332.1	2337.8
20°	1784.1	1857.3	1949.0	2034.8	2112.6	2187.9	2247.2	2286.8	2293.4	2294.0	2259.1
22.5°	1750.8	1833.6	1929.5	2017.4	2110.6	2194.2	2240.4	2257.3	2231.1	2186.4	2118.7
25°	1689.7	1785.4	1896.9	1997.2	2098.8	2178.0	2193.8	2164.1	2072.4	1976.1	1854.0
27.5°	1623.5	1731.0	1850.5	1962.0	2070.3	2119.4	2085.2	1978.1	1813.0	1669.4	1495.4
30°	1574.9	1695.7	1813.1	1937.8	2038.1	2059.2	1980.7	1823.0	1630.3	1413.9	1240.4
32.5°	1519.5	1646.1	1775.1	1904.0	1988.0	1967.4	1837.6	1643.6	1417.6	1204.9	1040.9
35°	1440.3	1571.0	1710.2	1839.5	1892.9	1803.9	1609.9	1357.2	1126.3	927.6	814.9
37.5°	1348.8	1491.2	1635.9	1754.6	1750.8	1602.4	1338.2	1077.3	883.2	765.8	685.4
40°	1283.9	1427.8	1584.2	1684.5	1641.6	1448.2	1161.9	915.8	774.0	680.3	621.6
42.5°	1221.7	1366.1	1521.4	1601.0	1526.5	1288.8	1003.6	810.7	693.7	620.6	573.0
45°	1115.7	1268.1	1412.0	1456.1	1322.8	1060.9	811.6	671.7	593.8	539.7	506.7
47.5°	1012.1	1162.0	1293.3	1294.1	1113.9	860.4	684.6	581.3	514.8	472.9	448.9
50°	948.7	1091.3	1201.4	1184.3	979.8	765.3	612.3	523.2	467.8	435.5	410.4
52.5°	877.5	1015.8	1111.2	1062.4	866.3	673.5	547.3	472.5	426.6	398.5	376.1
55°	774.0	896.6	964.0	890.0	706.6	560.2	462.5	403.8	369.5	345.7	326.6
57.5°	672.2	773.4	815.8	729.7	582.0	464.5	391.2	347.2	313.1	296.1	286.2
60°	608.3	694.7	724.4	629.5	506.1	406.4	346.4	305.5	280.4	269.2	259.3
62.5°	545.5	616.1	628.4	541.3	441.2	355.8	304.2	269.6	253.0	242.3	232.9
65°	452.6	503.4	497.5	427.6	349.0	282.4	244.8	223.7	211.1	196.0	179.4
67.5°	372.6	403.6	385.0	332.5	266.4	219.5	194.9	178.9	163.3	149.0	145.2
70°	322.0	339.8	320.0	271.8	218.3	184.1	164.3	145.2	136.0	132.6	126.7
72.5°	273.5	279.7	258.2	217.0	177.7	152.4	133.1	122.4	117.4	114.7	110.8
75°	205.2	200.6	182.1	149.8	123.4	106.2	100.3	96.3	93.0	90.4	88.4
77.5°	144.1	137.3	120.9	99.8	85.9	77.7	74.1	72.1	70.4	69.1	67.2
80°	108.2	103.6	87.1	71.3	65.3	61.4	59.4	56.7	56.7	55.4	53.5
82.5°	79.2	74.0	59.7	52.3	49.0	46.6	45.1	43.6	43.0	43.3	41.8
85°	41.6	33.7	29.7	28.4	26.4	25.1	25.7	24.5	24.5	24.5	23.8
87.5°	13.1	10.8	10.5	10.3	11.1	11.3	11.0	11.2	12.0	11.5	12.2
90°	2.2	3.6	5.2	6.6	7.9	9.0	10.2	11.2	12.3	13.0	13.7
92.5°	12.3	12.1	12.1	11.9	12.1	12.7	13.2	13.8	14.3	14.6	15.0
95°	35.6	31.0	26.5	22.0	20.1	21.2	22.1	23.1	24.0	24.7	25.4
97.5°	66.7	54.0	41.2	28.5	23.2	25.5	27.7	30.0	32.1	32.7	33.2
100°	90.2	71.5	52.8	34.0	25.8	28.2	30.5	32.8	35.1	36.2	37.3
102.5°	137.6	133.6	129.7	125.6	113.9	94.5	75.0	55.5	36.1	37.5	38.9
105°	191.3	195.4	199.6	203.6	187.0	149.6	112.3	74.9	37.5	39.1	40.6
107.5°	242.6	246.0	249.3	252.6	231.9	187.0	142.2	97.4	52.6	51.1	49.5
110°	275.7	278.6	281.5	284.3	266.0	226.4	186.9	147.3	107.8	94.1	80.4





TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	306.9	309.4	312.0	314.5	310.9	301.2	291.4	281.6	271.8	222.0	172.0
115°	356.5	358.8	361.1	363.4	366.4	369.7	373.2	376.6	380.0	316.7	253.3
117.5°	401.2	403.8	406.4	409.0	411.5	413.9	416.2	418.5	420.9	405.6	390.3
120°	433.2	435.2	437.3	439.4	441.6	444.1	446.5	449.0	451.4	453.1	454.8
122.5°	460.9	463.0	465.2	467.4	469.8	472.5	475.2	477.9	480.5	481.5	482.5
125°	502.5	504.3	506.1	507.8	510.1	512.6	515.2	517.8	520.5	521.4	522.4
127.5°	540.8	542.8	544.7	546.6	548.6	550.6	552.5	554.5	556.4	557.8	559.2
130°	565.2	567.3	569.5	571.7	573.5	575.1	576.5	578.1	579.5	581.1	582.6
132.5°	589.4	591.3	593.1	595.0	596.7	598.2	599.7	601.2	602.7	604.0	605.3
135°	621.8	624.0	626.2	628.4	630.1	631.3	632.5	633.8	635.0	636.4	637.7
137.5°	653.5	655.0	656.6	658.1	659.6	661.0	662.4	663.7	665.2	666.5	667.9
140°	674.2	675.4	676.5	677.5	678.9	680.4	681.9	683.4	684.9	686.1	687.3
142.5°	691.9	692.9	693.9	694.8	696.2	697.9	699.6	701.4	703.1	704.2	705.3
145°	718.6	718.5	718.3	718.2	719.3	721.6	723.9	726.3	728.6	729.6	730.6
147.5°	742.5	742.0	741.5	741.0	741.8	744.2	746.4	748.7	751.1	751.7	752.4
150°	757.9	756.9	756.0	754.9	755.6	757.8	759.9	762.2	764.3	765.2	765.9
152.5°	771.0	770.0	768.9	767.8	768.4	770.4	772.5	774.6	776.6	777.5	778.3
155°	790.2	788.9	787.7	786.5	786.7	788.3	790.0	791.6	793.2	794.1	795.0
157.5°	805.6	804.5	803.5	802.5	802.5	803.7	804.8	805.9	807.1	808.0	808.9
160°	814.6	813.8	813.0	812.2	812.2	813.0	813.8	814.6	815.5	816.3	817.1
162.5°	822.5	821.7	820.9	820.0	820.0	820.7	821.4	822.2	822.9	823.8	824.7
165°	833.1	832.3	831.5	830.6	830.4	830.9	831.3	831.6	832.1	833.0	834.0
167.5°	841.0	840.2	839.4	838.5	838.3	838.7	839.0	839.5	839.8	840.8	841.8
170°	845.4	844.6	843.8	843.0	842.7	843.0	843.3	843.5	843.8	844.7	845.7
172.5°	848.3	847.6	846.7	845.9	845.7	845.9	846.2	846.4	846.7	847.7	848.7
175°	852.0	851.1	850.2	849.2	848.9	849.1	849.4	849.6	850.0	850.9	851.9
177.5°	852.9	852.1	851.4	850.6	850.2	850.3	850.5	850.6	850.7	851.4	852.2
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1965.4	1972.2	1975.4	1975.4	1979.1	1977.5	1975.9
5°	2078.4	2090.9	2093.5	2105.4	2113.9	2111.3	2112.6
7.5°	2190.6	2210.8	2230.8	2239.9	2241.3	2246.6	2248.6
10°	2259.8	2276.3	2307.3	2302.7	2325.7	2339.0	2317.2
12.5°	2326.2	2348.5	2370.1	2376.0	2389.1	2393.3	2384.7
15°	2386.4	2398.3	2399.7	2396.3	2400.3	2397.0	2384.5
17.5°	2330.2	2311.0	2271.9	2253.4	2238.8	2217.2	2208.5
20°	2237.3	2180.6	2114.6	2088.3	2057.2	1996.5	2011.0
22.5°	2036.8	1972.1	1906.2	1829.1	1792.3	1734.7	1731.3
25°	1724.7	1613.2	1490.5	1404.7	1354.5	1297.2	1272.0
27.5°	1340.9	1200.6	1100.0	1049.0	1002.7	957.3	955.4
30°	1088.6	983.1	905.3	861.7	833.3	814.2	818.1
32.5°	917.7	845.3	792.8	756.6	735.6	721.3	721.0
35°	750.2	700.7	667.0	651.9	636.7	626.1	626.8
37.5°	642.0	612.3	593.6	576.8	567.3	562.1	559.2
40°	586.5	562.1	547.6	537.7	529.8	522.5	521.2
42.5°	542.8	522.5	508.1	500.2	492.8	487.8	486.4
45°	481.6	465.1	451.9	443.4	440.1	435.5	435.5
47.5°	428.4	412.2	401.9	396.6	390.9	387.8	387.7
50°	392.6	380.0	370.8	367.5	362.9	360.9	360.2
52.5°	360.4	351.0	344.4	342.2	340.2	337.7	338.1
55°	316.7	311.4	308.8	306.8	303.5	299.5	302.2
57.5°	279.9	275.4	268.3	262.1	259.1	256.2	257.4
60°	254.0	244.8	235.6	228.3	226.3	220.3	220.3
62.5°	221.3	208.4	197.0	193.0	191.0	188.2	187.6
65°	170.2	165.0	162.3	159.6	158.3	158.3	157.0
67.5°	141.0	139.0	136.0	135.3	134.1	133.7	133.3
70°	124.7	122.1	120.7	120.1	118.7	119.4	117.4
72.5°	108.8	106.8	106.5	104.8	104.0	104.1	102.6
75°	85.8	85.8	85.2	84.5	83.2	82.5	83.2
77.5°	66.0	66.1	64.9	64.8	64.7	64.8	64.1
80°	52.8	53.5	52.8	52.1	51.5	52.1	51.5
82.5°	41.7	40.8	40.6	40.6	40.4	40.0	39.9
85°	23.8	24.5	23.8	23.1	23.1	23.1	23.8
87.5°	11.9	12.0	12.1	12.1	12.2	12.2	11.8
90°	14.4	15.1	15.5	15.8	16.1	16.4	16.6
92.5°	15.3	15.7	16.0	16.1	16.3	16.4	16.6
95°	26.1	26.8	27.0	26.9	26.8	26.6	26.5
97.5°	33.8	34.4	34.7	34.9	35.0	35.2	35.4
100°	38.4	39.5	40.2	40.5	40.7	41.0	41.2
102.5°	40.4	41.8	42.7	43.0	43.5	43.8	44.3
105°	42.1	43.6	44.6	45.2	45.7	46.2	46.8
107.5°	48.0	46.5	46.0	46.5	47.1	47.6	48.1
110°	66.7	53.0	46.5	47.0	47.5	48.1	48.6



TEST NUMBER: P331747-935

CATALOG NUMBER: S122RDIP-S1005D725U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	122.1	72.2	47.4	47.9	48.3	48.7	49.2
115°	189.9	126.6	89.9	80.1	70.2	60.4	50.5
117.5°	374.9	359.6	335.7	303.3	271.0	238.6	206.2
120°	456.4	458.1	449.6	431.1	412.7	394.2	375.7
122.5°	483.5	484.5	483.2	479.6	476.0	472.4	468.8
125°	523.3	524.3	525.0	525.4	525.8	526.2	526.6
127.5°	560.6	562.0	562.7	562.8	562.9	563.0	563.1
130°	584.1	585.6	586.3	586.2	586.0	585.8	585.7
132.5°	606.6	607.9	608.5	608.3	608.2	608.0	607.9
135°	639.1	640.5	641.0	640.8	640.5	640.2	639.9
137.5°	669.2	670.5	671.0	670.5	670.0	669.6	669.1
140°	688.5	689.8	690.1	689.4	688.7	688.0	687.3
142.5°	706.5	707.6	707.8	707.1	706.5	705.8	705.1
145°	731.5	732.5	732.5	731.9	731.2	730.6	729.9
147.5°	753.2	753.9	754.0	753.4	752.8	752.3	751.7
150°	766.8	767.6	767.7	767.0	766.3	765.6	764.9
152.5°	779.1	780.0	779.9	779.0	778.1	777.2	776.3
155°	795.7	796.6	796.4	795.3	794.3	793.2	792.0
157.5°	809.9	810.8	810.7	809.7	808.6	807.5	806.5
160°	817.9	818.7	818.6	817.7	816.7	815.8	814.9
162.5°	825.6	826.6	826.5	825.3	824.1	822.9	821.7
165°	835.0	835.9	835.9	835.0	834.0	833.0	832.1
167.5°	842.7	843.7	843.5	842.3	841.1	839.8	838.6
170°	846.6	847.7	847.5	846.3	845.0	843.8	842.6
172.5°	849.6	850.6	850.4	849.2	848.0	846.7	845.5
175°	852.8	853.8	853.6	852.2	850.8	849.5	848.1
177.5°	853.0	853.8	853.7	852.6	851.7	850.7	849.7
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2

(END OF REPORT)