

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644462

Luminaire Tested: CRQ4DP-SR4F0-100D930-FLL-1DUDD-WW

Issue Date: 2/20/2023



Test Information

Test Method: LM-79-2019
Report Number: P644462
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2206-689-14)
Test Lab: INNOVATION CENTER
Issue Date: 2/20/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: CRQ4DP-SR4F0-100D930-FLL-1DUDD-WW
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE
DOWNLIGHT - CURVED FROSTED LENS - 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3414.5 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.02')
CIE Type: Direct

Input Watts (W): 29.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644462
CATALOG NUMBER: CRQ4DP-SR4F0-100D930-FLL-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644462

CATALOG NUMBER: CRQ4DP-SR4F0-100D930-FLL-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	110	110	110	105	105	105	100	100	100	98
1	108	103	99	95	105	101	97	93	96	93	90	92	89	87	88	86	84	82
2	99	91	84	78	96	88	82	77	85	79	75	81	77	73	78	74	71	69
3	90	80	72	65	88	78	71	65	75	69	63	72	67	62	69	65	61	58
4	83	71	62	56	80	70	62	55	67	60	54	64	58	53	62	57	53	50
5	76	64	55	48	74	63	54	48	60	53	47	58	52	47	56	50	46	44
6	71	58	49	43	69	57	48	42	55	47	42	53	46	41	51	45	41	39
7	66	52	44	38	64	51	43	38	50	42	37	48	42	37	47	41	36	34
8	61	48	40	34	60	47	39	34	46	38	33	44	38	33	43	37	33	31
9	57	44	36	31	56	43	36	30	42	35	30	41	35	30	40	34	30	28
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21385	21385	21385
5°	21121	21110	21218
10°	20985	20758	20826
15°	20823	20378	20412
20°	20493	19930	19812
25°	20005	19333	19031
30°	19530	18523	18134
35°	18834	17660	17050
40°	18199	16779	15830
45°	17448	15693	14486
50°	16650	14532	13075
55°	15814	13462	11666
60°	15059	12270	10404
65°	14103	11036	9302
70°	13283	9959	8441
75°	12314	9090	7855
80°	11422	8449	7521
85°	10668	8424	7534

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17448 cd/sqm



TEST NUMBER: P644462

CATALOG NUMBER: CRQ4DP-SR4F0-100D930-FLL-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.0	3.7
10°-20°	354.7	10.4
20°-30°	523.7	15.3
30°-40°	602.1	17.6
40°-50°	584.0	17.1
50°-60°	488.9	14.3
60°-70°	352.2	10.3
70°-80°	215.2	6.3
80°-90°	104.6	3.1
90°-100°	41.4	1.2
100°-110°	15.0	0.4
110°-120°	5.2	0.2
120°-130°	2.2	0.1
130°-140°	0.3	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1003.4	29.4
0°-40°	1605.5	47.0
0°-60°	2678.5	78.4
0°-90°	3350.5	98.1
90°-120°	61.6	1.8
90°-150°	64.0	1.9
90°-180°	64.0	1.9
0°-180°	3414.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1324	1324	1324	1324	1324	
5°	1304	1328	1315	1317	1326	124
15°	1248	1266	1255	1261	1270	351
25°	1126	1144	1141	1136	1143	519
35°	960	974	965	956	956	601
45°	769	776	763	740	730	593
55°	567	574	554	520	503	508
65°	374	376	357	331	322	372
75°	202	202	206	200	196	216
85°	62	74	103	110	110	65
90°	6	37	67	79	80	7
95°	19	17	39	52	54	16
105°	19	8	9	17	21	20
115°	13	6	4	4	4	13
125°	8	4	2	0	0	6
135°	0	0	0	0	0	1
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0



TEST NUMBER: P644462

CATALOG NUMBER: CRQ4DP-SR4F0-100D930-FLL-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1324.5	1324.5	1324.5	1324.5	1324.5
2.5°	1312.5	1331.5	1320.0	1323.0	1324.5
5°	1303.9	1327.7	1315.1	1317.2	1326.3
7.5°	1291.9	1313.9	1302.8	1305.2	1315.9
10°	1281.4	1303.4	1290.8	1294.7	1303.9
12.5°	1268.0	1288.4	1278.8	1282.8	1291.9
15°	1247.8	1266.0	1255.2	1261.1	1270.2
17.5°	1217.8	1237.6	1226.1	1229.3	1238.4
20°	1195.4	1213.7	1206.6	1206.8	1216.0
22.5°	1168.4	1188.2	1182.7	1178.4	1189.0
25°	1126.2	1144.5	1141.1	1135.7	1143.0
27.5°	1084.3	1097.8	1091.4	1085.9	1091.4
30°	1051.3	1067.8	1056.9	1051.5	1056.9
32.5°	1015.4	1031.9	1021.0	1014.0	1016.5
35°	959.7	974.3	965.3	955.9	955.9
37.5°	906.9	916.4	910.3	894.5	890.5
40°	868.0	879.0	869.9	851.0	845.6
42.5°	827.6	838.6	828.0	807.6	799.2
45°	768.9	776.2	763.2	740.5	729.6
47.5°	708.2	715.9	698.1	673.2	660.0
50°	667.8	677.0	654.7	628.2	613.6
52.5°	628.9	635.1	614.3	583.4	570.2
55°	566.8	574.1	553.7	519.7	503.2
57.5°	508.8	515.8	491.6	459.2	446.3
60°	471.4	476.9	452.7	418.7	405.9
62.5°	429.5	435.0	412.3	382.8	370.0
65°	374.1	376.0	357.3	330.9	321.8
67.5°	322.1	322.1	306.4	286.8	279.5
70°	286.2	286.2	275.0	259.9	252.5
72.5°	253.3	251.8	245.1	234.5	228.6
75°	202.0	202.0	205.8	200.1	196.4
77.5°	157.1	154.2	170.2	169.4	167.6
80°	127.2	127.2	147.8	151.5	149.7
82.5°	100.3	103.2	129.8	135.0	133.2
85°	61.7	74.5	102.9	110.4	110.4
87.5°	28.1	50.4	80.8	90.6	90.9
90°	5.6	36.7	67.3	78.6	80.4
92.5°	11.6	28.1	55.4	66.7	70.0
95°	18.7	16.9	39.3	52.4	54.3
97.5°	22.4	11.1	28.4	39.3	41.5
100°	22.4	9.6	22.4	31.9	35.5
102.5°	21.0	8.1	16.5	25.9	28.1
105°	18.7	7.7	9.4	16.9	20.6
107.5°	16.5	5.9	5.2	10.5	12.3
110°	15.0	5.8	3.7	7.5	9.4



TEST NUMBER: P644462

CATALOG NUMBER: CRQ4DP-SR4F0-100D930-FLL-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	15.0	5.8	3.7	4.5	6.4
115°	13.1	5.8	3.7	3.7	3.7
117.5°	10.9	5.7	3.4	1.5	1.5
120°	9.4	5.7	1.9	0.0	0.0
122.5°	9.4	4.2	1.9	0.0	0.0
125°	7.5	3.8	1.9	0.0	0.0
127.5°	5.2	3.8	1.9	0.0	0.0
130°	3.7	3.7	1.9	0.0	0.0
132.5°	0.7	0.7	0.4	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)