

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331753-935

Luminaire Tested: **S122RDIP-S1005D925U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331753-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S1005D925U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6469.1 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51	
1	99	95	91	88	91	88	85	82	75	72	70	63	61	60	51	50	49	44	44	44	44	
2	91	84	78	73	84	78	73	68	66	63	60	56	53	51	46	45	43	38	38	38	38	
3	83	74	67	62	77	69	63	58	59	55	51	50	47	44	42	40	38	34	34	34	34	
4	77	66	59	53	71	62	55	50	53	48	44	45	42	39	38	35	33	30	30	30	30	
5	71	60	52	46	65	56	49	44	48	43	39	41	37	34	35	32	30	26	26	26	26	
6	65	54	46	41	60	50	44	39	44	38	34	38	34	30	32	29	27	24	24	24	24	
7	61	49	41	36	56	46	39	34	40	35	31	35	30	27	29	26	24	21	21	21	21	
8	57	45	37	32	52	42	35	31	37	32	28	32	28	25	27	24	22	20	20	20	20	
9	53	41	34	29	49	39	32	28	34	29	25	30	25	23	25	22	20	18	18	18	18	
10	50	38	31	26	46	36	29	25	31	26	23	27	23	21	24	21	18	16	16	16	16	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30658	30658	30658	30658
5°	34240	30851	27353	30851
10°	37990	30634	23710	30634
15°	39858	30186	18683	30186
20°	34553	29520	16167	29520
25°	22661	28609	14434	28609
30°	15252	27505	13064	27505
35°	12354	26112	11783	26112
40°	10985	24601	10903	24601
45°	9944	22825	9732	22825
50°	9048	21064	9018	21064
55°	8507	19111	8397	19111
60°	7114	17321	7030	17321
65°	5998	15729	6804	15729
70°	5542	14049	6420	14049
75°	5190	12227	5926	12227
80°	4788	10060	5272	10060
85°	4409	7947	4650	7947



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.0	2.8
10°-20°	501.6	7.8
20°-30°	646.3	10.0
30°-40°	614.2	9.5
40°-50°	526.2	8.1
50°-60°	400.7	6.2
60°-70°	253.3	3.9
70°-80°	126.5	2.0
80°-90°	35.6	0.6
90°-100°	36.2	0.6
100°-110°	132.9	2.1
110°-120°	355.3	5.5
120°-130°	586.6	9.1
130°-140°	623.8	9.6
140°-150°	579.8	9.0
150°-160°	466.2	7.2
160°-170°	300.4	4.6
170°-180°	103.4	1.6
0°-30°	1327.9	20.5
0°-40°	1942.1	30.0
0°-60°	2869.0	44.3
0°-90°	3284.4	50.8
90°-120°	524.5	8.1
90°-150°	2314.7	35.8
90°-180°	3185.0	49.2
0°-180°	6469.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2113	1904	1688	1904	2113	209
15°	2384	1806	1118	1806	2384	643
25°	1272	1606	810	1606	1272	604
35°	627	1325	598	1325	627	401
45°	436	1000	426	1000	436	337
55°	302	679	298	679	302	265
65°	157	412	178	412	157	160
75°	83	196	95	196	83	88
85°	24	43	25	43	24	26
90°	21	1	21	1	21	10
95°	34	51	34	51	34	32
105°	60	239	60	239	60	62
115°	64	452	64	452	64	162
125°	672	639	672	639	672	582
135°	817	791	817	791	817	630
145°	932	918	932	918	932	583
155°	1011	1010	1011	1010	1011	467
165°	1062	1065	1062	1065	1062	300
175°	1083	1089	1083	1089	1083	103
180°	1087	1087	1087	1087	1087	



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1975.9	1977.5	1979.1	1975.4	1975.4	1972.2	1965.4	1960.1	1945.3	1943.2	1943.2
5°	2112.6	2111.3	2113.9	2105.4	2093.5	2090.9	2078.4	2061.8	2044.7	2025.6	2021.6
7.5°	2248.6	2246.6	2241.3	2239.9	2230.8	2210.8	2190.6	2169.1	2140.6	2112.8	2098.8
10°	2317.2	2339.0	2325.7	2302.7	2307.3	2276.3	2259.8	2231.5	2207.7	2166.1	2156.9
12.5°	2384.7	2393.3	2389.1	2376.0	2370.1	2348.5	2326.2	2301.6	2257.8	2220.4	2188.0
15°	2384.5	2397.0	2400.3	2396.3	2399.7	2398.3	2386.4	2366.0	2327.7	2286.8	2251.2
17.5°	2208.5	2217.2	2238.8	2253.4	2271.9	2311.0	2330.2	2337.8	2332.1	2308.8	2283.6
20°	2011.0	1996.5	2057.2	2088.3	2114.6	2180.6	2237.3	2259.1	2294.0	2293.4	2286.8
22.5°	1731.3	1734.7	1792.3	1829.1	1906.2	1972.1	2036.8	2118.7	2186.4	2231.1	2257.3
25°	1272.0	1297.2	1354.5	1404.7	1490.5	1613.2	1724.7	1854.0	1976.1	2072.4	2164.1
27.5°	955.4	957.3	1002.7	1049.0	1100.0	1200.6	1340.9	1495.4	1669.4	1813.0	1978.1
30°	818.1	814.2	833.3	861.7	905.3	983.1	1088.6	1240.4	1413.9	1630.3	1823.0
32.5°	721.0	721.3	735.6	756.6	792.8	845.3	917.7	1040.9	1204.9	1417.6	1643.6
35°	626.8	626.1	636.7	651.9	667.0	700.7	750.2	814.9	927.6	1126.3	1357.2
37.5°	559.2	562.1	567.3	576.8	593.6	612.3	642.0	685.4	765.8	883.2	1077.3
40°	521.2	522.5	529.8	537.7	547.6	562.1	586.5	621.6	680.3	774.0	915.8
42.5°	486.4	487.8	492.8	500.2	508.1	522.5	542.8	573.0	620.6	693.7	810.7
45°	435.5	435.5	440.1	443.4	451.9	465.1	481.6	506.7	539.7	593.8	671.7
47.5°	387.7	387.8	390.9	396.6	401.9	412.2	428.4	448.9	472.9	514.8	581.3
50°	360.2	360.9	362.9	367.5	370.8	380.0	392.6	410.4	435.5	467.8	523.2
52.5°	338.1	337.7	340.2	342.2	344.4	351.0	360.4	376.1	398.5	426.6	472.5
55°	302.2	299.5	303.5	306.8	308.8	311.4	316.7	326.6	345.7	369.5	403.8
57.5°	257.4	256.2	259.1	262.1	268.3	275.4	279.9	286.2	296.1	313.1	347.2
60°	220.3	220.3	226.3	228.3	235.6	244.8	254.0	259.3	269.2	280.4	305.5
62.5°	187.6	188.2	191.0	193.0	197.0	208.4	221.3	232.9	242.3	253.0	269.6
65°	157.0	158.3	158.3	159.6	162.3	165.0	170.2	179.4	196.0	211.1	223.7
67.5°	133.3	133.7	134.1	135.3	136.0	139.0	141.0	145.2	149.0	163.3	178.9
70°	117.4	119.4	118.7	120.1	120.7	122.1	124.7	126.7	132.6	136.0	145.2
72.5°	102.6	104.1	104.0	104.8	106.5	106.8	108.8	110.8	114.7	117.4	122.4
75°	83.2	82.5	83.2	84.5	85.2	85.8	85.8	88.4	90.4	93.0	96.3
77.5°	64.1	64.8	64.7	64.8	64.9	66.1	66.0	67.2	69.1	70.4	72.1
80°	51.5	52.1	51.5	52.1	52.8	53.5	52.8	53.5	55.4	56.7	56.7
82.5°	39.9	40.0	40.4	40.6	40.6	40.8	41.7	41.8	43.3	43.0	43.6
85°	23.8	23.1	23.1	23.1	23.8	24.5	23.8	23.8	24.5	24.5	24.5
87.5°	12.7	13.2	13.1	13.0	12.9	12.8	12.7	13.0	12.3	12.7	11.9
90°	21.3	20.9	20.5	20.1	19.8	19.2	18.3	17.5	16.6	15.8	14.3
92.5°	21.3	21.0	20.8	20.6	20.4	20.1	19.6	19.1	18.7	18.3	17.6
95°	33.8	34.0	34.2	34.4	34.5	34.2	33.3	32.4	31.5	30.7	29.4
97.5°	45.1	44.9	44.7	44.5	44.3	43.8	43.1	42.4	41.8	41.1	38.2
100°	52.7	52.3	52.0	51.7	51.3	50.5	49.0	47.6	46.2	44.9	41.8
102.5°	56.5	56.0	55.4	55.0	54.5	53.4	51.6	49.7	47.9	46.1	70.9
105°	59.8	59.1	58.4	57.7	57.0	55.6	53.7	51.8	49.9	48.0	95.7
107.5°	61.5	60.8	60.1	59.4	58.7	59.3	61.3	63.2	65.2	67.2	124.3
110°	62.2	61.4	60.7	60.0	59.3	67.7	85.2	102.6	120.1	137.6	188.1



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.8	62.2	61.6	61.0	60.5	92.1	155.8	219.6	283.4	347.1	359.6
115°	64.5	77.1	89.6	102.2	114.8	161.5	242.5	323.4	404.2	485.2	480.8
117.5°	263.3	304.6	345.9	387.3	428.6	459.1	478.7	498.3	517.8	537.4	534.4
120°	479.7	503.3	526.8	550.4	574.0	584.8	582.7	580.6	578.5	576.4	573.3
122.5°	598.6	603.1	607.7	612.3	616.9	618.5	617.3	616.0	614.8	613.5	610.1
125°	672.4	671.8	671.2	670.7	670.2	669.3	668.1	666.9	665.7	664.4	661.2
127.5°	718.8	718.8	718.7	718.6	718.4	717.6	715.7	713.9	712.1	710.4	707.9
130°	747.8	748.0	748.1	748.4	748.6	747.6	745.7	743.8	741.8	739.9	738.0
132.5°	776.1	776.3	776.4	776.6	776.8	776.1	774.5	772.8	771.2	769.5	767.6
135°	817.0	817.3	817.7	818.0	818.4	817.7	816.0	814.2	812.4	810.7	809.2
137.5°	854.3	854.9	855.5	856.1	856.7	856.1	854.4	852.6	850.9	849.3	847.5
140°	877.5	878.5	879.3	880.2	881.1	880.7	879.2	877.5	876.0	874.4	872.5
142.5°	900.2	901.1	902.0	902.8	903.7	903.4	902.0	900.5	899.1	897.7	895.5
145°	931.9	932.7	933.6	934.4	935.3	935.1	933.9	932.7	931.4	930.2	927.3
147.5°	959.7	960.4	961.1	961.8	962.6	962.5	961.6	960.7	959.8	958.9	956.0
150°	976.6	977.5	978.4	979.3	980.2	980.1	979.0	977.9	976.9	975.9	973.1
152.5°	991.1	992.3	993.4	994.5	995.7	995.7	994.7	993.7	992.6	991.6	988.9
155°	1011.2	1012.6	1014.0	1015.5	1016.8	1017.0	1016.0	1014.9	1013.8	1012.8	1010.7
157.5°	1029.7	1031.0	1032.3	1033.7	1035.1	1035.2	1034.0	1032.8	1031.7	1030.4	1029.0
160°	1040.3	1041.6	1042.8	1044.0	1045.3	1045.3	1044.3	1043.2	1042.2	1041.1	1040.1
162.5°	1049.1	1050.7	1052.1	1053.7	1055.2	1055.3	1054.1	1052.9	1051.7	1050.6	1049.6
165°	1062.4	1063.6	1064.8	1066.0	1067.2	1067.2	1066.0	1064.8	1063.6	1062.4	1061.9
167.5°	1070.7	1072.3	1073.8	1075.4	1076.9	1077.2	1075.9	1074.7	1073.5	1072.3	1071.8
170°	1075.7	1077.3	1078.8	1080.5	1082.0	1082.2	1081.0	1079.8	1078.5	1077.3	1076.9
172.5°	1079.5	1081.1	1082.6	1084.2	1085.8	1086.0	1084.8	1083.5	1082.3	1081.1	1080.7
175°	1082.8	1084.5	1086.3	1088.0	1089.8	1090.0	1088.8	1087.6	1086.4	1085.1	1084.8
177.5°	1084.9	1086.1	1087.4	1088.6	1089.9	1090.0	1089.1	1088.0	1087.1	1086.1	1086.0
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1944.3	1940.0	1936.4	1926.8	1922.1	1911.5	1910.0	1909.4	1895.7	1882.5	1878.8
5°	2011.0	2000.4	1984.7	1966.2	1947.1	1927.3	1914.1	1903.5	1877.1	1852.0	1837.5
7.5°	2078.4	2055.6	2028.3	1993.4	1964.2	1931.5	1907.2	1885.4	1848.0	1812.1	1787.9
10°	2128.5	2091.5	2055.2	2007.1	1969.5	1932.5	1898.2	1868.5	1826.3	1778.8	1745.2
12.5°	2159.6	2119.0	2069.0	2021.9	1973.2	1926.2	1880.3	1842.1	1792.5	1743.4	1703.5
15°	2201.7	2158.2	2097.5	2030.2	1967.5	1906.2	1853.4	1805.9	1741.2	1682.5	1633.7
17.5°	2236.2	2176.3	2111.1	2033.3	1960.7	1882.7	1814.7	1754.0	1682.0	1611.2	1553.7
20°	2247.2	2187.9	2112.6	2034.8	1949.0	1857.3	1784.1	1718.1	1640.9	1563.7	1497.7
22.5°	2240.4	2194.2	2110.6	2017.4	1929.5	1833.6	1750.8	1674.3	1588.6	1509.8	1433.3
25°	2193.8	2178.0	2098.8	1997.2	1896.9	1785.4	1689.7	1605.9	1508.3	1423.8	1340.7
27.5°	2085.2	2119.4	2070.3	1962.0	1850.5	1731.0	1623.5	1528.1	1426.8	1331.7	1248.9
30°	1980.7	2059.2	2038.1	1937.8	1813.1	1695.7	1574.9	1475.3	1367.1	1269.5	1187.7
32.5°	1837.6	1967.4	1988.0	1904.0	1775.1	1646.1	1519.5	1420.4	1307.4	1204.5	1124.8
35°	1609.9	1803.9	1892.9	1839.5	1710.2	1571.0	1440.3	1324.8	1211.3	1109.7	1030.6
37.5°	1338.2	1602.4	1750.8	1754.6	1635.9	1491.2	1348.8	1234.2	1118.1	1018.3	932.7
40°	1161.9	1448.2	1641.6	1684.5	1584.2	1427.8	1283.9	1167.2	1053.7	956.1	857.7
42.5°	1003.6	1288.8	1526.5	1601.0	1521.4	1366.1	1221.7	1099.6	989.3	896.9	796.5
45°	811.6	1060.9	1322.8	1456.1	1412.0	1268.1	1115.7	999.6	896.0	816.1	719.8
47.5°	684.6	860.4	1113.9	1294.1	1293.3	1162.0	1012.1	900.9	804.8	730.0	652.0
50°	612.3	765.3	979.8	1184.3	1201.4	1091.3	948.7	838.6	748.9	670.4	607.7
52.5°	547.3	673.5	866.3	1062.4	1111.2	1015.8	877.5	775.8	688.7	616.5	562.8
55°	462.5	560.2	706.6	890.0	964.0	896.6	774.0	678.9	608.3	547.6	501.4
57.5°	391.2	464.5	582.0	729.7	815.8	773.4	672.2	595.0	534.6	479.7	443.2
60°	346.4	406.4	506.1	629.5	724.4	694.7	608.3	536.4	484.9	437.5	403.1
62.5°	304.2	355.8	441.2	541.3	628.4	616.1	545.5	485.2	440.1	396.8	367.7
65°	244.8	282.4	349.0	427.6	497.5	503.4	452.6	411.7	371.4	337.2	311.4
67.5°	194.9	219.5	266.4	332.5	385.0	403.6	372.6	341.4	309.4	282.9	260.6
70°	164.3	184.1	218.3	271.8	320.0	339.8	322.0	297.6	269.8	248.1	228.9
72.5°	133.1	152.4	177.7	217.0	258.2	279.7	273.5	255.9	233.4	215.3	197.3
75°	100.3	106.2	123.4	149.8	182.1	200.6	205.2	196.0	178.1	164.3	153.7
77.5°	74.1	77.7	85.9	99.8	120.9	137.3	144.1	143.0	130.8	122.7	112.8
80°	59.4	61.4	65.3	71.3	87.1	103.6	108.2	108.2	99.6	96.3	86.4
82.5°	45.1	46.6	49.0	52.3	59.7	74.0	79.2	80.2	74.8	70.4	62.7
85°	25.7	25.1	26.4	28.4	29.7	33.7	41.6	42.9	41.6	36.2	34.3
87.5°	11.5	11.8	11.5	10.7	10.8	10.9	13.2	15.5	13.8	12.6	11.9
90°	12.9	11.5	10.2	8.4	6.5	4.6	2.7	0.8	2.7	4.6	6.5
92.5°	16.9	16.2	15.4	15.2	15.3	15.5	15.7	15.8	15.7	15.5	15.3
95°	28.2	27.0	25.7	28.1	33.8	39.6	45.4	51.1	45.4	39.6	33.8
97.5°	35.4	32.5	29.7	36.4	52.7	69.0	85.2	101.4	85.2	69.0	52.7
100°	38.9	35.9	33.0	43.4	67.3	91.3	115.2	139.2	115.2	91.3	67.3
102.5°	95.7	120.6	145.5	160.4	165.5	170.6	175.6	180.7	175.6	170.6	165.5
105°	143.4	191.1	238.8	260.0	254.8	249.5	244.3	239.0	244.3	249.5	254.8
107.5°	181.6	238.8	296.0	322.5	318.2	314.0	309.8	305.6	309.8	314.0	318.2
110°	238.6	289.1	339.6	363.0	359.4	355.7	352.1	348.4	352.1	355.7	359.4



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	372.0	384.5	397.0	401.6	398.4	395.1	391.8	388.6	391.8	395.1	398.4
115°	476.5	472.1	467.7	464.0	461.1	458.1	455.1	452.1	455.1	458.1	461.1
117.5°	531.4	528.4	525.4	522.2	518.9	515.6	512.2	508.9	512.2	515.6	518.9
120°	570.1	567.0	563.8	560.9	558.3	555.7	553.0	550.4	553.0	555.7	558.3
122.5°	606.7	603.2	599.8	596.7	593.9	591.2	588.4	585.7	588.4	591.2	593.9
125°	657.8	654.5	651.2	648.4	646.1	643.9	641.5	639.3	641.5	643.9	646.1
127.5°	705.4	702.9	700.4	697.9	695.4	692.9	690.4	687.9	690.4	692.9	695.4
130°	736.1	734.2	732.3	729.9	727.1	724.3	721.5	718.8	721.5	724.3	727.1
132.5°	765.7	763.8	761.8	759.7	757.3	754.9	752.5	750.2	752.5	754.9	757.3
135°	807.6	806.0	804.4	802.3	799.4	796.7	793.8	791.1	793.8	796.7	799.4
137.5°	845.7	843.9	842.1	840.2	838.3	836.4	834.4	832.4	834.4	836.4	838.3
140°	870.6	868.7	866.8	865.0	863.7	862.3	860.9	859.5	860.9	862.3	863.7
142.5°	893.3	891.0	888.9	887.2	885.9	884.7	883.4	882.1	883.4	884.7	885.9
145°	924.3	921.4	918.3	917.0	917.1	917.3	917.5	917.7	917.5	917.3	917.1
147.5°	953.0	950.0	947.1	946.0	946.7	947.4	948.0	948.6	948.0	947.4	946.7
150°	970.3	967.5	964.7	963.9	965.1	966.3	967.6	968.8	967.6	966.3	965.1
152.5°	986.3	983.6	980.9	980.3	981.7	983.0	984.4	985.8	984.4	983.0	981.7
155°	1008.7	1006.5	1004.4	1004.2	1005.7	1007.3	1008.9	1010.5	1008.9	1007.3	1005.7
157.5°	1027.5	1026.1	1024.6	1024.5	1025.8	1027.2	1028.5	1029.8	1028.5	1027.2	1025.8
160°	1039.1	1037.9	1036.9	1036.9	1037.9	1039.1	1040.1	1041.1	1040.1	1039.1	1037.9
162.5°	1048.7	1047.8	1046.9	1047.0	1048.0	1049.1	1050.2	1051.2	1050.2	1049.1	1048.0
165°	1061.3	1060.8	1060.2	1060.5	1061.5	1062.6	1063.7	1064.7	1063.7	1062.6	1061.5
167.5°	1071.3	1070.8	1070.3	1070.6	1071.6	1072.7	1073.8	1074.8	1073.8	1072.7	1071.6
170°	1076.6	1076.2	1075.9	1076.2	1077.3	1078.3	1079.3	1080.5	1079.3	1078.3	1077.3
172.5°	1080.4	1080.0	1079.7	1080.0	1081.1	1082.1	1083.1	1084.2	1083.1	1082.1	1081.1
175°	1084.4	1084.1	1083.7	1084.2	1085.4	1086.7	1087.9	1089.1	1087.9	1086.7	1085.4
177.5°	1085.8	1085.7	1085.5	1086.0	1086.9	1088.0	1088.9	1089.9	1088.9	1088.0	1086.9
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1872.0	1868.3	1861.4	1850.8	1844.5	1833.4	1826.0	1830.2	1831.3	1830.2	1829.2
5°	1821.7	1807.8	1788.7	1770.2	1753.1	1734.6	1724.1	1719.4	1710.2	1704.9	1702.3
7.5°	1760.8	1737.0	1709.9	1677.7	1650.4	1621.8	1607.1	1599.8	1581.0	1570.7	1561.7
10°	1715.5	1677.8	1650.8	1608.6	1582.9	1545.2	1519.5	1520.2	1494.4	1479.9	1469.4
12.5°	1665.3	1624.0	1579.0	1541.0	1505.3	1475.1	1444.0	1431.5	1404.2	1390.2	1361.7
15°	1582.2	1534.0	1486.5	1435.0	1398.8	1351.9	1307.1	1252.3	1208.1	1169.8	1159.3
17.5°	1491.4	1431.8	1384.1	1323.7	1261.5	1182.8	1130.8	1099.0	1072.3	1052.1	1037.1
20°	1429.1	1368.4	1317.6	1226.6	1142.7	1089.3	1051.0	1026.7	998.9	977.1	965.3
22.5°	1363.7	1300.3	1231.1	1129.5	1064.1	1021.2	987.1	959.1	940.3	923.3	912.5
25°	1270.7	1201.4	1087.4	1017.4	964.6	919.7	896.0	878.8	859.0	835.9	825.4
27.5°	1172.6	1062.4	980.4	928.4	878.0	848.9	827.5	801.9	784.2	773.8	762.8
30°	1099.2	989.0	925.1	868.3	832.7	800.3	775.2	760.8	743.6	725.7	718.5
32.5°	1017.4	929.4	868.1	820.8	784.6	757.1	737.3	713.8	701.4	690.4	675.2
35°	915.8	849.1	793.1	754.8	720.5	698.1	674.9	661.1	638.7	629.5	623.5
37.5°	829.7	772.0	730.1	689.7	662.5	637.7	623.6	601.6	591.9	579.0	566.5
40°	781.2	724.4	684.2	651.2	620.9	602.4	584.5	566.8	552.2	546.3	531.2
42.5°	731.6	685.4	645.1	609.0	588.7	569.1	546.6	533.5	518.5	508.9	499.5
45°	663.1	622.2	587.9	558.2	535.7	515.3	500.8	479.0	470.5	451.3	443.4
47.5°	603.0	564.9	532.2	503.9	482.1	468.7	447.5	430.4	416.7	405.0	394.9
50°	560.2	528.5	496.8	471.7	451.9	432.8	411.0	402.4	381.3	375.4	369.5
52.5°	521.1	491.0	462.0	437.5	417.7	399.1	379.9	368.7	354.5	348.5	344.1
55°	466.5	437.5	409.7	388.0	368.2	349.0	337.2	323.3	316.7	312.1	306.8
57.5°	411.6	385.5	364.2	342.2	322.3	307.0	293.3	285.0	278.2	272.1	265.8
60°	376.8	351.6	332.5	312.1	291.6	279.1	268.5	258.6	250.7	241.5	238.8
62.5°	339.8	317.9	300.3	280.4	262.6	251.2	241.1	231.7	222.2	208.8	205.1
65°	289.0	271.8	253.4	236.9	221.0	209.8	195.3	184.8	180.8	179.4	178.8
67.5°	243.1	226.9	211.0	194.1	179.7	169.3	162.0	160.3	157.6	156.8	154.9
70°	212.5	197.3	181.4	165.6	151.8	149.8	147.1	144.5	141.2	139.9	138.5
72.5°	185.0	169.3	153.4	140.8	134.8	132.3	129.8	127.1	124.8	123.6	122.7
75°	141.9	127.3	116.8	112.2	108.8	106.9	102.9	100.9	99.6	97.6	96.9
77.5°	102.1	93.9	89.1	86.2	82.7	80.6	78.4	76.4	75.0	74.6	73.5
80°	77.8	73.9	70.6	66.6	65.3	62.7	62.0	60.0	60.7	58.7	58.7
82.5°	60.4	55.4	52.7	50.8	49.5	47.4	46.8	45.8	45.9	44.4	44.4
85°	31.0	29.7	28.4	27.0	27.0	25.1	25.7	25.1	25.1	23.8	23.1
87.5°	11.7	11.5	10.8	11.0	11.3	11.0	11.3	10.8	11.0	11.2	10.8
90°	8.4	10.2	11.5	12.9	14.3	15.8	16.6	17.5	18.3	19.2	19.8
92.5°	15.2	15.4	16.2	16.9	17.6	18.3	18.7	19.1	19.6	20.1	20.4
95°	28.1	25.7	27.0	28.2	29.4	30.7	31.5	32.4	33.3	34.2	34.5
97.5°	36.4	29.7	32.5	35.4	38.2	41.1	41.8	42.4	43.1	43.8	44.3
100°	43.4	33.0	35.9	38.9	41.8	44.9	46.2	47.6	49.0	50.5	51.3
102.5°	160.4	145.5	120.6	95.7	70.9	46.1	47.9	49.7	51.6	53.4	54.5
105°	260.0	238.8	191.1	143.4	95.7	48.0	49.9	51.8	53.7	55.6	57.0
107.5°	322.5	296.0	238.8	181.6	124.3	67.2	65.2	63.2	61.3	59.3	58.7
110°	363.0	339.6	289.1	238.6	188.1	137.6	120.1	102.6	85.2	67.7	59.3



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	401.6	397.0	384.5	372.0	359.6	347.1	283.4	219.6	155.8	92.1	60.5
115°	464.0	467.7	472.1	476.5	480.8	485.2	404.2	323.4	242.5	161.5	114.8
117.5°	522.2	525.4	528.4	531.4	534.4	537.4	517.8	498.3	478.7	459.1	428.6
120°	560.9	563.8	567.0	570.1	573.3	576.4	578.5	580.6	582.7	584.8	574.0
122.5°	596.7	599.8	603.2	606.7	610.1	613.5	614.8	616.0	617.3	618.5	616.9
125°	648.4	651.2	654.5	657.8	661.2	664.4	665.7	666.9	668.1	669.3	670.2
127.5°	697.9	700.4	702.9	705.4	707.9	710.4	712.1	713.9	715.7	717.6	718.4
130°	729.9	732.3	734.2	736.1	738.0	739.9	741.8	743.8	745.7	747.6	748.6
132.5°	759.7	761.8	763.8	765.7	767.6	769.5	771.2	772.8	774.5	776.1	776.8
135°	802.3	804.4	806.0	807.6	809.2	810.7	812.4	814.2	816.0	817.7	818.4
137.5°	840.2	842.1	843.9	845.7	847.5	849.3	850.9	852.6	854.4	856.1	856.7
140°	865.0	866.8	868.7	870.6	872.5	874.4	876.0	877.5	879.2	880.7	881.1
142.5°	887.2	888.9	891.0	893.3	895.5	897.7	899.1	900.5	902.0	903.4	903.7
145°	917.0	918.3	921.4	924.3	927.3	930.2	931.4	932.7	933.9	935.1	935.3
147.5°	946.0	947.1	950.0	953.0	956.0	958.9	959.8	960.7	961.6	962.5	962.6
150°	963.9	964.7	967.5	970.3	973.1	975.9	976.9	977.9	979.0	980.1	980.2
152.5°	980.3	980.9	983.6	986.3	988.9	991.6	992.6	993.7	994.7	995.7	995.7
155°	1004.2	1004.4	1006.5	1008.7	1010.7	1012.8	1013.8	1014.9	1016.0	1017.0	1016.8
157.5°	1024.5	1024.6	1026.1	1027.5	1029.0	1030.4	1031.7	1032.8	1034.0	1035.2	1035.1
160°	1036.9	1036.9	1037.9	1039.1	1040.1	1041.1	1042.2	1043.2	1044.3	1045.3	1045.3
162.5°	1047.0	1046.9	1047.8	1048.7	1049.6	1050.6	1051.7	1052.9	1054.1	1055.3	1055.2
165°	1060.5	1060.2	1060.8	1061.3	1061.9	1062.4	1063.6	1064.8	1066.0	1067.2	1067.2
167.5°	1070.6	1070.3	1070.8	1071.3	1071.8	1072.3	1073.5	1074.7	1075.9	1077.2	1076.9
170°	1076.2	1075.9	1076.2	1076.6	1076.9	1077.3	1078.5	1079.8	1081.0	1082.2	1082.0
172.5°	1080.0	1079.7	1080.0	1080.4	1080.7	1081.1	1082.3	1083.5	1084.8	1086.0	1085.8
175°	1084.2	1083.7	1084.1	1084.4	1084.8	1085.1	1086.4	1087.6	1088.8	1090.0	1089.8
177.5°	1086.0	1085.5	1085.7	1085.8	1086.0	1086.1	1087.1	1088.0	1089.1	1090.0	1089.9
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1823.4	1824.5	1822.9	1823.9	1822.9	1824.5	1823.4	1829.2	1830.2	1831.3	1830.2
5°	1698.9	1691.0	1689.7	1687.7	1689.7	1691.0	1698.9	1702.3	1704.9	1710.2	1719.4
7.5°	1550.4	1549.2	1545.9	1541.3	1545.9	1549.2	1550.4	1561.7	1570.7	1581.0	1599.8
10°	1454.8	1451.6	1450.9	1446.2	1450.9	1451.6	1454.8	1469.4	1479.9	1494.4	1520.2
12.5°	1342.9	1321.7	1319.5	1307.9	1319.5	1321.7	1342.9	1361.7	1390.2	1404.2	1431.5
15°	1143.4	1139.4	1126.3	1117.7	1126.3	1139.4	1143.4	1159.3	1169.8	1208.1	1252.3
17.5°	1029.4	1016.5	1012.4	1010.6	1012.4	1016.5	1029.4	1037.1	1052.1	1072.3	1099.0
20°	956.1	944.2	942.2	940.9	942.2	944.2	956.1	965.3	977.1	998.9	1026.7
22.5°	905.3	892.9	887.8	883.8	887.8	892.9	905.3	912.5	923.3	940.3	959.1
25°	818.8	814.2	811.6	810.2	811.6	814.2	818.8	825.4	835.9	859.0	878.8
27.5°	751.1	741.0	739.0	735.6	739.0	741.0	751.1	762.8	773.8	784.2	801.9
30°	712.6	709.3	704.6	700.7	704.6	709.3	712.6	718.5	725.7	743.6	760.8
32.5°	667.2	664.4	660.3	658.5	660.3	664.4	667.2	675.2	690.4	701.4	713.8
35°	616.9	607.7	603.7	597.8	603.7	607.7	616.9	623.5	629.5	638.7	661.1
37.5°	563.7	558.9	553.3	555.3	553.3	558.9	563.7	566.5	579.0	591.9	601.6
40°	522.5	519.3	518.0	517.3	518.0	519.3	522.5	531.2	546.3	552.2	566.8
42.5°	489.8	480.7	477.3	477.2	477.3	480.7	489.8	499.5	508.9	518.5	533.5
45°	440.1	431.5	425.6	426.2	425.6	431.5	440.1	443.4	451.3	470.5	479.0
47.5°	389.2	388.9	385.2	386.3	385.2	388.9	389.2	394.9	405.0	416.7	430.4
50°	364.9	360.9	358.3	359.0	358.3	360.9	364.9	369.5	375.4	381.3	402.4
52.5°	341.6	338.2	336.1	338.9	336.1	338.2	341.6	344.1	348.5	354.5	368.7
55°	303.5	299.5	298.9	298.3	298.9	299.5	303.5	306.8	312.1	316.7	323.3
57.5°	260.9	258.2	254.3	252.5	254.3	258.2	260.9	265.8	272.1	278.2	285.0
60°	230.2	225.0	218.3	217.7	218.3	225.0	230.2	238.8	241.5	250.7	258.6
62.5°	202.2	201.2	199.9	199.8	199.9	201.2	202.2	205.1	208.8	222.2	231.7
65°	177.5	176.8	177.5	178.1	177.5	176.8	177.5	178.8	179.4	180.8	184.8
67.5°	154.6	153.4	152.3	152.8	152.3	153.4	154.6	154.9	156.8	157.6	160.3
70°	137.2	136.6	136.0	136.0	136.0	136.6	137.2	138.5	139.9	141.2	144.5
72.5°	120.4	120.2	119.6	119.0	119.6	120.2	120.4	122.7	123.6	124.8	127.1
75°	96.3	95.0	95.0	95.0	95.0	95.0	96.3	96.9	97.6	99.6	100.9
77.5°	73.4	72.7	72.1	71.5	72.1	72.7	73.4	73.5	74.6	75.0	76.4
80°	58.0	57.4	56.7	56.7	56.7	57.4	58.0	58.7	58.7	60.7	60.0
82.5°	44.3	43.7	43.6	43.0	43.6	43.7	44.3	44.4	44.4	45.9	45.8
85°	23.8	24.5	23.8	25.1	23.8	24.5	23.8	23.1	23.8	25.1	25.1
87.5°	10.9	10.4	11.0	10.6	11.0	10.4	10.9	10.8	11.2	11.0	10.8
90°	20.1	20.5	20.9	21.3	20.9	20.5	20.1	19.8	19.2	18.3	17.5
92.5°	20.6	20.8	21.0	21.3	21.0	20.8	20.6	20.4	20.1	19.6	19.1
95°	34.4	34.2	34.0	33.8	34.0	34.2	34.4	34.5	34.2	33.3	32.4
97.5°	44.5	44.7	44.9	45.1	44.9	44.7	44.5	44.3	43.8	43.1	42.4
100°	51.7	52.0	52.3	52.7	52.3	52.0	51.7	51.3	50.5	49.0	47.6
102.5°	55.0	55.4	56.0	56.5	56.0	55.4	55.0	54.5	53.4	51.6	49.7
105°	57.7	58.4	59.1	59.8	59.1	58.4	57.7	57.0	55.6	53.7	51.8
107.5°	59.4	60.1	60.8	61.5	60.8	60.1	59.4	58.7	59.3	61.3	63.2
110°	60.0	60.7	61.4	62.2	61.4	60.7	60.0	59.3	67.7	85.2	102.6



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	61.0	61.6	62.2	62.8	62.2	61.6	61.0	60.5	92.1	155.8	219.6
115°	102.2	89.6	77.1	64.5	77.1	89.6	102.2	114.8	161.5	242.5	323.4
117.5°	387.3	345.9	304.6	263.3	304.6	345.9	387.3	428.6	459.1	478.7	498.3
120°	550.4	526.8	503.3	479.7	503.3	526.8	550.4	574.0	584.8	582.7	580.6
122.5°	612.3	607.7	603.1	598.6	603.1	607.7	612.3	616.9	618.5	617.3	616.0
125°	670.7	671.2	671.8	672.4	671.8	671.2	670.7	670.2	669.3	668.1	666.9
127.5°	718.6	718.7	718.8	718.8	718.8	718.7	718.6	718.4	717.6	715.7	713.9
130°	748.4	748.1	748.0	747.8	748.0	748.1	748.4	748.6	747.6	745.7	743.8
132.5°	776.6	776.4	776.3	776.1	776.3	776.4	776.6	776.8	776.1	774.5	772.8
135°	818.0	817.7	817.3	817.0	817.3	817.7	818.0	818.4	817.7	816.0	814.2
137.5°	856.1	855.5	854.9	854.3	854.9	855.5	856.1	856.7	856.1	854.4	852.6
140°	880.2	879.3	878.5	877.5	878.5	879.3	880.2	881.1	880.7	879.2	877.5
142.5°	902.8	902.0	901.1	900.2	901.1	902.0	902.8	903.7	903.4	902.0	900.5
145°	934.4	933.6	932.7	931.9	932.7	933.6	934.4	935.3	935.1	933.9	932.7
147.5°	961.8	961.1	960.4	959.7	960.4	961.1	961.8	962.6	962.5	961.6	960.7
150°	979.3	978.4	977.5	976.6	977.5	978.4	979.3	980.2	980.1	979.0	977.9
152.5°	994.5	993.4	992.3	991.1	992.3	993.4	994.5	995.7	995.7	994.7	993.7
155°	1015.5	1014.0	1012.6	1011.2	1012.6	1014.0	1015.5	1016.8	1017.0	1016.0	1014.9
157.5°	1033.7	1032.3	1031.0	1029.7	1031.0	1032.3	1033.7	1035.1	1035.2	1034.0	1032.8
160°	1044.0	1042.8	1041.6	1040.3	1041.6	1042.8	1044.0	1045.3	1045.3	1044.3	1043.2
162.5°	1053.7	1052.1	1050.7	1049.1	1050.7	1052.1	1053.7	1055.2	1055.3	1054.1	1052.9
165°	1066.0	1064.8	1063.6	1062.4	1063.6	1064.8	1066.0	1067.2	1067.2	1066.0	1064.8
167.5°	1075.4	1073.8	1072.3	1070.7	1072.3	1073.8	1075.4	1076.9	1077.2	1075.9	1074.7
170°	1080.5	1078.8	1077.3	1075.7	1077.3	1078.8	1080.5	1082.0	1082.2	1081.0	1079.8
172.5°	1084.2	1082.6	1081.1	1079.5	1081.1	1082.6	1084.2	1085.8	1086.0	1084.8	1083.5
175°	1088.0	1086.3	1084.5	1082.8	1084.5	1086.3	1088.0	1089.8	1090.0	1088.8	1087.6
177.5°	1088.6	1087.4	1086.1	1084.9	1086.1	1087.4	1088.6	1089.9	1090.0	1089.1	1088.0
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1826.0	1833.4	1844.5	1850.8	1861.4	1868.3	1872.0	1878.8	1882.5	1895.7	1909.4
5°	1724.1	1734.6	1753.1	1770.2	1788.7	1807.8	1821.7	1837.5	1852.0	1877.1	1903.5
7.5°	1607.1	1621.8	1650.4	1677.7	1709.9	1737.0	1760.8	1787.9	1812.1	1848.0	1885.4
10°	1519.5	1545.2	1582.9	1608.6	1650.8	1677.8	1715.5	1745.2	1778.8	1826.3	1868.5
12.5°	1444.0	1475.1	1505.3	1541.0	1579.0	1624.0	1665.3	1703.5	1743.4	1792.5	1842.1
15°	1307.1	1351.9	1398.8	1435.0	1486.5	1534.0	1582.2	1633.7	1682.5	1741.2	1805.9
17.5°	1130.8	1182.8	1261.5	1323.7	1384.1	1431.8	1491.4	1553.7	1611.2	1682.0	1754.0
20°	1051.0	1089.3	1142.7	1226.6	1317.6	1368.4	1429.1	1497.7	1563.7	1640.9	1718.1
22.5°	987.1	1021.2	1064.1	1129.5	1231.1	1300.3	1363.7	1433.3	1509.8	1588.6	1674.3
25°	896.0	919.7	964.6	1017.4	1087.4	1201.4	1270.7	1340.7	1423.8	1508.3	1605.9
27.5°	827.5	848.9	878.0	928.4	980.4	1062.4	1172.6	1248.9	1331.7	1426.8	1528.1
30°	775.2	800.3	832.7	868.3	925.1	989.0	1099.2	1187.7	1269.5	1367.1	1475.3
32.5°	737.3	757.1	784.6	820.8	868.1	929.4	1017.4	1124.8	1204.5	1307.4	1420.4
35°	674.9	698.1	720.5	754.8	793.1	849.1	915.8	1030.6	1109.7	1211.3	1324.8
37.5°	623.6	637.7	662.5	689.7	730.1	772.0	829.7	932.7	1018.3	1118.1	1234.2
40°	584.5	602.4	620.9	651.2	684.2	724.4	781.2	857.7	956.1	1053.7	1167.2
42.5°	546.6	569.1	588.7	609.0	645.1	685.4	731.6	796.5	896.9	989.3	1099.6
45°	500.8	515.3	535.7	558.2	587.9	622.2	663.1	719.8	816.1	896.0	999.6
47.5°	447.5	468.7	482.1	503.9	532.2	564.9	603.0	652.0	730.0	804.8	900.9
50°	411.0	432.8	451.9	471.7	496.8	528.5	560.2	607.7	670.4	748.9	838.6
52.5°	379.9	399.1	417.7	437.5	462.0	491.0	521.1	562.8	616.5	688.7	775.8
55°	337.2	349.0	368.2	388.0	409.7	437.5	466.5	501.4	547.6	608.3	678.9
57.5°	293.3	307.0	322.3	342.2	364.2	385.5	411.6	443.2	479.7	534.6	595.0
60°	268.5	279.1	291.6	312.1	332.5	351.6	376.8	403.1	437.5	484.9	536.4
62.5°	241.1	251.2	262.6	280.4	300.3	317.9	339.8	367.7	396.8	440.1	485.2
65°	195.3	209.8	221.0	236.9	253.4	271.8	289.0	311.4	337.2	371.4	411.7
67.5°	162.0	169.3	179.7	194.1	211.0	226.9	243.1	260.6	282.9	309.4	341.4
70°	147.1	149.8	151.8	165.6	181.4	197.3	212.5	228.9	248.1	269.8	297.6
72.5°	129.8	132.3	134.8	140.8	153.4	169.3	185.0	197.3	215.3	233.4	255.9
75°	102.9	106.9	108.8	112.2	116.8	127.3	141.9	153.7	164.3	178.1	196.0
77.5°	78.4	80.6	82.7	86.2	89.1	93.9	102.1	112.8	122.7	130.8	143.0
80°	62.0	62.7	65.3	66.6	70.6	73.9	77.8	86.4	96.3	99.6	108.2
82.5°	46.8	47.4	49.5	50.8	52.7	55.4	60.4	62.7	70.4	74.8	80.2
85°	25.7	25.1	27.0	27.0	28.4	29.7	31.0	34.3	36.2	41.6	42.9
87.5°	11.3	11.0	11.3	11.0	10.8	11.5	11.7	11.9	12.6	13.8	15.5
90°	16.6	15.8	14.3	12.9	11.5	10.2	8.4	6.5	4.6	2.7	0.8
92.5°	18.7	18.3	17.6	16.9	16.2	15.4	15.2	15.3	15.5	15.7	15.8
95°	31.5	30.7	29.4	28.2	27.0	25.7	28.1	33.8	39.6	45.4	51.1
97.5°	41.8	41.1	38.2	35.4	32.5	29.7	36.4	52.7	69.0	85.2	101.4
100°	46.2	44.9	41.8	38.9	35.9	33.0	43.4	67.3	91.3	115.2	139.2
102.5°	47.9	46.1	70.9	95.7	120.6	145.5	160.4	165.5	170.6	175.6	180.7
105°	49.9	48.0	95.7	143.4	191.1	238.8	260.0	254.8	249.5	244.3	239.0
107.5°	65.2	67.2	124.3	181.6	238.8	296.0	322.5	318.2	314.0	309.8	305.6
110°	120.1	137.6	188.1	238.6	289.1	339.6	363.0	359.4	355.7	352.1	348.4



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	283.4	347.1	359.6	372.0	384.5	397.0	401.6	398.4	395.1	391.8	388.6
115°	404.2	485.2	480.8	476.5	472.1	467.7	464.0	461.1	458.1	455.1	452.1
117.5°	517.8	537.4	534.4	531.4	528.4	525.4	522.2	518.9	515.6	512.2	508.9
120°	578.5	576.4	573.3	570.1	567.0	563.8	560.9	558.3	555.7	553.0	550.4
122.5°	614.8	613.5	610.1	606.7	603.2	599.8	596.7	593.9	591.2	588.4	585.7
125°	665.7	664.4	661.2	657.8	654.5	651.2	648.4	646.1	643.9	641.5	639.3
127.5°	712.1	710.4	707.9	705.4	702.9	700.4	697.9	695.4	692.9	690.4	687.9
130°	741.8	739.9	738.0	736.1	734.2	732.3	729.9	727.1	724.3	721.5	718.8
132.5°	771.2	769.5	767.6	765.7	763.8	761.8	759.7	757.3	754.9	752.5	750.2
135°	812.4	810.7	809.2	807.6	806.0	804.4	802.3	799.4	796.7	793.8	791.1
137.5°	850.9	849.3	847.5	845.7	843.9	842.1	840.2	838.3	836.4	834.4	832.4
140°	876.0	874.4	872.5	870.6	868.7	866.8	865.0	863.7	862.3	860.9	859.5
142.5°	899.1	897.7	895.5	893.3	891.0	888.9	887.2	885.9	884.7	883.4	882.1
145°	931.4	930.2	927.3	924.3	921.4	918.3	917.0	917.1	917.3	917.5	917.7
147.5°	959.8	958.9	956.0	953.0	950.0	947.1	946.0	946.7	947.4	948.0	948.6
150°	976.9	975.9	973.1	970.3	967.5	964.7	963.9	965.1	966.3	967.6	968.8
152.5°	992.6	991.6	988.9	986.3	983.6	980.9	980.3	981.7	983.0	984.4	985.8
155°	1013.8	1012.8	1010.7	1008.7	1006.5	1004.4	1004.2	1005.7	1007.3	1008.9	1010.5
157.5°	1031.7	1030.4	1029.0	1027.5	1026.1	1024.6	1024.5	1025.8	1027.2	1028.5	1029.8
160°	1042.2	1041.1	1040.1	1039.1	1037.9	1036.9	1036.9	1037.9	1039.1	1040.1	1041.1
162.5°	1051.7	1050.6	1049.6	1048.7	1047.8	1046.9	1047.0	1048.0	1049.1	1050.2	1051.2
165°	1063.6	1062.4	1061.9	1061.3	1060.8	1060.2	1060.5	1061.5	1062.6	1063.7	1064.7
167.5°	1073.5	1072.3	1071.8	1071.3	1070.8	1070.3	1070.6	1071.6	1072.7	1073.8	1074.8
170°	1078.5	1077.3	1076.9	1076.6	1076.2	1075.9	1076.2	1077.3	1078.3	1079.3	1080.5
172.5°	1082.3	1081.1	1080.7	1080.4	1080.0	1079.7	1080.0	1081.1	1082.1	1083.1	1084.2
175°	1086.4	1085.1	1084.8	1084.4	1084.1	1083.7	1084.2	1085.4	1086.7	1087.9	1089.1
177.5°	1087.1	1086.1	1086.0	1085.8	1085.7	1085.5	1086.0	1086.9	1088.0	1088.9	1089.9
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1910.0	1911.5	1922.1	1926.8	1936.4	1940.0	1944.3	1943.2	1943.2	1945.3	1960.1
5°	1914.1	1927.3	1947.1	1966.2	1984.7	2000.4	2011.0	2021.6	2025.6	2044.7	2061.8
7.5°	1907.2	1931.5	1964.2	1993.4	2028.3	2055.6	2078.4	2098.8	2112.8	2140.6	2169.1
10°	1898.2	1932.5	1969.5	2007.1	2055.2	2091.5	2128.5	2156.9	2166.1	2207.7	2231.5
12.5°	1880.3	1926.2	1973.2	2021.9	2069.0	2119.0	2159.6	2188.0	2220.4	2257.8	2301.6
15°	1853.4	1906.2	1967.5	2030.2	2097.5	2158.2	2201.7	2251.2	2286.8	2327.7	2366.0
17.5°	1814.7	1882.7	1960.7	2033.3	2111.1	2176.3	2236.2	2283.6	2308.8	2332.1	2337.8
20°	1784.1	1857.3	1949.0	2034.8	2112.6	2187.9	2247.2	2286.8	2293.4	2294.0	2259.1
22.5°	1750.8	1833.6	1929.5	2017.4	2110.6	2194.2	2240.4	2257.3	2231.1	2186.4	2118.7
25°	1689.7	1785.4	1896.9	1997.2	2098.8	2178.0	2193.8	2164.1	2072.4	1976.1	1854.0
27.5°	1623.5	1731.0	1850.5	1962.0	2070.3	2119.4	2085.2	1978.1	1813.0	1669.4	1495.4
30°	1574.9	1695.7	1813.1	1937.8	2038.1	2059.2	1980.7	1823.0	1630.3	1413.9	1240.4
32.5°	1519.5	1646.1	1775.1	1904.0	1988.0	1967.4	1837.6	1643.6	1417.6	1204.9	1040.9
35°	1440.3	1571.0	1710.2	1839.5	1892.9	1803.9	1609.9	1357.2	1126.3	927.6	814.9
37.5°	1348.8	1491.2	1635.9	1754.6	1750.8	1602.4	1338.2	1077.3	883.2	765.8	685.4
40°	1283.9	1427.8	1584.2	1684.5	1641.6	1448.2	1161.9	915.8	774.0	680.3	621.6
42.5°	1221.7	1366.1	1521.4	1601.0	1526.5	1288.8	1003.6	810.7	693.7	620.6	573.0
45°	1115.7	1268.1	1412.0	1456.1	1322.8	1060.9	811.6	671.7	593.8	539.7	506.7
47.5°	1012.1	1162.0	1293.3	1294.1	1113.9	860.4	684.6	581.3	514.8	472.9	448.9
50°	948.7	1091.3	1201.4	1184.3	979.8	765.3	612.3	523.2	467.8	435.5	410.4
52.5°	877.5	1015.8	1111.2	1062.4	866.3	673.5	547.3	472.5	426.6	398.5	376.1
55°	774.0	896.6	964.0	890.0	706.6	560.2	462.5	403.8	369.5	345.7	326.6
57.5°	672.2	773.4	815.8	729.7	582.0	464.5	391.2	347.2	313.1	296.1	286.2
60°	608.3	694.7	724.4	629.5	506.1	406.4	346.4	305.5	280.4	269.2	259.3
62.5°	545.5	616.1	628.4	541.3	441.2	355.8	304.2	269.6	253.0	242.3	232.9
65°	452.6	503.4	497.5	427.6	349.0	282.4	244.8	223.7	211.1	196.0	179.4
67.5°	372.6	403.6	385.0	332.5	266.4	219.5	194.9	178.9	163.3	149.0	145.2
70°	322.0	339.8	320.0	271.8	218.3	184.1	164.3	145.2	136.0	132.6	126.7
72.5°	273.5	279.7	258.2	217.0	177.7	152.4	133.1	122.4	117.4	114.7	110.8
75°	205.2	200.6	182.1	149.8	123.4	106.2	100.3	96.3	93.0	90.4	88.4
77.5°	144.1	137.3	120.9	99.8	85.9	77.7	74.1	72.1	70.4	69.1	67.2
80°	108.2	103.6	87.1	71.3	65.3	61.4	59.4	56.7	56.7	55.4	53.5
82.5°	79.2	74.0	59.7	52.3	49.0	46.6	45.1	43.6	43.0	43.3	41.8
85°	41.6	33.7	29.7	28.4	26.4	25.1	25.7	24.5	24.5	24.5	23.8
87.5°	13.2	10.9	10.8	10.7	11.5	11.8	11.5	11.9	12.7	12.3	13.0
90°	2.7	4.6	6.5	8.4	10.2	11.5	12.9	14.3	15.8	16.6	17.5
92.5°	15.7	15.5	15.3	15.2	15.4	16.2	16.9	17.6	18.3	18.7	19.1
95°	45.4	39.6	33.8	28.1	25.7	27.0	28.2	29.4	30.7	31.5	32.4
97.5°	85.2	69.0	52.7	36.4	29.7	32.5	35.4	38.2	41.1	41.8	42.4
100°	115.2	91.3	67.3	43.4	33.0	35.9	38.9	41.8	44.9	46.2	47.6
102.5°	175.6	170.6	165.5	160.4	145.5	120.6	95.7	70.9	46.1	47.9	49.7
105°	244.3	249.5	254.8	260.0	238.8	191.1	143.4	95.7	48.0	49.9	51.8
107.5°	309.8	314.0	318.2	322.5	296.0	238.8	181.6	124.3	67.2	65.2	63.2
110°	352.1	355.7	359.4	363.0	339.6	289.1	238.6	188.1	137.6	120.1	102.6



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	391.8	395.1	398.4	401.6	397.0	384.5	372.0	359.6	347.1	283.4	219.6
115°	455.1	458.1	461.1	464.0	467.7	472.1	476.5	480.8	485.2	404.2	323.4
117.5°	512.2	515.6	518.9	522.2	525.4	528.4	531.4	534.4	537.4	517.8	498.3
120°	553.0	555.7	558.3	560.9	563.8	567.0	570.1	573.3	576.4	578.5	580.6
122.5°	588.4	591.2	593.9	596.7	599.8	603.2	606.7	610.1	613.5	614.8	616.0
125°	641.5	643.9	646.1	648.4	651.2	654.5	657.8	661.2	664.4	665.7	666.9
127.5°	690.4	692.9	695.4	697.9	700.4	702.9	705.4	707.9	710.4	712.1	713.9
130°	721.5	724.3	727.1	729.9	732.3	734.2	736.1	738.0	739.9	741.8	743.8
132.5°	752.5	754.9	757.3	759.7	761.8	763.8	765.7	767.6	769.5	771.2	772.8
135°	793.8	796.7	799.4	802.3	804.4	806.0	807.6	809.2	810.7	812.4	814.2
137.5°	834.4	836.4	838.3	840.2	842.1	843.9	845.7	847.5	849.3	850.9	852.6
140°	860.9	862.3	863.7	865.0	866.8	868.7	870.6	872.5	874.4	876.0	877.5
142.5°	883.4	884.7	885.9	887.2	888.9	891.0	893.3	895.5	897.7	899.1	900.5
145°	917.5	917.3	917.1	917.0	918.3	921.4	924.3	927.3	930.2	931.4	932.7
147.5°	948.0	947.4	946.7	946.0	947.1	950.0	953.0	956.0	958.9	959.8	960.7
150°	967.6	966.3	965.1	963.9	964.7	967.5	970.3	973.1	975.9	976.9	977.9
152.5°	984.4	983.0	981.7	980.3	980.9	983.6	986.3	988.9	991.6	992.6	993.7
155°	1008.9	1007.3	1005.7	1004.2	1004.4	1006.5	1008.7	1010.7	1012.8	1013.8	1014.9
157.5°	1028.5	1027.2	1025.8	1024.5	1024.6	1026.1	1027.5	1029.0	1030.4	1031.7	1032.8
160°	1040.1	1039.1	1037.9	1036.9	1036.9	1037.9	1039.1	1040.1	1041.1	1042.2	1043.2
162.5°	1050.2	1049.1	1048.0	1047.0	1046.9	1047.8	1048.7	1049.6	1050.6	1051.7	1052.9
165°	1063.7	1062.6	1061.5	1060.5	1060.2	1060.8	1061.3	1061.9	1062.4	1063.6	1064.8
167.5°	1073.8	1072.7	1071.6	1070.6	1070.3	1070.8	1071.3	1071.8	1072.3	1073.5	1074.7
170°	1079.3	1078.3	1077.3	1076.2	1075.9	1076.2	1076.6	1076.9	1077.3	1078.5	1079.8
172.5°	1083.1	1082.1	1081.1	1080.0	1079.7	1080.0	1080.4	1080.7	1081.1	1082.3	1083.5
175°	1087.9	1086.7	1085.4	1084.2	1083.7	1084.1	1084.4	1084.8	1085.1	1086.4	1087.6
177.5°	1088.9	1088.0	1086.9	1086.0	1085.5	1085.7	1085.8	1086.0	1086.1	1087.1	1088.0
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1965.4	1972.2	1975.4	1975.4	1979.1	1977.5	1975.9
5°	2078.4	2090.9	2093.5	2105.4	2113.9	2111.3	2112.6
7.5°	2190.6	2210.8	2230.8	2239.9	2241.3	2246.6	2248.6
10°	2259.8	2276.3	2307.3	2302.7	2325.7	2339.0	2317.2
12.5°	2326.2	2348.5	2370.1	2376.0	2389.1	2393.3	2384.7
15°	2386.4	2398.3	2399.7	2396.3	2400.3	2397.0	2384.5
17.5°	2330.2	2311.0	2271.9	2253.4	2238.8	2217.2	2208.5
20°	2237.3	2180.6	2114.6	2088.3	2057.2	1996.5	2011.0
22.5°	2036.8	1972.1	1906.2	1829.1	1792.3	1734.7	1731.3
25°	1724.7	1613.2	1490.5	1404.7	1354.5	1297.2	1272.0
27.5°	1340.9	1200.6	1100.0	1049.0	1002.7	957.3	955.4
30°	1088.6	983.1	905.3	861.7	833.3	814.2	818.1
32.5°	917.7	845.3	792.8	756.6	735.6	721.3	721.0
35°	750.2	700.7	667.0	651.9	636.7	626.1	626.8
37.5°	642.0	612.3	593.6	576.8	567.3	562.1	559.2
40°	586.5	562.1	547.6	537.7	529.8	522.5	521.2
42.5°	542.8	522.5	508.1	500.2	492.8	487.8	486.4
45°	481.6	465.1	451.9	443.4	440.1	435.5	435.5
47.5°	428.4	412.2	401.9	396.6	390.9	387.8	387.7
50°	392.6	380.0	370.8	367.5	362.9	360.9	360.2
52.5°	360.4	351.0	344.4	342.2	340.2	337.7	338.1
55°	316.7	311.4	308.8	306.8	303.5	299.5	302.2
57.5°	279.9	275.4	268.3	262.1	259.1	256.2	257.4
60°	254.0	244.8	235.6	228.3	226.3	220.3	220.3
62.5°	221.3	208.4	197.0	193.0	191.0	188.2	187.6
65°	170.2	165.0	162.3	159.6	158.3	158.3	157.0
67.5°	141.0	139.0	136.0	135.3	134.1	133.7	133.3
70°	124.7	122.1	120.7	120.1	118.7	119.4	117.4
72.5°	108.8	106.8	106.5	104.8	104.0	104.1	102.6
75°	85.8	85.8	85.2	84.5	83.2	82.5	83.2
77.5°	66.0	66.1	64.9	64.8	64.7	64.8	64.1
80°	52.8	53.5	52.8	52.1	51.5	52.1	51.5
82.5°	41.7	40.8	40.6	40.6	40.4	40.0	39.9
85°	23.8	24.5	23.8	23.1	23.1	23.1	23.8
87.5°	12.7	12.8	12.9	13.0	13.1	13.2	12.7
90°	18.3	19.2	19.8	20.1	20.5	20.9	21.3
92.5°	19.6	20.1	20.4	20.6	20.8	21.0	21.3
95°	33.3	34.2	34.5	34.4	34.2	34.0	33.8
97.5°	43.1	43.8	44.3	44.5	44.7	44.9	45.1
100°	49.0	50.5	51.3	51.7	52.0	52.3	52.7
102.5°	51.6	53.4	54.5	55.0	55.4	56.0	56.5
105°	53.7	55.6	57.0	57.7	58.4	59.1	59.8
107.5°	61.3	59.3	58.7	59.4	60.1	60.8	61.5
110°	85.2	67.7	59.3	60.0	60.7	61.4	62.2



TEST NUMBER: P331753-935

CATALOG NUMBER: S122RDIP-S1005D925U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	155.8	92.1	60.5	61.0	61.6	62.2	62.8
115°	242.5	161.5	114.8	102.2	89.6	77.1	64.5
117.5°	478.7	459.1	428.6	387.3	345.9	304.6	263.3
120°	582.7	584.8	574.0	550.4	526.8	503.3	479.7
122.5°	617.3	618.5	616.9	612.3	607.7	603.1	598.6
125°	668.1	669.3	670.2	670.7	671.2	671.8	672.4
127.5°	715.7	717.6	718.4	718.6	718.7	718.8	718.8
130°	745.7	747.6	748.6	748.4	748.1	748.0	747.8
132.5°	774.5	776.1	776.8	776.6	776.4	776.3	776.1
135°	816.0	817.7	818.4	818.0	817.7	817.3	817.0
137.5°	854.4	856.1	856.7	856.1	855.5	854.9	854.3
140°	879.2	880.7	881.1	880.2	879.3	878.5	877.5
142.5°	902.0	903.4	903.7	902.8	902.0	901.1	900.2
145°	933.9	935.1	935.3	934.4	933.6	932.7	931.9
147.5°	961.6	962.5	962.6	961.8	961.1	960.4	959.7
150°	979.0	980.1	980.2	979.3	978.4	977.5	976.6
152.5°	994.7	995.7	995.7	994.5	993.4	992.3	991.1
155°	1016.0	1017.0	1016.8	1015.5	1014.0	1012.6	1011.2
157.5°	1034.0	1035.2	1035.1	1033.7	1032.3	1031.0	1029.7
160°	1044.3	1045.3	1045.3	1044.0	1042.8	1041.6	1040.3
162.5°	1054.1	1055.3	1055.2	1053.7	1052.1	1050.7	1049.1
165°	1066.0	1067.2	1067.2	1066.0	1064.8	1063.6	1062.4
167.5°	1075.9	1077.2	1076.9	1075.4	1073.8	1072.3	1070.7
170°	1081.0	1082.2	1082.0	1080.5	1078.8	1077.3	1075.7
172.5°	1084.8	1086.0	1085.8	1084.2	1082.6	1081.1	1079.5
175°	1088.8	1090.0	1089.8	1088.0	1086.3	1084.5	1082.8
177.5°	1089.1	1090.0	1089.9	1088.6	1087.4	1086.1	1084.9
180°	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8	1086.8

(END OF REPORT)