

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644348

Luminaire Tested: CRQ4DIP-SR4F0-50D150U935-FLLOOB-1DUDD-WW

Issue Date: 2/20/2023



**Test Information**

Test Method: LM-79-2019  
Report Number: P644348  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/20/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: CRQ4DIP-SR4F0-50D150U935-FLLOOB-1DUDD-WW  
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE  
DOWNLIGHT - CURVED FROSTED LENS - 500 LUMENS PER FOOT  
UPLIGHT - BATWING OPTIC - 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7111.1 lumens  
Efficiency: N/A  
Efficacy: 113.1 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.3  
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.33')  
CIE Type: Semi-Indirect

Input Watts (W): 62.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P644348

CATALOG NUMBER: CRQ4DIP-SR4F0-50D150U935-FLLOOB-1DUDD-WW

### Luminous Intensity Polar Plot





TEST NUMBER: P644348

CATALOG NUMBER: CRQ4DIP-SR4F0-50D150U935-FLLOOB-1DUDD-WW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	92	88	84	81	82	78	75	72	61	59	57	44	43	42	29	29	28	21
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	24	18
3	76	67	60	55	68	60	54	50	47	43	39	34	32	30	23	21	20	15
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	20	19	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	17	15	11
6	59	47	40	34	52	42	36	31	33	29	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	20	17	19	16	13	13	11	9	7
10	44	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	9	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11431	11431	11431
5°	11215	10093	9780
10°	11068	8980	8448
15°	10906	8042	7390
20°	10656	7214	6463
25°	10323	6442	5632
30°	9997	5692	4889
35°	9554	5006	4196
40°	9141	4383	3557
45°	8663	3767	2968
50°	8157	3190	2435
55°	7622	2684	1964
60°	7111	2200	1570
65°	6482	1754	1242
70°	5877	1375	981
75°	5139	1056	774
80°	4294	785	603
85°	3131	571	458

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8663 cd/sqm



TEST NUMBER: P644348

CATALOG NUMBER: CRQ4DIP-SR4F0-50D150U935-FLLOOB-1DUDD-WW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	66.8	0.9
10°-20°	189.6	2.7
20°-30°	279.9	3.9
30°-40°	321.8	4.5
40°-50°	312.2	4.4
50°-60°	261.3	3.7
60°-70°	188.3	2.6
70°-80°	115.0	1.6
80°-90°	58.1	0.8
90°-100°	143.1	2.0
100°-110°	869.8	12.2
110°-120°	1172.7	16.5
120°-130°	953.4	13.4
130°-140°	766.0	10.8
140°-150°	603.8	8.5
150°-160°	441.5	6.2
160°-170°	274.2	3.9
170°-180°	93.5	1.3
0°-30°	536.4	7.5
0°-40°	858.2	12.1
0°-60°	1431.8	20.1
0°-90°	1793.2	25.2
90°-120°	2185.5	30.7
90°-150°	4508.6	63.4
90°-180°	5318.0	74.8
0°-180°	7111.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	708	708	708	708	708	
5°	697	710	703	704	709	66
15°	667	677	671	674	679	188
25°	602	612	610	607	611	277
35°	513	521	516	511	511	321
45°	411	415	408	396	390	317
55°	303	307	296	278	269	272
65°	200	201	191	177	172	199
75°	108	108	110	107	105	115
85°	33	40	55	59	59	35
90°	3	26	48	61	62	6
95°	60	101	70	84	97	64
105°	202	299	1125	1439	958	213
115°	347	416	967	2008	2346	345
125°	493	557	910	1590	1881	438
135°	606	673	916	1310	1503	467
145°	718	778	922	1141	1262	451
155°	841	872	940	1034	1083	386
165°	934	946	965	990	1008	262
175°	984	990	984	977	971	93
180°	984	984	984	984	984	



TEST NUMBER: P644348

CATALOG NUMBER: CRQ4DIP-SR4F0-50D150U935-FLLOOB-1DUDD-WW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	708.0	708.0	708.0	708.0	708.0
2.5°	701.6	711.8	705.6	707.2	708.0
5°	697.0	709.7	703.0	704.1	709.0
7.5°	690.6	702.3	696.4	697.7	703.4
10°	685.0	696.7	690.0	692.1	697.0
12.5°	677.8	688.7	683.6	685.7	690.6
15°	667.0	676.8	671.0	674.1	679.0
17.5°	651.0	661.6	655.4	657.1	662.0
20°	639.0	648.8	645.0	645.1	650.0
22.5°	624.6	635.2	632.2	629.9	635.6
25°	602.0	611.8	610.0	607.1	611.0
27.5°	579.6	586.8	583.4	580.5	583.4
30°	562.0	570.8	565.0	562.1	565.0
32.5°	542.8	551.6	545.8	542.0	543.4
35°	513.0	520.8	516.0	511.0	511.0
37.5°	484.8	489.9	486.6	478.2	476.0
40°	464.0	469.9	465.0	454.9	452.0
42.5°	442.4	448.3	442.6	431.7	427.2
45°	411.0	414.9	408.0	395.9	390.0
47.5°	378.6	382.7	373.2	359.8	352.8
50°	357.0	361.9	350.0	335.8	328.0
52.5°	336.2	339.5	328.4	311.8	304.8
55°	303.0	306.9	296.0	277.8	269.0
57.5°	272.0	275.7	262.8	245.4	238.6
60°	252.0	254.9	242.0	223.8	217.0
62.5°	229.6	232.5	220.4	204.6	197.8
65°	200.0	201.0	191.0	176.9	172.0
67.5°	172.2	172.2	163.8	153.3	149.4
70°	153.0	153.0	147.0	138.9	135.0
72.5°	135.4	134.6	131.0	125.3	122.2
75°	108.0	108.0	110.0	107.0	105.0
77.5°	84.0	82.4	91.0	90.6	89.6
80°	68.0	68.0	79.0	81.0	80.0
82.5°	53.6	55.2	69.4	72.2	71.2
85°	33.0	39.8	55.0	59.0	59.0
87.5°	15.0	28.1	45.7	52.1	52.3
90°	3.0	25.7	48.4	60.6	61.6
92.5°	21.0	35.9	56.8	74.1	80.7
95°	59.5	100.9	70.5	84.0	97.0
97.5°	99.8	182.1	378.9	128.3	115.0
100°	129.5	225.5	742.0	231.9	161.3
102.5°	158.4	259.3	996.1	580.8	325.5
105°	201.8	298.7	1124.7	1439.4	957.5
107.5°	245.1	316.9	1071.8	2087.4	1956.5
110°	274.0	341.7	1041.3	2191.4	2355.7



TEST NUMBER: P644348

CATALOG NUMBER: CRQ4DIP-SR4F0-50D150U935-FLLOOB-1DUDD-WW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	303.7	371.4	1011.6	2128.0	2403.6
115°	347.2	415.9	967.0	2007.8	2346.5
117.5°	391.8	460.5	955.7	1876.9	2225.3
120°	425.7	490.2	935.1	1777.5	2140.4
122.5°	450.4	519.0	910.4	1692.7	2026.6
125°	492.7	557.3	910.4	1590.2	1880.6
127.5°	527.4	594.3	911.6	1471.4	1758.1
130°	546.4	619.0	916.5	1391.9	1664.1
132.5°	569.5	642.1	915.7	1356.1	1579.9
135°	606.2	672.8	915.5	1309.7	1503.2
137.5°	637.2	708.5	915.5	1258.3	1424.0
140°	661.9	728.5	915.5	1228.3	1379.5
142.5°	686.7	748.4	920.5	1193.4	1335.0
145°	717.6	778.1	921.7	1141.0	1262.0
147.5°	754.7	807.9	929.2	1103.2	1196.4
150°	779.5	827.8	934.1	1078.2	1156.8
152.5°	804.2	847.7	934.1	1058.0	1122.2
155°	841.3	871.6	940.3	1034.2	1082.6
157.5°	871.0	900.0	947.7	1019.0	1054.1
160°	890.8	915.0	952.7	1009.0	1039.3
162.5°	905.7	929.8	957.6	1003.9	1024.4
165°	934.1	946.2	965.0	990.2	1008.3
167.5°	950.2	961.1	971.2	983.8	994.7
170°	965.0	971.1	971.2	983.7	989.8
172.5°	970.0	980.9	976.2	978.8	984.8
175°	983.6	989.6	983.6	977.3	971.2
177.5°	983.6	988.4	983.6	983.5	978.6
180°	983.6	983.6	983.6	983.6	983.6

(END OF REPORT)