

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644420

Luminaire Tested: CRQ4DIP-SR4F0-75D150U935-FLLOOB-1DUDD-WW

Issue Date: 2/20/2023



Test Information

Test Method: LM-79-2019
Report Number: P644420
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-14)
Test Lab: INNOVATION CENTER
Issue Date: 2/20/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: CRQ4DIP-SR4F0-75D150U935-FLLOOB-1DUDD-WW
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE
DOWNLIGHT - CURVED FROSTED LENS - 750 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 1500 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7990.4 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.33')
CIE Type: Semi-Indirect

Input Watts (W): 70.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644420

CATALOG NUMBER: CRQ4DIP-SR4F0-75D150U935-FLLOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644420

CATALOG NUMBER: CRQ4DIP-SR4F0-75D150U935-FLLOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	82	84	81	78	75	65	62	60	50	48	47	36	35	34	28
2	85	78	72	67	77	71	66	61	57	53	50	44	41	39	32	30	29	23
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25	20
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21	17
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18	15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12
8	52	40	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16939	16939	16939
5°	16618	14956	14492
10°	16400	13306	12518
15°	16159	11916	10950
20°	15789	10689	9577
25°	15297	9546	8345
30°	14812	8435	7244
35°	14156	7418	6218
40°	13543	6494	5270
45°	12836	5582	4399
50°	12087	4727	3608
55°	11295	3978	2910
60°	10537	3260	2326
65°	9604	2600	1841
70°	8708	2037	1454
75°	7613	1565	1147
80°	6364	1164	893
85°	4640	846	679

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12836 cd/sqm



TEST NUMBER: P644420

CATALOG NUMBER: CRQ4DIP-SR4F0-75D150U935-FLLOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.0	1.2
10°-20°	281.0	3.5
20°-30°	414.8	5.2
30°-40°	476.9	6.0
40°-50°	462.6	5.8
50°-60°	387.3	4.8
60°-70°	279.0	3.5
70°-80°	170.5	2.1
80°-90°	85.0	1.1
90°-100°	153.7	1.9
100°-110°	873.6	10.9
110°-120°	1174.1	14.7
120°-130°	953.9	11.9
130°-140°	766.0	9.6
140°-150°	603.8	7.6
150°-160°	441.5	5.5
160°-170°	274.2	3.4
170°-180°	93.5	1.2
0°-30°	794.8	9.9
0°-40°	1271.7	15.9
0°-60°	2121.6	26.6
0°-90°	2656.1	33.2
90°-120°	2201.4	27.6
90°-150°	4525.1	56.6
90°-180°	5334.0	66.8
0°-180°	7990.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1049	1049	1049	1049	1049	
5°	1033	1052	1042	1043	1051	98
15°	988	1003	994	999	1006	278
25°	892	906	904	900	905	411
35°	760	772	765	757	757	476
45°	609	615	605	587	578	469
55°	449	455	439	412	399	403
65°	296	298	283	262	255	295
75°	160	160	163	158	156	171
85°	49	59	82	87	87	52
90°	4	35	66	81	82	8
95°	64	105	81	98	111	68
105°	207	301	1127	1444	963	218
115°	351	417	968	2009	2348	348
125°	495	558	911	1590	1881	439
135°	606	673	916	1310	1503	467
145°	718	778	922	1141	1262	451
155°	841	872	940	1034	1083	386
165°	934	946	965	990	1008	262
175°	984	990	984	977	971	93
180°	984	984	984	984	984	

TEST NUMBER: P644420

CATALOG NUMBER: CRQ4DIP-SR4F0-75D150U935-FLLOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1049.1	1049.1	1049.1	1049.1	1049.1
2.5°	1039.6	1054.7	1045.5	1047.9	1049.1
5°	1032.8	1051.6	1041.7	1043.3	1050.6
7.5°	1023.3	1040.7	1031.9	1033.9	1042.3
10°	1015.0	1032.4	1022.4	1025.5	1032.8
12.5°	1004.3	1020.6	1012.9	1016.0	1023.3
15°	988.3	1002.8	994.3	998.9	1006.1
17.5°	964.6	980.3	971.1	973.7	980.9
20°	946.8	961.3	955.7	955.9	963.1
22.5°	925.5	941.1	936.8	933.4	941.8
25°	892.0	906.5	903.9	899.6	905.3
27.5°	858.8	869.5	864.5	860.1	864.5
30°	832.7	845.8	837.2	832.8	837.2
32.5°	804.3	817.3	808.7	803.2	805.2
35°	760.1	771.7	764.6	757.2	757.2
37.5°	718.4	725.9	721.0	708.5	705.3
40°	687.5	696.2	689.0	674.1	669.7
42.5°	655.5	664.2	655.8	639.7	633.0
45°	609.0	614.8	604.6	586.6	577.9
47.5°	561.0	567.1	553.0	533.2	522.8
50°	529.0	536.2	518.6	497.6	486.0
52.5°	498.2	503.1	486.6	462.1	451.6
55°	449.0	454.8	438.6	411.6	398.6
57.5°	403.0	408.5	389.4	363.7	353.5
60°	373.4	377.7	358.6	331.7	321.5
62.5°	340.2	344.6	326.6	303.2	293.1
65°	296.3	297.8	283.0	262.1	254.9
67.5°	255.2	255.2	242.7	227.2	221.4
70°	226.7	226.7	217.8	205.8	200.0
72.5°	200.6	199.5	194.1	185.7	181.1
75°	160.0	160.0	163.0	158.5	155.6
77.5°	124.5	122.1	134.8	134.2	132.8
80°	100.8	100.8	117.1	120.0	118.5
82.5°	79.4	81.7	102.8	106.9	105.5
85°	48.9	59.0	81.5	87.4	87.4
87.5°	22.2	41.1	66.5	75.4	75.7
90°	4.4	35.1	65.7	80.8	82.3
92.5°	24.0	43.1	71.1	91.3	98.7
95°	64.3	105.2	80.6	97.5	111.0
97.5°	105.6	185.0	386.3	138.5	125.7
100°	135.3	228.0	747.7	240.1	170.4
102.5°	163.8	261.4	1000.3	587.5	332.8
105°	206.6	300.7	1127.1	1443.8	962.8
107.5°	249.3	318.4	1073.1	2090.1	1959.6
110°	277.9	343.2	1042.2	2193.4	2358.1



TEST NUMBER: P644420

CATALOG NUMBER: CRQ4DIP-SR4F0-75D150U935-FLLOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	307.6	372.9	1012.5	2129.2	2405.3
115°	350.6	417.4	968.0	2008.8	2347.5
117.5°	394.6	461.9	956.6	1877.3	2225.7
120°	428.1	491.7	935.6	1777.5	2140.4
122.5°	452.8	520.1	910.8	1692.7	2026.6
125°	494.6	558.3	910.8	1590.2	1880.6
127.5°	528.7	595.3	912.1	1471.4	1758.1
130°	547.3	619.9	917.0	1391.9	1664.1
132.5°	569.7	642.3	915.8	1356.1	1579.9
135°	606.2	672.8	915.5	1309.7	1503.2
137.5°	637.2	708.5	915.5	1258.3	1424.0
140°	661.9	728.5	915.5	1228.3	1379.5
142.5°	686.7	748.4	920.5	1193.4	1335.0
145°	717.6	778.1	921.7	1141.0	1262.0
147.5°	754.7	807.9	929.2	1103.2	1196.4
150°	779.5	827.8	934.1	1078.2	1156.8
152.5°	804.2	847.7	934.1	1058.0	1122.2
155°	841.3	871.6	940.3	1034.2	1082.6
157.5°	871.0	900.0	947.7	1019.0	1054.1
160°	890.8	915.0	952.7	1009.0	1039.3
162.5°	905.7	929.8	957.6	1003.9	1024.4
165°	934.1	946.2	965.0	990.2	1008.3
167.5°	950.2	961.1	971.2	983.8	994.7
170°	965.0	971.1	971.2	983.7	989.8
172.5°	970.0	980.9	976.2	978.8	984.8
175°	983.6	989.6	983.6	977.3	971.2
177.5°	983.6	988.4	983.6	983.5	978.6
180°	983.6	983.6	983.6	983.6	983.6

(END OF REPORT)