

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P644356

Luminaire Tested: CRQ4DIP-SR4F0-50D25U840-FLLOOB-1DUDD-WW

Issue Date: 2/20/2023



Test Information

Test Method: LM-79-2019
Report Number: P644356
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2206-689-14)
Test Lab: INNOVATION CENTER
Issue Date: 2/20/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: CRQ4DIP-SR4F0-50D25U840-FLLOOB-1DUDD-WW
Description: NEO-RAY CIRQUE SUSPENDED LED LUMINAIRE
DOWNLIGHT - CURVED FROSTED LENS - 500 LUMENS PER FOOT
UPLIGHT - BATWING OPTIC - 250 LUMENS PER FOOT
Light Source: 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3185.9 lumens
Efficiency: N/A
Efficacy: 141.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.33')
CIE Type: Semi-Direct

Input Watts (W): 22.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P644356
CATALOG NUMBER: CRQ4DIP-SR4F0-50D25U840-FLLOOB-1DUDD-WW

Luminous Intensity Polar Plot





TEST NUMBER: P644356

CATALOG NUMBER: CRQ4DIP-SR4F0-50D25U840-FLLOOB-1DUDD-WW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66
1	101	96	92	89	95	91	87	84	80	78	75	71	69	67	62	60	59	55
2	92	84	78	73	86	80	74	69	71	66	62	62	59	56	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	43	39
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	43	40	37	34
5	71	59	51	44	66	56	48	43	50	44	39	44	39	36	39	35	32	29
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25	23
8	56	44	36	30	53	42	34	29	37	31	27	34	29	25	30	26	23	21
9	53	40	32	27	49	38	31	26	34	29	24	31	26	22	28	24	21	19
10	49	37	29	25	46	35	28	24	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13322	13322	13322
5°	13070	11763	11398
10°	12899	10465	9846
15°	12709	9372	8612
20°	12419	8408	7532
25°	12031	7508	6564
30°	11651	6634	5698
35°	11133	5834	4890
40°	10651	5108	4146
45°	10096	4390	3459
50°	9505	3718	2838
55°	8882	3129	2288
60°	8288	2564	1829
65°	7555	2045	1448
70°	6849	1602	1143
75°	5991	1231	902
80°	5001	915	702
85°	3653	666	534

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10096 cd/sqm



TEST NUMBER: P644356

CATALOG NUMBER: CRQ4DIP-SR4F0-50D25U840-FLLOOB-1DUDD-WW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.9	2.4
10°-20°	221.0	6.9
20°-30°	326.2	10.2
30°-40°	375.1	11.8
40°-50°	363.8	11.4
50°-60°	304.6	9.6
60°-70°	219.4	6.9
70°-80°	134.1	4.2
80°-90°	65.6	2.1
90°-100°	50.0	1.6
100°-110°	181.9	5.7
110°-120°	237.6	7.5
120°-130°	192.1	6.0
130°-140°	153.6	4.8
140°-150°	120.9	3.8
150°-160°	88.4	2.8
160°-170°	54.9	1.7
170°-180°	18.7	0.6
0°-30°	625.1	19.6
0°-40°	1000.2	31.4
0°-60°	1668.6	52.4
0°-90°	2087.7	65.5
90°-120°	469.5	14.7
90°-150°	936.1	29.4
90°-180°	1098.0	34.5
0°-180°	3185.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	825	825	825	825	825	
5°	812	827	819	821	826	77
15°	777	789	782	786	791	219
25°	702	713	711	708	712	323
35°	598	607	601	596	596	374
45°	479	484	476	461	454	369
55°	353	358	345	324	314	317
65°	233	234	223	206	200	232
75°	126	126	128	125	122	135
85°	38	46	64	69	69	41
90°	4	24	44	53	54	5
95°	22	29	34	44	47	21
105°	50	64	230	297	202	53
115°	76	86	196	404	472	76
125°	102	114	183	318	377	91
135°	121	135	183	262	301	94
145°	144	156	185	228	253	90
155°	168	175	188	207	217	77
165°	187	190	193	198	202	53
175°	197	198	197	196	194	19
180°	197	197	197	197	197	

TEST NUMBER: P644356

CATALOG NUMBER: CRQ4DIP-SR4F0-50D25U840-FLLOOB-1DUDD-WW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	825.1	825.1	825.1	825.1	825.1
2.5°	817.6	829.5	822.3	824.2	825.1
5°	812.3	827.1	819.3	820.6	826.3
7.5°	804.8	818.5	811.6	813.1	819.7
10°	798.3	812.0	804.1	806.6	812.3
12.5°	789.9	802.7	796.7	799.1	804.8
15°	777.3	788.7	782.0	785.6	791.3
17.5°	758.7	771.0	763.8	765.8	771.5
20°	744.7	756.1	751.7	751.8	757.5
22.5°	727.9	740.2	736.8	734.1	740.7
25°	701.6	713.0	710.9	707.5	712.1
27.5°	675.5	683.9	679.9	676.5	679.9
30°	655.0	665.2	658.5	655.0	658.5
32.5°	632.6	642.8	636.1	631.7	633.3
35°	597.8	607.0	601.3	595.5	595.5
37.5°	565.0	570.9	567.1	557.2	554.7
40°	540.7	547.6	541.9	530.2	526.8
42.5°	515.6	522.4	515.8	503.1	497.9
45°	479.0	483.5	475.5	461.3	454.5
47.5°	441.2	446.0	434.9	419.4	411.2
50°	416.0	421.7	407.9	391.4	382.3
52.5°	391.8	395.7	382.7	363.4	355.2
55°	353.1	357.7	345.0	323.7	313.5
57.5°	317.0	321.3	306.3	286.0	278.1
60°	293.7	297.1	282.0	260.9	252.9
62.5°	267.6	271.0	256.9	238.5	230.5
65°	233.1	234.2	222.6	206.1	200.4
67.5°	200.7	200.7	190.9	178.7	174.1
70°	178.3	178.3	171.3	161.9	157.3
72.5°	157.8	156.9	152.7	146.1	142.4
75°	125.9	125.9	128.2	124.6	122.4
77.5°	97.9	96.1	106.1	105.6	104.4
80°	79.2	79.2	92.1	94.4	93.2
82.5°	62.5	64.3	80.9	84.1	83.0
85°	38.5	46.4	64.1	68.8	68.8
87.5°	17.5	31.6	50.8	57.2	57.4
90°	3.5	24.1	44.4	52.7	53.8
92.5°	10.2	21.7	39.9	49.2	52.3
95°	21.6	28.9	34.4	43.9	47.4
97.5°	31.6	42.2	90.6	46.0	44.5
100°	37.5	50.1	160.2	62.9	50.6
102.5°	42.5	56.1	208.0	129.7	79.7
105°	50.1	63.8	230.1	297.0	202.4
107.5°	57.6	66.5	217.4	423.5	398.2
110°	62.6	71.4	210.5	442.8	476.7



TEST NUMBER: P644356

CATALOG NUMBER: CRQ4DIP-SR4F0-50D25U840-FLLOOB-1DUDD-WW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	68.5	77.4	204.5	428.6	484.7
115°	76.3	86.3	195.6	404.1	471.9
117.5°	84.1	95.2	193.2	376.7	446.5
120°	90.1	101.1	188.3	356.0	428.7
122.5°	95.0	106.1	183.3	339.0	405.9
125°	102.5	113.6	183.3	318.5	376.7
127.5°	108.3	121.0	183.6	294.7	352.1
130°	111.4	125.9	184.5	278.8	333.3
132.5°	114.5	129.0	183.6	271.6	316.4
135°	121.4	134.8	183.4	262.3	301.1
137.5°	127.6	141.9	183.4	252.0	285.2
140°	132.6	145.9	183.4	246.0	276.3
142.5°	137.5	149.9	184.4	239.0	267.4
145°	143.7	155.8	184.6	228.5	252.8
147.5°	151.2	161.8	186.1	221.0	239.6
150°	156.1	165.8	187.1	216.0	231.7
152.5°	161.1	169.8	187.1	211.9	224.8
155°	168.5	174.6	188.3	207.1	216.8
157.5°	174.5	180.3	189.8	204.1	211.1
160°	178.4	183.3	190.8	202.1	208.2
162.5°	181.4	186.2	191.8	201.1	205.2
165°	187.1	189.5	193.3	198.3	202.0
167.5°	190.3	192.5	194.5	197.1	199.2
170°	193.3	194.5	194.5	197.0	198.2
172.5°	194.3	196.5	195.5	196.0	197.3
175°	197.0	198.2	197.0	195.7	194.5
177.5°	197.0	198.0	197.0	197.0	196.0
180°	197.0	197.0	197.0	197.0	197.0

(END OF REPORT)