

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331660-935

Luminaire Tested: **S122RDIP-S485D725U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331660-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S485D725U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3957.9 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331660-935

CATALOG NUMBER: S122RDIP-S485D725U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331660-935

CATALOG NUMBER: S122RDIP-S485D725U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	23
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24	20
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	23	22	18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	21	19	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13
9	49	38	30	25	45	35	28	24	29	24	20	23	20	17	18	16	14	12
10	46	34	27	23	42	32	26	21	27	22	18	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11472	11472	11472
5°	11515	11329	11391
10°	11429	11144	11049
15°	11296	10813	10502
20°	11115	10340	9821
25°	10929	9805	9164
30°	10670	9257	8321
35°	10419	8657	7579
40°	10163	8037	6721
45°	9866	7341	5948
50°	9560	6636	5184
55°	9250	5883	4453
60°	8887	5089	3694
65°	8478	4271	3366
70°	7983	3522	3097
75°	7380	3206	2888
80°	6518	2864	2631
85°	5113	2260	2260



TEST NUMBER: P331660-935

CATALOG NUMBER: S122RDIP-S485D725U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	1.7
10°-20°	182.6	4.6
20°-30°	256.4	6.5
30°-40°	279.6	7.1
40°-50°	257.1	6.5
50°-60°	201.9	5.1
60°-70°	131.7	3.3
70°-80°	67.9	1.7
80°-90°	19.7	0.5
90°-100°	28.4	0.7
100°-110°	104.1	2.6
110°-120°	278.3	7.0
120°-130°	459.4	11.6
130°-140°	488.6	12.3
140°-150°	454.1	11.5
150°-160°	365.1	9.2
160°-170°	235.3	5.9
170°-180°	81.0	2.0
0°-30°	505.6	12.8
0°-40°	785.2	19.8
0°-60°	1244.3	31.4
0°-90°	1463.5	37.0
90°-120°	410.8	10.4
90°-150°	1813.0	45.8
90°-180°	2494.0	63.0
0°-180°	3957.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	710	710	710	710	710	
5°	710	707	699	704	703	67
15°	676	668	647	635	628	190
25°	614	592	550	525	514	282
35°	529	494	439	400	384	331
45°	432	388	322	278	260	334
55°	329	277	209	172	158	293
65°	222	169	112	91	88	220
75°	118	75	51	47	46	125
85°	28	15	12	12	12	33
90°	1	7	12	15	17	3
95°	40	21	24	27	26	49
105°	187	195	38	44	47	200
115°	354	365	380	108	50	349
125°	501	509	520	525	527	446
135°	620	629	635	641	640	478
145°	719	719	729	732	730	449
155°	791	787	793	796	792	365
165°	834	830	832	836	832	236
175°	853	849	850	854	848	81
180°	851	851	851	851	851	



TEST NUMBER: P331660-935

CATALOG NUMBER: S122RDIP-S485D725U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	713.1	712.6	712.0	711.4	710.8	709.9	708.7	707.4	706.1	704.9	706.0
5°	710.5	709.8	709.1	708.4	707.7	706.4	704.6	702.7	700.9	699.0	700.3
7.5°	703.2	702.3	701.5	700.5	699.6	698.1	695.9	693.8	691.6	689.5	689.8
10°	697.1	696.0	695.0	694.1	693.0	691.1	688.3	685.4	682.5	679.7	679.2
12.5°	689.3	688.1	686.8	685.6	684.4	682.0	678.3	674.7	671.0	667.4	666.6
15°	675.8	674.2	672.7	671.1	669.5	666.3	661.4	656.6	651.8	646.9	644.2
17.5°	659.3	656.9	654.4	652.0	649.6	645.3	639.1	632.8	626.6	620.4	617.2
20°	646.9	644.0	641.2	638.3	635.4	630.4	623.3	616.1	609.0	601.8	598.3
22.5°	633.5	630.3	627.1	623.9	620.7	615.1	607.0	598.9	590.9	582.8	578.2
25°	613.5	608.9	604.3	599.7	595.1	588.1	578.7	569.3	559.8	550.4	544.6
27.5°	589.3	584.3	579.3	574.4	569.4	561.5	551.0	540.3	529.7	519.0	512.2
30°	572.3	566.9	561.5	556.0	550.6	542.2	530.7	519.3	507.8	496.5	489.1
32.5°	555.9	549.5	543.1	536.8	530.5	521.4	509.8	498.1	486.5	474.8	466.5
35°	528.6	521.2	514.0	506.7	499.4	489.5	476.9	464.3	451.8	439.2	430.2
37.5°	501.3	493.3	485.3	477.3	469.3	458.6	445.2	431.8	418.4	405.0	395.0
40°	482.2	473.7	465.1	456.6	448.0	436.8	422.9	409.1	395.2	381.3	371.2
42.5°	462.7	453.7	444.6	435.7	426.6	414.9	400.6	386.2	372.0	357.7	347.2
45°	432.1	422.6	412.9	403.4	393.8	381.5	366.5	351.5	336.5	321.5	311.3
47.5°	402.3	392.1	382.0	371.9	361.7	348.9	333.4	317.9	302.4	286.9	276.8
50°	380.6	370.5	360.4	350.3	340.1	327.2	311.4	295.8	280.0	264.2	254.4
52.5°	359.6	349.0	338.4	327.8	317.2	304.2	288.8	273.5	258.0	242.7	233.2
55°	328.6	317.5	306.3	295.2	284.0	270.7	255.3	239.9	224.4	209.0	200.4
57.5°	296.8	285.4	274.0	262.5	251.1	238.0	223.2	208.3	193.5	178.7	170.7
60°	275.2	263.8	252.4	240.9	229.5	216.5	201.7	187.0	172.3	157.6	150.2
62.5°	254.1	242.7	231.3	219.8	208.4	195.7	181.7	167.6	153.6	139.6	132.6
65°	221.9	210.3	198.7	187.1	175.6	163.3	150.5	137.6	124.8	111.8	107.0
67.5°	190.7	179.3	167.7	156.3	144.7	133.2	121.7	110.1	98.5	87.0	84.7
70°	169.1	158.0	146.8	135.7	124.5	114.0	104.2	94.3	84.5	74.6	73.2
72.5°	148.5	137.8	127.2	116.5	105.8	96.5	88.6	80.7	72.8	64.8	63.6
75°	118.3	108.3	98.3	88.3	78.3	70.9	66.0	61.1	56.3	51.4	50.5
77.5°	88.6	79.8	71.0	62.3	53.6	48.0	45.6	43.3	40.9	38.6	38.0
80°	70.1	62.8	55.5	48.2	40.9	36.6	35.1	33.8	32.3	30.8	30.3
82.5°	53.1	47.4	41.8	36.1	30.4	27.0	26.1	25.1	24.1	23.2	22.8
85°	27.6	24.6	21.6	18.7	15.7	13.9	13.5	13.1	12.7	12.2	12.2
87.5°	8.4	7.7	7.1	6.5	5.9	5.7	5.9	6.1	6.4	6.5	6.6
90°	0.6	2.2	3.6	5.2	6.6	7.9	9.0	10.2	11.2	12.3	13.0
92.5°	12.4	12.3	12.1	12.1	11.9	12.1	12.7	13.2	13.8	14.3	14.6
95°	40.0	35.6	31.0	26.5	22.0	20.1	21.2	22.1	23.1	24.0	24.7
97.5°	79.5	66.7	54.0	41.2	28.5	23.2	25.5	27.7	30.0	32.1	32.7
100°	109.0	90.2	71.5	52.8	34.0	25.8	28.2	30.5	32.8	35.1	36.2
102.5°	141.5	137.6	133.6	129.7	125.6	113.9	94.5	75.0	55.5	36.1	37.5
105°	187.3	191.3	195.4	199.6	203.6	187.0	149.6	112.3	74.9	37.5	39.1
107.5°	239.4	242.6	246.0	249.3	252.6	231.9	187.0	142.2	97.4	52.6	51.1
110°	272.9	275.7	278.6	281.5	284.3	266.0	226.4	186.9	147.3	107.8	94.1



TEST NUMBER: P331660-935

CATALOG NUMBER: S122RDIP-S485D725U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	304.4	306.9	309.4	312.0	314.5	310.9	301.2	291.4	281.6	271.8	222.0
115°	354.1	356.5	358.8	361.1	363.4	366.4	369.7	373.2	376.6	380.0	316.7
117.5°	398.6	401.2	403.8	406.4	409.0	411.5	413.9	416.2	418.5	420.9	405.6
120°	431.1	433.2	435.2	437.3	439.4	441.6	444.1	446.5	449.0	451.4	453.1
122.5°	458.7	460.9	463.0	465.2	467.4	469.8	472.5	475.2	477.9	480.5	481.5
125°	500.8	502.5	504.3	506.1	507.8	510.1	512.6	515.2	517.8	520.5	521.4
127.5°	538.8	540.8	542.8	544.7	546.6	548.6	550.6	552.5	554.5	556.4	557.8
130°	562.9	565.2	567.3	569.5	571.7	573.5	575.1	576.5	578.1	579.5	581.1
132.5°	587.5	589.4	591.3	593.1	595.0	596.7	598.2	599.7	601.2	602.7	604.0
135°	619.6	621.8	624.0	626.2	628.4	630.1	631.3	632.5	633.8	635.0	636.4
137.5°	652.0	653.5	655.0	656.6	658.1	659.6	661.0	662.4	663.7	665.2	666.5
140°	673.2	674.2	675.4	676.5	677.5	678.9	680.4	681.9	683.4	684.9	686.1
142.5°	691.0	691.9	692.9	693.9	694.8	696.2	697.9	699.6	701.4	703.1	704.2
145°	718.8	718.6	718.5	718.3	718.2	719.3	721.6	723.9	726.3	728.6	729.6
147.5°	743.0	742.5	742.0	741.5	741.0	741.8	744.2	746.4	748.7	751.1	751.7
150°	758.8	757.9	756.9	756.0	754.9	755.6	757.8	759.9	762.2	764.3	765.2
152.5°	772.1	771.0	770.0	768.9	767.8	768.4	770.4	772.5	774.6	776.6	777.5
155°	791.4	790.2	788.9	787.7	786.5	786.7	788.3	790.0	791.6	793.2	794.1
157.5°	806.6	805.6	804.5	803.5	802.5	802.5	803.7	804.8	805.9	807.1	808.0
160°	815.5	814.6	813.8	813.0	812.2	812.2	813.0	813.8	814.6	815.5	816.3
162.5°	823.4	822.5	821.7	820.9	820.0	820.0	820.7	821.4	822.2	822.9	823.8
165°	834.0	833.1	832.3	831.5	830.6	830.4	830.9	831.3	831.6	832.1	833.0
167.5°	841.8	841.0	840.2	839.4	838.5	838.3	838.7	839.0	839.5	839.8	840.8
170°	846.3	845.4	844.6	843.8	843.0	842.7	843.0	843.3	843.5	843.8	844.7
172.5°	849.2	848.3	847.6	846.7	845.9	845.7	845.9	846.2	846.4	846.7	847.7
175°	853.0	852.0	851.1	850.2	849.2	848.9	849.1	849.4	849.6	850.0	850.9
177.5°	853.7	852.9	852.1	851.4	850.6	850.2	850.3	850.5	850.6	850.7	851.4
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2



TEST NUMBER: P331660-935

CATALOG NUMBER: S122RDIP-S485D725U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	707.1	708.3	709.5	709.9	709.7	709.5	709.2	709.0
5°	701.5	702.8	704.1	704.6	704.1	703.7	703.3	702.8
7.5°	690.2	690.5	691.0	690.8	690.0	689.2	688.5	687.8
10°	678.8	678.4	678.0	677.3	676.5	675.6	674.8	673.9
12.5°	665.8	665.0	664.3	663.1	661.7	660.3	658.8	657.5
15°	641.4	638.8	636.0	634.0	632.5	631.1	629.6	628.3
17.5°	613.9	610.7	607.4	604.6	602.2	599.7	597.3	594.8
20°	594.7	591.2	587.5	584.2	581.1	577.9	574.8	571.6
22.5°	573.6	569.0	564.5	560.9	558.6	556.3	554.0	551.6
25°	538.7	532.9	527.0	523.0	520.8	518.7	516.6	514.4
27.5°	505.4	498.5	491.7	486.6	483.2	479.8	476.4	473.0
30°	481.8	474.6	467.3	461.7	457.8	454.0	450.1	446.3
32.5°	458.1	449.9	441.5	435.6	432.0	428.3	424.6	421.0
35°	421.2	412.2	403.2	397.1	394.0	390.8	387.7	384.5
37.5°	385.1	375.2	365.3	358.5	355.0	351.4	347.8	344.1
40°	361.0	350.9	340.7	333.8	330.1	326.4	322.6	318.9
42.5°	336.7	326.1	315.7	308.7	305.1	301.4	297.8	294.2
45°	301.2	291.1	280.9	274.1	270.7	267.3	263.8	260.5
47.5°	266.7	256.7	246.6	240.0	236.9	233.8	230.6	227.5
50°	244.5	234.7	224.8	218.4	215.4	212.4	209.4	206.4
52.5°	223.6	214.1	204.6	198.5	195.7	193.0	190.1	187.4
55°	191.8	183.2	174.7	169.0	166.3	163.6	160.9	158.2
57.5°	162.9	155.1	147.2	142.2	139.8	137.6	135.3	132.9
60°	142.9	135.7	128.4	123.6	121.3	119.0	116.8	114.4
62.5°	125.6	118.7	111.8	107.6	106.2	104.9	103.5	102.1
65°	102.2	97.3	92.5	89.8	89.4	88.9	88.5	88.1
67.5°	82.5	80.2	78.0	76.7	76.2	75.8	75.3	74.8
70°	71.7	70.3	68.9	67.8	67.3	66.7	66.1	65.6
72.5°	62.4	61.2	60.0	59.2	58.9	58.5	58.2	57.9
75°	49.4	48.5	47.4	46.8	46.8	46.6	46.4	46.3
77.5°	37.5	36.9	36.3	35.9	35.6	35.5	35.2	35.0
80°	29.7	29.2	28.6	28.3	28.3	28.3	28.3	28.3
82.5°	22.5	22.1	21.8	21.6	21.6	21.6	21.6	21.6
85°	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
87.5°	6.6	6.6	6.6	6.7	6.8	6.8	6.9	6.9
90°	13.7	14.4	15.1	15.5	15.8	16.1	16.4	16.6
92.5°	15.0	15.3	15.7	16.0	16.1	16.3	16.4	16.6
95°	25.4	26.1	26.8	27.0	26.9	26.8	26.6	26.5
97.5°	33.2	33.8	34.4	34.7	34.9	35.0	35.2	35.4
100°	37.3	38.4	39.5	40.2	40.5	40.7	41.0	41.2
102.5°	38.9	40.4	41.8	42.7	43.0	43.5	43.8	44.3
105°	40.6	42.1	43.6	44.6	45.2	45.7	46.2	46.8
107.5°	49.5	48.0	46.5	46.0	46.5	47.1	47.6	48.1
110°	80.4	66.7	53.0	46.5	47.0	47.5	48.1	48.6



TEST NUMBER: P331660-935

CATALOG NUMBER: S122RDIP-S485D725U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	172.0	122.1	72.2	47.4	47.9	48.3	48.7	49.2
115°	253.3	189.9	126.6	89.9	80.1	70.2	60.4	50.5
117.5°	390.3	374.9	359.6	335.7	303.3	271.0	238.6	206.2
120°	454.8	456.4	458.1	449.6	431.1	412.7	394.2	375.7
122.5°	482.5	483.5	484.5	483.2	479.6	476.0	472.4	468.8
125°	522.4	523.3	524.3	525.0	525.4	525.8	526.2	526.6
127.5°	559.2	560.6	562.0	562.7	562.8	562.9	563.0	563.1
130°	582.6	584.1	585.6	586.3	586.2	586.0	585.8	585.7
132.5°	605.3	606.6	607.9	608.5	608.3	608.2	608.0	607.9
135°	637.7	639.1	640.5	641.0	640.8	640.5	640.2	639.9
137.5°	667.9	669.2	670.5	671.0	670.5	670.0	669.6	669.1
140°	687.3	688.5	689.8	690.1	689.4	688.7	688.0	687.3
142.5°	705.3	706.5	707.6	707.8	707.1	706.5	705.8	705.1
145°	730.6	731.5	732.5	732.5	731.9	731.2	730.6	729.9
147.5°	752.4	753.2	753.9	754.0	753.4	752.8	752.3	751.7
150°	765.9	766.8	767.6	767.7	767.0	766.3	765.6	764.9
152.5°	778.3	779.1	780.0	779.9	779.0	778.1	777.2	776.3
155°	795.0	795.7	796.6	796.4	795.3	794.3	793.2	792.0
157.5°	808.9	809.9	810.8	810.7	809.7	808.6	807.5	806.5
160°	817.1	817.9	818.7	818.6	817.7	816.7	815.8	814.9
162.5°	824.7	825.6	826.6	826.5	825.3	824.1	822.9	821.7
165°	834.0	835.0	835.9	835.9	835.0	834.0	833.0	832.1
167.5°	841.8	842.7	843.7	843.5	842.3	841.1	839.8	838.6
170°	845.7	846.6	847.7	847.5	846.3	845.0	843.8	842.6
172.5°	848.7	849.6	850.6	850.4	849.2	848.0	846.7	845.5
175°	851.9	852.8	853.8	853.6	852.2	850.8	849.5	848.1
177.5°	852.2	853.0	853.8	853.7	852.6	851.7	850.7	849.7
180°	851.2	851.2	851.2	851.2	851.2	851.2	851.2	851.2

(END OF REPORT)