

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331734-935

Luminaire Tested: **S122RDIP-S865D1080U935-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331734-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIP-S865D1080U935-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6220.5 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331734-935

CATALOG NUMBER: S122RDIP-S865D1080U935-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331734-935

CATALOG NUMBER: S122RDIP-S865D1080U935-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42																				
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36																				
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31																				
3	81	71	64	59	73	66	60	55	55	50	46	44	41	39	35	33	31	27																				
4	74	63	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27	23																				
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24	20																				
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21	18																				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16																				
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17	15																				
9	50	38	31	26	46	35	29	25	30	25	22	25	21	18	20	17	15	13																				
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20384	20384	20384
5°	20462	20128	20238
10°	20305	19799	19630
15°	20072	19211	18658
20°	19747	18374	17452
25°	19417	17423	16283
30°	18957	16444	14783
35°	18510	15380	13466
40°	18061	14280	11944
45°	17532	13045	10565
50°	16990	11796	9211
55°	16434	10452	7910
60°	15791	9038	6568
65°	15060	7595	5979
70°	14186	6255	5500
75°	13119	5702	5128
80°	11576	5095	4677
85°	9114	4020	4020



TEST NUMBER: P331734-935

CATALOG NUMBER: S122RDIP-S865D1080U935-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.2	1.9
10°-20°	324.5	5.2
20°-30°	455.6	7.3
30°-40°	496.8	8.0
40°-50°	456.8	7.3
50°-60°	358.8	5.8
60°-70°	233.9	3.8
70°-80°	120.6	1.9
80°-90°	36.0	0.6
90°-100°	208.0	3.3
100°-110°	705.7	11.3
110°-120°	749.7	12.1
120°-130°	617.2	9.9
130°-140°	495.6	8.0
140°-150°	374.5	6.0
150°-160°	263.2	4.2
160°-170°	154.9	2.5
170°-180°	50.4	0.8
0°-30°	898.3	14.4
0°-40°	1395.1	22.4
0°-60°	2210.7	35.5
0°-90°	2601.2	41.8
90°-120°	1663.4	26.7
90°-150°	3150.7	50.6
90°-180°	3619.0	58.2
0°-180°	6220.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1262	1262	1262	1262	1262	
5°	1262	1256	1242	1251	1249	120
15°	1201	1187	1149	1128	1116	338
25°	1090	1051	978	933	914	501
35°	939	878	780	711	683	587
45°	768	689	571	493	463	593
55°	584	493	371	305	281	521
65°	394	301	199	162	156	391
75°	210	133	91	84	82	223
85°	49	26	22	22	22	58
90°	1	14	34	32	33	4
95°	35	86	392	148	114	37
105°	122	184	741	1325	1127	130
115°	215	272	620	1280	1483	213
125°	300	355	596	1037	1203	266
135°	352	420	589	871	997	272
145°	402	462	586	728	796	252
155°	457	494	569	644	669	210
165°	498	513	545	578	587	140
175°	519	520	524	531	529	49
180°	520	520	520	520	520	



TEST NUMBER: P331734-935

CATALOG NUMBER: S122RDIP-S865D1080U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1267.0	1266.0	1265.0	1263.9	1263.0	1261.4	1259.1	1256.9	1254.6	1252.4	1254.5
5°	1262.5	1261.2	1259.9	1258.6	1257.4	1255.1	1251.8	1248.5	1245.2	1241.9	1244.1
7.5°	1249.4	1247.8	1246.3	1244.7	1243.1	1240.4	1236.6	1232.7	1228.8	1224.9	1225.6
10°	1238.5	1236.7	1234.9	1233.1	1231.3	1228.0	1222.9	1217.8	1212.7	1207.6	1206.9
12.5°	1224.8	1222.5	1220.4	1218.2	1216.0	1211.7	1205.1	1198.7	1192.1	1185.7	1184.3
15°	1200.8	1198.0	1195.2	1192.4	1189.6	1183.9	1175.3	1166.7	1158.0	1149.3	1144.5
17.5°	1171.3	1167.0	1162.8	1158.5	1154.3	1146.6	1135.5	1124.4	1113.4	1102.3	1096.6
20°	1149.3	1144.3	1139.2	1134.1	1129.0	1120.2	1107.4	1094.8	1082.1	1069.4	1063.0
22.5°	1125.6	1119.9	1114.2	1108.5	1102.9	1092.9	1078.5	1064.2	1049.9	1035.5	1027.3
25°	1089.9	1081.8	1073.7	1065.6	1057.5	1045.0	1028.2	1011.5	994.7	978.0	967.6
27.5°	1047.0	1038.1	1029.3	1020.5	1011.7	997.8	978.9	960.0	941.1	922.2	910.1
30°	1016.8	1007.2	997.6	987.9	978.3	963.3	943.0	922.6	902.3	882.0	869.1
32.5°	987.6	976.3	965.0	953.7	942.5	926.5	905.8	885.0	864.4	843.6	828.9
35°	939.1	926.2	913.3	900.3	887.3	869.7	847.3	825.0	802.7	780.3	764.3
37.5°	890.7	876.5	862.3	848.0	833.8	814.8	791.0	767.2	743.4	719.5	701.9
40°	856.9	841.6	826.4	811.1	795.9	776.0	751.4	726.8	702.1	677.5	659.4
42.5°	822.2	806.1	790.1	774.0	757.9	737.2	711.8	686.3	660.9	635.4	616.8
45°	767.8	750.7	733.7	716.7	699.7	677.9	651.3	624.6	597.9	571.3	553.2
47.5°	714.7	696.7	678.7	660.6	642.7	619.8	592.4	564.8	537.3	509.8	491.9
50°	676.4	658.3	640.3	622.2	604.2	581.3	553.4	525.4	497.5	469.6	452.0
52.5°	638.9	620.0	601.2	582.4	563.5	540.4	513.2	485.8	458.5	431.2	414.2
55°	583.8	564.0	544.2	524.4	504.6	481.0	453.6	426.1	398.7	371.3	356.1
57.5°	527.4	507.0	486.7	466.4	446.2	422.8	396.4	370.1	343.7	317.4	303.4
60°	489.0	468.6	448.4	428.1	407.8	384.5	358.3	332.2	306.1	279.9	267.0
62.5°	451.5	431.2	410.9	390.5	370.2	347.7	322.7	297.8	272.9	247.9	235.6
65°	394.2	373.6	353.0	332.4	311.9	290.2	267.3	244.5	221.6	198.8	190.2
67.5°	338.9	318.5	298.1	277.6	257.2	236.7	216.2	195.6	175.0	154.5	150.5
70°	300.5	280.7	260.9	241.1	221.3	202.6	185.1	167.6	150.1	132.5	130.0
72.5°	263.9	245.0	225.9	207.0	188.0	171.4	157.4	143.3	129.2	115.2	113.0
75°	210.3	192.4	174.7	156.9	139.1	126.0	117.3	108.7	100.0	91.4	89.6
77.5°	157.5	141.8	126.2	110.6	95.1	85.2	81.0	76.9	72.8	68.5	67.5
80°	124.5	111.6	98.7	85.7	72.8	65.0	62.4	59.9	57.3	54.8	53.8
82.5°	94.4	84.3	74.1	64.1	54.0	48.0	46.3	44.6	42.9	41.2	40.6
85°	49.2	43.8	38.5	33.1	27.8	24.8	24.0	23.2	22.5	21.7	21.7
87.5°	14.8	13.8	13.0	11.7	10.5	10.3	11.3	12.7	13.9	14.1	13.7
90°	1.0	4.0	8.0	10.0	12.0	15.0	20.0	27.0	33.0	34.0	33.0
92.5°	12.2	17.6	24.8	29.2	36.0	45.4	68.0	99.8	128.2	130.0	109.9
95°	35.0	39.0	49.0	58.0	74.0	98.0	144.0	231.0	347.1	392.1	343.1
97.5°	57.0	62.4	73.0	86.6	105.0	132.2	190.0	311.3	504.1	669.3	702.1
100°	77.0	80.0	89.0	105.0	125.0	153.0	206.0	328.0	544.1	790.1	934.2
102.5°	95.4	97.6	106.6	122.6	143.4	171.4	220.4	328.9	528.9	794.2	1020.6
105°	122.0	126.1	133.0	148.0	170.0	198.0	245.0	334.1	499.1	741.1	1007.2
107.5°	150.8	154.0	160.8	174.6	196.5	224.6	270.3	347.8	484.3	684.3	919.4
110°	170.0	174.0	180.0	193.0	214.0	243.1	287.1	359.0	481.1	657.1	864.2



TEST NUMBER: P331734-935

CATALOG NUMBER: S122RDIP-S865D1080U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	187.6	191.7	198.5	210.6	230.8	260.6	303.1	371.1	481.9	639.6	825.8
115°	215.1	220.1	226.0	238.1	258.0	285.1	328.0	389.1	486.1	620.1	778.2
117.5°	243.5	247.5	253.5	264.1	283.3	311.3	351.0	408.3	493.3	610.7	748.1
120°	261.1	265.0	271.0	280.1	300.1	328.0	367.0	421.1	498.1	605.1	732.1
122.5°	277.8	281.0	287.1	296.9	316.8	345.7	382.3	432.3	503.7	601.9	718.5
125°	300.1	303.1	309.1	321.1	341.0	369.1	405.1	450.1	512.1	596.2	699.1
127.5°	317.6	321.7	330.1	343.3	362.5	391.2	426.3	466.7	520.7	592.7	681.1
130°	328.0	332.1	342.1	356.1	376.1	404.1	439.1	477.1	527.1	591.1	669.2
132.5°	337.7	342.5	353.3	368.1	388.9	416.9	450.3	487.5	533.5	590.3	659.5
135°	352.1	356.1	368.1	383.1	406.0	434.1	466.1	501.1	541.1	589.1	646.1
137.5°	365.7	370.5	382.5	398.5	421.3	447.3	478.9	511.5	547.9	588.9	636.7
140°	376.1	380.0	392.1	408.1	430.1	456.1	486.1	517.1	551.1	588.1	631.1
142.5°	386.5	389.7	400.9	416.9	438.1	462.5	491.7	521.9	553.5	588.1	625.5
145°	402.1	406.0	416.1	431.1	451.1	473.1	500.1	528.1	556.1	586.1	618.1
147.5°	418.9	421.9	431.4	445.3	461.9	481.5	506.9	531.5	556.9	582.6	610.5
150°	430.1	433.1	441.1	454.1	469.1	487.1	510.1	533.1	556.1	580.1	604.1
152.5°	441.3	442.7	450.6	462.1	476.3	492.7	513.3	533.9	554.5	576.1	598.5
155°	457.1	458.1	464.1	475.1	486.1	501.1	518.1	535.1	552.1	569.1	588.1
157.5°	470.3	471.3	476.1	485.7	494.5	507.1	521.5	535.1	547.5	561.9	578.3
160°	479.1	480.1	484.1	492.1	500.1	511.1	523.1	535.1	545.1	557.2	571.1
162.5°	487.9	487.3	491.3	497.7	504.9	513.5	523.9	534.3	542.7	553.1	564.7
165°	498.1	497.1	499.1	505.1	510.1	516.1	525.1	532.1	538.1	545.1	554.1
167.5°	506.5	505.3	507.1	510.9	514.5	518.3	524.9	530.7	533.5	538.1	543.7
170°	512.1	510.1	511.1	514.1	516.1	519.1	524.1	529.1	531.1	534.1	538.1
172.5°	515.3	514.1	513.5	516.5	517.7	519.9	523.3	526.7	527.9	529.3	532.5
175°	519.1	518.1	517.1	519.1	519.1	520.1	522.1	524.1	523.1	524.1	525.1
177.5°	520.9	519.3	518.5	520.1	520.1	520.1	520.9	522.5	520.9	520.1	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1



TEST NUMBER: P331734-935

CATALOG NUMBER: S122RDIP-S865D1080U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5	1262.5
2.5°	1256.5	1258.5	1260.5	1261.4	1260.9	1260.5	1260.2	1259.7
5°	1246.5	1248.7	1251.0	1251.8	1251.0	1250.3	1249.5	1248.7
7.5°	1226.3	1226.9	1227.6	1227.3	1226.0	1224.7	1223.3	1222.0
10°	1206.1	1205.3	1204.5	1203.4	1201.9	1200.4	1198.9	1197.3
12.5°	1182.9	1181.6	1180.2	1178.3	1175.7	1173.2	1170.6	1168.1
15°	1139.7	1134.9	1130.1	1126.4	1123.9	1121.3	1118.8	1116.2
17.5°	1090.8	1085.0	1079.3	1074.3	1069.9	1065.6	1061.2	1056.8
20°	1056.7	1050.3	1044.0	1038.0	1032.4	1026.8	1021.2	1015.7
22.5°	1019.3	1011.1	1002.9	996.7	992.6	988.3	984.2	980.1
25°	957.2	946.8	936.3	929.2	925.4	921.6	917.8	914.0
27.5°	897.9	885.8	873.7	864.6	858.6	852.5	846.4	840.4
30°	856.1	843.2	830.2	820.3	813.5	806.6	799.8	792.9
32.5°	814.1	799.3	784.5	773.9	767.5	761.0	754.6	748.1
35°	748.3	732.4	716.4	705.6	700.0	694.4	688.8	683.2
37.5°	684.3	666.7	649.1	637.1	630.7	624.2	617.9	611.5
40°	641.4	623.5	605.4	593.1	586.5	579.9	573.3	566.7
42.5°	598.2	579.5	560.9	548.4	542.0	535.6	529.2	522.8
45°	535.2	517.2	499.1	487.1	481.0	474.9	468.8	462.7
47.5°	473.9	456.0	438.1	426.4	420.9	415.3	409.7	404.2
50°	434.5	417.0	399.5	388.1	382.7	377.4	372.0	366.7
52.5°	397.4	380.5	363.5	352.7	347.7	342.8	337.9	332.9
55°	340.9	325.6	310.4	300.3	295.5	290.7	285.9	281.0
57.5°	289.5	275.5	261.6	252.5	248.5	244.4	240.3	236.3
60°	254.0	241.1	228.1	219.6	215.5	211.5	207.4	203.4
62.5°	223.3	210.9	198.5	191.1	188.7	186.3	183.8	181.4
65°	181.5	172.9	164.3	159.5	158.8	158.1	157.3	156.5
67.5°	146.5	142.6	138.6	136.2	135.4	134.6	133.8	133.0
70°	127.4	124.9	122.3	120.6	119.6	118.6	117.5	116.5
72.5°	110.9	108.7	106.6	105.3	104.6	104.0	103.4	102.8
75°	87.8	86.1	84.3	83.3	83.0	82.7	82.5	82.2
77.5°	66.6	65.5	64.5	63.8	63.4	62.9	62.6	62.2
80°	52.8	51.8	50.8	50.3	50.3	50.3	50.3	50.3
82.5°	40.0	39.3	38.7	38.4	38.4	38.4	38.4	38.4
85°	21.7	21.7	21.7	21.7	21.7	21.7	21.7	21.7
87.5°	13.3	12.7	12.9	13.0	13.0	13.0	13.0	13.0
90°	32.0	30.0	32.0	33.0	33.0	33.0	33.0	33.0
92.5°	87.2	74.8	66.4	60.2	59.4	56.2	57.0	55.4
95°	262.1	201.0	159.0	137.0	124.0	116.1	113.0	114.0
97.5°	611.5	500.3	392.1	319.9	272.1	247.5	232.8	224.5
100°	913.2	789.2	652.1	531.1	448.1	405.1	376.1	358.1
102.5°	1110.9	1082.8	982.6	854.4	764.1	690.8	654.5	630.2
105°	1215.2	1328.3	1341.3	1308.3	1246.2	1184.2	1141.3	1127.2
107.5°	1140.1	1310.3	1414.3	1462.7	1470.5	1467.1	1458.4	1439.9
110°	1075.2	1254.2	1382.2	1464.3	1507.3	1526.3	1535.3	1534.3



TEST NUMBER: P331734-935

CATALOG NUMBER: S122RDIP-S865D1080U935-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1016.0	1187.8	1324.6	1418.7	1478.5	1510.3	1527.3	1532.7
115°	943.2	1097.3	1228.2	1331.3	1402.3	1448.3	1474.3	1483.3
117.5°	888.4	1023.6	1142.5	1239.1	1311.5	1360.0	1387.5	1395.1
120°	861.2	985.2	1091.2	1182.2	1252.2	1299.2	1328.3	1338.3
122.5°	839.6	953.2	1053.6	1135.8	1198.6	1244.8	1270.7	1279.0
125°	808.1	911.2	999.2	1074.2	1132.2	1170.3	1195.2	1203.2
127.5°	777.1	870.4	953.4	1022.6	1073.2	1108.8	1130.4	1136.9
130°	757.2	843.2	922.2	988.2	1037.2	1071.3	1091.2	1099.2
132.5°	738.0	817.6	890.2	952.2	1000.4	1034.4	1052.8	1060.0
135°	711.1	777.1	843.2	899.1	942.2	975.2	993.2	997.2
137.5°	689.7	744.9	797.4	846.2	885.4	913.8	929.6	935.6
140°	676.1	724.2	770.2	814.2	846.2	872.2	887.2	893.2
142.5°	665.0	705.8	745.4	782.1	812.5	836.2	849.5	850.8
145°	649.1	682.2	713.2	742.2	766.1	783.2	793.2	796.2
147.5°	637.0	663.0	687.2	708.3	728.1	741.8	748.6	750.4
150°	628.1	650.1	671.1	689.1	704.1	716.2	722.1	723.2
152.5°	619.3	639.7	657.5	673.1	684.9	695.3	699.7	699.9
155°	607.1	623.1	638.1	649.1	660.1	667.1	671.1	669.2
157.5°	592.9	606.3	618.9	627.5	635.3	641.1	642.9	642.9
160°	584.1	595.1	606.1	613.1	620.1	625.1	626.1	626.1
162.5°	575.3	584.7	594.1	599.5	606.5	609.9	610.9	610.1
165°	562.1	569.1	576.1	580.1	584.1	588.1	588.1	587.1
167.5°	549.5	554.9	559.7	563.4	565.1	567.3	567.1	565.9
170°	543.1	546.1	550.1	552.1	553.1	556.1	555.1	553.1
172.5°	535.9	538.1	541.3	542.5	543.5	544.9	543.9	542.7
175°	528.1	529.1	530.1	531.1	531.1	532.1	531.1	529.1
177.5°	522.5	522.5	523.3	523.3	523.3	523.3	522.5	520.9
180°	520.1	520.1	520.1	520.1	520.1	520.1	520.1	520.1

(END OF REPORT)