

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331705-935

Luminaire Tested: **S122RDIP-S865D330U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331705-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S865D330U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3969.9 lumens  
Efficiency: N/A  
Efficacy: 91.3 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	76	76	76	76	76	72		
1	104	100	96	93	98	95	92	89	85	83	81	77	75	73	69	68	66	66	66	66	66	66	66	63		
2	95	88	83	78	90	84	79	75	76	72	69	69	66	63	62	60	58	58	58	58	58	58	58	54		
3	88	79	72	66	83	75	69	64	68	63	59	62	58	55	56	53	51	51	51	51	51	51	51	47		
4	81	71	63	57	77	68	61	56	62	56	52	56	52	48	51	48	45	45	45	45	45	45	45	42		
5	75	64	56	50	71	61	54	49	56	50	46	51	46	43	47	43	40	40	40	40	40	40	40	37		
6	70	58	50	45	66	56	49	43	51	45	41	47	42	38	43	39	36	36	36	36	36	36	36	33		
7	65	53	45	40	62	51	44	39	47	41	37	43	38	35	40	36	32	32	32	32	32	32	32	30		
8	61	49	41	36	58	47	40	35	43	37	33	40	35	31	37	33	30	30	30	30	30	30	30	28		
9	57	45	38	33	54	43	37	32	40	34	30	37	32	29	34	30	27	27	27	27	27	27	27	25		
10	53	42	35	30	51	40	34	29	37	32	28	35	30	26	32	28	25	25	25	25	25	25	25	23		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	26547	26547	26547	26547
5°	29648	26712	23686	26712
10°	32893	26525	20530	26525
15°	34511	26136	16177	26136
20°	29919	25560	13998	25560
25°	19621	24772	12497	24772
30°	13207	23815	11311	23815
35°	10697	22610	10200	22610
40°	9512	21300	9440	21300
45°	8608	19763	8426	19763
50°	7834	18239	7804	18239
55°	7367	16549	7268	16549
60°	6161	14996	6090	14996
65°	5196	13620	5891	13620
70°	4801	12161	5556	12161
75°	4492	10586	5128	10586
80°	4147	8712	4575	8712
85°	3816	6873	4020	6873



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.9	3.9
10°-20°	434.3	10.9
20°-30°	559.6	14.1
30°-40°	531.8	13.4
40°-50°	455.6	11.5
50°-60°	346.9	8.7
60°-70°	219.3	5.5
70°-80°	109.5	2.8
80°-90°	29.5	0.7
90°-100°	12.8	0.3
100°-110°	47.1	1.2
110°-120°	125.8	3.2
120°-130°	207.7	5.2
130°-140°	220.8	5.6
140°-150°	205.3	5.2
150°-160°	165.0	4.2
160°-170°	106.3	2.7
170°-180°	36.6	0.9
0°-30°	1149.8	29.0
0°-40°	1681.6	42.4
0°-60°	2484.1	62.6
0°-90°	2842.4	71.6
90°-120°	185.7	4.7
90°-150°	819.5	20.6
90°-180°	1127.0	28.4
0°-180°	3969.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1829	1648	1461	1648	1829	181
15°	2065	1564	968	1564	2065	557
25°	1101	1390	702	1390	1101	523
35°	543	1147	518	1147	543	347
45°	377	866	369	866	377	292
55°	262	588	258	588	262	230
65°	136	356	154	356	136	138
75°	72	170	82	170	72	76
85°	21	37	22	37	21	22
90°	8	0	8	0	8	4
95°	12	18	12	18	12	11
105°	21	85	21	85	21	22
115°	23	160	23	160	23	57
125°	238	226	238	226	238	206
135°	289	280	289	280	289	223
145°	330	325	330	325	330	206
155°	358	358	358	358	358	165
165°	376	377	376	377	376	106
175°	383	386	383	386	383	37
180°	385	385	385	385	385	



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1710.9	1712.3	1713.6	1710.4	1710.4	1707.7	1701.8	1697.2	1684.4	1682.6	1682.6
5°	1829.3	1828.1	1830.4	1823.0	1812.7	1810.4	1799.6	1785.3	1770.4	1753.9	1750.4
7.5°	1946.9	1945.2	1940.6	1939.4	1931.5	1914.3	1896.8	1878.2	1853.5	1829.4	1817.2
10°	2006.3	2025.2	2013.8	1993.7	1997.8	1970.9	1956.6	1932.1	1911.5	1875.5	1867.5
12.5°	2064.9	2072.3	2068.6	2057.3	2052.2	2033.5	2014.2	1992.9	1954.9	1922.6	1894.5
15°	2064.6	2075.4	2078.3	2074.9	2077.8	2076.6	2066.3	2048.6	2015.5	1980.0	1949.2
17.5°	1912.2	1919.8	1938.5	1951.1	1967.1	2001.0	2017.7	2024.1	2019.2	1999.0	1977.3
20°	1741.3	1728.7	1781.2	1808.1	1830.9	1888.1	1937.2	1956.1	1986.3	1985.8	1980.0
22.5°	1499.0	1502.0	1551.9	1583.7	1650.5	1707.5	1763.6	1834.5	1893.1	1931.8	1954.5
25°	1101.4	1123.2	1172.9	1216.2	1290.6	1396.8	1493.3	1605.3	1711.0	1794.4	1873.8
27.5°	827.2	828.8	868.2	908.4	952.4	1039.5	1161.1	1294.8	1445.4	1569.8	1712.8
30°	708.4	705.0	721.5	746.1	783.8	851.2	942.6	1074.0	1224.3	1411.6	1578.5
32.5°	624.3	624.5	637.0	655.1	686.5	731.9	794.5	901.3	1043.3	1227.4	1423.1
35°	542.7	542.2	551.3	564.4	577.6	606.7	649.5	705.5	803.2	975.2	1175.1
37.5°	484.2	486.7	491.2	499.4	513.9	530.1	555.9	593.5	663.1	764.7	932.8
40°	451.3	452.5	458.7	465.6	474.2	486.7	507.9	538.1	589.0	670.1	792.9
42.5°	421.1	422.3	426.7	433.2	439.9	452.5	469.9	496.1	537.4	600.6	702.0
45°	377.0	377.0	381.1	383.9	391.3	402.8	417.1	438.8	467.3	514.2	581.6
47.5°	335.7	335.8	338.5	343.4	348.0	357.0	371.0	388.7	409.5	445.7	503.3
50°	311.9	312.5	314.2	318.2	321.1	329.1	339.9	355.3	377.0	405.0	453.1
52.5°	292.7	292.4	294.5	296.3	298.3	303.9	312.0	325.6	345.1	369.4	409.1
55°	261.7	259.3	262.8	265.6	267.3	269.7	274.2	282.8	299.4	319.9	349.7
57.5°	222.8	221.9	224.3	226.9	232.3	238.4	242.4	247.8	256.4	271.1	300.6
60°	190.8	190.8	196.0	197.7	204.0	212.0	220.0	224.5	233.1	242.8	264.5
62.5°	162.5	162.9	165.3	167.0	170.6	180.4	191.6	201.6	209.7	219.0	233.4
65°	136.0	137.1	137.1	138.3	140.5	142.8	147.4	155.4	169.7	182.8	193.6
67.5°	115.4	115.7	116.1	117.3	117.8	120.3	122.2	125.7	129.0	141.5	154.9
70°	101.7	103.4	102.8	104.0	104.5	105.6	108.0	109.7	114.9	117.7	125.7
72.5°	88.9	90.1	90.1	90.7	92.2	92.5	94.3	96.0	99.3	101.7	106.0
75°	72.0	71.4	72.0	73.1	73.7	74.3	74.3	76.5	78.3	80.6	83.4
77.5°	55.5	56.1	56.0	56.1	56.2	57.3	57.2	58.1	59.8	61.0	62.4
80°	44.6	45.1	44.6	45.1	45.7	46.2	45.7	46.2	48.0	49.2	49.2
82.5°	34.5	34.6	35.0	35.0	35.2	35.3	36.1	36.2	37.5	37.3	37.7
85°	20.6	20.0	20.0	20.0	20.6	21.1	20.6	20.6	21.1	21.1	21.1
87.5°	8.8	9.2	9.2	9.2	9.2	9.1	9.0	9.5	9.0	9.3	8.8
90°	7.5	7.4	7.2	7.1	7.1	6.8	6.5	6.2	5.9	5.6	5.1
92.5°	7.5	7.4	7.4	7.3	7.2	7.1	7.0	6.8	6.6	6.5	6.2
95°	12.0	12.1	12.1	12.1	12.2	12.1	11.8	11.5	11.2	10.8	10.4
97.5°	16.0	15.9	15.8	15.8	15.7	15.5	15.2	15.1	14.8	14.6	13.5
100°	18.7	18.5	18.4	18.3	18.2	17.8	17.4	16.9	16.4	15.8	14.8
102.5°	20.0	19.8	19.6	19.5	19.3	18.9	18.3	17.6	17.0	16.3	25.1
105°	21.2	20.9	20.7	20.4	20.1	19.7	19.0	18.3	17.7	17.0	33.8
107.5°	21.8	21.5	21.3	21.0	20.8	21.0	21.7	22.4	23.1	23.8	44.0
110°	22.0	21.8	21.5	21.3	21.0	23.9	30.1	36.3	42.5	48.7	66.6



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	22.2	22.0	21.8	21.6	21.4	32.6	55.2	77.7	100.3	122.9	127.3
115°	22.8	27.3	31.8	36.2	40.6	57.2	85.8	114.5	143.1	171.8	170.2
117.5°	93.2	107.9	122.5	137.2	151.8	162.6	169.4	176.4	183.3	190.3	189.2
120°	169.8	178.1	186.5	194.8	203.2	207.0	206.3	205.5	204.8	204.1	202.9
122.5°	211.9	213.5	215.2	216.8	218.3	219.0	218.5	218.1	217.7	217.2	216.0
125°	238.0	237.8	237.6	237.5	237.3	236.9	236.5	236.1	235.7	235.2	234.0
127.5°	254.5	254.4	254.4	254.4	254.3	254.0	253.4	252.8	252.1	251.5	250.6
130°	264.8	264.8	264.8	264.9	265.0	264.7	264.0	263.3	262.6	262.0	261.3
132.5°	274.7	274.8	274.9	274.9	275.0	274.7	274.1	273.6	273.0	272.4	271.7
135°	289.2	289.4	289.5	289.6	289.7	289.5	288.9	288.3	287.7	287.1	286.5
137.5°	302.5	302.6	302.9	303.1	303.2	303.1	302.5	301.9	301.3	300.7	300.1
140°	310.6	311.0	311.3	311.6	311.9	311.8	311.3	310.6	310.1	309.5	308.9
142.5°	318.7	319.0	319.3	319.6	319.9	319.9	319.3	318.8	318.3	317.8	317.0
145°	329.8	330.2	330.5	330.8	331.1	331.1	330.6	330.2	329.8	329.3	328.3
147.5°	339.8	340.0	340.3	340.5	340.8	340.8	340.4	340.1	339.8	339.5	338.5
150°	345.8	346.0	346.4	346.7	347.0	347.0	346.6	346.2	345.9	345.5	344.5
152.5°	350.9	351.3	351.7	352.1	352.5	352.5	352.1	351.8	351.4	351.0	350.1
155°	358.0	358.5	359.0	359.5	360.0	360.1	359.6	359.3	359.0	358.5	357.8
157.5°	364.5	365.0	365.5	365.9	366.4	366.4	366.1	365.7	365.2	364.8	364.3
160°	368.3	368.8	369.2	369.6	370.1	370.1	369.7	369.4	368.9	368.6	368.2
162.5°	371.4	372.0	372.5	373.0	373.6	373.6	373.2	372.7	372.4	372.0	371.6
165°	376.1	376.5	376.9	377.4	377.8	377.8	377.4	376.9	376.5	376.1	375.9
167.5°	379.0	379.6	380.1	380.7	381.3	381.3	380.9	380.5	380.0	379.6	379.4
170°	380.8	381.4	381.9	382.5	383.1	383.1	382.7	382.3	381.9	381.4	381.3
172.5°	382.2	382.7	383.3	383.8	384.4	384.4	384.0	383.6	383.1	382.7	382.6
175°	383.3	383.9	384.6	385.2	385.8	385.9	385.5	385.0	384.6	384.2	384.1
177.5°	384.1	384.5	385.0	385.4	385.8	385.9	385.6	385.2	384.9	384.5	384.4
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1683.4	1679.8	1676.6	1668.4	1664.2	1655.1	1653.7	1653.3	1641.4	1630.0	1626.8
5°	1741.3	1732.2	1718.4	1702.5	1685.8	1668.7	1657.3	1648.1	1625.3	1603.6	1591.0
7.5°	1799.6	1779.9	1756.3	1726.0	1700.7	1672.4	1651.3	1632.5	1600.1	1569.0	1548.1
10°	1843.0	1810.9	1779.5	1737.8	1705.3	1673.3	1643.6	1617.9	1581.3	1540.2	1511.1
12.5°	1869.9	1834.7	1791.4	1750.7	1708.5	1667.8	1628.1	1595.0	1552.0	1509.6	1474.9
15°	1906.3	1868.6	1816.1	1757.8	1703.6	1650.5	1604.7	1563.6	1507.6	1456.7	1414.5
17.5°	1936.2	1884.3	1827.9	1760.5	1697.6	1630.1	1571.2	1518.7	1456.4	1395.1	1345.2
20°	1945.8	1894.4	1829.3	1761.9	1687.6	1608.2	1544.7	1487.6	1420.7	1353.9	1296.8
22.5°	1939.8	1899.9	1827.4	1746.7	1670.7	1587.6	1516.0	1449.7	1375.5	1307.3	1241.0
25°	1899.5	1885.8	1817.2	1729.2	1642.4	1545.9	1463.0	1390.5	1306.0	1232.9	1160.8
27.5°	1805.5	1835.0	1792.6	1698.8	1602.3	1498.8	1405.7	1323.1	1235.4	1153.1	1081.3
30°	1715.0	1783.0	1764.7	1677.8	1569.9	1468.2	1363.7	1277.4	1183.7	1099.2	1028.3
32.5°	1591.1	1703.4	1721.3	1648.6	1537.0	1425.2	1315.7	1229.9	1132.0	1042.9	973.9
35°	1394.0	1561.9	1639.0	1592.8	1480.7	1360.2	1247.1	1147.1	1048.9	960.9	892.3
37.5°	1158.6	1387.4	1516.0	1519.2	1416.4	1291.1	1167.9	1068.7	968.1	881.8	807.5
40°	1006.0	1254.0	1421.3	1458.4	1371.7	1236.2	1111.7	1010.6	912.3	827.8	742.7
42.5°	868.9	1115.9	1321.7	1386.3	1317.2	1182.8	1057.8	952.1	856.6	776.6	689.7
45°	702.7	918.6	1145.4	1260.8	1222.5	1098.0	966.0	865.5	775.8	706.7	623.3
47.5°	592.8	744.9	964.4	1120.5	1119.8	1006.2	876.3	780.1	696.8	632.1	564.6
50°	530.1	662.7	848.3	1025.5	1040.3	944.9	821.5	726.1	648.4	580.4	526.2
52.5°	473.9	583.2	750.1	919.9	962.2	879.5	759.8	671.8	596.3	533.8	487.3
55°	400.5	485.0	611.8	770.7	834.7	776.4	670.1	587.9	526.8	474.2	434.2
57.5°	338.8	402.2	503.9	631.8	706.4	669.7	582.0	515.2	462.9	415.3	383.7
60°	299.9	351.9	438.2	545.0	627.2	601.6	526.8	464.4	419.9	378.8	349.0
62.5°	263.4	308.1	381.9	468.6	544.1	533.5	472.3	420.1	381.1	343.5	318.4
65°	212.0	244.5	302.2	370.2	430.8	435.9	391.9	356.5	321.7	292.0	269.7
67.5°	168.8	190.0	230.7	287.9	333.3	349.5	322.6	295.6	267.9	245.0	225.7
70°	142.2	159.4	189.1	235.4	277.1	294.2	278.8	257.6	233.7	214.8	198.2
72.5°	115.3	132.0	153.9	187.9	223.6	242.1	236.8	221.5	202.1	186.5	170.8
75°	86.9	92.0	106.9	129.7	157.6	173.7	177.7	169.7	154.2	142.2	133.1
77.5°	64.2	67.3	74.4	86.4	104.7	118.9	124.8	123.8	113.2	106.2	97.7
80°	51.4	53.1	56.6	61.7	75.4	89.7	93.7	93.7	86.3	83.4	74.8
82.5°	39.1	40.3	42.4	45.2	51.7	64.1	68.5	69.5	64.7	61.0	54.2
85°	22.3	21.7	22.8	24.5	25.7	29.1	36.0	37.1	36.0	31.4	29.7
87.5°	8.7	9.0	9.0	8.4	8.7	9.0	11.2	13.3	11.6	10.4	9.6
90°	4.6	4.0	3.6	3.0	2.3	1.6	0.9	0.3	0.9	1.6	2.3
92.5°	5.9	5.7	5.5	5.3	5.4	5.5	5.6	5.6	5.6	5.5	5.4
95°	10.0	9.6	9.1	9.9	12.0	14.0	16.0	18.1	16.0	14.0	12.0
97.5°	12.5	11.5	10.5	12.9	18.7	24.4	30.1	35.9	30.1	24.4	18.7
100°	13.8	12.7	11.6	15.4	23.8	32.3	40.8	49.2	40.8	32.3	23.8
102.5°	33.9	42.7	51.5	56.8	58.6	60.4	62.2	64.0	62.2	60.4	58.6
105°	50.8	67.7	84.6	92.0	90.2	88.3	86.4	84.6	86.4	88.3	90.2
107.5°	64.3	84.6	104.8	114.2	112.7	111.2	109.7	108.1	109.7	111.2	112.7
110°	84.5	102.4	120.2	128.5	127.3	126.0	124.6	123.3	124.6	126.0	127.3





TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	131.7	136.1	140.5	142.2	141.0	139.9	138.7	137.6	138.7	139.9	141.0
115°	168.7	167.1	165.6	164.3	163.2	162.2	161.1	160.1	161.1	162.2	163.2
117.5°	188.1	187.1	186.0	184.9	183.7	182.5	181.3	180.2	181.3	182.5	183.7
120°	201.8	200.7	199.6	198.5	197.7	196.7	195.8	194.8	195.8	196.7	197.7
122.5°	214.7	213.5	212.3	211.3	210.3	209.3	208.4	207.3	208.4	209.3	210.3
125°	232.9	231.7	230.6	229.5	228.8	227.9	227.1	226.4	227.1	227.9	228.8
127.5°	249.8	248.8	248.0	247.1	246.2	245.3	244.4	243.5	244.4	245.3	246.2
130°	260.6	259.9	259.2	258.4	257.4	256.4	255.5	254.4	255.5	256.4	257.4
132.5°	271.0	270.4	269.7	269.0	268.1	267.3	266.4	265.6	266.4	267.3	268.1
135°	285.9	285.3	284.8	284.0	283.0	282.1	281.0	280.1	281.0	282.1	283.0
137.5°	299.4	298.8	298.2	297.5	296.8	296.1	295.4	294.7	295.4	296.1	296.8
140°	308.2	307.5	306.9	306.3	305.7	305.2	304.8	304.3	304.8	305.2	305.7
142.5°	316.2	315.5	314.7	314.1	313.7	313.1	312.7	312.3	312.7	313.1	313.7
145°	327.3	326.1	325.1	324.6	324.7	324.8	324.9	324.9	324.9	324.8	324.7
147.5°	337.4	336.3	335.3	334.9	335.1	335.4	335.6	335.9	335.6	335.4	335.1
150°	343.5	342.5	341.6	341.2	341.6	342.1	342.5	342.9	342.5	342.1	341.6
152.5°	349.1	348.2	347.2	347.1	347.5	348.0	348.5	349.0	348.5	348.0	347.5
155°	357.1	356.4	355.6	355.5	356.0	356.6	357.1	357.7	357.1	356.6	356.0
157.5°	363.8	363.3	362.7	362.7	363.2	363.6	364.1	364.5	364.1	363.6	363.2
160°	367.8	367.5	367.1	367.1	367.5	367.8	368.2	368.6	368.2	367.8	367.5
162.5°	371.3	370.9	370.7	370.7	371.0	371.4	371.8	372.1	371.8	371.4	371.0
165°	375.7	375.6	375.4	375.5	375.8	376.2	376.6	376.9	376.6	376.2	375.8
167.5°	379.3	379.1	378.9	379.0	379.4	379.8	380.1	380.5	380.1	379.8	379.4
170°	381.2	381.0	380.9	381.0	381.4	381.8	382.1	382.5	382.1	381.8	381.4
172.5°	382.5	382.4	382.2	382.4	382.7	383.1	383.5	383.8	383.5	383.1	382.7
175°	383.9	383.8	383.7	383.8	384.3	384.7	385.1	385.6	385.1	384.7	384.3
177.5°	384.4	384.4	384.4	384.4	384.8	385.1	385.5	385.8	385.5	385.1	384.8
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1620.8	1617.6	1611.7	1602.6	1597.1	1587.5	1581.1	1584.8	1585.6	1584.8	1583.8
5°	1577.3	1565.3	1548.8	1532.8	1517.9	1501.9	1492.7	1488.8	1480.7	1476.2	1473.9
7.5°	1524.7	1504.0	1480.5	1452.7	1429.0	1404.2	1391.5	1385.3	1368.9	1359.9	1352.2
10°	1485.3	1452.8	1429.3	1392.8	1370.5	1337.9	1315.7	1316.2	1293.9	1281.3	1272.2
12.5°	1441.9	1406.2	1367.2	1334.3	1303.3	1277.1	1250.3	1239.4	1215.8	1203.7	1179.0
15°	1369.9	1328.3	1287.1	1242.5	1211.1	1170.5	1131.7	1084.3	1046.0	1012.9	1003.8
17.5°	1291.3	1239.7	1198.4	1146.1	1092.3	1024.1	979.0	951.5	928.4	910.9	897.9
20°	1237.4	1184.8	1140.8	1062.0	989.5	943.2	910.1	888.9	865.0	846.1	835.8
22.5°	1180.7	1125.8	1065.9	977.9	921.4	884.2	854.7	830.4	814.2	799.4	790.1
25°	1100.3	1040.3	941.5	880.9	835.2	796.3	775.8	761.0	743.8	723.8	714.6
27.5°	1015.3	919.9	848.9	803.9	760.3	735.0	716.5	694.3	679.0	670.0	660.5
30°	951.7	856.4	800.9	751.8	720.9	692.9	671.2	658.7	643.9	628.4	622.2
32.5°	880.9	804.7	751.6	710.7	679.3	655.5	638.3	618.0	607.3	597.8	584.6
35°	792.9	735.2	686.6	653.6	623.9	604.4	584.4	572.4	553.0	545.0	539.8
37.5°	718.4	668.4	632.1	597.2	573.7	552.2	539.9	520.9	512.5	501.4	490.5
40°	676.4	627.2	592.5	563.9	537.6	521.6	506.2	490.8	478.2	473.0	459.9
42.5°	633.4	593.5	558.6	527.3	509.7	492.8	473.3	461.9	448.9	440.6	432.5
45°	574.1	538.7	509.0	483.3	463.9	446.2	433.6	414.7	407.3	390.7	383.9
47.5°	522.0	489.1	460.8	436.4	417.4	405.9	387.4	372.7	360.8	350.7	341.8
50°	485.0	457.6	430.2	408.5	391.3	374.8	355.9	348.4	330.2	325.0	319.9
52.5°	451.2	425.2	400.0	378.8	361.6	345.5	328.9	319.3	306.9	301.8	298.0
55°	403.9	378.8	354.7	335.9	318.7	302.2	292.0	279.9	274.2	270.2	265.6
57.5°	356.4	333.7	315.4	296.3	279.1	265.9	254.0	246.8	240.8	235.6	230.1
60°	326.2	304.4	287.9	270.2	252.5	241.7	232.5	223.9	217.1	209.1	206.8
62.5°	294.2	275.3	260.0	242.8	227.4	217.4	208.7	200.6	192.4	180.7	177.5
65°	250.2	235.4	219.4	205.1	191.4	181.7	169.1	160.0	156.5	155.4	154.8
67.5°	210.4	196.4	182.7	168.1	155.6	146.6	140.2	138.8	136.4	135.7	134.1
70°	183.9	170.8	157.1	143.4	131.4	129.7	127.4	125.1	122.3	121.1	119.9
72.5°	160.1	146.6	132.9	121.9	116.8	114.6	112.3	110.0	108.1	106.9	106.2
75°	122.9	110.3	101.1	97.1	94.3	92.6	89.1	87.4	86.3	84.6	83.9
77.5°	88.4	81.4	77.1	74.6	71.6	69.8	67.8	66.1	64.9	64.6	63.6
80°	67.4	64.0	61.1	57.7	56.6	54.2	53.7	52.0	52.5	50.9	50.9
82.5°	52.3	48.0	45.5	44.0	42.9	41.0	40.5	39.6	39.8	38.5	38.5
85°	26.9	25.7	24.5	23.4	23.4	21.7	22.3	21.7	21.7	20.6	20.0
87.5°	9.3	9.0	8.1	8.3	8.4	8.0	8.0	7.7	7.7	7.7	7.3
90°	3.0	3.6	4.0	4.6	5.1	5.6	5.9	6.2	6.5	6.8	7.1
92.5°	5.3	5.5	5.7	5.9	6.2	6.5	6.6	6.8	7.0	7.1	7.2
95°	9.9	9.1	9.6	10.0	10.4	10.8	11.2	11.5	11.8	12.1	12.2
97.5°	12.9	10.5	11.5	12.5	13.5	14.6	14.8	15.1	15.2	15.5	15.7
100°	15.4	11.6	12.7	13.8	14.8	15.8	16.4	16.9	17.4	17.8	18.2
102.5°	56.8	51.5	42.7	33.9	25.1	16.3	17.0	17.6	18.3	18.9	19.3
105°	92.0	84.6	67.7	50.8	33.8	17.0	17.7	18.3	19.0	19.7	20.1
107.5°	114.2	104.8	84.6	64.3	44.0	23.8	23.1	22.4	21.7	21.0	20.8
110°	128.5	120.2	102.4	84.5	66.6	48.7	42.5	36.3	30.1	23.9	21.0



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	142.2	140.5	136.1	131.7	127.3	122.9	100.3	77.7	55.2	32.6	21.4
115°	164.3	165.6	167.1	168.7	170.2	171.8	143.1	114.5	85.8	57.2	40.6
117.5°	184.9	186.0	187.1	188.1	189.2	190.3	183.3	176.4	169.4	162.6	151.8
120°	198.5	199.6	200.7	201.8	202.9	204.1	204.8	205.5	206.3	207.0	203.2
122.5°	211.3	212.3	213.5	214.7	216.0	217.2	217.7	218.1	218.5	219.0	218.3
125°	229.5	230.6	231.7	232.9	234.0	235.2	235.7	236.1	236.5	236.9	237.3
127.5°	247.1	248.0	248.8	249.8	250.6	251.5	252.1	252.8	253.4	254.0	254.3
130°	258.4	259.2	259.9	260.6	261.3	262.0	262.6	263.3	264.0	264.7	265.0
132.5°	269.0	269.7	270.4	271.0	271.7	272.4	273.0	273.6	274.1	274.7	275.0
135°	284.0	284.8	285.3	285.9	286.5	287.1	287.7	288.3	288.9	289.5	289.7
137.5°	297.5	298.2	298.8	299.4	300.1	300.7	301.3	301.9	302.5	303.1	303.2
140°	306.3	306.9	307.5	308.2	308.9	309.5	310.1	310.6	311.3	311.8	311.9
142.5°	314.1	314.7	315.5	316.2	317.0	317.8	318.3	318.8	319.3	319.9	319.9
145°	324.6	325.1	326.1	327.3	328.3	329.3	329.8	330.2	330.6	331.1	331.1
147.5°	334.9	335.3	336.3	337.4	338.5	339.5	339.8	340.1	340.4	340.8	340.8
150°	341.2	341.6	342.5	343.5	344.5	345.5	345.9	346.2	346.6	347.0	347.0
152.5°	347.1	347.2	348.2	349.1	350.1	351.0	351.4	351.8	352.1	352.5	352.5
155°	355.5	355.6	356.4	357.1	357.8	358.5	359.0	359.3	359.6	360.1	360.0
157.5°	362.7	362.7	363.3	363.8	364.3	364.8	365.2	365.7	366.1	366.4	366.4
160°	367.1	367.1	367.5	367.8	368.2	368.6	368.9	369.4	369.7	370.1	370.1
162.5°	370.7	370.7	370.9	371.3	371.6	372.0	372.4	372.7	373.2	373.6	373.6
165°	375.5	375.4	375.6	375.7	375.9	376.1	376.5	376.9	377.4	377.8	377.8
167.5°	379.0	378.9	379.1	379.3	379.4	379.6	380.0	380.5	380.9	381.3	381.3
170°	381.0	380.9	381.0	381.2	381.3	381.4	381.9	382.3	382.7	383.1	383.1
172.5°	382.4	382.2	382.4	382.5	382.6	382.7	383.1	383.6	384.0	384.4	384.4
175°	383.8	383.7	383.8	383.9	384.1	384.2	384.6	385.0	385.5	385.9	385.8
177.5°	384.4	384.4	384.4	384.4	384.4	384.5	384.9	385.2	385.6	385.9	385.8
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1578.8	1579.7	1578.3	1579.2	1578.3	1579.7	1578.8	1583.8	1584.8	1585.6	1584.8
5°	1471.0	1464.2	1463.0	1461.4	1463.0	1464.2	1471.0	1473.9	1476.2	1480.7	1488.8
7.5°	1342.4	1341.4	1338.5	1334.6	1338.5	1341.4	1342.4	1352.2	1359.9	1368.9	1385.3
10°	1259.6	1256.8	1256.3	1252.2	1256.3	1256.8	1259.6	1272.2	1281.3	1293.9	1316.2
12.5°	1162.8	1144.4	1142.5	1132.5	1142.5	1144.4	1162.8	1179.0	1203.7	1215.8	1239.4
15°	990.1	986.6	975.2	967.8	975.2	986.6	990.1	1003.8	1012.9	1046.0	1084.3
17.5°	891.3	880.1	876.6	874.9	876.6	880.1	891.3	897.9	910.9	928.4	951.5
20°	827.8	817.5	815.8	814.7	815.8	817.5	827.8	835.8	846.1	865.0	888.9
22.5°	783.9	773.2	768.7	765.3	768.7	773.2	783.9	790.1	799.4	814.2	830.4
25°	708.9	705.0	702.7	701.5	702.7	705.0	708.9	714.6	723.8	743.8	761.0
27.5°	650.3	641.5	639.8	636.9	639.8	641.5	650.3	660.5	670.0	679.0	694.3
30°	617.0	614.2	610.1	606.7	610.1	614.2	617.0	622.2	628.4	643.9	658.7
32.5°	577.6	575.3	571.7	570.2	571.7	575.3	577.6	584.6	597.8	607.3	618.0
35°	534.2	526.2	522.7	517.5	522.7	526.2	534.2	539.8	545.0	553.0	572.4
37.5°	488.1	483.9	479.1	480.8	479.1	483.9	488.1	490.5	501.4	512.5	520.9
40°	452.5	449.6	448.5	447.9	448.5	449.6	452.5	459.9	473.0	478.2	490.8
42.5°	424.1	416.2	413.3	413.1	413.3	416.2	424.1	432.5	440.6	448.9	461.9
45°	381.1	373.6	368.5	369.0	368.5	373.6	381.1	383.9	390.7	407.3	414.7
47.5°	336.9	336.7	333.6	334.6	333.6	336.7	336.9	341.8	350.7	360.8	372.7
50°	315.9	312.5	310.2	310.7	310.2	312.5	315.9	319.9	325.0	330.2	348.4
52.5°	295.8	292.8	291.0	293.4	291.0	292.8	295.8	298.0	301.8	306.9	319.3
55°	262.8	259.3	258.8	258.2	258.8	259.3	262.8	265.6	270.2	274.2	279.9
57.5°	225.9	223.6	220.2	218.7	220.2	223.6	225.9	230.1	235.6	240.8	246.8
60°	199.4	194.8	189.1	188.6	189.1	194.8	199.4	206.8	209.1	217.1	223.9
62.5°	175.1	174.3	173.1	173.0	173.1	174.3	175.1	177.5	180.7	192.4	200.6
65°	153.7	153.1	153.7	154.2	153.7	153.1	153.7	154.8	155.4	156.5	160.0
67.5°	133.9	132.9	131.8	132.3	131.8	132.9	133.9	134.1	135.7	136.4	138.8
70°	118.8	118.2	117.7	117.7	117.7	118.2	118.8	119.9	121.1	122.3	125.1
72.5°	104.2	104.1	103.5	103.1	103.5	104.1	104.2	106.2	106.9	108.1	110.0
75°	83.4	82.2	82.2	82.2	82.2	82.2	83.4	83.9	84.6	86.3	87.4
77.5°	63.5	62.9	62.4	61.9	62.4	62.9	63.5	63.6	64.6	64.9	66.1
80°	50.3	49.7	49.2	49.2	49.2	49.7	50.3	50.9	50.9	52.5	52.0
82.5°	38.4	37.8	37.7	37.3	37.7	37.8	38.4	38.5	38.5	39.8	39.6
85°	20.6	21.1	20.6	21.7	20.6	21.1	20.6	20.0	20.6	21.7	21.7
87.5°	7.4	7.0	7.4	7.0	7.4	7.0	7.4	7.3	7.7	7.7	7.7
90°	7.1	7.2	7.4	7.5	7.4	7.2	7.1	7.1	6.8	6.5	6.2
92.5°	7.3	7.4	7.4	7.5	7.4	7.4	7.3	7.2	7.1	7.0	6.8
95°	12.1	12.1	12.1	12.0	12.1	12.1	12.1	12.2	12.1	11.8	11.5
97.5°	15.8	15.8	15.9	16.0	15.9	15.8	15.8	15.7	15.5	15.2	15.1
100°	18.3	18.4	18.5	18.7	18.5	18.4	18.3	18.2	17.8	17.4	16.9
102.5°	19.5	19.6	19.8	20.0	19.8	19.6	19.5	19.3	18.9	18.3	17.6
105°	20.4	20.7	20.9	21.2	20.9	20.7	20.4	20.1	19.7	19.0	18.3
107.5°	21.0	21.3	21.5	21.8	21.5	21.3	21.0	20.8	21.0	21.7	22.4
110°	21.3	21.5	21.8	22.0	21.8	21.5	21.3	21.0	23.9	30.1	36.3



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	21.6	21.8	22.0	22.2	22.0	21.8	21.6	21.4	32.6	55.2	77.7
115°	36.2	31.8	27.3	22.8	27.3	31.8	36.2	40.6	57.2	85.8	114.5
117.5°	137.2	122.5	107.9	93.2	107.9	122.5	137.2	151.8	162.6	169.4	176.4
120°	194.8	186.5	178.1	169.8	178.1	186.5	194.8	203.2	207.0	206.3	205.5
122.5°	216.8	215.2	213.5	211.9	213.5	215.2	216.8	218.3	219.0	218.5	218.1
125°	237.5	237.6	237.8	238.0	237.8	237.6	237.5	237.3	236.9	236.5	236.1
127.5°	254.4	254.4	254.4	254.5	254.4	254.4	254.4	254.3	254.0	253.4	252.8
130°	264.9	264.8	264.8	264.8	264.8	264.8	264.9	265.0	264.7	264.0	263.3
132.5°	274.9	274.9	274.8	274.7	274.8	274.9	274.9	275.0	274.7	274.1	273.6
135°	289.6	289.5	289.4	289.2	289.4	289.5	289.6	289.7	289.5	288.9	288.3
137.5°	303.1	302.9	302.6	302.5	302.6	302.9	303.1	303.2	303.1	302.5	301.9
140°	311.6	311.3	311.0	310.6	311.0	311.3	311.6	311.9	311.8	311.3	310.6
142.5°	319.6	319.3	319.0	318.7	319.0	319.3	319.6	319.9	319.9	319.3	318.8
145°	330.8	330.5	330.2	329.8	330.2	330.5	330.8	331.1	331.1	330.6	330.2
147.5°	340.5	340.3	340.0	339.8	340.0	340.3	340.5	340.8	340.8	340.4	340.1
150°	346.7	346.4	346.0	345.8	346.0	346.4	346.7	347.0	347.0	346.6	346.2
152.5°	352.1	351.7	351.3	350.9	351.3	351.7	352.1	352.5	352.5	352.1	351.8
155°	359.5	359.0	358.5	358.0	358.5	359.0	359.5	360.0	360.1	359.6	359.3
157.5°	365.9	365.5	365.0	364.5	365.0	365.5	365.9	366.4	366.4	366.1	365.7
160°	369.6	369.2	368.8	368.3	368.8	369.2	369.6	370.1	370.1	369.7	369.4
162.5°	373.0	372.5	372.0	371.4	372.0	372.5	373.0	373.6	373.6	373.2	372.7
165°	377.4	376.9	376.5	376.1	376.5	376.9	377.4	377.8	377.8	377.4	376.9
167.5°	380.7	380.1	379.6	379.0	379.6	380.1	380.7	381.3	381.3	380.9	380.5
170°	382.5	381.9	381.4	380.8	381.4	381.9	382.5	383.1	383.1	382.7	382.3
172.5°	383.8	383.3	382.7	382.2	382.7	383.3	383.8	384.4	384.4	384.0	383.6
175°	385.2	384.6	383.9	383.3	383.9	384.6	385.2	385.8	385.9	385.5	385.0
177.5°	385.4	385.0	384.5	384.1	384.5	385.0	385.4	385.8	385.9	385.6	385.2
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1581.1	1587.5	1597.1	1602.6	1611.7	1617.6	1620.8	1626.8	1630.0	1641.4	1653.3
5°	1492.7	1501.9	1517.9	1532.8	1548.8	1565.3	1577.3	1591.0	1603.6	1625.3	1648.1
7.5°	1391.5	1404.2	1429.0	1452.7	1480.5	1504.0	1524.7	1548.1	1569.0	1600.1	1632.5
10°	1315.7	1337.9	1370.5	1392.8	1429.3	1452.8	1485.3	1511.1	1540.2	1581.3	1617.9
12.5°	1250.3	1277.1	1303.3	1334.3	1367.2	1406.2	1441.9	1474.9	1509.6	1552.0	1595.0
15°	1131.7	1170.5	1211.1	1242.5	1287.1	1328.3	1369.9	1414.5	1456.7	1507.6	1563.6
17.5°	979.0	1024.1	1092.3	1146.1	1198.4	1239.7	1291.3	1345.2	1395.1	1456.4	1518.7
20°	910.1	943.2	989.5	1062.0	1140.8	1184.8	1237.4	1296.8	1353.9	1420.7	1487.6
22.5°	854.7	884.2	921.4	977.9	1065.9	1125.8	1180.7	1241.0	1307.3	1375.5	1449.7
25°	775.8	796.3	835.2	880.9	941.5	1040.3	1100.3	1160.8	1232.9	1306.0	1390.5
27.5°	716.5	735.0	760.3	803.9	848.9	919.9	1015.3	1081.3	1153.1	1235.4	1323.1
30°	671.2	692.9	720.9	751.8	800.9	856.4	951.7	1028.3	1099.2	1183.7	1277.4
32.5°	638.3	655.5	679.3	710.7	751.6	804.7	880.9	973.9	1042.9	1132.0	1229.9
35°	584.4	604.4	623.9	653.6	686.6	735.2	792.9	892.3	960.9	1048.9	1147.1
37.5°	539.9	552.2	573.7	597.2	632.1	668.4	718.4	807.5	881.8	968.1	1068.7
40°	506.2	521.6	537.6	563.9	592.5	627.2	676.4	742.7	827.8	912.3	1010.6
42.5°	473.3	492.8	509.7	527.3	558.6	593.5	633.4	689.7	776.6	856.6	952.1
45°	433.6	446.2	463.9	483.3	509.0	538.7	574.1	623.3	706.7	775.8	865.5
47.5°	387.4	405.9	417.4	436.4	460.8	489.1	522.0	564.6	632.1	696.8	780.1
50°	355.9	374.8	391.3	408.5	430.2	457.6	485.0	526.2	580.4	648.4	726.1
52.5°	328.9	345.5	361.6	378.8	400.0	425.2	451.2	487.3	533.8	596.3	671.8
55°	292.0	302.2	318.7	335.9	354.7	378.8	403.9	434.2	474.2	526.8	587.9
57.5°	254.0	265.9	279.1	296.3	315.4	333.7	356.4	383.7	415.3	462.9	515.2
60°	232.5	241.7	252.5	270.2	287.9	304.4	326.2	349.0	378.8	419.9	464.4
62.5°	208.7	217.4	227.4	242.8	260.0	275.3	294.2	318.4	343.5	381.1	420.1
65°	169.1	181.7	191.4	205.1	219.4	235.4	250.2	269.7	292.0	321.7	356.5
67.5°	140.2	146.6	155.6	168.1	182.7	196.4	210.4	225.7	245.0	267.9	295.6
70°	127.4	129.7	131.4	143.4	157.1	170.8	183.9	198.2	214.8	233.7	257.6
72.5°	112.3	114.6	116.8	121.9	132.9	146.6	160.1	170.8	186.5	202.1	221.5
75°	89.1	92.6	94.3	97.1	101.1	110.3	122.9	133.1	142.2	154.2	169.7
77.5°	67.8	69.8	71.6	74.6	77.1	81.4	88.4	97.7	106.2	113.2	123.8
80°	53.7	54.2	56.6	57.7	61.1	64.0	67.4	74.8	83.4	86.3	93.7
82.5°	40.5	41.0	42.9	44.0	45.5	48.0	52.3	54.2	61.0	64.7	69.5
85°	22.3	21.7	23.4	23.4	24.5	25.7	26.9	29.7	31.4	36.0	37.1
87.5°	8.0	8.0	8.4	8.3	8.1	9.0	9.3	9.6	10.4	11.6	13.3
90°	5.9	5.6	5.1	4.6	4.0	3.6	3.0	2.3	1.6	0.9	0.3
92.5°	6.6	6.5	6.2	5.9	5.7	5.5	5.3	5.4	5.5	5.6	5.6
95°	11.2	10.8	10.4	10.0	9.6	9.1	9.9	12.0	14.0	16.0	18.1
97.5°	14.8	14.6	13.5	12.5	11.5	10.5	12.9	18.7	24.4	30.1	35.9
100°	16.4	15.8	14.8	13.8	12.7	11.6	15.4	23.8	32.3	40.8	49.2
102.5°	17.0	16.3	25.1	33.9	42.7	51.5	56.8	58.6	60.4	62.2	64.0
105°	17.7	17.0	33.8	50.8	67.7	84.6	92.0	90.2	88.3	86.4	84.6
107.5°	23.1	23.8	44.0	64.3	84.6	104.8	114.2	112.7	111.2	109.7	108.1
110°	42.5	48.7	66.6	84.5	102.4	120.2	128.5	127.3	126.0	124.6	123.3



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	100.3	122.9	127.3	131.7	136.1	140.5	142.2	141.0	139.9	138.7	137.6
115°	143.1	171.8	170.2	168.7	167.1	165.6	164.3	163.2	162.2	161.1	160.1
117.5°	183.3	190.3	189.2	188.1	187.1	186.0	184.9	183.7	182.5	181.3	180.2
120°	204.8	204.1	202.9	201.8	200.7	199.6	198.5	197.7	196.7	195.8	194.8
122.5°	217.7	217.2	216.0	214.7	213.5	212.3	211.3	210.3	209.3	208.4	207.3
125°	235.7	235.2	234.0	232.9	231.7	230.6	229.5	228.8	227.9	227.1	226.4
127.5°	252.1	251.5	250.6	249.8	248.8	248.0	247.1	246.2	245.3	244.4	243.5
130°	262.6	262.0	261.3	260.6	259.9	259.2	258.4	257.4	256.4	255.5	254.4
132.5°	273.0	272.4	271.7	271.0	270.4	269.7	269.0	268.1	267.3	266.4	265.6
135°	287.7	287.1	286.5	285.9	285.3	284.8	284.0	283.0	282.1	281.0	280.1
137.5°	301.3	300.7	300.1	299.4	298.8	298.2	297.5	296.8	296.1	295.4	294.7
140°	310.1	309.5	308.9	308.2	307.5	306.9	306.3	305.7	305.2	304.8	304.3
142.5°	318.3	317.8	317.0	316.2	315.5	314.7	314.1	313.7	313.1	312.7	312.3
145°	329.8	329.3	328.3	327.3	326.1	325.1	324.6	324.7	324.8	324.9	324.9
147.5°	339.8	339.5	338.5	337.4	336.3	335.3	334.9	335.1	335.4	335.6	335.9
150°	345.9	345.5	344.5	343.5	342.5	341.6	341.2	341.6	342.1	342.5	342.9
152.5°	351.4	351.0	350.1	349.1	348.2	347.2	347.1	347.5	348.0	348.5	349.0
155°	359.0	358.5	357.8	357.1	356.4	355.6	355.5	356.0	356.6	357.1	357.7
157.5°	365.2	364.8	364.3	363.8	363.3	362.7	362.7	363.2	363.6	364.1	364.5
160°	368.9	368.6	368.2	367.8	367.5	367.1	367.1	367.5	367.8	368.2	368.6
162.5°	372.4	372.0	371.6	371.3	370.9	370.7	370.7	371.0	371.4	371.8	372.1
165°	376.5	376.1	375.9	375.7	375.6	375.4	375.5	375.8	376.2	376.6	376.9
167.5°	380.0	379.6	379.4	379.3	379.1	378.9	379.0	379.4	379.8	380.1	380.5
170°	381.9	381.4	381.3	381.2	381.0	380.9	381.0	381.4	381.8	382.1	382.5
172.5°	383.1	382.7	382.6	382.5	382.4	382.2	382.4	382.7	383.1	383.5	383.8
175°	384.6	384.2	384.1	383.9	383.8	383.7	383.8	384.3	384.7	385.1	385.6
177.5°	384.9	384.5	384.4	384.4	384.4	384.4	384.4	384.8	385.1	385.5	385.8
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1653.7	1655.1	1664.2	1668.4	1676.6	1679.8	1683.4	1682.6	1682.6	1684.4	1697.2
5°	1657.3	1668.7	1685.8	1702.5	1718.4	1732.2	1741.3	1750.4	1753.9	1770.4	1785.3
7.5°	1651.3	1672.4	1700.7	1726.0	1756.3	1779.9	1799.6	1817.2	1829.4	1853.5	1878.2
10°	1643.6	1673.3	1705.3	1737.8	1779.5	1810.9	1843.0	1867.5	1875.5	1911.5	1932.1
12.5°	1628.1	1667.8	1708.5	1750.7	1791.4	1834.7	1869.9	1894.5	1922.6	1954.9	1992.9
15°	1604.7	1650.5	1703.6	1757.8	1816.1	1868.6	1906.3	1949.2	1980.0	2015.5	2048.6
17.5°	1571.2	1630.1	1697.6	1760.5	1827.9	1884.3	1936.2	1977.3	1999.0	2019.2	2024.1
20°	1544.7	1608.2	1687.6	1761.9	1829.3	1894.4	1945.8	1980.0	1985.8	1986.3	1956.1
22.5°	1516.0	1587.6	1670.7	1746.7	1827.4	1899.9	1939.8	1954.5	1931.8	1893.1	1834.5
25°	1463.0	1545.9	1642.4	1729.2	1817.2	1885.8	1899.5	1873.8	1794.4	1711.0	1605.3
27.5°	1405.7	1498.8	1602.3	1698.8	1792.6	1835.0	1805.5	1712.8	1569.8	1445.4	1294.8
30°	1363.7	1468.2	1569.9	1677.8	1764.7	1783.0	1715.0	1578.5	1411.6	1224.3	1074.0
32.5°	1315.7	1425.2	1537.0	1648.6	1721.3	1703.4	1591.1	1423.1	1227.4	1043.3	901.3
35°	1247.1	1360.2	1480.7	1592.8	1639.0	1561.9	1394.0	1175.1	975.2	803.2	705.5
37.5°	1167.9	1291.1	1416.4	1519.2	1516.0	1387.4	1158.6	932.8	764.7	663.1	593.5
40°	1111.7	1236.2	1371.7	1458.4	1421.3	1254.0	1006.0	792.9	670.1	589.0	538.1
42.5°	1057.8	1182.8	1317.2	1386.3	1321.7	1115.9	868.9	702.0	600.6	537.4	496.1
45°	966.0	1098.0	1222.5	1260.8	1145.4	918.6	702.7	581.6	514.2	467.3	438.8
47.5°	876.3	1006.2	1119.8	1120.5	964.4	744.9	592.8	503.3	445.7	409.5	388.7
50°	821.5	944.9	1040.3	1025.5	848.3	662.7	530.1	453.1	405.0	377.0	355.3
52.5°	759.8	879.5	962.2	919.9	750.1	583.2	473.9	409.1	369.4	345.1	325.6
55°	670.1	776.4	834.7	770.7	611.8	485.0	400.5	349.7	319.9	299.4	282.8
57.5°	582.0	669.7	706.4	631.8	503.9	402.2	338.8	300.6	271.1	256.4	247.8
60°	526.8	601.6	627.2	545.0	438.2	351.9	299.9	264.5	242.8	233.1	224.5
62.5°	472.3	533.5	544.1	468.6	381.9	308.1	263.4	233.4	219.0	209.7	201.6
65°	391.9	435.9	430.8	370.2	302.2	244.5	212.0	193.6	182.8	169.7	155.4
67.5°	322.6	349.5	333.3	287.9	230.7	190.0	168.8	154.9	141.5	129.0	125.7
70°	278.8	294.2	277.1	235.4	189.1	159.4	142.2	125.7	117.7	114.9	109.7
72.5°	236.8	242.1	223.6	187.9	153.9	132.0	115.3	106.0	101.7	99.3	96.0
75°	177.7	173.7	157.6	129.7	106.9	92.0	86.9	83.4	80.6	78.3	76.5
77.5°	124.8	118.9	104.7	86.4	74.4	67.3	64.2	62.4	61.0	59.8	58.1
80°	93.7	89.7	75.4	61.7	56.6	53.1	51.4	49.2	49.2	48.0	46.2
82.5°	68.5	64.1	51.7	45.2	42.4	40.3	39.1	37.7	37.3	37.5	36.2
85°	36.0	29.1	25.7	24.5	22.8	21.7	22.3	21.1	21.1	21.1	20.6
87.5°	11.2	9.0	8.7	8.4	9.0	9.0	8.7	8.8	9.3	9.0	9.5
90°	0.9	1.6	2.3	3.0	3.6	4.0	4.6	5.1	5.6	5.9	6.2
92.5°	5.6	5.5	5.4	5.3	5.5	5.7	5.9	6.2	6.5	6.6	6.8
95°	16.0	14.0	12.0	9.9	9.1	9.6	10.0	10.4	10.8	11.2	11.5
97.5°	30.1	24.4	18.7	12.9	10.5	11.5	12.5	13.5	14.6	14.8	15.1
100°	40.8	32.3	23.8	15.4	11.6	12.7	13.8	14.8	15.8	16.4	16.9
102.5°	62.2	60.4	58.6	56.8	51.5	42.7	33.9	25.1	16.3	17.0	17.6
105°	86.4	88.3	90.2	92.0	84.6	67.7	50.8	33.8	17.0	17.7	18.3
107.5°	109.7	111.2	112.7	114.2	104.8	84.6	64.3	44.0	23.8	23.1	22.4
110°	124.6	126.0	127.3	128.5	120.2	102.4	84.5	66.6	48.7	42.5	36.3





TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	138.7	139.9	141.0	142.2	140.5	136.1	131.7	127.3	122.9	100.3	77.7
115°	161.1	162.2	163.2	164.3	165.6	167.1	168.7	170.2	171.8	143.1	114.5
117.5°	181.3	182.5	183.7	184.9	186.0	187.1	188.1	189.2	190.3	183.3	176.4
120°	195.8	196.7	197.7	198.5	199.6	200.7	201.8	202.9	204.1	204.8	205.5
122.5°	208.4	209.3	210.3	211.3	212.3	213.5	214.7	216.0	217.2	217.7	218.1
125°	227.1	227.9	228.8	229.5	230.6	231.7	232.9	234.0	235.2	235.7	236.1
127.5°	244.4	245.3	246.2	247.1	248.0	248.8	249.8	250.6	251.5	252.1	252.8
130°	255.5	256.4	257.4	258.4	259.2	259.9	260.6	261.3	262.0	262.6	263.3
132.5°	266.4	267.3	268.1	269.0	269.7	270.4	271.0	271.7	272.4	273.0	273.6
135°	281.0	282.1	283.0	284.0	284.8	285.3	285.9	286.5	287.1	287.7	288.3
137.5°	295.4	296.1	296.8	297.5	298.2	298.8	299.4	300.1	300.7	301.3	301.9
140°	304.8	305.2	305.7	306.3	306.9	307.5	308.2	308.9	309.5	310.1	310.6
142.5°	312.7	313.1	313.7	314.1	314.7	315.5	316.2	317.0	317.8	318.3	318.8
145°	324.9	324.8	324.7	324.6	325.1	326.1	327.3	328.3	329.3	329.8	330.2
147.5°	335.6	335.4	335.1	334.9	335.3	336.3	337.4	338.5	339.5	339.8	340.1
150°	342.5	342.1	341.6	341.2	341.6	342.5	343.5	344.5	345.5	345.9	346.2
152.5°	348.5	348.0	347.5	347.1	347.2	348.2	349.1	350.1	351.0	351.4	351.8
155°	357.1	356.6	356.0	355.5	355.6	356.4	357.1	357.8	358.5	359.0	359.3
157.5°	364.1	363.6	363.2	362.7	362.7	363.3	363.8	364.3	364.8	365.2	365.7
160°	368.2	367.8	367.5	367.1	367.1	367.5	367.8	368.2	368.6	368.9	369.4
162.5°	371.8	371.4	371.0	370.7	370.7	370.9	371.3	371.6	372.0	372.4	372.7
165°	376.6	376.2	375.8	375.5	375.4	375.6	375.7	375.9	376.1	376.5	376.9
167.5°	380.1	379.8	379.4	379.0	378.9	379.1	379.3	379.4	379.6	380.0	380.5
170°	382.1	381.8	381.4	381.0	380.9	381.0	381.2	381.3	381.4	381.9	382.3
172.5°	383.5	383.1	382.7	382.4	382.2	382.4	382.5	382.6	382.7	383.1	383.6
175°	385.1	384.7	384.3	383.8	383.7	383.8	383.9	384.1	384.2	384.6	385.0
177.5°	385.5	385.1	384.8	384.4	384.4	384.4	384.4	384.4	384.5	384.9	385.2
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7	384.7



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1701.8	1707.7	1710.4	1710.4	1713.6	1712.3	1710.9
5°	1799.6	1810.4	1812.7	1823.0	1830.4	1828.1	1829.3
7.5°	1896.8	1914.3	1931.5	1939.4	1940.6	1945.2	1946.9
10°	1956.6	1970.9	1997.8	1993.7	2013.8	2025.2	2006.3
12.5°	2014.2	2033.5	2052.2	2057.3	2068.6	2072.3	2064.9
15°	2066.3	2076.6	2077.8	2074.9	2078.3	2075.4	2064.6
17.5°	2017.7	2001.0	1967.1	1951.1	1938.5	1919.8	1912.2
20°	1937.2	1888.1	1830.9	1808.1	1781.2	1728.7	1741.3
22.5°	1763.6	1707.5	1650.5	1583.7	1551.9	1502.0	1499.0
25°	1493.3	1396.8	1290.6	1216.2	1172.9	1123.2	1101.4
27.5°	1161.1	1039.5	952.4	908.4	868.2	828.8	827.2
30°	942.6	851.2	783.8	746.1	721.5	705.0	708.4
32.5°	794.5	731.9	686.5	655.1	637.0	624.5	624.3
35°	649.5	606.7	577.6	564.4	551.3	542.2	542.7
37.5°	555.9	530.1	513.9	499.4	491.2	486.7	484.2
40°	507.9	486.7	474.2	465.6	458.7	452.5	451.3
42.5°	469.9	452.5	439.9	433.2	426.7	422.3	421.1
45°	417.1	402.8	391.3	383.9	381.1	377.0	377.0
47.5°	371.0	357.0	348.0	343.4	338.5	335.8	335.7
50°	339.9	329.1	321.1	318.2	314.2	312.5	311.9
52.5°	312.0	303.9	298.3	296.3	294.5	292.4	292.7
55°	274.2	269.7	267.3	265.6	262.8	259.3	261.7
57.5°	242.4	238.4	232.3	226.9	224.3	221.9	222.8
60°	220.0	212.0	204.0	197.7	196.0	190.8	190.8
62.5°	191.6	180.4	170.6	167.0	165.3	162.9	162.5
65°	147.4	142.8	140.5	138.3	137.1	137.1	136.0
67.5°	122.2	120.3	117.8	117.3	116.1	115.7	115.4
70°	108.0	105.6	104.5	104.0	102.8	103.4	101.7
72.5°	94.3	92.5	92.2	90.7	90.1	90.1	88.9
75°	74.3	74.3	73.7	73.1	72.0	71.4	72.0
77.5°	57.2	57.3	56.2	56.1	56.0	56.1	55.5
80°	45.7	46.2	45.7	45.1	44.6	45.1	44.6
82.5°	36.1	35.3	35.2	35.0	35.0	34.6	34.5
85°	20.6	21.1	20.6	20.0	20.0	20.0	20.6
87.5°	9.0	9.1	9.2	9.2	9.2	9.2	8.8
90°	6.5	6.8	7.1	7.1	7.2	7.4	7.5
92.5°	7.0	7.1	7.2	7.3	7.4	7.4	7.5
95°	11.8	12.1	12.2	12.1	12.1	12.1	12.0
97.5°	15.2	15.5	15.7	15.8	15.8	15.9	16.0
100°	17.4	17.8	18.2	18.3	18.4	18.5	18.7
102.5°	18.3	18.9	19.3	19.5	19.6	19.8	20.0
105°	19.0	19.7	20.1	20.4	20.7	20.9	21.2
107.5°	21.7	21.0	20.8	21.0	21.3	21.5	21.8
110°	30.1	23.9	21.0	21.3	21.5	21.8	22.0



TEST NUMBER: P331705-935

CATALOG NUMBER: S122RDIP-S865D330U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	55.2	32.6	21.4	21.6	21.8	22.0	22.2
115°	85.8	57.2	40.6	36.2	31.8	27.3	22.8
117.5°	169.4	162.6	151.8	137.2	122.5	107.9	93.2
120°	206.3	207.0	203.2	194.8	186.5	178.1	169.8
122.5°	218.5	219.0	218.3	216.8	215.2	213.5	211.9
125°	236.5	236.9	237.3	237.5	237.6	237.8	238.0
127.5°	253.4	254.0	254.3	254.4	254.4	254.4	254.5
130°	264.0	264.7	265.0	264.9	264.8	264.8	264.8
132.5°	274.1	274.7	275.0	274.9	274.9	274.8	274.7
135°	288.9	289.5	289.7	289.6	289.5	289.4	289.2
137.5°	302.5	303.1	303.2	303.1	302.9	302.6	302.5
140°	311.3	311.8	311.9	311.6	311.3	311.0	310.6
142.5°	319.3	319.9	319.9	319.6	319.3	319.0	318.7
145°	330.6	331.1	331.1	330.8	330.5	330.2	329.8
147.5°	340.4	340.8	340.8	340.5	340.3	340.0	339.8
150°	346.6	347.0	347.0	346.7	346.4	346.0	345.8
152.5°	352.1	352.5	352.5	352.1	351.7	351.3	350.9
155°	359.6	360.1	360.0	359.5	359.0	358.5	358.0
157.5°	366.1	366.4	366.4	365.9	365.5	365.0	364.5
160°	369.7	370.1	370.1	369.6	369.2	368.8	368.3
162.5°	373.2	373.6	373.6	373.0	372.5	372.0	371.4
165°	377.4	377.8	377.8	377.4	376.9	376.5	376.1
167.5°	380.9	381.3	381.3	380.7	380.1	379.6	379.0
170°	382.7	383.1	383.1	382.5	381.9	381.4	380.8
172.5°	384.0	384.4	384.4	383.8	383.3	382.7	382.2
175°	385.5	385.9	385.8	385.2	384.6	383.9	383.3
177.5°	385.6	385.9	385.8	385.4	385.0	384.5	384.1
180°	384.7	384.7	384.7	384.7	384.7	384.7	384.7

(END OF REPORT)