

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331463-840

Luminaire Tested: **S122DIP-S1005D1080U840-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331463-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S1005D1080U840-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7987.3 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331463-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331463-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69		62	60	58		51	49	48	43
2	89	82	76	70	82	76	70	66	65	61	57		54	51	49		45	43	41	36
3	81	72	65	59	75	67	60	55	57	52	48		48	44	41		40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41		43	39	35		35	32	30	26
5	68	57	49	43	63	53	46	40	45	40	35		38	34	31		32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31		35	30	27		29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27		32	27	24		26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24		29	24	21		24	21	18	16
9	50	38	31	26	47	36	29	24	31	25	22		27	22	19		22	19	17	14
10	47	35	28	23	44	33	26	22	29	23	20		25	20	17		21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25987	25987	25987
5°	26086	25710	25861
10°	25932	25450	25576
15°	25611	25120	25095
20°	25156	24624	24598
25°	24704	24015	24015
30°	24121	23457	23256
35°	23580	22787	22450
40°	22898	22118	21692
45°	22229	21450	20922
50°	21499	20760	20022
55°	20738	19952	19212
60°	19888	18991	18290
65°	18980	18032	17207
70°	17825	16877	16074
75°	16220	15540	15159
80°	14393	13966	13240
85°	11745	11189	10022



TEST NUMBER: P331463-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.3	1.9
10°-20°	425.9	5.3
20°-30°	626.0	7.8
30°-40°	727.1	9.1
40°-50°	726.3	9.1
50°-60°	633.4	7.9
60°-70°	468.3	5.9
70°-80°	265.3	3.3
80°-90°	76.9	1.0
90°-100°	88.1	1.1
100°-110°	273.6	3.4
110°-120°	467.6	5.9
120°-130°	614.9	7.7
130°-140°	690.2	8.6
140°-150°	676.7	8.5
150°-160°	567.6	7.1
160°-170°	376.5	4.7
170°-180°	131.6	1.6
0°-30°	1203.2	15.1
0°-40°	1930.3	24.2
0°-60°	3290.0	41.2
0°-90°	4100.5	51.3
90°-120°	829.3	10.4
90°-150°	2811.1	35.2
90°-180°	3887.0	48.7
0°-180°	7987.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1610	1610	1610	1610	1610	
5°	1610	1603	1586	1598	1596	153
15°	1532	1522	1503	1508	1501	431
25°	1387	1374	1348	1351	1348	638
35°	1196	1180	1156	1147	1139	747
45°	974	962	939	923	916	751
55°	737	727	709	691	682	658
65°	497	487	472	458	450	491
75°	260	257	249	241	243	278
85°	63	62	60	56	54	73
90°	1	16	41	39	40	6
95°	61	72	75	75	73	70
105°	252	256	258	260	260	266
115°	469	476	474	473	469	464
125°	683	692	690	686	685	610
135°	883	896	899	897	894	682
145°	1072	1080	1087	1088	1084	670
155°	1226	1229	1233	1238	1235	564
165°	1334	1333	1333	1340	1335	376
175°	1388	1384	1382	1389	1383	132
180°	1390	1390	1390	1390	1390	



TEST NUMBER: P331463-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1617.0	1615.6	1614.3	1612.9	1611.4	1609.3	1606.3	1603.3	1600.2	1597.2	1599.9
5°	1609.5	1608.2	1606.8	1605.4	1604.1	1601.4	1597.7	1593.9	1590.1	1586.3	1589.1
7.5°	1595.3	1593.2	1591.0	1588.9	1586.8	1583.8	1579.9	1576.1	1572.3	1568.4	1571.1
10°	1581.7	1579.3	1576.9	1574.5	1572.1	1568.8	1564.7	1560.5	1556.4	1552.3	1555.1
12.5°	1563.2	1560.9	1558.8	1556.7	1554.6	1551.5	1547.3	1543.2	1539.1	1535.0	1536.9
15°	1532.2	1530.1	1528.0	1526.0	1523.9	1520.7	1516.2	1511.7	1507.2	1502.8	1504.2
17.5°	1492.6	1490.5	1488.4	1486.3	1484.3	1481.0	1476.4	1471.9	1467.3	1462.9	1464.4
20°	1464.1	1462.0	1460.0	1457.8	1455.8	1452.4	1447.5	1442.8	1437.9	1433.1	1434.1
22.5°	1435.6	1432.7	1429.9	1426.9	1424.0	1420.4	1415.8	1411.3	1406.7	1402.2	1402.4
25°	1386.7	1383.9	1381.2	1378.5	1375.7	1371.4	1365.5	1359.7	1353.8	1348.0	1348.7
27.5°	1331.0	1328.5	1326.1	1323.5	1321.1	1317.6	1312.9	1308.3	1303.7	1299.1	1298.1
30°	1293.8	1291.1	1288.3	1285.6	1282.8	1278.9	1273.7	1268.6	1263.4	1258.2	1257.2
32.5°	1254.3	1252.0	1249.8	1247.6	1245.4	1241.6	1236.2	1230.7	1225.3	1219.8	1218.0
35°	1196.3	1192.9	1189.4	1186.0	1182.6	1178.1	1172.6	1167.1	1161.6	1156.1	1154.1
37.5°	1131.0	1128.0	1125.0	1122.0	1118.9	1114.7	1109.1	1103.7	1098.1	1092.7	1090.0
40°	1086.4	1083.7	1081.0	1078.2	1075.4	1071.4	1065.8	1060.4	1054.8	1049.4	1046.2
42.5°	1043.1	1040.4	1037.6	1034.9	1032.1	1027.9	1022.5	1016.9	1011.5	1005.9	1002.6
45°	973.5	971.1	968.7	966.2	963.8	960.1	954.9	949.8	944.6	939.4	935.6
47.5°	904.1	901.9	899.6	897.4	895.0	891.2	885.9	880.5	875.1	869.8	865.8
50°	855.9	854.1	852.4	850.7	849.0	845.7	840.9	836.1	831.2	826.5	821.6
52.5°	808.8	806.6	804.3	802.0	799.7	796.3	791.7	787.2	782.7	778.2	774.2
55°	736.7	734.6	732.6	730.5	728.4	725.3	721.2	717.1	713.0	708.8	704.7
57.5°	664.3	662.6	661.0	659.3	657.6	654.6	650.1	645.5	641.0	636.4	632.4
60°	615.9	614.6	613.2	611.9	610.5	607.3	602.6	597.7	592.9	588.1	584.3
62.5°	569.0	566.7	564.5	562.3	560.1	557.1	553.4	549.8	546.0	542.3	538.8
65°	496.8	494.7	492.7	490.6	488.6	485.7	482.3	478.9	475.4	472.0	469.0
67.5°	423.4	421.8	420.1	418.5	416.9	414.4	411.3	408.3	405.2	402.1	399.7
70°	377.6	376.3	374.9	373.5	372.1	369.9	366.8	363.7	360.6	357.5	355.1
72.5°	330.5	329.2	327.8	326.5	325.1	323.4	321.4	319.4	317.4	315.4	313.0
75°	260.0	259.3	258.6	257.9	257.2	256.0	254.3	252.6	250.9	249.1	247.1
77.5°	196.8	195.7	194.5	193.4	192.2	191.3	190.6	189.9	189.1	188.5	187.4
80°	154.8	154.4	154.1	153.7	153.4	152.9	152.2	151.5	150.8	150.2	149.1
82.5°	115.1	115.1	115.0	114.9	114.8	114.6	114.2	113.8	113.4	113.0	111.7
85°	63.4	63.1	62.8	62.4	62.1	61.7	61.4	61.0	60.7	60.4	59.3
87.5°	22.5	22.6	22.7	22.7	22.8	23.1	23.7	24.3	24.9	25.5	24.6
90°	1.2	4.3	7.5	10.6	13.7	18.1	23.8	29.6	35.3	41.1	40.5
92.5°	20.9	23.1	25.4	27.8	30.1	31.9	33.2	34.6	36.0	37.3	37.4
95°	61.0	63.6	66.2	68.8	71.4	73.0	73.5	74.0	74.5	75.0	75.0
97.5°	111.5	113.7	116.0	118.4	120.6	122.3	123.2	124.2	125.2	126.2	126.2
100°	149.0	151.1	153.2	155.2	157.3	158.8	159.6	160.3	161.1	161.9	161.9
102.5°	188.4	190.1	191.8	193.4	195.1	196.4	197.4	198.3	199.3	200.4	200.6
105°	252.2	253.0	253.8	254.6	255.3	256.0	256.5	257.0	257.5	258.0	258.6
107.5°	316.5	317.6	318.8	319.9	321.0	321.6	321.6	321.6	321.6	321.6	321.8
110°	357.8	359.3	360.9	362.4	364.1	364.9	364.9	364.9	364.9	364.9	364.9



TEST NUMBER: P331463-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	402.8	404.3	406.0	407.5	409.1	409.8	409.5	409.3	409.1	408.9	408.3
115°	469.2	470.8	472.3	473.9	475.4	475.9	475.4	474.9	474.4	473.9	473.6
117.5°	535.3	537.5	539.6	541.6	543.7	544.0	542.6	541.1	539.7	538.2	537.6
120°	579.5	581.6	583.7	585.7	587.8	587.8	585.7	583.7	581.6	579.5	579.5
122.5°	619.9	622.4	624.8	627.3	629.9	630.4	628.9	627.4	626.0	624.5	623.9
125°	682.7	685.1	687.4	689.7	692.1	692.9	692.1	691.4	690.5	689.7	688.9
127.5°	744.0	746.9	749.9	752.9	755.8	756.9	755.9	755.0	754.1	753.1	752.1
130°	782.4	785.8	789.2	792.5	796.0	797.4	796.9	796.4	795.9	795.4	794.8
132.5°	825.6	828.4	831.1	833.8	836.7	838.1	838.2	838.3	838.4	838.5	837.4
135°	883.3	886.2	889.1	891.9	894.7	896.5	897.0	897.5	898.1	898.6	898.3
137.5°	944.0	946.4	948.8	951.1	953.4	954.9	955.6	956.3	956.9	957.7	957.5
140°	980.7	983.0	985.3	987.7	990.1	991.9	993.2	994.5	995.8	997.0	997.0
142.5°	1018.2	1020.6	1022.9	1025.2	1027.5	1029.2	1030.1	1031.0	1031.9	1032.8	1033.0
145°	1072.2	1074.0	1075.8	1077.6	1079.4	1081.2	1082.7	1084.3	1085.8	1087.4	1087.6
147.5°	1120.2	1122.5	1124.6	1126.8	1129.0	1130.6	1131.7	1132.8	1133.8	1134.8	1135.4
150°	1153.1	1154.7	1156.2	1157.8	1159.3	1160.6	1161.7	1162.8	1163.8	1164.9	1165.6
152.5°	1182.1	1183.8	1185.3	1186.9	1188.4	1189.8	1191.1	1192.3	1193.7	1194.9	1195.9
155°	1225.9	1226.6	1227.4	1228.2	1229.0	1229.7	1230.5	1231.3	1232.1	1232.8	1234.2
157.5°	1263.1	1263.6	1264.1	1264.7	1265.3	1265.7	1266.2	1266.7	1267.1	1267.6	1269.4
160°	1285.7	1286.2	1286.7	1287.2	1287.8	1288.1	1288.4	1288.7	1288.9	1289.2	1290.7
162.5°	1306.3	1306.4	1306.5	1306.6	1306.8	1306.9	1307.2	1307.4	1307.7	1308.0	1309.7
165°	1333.7	1333.5	1333.2	1332.9	1332.7	1332.6	1332.6	1332.6	1332.6	1332.6	1334.4
167.5°	1356.8	1355.9	1355.1	1354.4	1353.6	1353.2	1353.1	1353.1	1353.0	1353.0	1354.8
170°	1369.0	1368.2	1367.4	1366.5	1365.8	1365.3	1365.0	1364.7	1364.5	1364.2	1366.0
172.5°	1377.4	1376.6	1375.8	1375.0	1374.2	1373.7	1373.5	1373.2	1372.9	1372.7	1374.5
175°	1387.8	1386.9	1386.1	1385.3	1384.6	1383.9	1383.4	1382.9	1382.4	1381.8	1383.7
177.5°	1391.9	1391.3	1390.7	1390.1	1389.5	1388.9	1388.5	1388.1	1387.7	1387.3	1388.5
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1



TEST NUMBER: P331463-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5	1609.5
2.5°	1602.7	1605.4	1608.2	1609.3	1608.7	1608.2	1607.6	1607.1
5°	1591.9	1594.6	1597.3	1598.4	1597.7	1597.0	1596.3	1595.6
7.5°	1573.9	1576.6	1579.4	1580.4	1579.6	1578.9	1578.1	1577.4
10°	1557.8	1560.5	1563.3	1564.2	1563.2	1562.1	1561.0	1560.0
12.5°	1538.8	1540.8	1542.7	1543.3	1542.5	1541.8	1541.0	1540.2
15°	1505.5	1506.9	1508.2	1508.1	1506.4	1504.7	1503.0	1501.3
17.5°	1466.0	1467.6	1469.2	1469.2	1467.4	1465.8	1464.2	1462.5
20°	1435.2	1436.2	1437.2	1437.0	1435.7	1434.3	1433.0	1431.6
22.5°	1402.6	1402.8	1403.0	1402.7	1401.9	1401.1	1400.2	1399.4
25°	1349.4	1350.1	1350.8	1350.8	1350.1	1349.4	1348.7	1348.0
27.5°	1297.1	1296.0	1294.9	1293.6	1292.0	1290.3	1288.7	1287.1
30°	1256.2	1255.2	1254.2	1252.9	1251.5	1250.1	1248.8	1247.4
32.5°	1216.2	1214.3	1212.4	1210.8	1209.4	1208.1	1206.7	1205.3
35°	1152.0	1149.9	1147.8	1146.0	1144.3	1142.6	1140.7	1139.0
37.5°	1087.5	1085.0	1082.5	1080.4	1078.7	1077.0	1075.4	1073.8
40°	1043.1	1040.1	1036.9	1034.7	1033.3	1032.0	1030.6	1029.2
42.5°	999.3	995.8	992.5	989.9	988.0	986.0	984.1	982.1
45°	931.9	928.1	924.3	921.7	920.3	919.0	917.6	916.3
47.5°	861.8	857.8	853.8	850.8	848.8	846.9	844.9	842.8
50°	816.8	812.0	807.2	804.0	802.2	800.5	798.8	797.1
52.5°	770.2	766.2	762.2	759.1	756.8	754.6	752.2	750.0
55°	700.5	696.4	692.4	689.4	687.7	686.0	684.3	682.5
57.5°	628.2	624.2	620.2	617.4	616.2	614.9	613.6	612.3
60°	580.6	576.7	573.0	570.6	569.6	568.6	567.4	566.4
62.5°	535.3	531.8	528.3	525.8	524.5	523.2	521.9	520.6
65°	465.9	462.7	459.7	457.3	455.6	453.8	452.1	450.4
67.5°	397.3	394.9	392.4	390.5	389.2	387.8	386.5	385.1
70°	352.6	350.3	347.9	346.0	344.6	343.3	341.8	340.5
72.5°	310.6	308.2	305.8	304.1	303.0	301.8	300.7	299.6
75°	245.1	243.0	241.0	240.2	241.0	241.6	242.3	243.0
77.5°	186.4	185.4	184.4	183.4	182.4	181.5	180.5	179.6
80°	148.0	147.0	146.0	145.1	144.4	143.8	143.1	142.4
82.5°	110.4	109.1	107.8	107.0	106.8	106.7	106.6	106.4
85°	58.3	57.3	56.2	55.5	55.2	54.8	54.5	54.1
87.5°	23.7	22.7	21.8	21.2	21.0	20.8	20.6	20.4
90°	40.0	39.5	39.0	38.9	39.1	39.4	39.6	39.9
92.5°	37.5	37.6	37.8	37.8	37.9	37.9	38.0	38.0
95°	75.0	75.0	75.0	74.8	74.3	73.8	73.2	72.7
97.5°	126.2	126.2	126.2	126.2	126.1	126.1	126.0	126.0
100°	161.9	161.9	161.9	161.8	161.5	161.3	161.0	160.7
102.5°	200.8	201.0	201.2	201.2	200.9	200.7	200.4	200.2
105°	259.1	259.6	260.1	260.4	260.4	260.4	260.4	260.4
107.5°	322.0	322.2	322.4	321.9	320.8	319.6	318.4	317.2
110°	364.9	364.9	364.9	364.5	363.7	362.8	362.0	361.3





TEST NUMBER: P331463-840

CATALOG NUMBER: S122DIP-S1005D1080U840-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	407.7	407.1	406.5	405.9	405.3	404.7	404.1	403.5
115°	473.4	473.1	472.8	472.3	471.6	470.8	470.0	469.2
117.5°	536.9	536.3	535.7	535.0	534.2	533.4	532.6	531.9
120°	579.5	579.5	579.5	579.1	578.3	577.5	576.7	575.9
122.5°	623.3	622.7	622.0	621.5	620.9	620.3	619.8	619.1
125°	688.2	687.4	686.6	686.1	685.8	685.6	685.3	685.1
127.5°	751.2	750.2	749.3	748.4	747.6	746.8	746.0	745.1
130°	794.3	793.8	793.2	792.4	791.4	790.3	789.3	788.3
132.5°	836.2	835.1	833.9	832.9	832.1	831.2	830.4	829.6
135°	898.1	897.8	897.5	897.0	896.2	895.4	894.6	893.8
137.5°	957.3	957.0	956.8	956.2	955.1	954.1	953.1	952.0
140°	997.0	997.0	997.0	996.5	995.5	994.5	993.4	992.4
142.5°	1033.2	1033.4	1033.6	1033.2	1032.1	1031.1	1030.1	1029.0
145°	1087.9	1088.2	1088.4	1088.0	1087.0	1086.0	1084.9	1083.9
147.5°	1136.0	1136.5	1137.1	1136.9	1135.9	1134.9	1133.9	1133.0
150°	1166.4	1167.2	1168.0	1168.0	1167.2	1166.4	1165.6	1164.9
152.5°	1196.9	1197.8	1198.8	1198.8	1197.8	1196.9	1195.9	1194.9
155°	1235.5	1236.8	1238.1	1238.3	1237.6	1236.8	1236.0	1235.2
157.5°	1271.1	1272.9	1274.7	1275.0	1273.6	1272.4	1271.2	1269.9
160°	1292.3	1293.8	1295.5	1295.7	1294.6	1293.6	1292.5	1291.5
162.5°	1311.5	1313.2	1315.0	1315.2	1314.0	1312.8	1311.5	1310.3
165°	1336.3	1338.1	1339.9	1340.1	1338.9	1337.6	1336.3	1334.9
167.5°	1356.7	1358.5	1360.3	1360.5	1359.2	1357.8	1356.5	1355.1
170°	1367.9	1369.7	1371.5	1371.7	1370.1	1368.6	1367.0	1365.4
172.5°	1376.3	1378.2	1380.0	1380.1	1378.6	1377.0	1375.4	1373.8
175°	1385.5	1387.4	1389.2	1389.3	1387.8	1386.1	1384.6	1383.0
177.5°	1389.8	1391.0	1392.2	1392.2	1391.0	1389.8	1388.5	1387.3
180°	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1	1390.1

(END OF REPORT)