

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331439-840

Luminaire Tested: **S122DIP-S1005D725U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331439-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S1005D725U840-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7061.9 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63																			
1	101	97	93	90	95	91	88	85	80	78	76	70	69	67	61	60	59	54																			
2	93	86	80	75	87	81	75	71	71	67	64	62	59	57	54	52	50	46																			
3	85	76	69	63	80	71	65	60	63	58	54	56	52	49	49	46	44	40																			
4	78	68	60	54	73	64	57	51	57	51	47	50	46	42	44	41	38	35																			
5	72	61	53	47	67	57	50	45	51	45	41	45	41	37	40	36	34	31																			
6	67	55	47	41	62	52	45	39	46	40	36	41	37	33	37	33	30	27																			
7	62	50	42	36	58	47	40	35	42	36	32	38	33	29	34	30	27	24																			
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24	22																			
9	54	42	34	29	50	40	33	28	36	30	26	32	27	24	29	25	22	20																			
10	50	38	31	26	47	36	30	25	33	27	24	30	25	22	27	23	20	18																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32513	32513	32513	32513
5°	36451	32725	29000	32725
10°	41769	32455	25097	32455
15°	46208	31861	22173	31861
20°	45505	31223	20213	31223
25°	41031	30375	18971	30375
30°	33907	29015	18066	29015
35°	24711	27595	17420	27595
40°	19736	25918	17062	25918
45°	17249	23980	16575	23980
50°	16211	22102	16252	22102
55°	14945	20194	15817	20194
60°	13695	18167	15145	18167
65°	12478	16351	14487	16351
70°	11325	14578	13520	14578
75°	10044	12601	11977	12601
80°	8638	10432	9642	10432
85°	7744	7744	5743	7744



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.8	2.7
10°-20°	557.5	7.9
20°-30°	809.1	11.5
30°-40°	853.9	12.1
40°-50°	756.0	10.7
50°-60°	603.3	8.5
60°-70°	410.1	5.8
70°-80°	210.2	3.0
80°-90°	54.4	0.8
90°-100°	59.3	0.8
100°-110°	184.1	2.6
110°-120°	314.7	4.5
120°-130°	413.8	5.9
130°-140°	464.4	6.6
140°-150°	455.4	6.4
150°-160°	382.0	5.4
160°-170°	253.3	3.6
170°-180°	88.5	1.3
0°-30°	1558.5	22.1
0°-40°	2412.3	34.2
0°-60°	3771.7	53.4
0°-90°	4446.4	63.0
90°-120°	558.0	7.9
90°-150°	1891.7	26.8
90°-180°	2616.0	37.0
0°-180°	7061.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2014	2014	2014	2014	2014	
5°	2249	2019	1789	2019	2249	225
15°	2764	1906	1326	1906	2764	763
25°	2303	1705	1065	1705	2303	1041
35°	1254	1400	884	1400	1254	815
45°	755	1050	726	1050	755	594
55°	531	717	562	717	531	476
65°	327	428	379	428	327	325
75°	161	202	192	202	161	172
85°	42	42	31	42	42	46
90°	27	1	27	1	27	14
95°	49	41	49	41	49	55
105°	175	170	175	170	175	184
115°	316	316	316	316	316	312
125°	461	459	461	459	461	411
135°	602	594	602	594	602	463
145°	729	721	729	721	729	455
155°	831	825	831	825	831	383
165°	898	898	898	898	898	253
175°	931	934	931	934	931	88
180°	935	935	935	935	935	



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2106.6	2107.2	2108.4	2098.5	2097.3	2097.3	2088.6	2081.2	2072.5	2060.7	2062.0
5°	2249.0	2257.5	2260.6	2251.3	2237.4	2235.8	2222.7	2201.0	2180.9	2164.6	2153.0
7.5°	2418.9	2422.4	2414.8	2402.6	2392.2	2373.6	2349.1	2325.1	2291.6	2260.8	2237.9
10°	2547.7	2552.3	2539.2	2521.4	2506.7	2485.1	2449.4	2413.1	2368.9	2326.4	2292.3
12.5°	2645.5	2657.0	2640.1	2637.8	2612.6	2582.8	2540.4	2522.0	2459.9	2400.7	2364.2
15°	2764.4	2763.6	2765.2	2750.5	2731.9	2727.2	2682.4	2633.6	2546.2	2511.3	2450.9
17.5°	2730.1	2741.8	2747.2	2747.0	2746.6	2743.7	2729.3	2698.5	2654.6	2598.2	2528.5
20°	2648.4	2663.8	2666.1	2683.9	2694.0	2707.1	2712.6	2704.0	2677.0	2629.8	2569.4
22.5°	2522.0	2526.4	2533.7	2561.3	2583.1	2616.2	2633.3	2661.9	2651.6	2628.5	2578.1
25°	2303.2	2295.4	2322.5	2336.4	2386.7	2439.3	2477.3	2519.1	2556.3	2578.7	2563.9
27.5°	2040.3	2028.7	2069.3	2106.3	2147.2	2204.1	2263.2	2333.0	2391.1	2463.7	2488.6
30°	1818.7	1825.6	1864.3	1903.8	1965.7	2046.2	2112.7	2189.4	2272.2	2353.5	2409.9
32.5°	1579.7	1606.5	1630.9	1691.4	1746.0	1835.7	1933.2	2029.0	2132.3	2224.7	2312.2
35°	1253.7	1284.6	1318.8	1362.8	1439.5	1528.4	1623.7	1752.9	1893.8	2019.9	2123.6
37.5°	1055.3	1050.4	1069.9	1101.8	1163.8	1235.7	1345.2	1472.9	1638.7	1787.0	1933.2
40°	936.4	933.3	947.3	976.6	1023.9	1076.5	1172.5	1284.6	1438.7	1619.8	1793.9
42.5°	854.7	856.6	864.3	885.0	917.4	960.7	1032.6	1128.0	1269.1	1439.7	1626.8
45°	755.4	760.7	769.3	779.3	797.9	833.5	873.7	941.9	1053.3	1195.7	1379.9
47.5°	683.8	684.0	692.7	701.5	712.5	732.6	765.4	808.1	886.8	1002.7	1161.0
50°	645.4	640.1	646.2	653.2	664.8	678.7	700.3	740.6	793.2	886.9	1019.3
52.5°	598.3	598.5	604.1	606.7	617.1	631.1	650.9	678.7	726.4	799.6	908.4
55°	530.9	534.7	537.9	542.5	551.8	561.9	577.3	595.9	633.1	688.0	768.5
57.5°	467.5	468.7	471.8	480.6	486.5	495.7	510.5	527.4	551.5	592.2	652.7
60°	424.1	424.1	430.3	434.1	441.9	451.2	462.8	479.1	500.7	534.0	582.8
62.5°	384.5	383.8	386.4	392.6	398.6	407.3	418.8	432.6	453.0	482.6	522.7
65°	326.6	325.1	329.7	331.2	337.4	346.0	355.3	369.9	386.2	407.9	443.4
67.5°	270.8	272.8	275.2	278.1	281.6	290.5	296.7	307.1	320.8	338.8	362.9
70°	239.9	239.9	239.9	242.3	246.9	251.6	257.7	266.2	279.4	294.9	316.5
72.5°	205.2	207.7	210.2	208.8	214.7	217.4	224.9	229.7	242.3	252.2	271.4
75°	161.0	161.0	161.0	164.8	167.1	169.5	174.1	178.7	185.0	197.3	207.4
77.5°	120.1	119.8	120.6	121.5	124.0	126.7	128.2	132.3	138.0	143.8	152.3
80°	92.9	94.4	95.2	96.7	96.7	98.3	99.1	104.5	108.4	112.2	117.6
82.5°	71.8	72.1	72.3	72.6	73.2	74.1	76.1	77.9	79.3	82.5	86.6
85°	41.8	41.0	41.0	42.5	41.8	41.8	43.3	44.8	44.8	45.6	48.0
87.5°	21.5	21.4	22.0	21.4	21.3	21.9	22.0	21.5	22.2	22.8	22.7
90°	26.9	26.7	26.5	26.4	26.2	26.3	26.6	27.0	27.3	27.7	23.7
92.5°	25.5	25.5	25.5	25.4	25.4	25.3	25.3	25.2	25.1	25.1	24.2
95°	49.0	49.3	49.7	50.0	50.4	50.5	50.5	50.5	50.5	50.5	50.2
97.5°	84.7	84.8	84.8	84.9	84.9	84.9	84.9	84.9	84.9	84.9	84.2
100°	108.2	108.4	108.5	108.7	108.9	109.0	109.0	109.0	109.0	109.0	108.4
102.5°	134.6	134.8	135.0	135.2	135.3	135.4	135.2	135.1	134.9	134.8	134.1
105°	175.2	175.2	175.2	175.2	175.2	175.1	174.7	174.4	174.0	173.7	173.3
107.5°	213.5	214.3	215.1	215.9	216.7	217.0	216.8	216.7	216.6	216.4	216.4
110°	243.1	243.7	244.2	244.7	245.2	245.5	245.5	245.5	245.5	245.5	245.5



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	271.6	272.0	272.3	272.7	273.1	273.5	273.9	274.3	274.8	275.2	275.3
115°	315.8	316.3	316.8	317.3	317.8	318.2	318.4	318.5	318.7	318.9	319.2
117.5°	357.9	358.4	358.9	359.5	360.0	360.4	360.9	361.3	361.7	362.1	363.1
120°	387.6	388.1	388.6	389.1	389.7	389.9	389.9	389.9	389.9	389.9	391.3
122.5°	416.7	417.0	417.4	417.8	418.2	418.6	419.0	419.4	419.8	420.2	421.2
125°	461.0	461.2	461.3	461.5	461.7	462.0	462.5	463.1	463.6	464.1	464.6
127.5°	501.4	502.0	502.5	503.1	503.6	504.2	504.8	505.5	506.1	506.8	507.4
130°	530.5	531.2	531.9	532.5	533.2	533.8	534.1	534.5	534.8	535.2	535.5
132.5°	558.3	558.8	559.4	559.9	560.5	561.2	561.9	562.7	563.5	564.2	564.1
135°	601.5	602.0	602.6	603.1	603.6	603.9	604.1	604.3	604.5	604.6	604.3
137.5°	640.7	641.4	642.1	642.8	643.5	643.9	644.0	644.2	644.3	644.4	644.0
140°	667.8	668.5	669.2	669.9	670.6	671.0	671.0	671.0	671.0	671.0	670.0
142.5°	692.5	693.2	693.8	694.5	695.2	695.5	695.4	695.2	695.1	695.0	694.4
145°	729.3	730.0	730.7	731.4	732.2	732.5	732.3	732.1	732.0	731.7	730.6
147.5°	762.3	763.1	763.7	764.4	765.1	765.2	764.8	764.4	764.0	763.7	763.0
150°	783.9	784.4	784.9	785.4	786.0	786.0	785.4	784.9	784.4	783.9	783.2
152.5°	804.1	804.7	805.4	806.1	806.7	806.7	806.1	805.4	804.7	804.1	803.1
155°	831.2	831.7	832.2	832.7	833.3	833.1	832.2	831.3	830.5	829.6	829.1
157.5°	854.5	855.4	856.3	857.1	857.9	857.8	856.6	855.4	854.1	852.9	852.6
160°	869.1	869.8	870.5	871.2	871.9	871.7	870.7	869.6	868.6	867.5	867.4
162.5°	881.7	882.5	883.4	884.2	885.0	884.9	883.7	882.5	881.3	880.1	880.0
165°	898.3	899.2	900.0	900.9	901.8	901.6	900.4	899.2	898.0	896.7	896.7
167.5°	911.9	912.8	913.7	914.6	915.5	915.3	914.1	912.9	911.7	910.4	910.5
170°	918.8	919.9	920.9	922.0	923.0	922.9	921.7	920.5	919.3	918.0	918.2
172.5°	924.5	925.5	926.6	927.7	928.7	928.6	927.4	926.1	924.9	923.7	923.9
175°	930.7	931.7	932.7	933.8	934.8	934.7	933.5	932.3	931.1	929.9	930.2
177.5°	933.5	934.3	935.1	936.0	936.9	936.9	936.0	935.1	934.3	933.5	933.7
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2066.4	2061.4	2058.3	2047.2	2037.2	2027.3	2024.3	2025.5	2011.9	1998.8	1993.3
5°	2146.9	2131.3	2116.7	2095.8	2071.0	2043.9	2029.9	2019.1	1992.1	1962.7	1945.6
7.5°	2219.0	2196.9	2168.5	2129.2	2093.1	2050.5	2023.5	1999.4	1959.8	1918.3	1893.0
10°	2262.9	2232.7	2196.4	2148.4	2104.3	2052.4	2016.0	1979.6	1933.2	1883.7	1852.7
12.5°	2300.7	2260.0	2224.2	2162.6	2110.4	2045.6	2002.5	1951.2	1902.3	1843.4	1813.1
15°	2390.7	2315.5	2247.5	2177.8	2113.5	2023.0	1975.0	1906.1	1841.9	1769.2	1734.3
17.5°	2460.1	2375.7	2268.5	2180.0	2105.1	2004.8	1934.3	1851.8	1775.8	1692.7	1645.4
20°	2499.7	2403.0	2287.6	2182.4	2092.6	1978.1	1901.5	1817.2	1728.2	1634.5	1583.5
22.5°	2523.2	2421.6	2307.5	2173.1	2067.9	1956.4	1860.0	1767.6	1677.4	1576.3	1522.8
25°	2530.7	2437.8	2317.1	2165.5	2036.9	1910.8	1794.7	1705.0	1595.8	1501.4	1423.2
27.5°	2493.9	2427.3	2311.2	2150.8	2001.1	1853.7	1724.2	1622.6	1507.4	1404.9	1326.4
30°	2448.6	2409.9	2296.9	2136.0	1972.7	1814.0	1671.6	1556.3	1441.8	1338.1	1257.6
32.5°	2378.7	2370.4	2271.0	2115.0	1942.4	1763.9	1616.6	1500.0	1373.1	1271.2	1194.5
35°	2241.3	2278.4	2215.7	2067.9	1885.2	1692.5	1533.1	1400.0	1268.5	1170.9	1098.9
37.5°	2057.1	2149.3	2132.9	1999.0	1808.2	1614.9	1438.9	1299.7	1174.4	1075.9	1005.3
40°	1930.2	2047.8	2064.8	1946.4	1753.7	1554.8	1368.3	1229.7	1107.4	1017.7	946.4
42.5°	1793.9	1931.4	1978.1	1883.2	1694.3	1491.7	1305.1	1161.6	1040.6	953.3	890.2
45°	1565.6	1747.5	1831.9	1777.7	1595.1	1387.7	1195.7	1050.2	940.3	858.3	809.5
47.5°	1352.2	1551.0	1664.4	1645.2	1484.7	1279.3	1089.5	949.9	842.9	777.5	733.9
50°	1201.1	1405.4	1542.4	1548.6	1405.4	1201.8	1011.5	879.9	781.6	720.5	684.9
52.5°	1069.9	1264.9	1414.2	1447.0	1316.9	1121.4	941.5	810.6	724.1	667.9	636.0
55°	898.5	1063.4	1229.0	1289.3	1184.9	999.2	832.7	717.4	636.1	597.4	569.6
57.5°	747.0	884.4	1037.3	1104.1	1039.7	880.7	724.7	624.5	558.7	524.7	503.3
60°	667.1	775.5	911.7	991.4	935.6	794.1	657.8	562.6	508.5	478.3	458.2
62.5°	592.8	688.8	804.0	876.9	846.5	713.0	591.0	507.0	460.2	431.8	417.3
65°	489.1	564.9	654.0	721.2	701.1	599.8	500.0	428.0	390.8	368.4	356.8
67.5°	402.7	457.6	519.3	578.2	562.0	490.2	410.0	354.0	326.3	306.9	299.9
70°	348.3	390.0	445.0	492.2	479.1	420.2	356.8	308.8	284.8	268.5	261.6
72.5°	296.3	330.6	372.5	411.1	402.2	353.4	300.4	264.2	245.8	230.8	225.1
75°	223.7	249.9	275.5	301.0	298.7	260.8	229.8	202.0	187.3	175.7	173.4
77.5°	165.1	179.9	197.2	212.4	208.1	186.5	162.2	146.2	135.4	127.6	126.4
80°	126.1	134.6	147.0	157.8	152.5	143.2	123.8	112.2	104.5	96.7	93.6
82.5°	91.5	100.0	107.4	113.3	109.2	100.5	88.6	80.7	76.0	70.7	69.5
85°	48.0	52.6	55.7	57.3	55.7	50.3	44.8	41.8	38.0	35.6	34.8
87.5°	22.5	21.8	21.0	21.6	19.4	19.0	16.1	13.7	13.5	13.4	12.5
90°	19.9	16.1	12.2	9.2	7.1	5.0	2.9	0.8	2.9	5.0	7.1
92.5°	23.2	22.3	21.4	20.2	18.7	17.2	15.6	14.0	15.6	17.2	18.7
95°	49.8	49.5	49.1	48.1	46.4	44.5	42.8	41.0	42.8	44.5	46.4
97.5°	83.6	82.9	82.3	81.2	79.6	78.1	76.5	75.0	76.5	78.1	79.6
100°	107.9	107.3	106.8	105.8	104.4	103.0	101.7	100.3	101.7	103.0	104.4
102.5°	133.5	132.8	132.2	131.3	130.2	129.1	127.8	126.7	127.8	129.1	130.2
105°	173.0	172.6	172.3	171.8	171.3	170.8	170.3	169.8	170.3	170.8	171.3
107.5°	216.4	216.4	216.4	216.0	215.3	214.5	213.8	213.0	213.8	214.5	215.3
110°	245.5	245.5	245.5	245.0	243.9	242.9	241.8	240.8	241.8	242.9	243.9



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.5	275.6	275.7	275.3	274.2	273.2	272.2	271.0	272.2	273.2	274.2
115°	319.6	319.9	320.3	319.9	318.9	317.8	316.8	315.8	316.8	317.8	318.9
117.5°	364.2	365.1	366.1	365.9	364.5	363.0	361.6	360.2	361.6	363.0	364.5
120°	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9	391.3	392.7	394.2
122.5°	422.2	423.2	424.1	423.8	422.1	420.5	418.8	417.1	418.8	420.5	422.1
125°	465.1	465.7	466.3	465.7	464.1	462.5	461.0	459.4	461.0	462.5	464.1
127.5°	508.1	508.7	509.3	508.6	506.6	504.6	502.6	500.6	502.6	504.6	506.6
130°	535.8	536.2	536.5	535.6	533.3	531.1	528.8	526.5	528.8	531.1	533.3
132.5°	564.1	564.0	563.9	563.0	561.1	559.3	557.4	555.5	557.4	559.3	561.1
135°	603.9	603.6	603.2	602.1	600.2	598.2	596.3	594.4	596.3	598.2	600.2
137.5°	643.5	643.1	642.6	641.6	640.1	638.4	636.8	635.3	636.8	638.4	640.1
140°	669.2	668.3	667.4	666.2	664.6	663.1	661.5	659.9	661.5	663.1	664.6
142.5°	693.8	693.2	692.6	691.5	689.9	688.3	686.7	685.2	686.7	688.3	689.9
145°	729.6	728.6	727.5	726.4	725.2	724.0	722.7	721.4	722.7	724.0	725.2
147.5°	762.2	761.5	760.8	759.7	758.2	756.8	755.3	753.9	755.3	756.8	758.2
150°	782.4	781.7	781.0	780.1	779.1	778.0	777.0	776.0	777.0	778.0	779.1
152.5°	802.3	801.5	800.6	799.7	798.7	797.6	796.6	795.5	796.6	797.6	798.7
155°	828.6	828.0	827.5	827.0	826.5	826.0	825.4	824.9	825.4	826.0	826.5
157.5°	852.3	852.0	851.7	851.4	851.0	850.7	850.3	850.0	850.3	850.7	851.0
160°	867.2	867.0	866.8	866.6	866.2	865.9	865.5	865.2	865.5	865.9	866.2
162.5°	879.8	879.6	879.4	879.3	879.2	879.2	879.1	879.0	879.1	879.2	879.2
165°	896.7	896.7	896.7	896.8	897.0	897.2	897.4	897.5	897.4	897.2	897.0
167.5°	910.5	910.6	910.6	910.9	911.4	911.9	912.4	912.9	912.4	911.9	911.4
170°	918.4	918.6	918.7	919.1	919.6	920.1	920.7	921.2	920.7	920.1	919.6
172.5°	924.0	924.2	924.4	924.7	925.2	925.8	926.3	926.9	926.3	925.8	925.2
175°	930.6	930.9	931.3	931.7	932.2	932.7	933.3	933.8	933.3	932.7	932.2
177.5°	934.0	934.3	934.6	934.9	935.3	935.8	936.2	936.6	936.2	935.8	935.3
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1987.1	1983.4	1970.3	1963.6	1952.5	1941.9	1935.1	1938.2	1940.7	1939.4	1937.5
5°	1930.2	1915.4	1893.0	1873.6	1859.7	1834.2	1823.3	1818.0	1813.3	1807.9	1802.4
7.5°	1862.3	1839.2	1807.0	1779.4	1753.3	1721.6	1703.5	1692.7	1681.5	1669.3	1658.5
10°	1814.0	1781.5	1747.5	1708.8	1677.9	1649.2	1623.7	1606.6	1591.1	1576.5	1565.6
12.5°	1763.3	1725.9	1683.7	1630.8	1596.7	1555.7	1551.9	1521.9	1497.6	1488.5	1475.8
15°	1682.4	1629.8	1576.5	1513.8	1486.7	1449.6	1426.3	1403.1	1382.2	1367.5	1363.6
17.5°	1590.7	1522.6	1469.5	1424.4	1380.1	1342.0	1320.6	1302.0	1284.9	1265.2	1262.5
20°	1520.8	1461.9	1403.9	1364.4	1318.8	1280.0	1253.7	1235.2	1220.4	1208.8	1198.8
22.5°	1454.5	1390.1	1337.0	1293.8	1248.8	1217.5	1196.8	1178.8	1166.6	1153.8	1144.3
25°	1348.2	1297.9	1239.8	1191.0	1153.9	1133.8	1116.7	1101.3	1093.6	1085.0	1074.2
27.5°	1255.2	1199.2	1144.9	1107.1	1074.5	1056.7	1044.6	1034.1	1026.8	1021.9	1015.7
30°	1189.5	1133.0	1090.5	1053.3	1026.2	1008.5	1000.7	994.5	985.9	982.9	979.8
32.5°	1126.3	1075.4	1039.1	1006.8	981.0	969.4	962.3	956.7	950.1	947.0	940.8
35°	1037.0	994.5	958.9	941.1	920.2	910.1	904.7	897.0	890.8	887.7	886.9
37.5°	953.0	916.0	892.6	869.7	860.9	854.7	847.3	842.0	840.2	839.7	838.9
40°	898.5	868.3	847.5	828.9	825.0	815.7	809.5	804.9	804.9	805.7	804.9
42.5°	849.0	821.9	803.4	787.4	782.8	777.3	771.1	770.8	772.0	774.7	772.0
45°	774.0	754.6	741.4	733.7	725.2	719.7	718.9	721.2	722.1	722.9	725.2
47.5°	704.9	692.1	680.1	671.6	667.9	666.9	666.0	670.0	673.8	675.2	678.7
50°	664.0	649.3	639.2	633.8	630.8	629.1	630.8	635.4	638.4	642.4	644.7
52.5°	618.2	607.8	600.9	596.7	595.4	596.4	596.7	602.0	606.9	608.3	609.4
55°	554.9	547.1	545.6	538.7	541.7	541.0	544.8	548.0	552.6	557.2	558.0
57.5°	491.7	485.5	481.4	482.0	482.9	486.4	489.6	495.0	500.0	504.9	505.3
60°	449.7	446.6	444.2	444.2	445.8	450.4	454.2	459.7	462.8	465.9	468.2
62.5°	411.2	408.2	405.9	407.1	411.1	413.8	418.4	421.3	424.4	427.5	428.6
65°	350.6	349.0	351.3	352.9	353.7	357.6	362.9	365.3	368.4	369.9	375.4
67.5°	294.7	295.0	294.7	296.9	301.3	302.3	307.4	312.9	313.5	316.4	319.9
70°	256.9	258.5	260.0	261.6	265.5	267.0	270.8	273.2	276.3	278.6	280.9
72.5°	222.3	222.6	224.1	223.8	227.0	230.5	233.7	236.0	239.1	242.1	244.4
75°	171.1	171.1	172.6	173.4	177.2	181.1	180.4	181.9	185.0	188.0	189.7
77.5°	124.9	123.2	124.9	125.7	126.9	130.2	130.8	133.0	136.5	135.4	137.1
80°	95.2	92.9	95.2	95.9	95.9	99.9	99.9	101.4	103.7	101.4	103.7
82.5°	68.0	66.9	68.6	68.8	70.0	70.1	71.4	71.7	74.0	72.9	74.0
85°	34.0	33.3	34.0	33.3	34.0	34.8	34.8	34.0	34.0	35.6	33.3
87.5°	12.3	12.3	12.5	13.2	13.4	13.5	12.9	12.8	12.7	11.4	11.4
90°	9.2	12.2	16.1	19.9	23.7	27.7	27.3	27.0	26.6	26.3	26.2
92.5°	20.2	21.4	22.3	23.2	24.2	25.1	25.1	25.2	25.3	25.3	25.4
95°	48.1	49.1	49.5	49.8	50.2	50.5	50.5	50.5	50.5	50.5	50.4
97.5°	81.2	82.3	82.9	83.6	84.2	84.9	84.9	84.9	84.9	84.9	84.9
100°	105.8	106.8	107.3	107.9	108.4	109.0	109.0	109.0	109.0	109.0	108.9
102.5°	131.3	132.2	132.8	133.5	134.1	134.8	134.9	135.1	135.2	135.4	135.3
105°	171.8	172.3	172.6	173.0	173.3	173.7	174.0	174.4	174.7	175.1	175.2
107.5°	216.0	216.4	216.4	216.4	216.4	216.4	216.6	216.7	216.8	217.0	216.7
110°	245.0	245.5	245.5	245.5	245.5	245.5	245.5	245.5	245.5	245.5	245.2



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	275.3	275.7	275.6	275.5	275.3	275.2	274.8	274.3	273.9	273.5	273.1
115°	319.9	320.3	319.9	319.6	319.2	318.9	318.7	318.5	318.4	318.2	317.8
117.5°	365.9	366.1	365.1	364.2	363.1	362.1	361.7	361.3	360.9	360.4	360.0
120°	395.6	395.6	394.2	392.7	391.3	389.9	389.9	389.9	389.9	389.9	389.7
122.5°	423.8	424.1	423.2	422.2	421.2	420.2	419.8	419.4	419.0	418.6	418.2
125°	465.7	466.3	465.7	465.1	464.6	464.1	463.6	463.1	462.5	462.0	461.7
127.5°	508.6	509.3	508.7	508.1	507.4	506.8	506.1	505.5	504.8	504.2	503.6
130°	535.6	536.5	536.2	535.8	535.5	535.2	534.8	534.5	534.1	533.8	533.2
132.5°	563.0	563.9	564.0	564.1	564.1	564.2	563.5	562.7	561.9	561.2	560.5
135°	602.1	603.2	603.6	603.9	604.3	604.6	604.5	604.3	604.1	603.9	603.6
137.5°	641.6	642.6	643.1	643.5	644.0	644.4	644.3	644.2	644.0	643.9	643.5
140°	666.2	667.4	668.3	669.2	670.0	671.0	671.0	671.0	671.0	671.0	670.6
142.5°	691.5	692.6	693.2	693.8	694.4	695.0	695.1	695.2	695.4	695.5	695.2
145°	726.4	727.5	728.6	729.6	730.6	731.7	732.0	732.1	732.3	732.5	732.2
147.5°	759.7	760.8	761.5	762.2	763.0	763.7	764.0	764.4	764.8	765.2	765.1
150°	780.1	781.0	781.7	782.4	783.2	783.9	784.4	784.9	785.4	786.0	786.0
152.5°	799.7	800.6	801.5	802.3	803.1	804.1	804.7	805.4	806.1	806.7	806.7
155°	827.0	827.5	828.0	828.6	829.1	829.6	830.5	831.3	832.2	833.1	833.3
157.5°	851.4	851.7	852.0	852.3	852.6	852.9	854.1	855.4	856.6	857.8	857.9
160°	866.6	866.8	867.0	867.2	867.4	867.5	868.6	869.6	870.7	871.7	871.9
162.5°	879.3	879.4	879.6	879.8	880.0	880.1	881.3	882.5	883.7	884.9	885.0
165°	896.8	896.7	896.7	896.7	896.7	896.7	898.0	899.2	900.4	901.6	901.8
167.5°	910.9	910.6	910.6	910.5	910.5	910.4	911.7	912.9	914.1	915.3	915.5
170°	919.1	918.7	918.6	918.4	918.2	918.0	919.3	920.5	921.7	922.9	923.0
172.5°	924.7	924.4	924.2	924.0	923.9	923.7	924.9	926.1	927.4	928.6	928.7
175°	931.7	931.3	930.9	930.6	930.2	929.9	931.1	932.3	933.5	934.7	934.8
177.5°	934.9	934.6	934.3	934.0	933.7	933.5	934.3	935.1	936.0	936.9	936.9
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1931.4	1930.2	1930.2	1924.6	1930.2	1930.2	1931.4	1937.5	1939.4	1940.7	1938.2
5°	1791.6	1789.3	1785.4	1789.3	1785.4	1789.3	1791.6	1802.4	1807.9	1813.3	1818.0
7.5°	1653.4	1644.1	1642.7	1633.6	1642.7	1644.1	1653.4	1658.5	1669.3	1681.5	1692.7
10°	1552.5	1546.3	1545.5	1530.8	1545.5	1546.3	1552.5	1565.6	1576.5	1591.1	1606.6
12.5°	1475.7	1460.9	1463.8	1455.2	1463.8	1460.9	1475.7	1475.8	1488.5	1497.6	1521.9
15°	1342.7	1342.7	1339.7	1326.5	1339.7	1342.7	1342.7	1363.6	1367.5	1382.2	1403.1
17.5°	1247.3	1245.7	1238.3	1241.9	1238.3	1245.7	1247.3	1262.5	1265.2	1284.9	1302.0
20°	1190.2	1185.7	1176.4	1176.4	1176.4	1185.7	1190.2	1198.8	1208.8	1220.4	1235.2
22.5°	1136.4	1136.1	1126.2	1129.3	1126.2	1136.1	1136.4	1144.3	1153.8	1166.6	1178.8
25°	1073.4	1067.2	1062.6	1064.9	1062.6	1067.2	1073.4	1074.2	1085.0	1093.6	1101.3
27.5°	1013.7	1010.3	1010.0	1003.6	1010.0	1010.3	1013.7	1015.7	1021.9	1026.8	1034.1
30°	979.0	971.3	972.8	969.0	972.8	971.3	979.0	979.8	982.9	985.9	994.5
32.5°	939.4	936.5	935.0	931.8	935.0	936.5	939.4	940.8	947.0	950.1	956.7
35°	885.3	886.2	882.2	883.8	882.2	886.2	885.3	886.9	887.7	890.8	897.0
37.5°	838.2	840.6	838.8	839.2	838.8	840.6	838.2	838.9	839.7	840.2	842.0
40°	807.2	807.2	807.2	809.5	807.2	807.2	807.2	804.9	805.7	804.9	804.9
42.5°	777.5	776.3	775.0	774.9	775.0	776.3	777.5	772.0	774.7	772.0	770.8
45°	726.7	729.0	729.8	725.9	729.8	729.0	726.7	725.2	722.9	722.1	721.2
47.5°	680.8	681.1	680.8	684.2	680.8	681.1	680.8	678.7	675.2	673.8	670.0
50°	648.5	647.0	648.5	647.0	648.5	647.0	648.5	644.7	642.4	638.4	635.4
52.5°	614.5	614.8	613.9	613.6	613.9	614.8	614.5	609.4	608.3	606.9	602.0
55°	561.1	562.6	561.9	561.9	561.9	562.6	561.1	558.0	557.2	552.6	548.0
57.5°	505.8	507.3	508.3	504.9	508.3	507.3	505.8	505.3	504.9	500.0	495.0
60°	467.5	471.3	470.5	469.0	470.5	471.3	467.5	468.2	465.9	462.8	459.7
62.5°	432.1	433.5	433.4	433.1	433.4	433.5	432.1	428.6	427.5	424.4	421.3
65°	377.7	379.2	376.9	379.2	376.9	379.2	377.7	375.4	369.9	368.4	365.3
67.5°	319.0	319.5	321.1	322.2	321.1	319.5	319.0	319.9	316.4	313.5	312.9
70°	282.5	281.8	284.1	286.4	284.1	281.8	282.5	280.9	278.6	276.3	273.2
72.5°	244.1	245.8	245.0	246.7	245.0	245.8	244.1	244.4	242.1	239.1	236.0
75°	188.0	190.4	189.7	192.0	189.7	190.4	188.0	189.7	188.0	185.0	181.9
77.5°	135.9	136.2	135.9	137.1	135.9	136.2	135.9	137.1	135.4	136.5	133.0
80°	103.7	102.2	100.6	103.7	100.6	102.2	103.7	103.7	101.4	103.7	101.4
82.5°	72.1	73.0	71.5	71.5	71.5	73.0	72.1	74.0	72.9	74.0	71.7
85°	33.3	32.5	31.0	31.0	31.0	32.5	33.3	33.3	35.6	34.0	34.0
87.5°	11.4	10.9	10.9	10.3	10.9	10.9	11.4	11.4	11.4	12.7	12.8
90°	26.4	26.5	26.7	26.9	26.7	26.5	26.4	26.2	26.3	26.6	27.0
92.5°	25.4	25.5	25.5	25.5	25.5	25.5	25.4	25.4	25.3	25.3	25.2
95°	50.0	49.7	49.3	49.0	49.3	49.7	50.0	50.4	50.5	50.5	50.5
97.5°	84.9	84.8	84.8	84.7	84.8	84.8	84.9	84.9	84.9	84.9	84.9
100°	108.7	108.5	108.4	108.2	108.4	108.5	108.7	108.9	109.0	109.0	109.0
102.5°	135.2	135.0	134.8	134.6	134.8	135.0	135.2	135.3	135.4	135.2	135.1
105°	175.2	175.2	175.2	175.2	175.2	175.2	175.2	175.2	175.1	174.7	174.4
107.5°	215.9	215.1	214.3	213.5	214.3	215.1	215.9	216.7	217.0	216.8	216.7
110°	244.7	244.2	243.7	243.1	243.7	244.2	244.7	245.2	245.5	245.5	245.5



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	272.7	272.3	272.0	271.6	272.0	272.3	272.7	273.1	273.5	273.9	274.3
115°	317.3	316.8	316.3	315.8	316.3	316.8	317.3	317.8	318.2	318.4	318.5
117.5°	359.5	358.9	358.4	357.9	358.4	358.9	359.5	360.0	360.4	360.9	361.3
120°	389.1	388.6	388.1	387.6	388.1	388.6	389.1	389.7	389.9	389.9	389.9
122.5°	417.8	417.4	417.0	416.7	417.0	417.4	417.8	418.2	418.6	419.0	419.4
125°	461.5	461.3	461.2	461.0	461.2	461.3	461.5	461.7	462.0	462.5	463.1
127.5°	503.1	502.5	502.0	501.4	502.0	502.5	503.1	503.6	504.2	504.8	505.5
130°	532.5	531.9	531.2	530.5	531.2	531.9	532.5	533.2	533.8	534.1	534.5
132.5°	559.9	559.4	558.8	558.3	558.8	559.4	559.9	560.5	561.2	561.9	562.7
135°	603.1	602.6	602.0	601.5	602.0	602.6	603.1	603.6	603.9	604.1	604.3
137.5°	642.8	642.1	641.4	640.7	641.4	642.1	642.8	643.5	643.9	644.0	644.2
140°	669.9	669.2	668.5	667.8	668.5	669.2	669.9	670.6	671.0	671.0	671.0
142.5°	694.5	693.8	693.2	692.5	693.2	693.8	694.5	695.2	695.5	695.4	695.2
145°	731.4	730.7	730.0	729.3	730.0	730.7	731.4	732.2	732.5	732.3	732.1
147.5°	764.4	763.7	763.1	762.3	763.1	763.7	764.4	765.1	765.2	764.8	764.4
150°	785.4	784.9	784.4	783.9	784.4	784.9	785.4	786.0	786.0	785.4	784.9
152.5°	806.1	805.4	804.7	804.1	804.7	805.4	806.1	806.7	806.7	806.1	805.4
155°	832.7	832.2	831.7	831.2	831.7	832.2	832.7	833.3	833.1	832.2	831.3
157.5°	857.1	856.3	855.4	854.5	855.4	856.3	857.1	857.9	857.8	856.6	855.4
160°	871.2	870.5	869.8	869.1	869.8	870.5	871.2	871.9	871.7	870.7	869.6
162.5°	884.2	883.4	882.5	881.7	882.5	883.4	884.2	885.0	884.9	883.7	882.5
165°	900.9	900.0	899.2	898.3	899.2	900.0	900.9	901.8	901.6	900.4	899.2
167.5°	914.6	913.7	912.8	911.9	912.8	913.7	914.6	915.5	915.3	914.1	912.9
170°	922.0	920.9	919.9	918.8	919.9	920.9	922.0	923.0	922.9	921.7	920.5
172.5°	927.7	926.6	925.5	924.5	925.5	926.6	927.7	928.7	928.6	927.4	926.1
175°	933.8	932.7	931.7	930.7	931.7	932.7	933.8	934.8	934.7	933.5	932.3
177.5°	936.0	935.1	934.3	933.5	934.3	935.1	936.0	936.9	936.9	936.0	935.1
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	1935.1	1941.9	1952.5	1963.6	1970.3	1983.4	1987.1	1993.3	1998.8	2011.9	2025.5
5°	1823.3	1834.2	1859.7	1873.6	1893.0	1915.4	1930.2	1945.6	1962.7	1992.1	2019.1
7.5°	1703.5	1721.6	1753.3	1779.4	1807.0	1839.2	1862.3	1893.0	1918.3	1959.8	1999.4
10°	1623.7	1649.2	1677.9	1708.8	1747.5	1781.5	1814.0	1852.7	1883.7	1933.2	1979.6
12.5°	1551.9	1555.7	1596.7	1630.8	1683.7	1725.9	1763.3	1813.1	1843.4	1902.3	1951.2
15°	1426.3	1449.6	1486.7	1513.8	1576.5	1629.8	1682.4	1734.3	1769.2	1841.9	1906.1
17.5°	1320.6	1342.0	1380.1	1424.4	1469.5	1522.6	1590.7	1645.4	1692.7	1775.8	1851.8
20°	1253.7	1280.0	1318.8	1364.4	1403.9	1461.9	1520.8	1583.5	1634.5	1728.2	1817.2
22.5°	1196.8	1217.5	1248.8	1293.8	1337.0	1390.1	1454.5	1522.8	1576.3	1677.4	1767.6
25°	1116.7	1133.8	1153.9	1191.0	1239.8	1297.9	1348.2	1423.2	1501.4	1595.8	1705.0
27.5°	1044.6	1056.7	1074.5	1107.1	1144.9	1199.2	1255.2	1326.4	1404.9	1507.4	1622.6
30°	1000.7	1008.5	1026.2	1053.3	1090.5	1133.0	1189.5	1257.6	1338.1	1441.8	1556.3
32.5°	962.3	969.4	981.0	1006.8	1039.1	1075.4	1126.3	1194.5	1271.2	1373.1	1500.0
35°	904.7	910.1	920.2	941.1	958.9	994.5	1037.0	1098.9	1170.9	1268.5	1400.0
37.5°	847.3	854.7	860.9	869.7	892.6	916.0	953.0	1005.3	1075.9	1174.4	1299.7
40°	809.5	815.7	825.0	828.9	847.5	868.3	898.5	946.4	1017.7	1107.4	1229.7
42.5°	771.1	777.3	782.8	787.4	803.4	821.9	849.0	890.2	953.3	1040.6	1161.6
45°	718.9	719.7	725.2	733.7	741.4	754.6	774.0	809.5	858.3	940.3	1050.2
47.5°	666.0	666.9	667.9	671.6	680.1	692.1	704.9	733.9	777.5	842.9	949.9
50°	630.8	629.1	630.8	633.8	639.2	649.3	664.0	684.9	720.5	781.6	879.9
52.5°	596.7	596.4	595.4	596.7	600.9	607.8	618.2	636.0	667.9	724.1	810.6
55°	544.8	541.0	541.7	538.7	545.6	547.1	554.9	569.6	597.4	636.1	717.4
57.5°	489.6	486.4	482.9	482.0	481.4	485.5	491.7	503.3	524.7	558.7	624.5
60°	454.2	450.4	445.8	444.2	444.2	446.6	449.7	458.2	478.3	508.5	562.6
62.5°	418.4	413.8	411.1	407.1	405.9	408.2	411.2	417.3	431.8	460.2	507.0
65°	362.9	357.6	353.7	352.9	351.3	349.0	350.6	356.8	368.4	390.8	428.0
67.5°	307.4	302.3	301.3	296.9	294.7	295.0	294.7	299.9	306.9	326.3	354.0
70°	270.8	267.0	265.5	261.6	260.0	258.5	256.9	261.6	268.5	284.8	308.8
72.5°	233.7	230.5	227.0	223.8	224.1	222.6	222.3	225.1	230.8	245.8	264.2
75°	180.4	181.1	177.2	173.4	172.6	171.1	171.1	173.4	175.7	187.3	202.0
77.5°	130.8	130.2	126.9	125.7	124.9	123.2	124.9	126.4	127.6	135.4	146.2
80°	99.9	99.9	95.9	95.9	95.2	92.9	95.2	93.6	96.7	104.5	112.2
82.5°	71.4	70.1	70.0	68.8	68.6	66.9	68.0	69.5	70.7	76.0	80.7
85°	34.8	34.8	34.0	33.3	34.0	33.3	34.0	34.8	35.6	38.0	41.8
87.5°	12.9	13.5	13.4	13.2	12.5	12.3	12.3	12.5	13.4	13.5	13.7
90°	27.3	27.7	23.7	19.9	16.1	12.2	9.2	7.1	5.0	2.9	0.8
92.5°	25.1	25.1	24.2	23.2	22.3	21.4	20.2	18.7	17.2	15.6	14.0
95°	50.5	50.5	50.2	49.8	49.5	49.1	48.1	46.4	44.5	42.8	41.0
97.5°	84.9	84.9	84.2	83.6	82.9	82.3	81.2	79.6	78.1	76.5	75.0
100°	109.0	109.0	108.4	107.9	107.3	106.8	105.8	104.4	103.0	101.7	100.3
102.5°	134.9	134.8	134.1	133.5	132.8	132.2	131.3	130.2	129.1	127.8	126.7
105°	174.0	173.7	173.3	173.0	172.6	172.3	171.8	171.3	170.8	170.3	169.8
107.5°	216.6	216.4	216.4	216.4	216.4	216.4	216.0	215.3	214.5	213.8	213.0
110°	245.5	245.5	245.5	245.5	245.5	245.5	245.0	243.9	242.9	241.8	240.8



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	274.8	275.2	275.3	275.5	275.6	275.7	275.3	274.2	273.2	272.2	271.0
115°	318.7	318.9	319.2	319.6	319.9	320.3	319.9	318.9	317.8	316.8	315.8
117.5°	361.7	362.1	363.1	364.2	365.1	366.1	365.9	364.5	363.0	361.6	360.2
120°	389.9	389.9	391.3	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9
122.5°	419.8	420.2	421.2	422.2	423.2	424.1	423.8	422.1	420.5	418.8	417.1
125°	463.6	464.1	464.6	465.1	465.7	466.3	465.7	464.1	462.5	461.0	459.4
127.5°	506.1	506.8	507.4	508.1	508.7	509.3	508.6	506.6	504.6	502.6	500.6
130°	534.8	535.2	535.5	535.8	536.2	536.5	535.6	533.3	531.1	528.8	526.5
132.5°	563.5	564.2	564.1	564.1	564.0	563.9	563.0	561.1	559.3	557.4	555.5
135°	604.5	604.6	604.3	603.9	603.6	603.2	602.1	600.2	598.2	596.3	594.4
137.5°	644.3	644.4	644.0	643.5	643.1	642.6	641.6	640.1	638.4	636.8	635.3
140°	671.0	671.0	670.0	669.2	668.3	667.4	666.2	664.6	663.1	661.5	659.9
142.5°	695.1	695.0	694.4	693.8	693.2	692.6	691.5	689.9	688.3	686.7	685.2
145°	732.0	731.7	730.6	729.6	728.6	727.5	726.4	725.2	724.0	722.7	721.4
147.5°	764.0	763.7	763.0	762.2	761.5	760.8	759.7	758.2	756.8	755.3	753.9
150°	784.4	783.9	783.2	782.4	781.7	781.0	780.1	779.1	778.0	777.0	776.0
152.5°	804.7	804.1	803.1	802.3	801.5	800.6	799.7	798.7	797.6	796.6	795.5
155°	830.5	829.6	829.1	828.6	828.0	827.5	827.0	826.5	826.0	825.4	824.9
157.5°	854.1	852.9	852.6	852.3	852.0	851.7	851.4	851.0	850.7	850.3	850.0
160°	868.6	867.5	867.4	867.2	867.0	866.8	866.6	866.2	865.9	865.5	865.2
162.5°	881.3	880.1	880.0	879.8	879.6	879.4	879.3	879.2	879.2	879.1	879.0
165°	898.0	896.7	896.7	896.7	896.7	896.7	896.8	897.0	897.2	897.4	897.5
167.5°	911.7	910.4	910.5	910.5	910.6	910.6	910.9	911.4	911.9	912.4	912.9
170°	919.3	918.0	918.2	918.4	918.6	918.7	919.1	919.6	920.1	920.7	921.2
172.5°	924.9	923.7	923.9	924.0	924.2	924.4	924.7	925.2	925.8	926.3	926.9
175°	931.1	929.9	930.2	930.6	930.9	931.3	931.7	932.2	932.7	933.3	933.8
177.5°	934.3	933.5	933.7	934.0	934.3	934.6	934.9	935.3	935.8	936.2	936.6
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2024.3	2027.3	2037.2	2047.2	2058.3	2061.4	2066.4	2062.0	2060.7	2072.5	2081.2
5°	2029.9	2043.9	2071.0	2095.8	2116.7	2131.3	2146.9	2153.0	2164.6	2180.9	2201.0
7.5°	2023.5	2050.5	2093.1	2129.2	2168.5	2196.9	2219.0	2237.9	2260.8	2291.6	2325.1
10°	2016.0	2052.4	2104.3	2148.4	2196.4	2232.7	2262.9	2292.3	2326.4	2368.9	2413.1
12.5°	2002.5	2045.6	2110.4	2162.6	2224.2	2260.0	2300.7	2364.2	2400.7	2459.9	2522.0
15°	1975.0	2023.0	2113.5	2177.8	2247.5	2315.5	2390.7	2450.9	2511.3	2546.2	2633.6
17.5°	1934.3	2004.8	2105.1	2180.0	2268.5	2375.7	2460.1	2528.5	2598.2	2654.6	2698.5
20°	1901.5	1978.1	2092.6	2182.4	2287.6	2403.0	2499.7	2569.4	2629.8	2677.0	2704.0
22.5°	1860.0	1956.4	2067.9	2173.1	2307.5	2421.6	2523.2	2578.1	2628.5	2651.6	2661.9
25°	1794.7	1910.8	2036.9	2165.5	2317.1	2437.8	2530.7	2563.9	2578.7	2556.3	2519.1
27.5°	1724.2	1853.7	2001.1	2150.8	2311.2	2427.3	2493.9	2488.6	2463.7	2391.1	2333.0
30°	1671.6	1814.0	1972.7	2136.0	2296.9	2409.9	2448.6	2409.9	2353.5	2272.2	2189.4
32.5°	1616.6	1763.9	1942.4	2115.0	2271.0	2370.4	2378.7	2312.2	2224.7	2132.3	2029.0
35°	1533.1	1692.5	1885.2	2067.9	2215.7	2278.4	2241.3	2123.6	2019.9	1893.8	1752.9
37.5°	1438.9	1614.9	1808.2	1999.0	2132.9	2149.3	2057.1	1933.2	1787.0	1638.7	1472.9
40°	1368.3	1554.8	1753.7	1946.4	2064.8	2047.8	1930.2	1793.9	1619.8	1438.7	1284.6
42.5°	1305.1	1491.7	1694.3	1883.2	1978.1	1931.4	1793.9	1626.8	1439.7	1269.1	1128.0
45°	1195.7	1387.7	1595.1	1777.7	1831.9	1747.5	1565.6	1379.9	1195.7	1053.3	941.9
47.5°	1089.5	1279.3	1484.7	1645.2	1664.4	1551.0	1352.2	1161.0	1002.7	886.8	808.1
50°	1011.5	1201.8	1405.4	1548.6	1542.4	1405.4	1201.1	1019.3	886.9	793.2	740.6
52.5°	941.5	1121.4	1316.9	1447.0	1414.2	1264.9	1069.9	908.4	799.6	726.4	678.7
55°	832.7	999.2	1184.9	1289.3	1229.0	1063.4	898.5	768.5	688.0	633.1	595.9
57.5°	724.7	880.7	1039.7	1104.1	1037.3	884.4	747.0	652.7	592.2	551.5	527.4
60°	657.8	794.1	935.6	991.4	911.7	775.5	667.1	582.8	534.0	500.7	479.1
62.5°	591.0	713.0	846.5	876.9	804.0	688.8	592.8	522.7	482.6	453.0	432.6
65°	500.0	599.8	701.1	721.2	654.0	564.9	489.1	443.4	407.9	386.2	369.9
67.5°	410.0	490.2	562.0	578.2	519.3	457.6	402.7	362.9	338.8	320.8	307.1
70°	356.8	420.2	479.1	492.2	445.0	390.0	348.3	316.5	294.9	279.4	266.2
72.5°	300.4	353.4	402.2	411.1	372.5	330.6	296.3	271.4	252.2	242.3	229.7
75°	229.8	260.8	298.7	301.0	275.5	249.9	223.7	207.4	197.3	185.0	178.7
77.5°	162.2	186.5	208.1	212.4	197.2	179.9	165.1	152.3	143.8	138.0	132.3
80°	123.8	143.2	152.5	157.8	147.0	134.6	126.1	117.6	112.2	108.4	104.5
82.5°	88.6	100.5	109.2	113.3	107.4	100.0	91.5	86.6	82.5	79.3	77.9
85°	44.8	50.3	55.7	57.3	55.7	52.6	48.0	48.0	45.6	44.8	44.8
87.5°	16.1	19.0	19.4	21.6	21.0	21.8	22.5	22.7	22.8	22.2	21.5
90°	2.9	5.0	7.1	9.2	12.2	16.1	19.9	23.7	27.7	27.3	27.0
92.5°	15.6	17.2	18.7	20.2	21.4	22.3	23.2	24.2	25.1	25.1	25.2
95°	42.8	44.5	46.4	48.1	49.1	49.5	49.8	50.2	50.5	50.5	50.5
97.5°	76.5	78.1	79.6	81.2	82.3	82.9	83.6	84.2	84.9	84.9	84.9
100°	101.7	103.0	104.4	105.8	106.8	107.3	107.9	108.4	109.0	109.0	109.0
102.5°	127.8	129.1	130.2	131.3	132.2	132.8	133.5	134.1	134.8	134.9	135.1
105°	170.3	170.8	171.3	171.8	172.3	172.6	173.0	173.3	173.7	174.0	174.4
107.5°	213.8	214.5	215.3	216.0	216.4	216.4	216.4	216.4	216.4	216.6	216.7
110°	241.8	242.9	243.9	245.0	245.5	245.5	245.5	245.5	245.5	245.5	245.5



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.2	273.2	274.2	275.3	275.7	275.6	275.5	275.3	275.2	274.8	274.3
115°	316.8	317.8	318.9	319.9	320.3	319.9	319.6	319.2	318.9	318.7	318.5
117.5°	361.6	363.0	364.5	365.9	366.1	365.1	364.2	363.1	362.1	361.7	361.3
120°	391.3	392.7	394.2	395.6	395.6	394.2	392.7	391.3	389.9	389.9	389.9
122.5°	418.8	420.5	422.1	423.8	424.1	423.2	422.2	421.2	420.2	419.8	419.4
125°	461.0	462.5	464.1	465.7	466.3	465.7	465.1	464.6	464.1	463.6	463.1
127.5°	502.6	504.6	506.6	508.6	509.3	508.7	508.1	507.4	506.8	506.1	505.5
130°	528.8	531.1	533.3	535.6	536.5	536.2	535.8	535.5	535.2	534.8	534.5
132.5°	557.4	559.3	561.1	563.0	563.9	564.0	564.1	564.1	564.2	563.5	562.7
135°	596.3	598.2	600.2	602.1	603.2	603.6	603.9	604.3	604.6	604.5	604.3
137.5°	636.8	638.4	640.1	641.6	642.6	643.1	643.5	644.0	644.4	644.3	644.2
140°	661.5	663.1	664.6	666.2	667.4	668.3	669.2	670.0	671.0	671.0	671.0
142.5°	686.7	688.3	689.9	691.5	692.6	693.2	693.8	694.4	695.0	695.1	695.2
145°	722.7	724.0	725.2	726.4	727.5	728.6	729.6	730.6	731.7	732.0	732.1
147.5°	755.3	756.8	758.2	759.7	760.8	761.5	762.2	763.0	763.7	764.0	764.4
150°	777.0	778.0	779.1	780.1	781.0	781.7	782.4	783.2	783.9	784.4	784.9
152.5°	796.6	797.6	798.7	799.7	800.6	801.5	802.3	803.1	804.1	804.7	805.4
155°	825.4	826.0	826.5	827.0	827.5	828.0	828.6	829.1	829.6	830.5	831.3
157.5°	850.3	850.7	851.0	851.4	851.7	852.0	852.3	852.6	852.9	854.1	855.4
160°	865.5	865.9	866.2	866.6	866.8	867.0	867.2	867.4	867.5	868.6	869.6
162.5°	879.1	879.2	879.2	879.3	879.4	879.6	879.8	880.0	880.1	881.3	882.5
165°	897.4	897.2	897.0	896.8	896.7	896.7	896.7	896.7	896.7	898.0	899.2
167.5°	912.4	911.9	911.4	910.9	910.6	910.6	910.5	910.5	910.4	911.7	912.9
170°	920.7	920.1	919.6	919.1	918.7	918.6	918.4	918.2	918.0	919.3	920.5
172.5°	926.3	925.8	925.2	924.7	924.4	924.2	924.0	923.9	923.7	924.9	926.1
175°	933.3	932.7	932.2	931.7	931.3	930.9	930.6	930.2	929.9	931.1	932.3
177.5°	936.2	935.8	935.3	934.9	934.6	934.3	934.0	933.7	933.5	934.3	935.1
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7	2013.7
2.5°	2088.6	2097.3	2097.3	2098.5	2108.4	2107.2	2106.6
5°	2222.7	2235.8	2237.4	2251.3	2260.6	2257.5	2249.0
7.5°	2349.1	2373.6	2392.2	2402.6	2414.8	2422.4	2418.9
10°	2449.4	2485.1	2506.7	2521.4	2539.2	2552.3	2547.7
12.5°	2540.4	2582.8	2612.6	2637.8	2640.1	2657.0	2645.5
15°	2682.4	2727.2	2731.9	2750.5	2765.2	2763.6	2764.4
17.5°	2729.3	2743.7	2746.6	2747.0	2747.2	2741.8	2730.1
20°	2712.6	2707.1	2694.0	2683.9	2666.1	2663.8	2648.4
22.5°	2633.3	2616.2	2583.1	2561.3	2533.7	2526.4	2522.0
25°	2477.3	2439.3	2386.7	2336.4	2322.5	2295.4	2303.2
27.5°	2263.2	2204.1	2147.2	2106.3	2069.3	2028.7	2040.3
30°	2112.7	2046.2	1965.7	1903.8	1864.3	1825.6	1818.7
32.5°	1933.2	1835.7	1746.0	1691.4	1630.9	1606.5	1579.7
35°	1623.7	1528.4	1439.5	1362.8	1318.8	1284.6	1253.7
37.5°	1345.2	1235.7	1163.8	1101.8	1069.9	1050.4	1055.3
40°	1172.5	1076.5	1023.9	976.6	947.3	933.3	936.4
42.5°	1032.6	960.7	917.4	885.0	864.3	856.6	854.7
45°	873.7	833.5	797.9	779.3	769.3	760.7	755.4
47.5°	765.4	732.6	712.5	701.5	692.7	684.0	683.8
50°	700.3	678.7	664.8	653.2	646.2	640.1	645.4
52.5°	650.9	631.1	617.1	606.7	604.1	598.5	598.3
55°	577.3	561.9	551.8	542.5	537.9	534.7	530.9
57.5°	510.5	495.7	486.5	480.6	471.8	468.7	467.5
60°	462.8	451.2	441.9	434.1	430.3	424.1	424.1
62.5°	418.8	407.3	398.6	392.6	386.4	383.8	384.5
65°	355.3	346.0	337.4	331.2	329.7	325.1	326.6
67.5°	296.7	290.5	281.6	278.1	275.2	272.8	270.8
70°	257.7	251.6	246.9	242.3	239.9	239.9	239.9
72.5°	224.9	217.4	214.7	208.8	210.2	207.7	205.2
75°	174.1	169.5	167.1	164.8	161.0	161.0	161.0
77.5°	128.2	126.7	124.0	121.5	120.6	119.8	120.1
80°	99.1	98.3	96.7	96.7	95.2	94.4	92.9
82.5°	76.1	74.1	73.2	72.6	72.3	72.1	71.8
85°	43.3	41.8	41.8	42.5	41.0	41.0	41.8
87.5°	22.0	21.9	21.3	21.4	22.0	21.4	21.5
90°	26.6	26.3	26.2	26.4	26.5	26.7	26.9
92.5°	25.3	25.3	25.4	25.4	25.5	25.5	25.5
95°	50.5	50.5	50.4	50.0	49.7	49.3	49.0
97.5°	84.9	84.9	84.9	84.9	84.8	84.8	84.7
100°	109.0	109.0	108.9	108.7	108.5	108.4	108.2
102.5°	135.2	135.4	135.3	135.2	135.0	134.8	134.6
105°	174.7	175.1	175.2	175.2	175.2	175.2	175.2
107.5°	216.8	217.0	216.7	215.9	215.1	214.3	213.5
110°	245.5	245.5	245.2	244.7	244.2	243.7	243.1



TEST NUMBER: P331439-840

CATALOG NUMBER: S122DIP-S1005D725U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	273.9	273.5	273.1	272.7	272.3	272.0	271.6
115°	318.4	318.2	317.8	317.3	316.8	316.3	315.8
117.5°	360.9	360.4	360.0	359.5	358.9	358.4	357.9
120°	389.9	389.9	389.7	389.1	388.6	388.1	387.6
122.5°	419.0	418.6	418.2	417.8	417.4	417.0	416.7
125°	462.5	462.0	461.7	461.5	461.3	461.2	461.0
127.5°	504.8	504.2	503.6	503.1	502.5	502.0	501.4
130°	534.1	533.8	533.2	532.5	531.9	531.2	530.5
132.5°	561.9	561.2	560.5	559.9	559.4	558.8	558.3
135°	604.1	603.9	603.6	603.1	602.6	602.0	601.5
137.5°	644.0	643.9	643.5	642.8	642.1	641.4	640.7
140°	671.0	671.0	670.6	669.9	669.2	668.5	667.8
142.5°	695.4	695.5	695.2	694.5	693.8	693.2	692.5
145°	732.3	732.5	732.2	731.4	730.7	730.0	729.3
147.5°	764.8	765.2	765.1	764.4	763.7	763.1	762.3
150°	785.4	786.0	786.0	785.4	784.9	784.4	783.9
152.5°	806.1	806.7	806.7	806.1	805.4	804.7	804.1
155°	832.2	833.1	833.3	832.7	832.2	831.7	831.2
157.5°	856.6	857.8	857.9	857.1	856.3	855.4	854.5
160°	870.7	871.7	871.9	871.2	870.5	869.8	869.1
162.5°	883.7	884.9	885.0	884.2	883.4	882.5	881.7
165°	900.4	901.6	901.8	900.9	900.0	899.2	898.3
167.5°	914.1	915.3	915.5	914.6	913.7	912.8	911.9
170°	921.7	922.9	923.0	922.0	920.9	919.9	918.8
172.5°	927.4	928.6	928.7	927.7	926.6	925.5	924.5
175°	933.5	934.7	934.8	933.8	932.7	931.7	930.7
177.5°	936.0	936.9	936.9	936.0	935.1	934.3	933.5
180°	935.3	935.3	935.3	935.3	935.3	935.3	935.3

(END OF REPORT)