

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331442-927

Luminaire Tested: **S122DIP-S1005D725U927-4F0-1E-UDD-D1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331442-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S1005D725U927-4F0-1E-UDD-D1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5250.5 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331442-927

CATALOG NUMBER: S122DIP-S1005D725U927-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P331442-927

CATALOG NUMBER: S122DIP-S1005D725U927-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	97	92	87	83	90	85	81	78	73	70	67	61	59	57	50	49	47
2	88	79	73	67	81	74	68	62	63	58	54	53	49	46	43	41	39
3	80	69	61	55	73	64	57	51	55	49	45	46	42	38	38	35	32
4	73	61	52	46	67	57	49	43	48	42	38	41	36	32	34	30	27
5	67	54	45	39	61	50	43	37	43	37	32	36	32	28	30	26	23
6	61	48	40	34	56	45	37	32	39	33	28	33	28	24	27	23	20
7	57	44	35	29	52	41	33	28	35	29	24	30	25	21	25	21	18
8	52	40	31	26	48	37	30	24	32	26	22	27	22	19	23	19	16
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	14
10	46	33	26	21	42	31	24	19	27	21	17	23	18	15	19	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13525	13525	13525
5°	13591	13020	12971
10°	13506	12635	12493
15°	13320	12228	11990
20°	13085	11791	11506
25°	12852	11370	11066
30°	12525	10939	10626
35°	12192	10521	10314
40°	11845	10165	10004
45°	11515	9846	9739
50°	11159	9559	9477
55°	10787	9249	9211
60°	10329	8927	8928
65°	9856	8551	8595
70°	9323	8147	8233
75°	8642	7750	7901
80°	7567	7345	7563
85°	6539	6995	7303



TEST NUMBER: P331442-927

CATALOG NUMBER: S122DIP-S1005D725U927-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.4	1.5
10°-20°	227.6	4.3
20°-30°	344.9	6.6
30°-40°	420.1	8.0
40°-50°	452.0	8.6
50°-60°	438.9	8.4
60°-70°	383.2	7.3
70°-80°	295.0	5.6
80°-90°	200.9	3.8
90°-100°	182.9	3.5
100°-110°	244.0	4.6
110°-120°	312.6	6.0
120°-130°	361.3	6.9
130°-140°	379.7	7.2
140°-150°	359.9	6.9
150°-160°	299.6	5.7
160°-170°	198.7	3.8
170°-180°	69.5	1.3
0°-30°	651.9	12.4
0°-40°	1072.0	20.4
0°-60°	1962.9	37.4
0°-90°	2842.1	54.1
90°-120°	739.6	14.1
90°-150°	1840.5	35.1
90°-180°	2408.0	45.9
0°-180°	5250.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	838	838	838	838	838	
5°	840	836	829	836	835	80
15°	801	804	804	814	813	226
25°	728	737	748	762	766	335
35°	628	648	671	697	706	392
45°	515	548	590	626	640	397
55°	395	439	501	544	561	353
65°	270	330	401	449	466	268
75°	149	218	295	345	363	158
85°	44	119	197	246	265	47
90°	13	91	182	227	244	10
95°	42	106	179	224	239	45
105°	139	178	241	283	298	147
115°	252	272	323	357	370	249
125°	363	370	405	435	447	324
135°	468	475	488	512	520	361
145°	566	570	574	582	586	354
155°	647	649	651	654	652	298
165°	704	703	703	707	705	198
175°	732	731	729	733	730	70
180°	734	734	734	734	734	



TEST NUMBER: P331442-927

CATALOG NUMBER: S122DIP-S1005D725U927-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	837.7	837.7	837.7	837.7	837.7	837.7	837.7	837.7	837.7	837.7	837.7
2.5°	842.6	841.9	841.2	840.6	840.0	838.8	837.3	835.8	834.3	832.8	833.9
5°	840.1	839.3	838.5	837.7	836.9	835.7	834.1	832.4	830.8	829.2	830.8
7.5°	832.6	832.0	831.5	831.0	830.4	829.6	828.3	827.0	825.9	824.6	826.5
10°	826.8	826.2	825.7	825.1	824.6	823.9	823.2	822.3	821.5	820.7	822.8
12.5°	817.1	817.1	817.3	817.4	817.5	817.2	816.7	816.0	815.5	814.8	817.1
15°	801.3	801.8	802.3	802.9	803.4	803.7	803.7	803.7	803.7	803.7	806.1
17.5°	780.9	782.0	783.2	784.3	785.4	786.4	787.3	788.1	789.0	789.9	792.4
20°	767.3	768.7	770.0	771.3	772.7	773.9	775.0	776.0	777.1	778.2	781.2
22.5°	752.7	754.2	755.8	757.4	759.0	760.5	762.0	763.5	765.0	766.5	769.5
25°	728.4	730.3	732.2	734.1	736.0	738.2	740.5	743.0	745.4	747.8	751.1
27.5°	699.3	702.3	705.4	708.5	711.6	714.5	717.4	720.3	723.1	726.0	730.1
30°	679.9	683.3	686.9	690.4	693.9	697.4	700.9	704.4	707.9	711.5	715.7
32.5°	658.5	662.4	666.4	670.3	674.2	678.3	682.5	686.6	690.8	694.9	699.9
35°	627.6	632.2	636.8	641.4	646.0	650.9	656.0	661.1	666.2	671.4	677.3
37.5°	594.1	599.4	604.8	610.0	615.3	621.2	627.9	634.5	641.2	647.8	654.4
40°	571.8	577.7	583.7	589.6	595.6	602.1	609.4	616.7	624.0	631.3	638.3
42.5°	550.5	556.3	562.3	568.2	574.2	581.3	589.7	598.1	606.4	614.8	622.4
45°	514.8	522.0	529.3	536.6	543.9	552.2	561.7	571.2	580.6	590.0	598.4
47.5°	479.6	487.5	495.4	503.4	511.3	520.8	531.9	542.9	554.0	565.0	573.8
50°	455.3	463.7	472.0	480.4	488.7	499.0	511.1	523.2	535.4	547.6	556.7
52.5°	432.0	440.8	449.6	458.4	467.1	477.9	490.7	503.5	516.3	529.1	538.4
55°	394.6	404.3	414.0	423.7	433.4	445.3	459.3	473.3	487.4	501.4	511.1
57.5°	357.7	368.6	379.5	390.5	401.5	414.1	428.4	442.7	457.0	471.3	481.7
60°	331.4	343.0	354.7	366.2	377.9	391.3	406.7	422.1	437.4	452.8	463.1
62.5°	308.2	320.1	332.2	344.2	356.2	369.9	385.3	400.7	416.1	431.5	442.4
65°	269.5	282.7	296.0	309.2	322.4	337.0	352.9	368.8	384.7	400.6	411.7
67.5°	234.1	247.9	261.7	275.5	289.3	304.4	320.7	337.0	353.2	369.6	380.7
70°	208.8	222.8	236.9	250.9	264.9	280.3	297.1	313.8	330.5	347.2	358.8
72.5°	185.5	199.9	214.4	228.9	243.4	259.0	276.0	292.9	309.9	326.9	338.2
75°	149.3	164.5	179.5	194.6	209.8	225.9	243.2	260.5	277.7	295.0	306.6
77.5°	114.4	130.2	146.0	161.8	177.6	194.2	211.8	229.3	246.8	264.4	276.0
80°	91.0	107.5	124.0	140.5	156.9	173.9	191.4	209.0	226.5	244.0	255.3
82.5°	71.6	87.9	104.1	120.3	136.6	153.6	171.3	189.1	206.8	224.6	235.9
85°	43.7	60.4	77.2	93.9	110.6	127.6	144.9	162.2	179.4	196.7	208.0
87.5°	23.9	40.3	56.7	73.1	89.6	106.7	124.5	142.4	160.3	178.2	189.2
90°	12.8	30.0	47.4	64.6	82.0	100.8	121.0	141.3	161.6	182.0	192.4
92.5°	22.2	37.9	53.8	69.6	85.3	101.9	119.2	136.6	153.8	171.2	181.8
95°	41.9	55.9	70.0	84.1	98.2	113.4	129.8	146.3	162.8	179.3	189.5
97.5°	67.3	79.8	92.3	104.8	117.2	131.6	147.6	163.7	179.7	195.8	205.8
100°	87.1	98.2	109.3	120.4	131.5	144.7	160.3	175.8	191.3	206.8	216.8
102.5°	106.9	117.0	127.0	137.0	146.9	159.5	174.8	190.0	205.2	220.4	230.2
105°	139.2	147.4	155.7	163.9	172.1	183.4	197.7	212.0	226.3	240.7	250.3
107.5°	172.9	179.7	186.6	193.5	200.3	210.5	223.9	237.3	250.8	264.3	273.4
110°	193.7	199.9	206.1	212.4	218.6	228.3	241.5	254.8	268.0	281.2	289.9



TEST NUMBER: P331442-927

CATALOG NUMBER: S122DIP-S1005D725U927-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.5	222.8	228.2	233.5	238.9	247.8	260.3	272.7	285.2	297.7	306.0
115°	252.5	256.4	260.2	264.0	267.7	275.5	287.4	299.3	311.2	323.0	331.0
117.5°	286.2	289.3	292.3	295.4	298.4	305.1	315.6	326.1	336.5	347.0	354.7
120°	309.5	311.7	313.9	316.1	318.2	324.2	333.9	343.6	353.2	363.0	370.5
122.5°	330.8	332.6	334.3	336.1	337.9	343.4	352.8	362.2	371.5	380.9	387.9
125°	362.8	364.0	365.3	366.5	367.7	372.5	380.7	389.0	397.1	405.4	412.3
127.5°	395.1	396.4	397.8	399.0	400.3	404.2	410.7	417.2	423.6	430.1	436.3
130°	415.4	416.9	418.5	420.0	421.5	425.0	430.4	435.8	441.2	446.6	452.7
132.5°	438.2	439.4	440.6	441.8	443.0	445.8	450.2	454.6	459.1	463.5	469.1
135°	467.5	469.0	470.5	472.0	473.6	475.8	478.7	481.7	484.7	487.7	493.2
137.5°	499.6	500.7	501.9	503.1	504.3	505.6	507.2	508.7	510.3	511.8	516.7
140°	518.9	519.8	520.8	521.8	522.8	523.9	525.1	526.3	527.5	528.8	533.1
142.5°	538.7	539.6	540.6	541.6	542.6	543.4	543.9	544.5	545.0	545.7	549.2
145°	565.9	566.9	567.9	568.9	569.8	570.7	571.6	572.4	573.1	574.0	575.8
147.5°	591.4	592.5	593.7	594.8	596.0	596.8	597.4	597.9	598.5	599.0	599.5
150°	608.7	609.5	610.3	611.2	612.0	612.7	613.2	613.8	614.3	614.9	615.3
152.5°	624.0	624.9	625.7	626.5	627.3	628.0	628.8	629.4	630.0	630.7	631.2
155°	647.1	647.5	647.9	648.3	648.7	649.1	649.5	650.0	650.4	650.8	651.5
157.5°	666.8	667.0	667.3	667.6	667.9	668.1	668.4	668.6	668.8	669.1	670.0
160°	678.7	678.9	679.2	679.5	679.8	679.9	680.1	680.2	680.4	680.5	681.4
162.5°	689.5	689.6	689.7	689.7	689.8	689.8	690.0	690.1	690.3	690.4	691.3
165°	704.0	703.9	703.8	703.6	703.5	703.4	703.4	703.4	703.4	703.4	704.4
167.5°	716.1	715.7	715.3	714.9	714.5	714.3	714.3	714.2	714.2	714.2	715.2
170°	722.6	722.2	721.8	721.4	721.0	720.6	720.6	720.4	720.3	720.1	721.1
172.5°	727.1	726.7	726.3	725.8	725.4	725.2	725.0	724.8	724.8	724.6	725.6
175°	732.5	732.1	731.7	731.3	730.9	730.6	730.2	730.0	729.7	729.4	730.4
177.5°	734.7	734.4	734.1	733.7	733.4	733.2	732.9	732.7	732.5	732.3	732.9
180°	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7



TEST NUMBER: P331442-927

CATALOG NUMBER: S122DIP-S1005D725U927-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	837.7	837.7	837.7	837.7	837.7	837.7	837.7	837.7
2.5°	835.0	836.1	837.2	837.5	837.0	836.6	836.1	835.8
5°	832.4	834.1	835.7	836.3	836.1	835.8	835.5	835.3
7.5°	828.5	830.4	832.3	833.2	832.9	832.7	832.3	832.1
10°	825.0	827.2	829.3	830.3	830.0	829.7	829.5	829.2
12.5°	819.2	821.3	823.5	824.4	824.2	823.9	823.6	823.4
15°	808.6	811.0	813.4	814.5	814.2	814.0	813.7	813.4
17.5°	795.0	797.5	800.0	801.3	801.3	801.3	801.3	801.3
20°	784.1	787.1	790.0	791.5	791.5	791.5	791.5	791.5
22.5°	772.5	775.5	778.4	780.1	780.5	781.0	781.4	781.9
25°	754.3	757.6	760.8	762.8	763.7	764.5	765.2	766.0
27.5°	734.2	738.3	742.4	744.7	745.4	745.9	746.6	747.1
30°	720.1	724.4	728.7	731.3	732.1	732.8	733.7	734.5
32.5°	704.9	709.8	714.8	718.0	719.5	720.9	722.4	723.8
35°	683.3	689.2	695.1	699.0	700.9	702.8	704.7	706.5
37.5°	661.0	667.6	674.1	678.4	680.4	682.5	684.4	686.4
40°	645.3	652.4	659.3	664.1	666.5	668.9	671.4	673.8
42.5°	630.1	637.8	645.5	650.5	652.9	655.4	657.7	660.2
45°	606.7	615.1	623.4	629.0	631.7	634.4	637.1	639.8
47.5°	582.5	591.2	600.0	605.9	608.8	611.8	614.7	617.7
50°	565.9	575.0	584.2	590.3	593.3	596.2	599.2	602.1
52.5°	547.9	557.2	566.6	572.9	576.1	579.3	582.5	585.7
55°	520.9	530.5	540.3	546.8	550.3	553.9	557.4	560.9
57.5°	492.3	502.7	513.2	520.1	523.7	527.3	530.8	534.4
60°	473.3	483.6	493.8	500.9	504.6	508.4	512.2	515.9
62.5°	453.3	464.1	475.1	482.3	485.8	489.4	493.0	496.5
65°	422.8	433.8	444.9	452.2	455.7	459.1	462.7	466.2
67.5°	391.9	403.1	414.2	421.7	425.3	429.0	432.7	436.3
70°	370.4	382.0	393.6	401.0	404.3	407.5	410.7	414.0
72.5°	349.6	361.0	372.3	380.0	383.9	387.8	391.7	395.5
75°	318.2	329.8	341.4	349.0	352.4	356.0	359.5	363.0
77.5°	287.5	299.0	310.6	318.3	322.0	325.8	329.6	333.4
80°	266.6	278.1	289.4	296.9	300.7	304.4	308.2	312.0
82.5°	247.2	258.6	269.9	277.3	280.9	284.5	288.0	291.6
85°	219.4	230.7	242.0	249.5	253.3	257.1	260.9	264.7
87.5°	200.1	211.0	222.0	229.2	232.7	236.1	239.6	243.1
90°	203.0	213.5	224.0	230.9	234.3	237.7	241.1	244.5
92.5°	192.5	203.1	213.7	220.7	223.9	227.2	230.4	233.8
95°	199.7	210.0	220.2	226.9	229.8	232.8	235.8	238.7
97.5°	215.8	225.8	235.8	242.3	245.4	248.6	251.8	254.9
100°	226.8	236.8	246.8	253.2	256.0	258.9	261.7	264.5
102.5°	240.1	250.0	259.8	266.3	269.0	271.9	274.7	277.6
105°	260.1	269.8	279.5	285.8	288.8	291.8	294.8	297.7
107.5°	282.6	291.8	301.0	306.7	309.0	311.3	313.7	316.0
110°	298.5	307.1	315.8	321.3	323.8	326.5	329.0	331.5



TEST NUMBER: P331442-927

CATALOG NUMBER: S122DIP-S1005D725U927-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	314.3	322.6	330.9	336.4	339.1	341.7	344.4	347.1
115°	338.9	346.9	354.8	360.0	362.7	365.2	367.7	370.3
117.5°	362.3	369.9	377.6	382.6	384.9	387.3	389.6	392.0
120°	378.0	385.6	393.2	398.2	400.8	403.3	405.9	408.4
122.5°	394.9	402.0	408.9	413.5	415.8	418.0	420.3	422.5
125°	419.1	426.0	432.8	437.4	439.7	442.0	444.3	446.6
127.5°	442.4	448.6	454.9	458.9	460.8	462.8	464.7	466.7
130°	458.9	465.1	471.3	475.2	476.8	478.5	480.1	481.6
132.5°	474.8	480.5	486.1	489.8	491.5	493.2	495.0	496.7
135°	498.8	504.2	509.8	513.4	515.2	516.9	518.6	520.4
137.5°	521.6	526.4	531.2	534.3	535.6	536.9	538.1	539.5
140°	537.4	541.7	546.1	548.7	549.8	550.9	551.9	553.0
142.5°	552.8	556.3	559.9	562.1	562.9	563.8	564.7	565.5
145°	577.5	579.2	581.1	582.3	583.1	583.9	584.7	585.5
147.5°	600.1	600.6	601.1	601.4	601.5	601.7	601.8	601.9
150°	615.7	616.1	616.6	616.6	616.1	615.7	615.3	614.9
152.5°	631.8	632.3	632.8	632.8	632.3	631.8	631.2	630.7
155°	652.1	652.8	653.6	653.7	653.2	652.8	652.4	652.0
157.5°	671.0	671.9	672.9	673.0	672.3	671.7	671.0	670.3
160°	682.1	683.0	683.8	684.0	683.4	682.9	682.3	681.8
162.5°	692.3	693.2	694.2	694.3	693.6	693.0	692.3	691.7
165°	705.4	706.3	707.3	707.4	706.7	706.0	705.4	704.6
167.5°	716.1	717.1	718.0	718.2	717.5	716.8	716.1	715.3
170°	722.1	723.0	724.0	724.1	723.3	722.4	721.6	720.7
172.5°	726.5	727.5	728.4	728.5	727.7	726.8	726.0	725.2
175°	731.3	732.3	733.2	733.3	732.5	731.7	730.9	730.1
177.5°	733.6	734.3	734.9	734.9	734.3	733.6	732.9	732.3
180°	733.7	733.7	733.7	733.7	733.7	733.7	733.7	733.7

(END OF REPORT)