

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331309-840

Luminaire Tested: **S122DIP-S485D725U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331309-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D725U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4923.7 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331309-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331309-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	96	91	88	84	87	83	80	77	68	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	29
3	79	70	63	57	72	64	58	53	53	48	45	42	39	36	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	45	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	25	21	19	20	17	15	13
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12665	12665	12665
5°	12713	12530	12603
10°	12637	12403	12463
15°	12481	12242	12227
20°	12259	12000	11986
25°	12039	11703	11703
30°	11757	11432	11332
35°	11491	11105	10941
40°	11160	10779	10570
45°	10832	10453	10195
50°	10477	10115	9756
55°	10106	9723	9362
60°	9691	9255	8913
65°	9249	8787	8382
70°	8686	8224	7832
75°	7904	7573	7392
80°	7011	6797	6453
85°	5724	5446	4891



TEST NUMBER: P331309-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	1.5
10°-20°	207.5	4.2
20°-30°	305.0	6.2
30°-40°	354.3	7.2
40°-50°	354.0	7.2
50°-60°	308.7	6.3
60°-70°	228.2	4.6
70°-80°	129.3	2.6
80°-90°	37.2	0.8
90°-100°	33.3	0.7
100°-110°	122.1	2.5
110°-120°	326.4	6.6
120°-130°	538.9	10.9
130°-140°	573.1	11.6
140°-150°	532.7	10.8
150°-160°	428.3	8.7
160°-170°	276.0	5.6
170°-180°	95.0	1.9
0°-30°	586.3	11.9
0°-40°	940.7	19.1
0°-60°	1603.3	32.6
0°-90°	1998.0	40.6
90°-120°	481.9	9.8
90°-150°	2126.5	43.2
90°-180°	2926.0	59.4
0°-180°	4923.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	784	784	784	784	784	
5°	784	781	773	779	778	74
15°	747	742	732	735	732	210
25°	676	669	657	658	657	311
35°	583	575	563	559	555	364
45°	474	469	458	450	446	366
55°	359	354	345	337	333	321
65°	242	237	230	223	219	239
75°	127	125	121	117	118	135
85°	31	30	29	27	26	35
90°	1	9	14	18	20	4
95°	47	25	28	32	31	57
105°	220	229	44	52	55	235
115°	415	428	446	127	59	409
125°	587	597	610	615	618	523
135°	727	738	745	752	750	561
145°	843	843	854	859	856	527
155°	928	923	930	934	929	428
165°	978	974	976	980	976	276
175°	1000	996	997	1001	995	95
180°	998	998	998	998	998	



TEST NUMBER: P331309-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	788.0	787.3	786.7	786.0	785.3	784.3	782.7	781.3	779.8	778.3	779.7
5°	784.4	783.7	783.0	782.3	781.7	780.4	778.6	776.8	774.9	773.1	774.4
7.5°	777.4	776.4	775.4	774.3	773.3	771.8	769.9	768.1	766.2	764.3	765.7
10°	770.8	769.6	768.4	767.3	766.1	764.5	762.4	760.5	758.5	756.5	757.8
12.5°	761.7	760.7	759.6	758.6	757.6	756.1	754.1	752.0	750.0	748.0	748.9
15°	746.7	745.7	744.7	743.7	742.7	741.0	738.8	736.7	734.5	732.4	733.0
17.5°	727.3	726.4	725.4	724.4	723.4	721.8	719.5	717.3	715.1	712.9	713.7
20°	713.5	712.5	711.4	710.4	709.4	707.8	705.4	703.1	700.7	698.4	698.9
22.5°	699.6	698.2	696.8	695.4	694.0	692.2	689.9	687.7	685.5	683.3	683.4
25°	675.8	674.4	673.1	671.8	670.4	668.3	665.5	662.6	659.7	656.9	657.2
27.5°	648.6	647.4	646.2	645.0	643.8	642.1	639.9	637.5	635.3	633.1	632.6
30°	630.6	629.1	627.8	626.5	625.1	623.2	620.7	618.2	615.7	613.2	612.7
32.5°	611.2	610.2	609.0	607.9	606.9	605.0	602.4	599.8	597.1	594.5	593.6
35°	583.0	581.3	579.7	577.9	576.3	574.1	571.5	568.8	566.0	563.4	562.4
37.5°	551.2	549.7	548.3	546.7	545.2	543.2	540.5	537.9	535.1	532.5	531.2
40°	529.5	528.1	526.7	525.4	524.1	522.1	519.4	516.7	514.0	511.4	509.9
42.5°	508.4	507.0	505.6	504.3	503.0	501.0	498.3	495.6	492.9	490.2	488.6
45°	474.4	473.2	472.0	470.9	469.7	467.9	465.3	462.8	460.3	457.8	456.0
47.5°	440.6	439.5	438.4	437.3	436.2	434.3	431.7	429.1	426.5	423.8	421.9
50°	417.1	416.3	415.4	414.5	413.7	412.1	409.8	407.5	405.1	402.7	400.4
52.5°	394.2	393.0	391.9	390.8	389.7	388.1	385.9	383.6	381.4	379.2	377.3
55°	359.0	358.0	357.0	356.0	355.0	353.5	351.4	349.4	347.4	345.4	343.5
57.5°	323.7	322.9	322.0	321.3	320.5	319.0	316.8	314.6	312.4	310.1	308.1
60°	300.1	299.5	298.8	298.1	297.5	296.0	293.7	291.2	288.9	286.6	284.8
62.5°	277.2	276.2	275.1	274.0	273.0	271.6	269.7	267.9	266.1	264.3	262.6
65°	242.1	241.1	240.0	239.0	238.1	236.7	235.1	233.4	231.7	230.0	228.5
67.5°	206.3	205.5	204.7	203.9	203.1	202.0	200.5	198.9	197.4	195.9	194.8
70°	184.0	183.4	182.7	182.0	181.4	180.3	178.7	177.2	175.7	174.2	173.1
72.5°	161.1	160.5	159.8	159.1	158.4	157.6	156.6	155.6	154.7	153.7	152.5
75°	126.7	126.3	126.0	125.7	125.3	124.8	123.9	123.1	122.3	121.4	120.4
77.5°	95.9	95.3	94.8	94.2	93.6	93.2	92.9	92.5	92.2	91.9	91.4
80°	75.4	75.2	75.1	74.9	74.7	74.5	74.1	73.8	73.5	73.1	72.6
82.5°	56.1	56.0	56.0	56.0	55.9	55.8	55.6	55.4	55.2	55.0	54.4
85°	30.9	30.8	30.6	30.4	30.3	30.1	29.9	29.8	29.6	29.4	28.9
87.5°	11.0	11.1	11.2	11.3	11.3	11.4	11.4	11.3	11.3	11.3	11.1
90°	0.7	2.5	4.2	6.1	7.8	9.3	10.6	11.9	13.1	14.4	15.2
92.5°	14.5	14.4	14.2	14.1	13.9	14.2	14.8	15.5	16.2	16.8	17.2
95°	47.0	41.7	36.4	31.1	25.8	23.6	24.8	26.0	27.1	28.2	29.0
97.5°	93.2	78.3	63.3	48.4	33.4	27.3	29.9	32.5	35.1	37.7	38.4
100°	127.8	105.8	83.9	61.9	39.9	30.3	33.0	35.7	38.5	41.2	42.4
102.5°	166.0	161.4	156.7	152.1	147.3	133.6	110.8	88.0	65.1	42.3	44.0
105°	219.6	224.4	229.2	234.1	238.8	219.3	175.5	131.7	87.9	44.0	45.8
107.5°	280.7	284.6	288.5	292.4	296.3	272.0	219.3	166.8	114.2	61.7	59.9
110°	320.0	323.4	326.8	330.1	333.5	311.9	265.6	219.2	172.8	126.4	110.4



TEST NUMBER: P331309-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	357.0	360.0	362.9	366.0	368.9	364.7	353.3	341.7	330.3	318.8	260.3
115°	415.4	418.1	420.8	423.5	426.3	429.7	433.6	437.7	441.7	445.8	371.4
117.5°	467.6	470.6	473.6	476.7	479.7	482.6	485.4	488.2	490.9	493.7	475.7
120°	505.6	508.1	510.5	512.9	515.3	518.0	520.9	523.7	526.6	529.5	531.4
122.5°	538.1	540.6	543.1	545.6	548.2	551.0	554.2	557.3	560.5	563.6	564.7
125°	587.3	589.4	591.5	593.6	595.6	598.2	601.3	604.3	607.3	610.5	611.6
127.5°	632.0	634.3	636.6	638.8	641.2	643.5	645.8	648.0	650.4	652.6	654.3
130°	660.2	662.9	665.4	667.9	670.6	672.7	674.5	676.2	678.0	679.7	681.6
132.5°	689.1	691.4	693.6	695.7	697.9	699.8	701.7	703.4	705.2	706.9	708.4
135°	726.7	729.3	731.8	734.5	737.0	739.0	740.4	741.8	743.4	744.8	746.4
137.5°	764.8	766.5	768.3	770.1	771.9	773.7	775.3	776.9	778.5	780.2	781.7
140°	789.6	790.8	792.1	793.5	794.7	796.3	798.0	799.8	801.5	803.3	804.8
142.5°	810.4	811.5	812.7	813.9	815.0	816.6	818.6	820.6	822.6	824.7	826.0
145°	843.0	842.8	842.7	842.5	842.4	843.6	846.4	849.1	851.8	854.5	855.8
147.5°	871.5	870.9	870.3	869.7	869.1	870.1	872.8	875.5	878.2	880.9	881.7
150°	890.0	888.9	887.8	886.7	885.4	886.3	888.8	891.3	893.9	896.5	897.5
152.5°	905.5	904.3	903.1	901.8	900.6	901.2	903.6	906.1	908.5	910.9	911.9
155°	928.3	926.9	925.3	923.9	922.5	922.7	924.6	926.6	928.5	930.4	931.4
157.5°	946.0	944.8	943.6	942.4	941.2	941.2	942.6	943.9	945.2	946.6	947.8
160°	956.4	955.4	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4	957.5
162.5°	965.7	964.7	963.8	962.8	961.8	961.8	962.6	963.4	964.3	965.1	966.2
165°	978.2	977.1	976.2	975.2	974.2	974.0	974.5	975.0	975.4	975.9	977.0
167.5°	987.3	986.4	985.4	984.5	983.5	983.2	983.7	984.1	984.6	985.0	986.1
170°	992.6	991.6	990.7	989.7	988.8	988.4	988.8	989.1	989.4	989.7	990.8
172.5°	996.0	995.0	994.1	993.1	992.2	991.9	992.2	992.5	992.8	993.1	994.3
175°	1000.5	999.4	998.3	997.1	996.0	995.6	995.9	996.2	996.5	996.9	998.0
177.5°	1001.3	1000.4	999.5	998.6	997.6	997.2	997.3	997.5	997.6	997.7	998.7
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331309-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	784.4	784.4	784.4	784.4	784.4	784.4	784.4	784.4
2.5°	781.0	782.3	783.7	784.3	784.0	783.7	783.5	783.2
5°	775.8	777.1	778.4	778.9	778.6	778.2	777.9	777.6
7.5°	767.0	768.3	769.7	770.1	769.8	769.4	769.0	768.7
10°	759.1	760.5	761.8	762.2	761.7	761.2	760.7	760.2
12.5°	749.9	750.8	751.7	752.0	751.6	751.3	750.9	750.5
15°	733.7	734.4	735.0	734.9	734.1	733.3	732.5	731.5
17.5°	714.4	715.2	716.0	715.9	715.1	714.4	713.6	712.8
20°	699.4	699.9	700.4	700.3	699.6	698.9	698.3	697.6
22.5°	683.5	683.6	683.7	683.6	683.2	682.8	682.4	682.0
25°	657.6	657.9	658.2	658.2	657.9	657.6	657.2	656.9
27.5°	632.1	631.6	631.1	630.5	629.7	628.8	628.0	627.2
30°	612.2	611.7	611.2	610.6	609.9	609.3	608.5	607.8
32.5°	592.7	591.8	590.9	590.1	589.4	588.8	588.0	587.3
35°	561.4	560.4	559.4	558.5	557.6	556.7	555.9	555.1
37.5°	530.0	528.8	527.6	526.4	525.6	524.8	524.0	523.3
40°	508.4	506.9	505.3	504.2	503.5	502.9	502.2	501.5
42.5°	487.0	485.3	483.6	482.4	481.4	480.5	479.6	478.6
45°	454.1	452.3	450.4	449.2	448.5	447.9	447.2	446.5
47.5°	420.0	418.0	416.1	414.7	413.6	412.7	411.7	410.7
50°	398.1	395.7	393.3	391.7	390.9	390.1	389.2	388.4
52.5°	375.4	373.3	371.4	369.9	368.8	367.7	366.6	365.5
55°	341.4	339.4	337.4	336.0	335.1	334.3	333.5	332.6
57.5°	306.2	304.2	302.3	300.9	300.2	299.6	299.0	298.3
60°	282.9	281.0	279.2	278.0	277.5	277.0	276.5	276.0
62.5°	260.8	259.1	257.4	256.3	255.6	255.0	254.4	253.7
65°	227.0	225.5	224.0	222.8	222.0	221.2	220.4	219.4
67.5°	193.6	192.4	191.3	190.4	189.7	188.9	188.3	187.6
70°	171.9	170.7	169.6	168.6	167.9	167.2	166.6	165.9
72.5°	151.4	150.2	149.1	148.1	147.6	147.0	146.5	146.0
75°	119.4	118.5	117.4	117.0	117.4	117.8	118.1	118.5
77.5°	90.9	90.4	89.9	89.4	88.9	88.5	88.0	87.5
80°	72.1	71.6	71.2	70.7	70.4	70.1	69.7	69.4
82.5°	53.8	53.1	52.5	52.1	52.1	52.0	51.9	51.9
85°	28.4	27.9	27.4	27.1	26.9	26.8	26.6	26.4
87.5°	10.8	10.6	10.4	10.2	10.1	10.1	10.0	9.9
90°	16.1	16.9	17.7	18.2	18.6	18.9	19.2	19.5
92.5°	17.6	18.0	18.4	18.8	18.9	19.1	19.3	19.5
95°	29.8	30.6	31.4	31.7	31.5	31.4	31.2	31.1
97.5°	39.0	39.6	40.3	40.7	40.9	41.1	41.3	41.5
100°	43.7	45.0	46.4	47.2	47.5	47.8	48.1	48.4
102.5°	45.6	47.4	49.0	50.1	50.5	51.0	51.4	51.9
105°	47.6	49.4	51.1	52.3	53.0	53.6	54.2	54.9
107.5°	58.1	56.2	54.5	53.9	54.5	55.2	55.8	56.5
110°	94.3	78.3	62.2	54.5	55.1	55.7	56.5	57.1



TEST NUMBER: P331309-840

CATALOG NUMBER: S122DIP-S485D725U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	201.8	143.2	84.6	55.5	56.1	56.7	57.2	57.7
115°	297.1	222.8	148.5	105.4	93.9	82.3	70.8	59.3
117.5°	457.8	439.7	421.7	393.7	355.8	317.8	279.8	241.9
120°	533.4	535.3	537.2	527.4	505.6	484.0	462.3	440.7
122.5°	565.9	567.0	568.3	566.7	562.5	558.3	554.1	549.9
125°	612.7	613.8	614.9	615.7	616.2	616.7	617.1	617.6
127.5°	655.9	657.5	659.1	660.0	660.1	660.2	660.4	660.5
130°	683.3	685.1	686.8	687.6	687.5	687.3	687.1	687.0
132.5°	709.9	711.4	713.0	713.7	713.5	713.4	713.2	713.0
135°	748.0	749.6	751.2	751.8	751.5	751.2	750.8	750.5
137.5°	783.4	784.9	786.5	787.0	786.5	785.9	785.4	784.8
140°	806.2	807.6	809.1	809.4	808.6	807.8	807.0	806.2
142.5°	827.3	828.6	829.9	830.2	829.4	828.6	827.8	827.0
145°	856.9	858.0	859.1	859.2	858.5	857.7	856.9	856.1
147.5°	882.5	883.4	884.2	884.3	883.6	882.9	882.3	881.6
150°	898.4	899.4	900.3	900.4	899.6	898.8	898.0	897.2
152.5°	912.8	913.8	914.8	914.7	913.7	912.6	911.6	910.5
155°	932.4	933.3	934.3	934.1	932.8	931.6	930.3	929.0
157.5°	948.8	949.9	951.0	950.9	949.7	948.4	947.2	945.9
160°	958.4	959.4	960.3	960.2	959.1	958.0	956.8	955.7
162.5°	967.2	968.4	969.5	969.4	968.0	966.5	965.2	963.8
165°	978.2	979.4	980.5	980.5	979.4	978.2	977.0	975.9
167.5°	987.3	988.5	989.6	989.4	988.0	986.5	985.0	983.6
170°	991.9	993.0	994.2	994.0	992.6	991.1	989.7	988.3
172.5°	995.4	996.5	997.6	997.4	996.0	994.6	993.1	991.7
175°	999.2	1000.3	1001.4	1001.2	999.6	997.9	996.3	994.7
177.5°	999.6	1000.5	1001.4	1001.3	1000.1	999.0	997.7	996.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4

(END OF REPORT)