

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331264-927

Luminaire Tested: **S122DIP-S290D725U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331264-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S290D725U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3249.1 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331264-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331264-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25				
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	28	26	21				
3	77	68	61	55	69	61	55	51	48	44	41	37	34	31	26	24	22	18				
4	71	60	53	47	63	54	48	43	43	38	35	33	29	27	23	21	19	15				
5	65	54	46	40	58	48	42	36	38	34	30	29	26	23	21	18	17	13				
6	60	48	40	34	53	43	36	32	34	30	26	26	23	20	19	16	15	11				
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	15	13	10				
8	51	39	32	26	45	35	29	24	28	23	20	22	18	16	16	13	12	9				
9	47	35	28	23	42	32	26	21	26	21	18	20	17	14	14	12	11	8				
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	10	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6042	6042	6042
5°	6065	5977	6015
10°	6030	5917	5946
15°	5954	5840	5835
20°	5849	5727	5720
25°	5744	5585	5585
30°	5610	5455	5407
35°	5483	5298	5219
40°	5324	5143	5044
45°	5167	4987	4864
50°	4999	4828	4657
55°	4822	4642	4467
60°	4624	4414	4253
65°	4413	4195	4000
70°	4145	3923	3734
75°	3768	3612	3525
80°	3347	3245	3078
85°	2723	2594	2334



TEST NUMBER: P331264-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.2	1.1
10°-20°	99.0	3.0
20°-30°	145.6	4.5
30°-40°	169.1	5.2
40°-50°	168.9	5.2
50°-60°	147.3	4.5
60°-70°	108.9	3.4
70°-80°	61.7	1.9
80°-90°	18.5	0.6
90°-100°	26.1	0.8
100°-110°	95.8	2.9
110°-120°	256.1	7.9
120°-130°	422.7	13.0
130°-140°	449.6	13.8
140°-150°	417.8	12.9
150°-160°	335.9	10.3
160°-170°	216.5	6.7
170°-180°	74.5	2.3
0°-30°	279.8	8.6
0°-40°	448.8	13.8
0°-60°	765.0	23.5
0°-90°	954.1	29.4
90°-120°	378.0	11.6
90°-150°	1668.1	51.3
90°-180°	2295.0	70.6
0°-180°	3249.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	374	374	374	374	374	
5°	374	373	369	372	371	35
15°	356	354	349	351	349	100
25°	322	319	314	314	314	148
35°	278	274	269	267	265	174
45°	226	224	218	215	213	175
55°	171	169	165	161	159	153
65°	116	113	110	107	105	114
75°	60	60	58	56	56	65
85°	15	14	14	13	13	17
90°	1	7	11	14	15	2
95°	37	19	22	25	24	45
105°	172	180	34	41	43	184
115°	326	336	350	100	46	321
125°	461	468	479	483	484	411
135°	570	579	584	590	589	440
145°	661	661	670	674	672	413
155°	728	724	730	733	729	335
165°	767	764	766	769	766	217
175°	785	781	782	785	780	75
180°	783	783	783	783	783	



TEST NUMBER: P331264-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	376.0	375.7	375.3	375.0	374.7	374.2	373.5	372.8	372.1	371.4	372.0
5°	374.2	373.9	373.6	373.3	373.0	372.4	371.5	370.7	369.7	368.8	369.5
7.5°	371.0	370.4	369.9	369.5	369.0	368.3	367.4	366.5	365.6	364.7	365.4
10°	367.8	367.3	366.7	366.1	365.5	364.8	363.8	362.9	361.9	360.9	361.6
12.5°	363.5	363.0	362.5	361.9	361.5	360.8	359.8	358.9	357.9	357.0	357.4
15°	356.2	355.8	355.3	354.8	354.3	353.6	352.5	351.5	350.5	349.4	349.7
17.5°	347.1	346.6	346.1	345.6	345.2	344.4	343.3	342.2	341.2	340.2	340.5
20°	340.4	339.9	339.5	339.0	338.5	337.7	336.6	335.5	334.4	333.3	333.5
22.5°	333.8	333.1	332.5	331.8	331.1	330.3	329.2	328.1	327.1	326.1	326.1
25°	322.4	321.8	321.2	320.5	319.9	318.9	317.5	316.2	314.8	313.5	313.6
27.5°	309.5	309.0	308.3	307.8	307.2	306.3	305.3	304.2	303.2	302.1	301.8
30°	300.9	300.2	299.6	299.0	298.3	297.4	296.2	295.0	293.7	292.6	292.3
32.5°	291.6	291.1	290.7	290.1	289.6	288.7	287.4	286.2	284.9	283.7	283.2
35°	278.2	277.3	276.6	275.8	275.0	273.9	272.7	271.4	270.1	268.8	268.3
37.5°	263.0	262.3	261.6	260.9	260.2	259.2	257.9	256.7	255.3	254.1	253.5
40°	252.6	252.0	251.4	250.7	250.1	249.1	247.8	246.5	245.3	244.0	243.3
42.5°	242.6	241.9	241.3	240.7	240.0	239.0	237.7	236.5	235.2	233.9	233.1
45°	226.3	225.8	225.2	224.7	224.1	223.2	222.0	220.9	219.7	218.4	217.5
47.5°	210.2	209.7	209.2	208.7	208.1	207.2	206.0	204.8	203.5	202.2	201.3
50°	199.0	198.6	198.2	197.8	197.4	196.6	195.5	194.4	193.3	192.2	191.1
52.5°	188.1	187.5	187.0	186.5	185.9	185.1	184.1	183.1	182.0	180.9	180.0
55°	171.3	170.8	170.3	169.8	169.4	168.7	167.7	166.8	165.8	164.9	163.8
57.5°	154.5	154.1	153.7	153.3	152.9	152.2	151.1	150.1	149.0	148.0	147.0
60°	143.2	142.9	142.6	142.3	142.0	141.2	140.1	139.0	137.8	136.7	135.9
62.5°	132.3	131.7	131.3	130.8	130.2	129.5	128.7	127.9	127.0	126.1	125.2
65°	115.5	115.0	114.5	114.1	113.6	113.0	112.2	111.4	110.6	109.8	109.0
67.5°	98.5	98.1	97.7	97.3	97.0	96.4	95.6	94.9	94.2	93.5	92.9
70°	87.8	87.5	87.1	86.8	86.5	86.0	85.3	84.6	83.8	83.1	82.5
72.5°	76.8	76.5	76.2	75.9	75.6	75.2	74.7	74.3	73.8	73.4	72.8
75°	60.4	60.3	60.1	60.0	59.8	59.6	59.2	58.7	58.3	57.9	57.4
77.5°	45.8	45.5	45.2	45.0	44.7	44.4	44.3	44.1	44.0	43.8	43.6
80°	36.0	35.9	35.8	35.7	35.6	35.6	35.4	35.3	35.1	34.9	34.7
82.5°	26.8	26.8	26.8	26.7	26.7	26.6	26.5	26.5	26.4	26.3	26.0
85°	14.7	14.7	14.6	14.5	14.4	14.3	14.3	14.2	14.1	14.0	13.8
87.5°	5.3	5.5	5.6	5.7	5.9	6.0	6.1	6.2	6.3	6.3	6.3
90°	0.6	2.0	3.3	4.8	6.1	7.3	8.3	9.3	10.3	11.3	12.0
92.5°	11.4	11.3	11.2	11.1	10.9	11.2	11.6	12.1	12.7	13.2	13.5
95°	36.8	32.7	28.5	24.4	20.2	18.5	19.5	20.4	21.2	22.1	22.7
97.5°	73.1	61.4	49.7	37.9	26.2	21.4	23.4	25.5	27.6	29.5	30.1
100°	100.3	83.0	65.8	48.6	31.3	23.8	25.9	28.0	30.2	32.3	33.3
102.5°	130.2	126.6	122.9	119.3	115.6	104.8	86.9	69.0	51.1	33.2	34.5
105°	172.3	176.0	179.8	183.6	187.4	172.1	137.7	103.3	68.9	34.5	36.0
107.5°	220.2	223.2	226.3	229.3	232.4	213.3	172.1	130.9	89.6	48.4	47.0
110°	251.0	253.7	256.4	259.0	261.6	244.7	208.3	172.0	135.5	99.2	86.6



TEST NUMBER: P331264-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	280.0	282.4	284.7	287.1	289.4	286.1	277.1	268.1	259.1	250.1	204.2
115°	325.8	328.0	330.1	332.2	334.4	337.1	340.2	343.3	346.5	349.7	291.4
117.5°	366.8	369.2	371.5	373.9	376.3	378.6	380.8	382.9	385.1	387.3	373.2
120°	396.6	398.5	400.4	402.3	404.3	406.3	408.6	410.8	413.1	415.3	416.8
122.5°	422.1	424.1	426.0	428.0	430.0	432.2	434.7	437.2	439.7	442.1	443.0
125°	460.7	462.3	464.0	465.6	467.2	469.3	471.7	474.0	476.4	478.9	479.7
127.5°	495.7	497.6	499.4	501.1	503.0	504.8	506.6	508.3	510.2	511.9	513.3
130°	517.9	520.0	522.0	523.9	526.0	527.7	529.1	530.4	531.9	533.2	534.6
132.5°	540.6	542.3	544.1	545.7	547.5	549.0	550.4	551.8	553.2	554.5	555.7
135°	570.1	572.1	574.1	576.2	578.1	579.7	580.8	581.9	583.1	584.2	585.5
137.5°	599.9	601.3	602.7	604.1	605.5	606.9	608.2	609.4	610.7	612.0	613.2
140°	619.4	620.4	621.4	622.4	623.4	624.6	626.0	627.4	628.8	630.2	631.3
142.5°	635.7	636.6	637.5	638.4	639.3	640.6	642.1	643.7	645.3	646.9	647.9
145°	661.3	661.2	661.1	660.9	660.8	661.8	663.9	666.1	668.2	670.3	671.3
147.5°	683.7	683.2	682.7	682.2	681.8	682.5	684.7	686.7	688.9	691.0	691.7
150°	698.2	697.3	696.4	695.5	694.6	695.2	697.2	699.2	701.2	703.2	704.0
152.5°	710.3	709.4	708.4	707.4	706.5	706.9	708.8	710.7	712.6	714.5	715.3
155°	728.2	727.1	725.9	724.8	723.7	723.8	725.3	726.8	728.3	729.8	730.6
157.5°	742.1	741.2	740.2	739.3	738.3	738.3	739.4	740.5	741.5	742.6	743.5
160°	750.3	749.5	748.8	748.0	747.3	747.3	748.0	748.8	749.5	750.3	751.1
162.5°	757.6	756.8	756.1	755.3	754.5	754.5	755.1	755.7	756.5	757.1	758.0
165°	767.3	766.5	765.8	765.0	764.2	764.1	764.5	764.9	765.2	765.6	766.4
167.5°	774.5	773.8	773.0	772.3	771.5	771.3	771.7	772.0	772.4	772.7	773.6
170°	778.6	777.8	777.1	776.3	775.6	775.3	775.6	775.9	776.1	776.3	777.2
172.5°	781.3	780.5	779.8	779.0	778.3	778.1	778.3	778.6	778.8	779.0	780.0
175°	784.8	783.9	783.1	782.2	781.3	781.0	781.3	781.5	781.7	782.0	782.9
177.5°	785.4	784.7	784.0	783.3	782.6	782.3	782.4	782.5	782.6	782.7	783.4
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331264-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	374.2	374.2	374.2	374.2	374.2	374.2	374.2	374.2
2.5°	372.6	373.3	373.9	374.2	374.1	373.9	373.8	373.7
5°	370.2	370.8	371.5	371.7	371.5	371.4	371.2	371.1
7.5°	366.0	366.6	367.3	367.5	367.3	367.1	366.9	366.8
10°	362.3	362.9	363.5	363.7	363.5	363.2	363.0	362.7
12.5°	357.8	358.2	358.7	358.9	358.7	358.5	358.3	358.1
15°	350.1	350.4	350.7	350.7	350.3	349.9	349.5	349.1
17.5°	340.9	341.3	341.6	341.6	341.2	340.9	340.5	340.1
20°	333.7	334.0	334.2	334.1	333.8	333.5	333.2	332.9
22.5°	326.1	326.2	326.2	326.1	326.0	325.7	325.6	325.4
25°	313.8	313.9	314.1	314.1	313.9	313.8	313.6	313.5
27.5°	301.6	301.3	301.1	300.8	300.4	300.0	299.7	299.3
30°	292.1	291.8	291.6	291.4	291.0	290.7	290.4	290.0
32.5°	282.8	282.3	281.9	281.5	281.2	280.9	280.6	280.3
35°	267.8	267.4	266.9	266.5	266.1	265.7	265.3	264.8
37.5°	252.9	252.3	251.7	251.2	250.8	250.4	250.1	249.7
40°	242.6	241.9	241.1	240.6	240.3	240.0	239.6	239.3
42.5°	232.3	231.6	230.8	230.1	229.7	229.3	228.9	228.4
45°	216.7	215.8	214.9	214.3	214.0	213.7	213.3	213.0
47.5°	200.4	199.5	198.5	197.8	197.4	196.9	196.5	196.0
50°	190.0	188.8	187.7	187.0	186.6	186.2	185.8	185.4
52.5°	179.1	178.2	177.2	176.5	175.9	175.5	174.9	174.4
55°	162.9	161.9	161.0	160.3	159.9	159.5	159.1	158.7
57.5°	146.1	145.1	144.2	143.5	143.3	143.0	142.7	142.4
60°	135.0	134.1	133.2	132.7	132.5	132.2	132.0	131.7
62.5°	124.5	123.7	122.9	122.3	122.0	121.7	121.4	121.0
65°	108.3	107.6	106.9	106.3	105.9	105.5	105.1	104.7
67.5°	92.4	91.8	91.3	90.8	90.5	90.2	89.8	89.5
70°	82.0	81.4	80.9	80.5	80.2	79.8	79.5	79.1
72.5°	72.2	71.7	71.1	70.7	70.4	70.2	69.9	69.6
75°	57.0	56.5	56.0	55.8	56.0	56.2	56.3	56.5
77.5°	43.3	43.1	42.9	42.6	42.4	42.2	42.0	41.7
80°	34.5	34.2	34.0	33.7	33.6	33.4	33.3	33.1
82.5°	25.7	25.3	25.0	24.9	24.9	24.8	24.8	24.8
85°	13.5	13.3	13.1	12.9	12.8	12.8	12.7	12.6
87.5°	6.2	6.1	6.0	6.0	5.9	5.9	5.9	5.9
90°	12.6	13.2	13.9	14.3	14.6	14.8	15.1	15.3
92.5°	13.8	14.1	14.4	14.7	14.8	15.0	15.1	15.3
95°	23.4	24.0	24.6	24.9	24.7	24.6	24.5	24.4
97.5°	30.6	31.1	31.6	31.9	32.1	32.2	32.4	32.6
100°	34.3	35.3	36.4	37.0	37.2	37.5	37.7	37.9
102.5°	35.8	37.2	38.4	39.3	39.6	40.0	40.3	40.7
105°	37.3	38.7	40.1	41.0	41.6	42.1	42.5	43.1
107.5°	45.6	44.1	42.8	42.3	42.8	43.3	43.8	44.3
110°	74.0	61.4	48.8	42.8	43.3	43.7	44.3	44.8



TEST NUMBER: P331264-927

CATALOG NUMBER: S122DIP-S290D725U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	158.3	112.3	66.4	43.6	44.0	44.4	44.8	45.2
115°	233.1	174.8	116.5	82.7	73.7	64.6	55.5	46.5
117.5°	359.1	344.9	330.8	308.9	279.1	249.3	219.5	189.7
120°	418.4	419.9	421.4	413.7	396.6	379.7	362.7	345.7
122.5°	443.9	444.8	445.8	444.6	441.2	437.9	434.7	431.3
125°	480.6	481.5	482.4	483.0	483.4	483.8	484.1	484.5
127.5°	514.5	515.8	517.1	517.8	517.8	517.9	518.0	518.1
130°	536.0	537.4	538.8	539.4	539.3	539.2	539.0	538.9
132.5°	556.9	558.1	559.3	559.8	559.7	559.6	559.4	559.3
135°	586.8	588.0	589.3	589.8	589.5	589.3	589.0	588.7
137.5°	614.5	615.7	617.0	617.3	617.0	616.5	616.1	615.6
140°	632.4	633.5	634.7	634.9	634.3	633.7	633.0	632.4
142.5°	649.0	650.0	651.0	651.3	650.6	650.0	649.4	648.7
145°	672.2	673.0	673.9	674.0	673.4	672.8	672.2	671.5
147.5°	692.3	693.0	693.6	693.7	693.2	692.6	692.1	691.6
150°	704.7	705.5	706.2	706.3	705.7	705.0	704.4	703.8
152.5°	716.1	716.8	717.6	717.6	716.8	715.9	715.1	714.2
155°	731.4	732.1	732.9	732.8	731.7	730.8	729.8	728.7
157.5°	744.3	745.1	746.0	745.9	745.0	743.9	743.0	742.0
160°	751.8	752.6	753.3	753.2	752.3	751.5	750.6	749.7
162.5°	758.8	759.6	760.5	760.4	759.3	758.2	757.2	756.1
165°	767.3	768.3	769.1	769.1	768.3	767.3	766.4	765.6
167.5°	774.5	775.4	776.3	776.1	775.0	773.9	772.7	771.6
170°	778.1	779.0	779.9	779.7	778.6	777.4	776.3	775.2
172.5°	780.9	781.7	782.6	782.4	781.3	780.2	779.0	777.9
175°	783.8	784.7	785.5	785.4	784.1	782.8	781.6	780.3
177.5°	784.1	784.8	785.5	785.4	784.5	783.6	782.7	781.8
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2

(END OF REPORT)