

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331345-840

Luminaire Tested: **S122DIP-S675D530U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331345-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S675D530U840-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4864.0 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331345-840

CATALOG NUMBER: S122DIP-S675D530U840-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331345-840

CATALOG NUMBER: S122DIP-S675D530U840-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	74	71	65	63	61	55	53	52	47
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44	40
3	82	73	65	59	76	68	61	56	59	54	50	50	47	43	43	40	37	34
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28	25
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25	22
7	59	47	39	33	55	44	36	31	38	32	28	33	29	25	28	25	22	19
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	30	25	32	26	22	28	23	20	24	21	18	16
10	48	36	28	23	44	34	27	22	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17312	17312	17312
5°	17378	17126	17227
10°	17274	16952	17038
15°	17060	16732	16715
20°	16756	16402	16385
25°	16456	15998	15998
30°	16067	15627	15491
35°	15707	15179	14954
40°	15253	14731	14450
45°	14805	14289	13935
50°	14320	13828	13335
55°	13813	13292	12797
60°	13249	12649	12184
65°	12642	12015	11461
70°	11877	11240	10707
75°	10805	10356	10100
80°	9586	9298	8815
85°	7836	7447	6688



TEST NUMBER: P331345-840

CATALOG NUMBER: S122DIP-S675D530U840-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.8	2.1
10°-20°	283.7	5.8
20°-30°	417.0	8.6
30°-40°	484.3	10.0
40°-50°	483.8	9.9
50°-60°	421.9	8.7
60°-70°	312.0	6.4
70°-80°	176.7	3.6
80°-90°	49.3	1.0
90°-100°	24.3	0.5
100°-110°	89.1	1.8
110°-120°	238.2	4.9
120°-130°	393.1	8.1
130°-140°	418.1	8.6
140°-150°	388.6	8.0
150°-160°	312.4	6.4
160°-170°	201.3	4.1
170°-180°	69.3	1.4
0°-30°	801.5	16.5
0°-40°	1285.8	26.4
0°-60°	2191.5	45.1
0°-90°	2729.5	56.1
90°-120°	351.5	7.2
90°-150°	1551.4	31.9
90°-180°	2134.0	43.9
0°-180°	4864.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1072	1072	1072	1072	1072	
5°	1072	1068	1057	1064	1063	102
15°	1021	1014	1001	1005	1000	287
25°	924	915	898	900	898	425
35°	797	786	770	764	759	497
45°	648	641	626	615	610	500
55°	491	484	472	460	455	439
65°	331	324	314	305	300	327
75°	173	171	166	160	162	185
85°	42	41	40	37	36	48
90°	0	6	10	13	14	4
95°	34	18	21	23	23	42
105°	160	167	32	38	40	171
115°	303	312	325	93	43	298
125°	428	436	445	449	451	382
135°	530	538	543	548	548	409
145°	615	615	624	627	624	385
155°	677	673	679	682	678	312
165°	714	711	712	715	712	202
175°	730	726	727	730	726	69
180°	728	728	728	728	728	



TEST NUMBER: P331345-840

CATALOG NUMBER: S122DIP-S675D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1077.1	1076.2	1075.3	1074.4	1073.5	1072.0	1070.0	1067.9	1065.9	1063.9	1065.7
5°	1072.2	1071.3	1070.4	1069.4	1068.5	1066.8	1064.3	1061.8	1059.2	1056.7	1058.5
7.5°	1062.7	1061.3	1059.9	1058.4	1057.0	1055.0	1052.5	1049.9	1047.3	1044.7	1046.5
10°	1053.6	1052.0	1050.4	1048.7	1047.2	1045.0	1042.3	1039.6	1036.7	1034.0	1035.8
12.5°	1041.3	1039.9	1038.3	1036.9	1035.5	1033.5	1030.7	1027.9	1025.2	1022.5	1023.8
15°	1020.6	1019.3	1017.8	1016.5	1015.1	1012.9	1010.0	1006.9	1004.0	1001.0	1002.0
17.5°	994.2	992.8	991.5	990.1	988.8	986.5	983.5	980.5	977.4	974.4	975.5
20°	975.2	973.9	972.5	971.1	969.8	967.5	964.2	961.1	957.9	954.6	955.3
22.5°	956.2	954.3	952.4	950.5	948.6	946.1	943.1	940.1	937.1	934.0	934.1
25°	923.7	921.9	920.1	918.2	916.4	913.5	909.6	905.7	901.8	898.0	898.4
27.5°	886.6	884.9	883.3	881.6	880.0	877.7	874.5	871.5	868.4	865.4	864.6
30°	861.8	860.0	858.2	856.4	854.5	851.9	848.5	845.1	841.6	838.2	837.5
32.5°	835.5	833.9	832.5	831.0	829.6	827.1	823.4	819.8	816.2	812.5	811.3
35°	796.9	794.7	792.3	790.0	787.7	784.8	781.1	777.4	773.8	770.1	768.7
37.5°	753.4	751.3	749.3	747.3	745.4	742.5	738.8	735.2	731.5	727.8	726.1
40°	723.7	721.9	720.0	718.2	716.4	713.7	709.9	706.3	702.7	698.9	696.9
42.5°	694.9	693.0	691.2	689.3	687.5	684.8	681.1	677.4	673.8	670.1	667.8
45°	648.4	646.8	645.2	643.7	642.1	639.5	636.1	632.7	629.2	625.8	623.3
47.5°	602.3	600.8	599.3	597.7	596.2	593.7	590.1	586.5	583.0	579.4	576.7
50°	570.1	569.0	567.8	566.6	565.5	563.3	560.2	556.9	553.7	550.5	547.3
52.5°	538.8	537.2	535.7	534.2	532.7	530.5	527.5	524.4	521.4	518.4	515.7
55°	490.7	489.4	488.0	486.6	485.2	483.1	480.4	477.7	474.9	472.2	469.4
57.5°	442.4	441.4	440.3	439.2	438.1	436.1	433.0	430.0	427.0	423.9	421.2
60°	410.3	409.4	408.5	407.6	406.7	404.6	401.4	398.2	395.0	391.7	389.2
62.5°	379.0	377.5	376.1	374.6	373.1	371.1	368.7	366.2	363.8	361.2	358.9
65°	330.9	329.5	328.2	326.8	325.4	323.6	321.3	319.0	316.7	314.5	312.4
67.5°	282.1	280.9	279.8	278.7	277.6	276.1	274.0	272.0	269.9	267.8	266.2
70°	251.6	250.6	249.7	248.8	247.9	246.4	244.3	242.3	240.2	238.1	236.5
72.5°	220.3	219.2	218.3	217.4	216.5	215.4	214.1	212.8	211.5	210.1	208.5
75°	173.2	172.7	172.3	171.8	171.4	170.6	169.5	168.2	167.1	166.0	164.6
77.5°	131.2	130.4	129.6	128.8	128.1	127.4	126.9	126.4	126.0	125.5	124.9
80°	103.1	102.9	102.6	102.4	102.2	101.8	101.4	100.9	100.5	100.0	99.3
82.5°	76.7	76.6	76.6	76.5	76.5	76.3	76.0	75.8	75.5	75.2	74.4
85°	42.3	42.0	41.8	41.6	41.3	41.1	40.9	40.7	40.4	40.2	39.5
87.5°	14.9	14.8	14.7	14.6	14.5	14.3	14.2	14.0	13.8	13.6	13.2
90°	0.5	1.8	3.1	4.3	5.7	6.8	7.8	8.7	9.6	10.5	11.1
92.5°	10.6	10.5	10.4	10.3	10.2	10.4	10.8	11.3	11.7	12.2	12.5
95°	34.2	30.4	26.6	22.6	18.8	17.3	18.1	18.9	19.7	20.6	21.1
97.5°	68.0	57.1	46.3	35.3	24.4	19.9	21.8	23.7	25.7	27.5	28.0
100°	93.3	77.3	61.2	45.1	29.1	22.1	24.0	26.1	28.1	30.0	31.0
102.5°	121.1	117.8	114.3	110.9	107.6	97.5	80.9	64.2	47.6	30.9	32.1
105°	160.2	163.7	167.2	170.8	174.3	160.1	128.1	96.1	64.1	32.1	33.4
107.5°	204.8	207.6	210.5	213.3	216.1	198.3	160.1	121.7	83.3	45.0	43.7
110°	233.5	235.9	238.4	240.9	243.3	227.6	193.8	160.0	126.0	92.2	80.5



TEST NUMBER: P331345-840

CATALOG NUMBER: S122DIP-S675D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	260.4	262.7	264.8	267.0	269.1	266.1	257.7	249.3	241.0	232.7	189.9
115°	303.1	305.0	307.0	309.0	311.0	313.5	316.4	319.3	322.2	325.2	270.9
117.5°	341.1	343.4	345.6	347.8	350.0	352.1	354.2	356.2	358.2	360.1	347.1
120°	368.9	370.6	372.4	374.2	376.0	377.9	380.0	382.1	384.2	386.3	387.7
122.5°	392.5	394.4	396.3	398.1	399.9	402.0	404.2	406.6	408.9	411.2	412.0
125°	428.5	430.0	431.5	433.0	434.5	436.5	438.7	440.9	443.1	445.4	446.2
127.5°	461.0	462.7	464.4	466.1	467.8	469.5	471.1	472.8	474.4	476.2	477.3
130°	481.7	483.5	485.4	487.4	489.2	490.8	492.1	493.3	494.6	495.9	497.3
132.5°	502.8	504.3	505.9	507.6	509.2	510.6	511.9	513.2	514.4	515.7	516.8
135°	530.2	532.1	533.9	535.8	537.7	539.2	540.2	541.3	542.3	543.3	544.5
137.5°	558.0	559.2	560.5	561.8	563.1	564.4	565.6	566.8	567.9	569.2	570.4
140°	576.0	576.9	577.9	578.9	579.8	580.9	582.2	583.5	584.7	586.0	587.1
142.5°	591.2	592.1	592.9	593.7	594.6	595.7	597.2	598.6	600.2	601.7	602.6
145°	615.0	614.9	614.8	614.7	614.6	615.5	617.5	619.5	621.5	623.5	624.3
147.5°	635.8	635.3	634.9	634.5	634.0	634.8	636.7	638.7	640.7	642.7	643.3
150°	649.2	648.4	647.6	646.8	646.0	646.5	648.4	650.3	652.2	654.0	654.7
152.5°	660.7	659.7	658.8	657.9	657.0	657.4	659.2	661.1	662.8	664.6	665.3
155°	677.2	676.2	675.1	674.1	673.0	673.2	674.6	676.0	677.4	678.8	679.5
157.5°	690.1	689.3	688.4	687.5	686.6	686.7	687.6	688.6	689.6	690.6	691.4
160°	697.8	697.1	696.4	695.7	695.0	695.0	695.7	696.4	697.1	697.8	698.5
162.5°	704.5	703.8	703.1	702.4	701.8	701.7	702.3	702.9	703.5	704.1	704.9
165°	713.6	712.9	712.2	711.4	710.7	710.6	710.9	711.2	711.7	712.0	712.9
167.5°	720.3	719.6	718.9	718.2	717.5	717.3	717.6	718.0	718.3	718.6	719.4
170°	724.1	723.5	722.8	722.1	721.3	721.0	721.3	721.5	721.8	722.1	722.9
172.5°	726.7	726.0	725.3	724.6	723.9	723.6	723.9	724.1	724.3	724.6	725.4
175°	729.9	729.1	728.3	727.5	726.6	726.4	726.6	726.8	727.0	727.3	728.1
177.5°	730.4	729.8	729.1	728.5	727.8	727.5	727.6	727.7	727.8	727.9	728.6
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3



TEST NUMBER: P331345-840

CATALOG NUMBER: S122DIP-S675D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2	1072.2
2.5°	1067.5	1069.4	1071.3	1072.0	1071.6	1071.3	1070.9	1070.6
5°	1060.4	1062.2	1064.0	1064.7	1064.3	1063.8	1063.4	1062.9
7.5°	1048.4	1050.3	1052.1	1052.7	1052.2	1051.8	1051.3	1050.8
10°	1037.6	1039.6	1041.4	1041.9	1041.3	1040.6	1039.9	1039.2
12.5°	1025.0	1026.3	1027.6	1027.9	1027.4	1027.0	1026.5	1026.0
15°	1002.9	1003.8	1004.7	1004.6	1003.4	1002.3	1001.2	1000.0
17.5°	976.5	977.5	978.7	978.7	977.5	976.4	975.3	974.2
20°	956.0	956.7	957.4	957.3	956.3	955.4	954.5	953.6
22.5°	934.3	934.4	934.5	934.3	933.8	933.2	932.7	932.2
25°	898.9	899.3	899.8	899.8	899.3	898.9	898.4	898.0
27.5°	863.9	863.3	862.6	861.7	860.6	859.5	858.4	857.3
30°	836.8	836.1	835.4	834.6	833.6	832.7	831.8	830.9
32.5°	810.1	808.9	807.6	806.6	805.7	804.8	803.8	802.8
35°	767.4	766.0	764.6	763.4	762.2	761.0	759.9	758.7
37.5°	724.5	722.8	721.0	719.6	718.5	717.4	716.4	715.3
40°	694.9	692.8	690.7	689.2	688.3	687.4	686.5	685.6
42.5°	665.6	663.4	661.2	659.3	658.0	656.8	655.5	654.2
45°	620.8	618.2	615.7	614.0	613.1	612.2	611.3	610.3
47.5°	574.1	571.4	568.8	566.7	565.4	564.1	562.8	561.5
50°	544.1	540.9	537.7	535.5	534.3	533.2	532.1	530.9
52.5°	513.0	510.4	507.8	505.6	504.1	502.6	501.1	499.6
55°	466.7	463.9	461.2	459.2	458.1	457.0	455.8	454.6
57.5°	418.5	415.8	413.1	411.3	410.4	409.6	408.7	407.8
60°	386.7	384.2	381.6	380.1	379.4	378.7	378.0	377.3
62.5°	356.6	354.3	351.9	350.3	349.4	348.5	347.7	346.8
65°	310.3	308.2	306.2	304.6	303.5	302.3	301.1	300.0
67.5°	264.6	263.1	261.5	260.1	259.2	258.3	257.4	256.5
70°	234.9	233.4	231.8	230.5	229.5	228.6	227.7	226.8
72.5°	206.9	205.3	203.7	202.5	201.8	201.1	200.4	199.5
75°	163.2	161.9	160.5	160.1	160.5	161.0	161.4	161.9
77.5°	124.2	123.5	122.8	122.2	121.5	120.9	120.3	119.6
80°	98.7	98.0	97.3	96.6	96.2	95.7	95.3	94.8
82.5°	73.5	72.6	71.8	71.3	71.2	71.1	71.0	70.9
85°	38.9	38.2	37.5	37.0	36.8	36.6	36.4	36.1
87.5°	12.8	12.3	11.9	11.6	11.5	11.4	11.2	11.1
90°	11.7	12.3	12.9	13.3	13.5	13.7	14.0	14.2
92.5°	12.8	13.1	13.4	13.6	13.8	13.9	14.1	14.2
95°	21.7	22.3	22.9	23.1	23.0	22.9	22.8	22.6
97.5°	28.5	28.9	29.4	29.7	29.8	30.0	30.1	30.3
100°	31.9	32.8	33.8	34.3	34.6	34.8	35.0	35.3
102.5°	33.3	34.5	35.7	36.6	36.9	37.2	37.5	37.9
105°	34.7	36.1	37.3	38.2	38.7	39.1	39.6	40.1
107.5°	42.4	41.1	39.8	39.4	39.8	40.3	40.7	41.2
110°	68.8	57.1	45.3	39.8	40.2	40.7	41.2	41.6



TEST NUMBER: P331345-840

CATALOG NUMBER: S122DIP-S675D530U840-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	147.1	104.4	61.7	40.6	40.9	41.3	41.7	42.0
115°	216.7	162.5	108.3	77.0	68.5	60.1	51.6	43.2
117.5°	334.0	320.8	307.7	287.3	259.5	231.9	204.2	176.4
120°	389.1	390.5	391.9	384.8	368.9	353.1	337.3	321.4
122.5°	412.8	413.7	414.5	413.4	410.4	407.3	404.2	401.1
125°	447.0	447.8	448.6	449.2	449.6	449.9	450.3	450.6
127.5°	478.5	479.7	480.9	481.5	481.6	481.7	481.7	481.8
130°	498.5	499.8	501.1	501.7	501.5	501.4	501.3	501.2
132.5°	518.0	519.1	520.2	520.6	520.5	520.4	520.3	520.2
135°	545.7	546.8	548.1	548.6	548.3	548.1	547.9	547.5
137.5°	571.5	572.6	573.8	574.1	573.7	573.3	573.0	572.6
140°	588.1	589.2	590.3	590.5	589.9	589.4	588.8	588.1
142.5°	603.6	604.5	605.5	605.7	605.1	604.5	603.9	603.3
145°	625.1	625.9	626.7	626.8	626.3	625.7	625.1	624.5
147.5°	643.9	644.5	645.1	645.1	644.7	644.2	643.7	643.2
150°	655.4	656.1	656.8	656.9	656.3	655.7	655.1	654.6
152.5°	666.0	666.7	667.4	667.3	666.6	665.8	665.0	664.3
155°	680.2	681.0	681.7	681.5	680.5	679.6	678.7	677.7
157.5°	692.2	693.0	693.8	693.8	692.8	691.9	690.9	690.0
160°	699.1	699.8	700.5	700.5	699.7	698.9	698.0	697.2
162.5°	705.7	706.5	707.3	707.2	706.2	705.2	704.2	703.2
165°	713.7	714.5	715.3	715.3	714.5	713.7	712.9	712.0
167.5°	720.2	721.1	722.0	721.9	720.7	719.7	718.6	717.6
170°	723.7	724.5	725.3	725.2	724.1	723.1	722.1	720.9
172.5°	726.2	727.0	727.8	727.7	726.7	725.6	724.6	723.5
175°	728.9	729.7	730.5	730.4	729.2	728.0	726.9	725.7
177.5°	729.2	729.9	730.5	730.4	729.6	728.7	727.9	727.1
180°	728.3	728.3	728.3	728.3	728.3	728.3	728.3	728.3

(END OF REPORT)