

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331321-927

Luminaire Tested: **S122DIP-S485D1080U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331321-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S485D1080U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5111.8 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35	29
2	86	79	73	68	77	72	67	63	58	54	51	45	42	40	32	31	30	24
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26	21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	23	18
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16	13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12429	12429	12429	12429
5°	13935	12511	11086	12511
10°	15967	12408	9594	12408
15°	17665	12179	8476	12179
20°	17395	11936	7727	11936
25°	15684	11610	7252	11610
30°	12961	11091	6906	11091
35°	9447	10549	6660	10549
40°	7546	9908	6521	9908
45°	6594	9168	6336	9168
50°	6199	8450	6212	8450
55°	5714	7721	6046	7721
60°	5238	6946	5790	6946
65°	4768	6250	5540	6250
70°	4329	5570	5169	5570
75°	3843	4816	4579	4816
80°	3301	3989	3682	3989
85°	2964	2964	2186	2964



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	1.4
10°-20°	213.1	4.2
20°-30°	309.3	6.1
30°-40°	326.4	6.4
40°-50°	289.0	5.7
50°-60°	230.6	4.5
60°-70°	156.8	3.1
70°-80°	80.4	1.6
80°-90°	22.2	0.4
90°-100°	38.8	0.8
100°-110°	142.4	2.8
110°-120°	380.6	7.4
120°-130°	628.2	12.3
130°-140°	668.1	13.1
140°-150°	620.9	12.1
150°-160°	499.2	9.8
160°-170°	321.7	6.3
170°-180°	110.7	2.2
0°-30°	595.8	11.7
0°-40°	922.2	18.0
0°-60°	1441.8	28.2
0°-90°	1701.2	33.3
90°-120°	561.7	11.0
90°-150°	2478.9	48.5
90°-180°	3411.0	66.7
0°-180°	5111.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	770	770	770	770	770	
5°	860	772	684	772	860	86
15°	1057	729	507	729	1057	292
25°	880	652	407	652	880	398
35°	479	535	338	535	479	312
45°	289	402	278	402	289	227
55°	203	274	215	274	203	182
65°	125	164	145	164	125	124
75°	62	77	73	77	62	66
85°	16	16	12	16	16	18
90°	23	1	23	1	23	11
95°	36	55	36	55	36	34
105°	64	256	64	256	64	67
115°	69	484	69	484	69	173
125°	720	685	720	685	720	623
135°	875	847	875	847	875	674
145°	998	983	998	983	998	624
155°	1083	1082	1083	1082	1083	500
165°	1138	1140	1138	1140	1138	321
175°	1160	1166	1160	1166	1160	110
180°	1164	1164	1164	1164	1164	



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	805.3	805.6	806.0	802.2	801.8	801.8	798.4	795.6	792.3	787.7	788.2
5°	859.8	863.0	864.2	860.6	855.3	854.7	849.7	841.4	833.7	827.5	823.1
7.5°	924.7	926.0	923.1	918.5	914.5	907.4	898.0	888.8	876.0	864.2	855.5
10°	973.9	975.7	970.7	963.8	958.2	950.0	936.4	922.4	905.6	889.3	876.3
12.5°	1011.3	1015.7	1009.2	1008.4	998.7	987.4	971.1	964.1	940.4	917.7	903.7
15°	1056.8	1056.5	1057.1	1051.5	1044.3	1042.6	1025.4	1006.8	973.4	960.0	936.9
17.5°	1043.6	1048.1	1050.2	1050.1	1050.0	1048.8	1043.3	1031.6	1014.8	993.2	966.6
20°	1012.4	1018.3	1019.2	1026.0	1029.8	1034.9	1037.0	1033.7	1023.3	1005.3	982.2
22.5°	964.1	965.7	968.5	979.1	987.5	1000.1	1006.6	1017.6	1013.6	1004.8	985.6
25°	880.4	877.5	887.8	893.2	912.4	932.5	947.0	963.0	977.2	985.8	980.2
27.5°	780.0	775.5	791.1	805.2	820.8	842.6	865.1	891.8	914.0	941.8	951.3
30°	695.2	697.9	712.7	727.8	751.5	782.2	807.6	836.9	868.6	899.7	921.2
32.5°	603.9	614.1	623.4	646.6	667.4	701.7	739.0	775.6	815.2	850.4	883.8
35°	479.3	491.1	504.1	521.0	550.2	584.3	620.7	670.1	724.0	772.1	811.8
37.5°	403.4	401.6	409.0	421.2	444.9	472.4	514.2	563.1	626.5	683.1	739.0
40°	358.0	356.8	362.1	373.4	391.4	411.5	448.2	491.1	550.0	619.2	685.8
42.5°	326.7	327.4	330.4	338.3	350.7	367.3	394.7	431.3	485.1	550.3	621.9
45°	288.8	290.8	294.1	297.9	305.0	318.6	334.0	360.0	402.7	457.1	527.5
47.5°	261.4	261.5	264.7	268.2	272.4	280.0	292.6	309.0	339.0	383.3	443.9
50°	246.8	244.6	247.0	249.7	254.1	259.4	267.8	283.1	303.2	339.1	389.6
52.5°	228.8	228.8	230.9	232.0	235.9	241.2	248.8	259.4	277.7	305.7	347.3
55°	203.0	204.5	205.7	207.4	211.0	214.8	220.7	227.8	242.0	263.0	293.7
57.5°	178.7	179.2	180.4	183.7	186.0	189.5	195.1	201.6	210.8	226.4	249.5
60°	162.2	162.2	164.5	166.0	168.9	172.5	176.9	183.2	191.4	204.1	222.8
62.5°	146.9	146.7	147.7	150.1	152.3	155.7	160.1	165.4	173.2	184.5	199.8
65°	124.8	124.3	126.0	126.6	129.0	132.2	135.8	141.4	147.7	155.9	169.5
67.5°	103.5	104.3	105.2	106.3	107.7	111.1	113.4	117.4	122.6	129.5	138.8
70°	91.7	91.7	91.7	92.6	94.3	96.2	98.5	101.8	106.8	112.7	121.0
72.5°	78.4	79.4	80.3	79.9	82.1	83.1	86.0	87.8	92.6	96.4	103.7
75°	61.6	61.6	61.6	63.0	63.9	64.8	66.5	68.4	70.7	75.4	79.3
77.5°	45.9	45.8	46.1	46.4	47.4	48.5	49.0	50.6	52.8	55.0	58.2
80°	35.5	36.1	36.4	37.0	37.0	37.5	37.9	39.9	41.4	42.9	45.0
82.5°	27.5	27.6	27.6	27.7	28.0	28.4	29.1	29.8	30.3	31.5	33.1
85°	16.0	15.7	15.7	16.2	16.0	16.0	16.6	17.2	17.2	17.4	18.4
87.5°	10.7	10.6	10.8	10.5	10.4	10.5	10.3	9.9	10.0	10.0	9.9
90°	22.7	22.3	22.0	21.6	21.2	20.6	19.6	18.7	17.7	16.9	15.4
92.5°	22.7	22.5	22.3	22.1	21.9	21.5	21.0	20.5	20.0	19.6	18.8
95°	36.2	36.4	36.6	36.8	37.0	36.6	35.6	34.7	33.7	32.9	31.5
97.5°	48.3	48.1	47.9	47.7	47.5	47.0	46.2	45.5	44.7	44.0	41.0
100°	56.4	56.1	55.7	55.3	54.9	54.0	52.5	51.0	49.5	48.0	44.8
102.5°	60.4	60.0	59.4	58.9	58.4	57.1	55.2	53.2	51.3	49.4	46.0
105°	64.0	63.2	62.5	61.8	61.0	59.6	57.5	55.5	53.4	51.3	48.4
107.5°	65.8	65.1	64.3	63.6	62.9	63.5	65.6	67.7	69.8	71.9	73.2
110°	66.5	65.8	65.0	64.2	63.5	72.5	91.3	110.0	128.7	147.3	201.5



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	67.2	66.6	66.0	65.4	64.8	98.6	166.9	235.2	303.5	371.7	385.1
115°	69.1	82.5	96.0	109.5	122.9	173.0	259.7	346.3	432.9	519.6	514.9
117.5°	281.9	326.2	370.5	414.8	459.1	491.7	512.6	533.6	554.5	575.5	572.3
120°	513.7	538.9	564.2	589.5	614.7	626.3	624.0	621.8	619.5	617.3	613.9
122.5°	641.0	645.9	650.9	655.8	660.6	662.4	661.1	659.7	658.4	657.0	653.4
125°	720.0	719.5	718.9	718.4	717.8	716.8	715.5	714.2	712.9	711.6	708.1
127.5°	769.8	769.8	769.7	769.5	769.4	768.4	766.5	764.6	762.7	760.8	758.1
130°	800.9	801.1	801.2	801.5	801.6	800.7	798.6	796.5	794.5	792.4	790.4
132.5°	831.2	831.4	831.6	831.7	831.9	831.2	829.4	827.6	825.9	824.1	822.0
135°	875.0	875.4	875.7	876.1	876.5	875.7	873.9	872.0	870.1	868.2	866.6
137.5°	914.9	915.5	916.2	916.8	917.4	916.8	915.0	913.1	911.3	909.5	907.6
140°	939.8	940.7	941.7	942.6	943.6	943.2	941.5	939.8	938.1	936.4	934.4
142.5°	964.1	965.0	965.9	966.9	967.8	967.5	966.0	964.4	962.9	961.4	959.0
145°	997.9	998.9	999.8	1000.8	1001.6	1001.5	1000.1	998.9	997.5	996.2	993.1
147.5°	1027.7	1028.5	1029.3	1030.1	1030.9	1030.8	1029.8	1028.8	1027.9	1026.9	1023.7
150°	1045.9	1046.9	1047.8	1048.7	1049.6	1049.6	1048.5	1047.3	1046.2	1045.0	1042.1
152.5°	1061.4	1062.6	1063.9	1065.1	1066.4	1066.4	1065.3	1064.1	1063.0	1061.9	1059.1
155°	1083.0	1084.5	1086.0	1087.4	1088.9	1089.2	1088.1	1086.9	1085.8	1084.7	1082.4
157.5°	1102.6	1104.1	1105.6	1107.1	1108.5	1108.6	1107.3	1106.0	1104.8	1103.5	1101.9
160°	1114.1	1115.5	1116.7	1118.1	1119.4	1119.4	1118.3	1117.2	1116.1	1115.0	1113.9
162.5°	1123.6	1125.1	1126.8	1128.4	1130.0	1130.2	1128.9	1127.6	1126.3	1125.1	1124.1
165°	1137.7	1139.0	1140.3	1141.6	1143.0	1143.0	1141.6	1140.3	1139.0	1137.7	1137.2
167.5°	1146.6	1148.3	1150.0	1151.7	1153.3	1153.6	1152.2	1151.0	1149.6	1148.3	1147.8
170°	1152.0	1153.7	1155.4	1157.1	1158.7	1159.0	1157.6	1156.3	1155.0	1153.7	1153.3
172.5°	1156.0	1157.8	1159.4	1161.1	1162.8	1163.0	1161.7	1160.4	1159.0	1157.8	1157.4
175°	1159.6	1161.5	1163.3	1165.2	1167.1	1167.4	1166.1	1164.7	1163.5	1162.1	1161.7
177.5°	1161.8	1163.2	1164.5	1165.9	1167.2	1167.4	1166.3	1165.2	1164.2	1163.2	1163.0
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	789.9	788.0	786.8	782.6	778.8	775.0	773.8	774.3	769.1	764.1	762.0
5°	820.7	814.8	809.1	801.1	791.7	781.3	776.0	771.9	761.5	750.3	743.8
7.5°	848.3	839.8	828.9	814.0	800.2	783.9	773.5	764.4	749.2	733.3	723.7
10°	865.1	853.5	839.6	821.3	804.4	784.6	770.7	756.8	739.0	720.1	708.3
12.5°	879.5	864.0	850.2	826.7	806.8	782.0	765.5	745.9	727.2	704.7	693.1
15°	913.9	885.2	859.1	832.5	807.9	773.3	755.0	728.6	704.1	676.3	663.0
17.5°	940.4	908.2	867.2	833.4	804.7	766.4	739.4	707.9	678.8	647.1	629.0
20°	955.6	918.6	874.5	834.3	799.9	756.2	726.9	694.7	660.6	624.8	605.3
22.5°	964.6	925.7	882.1	830.8	790.5	747.9	711.1	675.7	641.2	602.6	582.1
25°	967.4	931.9	885.7	827.8	778.6	730.5	686.0	651.7	610.1	573.9	544.1
27.5°	953.3	927.9	883.5	822.2	765.0	708.6	659.2	620.3	576.2	537.1	507.0
30°	936.0	921.2	878.1	816.5	754.1	693.5	639.1	594.9	551.2	511.5	480.8
32.5°	909.3	906.1	868.2	808.5	742.5	674.3	618.0	573.4	524.9	485.9	456.6
35°	856.7	871.0	847.0	790.5	720.6	647.1	586.1	535.2	484.9	447.6	420.1
37.5°	786.4	821.7	815.4	764.1	691.2	617.3	550.0	496.9	448.9	411.3	384.3
40°	737.8	782.8	789.3	744.0	670.4	594.4	523.1	470.1	423.3	389.0	361.8
42.5°	685.8	738.3	756.2	719.9	647.7	570.2	498.9	444.1	397.8	364.4	340.3
45°	598.5	668.0	700.3	679.5	609.7	530.4	457.1	401.5	359.5	328.1	309.4
47.5°	516.9	592.9	636.3	628.9	567.5	489.0	416.5	363.1	322.3	297.2	280.5
50°	459.1	537.3	589.6	592.0	537.3	459.5	386.7	336.4	298.8	275.4	261.8
52.5°	409.0	483.5	540.7	553.2	503.4	428.6	359.9	309.9	276.8	255.3	243.1
55°	343.5	406.5	469.8	492.9	453.0	381.9	318.3	274.3	243.2	228.4	217.8
57.5°	285.6	338.1	396.6	422.1	397.4	336.7	277.0	238.8	213.6	200.6	192.4
60°	255.0	296.4	348.5	379.0	357.7	303.6	251.4	215.1	194.4	182.8	175.2
62.5°	226.6	263.3	307.3	335.2	323.6	272.5	225.9	193.8	175.9	165.1	159.5
65°	187.0	215.9	250.0	275.8	268.1	229.3	191.2	163.6	149.4	140.9	136.4
67.5°	153.9	174.9	198.5	221.0	214.8	187.4	156.8	135.3	124.7	117.3	114.7
70°	133.2	149.1	170.1	188.1	183.2	160.7	136.4	118.0	108.8	102.7	100.0
72.5°	113.3	126.4	142.4	157.2	153.8	135.1	114.9	101.0	94.0	88.2	86.0
75°	85.5	95.5	105.4	115.1	114.2	99.7	87.9	77.2	71.6	67.2	66.3
77.5°	63.1	68.8	75.4	81.2	79.6	71.3	62.0	55.9	51.8	48.8	48.3
80°	48.2	51.5	56.2	60.4	58.3	54.7	47.4	42.9	39.9	37.0	35.8
82.5°	34.9	38.3	41.0	43.3	41.7	38.4	33.8	30.8	29.1	27.0	26.5
85°	18.4	20.1	21.3	21.9	21.3	19.3	17.2	16.0	14.5	13.6	13.3
87.5°	9.9	9.6	9.3	9.4	8.2	7.8	6.5	5.4	5.5	5.7	5.6
90°	13.9	12.4	10.9	9.1	7.1	5.0	2.9	0.9	2.9	5.0	7.1
92.5°	18.1	17.3	16.6	16.2	16.5	16.6	16.8	17.0	16.8	16.6	16.5
95°	30.3	28.9	27.6	30.0	36.2	42.4	48.6	54.7	48.6	42.4	36.2
97.5°	37.9	34.9	31.8	39.1	56.4	73.8	91.3	108.6	91.3	73.8	56.4
100°	41.7	38.4	35.3	46.5	72.2	97.8	123.4	149.1	123.4	97.8	72.2
102.5°	102.6	129.2	155.8	171.8	177.2	182.7	188.1	193.5	188.1	182.7	177.2
105°	153.5	204.6	255.7	278.5	272.8	267.2	261.7	256.0	261.7	267.2	272.8
107.5°	194.5	255.7	317.0	345.4	340.8	336.3	331.8	327.3	331.8	336.3	340.8
110°	255.6	309.6	363.7	388.8	384.8	381.0	377.0	373.0	377.0	381.0	384.8



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	398.5	411.8	425.2	430.1	426.6	423.1	419.7	416.2	419.7	423.1	426.6
115°	510.2	505.6	500.9	496.9	493.8	490.6	487.4	484.3	487.4	490.6	493.8
117.5°	569.1	565.9	562.6	559.3	555.7	552.2	548.6	545.0	548.6	552.2	555.7
120°	610.5	607.2	603.8	600.7	597.9	595.1	592.3	589.5	592.3	595.1	597.9
122.5°	649.7	646.0	642.4	639.1	636.1	633.1	630.2	627.2	630.2	633.1	636.1
125°	704.5	700.9	697.4	694.3	692.0	689.5	687.1	684.7	687.1	689.5	692.0
127.5°	755.4	752.8	750.1	747.5	744.8	742.1	739.4	736.7	739.4	742.1	744.8
130°	788.3	786.2	784.2	781.6	778.7	775.7	772.7	769.7	772.7	775.7	778.7
132.5°	820.0	817.9	815.9	813.6	811.0	808.5	806.0	803.4	806.0	808.5	811.0
135°	864.8	863.2	861.5	859.1	856.2	853.2	850.2	847.2	850.2	853.2	856.2
137.5°	905.7	903.8	901.8	899.8	897.8	895.6	893.6	891.4	893.6	895.6	897.8
140°	932.3	930.3	928.2	926.5	925.0	923.4	921.9	920.4	921.9	923.4	925.0
142.5°	956.6	954.3	952.0	950.1	948.7	947.4	946.0	944.7	946.0	947.4	948.7
145°	989.8	986.7	983.5	982.0	982.2	982.4	982.5	982.8	982.5	982.4	982.2
147.5°	1020.6	1017.5	1014.3	1013.1	1013.8	1014.5	1015.3	1016.0	1015.3	1014.5	1013.8
150°	1039.1	1036.1	1033.1	1032.3	1033.6	1034.9	1036.2	1037.5	1036.2	1034.9	1033.6
152.5°	1056.2	1053.4	1050.5	1049.9	1051.3	1052.7	1054.2	1055.7	1054.2	1052.7	1051.3
155°	1080.1	1077.9	1075.7	1075.4	1077.1	1078.8	1080.5	1082.1	1080.5	1078.8	1077.1
157.5°	1100.3	1098.8	1097.3	1097.2	1098.6	1100.0	1101.5	1102.9	1101.5	1100.0	1098.6
160°	1112.7	1111.6	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0	1113.9	1112.7	1111.6
162.5°	1123.2	1122.1	1121.2	1121.3	1122.4	1123.5	1124.7	1125.8	1124.7	1123.5	1122.4
165°	1136.6	1136.0	1135.4	1135.8	1136.9	1138.0	1139.1	1140.3	1139.1	1138.0	1136.9
167.5°	1147.2	1146.8	1146.2	1146.5	1147.6	1148.7	1149.9	1151.0	1149.9	1148.7	1147.6
170°	1152.9	1152.6	1152.2	1152.6	1153.7	1154.8	1156.0	1157.1	1156.0	1154.8	1153.7
172.5°	1157.0	1156.7	1156.3	1156.7	1157.8	1158.9	1160.0	1161.1	1160.0	1158.9	1157.8
175°	1161.4	1161.0	1160.6	1161.1	1162.4	1163.7	1165.1	1166.3	1165.1	1163.7	1162.4
177.5°	1162.8	1162.7	1162.5	1163.0	1164.0	1165.1	1166.2	1167.2	1166.2	1165.1	1164.0
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	759.6	758.2	753.2	750.6	746.4	742.4	739.7	740.9	741.9	741.4	740.7
5°	737.8	732.2	723.7	716.2	710.9	701.2	697.0	695.0	693.2	691.1	689.0
7.5°	711.9	703.1	690.8	680.2	670.3	658.1	651.3	647.1	642.8	638.1	634.0
10°	693.5	681.0	668.0	653.2	641.4	630.4	620.7	614.2	608.2	602.6	598.5
12.5°	674.1	659.7	643.6	623.4	610.4	594.7	593.3	581.8	572.5	569.0	564.2
15°	643.2	623.1	602.6	578.7	568.3	554.1	545.3	536.4	528.4	522.8	521.3
17.5°	608.1	582.0	561.7	544.5	527.6	513.0	504.9	497.7	491.2	483.6	482.7
20°	581.3	558.9	536.7	521.6	504.1	489.3	479.3	472.1	466.5	462.1	458.3
22.5°	556.0	531.4	511.1	494.6	477.4	465.4	457.5	450.7	446.0	441.1	437.4
25°	515.4	496.1	474.0	455.3	441.1	433.4	426.9	421.0	418.0	414.8	410.7
27.5°	479.8	458.4	437.7	423.3	410.7	403.9	399.3	395.3	392.5	390.6	388.2
30°	454.7	433.1	416.8	402.7	392.3	385.5	382.5	380.2	376.9	375.7	374.5
32.5°	430.6	411.1	397.2	384.9	375.0	370.6	367.9	365.8	363.2	362.0	359.7
35°	396.4	380.2	366.5	359.7	351.7	347.9	345.9	342.9	340.6	339.4	339.1
37.5°	364.3	350.1	341.2	332.5	329.1	326.7	323.9	321.9	321.2	321.0	320.7
40°	343.5	331.9	323.9	316.9	315.4	311.8	309.4	307.7	307.7	308.0	307.7
42.5°	324.6	314.2	307.1	301.0	299.3	297.1	294.8	294.7	295.2	296.1	295.2
45°	295.9	288.4	283.4	280.4	277.2	275.1	274.8	275.8	276.0	276.3	277.2
47.5°	269.4	264.5	260.0	256.7	255.3	254.9	254.6	256.1	257.5	258.1	259.4
50°	253.8	248.2	244.4	242.3	241.1	240.5	241.1	242.9	244.1	245.6	246.4
52.5°	236.3	232.3	229.7	228.1	227.6	228.0	228.1	230.1	232.0	232.5	233.0
55°	212.1	209.1	208.6	205.9	207.1	206.8	208.3	209.5	211.2	213.0	213.3
57.5°	188.0	185.6	184.0	184.3	184.6	185.9	187.1	189.3	191.2	193.0	193.2
60°	171.9	170.7	169.8	169.8	170.4	172.2	173.6	175.7	176.9	178.1	179.0
62.5°	157.2	156.1	155.1	155.6	157.2	158.2	159.9	161.1	162.2	163.4	163.8
65°	134.0	133.4	134.4	134.9	135.2	136.7	138.8	139.7	140.9	141.4	143.5
67.5°	112.6	112.8	112.6	113.5	115.2	115.6	117.5	119.6	119.9	121.0	122.3
70°	98.2	98.8	99.4	100.0	101.5	102.0	103.5	104.4	105.6	106.5	107.4
72.5°	85.0	85.1	85.7	85.6	86.8	88.1	89.4	90.2	91.4	92.5	93.4
75°	65.4	65.4	66.0	66.3	67.7	69.2	68.9	69.6	70.7	71.9	72.5
77.5°	47.8	47.1	47.8	48.0	48.5	49.7	50.0	50.9	52.2	51.8	52.4
80°	36.4	35.5	36.4	36.7	36.7	38.2	38.2	38.7	39.6	38.7	39.6
82.5°	26.0	25.6	26.2	26.3	26.8	26.8	27.3	27.4	28.3	27.9	28.3
85°	13.0	12.8	13.0	12.8	13.0	13.3	13.3	13.0	13.0	13.6	12.8
87.5°	5.9	5.9	6.0	6.3	6.4	6.4	6.4	6.6	6.7	6.5	6.7
90°	9.1	10.9	12.4	13.9	15.4	16.9	17.7	18.7	19.6	20.6	21.2
92.5°	16.2	16.6	17.3	18.1	18.8	19.6	20.0	20.5	21.0	21.5	21.9
95°	30.0	27.6	28.9	30.3	31.5	32.9	33.7	34.7	35.6	36.6	37.0
97.5°	39.1	31.8	34.9	37.9	41.0	44.0	44.7	45.5	46.2	47.0	47.5
100°	46.5	35.3	38.4	41.7	44.8	48.0	49.5	51.0	52.5	54.0	54.9
102.5°	171.8	155.8	129.2	102.6	76.0	49.4	51.3	53.2	55.2	57.1	58.4
105°	278.5	255.7	204.6	153.5	102.4	51.3	53.4	55.5	57.5	59.6	61.0
107.5°	345.4	317.0	255.7	194.5	133.2	71.9	69.8	67.7	65.6	63.5	62.9
110°	388.8	363.7	309.6	255.6	201.5	147.3	128.7	110.0	91.3	72.5	63.5



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	430.1	425.2	411.8	398.5	385.1	371.7	303.5	235.2	166.9	98.6	64.8
115°	496.9	500.9	505.6	510.2	514.9	519.6	432.9	346.3	259.7	173.0	122.9
117.5°	559.3	562.6	565.9	569.1	572.3	575.5	554.5	533.6	512.6	491.7	459.1
120°	600.7	603.8	607.2	610.5	613.9	617.3	619.5	621.8	624.0	626.3	614.7
122.5°	639.1	642.4	646.0	649.7	653.4	657.0	658.4	659.7	661.1	662.4	660.6
125°	694.3	697.4	700.9	704.5	708.1	711.6	712.9	714.2	715.5	716.8	717.8
127.5°	747.5	750.1	752.8	755.4	758.1	760.8	762.7	764.6	766.5	768.4	769.4
130°	781.6	784.2	786.2	788.3	790.4	792.4	794.5	796.5	798.6	800.7	801.6
132.5°	813.6	815.9	817.9	820.0	822.0	824.1	825.9	827.6	829.4	831.2	831.9
135°	859.1	861.5	863.2	864.8	866.6	868.2	870.1	872.0	873.9	875.7	876.5
137.5°	899.8	901.8	903.8	905.7	907.6	909.5	911.3	913.1	915.0	916.8	917.4
140°	926.5	928.2	930.3	932.3	934.4	936.4	938.1	939.8	941.5	943.2	943.6
142.5°	950.1	952.0	954.3	956.6	959.0	961.4	962.9	964.4	966.0	967.5	967.8
145°	982.0	983.5	986.7	989.8	993.1	996.2	997.5	998.9	1000.1	1001.5	1001.6
147.5°	1013.1	1014.3	1017.5	1020.6	1023.7	1026.9	1027.9	1028.8	1029.8	1030.8	1030.9
150°	1032.3	1033.1	1036.1	1039.1	1042.1	1045.0	1046.2	1047.3	1048.5	1049.6	1049.6
152.5°	1049.9	1050.5	1053.4	1056.2	1059.1	1061.9	1063.0	1064.1	1065.3	1066.4	1066.4
155°	1075.4	1075.7	1077.9	1080.1	1082.4	1084.7	1085.8	1086.9	1088.1	1089.2	1088.9
157.5°	1097.2	1097.3	1098.8	1100.3	1101.9	1103.5	1104.8	1106.0	1107.3	1108.6	1108.5
160°	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0	1116.1	1117.2	1118.3	1119.4	1119.4
162.5°	1121.3	1121.2	1122.1	1123.2	1124.1	1125.1	1126.3	1127.6	1128.9	1130.2	1130.0
165°	1135.8	1135.4	1136.0	1136.6	1137.2	1137.7	1139.0	1140.3	1141.6	1143.0	1143.0
167.5°	1146.5	1146.2	1146.8	1147.2	1147.8	1148.3	1149.6	1151.0	1152.2	1153.6	1153.3
170°	1152.6	1152.2	1152.6	1152.9	1153.3	1153.7	1155.0	1156.3	1157.6	1159.0	1158.7
172.5°	1156.7	1156.3	1156.7	1157.0	1157.4	1157.8	1159.0	1160.4	1161.7	1163.0	1162.8
175°	1161.1	1160.6	1161.0	1161.4	1161.7	1162.1	1163.5	1164.7	1166.1	1167.4	1167.1
177.5°	1163.0	1162.5	1162.7	1162.8	1163.0	1163.2	1164.2	1165.2	1166.3	1167.4	1167.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	738.3	737.8	737.8	735.7	737.8	737.8	738.3	740.7	741.4	741.9	740.9
5°	684.9	684.0	682.5	684.0	682.5	684.0	684.9	689.0	691.1	693.2	695.0
7.5°	632.1	628.5	628.0	624.5	628.0	628.5	632.1	634.0	638.1	642.8	647.1
10°	593.5	591.1	590.8	585.2	590.8	591.1	593.5	598.5	602.6	608.2	614.2
12.5°	564.1	558.4	559.6	556.3	559.6	558.4	564.1	564.2	569.0	572.5	581.8
15°	513.3	513.3	512.1	507.1	512.1	513.3	513.3	521.3	522.8	528.4	536.4
17.5°	476.8	476.2	473.3	474.8	473.3	476.2	476.8	482.7	483.6	491.2	497.7
20°	455.0	453.2	449.7	449.7	449.7	453.2	455.0	458.3	462.1	466.5	472.1
22.5°	434.4	434.3	430.6	431.7	430.6	434.3	434.4	437.4	441.1	446.0	450.7
25°	410.4	408.0	406.2	407.1	406.2	408.0	410.4	410.7	414.8	418.0	421.0
27.5°	387.5	386.2	386.1	383.7	386.1	386.2	387.5	388.2	390.6	392.5	395.3
30°	374.2	371.3	371.9	370.4	371.9	371.3	374.2	374.5	375.7	376.9	380.2
32.5°	359.1	358.1	357.4	356.2	357.4	358.1	359.1	359.7	362.0	363.2	365.8
35°	338.4	338.7	337.2	337.9	337.2	338.7	338.4	339.1	339.4	340.6	342.9
37.5°	320.4	321.4	320.7	320.8	320.7	321.4	320.4	320.7	321.0	321.2	321.9
40°	308.6	308.6	308.6	309.4	308.6	308.6	308.6	307.7	308.0	307.7	307.7
42.5°	297.2	296.8	296.3	296.2	296.3	296.8	297.2	295.2	296.1	295.2	294.7
45°	277.8	278.7	279.0	277.5	279.0	278.7	277.8	277.2	276.3	276.0	275.8
47.5°	260.2	260.3	260.2	261.5	260.2	260.3	260.2	259.4	258.1	257.5	256.1
50°	248.0	247.3	248.0	247.3	248.0	247.3	248.0	246.4	245.6	244.1	242.9
52.5°	234.9	235.0	234.6	234.6	234.6	235.0	234.9	233.0	232.5	232.0	230.1
55°	214.5	215.1	214.8	214.8	214.8	215.1	214.5	213.3	213.0	211.2	209.5
57.5°	193.4	193.9	194.3	193.0	194.3	193.9	193.4	193.2	193.0	191.2	189.3
60°	178.7	180.1	179.9	179.3	179.9	180.1	178.7	179.0	178.1	176.9	175.7
62.5°	165.2	165.7	165.6	165.6	165.6	165.7	165.2	163.8	163.4	162.2	161.1
65°	144.3	145.0	144.1	145.0	144.1	145.0	144.3	143.5	141.4	140.9	139.7
67.5°	121.9	122.2	122.8	123.2	122.8	122.2	121.9	122.3	121.0	119.9	119.6
70°	108.0	107.7	108.6	109.5	108.6	107.7	108.0	107.4	106.5	105.6	104.4
72.5°	93.3	94.0	93.6	94.3	93.6	94.0	93.3	93.4	92.5	91.4	90.2
75°	71.9	72.8	72.5	73.4	72.5	72.8	71.9	72.5	71.9	70.7	69.6
77.5°	52.0	52.0	52.0	52.4	52.0	52.0	52.0	52.4	51.8	52.2	50.9
80°	39.6	39.1	38.4	39.6	38.4	39.1	39.6	39.6	38.7	39.6	38.7
82.5°	27.6	28.0	27.3	27.3	27.3	28.0	27.6	28.3	27.9	28.3	27.4
85°	12.8	12.4	11.8	11.8	11.8	12.4	12.8	12.8	13.6	13.0	13.0
87.5°	6.7	6.5	6.6	6.4	6.6	6.5	6.7	6.7	6.5	6.7	6.6
90°	21.6	22.0	22.3	22.7	22.3	22.0	21.6	21.2	20.6	19.6	18.7
92.5°	22.1	22.3	22.5	22.7	22.5	22.3	22.1	21.9	21.5	21.0	20.5
95°	36.8	36.6	36.4	36.2	36.4	36.6	36.8	37.0	36.6	35.6	34.7
97.5°	47.7	47.9	48.1	48.3	48.1	47.9	47.7	47.5	47.0	46.2	45.5
100°	55.3	55.7	56.1	56.4	56.1	55.7	55.3	54.9	54.0	52.5	51.0
102.5°	58.9	59.4	60.0	60.4	60.0	59.4	58.9	58.4	57.1	55.2	53.2
105°	61.8	62.5	63.2	64.0	63.2	62.5	61.8	61.0	59.6	57.5	55.5
107.5°	63.6	64.3	65.1	65.8	65.1	64.3	63.6	62.9	63.5	65.6	67.7
110°	64.2	65.0	65.8	66.5	65.8	65.0	64.2	63.5	72.5	91.3	110.0



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	65.4	66.0	66.6	67.2	66.6	66.0	65.4	64.8	98.6	166.9	235.2
115°	109.5	96.0	82.5	69.1	82.5	96.0	109.5	122.9	173.0	259.7	346.3
117.5°	414.8	370.5	326.2	281.9	326.2	370.5	414.8	459.1	491.7	512.6	533.6
120°	589.5	564.2	538.9	513.7	538.9	564.2	589.5	614.7	626.3	624.0	621.8
122.5°	655.8	650.9	645.9	641.0	645.9	650.9	655.8	660.6	662.4	661.1	659.7
125°	718.4	718.9	719.5	720.0	719.5	718.9	718.4	717.8	716.8	715.5	714.2
127.5°	769.5	769.7	769.8	769.8	769.8	769.7	769.5	769.4	768.4	766.5	764.6
130°	801.5	801.2	801.1	800.9	801.1	801.2	801.5	801.6	800.7	798.6	796.5
132.5°	831.7	831.6	831.4	831.2	831.4	831.6	831.7	831.9	831.2	829.4	827.6
135°	876.1	875.7	875.4	875.0	875.4	875.7	876.1	876.5	875.7	873.9	872.0
137.5°	916.8	916.2	915.5	914.9	915.5	916.2	916.8	917.4	916.8	915.0	913.1
140°	942.6	941.7	940.7	939.8	940.7	941.7	942.6	943.6	943.2	941.5	939.8
142.5°	966.9	965.9	965.0	964.1	965.0	965.9	966.9	967.8	967.5	966.0	964.4
145°	1000.8	999.8	998.9	997.9	998.9	999.8	1000.8	1001.6	1001.5	1000.1	998.9
147.5°	1030.1	1029.3	1028.5	1027.7	1028.5	1029.3	1030.1	1030.9	1030.8	1029.8	1028.8
150°	1048.7	1047.8	1046.9	1045.9	1046.9	1047.8	1048.7	1049.6	1049.6	1048.5	1047.3
152.5°	1065.1	1063.9	1062.6	1061.4	1062.6	1063.9	1065.1	1066.4	1066.4	1065.3	1064.1
155°	1087.4	1086.0	1084.5	1083.0	1084.5	1086.0	1087.4	1088.9	1089.2	1088.1	1086.9
157.5°	1107.1	1105.6	1104.1	1102.6	1104.1	1105.6	1107.1	1108.5	1108.6	1107.3	1106.0
160°	1118.1	1116.7	1115.5	1114.1	1115.5	1116.7	1118.1	1119.4	1119.4	1118.3	1117.2
162.5°	1128.4	1126.8	1125.1	1123.6	1125.1	1126.8	1128.4	1130.0	1130.2	1128.9	1127.6
165°	1141.6	1140.3	1139.0	1137.7	1139.0	1140.3	1141.6	1143.0	1143.0	1141.6	1140.3
167.5°	1151.7	1150.0	1148.3	1146.6	1148.3	1150.0	1151.7	1153.3	1153.6	1152.2	1151.0
170°	1157.1	1155.4	1153.7	1152.0	1153.7	1155.4	1157.1	1158.7	1159.0	1157.6	1156.3
172.5°	1161.1	1159.4	1157.8	1156.0	1157.8	1159.4	1161.1	1162.8	1163.0	1161.7	1160.4
175°	1165.2	1163.3	1161.5	1159.6	1161.5	1163.3	1165.2	1167.1	1167.4	1166.1	1164.7
177.5°	1165.9	1164.5	1163.2	1161.8	1163.2	1164.5	1165.9	1167.2	1167.4	1166.3	1165.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	739.7	742.4	746.4	750.6	753.2	758.2	759.6	762.0	764.1	769.1	774.3
5°	697.0	701.2	710.9	716.2	723.7	732.2	737.8	743.8	750.3	761.5	771.9
7.5°	651.3	658.1	670.3	680.2	690.8	703.1	711.9	723.7	733.3	749.2	764.4
10°	620.7	630.4	641.4	653.2	668.0	681.0	693.5	708.3	720.1	739.0	756.8
12.5°	593.3	594.7	610.4	623.4	643.6	659.7	674.1	693.1	704.7	727.2	745.9
15°	545.3	554.1	568.3	578.7	602.6	623.1	643.2	663.0	676.3	704.1	728.6
17.5°	504.9	513.0	527.6	544.5	561.7	582.0	608.1	629.0	647.1	678.8	707.9
20°	479.3	489.3	504.1	521.6	536.7	558.9	581.3	605.3	624.8	660.6	694.7
22.5°	457.5	465.4	477.4	494.6	511.1	531.4	556.0	582.1	602.6	641.2	675.7
25°	426.9	433.4	441.1	455.3	474.0	496.1	515.4	544.1	573.9	610.1	651.7
27.5°	399.3	403.9	410.7	423.3	437.7	458.4	479.8	507.0	537.1	576.2	620.3
30°	382.5	385.5	392.3	402.7	416.8	433.1	454.7	480.8	511.5	551.2	594.9
32.5°	367.9	370.6	375.0	384.9	397.2	411.1	430.6	456.6	485.9	524.9	573.4
35°	345.9	347.9	351.7	359.7	366.5	380.2	396.4	420.1	447.6	484.9	535.2
37.5°	323.9	326.7	329.1	332.5	341.2	350.1	364.3	384.3	411.3	448.9	496.9
40°	309.4	311.8	315.4	316.9	323.9	331.9	343.5	361.8	389.0	423.3	470.1
42.5°	294.8	297.1	299.3	301.0	307.1	314.2	324.6	340.3	364.4	397.8	444.1
45°	274.8	275.1	277.2	280.4	283.4	288.4	295.9	309.4	328.1	359.5	401.5
47.5°	254.6	254.9	255.3	256.7	260.0	264.5	269.4	280.5	297.2	322.3	363.1
50°	241.1	240.5	241.1	242.3	244.4	248.2	253.8	261.8	275.4	298.8	336.4
52.5°	228.1	228.0	227.6	228.1	229.7	232.3	236.3	243.1	255.3	276.8	309.9
55°	208.3	206.8	207.1	205.9	208.6	209.1	212.1	217.8	228.4	243.2	274.3
57.5°	187.1	185.9	184.6	184.3	184.0	185.6	188.0	192.4	200.6	213.6	238.8
60°	173.6	172.2	170.4	169.8	169.8	170.7	171.9	175.2	182.8	194.4	215.1
62.5°	159.9	158.2	157.2	155.6	155.1	156.1	157.2	159.5	165.1	175.9	193.8
65°	138.8	136.7	135.2	134.9	134.4	133.4	134.0	136.4	140.9	149.4	163.6
67.5°	117.5	115.6	115.2	113.5	112.6	112.8	112.6	114.7	117.3	124.7	135.3
70°	103.5	102.0	101.5	100.0	99.4	98.8	98.2	100.0	102.7	108.8	118.0
72.5°	89.4	88.1	86.8	85.6	85.7	85.1	85.0	86.0	88.2	94.0	101.0
75°	68.9	69.2	67.7	66.3	66.0	65.4	65.4	66.3	67.2	71.6	77.2
77.5°	50.0	49.7	48.5	48.0	47.8	47.1	47.8	48.3	48.8	51.8	55.9
80°	38.2	38.2	36.7	36.7	36.4	35.5	36.4	35.8	37.0	39.9	42.9
82.5°	27.3	26.8	26.8	26.3	26.2	25.6	26.0	26.5	27.0	29.1	30.8
85°	13.3	13.3	13.0	12.8	13.0	12.8	13.0	13.3	13.6	14.5	16.0
87.5°	6.4	6.4	6.4	6.3	6.0	5.9	5.9	5.6	5.7	5.5	5.4
90°	17.7	16.9	15.4	13.9	12.4	10.9	9.1	7.1	5.0	2.9	0.9
92.5°	20.0	19.6	18.8	18.1	17.3	16.6	16.2	16.5	16.6	16.8	17.0
95°	33.7	32.9	31.5	30.3	28.9	27.6	30.0	36.2	42.4	48.6	54.7
97.5°	44.7	44.0	41.0	37.9	34.9	31.8	39.1	56.4	73.8	91.3	108.6
100°	49.5	48.0	44.8	41.7	38.4	35.3	46.5	72.2	97.8	123.4	149.1
102.5°	51.3	49.4	76.0	102.6	129.2	155.8	171.8	177.2	182.7	188.1	193.5
105°	53.4	51.3	102.4	153.5	204.6	255.7	278.5	272.8	267.2	261.7	256.0
107.5°	69.8	71.9	133.2	194.5	255.7	317.0	345.4	340.8	336.3	331.8	327.3
110°	128.7	147.3	201.5	255.6	309.6	363.7	388.8	384.8	381.0	377.0	373.0



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	303.5	371.7	385.1	398.5	411.8	425.2	430.1	426.6	423.1	419.7	416.2
115°	432.9	519.6	514.9	510.2	505.6	500.9	496.9	493.8	490.6	487.4	484.3
117.5°	554.5	575.5	572.3	569.1	565.9	562.6	559.3	555.7	552.2	548.6	545.0
120°	619.5	617.3	613.9	610.5	607.2	603.8	600.7	597.9	595.1	592.3	589.5
122.5°	658.4	657.0	653.4	649.7	646.0	642.4	639.1	636.1	633.1	630.2	627.2
125°	712.9	711.6	708.1	704.5	700.9	697.4	694.3	692.0	689.5	687.1	684.7
127.5°	762.7	760.8	758.1	755.4	752.8	750.1	747.5	744.8	742.1	739.4	736.7
130°	794.5	792.4	790.4	788.3	786.2	784.2	781.6	778.7	775.7	772.7	769.7
132.5°	825.9	824.1	822.0	820.0	817.9	815.9	813.6	811.0	808.5	806.0	803.4
135°	870.1	868.2	866.6	864.8	863.2	861.5	859.1	856.2	853.2	850.2	847.2
137.5°	911.3	909.5	907.6	905.7	903.8	901.8	899.8	897.8	895.6	893.6	891.4
140°	938.1	936.4	934.4	932.3	930.3	928.2	926.5	925.0	923.4	921.9	920.4
142.5°	962.9	961.4	959.0	956.6	954.3	952.0	950.1	948.7	947.4	946.0	944.7
145°	997.5	996.2	993.1	989.8	986.7	983.5	982.0	982.2	982.4	982.5	982.8
147.5°	1027.9	1026.9	1023.7	1020.6	1017.5	1014.3	1013.1	1013.8	1014.5	1015.3	1016.0
150°	1046.2	1045.0	1042.1	1039.1	1036.1	1033.1	1032.3	1033.6	1034.9	1036.2	1037.5
152.5°	1063.0	1061.9	1059.1	1056.2	1053.4	1050.5	1049.9	1051.3	1052.7	1054.2	1055.7
155°	1085.8	1084.7	1082.4	1080.1	1077.9	1075.7	1075.4	1077.1	1078.8	1080.5	1082.1
157.5°	1104.8	1103.5	1101.9	1100.3	1098.8	1097.3	1097.2	1098.6	1100.0	1101.5	1102.9
160°	1116.1	1115.0	1113.9	1112.7	1111.6	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0
162.5°	1126.3	1125.1	1124.1	1123.2	1122.1	1121.2	1121.3	1122.4	1123.5	1124.7	1125.8
165°	1139.0	1137.7	1137.2	1136.6	1136.0	1135.4	1135.8	1136.9	1138.0	1139.1	1140.3
167.5°	1149.6	1148.3	1147.8	1147.2	1146.8	1146.2	1146.5	1147.6	1148.7	1149.9	1151.0
170°	1155.0	1153.7	1153.3	1152.9	1152.6	1152.2	1152.6	1153.7	1154.8	1156.0	1157.1
172.5°	1159.0	1157.8	1157.4	1157.0	1156.7	1156.3	1156.7	1157.8	1158.9	1160.0	1161.1
175°	1163.5	1162.1	1161.7	1161.4	1161.0	1160.6	1161.1	1162.4	1163.7	1165.1	1166.3
177.5°	1164.2	1163.2	1163.0	1162.8	1162.7	1162.5	1163.0	1164.0	1165.1	1166.2	1167.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	773.8	775.0	778.8	782.6	786.8	788.0	789.9	788.2	787.7	792.3	795.6
5°	776.0	781.3	791.7	801.1	809.1	814.8	820.7	823.1	827.5	833.7	841.4
7.5°	773.5	783.9	800.2	814.0	828.9	839.8	848.3	855.5	864.2	876.0	888.8
10°	770.7	784.6	804.4	821.3	839.6	853.5	865.1	876.3	889.3	905.6	922.4
12.5°	765.5	782.0	806.8	826.7	850.2	864.0	879.5	903.7	917.7	940.4	964.1
15°	755.0	773.3	807.9	832.5	859.1	885.2	913.9	936.9	960.0	973.4	1006.8
17.5°	739.4	766.4	804.7	833.4	867.2	908.2	940.4	966.6	993.2	1014.8	1031.6
20°	726.9	756.2	799.9	834.3	874.5	918.6	955.6	982.2	1005.3	1023.3	1033.7
22.5°	711.1	747.9	790.5	830.8	882.1	925.7	964.6	985.6	1004.8	1013.6	1017.6
25°	686.0	730.5	778.6	827.8	885.7	931.9	967.4	980.2	985.8	977.2	963.0
27.5°	659.2	708.6	765.0	822.2	883.5	927.9	953.3	951.3	941.8	914.0	891.8
30°	639.1	693.5	754.1	816.5	878.1	921.2	936.0	921.2	899.7	868.6	836.9
32.5°	618.0	674.3	742.5	808.5	868.2	906.1	909.3	883.8	850.4	815.2	775.6
35°	586.1	647.1	720.6	790.5	847.0	871.0	856.7	811.8	772.1	724.0	670.1
37.5°	550.0	617.3	691.2	764.1	815.4	821.7	786.4	739.0	683.1	626.5	563.1
40°	523.1	594.4	670.4	744.0	789.3	782.8	737.8	685.8	619.2	550.0	491.1
42.5°	498.9	570.2	647.7	719.9	756.2	738.3	685.8	621.9	550.3	485.1	431.3
45°	457.1	530.4	609.7	679.5	700.3	668.0	598.5	527.5	457.1	402.7	360.0
47.5°	416.5	489.0	567.5	628.9	636.3	592.9	516.9	443.9	383.3	339.0	309.0
50°	386.7	459.5	537.3	592.0	589.6	537.3	459.1	389.6	339.1	303.2	283.1
52.5°	359.9	428.6	503.4	553.2	540.7	483.5	409.0	347.3	305.7	277.7	259.4
55°	318.3	381.9	453.0	492.9	469.8	406.5	343.5	293.7	263.0	242.0	227.8
57.5°	277.0	336.7	397.4	422.1	396.6	338.1	285.6	249.5	226.4	210.8	201.6
60°	251.4	303.6	357.7	379.0	348.5	296.4	255.0	222.8	204.1	191.4	183.2
62.5°	225.9	272.5	323.6	335.2	307.3	263.3	226.6	199.8	184.5	173.2	165.4
65°	191.2	229.3	268.1	275.8	250.0	215.9	187.0	169.5	155.9	147.7	141.4
67.5°	156.8	187.4	214.8	221.0	198.5	174.9	153.9	138.8	129.5	122.6	117.4
70°	136.4	160.7	183.2	188.1	170.1	149.1	133.2	121.0	112.7	106.8	101.8
72.5°	114.9	135.1	153.8	157.2	142.4	126.4	113.3	103.7	96.4	92.6	87.8
75°	87.9	99.7	114.2	115.1	105.4	95.5	85.5	79.3	75.4	70.7	68.4
77.5°	62.0	71.3	79.6	81.2	75.4	68.8	63.1	58.2	55.0	52.8	50.6
80°	47.4	54.7	58.3	60.4	56.2	51.5	48.2	45.0	42.9	41.4	39.9
82.5°	33.8	38.4	41.7	43.3	41.0	38.3	34.9	33.1	31.5	30.3	29.8
85°	17.2	19.3	21.3	21.9	21.3	20.1	18.4	18.4	17.4	17.2	17.2
87.5°	6.5	7.8	8.2	9.4	9.3	9.6	9.9	9.9	10.0	10.0	9.9
90°	2.9	5.0	7.1	9.1	10.9	12.4	13.9	15.4	16.9	17.7	18.7
92.5°	16.8	16.6	16.5	16.2	16.6	17.3	18.1	18.8	19.6	20.0	20.5
95°	48.6	42.4	36.2	30.0	27.6	28.9	30.3	31.5	32.9	33.7	34.7
97.5°	91.3	73.8	56.4	39.1	31.8	34.9	37.9	41.0	44.0	44.7	45.5
100°	123.4	97.8	72.2	46.5	35.3	38.4	41.7	44.8	48.0	49.5	51.0
102.5°	188.1	182.7	177.2	171.8	155.8	129.2	102.6	76.0	49.4	51.3	53.2
105°	261.7	267.2	272.8	278.5	255.7	204.6	153.5	102.4	51.3	53.4	55.5
107.5°	331.8	336.3	340.8	345.4	317.0	255.7	194.5	133.2	71.9	69.8	67.7
110°	377.0	381.0	384.8	388.8	363.7	309.6	255.6	201.5	147.3	128.7	110.0



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	419.7	423.1	426.6	430.1	425.2	411.8	398.5	385.1	371.7	303.5	235.2
115°	487.4	490.6	493.8	496.9	500.9	505.6	510.2	514.9	519.6	432.9	346.3
117.5°	548.6	552.2	555.7	559.3	562.6	565.9	569.1	572.3	575.5	554.5	533.6
120°	592.3	595.1	597.9	600.7	603.8	607.2	610.5	613.9	617.3	619.5	621.8
122.5°	630.2	633.1	636.1	639.1	642.4	646.0	649.7	653.4	657.0	658.4	659.7
125°	687.1	689.5	692.0	694.3	697.4	700.9	704.5	708.1	711.6	712.9	714.2
127.5°	739.4	742.1	744.8	747.5	750.1	752.8	755.4	758.1	760.8	762.7	764.6
130°	772.7	775.7	778.7	781.6	784.2	786.2	788.3	790.4	792.4	794.5	796.5
132.5°	806.0	808.5	811.0	813.6	815.9	817.9	820.0	822.0	824.1	825.9	827.6
135°	850.2	853.2	856.2	859.1	861.5	863.2	864.8	866.6	868.2	870.1	872.0
137.5°	893.6	895.6	897.8	899.8	901.8	903.8	905.7	907.6	909.5	911.3	913.1
140°	921.9	923.4	925.0	926.5	928.2	930.3	932.3	934.4	936.4	938.1	939.8
142.5°	946.0	947.4	948.7	950.1	952.0	954.3	956.6	959.0	961.4	962.9	964.4
145°	982.5	982.4	982.2	982.0	983.5	986.7	989.8	993.1	996.2	997.5	998.9
147.5°	1015.3	1014.5	1013.8	1013.1	1014.3	1017.5	1020.6	1023.7	1026.9	1027.9	1028.8
150°	1036.2	1034.9	1033.6	1032.3	1033.1	1036.1	1039.1	1042.1	1045.0	1046.2	1047.3
152.5°	1054.2	1052.7	1051.3	1049.9	1050.5	1053.4	1056.2	1059.1	1061.9	1063.0	1064.1
155°	1080.5	1078.8	1077.1	1075.4	1075.7	1077.9	1080.1	1082.4	1084.7	1085.8	1086.9
157.5°	1101.5	1100.0	1098.6	1097.2	1097.3	1098.8	1100.3	1101.9	1103.5	1104.8	1106.0
160°	1113.9	1112.7	1111.6	1110.5	1110.5	1111.6	1112.7	1113.9	1115.0	1116.1	1117.2
162.5°	1124.7	1123.5	1122.4	1121.3	1121.2	1122.1	1123.2	1124.1	1125.1	1126.3	1127.6
165°	1139.1	1138.0	1136.9	1135.8	1135.4	1136.0	1136.6	1137.2	1137.7	1139.0	1140.3
167.5°	1149.9	1148.7	1147.6	1146.5	1146.2	1146.8	1147.2	1147.8	1148.3	1149.6	1151.0
170°	1156.0	1154.8	1153.7	1152.6	1152.2	1152.6	1152.9	1153.3	1153.7	1155.0	1156.3
172.5°	1160.0	1158.9	1157.8	1156.7	1156.3	1156.7	1157.0	1157.4	1157.8	1159.0	1160.4
175°	1165.1	1163.7	1162.4	1161.1	1160.6	1161.0	1161.4	1161.7	1162.1	1163.5	1164.7
177.5°	1166.2	1165.1	1164.0	1163.0	1162.5	1162.7	1162.8	1163.0	1163.2	1164.2	1165.2
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	769.8	769.8	769.8	769.8	769.8	769.8	769.8
2.5°	798.4	801.8	801.8	802.2	806.0	805.6	805.3
5°	849.7	854.7	855.3	860.6	864.2	863.0	859.8
7.5°	898.0	907.4	914.5	918.5	923.1	926.0	924.7
10°	936.4	950.0	958.2	963.8	970.7	975.7	973.9
12.5°	971.1	987.4	998.7	1008.4	1009.2	1015.7	1011.3
15°	1025.4	1042.6	1044.3	1051.5	1057.1	1056.5	1056.8
17.5°	1043.3	1048.8	1050.0	1050.1	1050.2	1048.1	1043.6
20°	1037.0	1034.9	1029.8	1026.0	1019.2	1018.3	1012.4
22.5°	1006.6	1000.1	987.5	979.1	968.5	965.7	964.1
25°	947.0	932.5	912.4	893.2	887.8	877.5	880.4
27.5°	865.1	842.6	820.8	805.2	791.1	775.5	780.0
30°	807.6	782.2	751.5	727.8	712.7	697.9	695.2
32.5°	739.0	701.7	667.4	646.6	623.4	614.1	603.9
35°	620.7	584.3	550.2	521.0	504.1	491.1	479.3
37.5°	514.2	472.4	444.9	421.2	409.0	401.6	403.4
40°	448.2	411.5	391.4	373.4	362.1	356.8	358.0
42.5°	394.7	367.3	350.7	338.3	330.4	327.4	326.7
45°	334.0	318.6	305.0	297.9	294.1	290.8	288.8
47.5°	292.6	280.0	272.4	268.2	264.7	261.5	261.4
50°	267.8	259.4	254.1	249.7	247.0	244.6	246.8
52.5°	248.8	241.2	235.9	232.0	230.9	228.8	228.8
55°	220.7	214.8	211.0	207.4	205.7	204.5	203.0
57.5°	195.1	189.5	186.0	183.7	180.4	179.2	178.7
60°	176.9	172.5	168.9	166.0	164.5	162.2	162.2
62.5°	160.1	155.7	152.3	150.1	147.7	146.7	146.9
65°	135.8	132.2	129.0	126.6	126.0	124.3	124.8
67.5°	113.4	111.1	107.7	106.3	105.2	104.3	103.5
70°	98.5	96.2	94.3	92.6	91.7	91.7	91.7
72.5°	86.0	83.1	82.1	79.9	80.3	79.4	78.4
75°	66.5	64.8	63.9	63.0	61.6	61.6	61.6
77.5°	49.0	48.5	47.4	46.4	46.1	45.8	45.9
80°	37.9	37.5	37.0	37.0	36.4	36.1	35.5
82.5°	29.1	28.4	28.0	27.7	27.6	27.6	27.5
85°	16.6	16.0	16.0	16.2	15.7	15.7	16.0
87.5°	10.3	10.5	10.4	10.5	10.8	10.6	10.7
90°	19.6	20.6	21.2	21.6	22.0	22.3	22.7
92.5°	21.0	21.5	21.9	22.1	22.3	22.5	22.7
95°	35.6	36.6	37.0	36.8	36.6	36.4	36.2
97.5°	46.2	47.0	47.5	47.7	47.9	48.1	48.3
100°	52.5	54.0	54.9	55.3	55.7	56.1	56.4
102.5°	55.2	57.1	58.4	58.9	59.4	60.0	60.4
105°	57.5	59.6	61.0	61.8	62.5	63.2	64.0
107.5°	65.6	63.5	62.9	63.6	64.3	65.1	65.8
110°	91.3	72.5	63.5	64.2	65.0	65.8	66.5



TEST NUMBER: P331321-927

CATALOG NUMBER: S122DIP-S485D1080U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	166.9	98.6	64.8	65.4	66.0	66.6	67.2
115°	259.7	173.0	122.9	109.5	96.0	82.5	69.1
117.5°	512.6	491.7	459.1	414.8	370.5	326.2	281.9
120°	624.0	626.3	614.7	589.5	564.2	538.9	513.7
122.5°	661.1	662.4	660.6	655.8	650.9	645.9	641.0
125°	715.5	716.8	717.8	718.4	718.9	719.5	720.0
127.5°	766.5	768.4	769.4	769.5	769.7	769.8	769.8
130°	798.6	800.7	801.6	801.5	801.2	801.1	800.9
132.5°	829.4	831.2	831.9	831.7	831.6	831.4	831.2
135°	873.9	875.7	876.5	876.1	875.7	875.4	875.0
137.5°	915.0	916.8	917.4	916.8	916.2	915.5	914.9
140°	941.5	943.2	943.6	942.6	941.7	940.7	939.8
142.5°	966.0	967.5	967.8	966.9	965.9	965.0	964.1
145°	1000.1	1001.5	1001.6	1000.8	999.8	998.9	997.9
147.5°	1029.8	1030.8	1030.9	1030.1	1029.3	1028.5	1027.7
150°	1048.5	1049.6	1049.6	1048.7	1047.8	1046.9	1045.9
152.5°	1065.3	1066.4	1066.4	1065.1	1063.9	1062.6	1061.4
155°	1088.1	1089.2	1088.9	1087.4	1086.0	1084.5	1083.0
157.5°	1107.3	1108.6	1108.5	1107.1	1105.6	1104.1	1102.6
160°	1118.3	1119.4	1119.4	1118.1	1116.7	1115.5	1114.1
162.5°	1128.9	1130.2	1130.0	1128.4	1126.8	1125.1	1123.6
165°	1141.6	1143.0	1143.0	1141.6	1140.3	1139.0	1137.7
167.5°	1152.2	1153.6	1153.3	1151.7	1150.0	1148.3	1146.6
170°	1157.6	1159.0	1158.7	1157.1	1155.4	1153.7	1152.0
172.5°	1161.7	1163.0	1162.8	1161.1	1159.4	1157.8	1156.0
175°	1166.1	1167.4	1167.1	1165.2	1163.3	1161.5	1159.6
177.5°	1166.3	1167.4	1167.2	1165.9	1164.5	1163.2	1161.8
180°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8

(END OF REPORT)