

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331348-840

Luminaire Tested: **S122DIP-S675D725U840-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331348-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S675D725U840-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5887.5 lumens  
Efficiency: N/A  
Efficacy: 128.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	43
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37
3	82	73	66	61	76	68	62	57	58	53	50	49	46	43	40	38	36	32
4	76	65	57	52	70	61	54	49	52	47	43	44	40	37	36	34	31	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	32	33	30	28	25
6	64	52	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	44	37	33	38	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	22	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	20	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21658	21658	21658	21658
5°	24280	21797	19316	21797
10°	27824	21620	16718	21620
15°	30780	21224	14770	21224
20°	30311	20797	13464	20797
25°	27332	20232	12636	20232
30°	22585	19328	12033	19328
35°	16462	18382	11606	18382
40°	13148	17266	11367	17266
45°	11488	15972	11040	15972
50°	10798	14722	10826	14722
55°	9956	13453	10536	13453
60°	9122	12103	10091	12103
65°	8309	10892	9650	10892
70°	7544	9711	9007	9711
75°	6687	8390	7973	8390
80°	5755	6946	6425	6946
85°	5169	5169	3816	5169



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.7	2.2
10°-20°	371.4	6.3
20°-30°	539.0	9.2
30°-40°	568.8	9.7
40°-50°	503.6	8.6
50°-60°	401.9	6.8
60°-70°	273.2	4.6
70°-80°	140.0	2.4
80°-90°	36.2	0.6
90°-100°	33.3	0.6
100°-110°	122.1	2.1
110°-120°	326.4	5.5
120°-130°	538.9	9.2
130°-140°	573.1	9.7
140°-150°	532.7	9.0
150°-160°	428.3	7.3
160°-170°	276.0	4.7
170°-180°	95.0	1.6
0°-30°	1038.1	17.6
0°-40°	1606.9	27.3
0°-60°	2512.4	42.7
0°-90°	2961.8	50.3
90°-120°	481.9	8.2
90°-150°	2126.5	36.1
90°-180°	2926.0	49.7
0°-180°	5887.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1341	1341	1341	1341	1341	
5°	1498	1345	1192	1345	1498	150
15°	1841	1270	884	1270	1841	508
25°	1534	1136	709	1136	1534	693
35°	835	933	589	933	835	543
45°	503	700	484	700	503	396
55°	354	478	374	478	354	317
65°	218	285	253	285	218	216
75°	107	134	128	134	107	115
85°	28	28	21	28	28	31
90°	20	1	20	1	20	10
95°	31	47	31	47	31	29
105°	55	220	55	220	55	57
115°	59	415	59	415	59	148
125°	618	587	618	587	618	534
135°	750	727	750	727	750	578
145°	856	843	856	843	856	535
155°	929	928	929	928	929	429
165°	976	978	976	978	976	276
175°	995	1000	995	1000	995	95
180°	998	998	998	998	998	



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1403.2	1403.6	1404.5	1397.9	1397.0	1397.0	1391.3	1386.3	1380.6	1372.7	1373.5
5°	1498.1	1503.8	1505.8	1499.6	1490.4	1489.3	1480.6	1466.1	1452.7	1441.9	1434.2
7.5°	1611.3	1613.6	1608.5	1600.3	1593.5	1581.1	1564.8	1548.8	1526.4	1505.9	1490.7
10°	1697.1	1700.2	1691.4	1679.6	1669.8	1655.4	1631.6	1607.4	1578.0	1549.6	1526.9
12.5°	1762.2	1769.9	1758.7	1757.1	1740.3	1720.5	1692.2	1680.0	1638.6	1599.1	1574.8
15°	1841.4	1840.9	1842.0	1832.2	1819.8	1816.6	1786.8	1754.3	1696.1	1672.8	1632.6
17.5°	1818.6	1826.3	1830.0	1829.9	1829.6	1827.7	1818.1	1797.6	1768.4	1730.7	1684.3
20°	1764.1	1774.4	1775.9	1787.9	1794.5	1803.3	1806.9	1801.2	1783.2	1751.7	1711.5
22.5°	1680.0	1682.8	1687.7	1706.2	1720.7	1742.6	1754.1	1773.2	1766.3	1750.9	1717.3
25°	1534.2	1529.0	1547.1	1556.3	1589.8	1624.9	1650.2	1678.0	1702.7	1717.7	1707.9
27.5°	1359.1	1351.4	1378.4	1403.0	1430.3	1468.2	1507.6	1554.1	1592.8	1641.1	1657.7
30°	1211.4	1216.1	1241.9	1268.2	1309.4	1363.0	1407.3	1458.4	1513.6	1567.7	1605.3
32.5°	1052.3	1070.2	1086.4	1126.7	1163.0	1222.8	1287.8	1351.6	1420.4	1481.9	1540.1
35°	835.2	855.8	878.5	907.9	958.9	1018.1	1081.6	1167.6	1261.5	1345.5	1414.6
37.5°	703.0	699.6	712.7	733.9	775.3	823.0	896.1	981.2	1091.6	1190.3	1287.8
40°	623.8	621.7	631.0	650.6	682.1	717.1	781.0	855.8	958.4	1078.9	1195.0
42.5°	569.4	570.6	575.7	589.6	611.1	640.0	687.8	751.4	845.4	959.0	1083.6
45°	503.1	506.8	512.4	519.2	531.5	555.2	582.0	627.4	701.7	796.5	919.2
47.5°	455.6	455.7	461.4	467.3	474.6	488.0	509.9	538.3	590.7	667.9	773.4
50°	429.9	426.4	430.5	435.0	442.8	452.1	466.6	493.3	528.4	590.8	678.9
52.5°	398.6	398.7	402.4	404.1	411.1	420.3	433.5	452.1	483.8	532.6	605.1
55°	353.7	356.2	358.3	361.3	367.6	374.3	384.6	397.0	421.7	458.3	511.9
57.5°	311.3	312.1	314.3	320.1	324.1	330.2	340.0	351.2	367.4	394.5	434.7
60°	282.5	282.5	286.6	289.2	294.4	300.5	308.3	319.1	333.6	355.7	388.2
62.5°	256.1	255.7	257.3	261.6	265.5	271.2	279.0	288.2	301.7	321.4	348.2
65°	217.5	216.5	219.6	220.7	224.8	230.5	236.6	246.4	257.2	271.7	295.4
67.5°	180.5	181.7	183.3	185.3	187.5	193.5	197.6	204.6	213.7	225.7	241.8
70°	159.8	159.8	159.8	161.4	164.4	167.5	171.7	177.3	186.1	196.4	210.9
72.5°	136.7	138.4	140.0	139.1	143.0	144.8	149.8	153.0	161.4	167.9	180.8
75°	107.2	107.2	107.2	109.8	111.4	112.9	116.0	119.1	123.2	131.5	138.1
77.5°	80.0	79.8	80.3	80.9	82.6	84.4	85.3	88.2	92.0	95.7	101.5
80°	61.9	62.9	63.4	64.4	64.4	65.4	65.9	69.6	72.2	74.7	78.4
82.5°	47.9	48.1	48.2	48.4	48.8	49.4	50.7	51.9	52.8	54.9	57.8
85°	27.9	27.4	27.4	28.4	27.9	27.9	28.9	29.9	29.9	30.4	31.9
87.5°	14.6	14.5	14.9	14.4	14.3	14.6	14.5	13.9	14.1	14.4	14.6
90°	19.5	19.2	18.9	18.6	18.2	17.7	16.9	16.1	15.2	14.4	13.1
92.5°	19.5	19.3	19.1	18.9	18.8	18.4	18.0	17.6	17.2	16.8	16.2
95°	31.1	31.2	31.4	31.5	31.7	31.4	30.6	29.8	29.0	28.2	27.1
97.5°	41.5	41.3	41.1	40.9	40.7	40.3	39.6	39.0	38.4	37.7	35.1
100°	48.4	48.1	47.8	47.5	47.2	46.4	45.0	43.7	42.4	41.2	38.5
102.5°	51.9	51.4	51.0	50.5	50.1	49.0	47.4	45.6	44.0	42.3	38.5
105°	54.9	54.2	53.6	53.0	52.3	51.1	49.4	47.6	45.8	44.0	38.5
107.5°	56.5	55.8	55.2	54.5	53.9	54.5	56.2	58.1	59.9	61.7	114.2
110°	57.1	56.5	55.7	55.1	54.5	62.2	78.3	94.3	110.4	126.4	172.8



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.7	57.2	56.7	56.1	55.5	84.6	143.2	201.8	260.3	318.8	330.3
115°	59.3	70.8	82.3	93.9	105.4	148.5	222.8	297.1	371.4	445.8	441.7
117.5°	241.9	279.8	317.8	355.8	393.7	421.7	439.7	457.8	475.7	493.7	490.9
120°	440.7	462.3	484.0	505.6	527.4	537.2	535.3	533.4	531.4	529.5	526.6
122.5°	549.9	554.1	558.3	562.5	566.7	568.3	567.0	565.9	564.7	563.6	560.5
125°	617.6	617.1	616.7	616.2	615.7	614.9	613.8	612.7	611.6	610.5	607.3
127.5°	660.5	660.4	660.2	660.1	660.0	659.1	657.5	655.9	654.3	652.6	650.4
130°	687.0	687.1	687.3	687.5	687.6	686.8	685.1	683.3	681.6	679.7	678.0
132.5°	713.0	713.2	713.4	713.5	713.7	713.0	711.4	709.9	708.4	706.9	705.2
135°	750.5	750.8	751.2	751.5	751.8	751.2	749.6	748.0	746.4	744.8	743.4
137.5°	784.8	785.4	785.9	786.5	787.0	786.5	784.9	783.4	781.7	780.2	778.5
140°	806.2	807.0	807.8	808.6	809.4	809.1	807.6	806.2	804.8	803.3	801.5
142.5°	827.0	827.8	828.6	829.4	830.2	829.9	828.6	827.3	826.0	824.7	822.6
145°	856.1	856.9	857.7	858.5	859.2	859.1	858.0	856.9	855.8	854.5	851.8
147.5°	881.6	882.3	882.9	883.6	884.3	884.2	883.4	882.5	881.7	880.9	878.2
150°	897.2	898.0	898.8	899.6	900.4	900.3	899.4	898.4	897.5	896.5	893.9
152.5°	910.5	911.6	912.6	913.7	914.7	914.8	913.8	912.8	911.9	910.9	908.5
155°	929.0	930.3	931.6	932.8	934.1	934.3	933.3	932.4	931.4	930.4	928.5
157.5°	945.9	947.2	948.4	949.7	950.9	951.0	949.9	948.8	947.8	946.6	945.2
160°	955.7	956.8	958.0	959.1	960.2	960.3	959.4	958.4	957.5	956.4	955.4
162.5°	963.8	965.2	966.5	968.0	969.4	969.5	968.4	967.2	966.2	965.1	964.3
165°	975.9	977.0	978.2	979.4	980.5	980.5	979.4	978.2	977.0	975.9	975.4
167.5°	983.6	985.0	986.5	988.0	989.4	989.6	988.5	987.3	986.1	985.0	984.6
170°	988.3	989.7	991.1	992.6	994.0	994.2	993.0	991.9	990.8	989.7	989.4
172.5°	991.7	993.1	994.6	996.0	997.4	997.6	996.5	995.4	994.3	993.1	992.8
175°	994.7	996.3	997.9	999.6	1001.2	1001.4	1000.3	999.2	998.0	996.9	996.5
177.5°	996.6	997.7	999.0	1000.1	1001.3	1001.4	1000.5	999.6	998.7	997.7	997.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1376.4	1373.1	1371.1	1363.6	1357.1	1350.5	1348.4	1349.2	1340.2	1331.5	1327.8
5°	1430.1	1419.8	1410.0	1396.0	1379.6	1361.5	1352.2	1344.9	1327.0	1307.4	1296.1
7.5°	1478.1	1463.4	1444.5	1418.3	1394.3	1365.9	1347.9	1331.9	1305.5	1277.9	1260.9
10°	1507.4	1487.2	1463.0	1431.1	1401.7	1367.2	1342.9	1318.7	1287.8	1254.8	1234.2
12.5°	1532.6	1505.4	1481.6	1440.6	1405.8	1362.6	1333.8	1299.7	1267.2	1228.0	1207.8
15°	1592.5	1542.5	1497.0	1450.7	1407.9	1347.6	1315.7	1269.7	1226.9	1178.5	1155.3
17.5°	1638.7	1582.6	1511.1	1452.1	1402.2	1335.4	1288.5	1233.6	1183.0	1127.5	1096.0
20°	1665.2	1600.6	1523.9	1453.8	1393.9	1317.7	1266.7	1210.4	1151.1	1088.7	1054.7
22.5°	1680.8	1613.1	1537.1	1447.5	1377.5	1303.2	1239.0	1177.4	1117.3	1050.1	1014.3
25°	1685.8	1623.9	1543.5	1442.4	1356.9	1272.8	1195.5	1135.7	1063.0	1000.1	948.1
27.5°	1661.2	1616.9	1539.5	1432.7	1333.0	1234.8	1148.6	1080.9	1004.1	935.8	883.5
30°	1631.1	1605.3	1530.0	1422.8	1314.0	1208.4	1113.5	1036.7	960.4	891.3	837.7
32.5°	1584.5	1578.9	1512.8	1408.8	1293.8	1175.0	1076.8	999.2	914.6	846.8	795.7
35°	1493.0	1517.7	1475.9	1377.5	1255.8	1127.4	1021.3	932.6	845.0	780.0	732.1
37.5°	1370.3	1431.7	1420.8	1331.6	1204.5	1075.7	958.5	865.8	782.2	716.7	669.6
40°	1285.7	1364.0	1375.4	1296.6	1168.2	1035.7	911.4	819.2	737.7	677.9	630.5
42.5°	1195.0	1286.6	1317.7	1254.5	1128.5	993.6	869.4	773.8	693.2	635.0	593.0
45°	1042.9	1164.1	1220.2	1184.2	1062.5	924.3	796.5	699.5	626.3	571.7	539.3
47.5°	900.7	1033.1	1108.6	1095.9	989.0	852.1	725.8	632.8	561.5	517.9	488.8
50°	800.1	936.1	1027.4	1031.6	936.1	800.6	673.8	586.1	520.7	480.0	456.3
52.5°	712.7	842.5	942.1	963.9	877.2	747.0	627.2	540.0	482.3	444.8	423.6
55°	598.5	708.3	818.6	858.9	789.2	665.5	554.7	477.9	423.7	398.0	379.4
57.5°	497.6	589.2	691.1	735.5	692.6	586.6	482.7	416.1	372.1	349.5	335.3
60°	444.3	516.5	607.2	660.4	623.3	529.0	438.2	374.8	338.7	318.6	305.2
62.5°	394.9	458.8	535.5	584.1	563.9	474.9	393.6	337.7	306.5	287.6	278.0
65°	325.8	376.4	435.7	480.5	467.1	399.5	333.1	285.1	260.3	245.4	237.6
67.5°	268.3	304.8	345.9	385.2	374.4	326.5	273.2	235.8	217.3	204.5	199.9
70°	232.0	259.8	296.4	327.9	319.1	279.9	237.6	205.7	189.8	178.8	174.2
72.5°	197.3	220.3	248.1	273.9	267.9	235.4	200.2	176.0	163.7	153.7	149.9
75°	149.0	166.5	183.5	200.6	198.9	173.7	153.1	134.5	124.7	117.0	115.4
77.5°	110.0	119.8	131.4	141.5	138.7	124.2	108.1	97.5	90.2	85.0	84.2
80°	84.0	89.7	98.0	105.1	101.6	95.3	82.5	74.7	69.6	64.4	62.4
82.5°	60.9	66.7	71.6	75.4	72.7	67.0	59.0	53.7	50.6	47.2	46.3
85°	31.9	35.0	37.2	38.2	37.2	33.5	29.9	27.9	25.2	23.7	23.2
87.5°	14.7	14.4	14.2	14.7	13.1	12.8	10.8	9.2	9.2	9.1	8.6
90°	11.9	10.6	9.3	7.8	6.1	4.2	2.5	0.7	2.5	4.2	6.1
92.5°	15.5	14.8	14.2	13.9	14.1	14.2	14.4	14.5	14.4	14.2	14.1
95°	26.0	24.8	23.6	25.8	31.1	36.4	41.7	47.0	41.7	36.4	31.1
97.5°	32.5	29.9	27.3	33.4	48.4	63.3	78.3	93.2	78.3	63.3	48.4
100°	35.7	33.0	30.3	39.9	61.9	83.9	105.8	127.8	105.8	83.9	61.9
102.5°	88.0	110.8	133.6	147.3	152.1	156.7	161.4	166.0	161.4	156.7	152.1
105°	131.7	175.5	219.3	238.8	234.1	229.2	224.4	219.6	224.4	229.2	234.1
107.5°	166.8	219.3	272.0	296.3	292.4	288.5	284.6	280.7	284.6	288.5	292.4
110°	219.2	265.6	311.9	333.5	330.1	326.8	323.4	320.0	323.4	326.8	330.1





TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	341.7	353.3	364.7	368.9	366.0	362.9	360.0	357.0	360.0	362.9	366.0
115°	437.7	433.6	429.7	426.3	423.5	420.8	418.1	415.4	418.1	420.8	423.5
117.5°	488.2	485.4	482.6	479.7	476.7	473.6	470.6	467.6	470.6	473.6	476.7
120°	523.7	520.9	518.0	515.3	512.9	510.5	508.1	505.6	508.1	510.5	512.9
122.5°	557.3	554.2	551.0	548.2	545.6	543.1	540.6	538.1	540.6	543.1	545.6
125°	604.3	601.3	598.2	595.6	593.6	591.5	589.4	587.3	589.4	591.5	593.6
127.5°	648.0	645.8	643.5	641.2	638.8	636.6	634.3	632.0	634.3	636.6	638.8
130°	676.2	674.5	672.7	670.6	667.9	665.4	662.9	660.2	662.9	665.4	667.9
132.5°	703.4	701.7	699.8	697.9	695.7	693.6	691.4	689.1	691.4	693.6	695.7
135°	741.8	740.4	739.0	737.0	734.5	731.8	729.3	726.7	729.3	731.8	734.5
137.5°	776.9	775.3	773.7	771.9	770.1	768.3	766.5	764.8	766.5	768.3	770.1
140°	799.8	798.0	796.3	794.7	793.5	792.1	790.8	789.6	790.8	792.1	793.5
142.5°	820.6	818.6	816.6	815.0	813.9	812.7	811.5	810.4	811.5	812.7	813.9
145°	849.1	846.4	843.6	842.4	842.5	842.7	842.8	843.0	842.8	842.7	842.5
147.5°	875.5	872.8	870.1	869.1	869.7	870.3	870.9	871.5	870.9	870.3	869.7
150°	891.3	888.8	886.3	885.4	886.7	887.8	888.9	890.0	888.9	887.8	886.7
152.5°	906.1	903.6	901.2	900.6	901.8	903.1	904.3	905.5	904.3	903.1	901.8
155°	926.6	924.6	922.7	922.5	923.9	925.3	926.9	928.3	926.9	925.3	923.9
157.5°	943.9	942.6	941.2	941.2	942.4	943.6	944.8	946.0	944.8	943.6	942.4
160°	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4	955.4	954.5	953.5
162.5°	963.4	962.6	961.8	961.8	962.8	963.8	964.7	965.7	964.7	963.8	962.8
165°	975.0	974.5	974.0	974.2	975.2	976.2	977.1	978.2	977.1	976.2	975.2
167.5°	984.1	983.7	983.2	983.5	984.5	985.4	986.4	987.3	986.4	985.4	984.5
170°	989.1	988.8	988.4	988.8	989.7	990.7	991.6	992.6	991.6	990.7	989.7
172.5°	992.5	992.2	991.9	992.2	993.1	994.1	995.0	996.0	995.0	994.1	993.1
175°	996.2	995.9	995.6	996.0	997.1	998.3	999.4	1000.5	999.4	998.3	997.1
177.5°	997.5	997.3	997.2	997.6	998.6	999.5	1000.4	1001.3	1000.4	999.5	998.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1323.6	1321.2	1312.5	1308.0	1300.5	1293.5	1289.0	1291.1	1292.7	1291.9	1290.6
5°	1285.7	1275.9	1260.9	1248.1	1238.8	1221.7	1214.6	1210.9	1207.9	1204.3	1200.6
7.5°	1240.5	1225.1	1203.7	1185.3	1167.9	1146.8	1134.8	1127.5	1120.1	1112.0	1104.8
10°	1208.4	1186.7	1164.1	1138.2	1117.6	1098.5	1081.6	1070.3	1060.0	1050.2	1042.9
12.5°	1174.6	1149.6	1121.6	1086.3	1063.6	1036.3	1033.7	1013.7	997.6	991.6	983.1
15°	1120.7	1085.7	1050.2	1008.4	990.3	965.5	950.1	934.6	920.7	910.9	908.4
17.5°	1059.6	1014.2	978.9	948.9	919.3	893.9	879.7	867.3	855.9	842.7	841.0
20°	1013.0	973.8	935.1	908.9	878.5	852.6	835.2	822.7	812.9	805.3	798.5
22.5°	968.9	925.9	890.6	861.8	831.8	811.0	797.2	785.3	777.1	768.5	762.2
25°	898.1	864.5	825.9	793.3	768.6	755.3	743.9	733.6	728.4	722.8	715.6
27.5°	836.1	798.8	762.7	737.5	715.8	703.9	695.8	688.8	684.0	680.6	676.6
30°	792.3	754.7	726.4	701.7	683.6	671.8	666.6	662.5	656.8	654.7	652.7
32.5°	750.3	716.4	692.2	670.7	653.5	645.7	641.0	637.3	632.9	630.8	626.6
35°	690.7	662.5	638.7	626.8	613.0	606.2	602.7	597.4	593.4	591.3	590.8
37.5°	634.8	610.2	594.6	579.4	573.5	569.4	564.4	560.9	559.7	559.4	558.9
40°	598.5	578.5	564.5	552.1	549.6	543.3	539.3	536.1	536.1	536.6	536.1
42.5°	565.5	547.4	535.2	524.5	521.5	517.8	513.6	513.4	514.3	516.0	514.3
45°	515.5	502.6	493.8	488.7	483.0	479.4	478.9	480.5	481.0	481.5	483.0
47.5°	469.5	461.0	453.0	447.4	444.8	444.2	443.6	446.4	448.8	449.7	452.1
50°	442.3	432.5	425.9	422.2	420.1	419.1	420.1	423.2	425.3	427.9	429.4
52.5°	411.8	404.9	400.2	397.5	396.7	397.3	397.5	401.0	404.2	405.2	406.0
55°	369.6	364.5	363.5	358.8	360.8	360.3	362.9	365.0	368.1	371.1	371.7
57.5°	327.6	323.5	320.6	321.0	321.6	324.0	326.1	329.7	333.1	336.3	336.6
60°	299.5	297.4	295.9	295.9	296.9	300.0	302.7	306.2	308.3	310.3	311.8
62.5°	274.0	271.9	270.3	271.1	273.9	275.7	278.7	280.6	282.7	284.8	285.5
65°	233.5	232.5	234.1	235.1	235.6	238.1	241.8	243.3	245.4	246.4	250.0
67.5°	196.3	196.5	196.3	197.7	200.8	201.4	204.8	208.3	208.7	210.8	213.1
70°	171.2	172.2	173.2	174.2	176.8	177.8	180.5	182.0	184.0	185.6	187.1
72.5°	148.0	148.2	149.3	149.1	151.3	153.5	155.7	157.2	159.3	161.3	162.8
75°	113.9	113.9	114.9	115.4	118.1	120.7	120.1	121.2	123.2	125.2	126.3
77.5°	83.2	82.1	83.2	83.7	84.5	86.7	87.2	88.6	90.9	90.2	91.4
80°	63.4	61.9	63.4	63.9	63.9	66.6	66.6	67.6	69.1	67.6	69.1
82.5°	45.2	44.5	45.6	45.7	46.6	46.7	47.6	47.8	49.3	48.6	49.3
85°	22.7	22.2	22.7	22.2	22.7	23.2	23.2	22.7	22.7	23.7	22.2
87.5°	8.6	8.5	8.3	8.6	8.4	8.3	8.0	8.2	8.3	7.7	7.8
90°	7.8	9.3	10.6	11.9	13.1	14.4	15.2	16.1	16.9	17.7	18.2
92.5°	13.9	14.2	14.8	15.5	16.2	16.8	17.2	17.6	18.0	18.4	18.8
95°	25.8	23.6	24.8	26.0	27.1	28.2	29.0	29.8	30.6	31.4	31.7
97.5°	33.4	27.3	29.9	32.5	35.1	37.7	38.4	39.0	39.6	40.3	40.7
100°	39.9	30.3	33.0	35.7	38.5	41.2	42.4	43.7	45.0	46.4	47.2
102.5°	147.3	133.6	110.8	88.0	65.1	42.3	44.0	45.6	47.4	49.0	50.1
105°	238.8	219.3	175.5	131.7	87.9	44.0	45.8	47.6	49.4	51.1	52.3
107.5°	296.3	272.0	219.3	166.8	114.2	61.7	59.9	58.1	56.2	54.5	53.9
110°	333.5	311.9	265.6	219.2	172.8	126.4	110.4	94.3	78.3	62.2	54.5



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	368.9	364.7	353.3	341.7	330.3	318.8	260.3	201.8	143.2	84.6	55.5
115°	426.3	429.7	433.6	437.7	441.7	445.8	371.4	297.1	222.8	148.5	105.4
117.5°	479.7	482.6	485.4	488.2	490.9	493.7	475.7	457.8	439.7	421.7	393.7
120°	515.3	518.0	520.9	523.7	526.6	529.5	531.4	533.4	535.3	537.2	527.4
122.5°	548.2	551.0	554.2	557.3	560.5	563.6	564.7	565.9	567.0	568.3	566.7
125°	595.6	598.2	601.3	604.3	607.3	610.5	611.6	612.7	613.8	614.9	615.7
127.5°	641.2	643.5	645.8	648.0	650.4	652.6	654.3	655.9	657.5	659.1	660.0
130°	670.6	672.7	674.5	676.2	678.0	679.7	681.6	683.3	685.1	686.8	687.6
132.5°	697.9	699.8	701.7	703.4	705.2	706.9	708.4	709.9	711.4	713.0	713.7
135°	737.0	739.0	740.4	741.8	743.4	744.8	746.4	748.0	749.6	751.2	751.8
137.5°	771.9	773.7	775.3	776.9	778.5	780.2	781.7	783.4	784.9	786.5	787.0
140°	794.7	796.3	798.0	799.8	801.5	803.3	804.8	806.2	807.6	809.1	809.4
142.5°	815.0	816.6	818.6	820.6	822.6	824.7	826.0	827.3	828.6	829.9	830.2
145°	842.4	843.6	846.4	849.1	851.8	854.5	855.8	856.9	858.0	859.1	859.2
147.5°	869.1	870.1	872.8	875.5	878.2	880.9	881.7	882.5	883.4	884.2	884.3
150°	885.4	886.3	888.8	891.3	893.9	896.5	897.5	898.4	899.4	900.3	900.4
152.5°	900.6	901.2	903.6	906.1	908.5	910.9	911.9	912.8	913.8	914.8	914.7
155°	922.5	922.7	924.6	926.6	928.5	930.4	931.4	932.4	933.3	934.3	934.1
157.5°	941.2	941.2	942.6	943.9	945.2	946.6	947.8	948.8	949.9	951.0	950.9
160°	952.6	952.6	953.5	954.5	955.4	956.4	957.5	958.4	959.4	960.3	960.2
162.5°	961.8	961.8	962.6	963.4	964.3	965.1	966.2	967.2	968.4	969.5	969.4
165°	974.2	974.0	974.5	975.0	975.4	975.9	977.0	978.2	979.4	980.5	980.5
167.5°	983.5	983.2	983.7	984.1	984.6	985.0	986.1	987.3	988.5	989.6	989.4
170°	988.8	988.4	988.8	989.1	989.4	989.7	990.8	991.9	993.0	994.2	994.0
172.5°	992.2	991.9	992.2	992.5	992.8	993.1	994.3	995.4	996.5	997.6	997.4
175°	996.0	995.6	995.9	996.2	996.5	996.9	998.0	999.2	1000.3	1001.4	1001.2
177.5°	997.6	997.2	997.3	997.5	997.6	997.7	998.7	999.6	1000.5	1001.4	1001.3
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1286.6	1285.7	1285.7	1282.0	1285.7	1285.7	1286.6	1290.6	1291.9	1292.7	1291.1
5°	1193.5	1191.8	1189.3	1191.8	1189.3	1191.8	1193.5	1200.6	1204.3	1207.9	1210.9
7.5°	1101.4	1095.2	1094.3	1088.1	1094.3	1095.2	1101.4	1104.8	1112.0	1120.1	1127.5
10°	1034.1	1030.0	1029.5	1019.7	1029.5	1030.0	1034.1	1042.9	1050.2	1060.0	1070.3
12.5°	983.0	973.1	975.0	969.4	975.0	973.1	983.0	983.1	991.6	997.6	1013.7
15°	894.4	894.4	892.3	883.6	892.3	894.4	894.4	908.4	910.9	920.7	934.6
17.5°	830.8	829.8	824.9	827.3	824.9	829.8	830.8	841.0	842.7	855.9	867.3
20°	792.8	789.8	783.6	783.6	783.6	789.8	792.8	798.5	805.3	812.9	822.7
22.5°	757.0	756.8	750.2	752.2	750.2	756.8	757.0	762.2	768.5	777.1	785.3
25°	715.0	710.9	707.8	709.3	707.8	710.9	715.0	715.6	722.8	728.4	733.6
27.5°	675.2	673.0	672.8	668.5	672.8	673.0	675.2	676.6	680.6	684.0	688.8
30°	652.2	647.0	648.0	645.4	648.0	647.0	652.2	652.7	654.7	656.8	662.5
32.5°	625.7	623.9	622.9	620.7	622.9	623.9	625.7	626.6	630.8	632.9	637.3
35°	589.8	590.3	587.7	588.8	587.7	590.3	589.8	590.8	591.3	593.4	597.4
37.5°	558.4	560.0	558.8	559.1	558.8	560.0	558.4	558.9	559.4	559.7	560.9
40°	537.7	537.7	537.7	539.3	537.7	537.7	537.7	536.1	536.6	536.1	536.1
42.5°	517.9	517.1	516.2	516.1	516.2	517.1	517.9	514.3	516.0	514.3	513.4
45°	484.0	485.6	486.1	483.5	486.1	485.6	484.0	483.0	481.5	481.0	480.5
47.5°	453.4	453.6	453.4	455.8	453.4	453.6	453.4	452.1	449.7	448.8	446.4
50°	432.0	431.0	432.0	431.0	432.0	431.0	432.0	429.4	427.9	425.3	423.2
52.5°	409.3	409.5	408.9	408.7	408.9	409.5	409.3	406.0	405.2	404.2	401.0
55°	373.8	374.8	374.3	374.3	374.3	374.8	373.8	371.7	371.1	368.1	365.0
57.5°	337.0	337.9	338.6	336.3	338.6	337.9	337.0	336.6	336.3	333.1	329.7
60°	311.3	314.0	313.5	312.5	313.5	314.0	311.3	311.8	310.3	308.3	306.2
62.5°	287.9	288.8	288.7	288.5	288.7	288.8	287.9	285.5	284.8	282.7	280.6
65°	251.6	252.6	251.1	252.6	251.1	252.6	251.6	250.0	246.4	245.4	243.3
67.5°	212.5	212.8	214.0	214.7	214.0	212.8	212.5	213.1	210.8	208.7	208.3
70°	188.1	187.6	189.1	190.8	189.1	187.6	188.1	187.1	185.6	184.0	182.0
72.5°	162.6	163.7	163.2	164.3	163.2	163.7	162.6	162.8	161.3	159.3	157.2
75°	125.2	126.8	126.3	127.8	126.3	126.8	125.2	126.3	125.2	123.2	121.2
77.5°	90.5	90.7	90.5	91.4	90.5	90.7	90.5	91.4	90.2	90.9	88.6
80°	69.1	68.1	67.1	69.1	67.1	68.1	69.1	69.1	67.6	69.1	67.6
82.5°	48.1	48.7	47.7	47.7	47.7	48.7	48.1	49.3	48.6	49.3	47.8
85°	22.2	21.6	20.6	20.6	20.6	21.6	22.2	22.2	23.7	22.7	22.7
87.5°	7.9	7.5	7.6	7.2	7.6	7.5	7.9	7.8	7.7	8.3	8.2
90°	18.6	18.9	19.2	19.5	19.2	18.9	18.6	18.2	17.7	16.9	16.1
92.5°	18.9	19.1	19.3	19.5	19.3	19.1	18.9	18.8	18.4	18.0	17.6
95°	31.5	31.4	31.2	31.1	31.2	31.4	31.5	31.7	31.4	30.6	29.8
97.5°	40.9	41.1	41.3	41.5	41.3	41.1	40.9	40.7	40.3	39.6	39.0
100°	47.5	47.8	48.1	48.4	48.1	47.8	47.5	47.2	46.4	45.0	43.7
102.5°	50.5	51.0	51.4	51.9	51.4	51.0	50.5	50.1	49.0	47.4	45.6
105°	53.0	53.6	54.2	54.9	54.2	53.6	53.0	52.3	51.1	49.4	47.6
107.5°	54.5	55.2	55.8	56.5	55.8	55.2	54.5	53.9	54.5	56.2	58.1
110°	55.1	55.7	56.5	57.1	56.5	55.7	55.1	54.5	62.2	78.3	94.3



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	56.1	56.7	57.2	57.7	57.2	56.7	56.1	55.5	84.6	143.2	201.8
115°	93.9	82.3	70.8	59.3	70.8	82.3	93.9	105.4	148.5	222.8	297.1
117.5°	355.8	317.8	279.8	241.9	279.8	317.8	355.8	393.7	421.7	439.7	457.8
120°	505.6	484.0	462.3	440.7	462.3	484.0	505.6	527.4	537.2	535.3	533.4
122.5°	562.5	558.3	554.1	549.9	554.1	558.3	562.5	566.7	568.3	567.0	565.9
125°	616.2	616.7	617.1	617.6	617.1	616.7	616.2	615.7	614.9	613.8	612.7
127.5°	660.1	660.2	660.4	660.5	660.4	660.2	660.1	660.0	659.1	657.5	655.9
130°	687.5	687.3	687.1	687.0	687.1	687.3	687.5	687.6	686.8	685.1	683.3
132.5°	713.5	713.4	713.2	713.0	713.2	713.4	713.5	713.7	713.0	711.4	709.9
135°	751.5	751.2	750.8	750.5	750.8	751.2	751.5	751.8	751.2	749.6	748.0
137.5°	786.5	785.9	785.4	784.8	785.4	785.9	786.5	787.0	786.5	784.9	783.4
140°	808.6	807.8	807.0	806.2	807.0	807.8	808.6	809.4	809.1	807.6	806.2
142.5°	829.4	828.6	827.8	827.0	827.8	828.6	829.4	830.2	829.9	828.6	827.3
145°	858.5	857.7	856.9	856.1	856.9	857.7	858.5	859.2	859.1	858.0	856.9
147.5°	883.6	882.9	882.3	881.6	882.3	882.9	883.6	884.3	884.2	883.4	882.5
150°	899.6	898.8	898.0	897.2	898.0	898.8	899.6	900.4	900.3	899.4	898.4
152.5°	913.7	912.6	911.6	910.5	911.6	912.6	913.7	914.7	914.8	913.8	912.8
155°	932.8	931.6	930.3	929.0	930.3	931.6	932.8	934.1	934.3	933.3	932.4
157.5°	949.7	948.4	947.2	945.9	947.2	948.4	949.7	950.9	951.0	949.9	948.8
160°	959.1	958.0	956.8	955.7	956.8	958.0	959.1	960.2	960.3	959.4	958.4
162.5°	968.0	966.5	965.2	963.8	965.2	966.5	968.0	969.4	969.5	968.4	967.2
165°	979.4	978.2	977.0	975.9	977.0	978.2	979.4	980.5	980.5	979.4	978.2
167.5°	988.0	986.5	985.0	983.6	985.0	986.5	988.0	989.4	989.6	988.5	987.3
170°	992.6	991.1	989.7	988.3	989.7	991.1	992.6	994.0	994.2	993.0	991.9
172.5°	996.0	994.6	993.1	991.7	993.1	994.6	996.0	997.4	997.6	996.5	995.4
175°	999.6	997.9	996.3	994.7	996.3	997.9	999.6	1001.2	1001.4	1000.3	999.2
177.5°	1000.1	999.0	997.7	996.6	997.7	999.0	1000.1	1001.3	1001.4	1000.5	999.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1289.0	1293.5	1300.5	1308.0	1312.5	1321.2	1323.6	1327.8	1331.5	1340.2	1349.2
5°	1214.6	1221.7	1238.8	1248.1	1260.9	1275.9	1285.7	1296.1	1307.4	1327.0	1344.9
7.5°	1134.8	1146.8	1167.9	1185.3	1203.7	1225.1	1240.5	1260.9	1277.9	1305.5	1331.9
10°	1081.6	1098.5	1117.6	1138.2	1164.1	1186.7	1208.4	1234.2	1254.8	1287.8	1318.7
12.5°	1033.7	1036.3	1063.6	1086.3	1121.6	1149.6	1174.6	1207.8	1228.0	1267.2	1299.7
15°	950.1	965.5	990.3	1008.4	1050.2	1085.7	1120.7	1155.3	1178.5	1226.9	1269.7
17.5°	879.7	893.9	919.3	948.9	978.9	1014.2	1059.6	1096.0	1127.5	1183.0	1233.6
20°	835.2	852.6	878.5	908.9	935.1	973.8	1013.0	1054.7	1088.7	1151.1	1210.4
22.5°	797.2	811.0	831.8	861.8	890.6	925.9	968.9	1014.3	1050.1	1117.3	1177.4
25°	743.9	755.3	768.6	793.3	825.9	864.5	898.1	948.1	1000.1	1063.0	1135.7
27.5°	695.8	703.9	715.8	737.5	762.7	798.8	836.1	883.5	935.8	1004.1	1080.9
30°	666.6	671.8	683.6	701.7	726.4	754.7	792.3	837.7	891.3	960.4	1036.7
32.5°	641.0	645.7	653.5	670.7	692.2	716.4	750.3	795.7	846.8	914.6	999.2
35°	602.7	606.2	613.0	626.8	638.7	662.5	690.7	732.1	780.0	845.0	932.6
37.5°	564.4	569.4	573.5	579.4	594.6	610.2	634.8	669.6	716.7	782.2	865.8
40°	539.3	543.3	549.6	552.1	564.5	578.5	598.5	630.5	677.9	737.7	819.2
42.5°	513.6	517.8	521.5	524.5	535.2	547.4	565.5	593.0	635.0	693.2	773.8
45°	478.9	479.4	483.0	488.7	493.8	502.6	515.5	539.3	571.7	626.3	699.5
47.5°	443.6	444.2	444.8	447.4	453.0	461.0	469.5	488.8	517.9	561.5	632.8
50°	420.1	419.1	420.1	422.2	425.9	432.5	442.3	456.3	480.0	520.7	586.1
52.5°	397.5	397.3	396.7	397.5	400.2	404.9	411.8	423.6	444.8	482.3	540.0
55°	362.9	360.3	360.8	358.8	363.5	364.5	369.6	379.4	398.0	423.7	477.9
57.5°	326.1	324.0	321.6	321.0	320.6	323.5	327.6	335.3	349.5	372.1	416.1
60°	302.7	300.0	296.9	295.9	295.9	297.4	299.5	305.2	318.6	338.7	374.8
62.5°	278.7	275.7	273.9	271.1	270.3	271.9	274.0	278.0	287.6	306.5	337.7
65°	241.8	238.1	235.6	235.1	234.1	232.5	233.5	237.6	245.4	260.3	285.1
67.5°	204.8	201.4	200.8	197.7	196.3	196.5	196.3	199.9	204.5	217.3	235.8
70°	180.5	177.8	176.8	174.2	173.2	172.2	171.2	174.2	178.8	189.8	205.7
72.5°	155.7	153.5	151.3	149.1	149.3	148.2	148.0	149.9	153.7	163.7	176.0
75°	120.1	120.7	118.1	115.4	114.9	113.9	113.9	115.4	117.0	124.7	134.5
77.5°	87.2	86.7	84.5	83.7	83.2	82.1	83.2	84.2	85.0	90.2	97.5
80°	66.6	66.6	63.9	63.9	63.4	61.9	63.4	62.4	64.4	69.6	74.7
82.5°	47.6	46.7	46.6	45.7	45.6	44.5	45.2	46.3	47.2	50.6	53.7
85°	23.2	23.2	22.7	22.2	22.7	22.2	22.7	23.2	23.7	25.2	27.9
87.5°	8.0	8.3	8.4	8.6	8.3	8.5	8.6	8.6	9.1	9.2	9.2
90°	15.2	14.4	13.1	11.9	10.6	9.3	7.8	6.1	4.2	2.5	0.7
92.5°	17.2	16.8	16.2	15.5	14.8	14.2	13.9	14.1	14.2	14.4	14.5
95°	29.0	28.2	27.1	26.0	24.8	23.6	25.8	31.1	36.4	41.7	47.0
97.5°	38.4	37.7	35.1	32.5	29.9	27.3	33.4	48.4	63.3	78.3	93.2
100°	42.4	41.2	38.5	35.7	33.0	30.3	39.9	61.9	83.9	105.8	127.8
102.5°	44.0	42.3	65.1	88.0	110.8	133.6	147.3	152.1	156.7	161.4	166.0
105°	45.8	44.0	87.9	131.7	175.5	219.3	238.8	234.1	229.2	224.4	219.6
107.5°	59.9	61.7	114.2	166.8	219.3	272.0	296.3	292.4	288.5	284.6	280.7
110°	110.4	126.4	172.8	219.2	265.6	311.9	333.5	330.1	326.8	323.4	320.0



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.3	318.8	330.3	341.7	353.3	364.7	368.9	366.0	362.9	360.0	357.0
115°	371.4	445.8	441.7	437.7	433.6	429.7	426.3	423.5	420.8	418.1	415.4
117.5°	475.7	493.7	490.9	488.2	485.4	482.6	479.7	476.7	473.6	470.6	467.6
120°	531.4	529.5	526.6	523.7	520.9	518.0	515.3	512.9	510.5	508.1	505.6
122.5°	564.7	563.6	560.5	557.3	554.2	551.0	548.2	545.6	543.1	540.6	538.1
125°	611.6	610.5	607.3	604.3	601.3	598.2	595.6	593.6	591.5	589.4	587.3
127.5°	654.3	652.6	650.4	648.0	645.8	643.5	641.2	638.8	636.6	634.3	632.0
130°	681.6	679.7	678.0	676.2	674.5	672.7	670.6	667.9	665.4	662.9	660.2
132.5°	708.4	706.9	705.2	703.4	701.7	699.8	697.9	695.7	693.6	691.4	689.1
135°	746.4	744.8	743.4	741.8	740.4	739.0	737.0	734.5	731.8	729.3	726.7
137.5°	781.7	780.2	778.5	776.9	775.3	773.7	771.9	770.1	768.3	766.5	764.8
140°	804.8	803.3	801.5	799.8	798.0	796.3	794.7	793.5	792.1	790.8	789.6
142.5°	826.0	824.7	822.6	820.6	818.6	816.6	815.0	813.9	812.7	811.5	810.4
145°	855.8	854.5	851.8	849.1	846.4	843.6	842.4	842.5	842.7	842.8	843.0
147.5°	881.7	880.9	878.2	875.5	872.8	870.1	869.1	869.7	870.3	870.9	871.5
150°	897.5	896.5	893.9	891.3	888.8	886.3	885.4	886.7	887.8	888.9	890.0
152.5°	911.9	910.9	908.5	906.1	903.6	901.2	900.6	901.8	903.1	904.3	905.5
155°	931.4	930.4	928.5	926.6	924.6	922.7	922.5	923.9	925.3	926.9	928.3
157.5°	947.8	946.6	945.2	943.9	942.6	941.2	941.2	942.4	943.6	944.8	946.0
160°	957.5	956.4	955.4	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4
162.5°	966.2	965.1	964.3	963.4	962.6	961.8	961.8	962.8	963.8	964.7	965.7
165°	977.0	975.9	975.4	975.0	974.5	974.0	974.2	975.2	976.2	977.1	978.2
167.5°	986.1	985.0	984.6	984.1	983.7	983.2	983.5	984.5	985.4	986.4	987.3
170°	990.8	989.7	989.4	989.1	988.8	988.4	988.8	989.7	990.7	991.6	992.6
172.5°	994.3	993.1	992.8	992.5	992.2	991.9	992.2	993.1	994.1	995.0	996.0
175°	998.0	996.9	996.5	996.2	995.9	995.6	996.0	997.1	998.3	999.4	1000.5
177.5°	998.7	997.7	997.6	997.5	997.3	997.2	997.6	998.6	999.5	1000.4	1001.3
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1348.4	1350.5	1357.1	1363.6	1371.1	1373.1	1376.4	1373.5	1372.7	1380.6	1386.3
5°	1352.2	1361.5	1379.6	1396.0	1410.0	1419.8	1430.1	1434.2	1441.9	1452.7	1466.1
7.5°	1347.9	1365.9	1394.3	1418.3	1444.5	1463.4	1478.1	1490.7	1505.9	1526.4	1548.8
10°	1342.9	1367.2	1401.7	1431.1	1463.0	1487.2	1507.4	1526.9	1549.6	1578.0	1607.4
12.5°	1333.8	1362.6	1405.8	1440.6	1481.6	1505.4	1532.6	1574.8	1599.1	1638.6	1680.0
15°	1315.7	1347.6	1407.9	1450.7	1497.0	1542.5	1592.5	1632.6	1672.8	1696.1	1754.3
17.5°	1288.5	1335.4	1402.2	1452.1	1511.1	1582.6	1638.7	1684.3	1730.7	1768.4	1797.6
20°	1266.7	1317.7	1393.9	1453.8	1523.9	1600.6	1665.2	1711.5	1751.7	1783.2	1801.2
22.5°	1239.0	1303.2	1377.5	1447.5	1537.1	1613.1	1680.8	1717.3	1750.9	1766.3	1773.2
25°	1195.5	1272.8	1356.9	1442.4	1543.5	1623.9	1685.8	1707.9	1717.7	1702.7	1678.0
27.5°	1148.6	1234.8	1333.0	1432.7	1539.5	1616.9	1661.2	1657.7	1641.1	1592.8	1554.1
30°	1113.5	1208.4	1314.0	1422.8	1530.0	1605.3	1631.1	1605.3	1567.7	1513.6	1458.4
32.5°	1076.8	1175.0	1293.8	1408.8	1512.8	1578.9	1584.5	1540.1	1481.9	1420.4	1351.6
35°	1021.3	1127.4	1255.8	1377.5	1475.9	1517.7	1493.0	1414.6	1345.5	1261.5	1167.6
37.5°	958.5	1075.7	1204.5	1331.6	1420.8	1431.7	1370.3	1287.8	1190.3	1091.6	981.2
40°	911.4	1035.7	1168.2	1296.6	1375.4	1364.0	1285.7	1195.0	1078.9	958.4	855.8
42.5°	869.4	993.6	1128.5	1254.5	1317.7	1286.6	1195.0	1083.6	959.0	845.4	751.4
45°	796.5	924.3	1062.5	1184.2	1220.2	1164.1	1042.9	919.2	796.5	701.7	627.4
47.5°	725.8	852.1	989.0	1095.9	1108.6	1033.1	900.7	773.4	667.9	590.7	538.3
50°	673.8	800.6	936.1	1031.6	1027.4	936.1	800.1	678.9	590.8	528.4	493.3
52.5°	627.2	747.0	877.2	963.9	942.1	842.5	712.7	605.1	532.6	483.8	452.1
55°	554.7	665.5	789.2	858.9	818.6	708.3	598.5	511.9	458.3	421.7	397.0
57.5°	482.7	586.6	692.6	735.5	691.1	589.2	497.6	434.7	394.5	367.4	351.2
60°	438.2	529.0	623.3	660.4	607.2	516.5	444.3	388.2	355.7	333.6	319.1
62.5°	393.6	474.9	563.9	584.1	535.5	458.8	394.9	348.2	321.4	301.7	288.2
65°	333.1	399.5	467.1	480.5	435.7	376.4	325.8	295.4	271.7	257.2	246.4
67.5°	273.2	326.5	374.4	385.2	345.9	304.8	268.3	241.8	225.7	213.7	204.6
70°	237.6	279.9	319.1	327.9	296.4	259.8	232.0	210.9	196.4	186.1	177.3
72.5°	200.2	235.4	267.9	273.9	248.1	220.3	197.3	180.8	167.9	161.4	153.0
75°	153.1	173.7	198.9	200.6	183.5	166.5	149.0	138.1	131.5	123.2	119.1
77.5°	108.1	124.2	138.7	141.5	131.4	119.8	110.0	101.5	95.7	92.0	88.2
80°	82.5	95.3	101.6	105.1	98.0	89.7	84.0	78.4	74.7	72.2	69.6
82.5°	59.0	67.0	72.7	75.4	71.6	66.7	60.9	57.8	54.9	52.8	51.9
85°	29.9	33.5	37.2	38.2	37.2	35.0	31.9	31.9	30.4	29.9	29.9
87.5°	10.8	12.8	13.1	14.7	14.2	14.4	14.7	14.6	14.4	14.1	13.9
90°	2.5	4.2	6.1	7.8	9.3	10.6	11.9	13.1	14.4	15.2	16.1
92.5°	14.4	14.2	14.1	13.9	14.2	14.8	15.5	16.2	16.8	17.2	17.6
95°	41.7	36.4	31.1	25.8	23.6	24.8	26.0	27.1	28.2	29.0	29.8
97.5°	78.3	63.3	48.4	33.4	27.3	29.9	32.5	35.1	37.7	38.4	39.0
100°	105.8	83.9	61.9	39.9	30.3	33.0	35.7	38.5	41.2	42.4	43.7
102.5°	161.4	156.7	152.1	147.3	133.6	110.8	88.0	65.1	42.3	44.0	45.6
105°	224.4	229.2	234.1	238.8	219.3	175.5	131.7	87.9	44.0	45.8	47.6
107.5°	284.6	288.5	292.4	296.3	272.0	219.3	166.8	114.2	61.7	59.9	58.1
110°	323.4	326.8	330.1	333.5	311.9	265.6	219.2	172.8	126.4	110.4	94.3





TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	360.0	362.9	366.0	368.9	364.7	353.3	341.7	330.3	318.8	260.3	201.8
115°	418.1	420.8	423.5	426.3	429.7	433.6	437.7	441.7	445.8	371.4	297.1
117.5°	470.6	473.6	476.7	479.7	482.6	485.4	488.2	490.9	493.7	475.7	457.8
120°	508.1	510.5	512.9	515.3	518.0	520.9	523.7	526.6	529.5	531.4	533.4
122.5°	540.6	543.1	545.6	548.2	551.0	554.2	557.3	560.5	563.6	564.7	565.9
125°	589.4	591.5	593.6	595.6	598.2	601.3	604.3	607.3	610.5	611.6	612.7
127.5°	634.3	636.6	638.8	641.2	643.5	645.8	648.0	650.4	652.6	654.3	655.9
130°	662.9	665.4	667.9	670.6	672.7	674.5	676.2	678.0	679.7	681.6	683.3
132.5°	691.4	693.6	695.7	697.9	699.8	701.7	703.4	705.2	706.9	708.4	709.9
135°	729.3	731.8	734.5	737.0	739.0	740.4	741.8	743.4	744.8	746.4	748.0
137.5°	766.5	768.3	770.1	771.9	773.7	775.3	776.9	778.5	780.2	781.7	783.4
140°	790.8	792.1	793.5	794.7	796.3	798.0	799.8	801.5	803.3	804.8	806.2
142.5°	811.5	812.7	813.9	815.0	816.6	818.6	820.6	822.6	824.7	826.0	827.3
145°	842.8	842.7	842.5	842.4	843.6	846.4	849.1	851.8	854.5	855.8	856.9
147.5°	870.9	870.3	869.7	869.1	870.1	872.8	875.5	878.2	880.9	881.7	882.5
150°	888.9	887.8	886.7	885.4	886.3	888.8	891.3	893.9	896.5	897.5	898.4
152.5°	904.3	903.1	901.8	900.6	901.2	903.6	906.1	908.5	910.9	911.9	912.8
155°	926.9	925.3	923.9	922.5	922.7	924.6	926.6	928.5	930.4	931.4	932.4
157.5°	944.8	943.6	942.4	941.2	941.2	942.6	943.9	945.2	946.6	947.8	948.8
160°	955.4	954.5	953.5	952.6	952.6	953.5	954.5	955.4	956.4	957.5	958.4
162.5°	964.7	963.8	962.8	961.8	961.8	962.6	963.4	964.3	965.1	966.2	967.2
165°	977.1	976.2	975.2	974.2	974.0	974.5	975.0	975.4	975.9	977.0	978.2
167.5°	986.4	985.4	984.5	983.5	983.2	983.7	984.1	984.6	985.0	986.1	987.3
170°	991.6	990.7	989.7	988.8	988.4	988.8	989.1	989.4	989.7	990.8	991.9
172.5°	995.0	994.1	993.1	992.2	991.9	992.2	992.5	992.8	993.1	994.3	995.4
175°	999.4	998.3	997.1	996.0	995.6	995.9	996.2	996.5	996.9	998.0	999.2
177.5°	1000.4	999.5	998.6	997.6	997.2	997.3	997.5	997.6	997.7	998.7	999.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4	998.4



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4	1341.4
2.5°	1391.3	1397.0	1397.0	1397.9	1404.5	1403.6	1403.2
5°	1480.6	1489.3	1490.4	1499.6	1505.8	1503.8	1498.1
7.5°	1564.8	1581.1	1593.5	1600.3	1608.5	1613.6	1611.3
10°	1631.6	1655.4	1669.8	1679.6	1691.4	1700.2	1697.1
12.5°	1692.2	1720.5	1740.3	1757.1	1758.7	1769.9	1762.2
15°	1786.8	1816.6	1819.8	1832.2	1842.0	1840.9	1841.4
17.5°	1818.1	1827.7	1829.6	1829.9	1830.0	1826.3	1818.6
20°	1806.9	1803.3	1794.5	1787.9	1775.9	1774.4	1764.1
22.5°	1754.1	1742.6	1720.7	1706.2	1687.7	1682.8	1680.0
25°	1650.2	1624.9	1589.8	1556.3	1547.1	1529.0	1534.2
27.5°	1507.6	1468.2	1430.3	1403.0	1378.4	1351.4	1359.1
30°	1407.3	1363.0	1309.4	1268.2	1241.9	1216.1	1211.4
32.5°	1287.8	1222.8	1163.0	1126.7	1086.4	1070.2	1052.3
35°	1081.6	1018.1	958.9	907.9	878.5	855.8	835.2
37.5°	896.1	823.0	775.3	733.9	712.7	699.6	703.0
40°	781.0	717.1	682.1	650.6	631.0	621.7	623.8
42.5°	687.8	640.0	611.1	589.6	575.7	570.6	569.4
45°	582.0	555.2	531.5	519.2	512.4	506.8	503.1
47.5°	509.9	488.0	474.6	467.3	461.4	455.7	455.6
50°	466.6	452.1	442.8	435.0	430.5	426.4	429.9
52.5°	433.5	420.3	411.1	404.1	402.4	398.7	398.6
55°	384.6	374.3	367.6	361.3	358.3	356.2	353.7
57.5°	340.0	330.2	324.1	320.1	314.3	312.1	311.3
60°	308.3	300.5	294.4	289.2	286.6	282.5	282.5
62.5°	279.0	271.2	265.5	261.6	257.3	255.7	256.1
65°	236.6	230.5	224.8	220.7	219.6	216.5	217.5
67.5°	197.6	193.5	187.5	185.3	183.3	181.7	180.5
70°	171.7	167.5	164.4	161.4	159.8	159.8	159.8
72.5°	149.8	144.8	143.0	139.1	140.0	138.4	136.7
75°	116.0	112.9	111.4	109.8	107.2	107.2	107.2
77.5°	85.3	84.4	82.6	80.9	80.3	79.8	80.0
80°	65.9	65.4	64.4	64.4	63.4	62.9	61.9
82.5°	50.7	49.4	48.8	48.4	48.2	48.1	47.9
85°	28.9	27.9	27.9	28.4	27.4	27.4	27.9
87.5°	14.5	14.6	14.3	14.4	14.9	14.5	14.6
90°	16.9	17.7	18.2	18.6	18.9	19.2	19.5
92.5°	18.0	18.4	18.8	18.9	19.1	19.3	19.5
95°	30.6	31.4	31.7	31.5	31.4	31.2	31.1
97.5°	39.6	40.3	40.7	40.9	41.1	41.3	41.5
100°	45.0	46.4	47.2	47.5	47.8	48.1	48.4
102.5°	47.4	49.0	50.1	50.5	51.0	51.4	51.9
105°	49.4	51.1	52.3	53.0	53.6	54.2	54.9
107.5°	56.2	54.5	53.9	54.5	55.2	55.8	56.5
110°	78.3	62.2	54.5	55.1	55.7	56.5	57.1



TEST NUMBER: P331348-840

CATALOG NUMBER: S122DIP-S675D725U840-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	143.2	84.6	55.5	56.1	56.7	57.2	57.7
115°	222.8	148.5	105.4	93.9	82.3	70.8	59.3
117.5°	439.7	421.7	393.7	355.8	317.8	279.8	241.9
120°	535.3	537.2	527.4	505.6	484.0	462.3	440.7
122.5°	567.0	568.3	566.7	562.5	558.3	554.1	549.9
125°	613.8	614.9	615.7	616.2	616.7	617.1	617.6
127.5°	657.5	659.1	660.0	660.1	660.2	660.4	660.5
130°	685.1	686.8	687.6	687.5	687.3	687.1	687.0
132.5°	711.4	713.0	713.7	713.5	713.4	713.2	713.0
135°	749.6	751.2	751.8	751.5	751.2	750.8	750.5
137.5°	784.9	786.5	787.0	786.5	785.9	785.4	784.8
140°	807.6	809.1	809.4	808.6	807.8	807.0	806.2
142.5°	828.6	829.9	830.2	829.4	828.6	827.8	827.0
145°	858.0	859.1	859.2	858.5	857.7	856.9	856.1
147.5°	883.4	884.2	884.3	883.6	882.9	882.3	881.6
150°	899.4	900.3	900.4	899.6	898.8	898.0	897.2
152.5°	913.8	914.8	914.7	913.7	912.6	911.6	910.5
155°	933.3	934.3	934.1	932.8	931.6	930.3	929.0
157.5°	949.9	951.0	950.9	949.7	948.4	947.2	945.9
160°	959.4	960.3	960.2	959.1	958.0	956.8	955.7
162.5°	968.4	969.5	969.4	968.0	966.5	965.2	963.8
165°	979.4	980.5	980.5	979.4	978.2	977.0	975.9
167.5°	988.5	989.6	989.4	988.0	986.5	985.0	983.6
170°	993.0	994.2	994.0	992.6	991.1	989.7	988.3
172.5°	996.5	997.6	997.4	996.0	994.6	993.1	991.7
175°	1000.3	1001.4	1001.2	999.6	997.9	996.3	994.7
177.5°	1000.5	1001.4	1001.3	1000.1	999.0	997.7	996.6
180°	998.4	998.4	998.4	998.4	998.4	998.4	998.4

(END OF REPORT)