

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331373-927

Luminaire Tested: **S122DIP-S675D1080U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331373-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S675D1080U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5193.1 lumens  
Efficiency: N/A  
Efficacy: 91.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331373-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331373-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41																			
1	96	92	88	84	87	84	80	77	69	66	64	55	54	52	42	41	41	35																			
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29																			
3	80	70	63	57	72	64	58	53	53	49	45	43	39	37	33	31	29	25																			
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21																			
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18																			
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16																			
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14																			
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13																			
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	12																			
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13580	13580	13580
5°	13632	13434	13514
10°	13550	13298	13365
15°	13382	13125	13112
20°	13144	12866	12854
25°	12909	12549	12549
30°	12603	12258	12152
35°	12321	11907	11732
40°	11965	11556	11335
45°	11615	11209	10930
50°	11233	10846	10462
55°	10835	10427	10038
60°	10395	9923	9558
65°	9918	9425	8993
70°	9314	8818	8398
75°	8478	8122	7923
80°	7522	7290	6918
85°	6150	5835	5243



TEST NUMBER: P331373-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.1	1.5
10°-20°	222.5	4.3
20°-30°	327.1	6.3
30°-40°	379.9	7.3
40°-50°	379.5	7.3
50°-60°	331.0	6.4
60°-70°	244.7	4.7
70°-80°	138.6	2.7
80°-90°	41.6	0.8
90°-100°	69.1	1.3
100°-110°	214.6	4.1
110°-120°	366.8	7.1
120°-130°	482.4	9.3
130°-140°	541.4	10.4
140°-150°	530.9	10.2
150°-160°	445.3	8.6
160°-170°	295.3	5.7
170°-180°	103.2	2.0
0°-30°	628.7	12.1
0°-40°	1008.6	19.4
0°-60°	1719.1	33.1
0°-90°	2144.1	41.3
90°-120°	650.5	12.5
90°-150°	2205.2	42.5
90°-180°	3049.0	58.7
0°-180°	5193.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	841	841	841	841	841	
5°	841	838	829	835	834	80
15°	801	795	785	788	784	225
25°	725	718	704	706	704	333
35°	625	617	604	599	595	390
45°	509	503	491	482	479	392
55°	385	380	370	361	357	344
65°	260	254	247	240	235	257
75°	136	134	130	126	127	145
85°	33	32	32	29	28	38
90°	1	12	32	31	31	4
95°	48	57	59	59	57	55
105°	198	201	202	204	204	209
115°	368	373	372	371	368	364
125°	536	543	541	538	537	478
135°	693	703	705	704	701	535
145°	841	847	853	854	850	525
155°	962	964	967	971	969	442
165°	1046	1045	1045	1051	1047	295
175°	1089	1086	1084	1090	1085	103
180°	1090	1090	1090	1090	1090	



TEST NUMBER: P331373-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	844.9	844.2	843.5	842.8	842.1	840.9	839.3	837.7	836.1	834.6	836.0
5°	841.1	840.3	839.6	838.9	838.2	836.9	834.9	832.9	830.9	828.9	830.4
7.5°	833.6	832.5	831.4	830.3	829.2	827.6	825.6	823.6	821.6	819.5	820.9
10°	826.5	825.2	823.9	822.7	821.5	819.8	817.6	815.5	813.3	811.1	812.5
12.5°	816.8	815.7	814.5	813.4	812.3	810.7	808.5	806.4	804.2	802.1	803.1
15°	800.6	799.5	798.4	797.4	796.3	794.6	792.3	789.9	787.6	785.2	786.0
17.5°	779.9	778.8	777.8	776.7	775.6	773.9	771.5	769.1	766.8	764.4	765.2
20°	765.0	764.0	762.9	761.8	760.7	758.9	756.4	753.9	751.4	748.8	749.4
22.5°	750.1	748.6	747.1	745.6	744.1	742.2	739.8	737.4	735.1	732.7	732.8
25°	724.6	723.2	721.8	720.3	718.8	716.6	713.5	710.5	707.4	704.4	704.7
27.5°	695.5	694.2	692.9	691.6	690.3	688.5	686.0	683.7	681.2	678.8	678.3
30°	676.0	674.6	673.2	671.8	670.3	668.3	665.6	662.9	660.2	657.5	657.0
32.5°	655.4	654.2	653.1	651.9	650.8	648.8	645.9	643.1	640.2	637.4	636.4
35°	625.1	623.4	621.5	619.7	617.9	615.6	612.8	609.8	607.0	604.1	603.0
37.5°	591.0	589.4	587.8	586.2	584.7	582.4	579.6	576.7	573.9	570.9	569.6
40°	567.7	566.3	564.8	563.4	562.0	559.8	556.9	554.1	551.2	548.3	546.7
42.5°	545.1	543.6	542.2	540.7	539.3	537.2	534.2	531.4	528.5	525.7	523.9
45°	508.7	507.4	506.1	504.9	503.7	501.7	499.0	496.3	493.6	490.9	488.9
47.5°	472.5	471.3	470.1	468.9	467.7	465.7	462.9	460.1	457.3	454.5	452.4
50°	447.2	446.3	445.4	444.5	443.6	441.9	439.4	436.9	434.4	431.8	429.4
52.5°	422.6	421.4	420.3	419.1	417.9	416.1	413.8	411.4	409.0	406.6	404.6
55°	384.9	383.9	382.8	381.7	380.6	379.0	376.8	374.7	372.6	370.4	368.2
57.5°	347.1	346.3	345.4	344.5	343.6	342.1	339.7	337.3	334.9	332.6	330.4
60°	321.9	321.2	320.4	319.7	319.0	317.3	314.9	312.4	309.8	307.3	305.3
62.5°	297.3	296.1	295.0	293.8	292.7	291.1	289.2	287.2	285.3	283.4	281.5
65°	259.6	258.5	257.5	256.4	255.2	253.8	252.1	250.3	248.4	246.7	245.0
67.5°	221.3	220.4	219.5	218.6	217.8	216.6	214.9	213.3	211.8	210.1	208.8
70°	197.3	196.6	195.9	195.2	194.5	193.3	191.6	190.0	188.5	186.8	185.5
72.5°	172.8	172.0	171.3	170.6	169.8	169.0	167.9	166.9	165.9	164.8	163.6
75°	135.9	135.5	135.1	134.8	134.4	133.8	132.9	132.0	131.1	130.2	129.1
77.5°	102.9	102.3	101.6	101.0	100.4	100.0	99.6	99.2	98.9	98.5	98.0
80°	80.9	80.7	80.5	80.3	80.2	79.9	79.5	79.1	78.8	78.4	77.9
82.5°	60.2	60.1	60.1	60.0	60.0	59.9	59.7	59.5	59.3	59.0	58.4
85°	33.2	33.0	32.8	32.6	32.4	32.2	32.1	31.9	31.7	31.5	31.0
87.5°	11.8	12.0	12.2	12.4	12.7	13.1	13.6	14.3	14.9	15.5	15.0
90°	1.0	3.4	5.9	8.3	10.8	14.2	18.7	23.2	27.7	32.2	31.8
92.5°	16.4	18.1	20.0	21.8	23.6	25.0	26.1	27.2	28.2	29.2	29.3
95°	47.8	49.9	52.0	53.9	56.0	57.3	57.7	58.1	58.5	58.9	58.9
97.5°	87.5	89.2	91.0	92.8	94.6	95.9	96.6	97.4	98.2	99.0	99.0
100°	116.8	118.5	120.2	121.8	123.4	124.5	125.2	125.7	126.4	127.0	127.0
102.5°	147.8	149.1	150.4	151.7	153.0	154.1	154.9	155.6	156.4	157.2	157.3
105°	197.8	198.4	199.1	199.7	200.3	200.8	201.2	201.6	202.0	202.4	202.9
107.5°	248.3	249.1	250.1	251.0	251.8	252.3	252.3	252.3	252.3	252.3	252.5
110°	280.7	281.9	283.1	284.3	285.6	286.2	286.2	286.2	286.2	286.2	286.2



TEST NUMBER: P331373-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	316.0	317.2	318.5	319.6	320.9	321.5	321.2	321.1	320.9	320.8	320.3
115°	368.0	369.3	370.5	371.8	373.0	373.4	373.0	372.6	372.2	371.8	371.5
117.5°	419.9	421.6	423.3	424.8	426.5	426.7	425.6	424.5	423.3	422.2	421.7
120°	454.6	456.2	457.9	459.5	461.1	461.1	459.5	457.9	456.2	454.6	454.6
122.5°	486.2	488.2	490.1	492.1	494.1	494.5	493.4	492.2	491.1	489.9	489.4
125°	535.5	537.4	539.2	541.1	542.9	543.5	542.9	542.3	541.7	541.1	540.4
127.5°	583.6	585.9	588.3	590.6	592.9	593.7	592.9	592.2	591.5	590.7	590.0
130°	613.8	616.4	619.1	621.7	624.4	625.5	625.1	624.7	624.3	623.9	623.4
132.5°	647.6	649.8	652.0	654.1	656.3	657.4	657.5	657.6	657.7	657.7	656.9
135°	692.9	695.1	697.4	699.7	701.9	703.2	703.6	704.0	704.5	704.9	704.6
137.5°	740.5	742.4	744.3	746.1	747.9	749.1	749.6	750.2	750.7	751.2	751.1
140°	769.3	771.1	772.9	774.8	776.7	778.1	779.1	780.1	781.2	782.1	782.1
142.5°	798.8	800.6	802.4	804.2	806.0	807.3	808.0	808.7	809.5	810.2	810.3
145°	841.1	842.5	843.9	845.3	846.8	848.1	849.3	850.6	851.8	853.0	853.2
147.5°	878.8	880.5	882.2	883.9	885.7	886.9	887.7	888.6	889.4	890.2	890.7
150°	904.5	905.8	907.0	908.2	909.4	910.5	911.3	912.1	912.9	913.8	914.3
152.5°	927.3	928.6	929.8	931.1	932.2	933.3	934.4	935.3	936.4	937.3	938.1
155°	961.6	962.2	962.8	963.5	964.1	964.6	965.3	965.9	966.5	967.1	968.1
157.5°	990.9	991.3	991.7	992.0	992.5	992.8	993.2	993.6	994.0	994.3	995.8
160°	1008.5	1008.9	1009.3	1009.7	1010.2	1010.4	1010.7	1010.9	1011.1	1011.3	1012.5
162.5°	1024.7	1024.8	1024.8	1024.9	1025.1	1025.2	1025.4	1025.6	1025.8	1026.0	1027.4
165°	1046.2	1046.1	1045.8	1045.6	1045.4	1045.4	1045.4	1045.4	1045.4	1045.4	1046.8
167.5°	1064.3	1063.7	1063.0	1062.5	1061.8	1061.5	1061.4	1061.4	1061.4	1061.4	1062.8
170°	1073.9	1073.2	1072.6	1072.0	1071.4	1071.0	1070.8	1070.6	1070.4	1070.2	1071.6
172.5°	1080.5	1079.9	1079.3	1078.6	1078.0	1077.6	1077.4	1077.2	1077.0	1076.8	1078.2
175°	1088.6	1088.0	1087.3	1086.7	1086.2	1085.6	1085.2	1084.8	1084.4	1083.9	1085.4
177.5°	1091.9	1091.4	1090.9	1090.4	1090.0	1089.5	1089.2	1088.9	1088.5	1088.2	1089.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4



TEST NUMBER: P331373-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	837.4	838.9	840.3	840.9	840.6	840.3	840.0	839.8
5°	831.8	833.2	834.6	835.2	834.9	834.5	834.2	833.8
7.5°	822.4	823.9	825.3	825.8	825.4	825.1	824.7	824.3
10°	814.0	815.5	816.9	817.3	816.8	816.3	815.7	815.2
12.5°	804.1	805.1	806.1	806.4	806.0	805.6	805.3	804.9
15°	786.7	787.4	788.1	788.1	787.1	786.2	785.4	784.4
17.5°	766.0	766.8	767.7	767.7	766.8	766.0	765.1	764.2
20°	750.0	750.5	751.0	750.9	750.2	749.5	748.8	748.1
22.5°	732.9	733.0	733.1	732.9	732.5	732.1	731.7	731.3
25°	705.1	705.4	705.8	705.8	705.4	705.1	704.7	704.4
27.5°	677.7	677.2	676.7	676.0	675.1	674.2	673.4	672.5
30°	656.4	655.8	655.3	654.7	653.9	653.2	652.5	651.8
32.5°	635.5	634.5	633.5	632.7	632.0	631.3	630.5	629.8
35°	602.0	600.9	599.8	598.8	597.9	597.0	596.1	595.2
37.5°	568.3	567.0	565.6	564.5	563.6	562.8	562.0	561.1
40°	545.1	543.4	541.9	540.7	540.0	539.2	538.5	537.8
42.5°	522.1	520.4	518.6	517.2	516.2	515.2	514.2	513.2
45°	487.0	485.0	483.0	481.6	480.9	480.2	479.5	478.7
47.5°	450.4	448.2	446.2	444.6	443.5	442.5	441.5	440.5
50°	426.8	424.3	421.8	420.1	419.1	418.3	417.4	416.5
52.5°	402.4	400.4	398.3	396.6	395.5	394.3	393.1	391.9
55°	366.1	363.9	361.8	360.2	359.3	358.5	357.5	356.6
57.5°	328.3	326.1	324.1	322.7	321.9	321.3	320.6	319.9
60°	303.3	301.3	299.4	298.2	297.6	297.1	296.5	296.0
62.5°	279.7	277.9	276.1	274.8	274.1	273.4	272.7	272.0
65°	243.4	241.8	240.2	238.9	238.1	237.1	236.2	235.4
67.5°	207.6	206.4	205.1	204.1	203.4	202.6	201.9	201.2
70°	184.3	183.1	181.8	180.8	180.1	179.4	178.6	177.9
72.5°	162.3	161.1	159.8	158.8	158.3	157.7	157.2	156.5
75°	128.0	127.0	125.9	125.6	125.9	126.3	126.6	127.0
77.5°	97.4	96.9	96.3	95.9	95.3	94.8	94.3	93.8
80°	77.4	76.8	76.3	75.8	75.5	75.1	74.8	74.4
82.5°	57.7	57.0	56.3	55.9	55.8	55.8	55.7	55.6
85°	30.5	29.9	29.4	29.0	28.8	28.7	28.5	28.3
87.5°	14.5	13.9	13.5	13.2	13.1	12.9	12.8	12.8
90°	31.4	31.0	30.6	30.5	30.7	30.9	31.1	31.3
92.5°	29.4	29.5	29.6	29.6	29.7	29.7	29.8	29.8
95°	58.9	58.9	58.9	58.7	58.3	57.9	57.4	57.0
97.5°	99.0	99.0	99.0	99.0	98.9	98.9	98.9	98.9
100°	127.0	127.0	127.0	126.9	126.7	126.5	126.3	126.0
102.5°	157.5	157.6	157.8	157.8	157.6	157.4	157.2	157.0
105°	203.3	203.7	204.1	204.3	204.3	204.3	204.3	204.3
107.5°	252.6	252.8	252.9	252.5	251.7	250.7	249.8	248.8
110°	286.2	286.2	286.2	285.9	285.3	284.6	284.0	283.4





TEST NUMBER: P331373-927

CATALOG NUMBER: S122DIP-S675D1080U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	319.8	319.3	318.9	318.4	317.9	317.4	317.0	316.6
115°	371.4	371.1	370.9	370.5	369.9	369.3	368.7	368.0
117.5°	421.2	420.7	420.3	419.7	419.1	418.4	417.8	417.2
120°	454.6	454.6	454.6	454.2	453.7	453.0	452.4	451.8
122.5°	488.9	488.5	487.9	487.5	487.0	486.6	486.2	485.7
125°	539.9	539.2	538.6	538.2	538.0	537.8	537.6	537.4
127.5°	589.3	588.5	587.8	587.1	586.5	585.8	585.2	584.5
130°	623.1	622.7	622.3	621.6	620.8	620.0	619.2	618.4
132.5°	655.9	655.1	654.2	653.4	652.8	652.0	651.4	650.8
135°	704.5	704.3	704.0	703.6	703.0	702.4	701.8	701.2
137.5°	750.9	750.8	750.6	750.1	749.2	748.5	747.7	746.8
140°	782.1	782.1	782.1	781.7	780.9	780.1	779.3	778.5
142.5°	810.5	810.6	810.8	810.5	809.6	808.8	808.0	807.2
145°	853.4	853.7	853.8	853.5	852.7	851.9	851.0	850.2
147.5°	891.1	891.5	892.0	891.8	891.0	890.3	889.5	888.7
150°	915.0	915.6	916.2	916.2	915.6	915.0	914.3	913.8
152.5°	938.9	939.6	940.4	940.4	939.6	938.9	938.1	937.3
155°	969.2	970.2	971.2	971.4	970.8	970.2	969.6	968.9
157.5°	997.1	998.5	999.9	1000.1	999.1	998.1	997.2	996.2
160°	1013.8	1014.9	1016.2	1016.4	1015.6	1014.8	1013.9	1013.1
162.5°	1028.8	1030.2	1031.6	1031.7	1030.8	1029.8	1028.8	1027.9
165°	1048.2	1049.6	1051.1	1051.2	1050.3	1049.2	1048.2	1047.2
167.5°	1064.2	1065.6	1067.1	1067.2	1066.2	1065.1	1064.1	1063.0
170°	1073.0	1074.4	1075.9	1076.0	1074.8	1073.6	1072.3	1071.1
172.5°	1079.7	1081.1	1082.5	1082.6	1081.4	1080.1	1079.0	1077.7
175°	1086.9	1088.3	1089.7	1089.8	1088.6	1087.3	1086.2	1084.9
177.5°	1090.2	1091.2	1092.1	1092.1	1091.2	1090.2	1089.2	1088.2
180°	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4	1090.4

(END OF REPORT)