

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331395-840

Luminaire Tested: **S122DIP-S865D725U840-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331395-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S865D725U840-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6706.9 lumens  
Efficiency: N/A  
Efficacy: 123.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	56	55	54	49
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	47	42
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40	36
4	77	66	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35	32
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31	28
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25	22
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	27	23	20	18
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	28150	28150	28150	28150
5°	31561	28336	25109	28336
10°	36166	28103	21730	28103
15°	40010	27587	19198	27587
20°	39400	27034	17500	27034
25°	35527	26298	16425	26298
30°	29358	25124	15642	25124
35°	21396	23893	15084	23893
40°	17089	22443	14773	22443
45°	14933	20763	14351	20763
50°	14039	19138	14071	19138
55°	12940	17486	13695	17486
60°	11858	15733	13114	15733
65°	10804	14155	12542	14155
70°	9805	12623	11703	12623
75°	8696	10911	10368	10911
80°	7476	9028	8350	9028
85°	6706	6706	4965	6706



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.1	2.5
10°-20°	482.7	7.2
20°-30°	700.6	10.4
30°-40°	739.3	11.0
40°-50°	654.6	9.8
50°-60°	522.4	7.8
60°-70°	355.1	5.3
70°-80°	182.0	2.7
80°-90°	47.6	0.7
90°-100°	164.1	2.4
100°-110°	557.0	8.3
110°-120°	591.7	8.8
120°-130°	487.1	7.3
130°-140°	391.2	5.8
140°-150°	295.6	4.4
150°-160°	207.7	3.1
160°-170°	122.3	1.8
170°-180°	39.8	0.6
0°-30°	1349.4	20.1
0°-40°	2088.7	31.1
0°-60°	3265.7	48.7
0°-90°	3850.4	57.4
90°-120°	1312.8	19.6
90°-150°	2486.7	37.1
90°-180°	2856.0	42.6
0°-180°	6706.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1744	1744	1744	1744	1744	
5°	1947	1748	1549	1748	1947	194
15°	2394	1650	1148	1650	2394	660
25°	1994	1476	922	1476	1994	901
35°	1086	1212	765	1212	1086	706
45°	654	909	628	909	654	514
55°	460	621	486	621	460	412
65°	283	370	328	370	283	281
75°	139	175	166	175	139	149
85°	36	36	27	36	36	40
90°	26	1	26	1	26	16
95°	90	28	90	28	90	117
105°	890	96	890	96	890	861
115°	1171	170	1171	170	1171	1146
125°	950	237	950	237	950	858
135°	787	278	787	278	787	611
145°	628	317	628	317	628	399
155°	528	361	528	361	528	246
165°	463	393	463	393	463	132
175°	418	410	418	410	418	41
180°	410	410	410	410	410	



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1824.0	1824.5	1825.6	1817.1	1815.9	1815.9	1808.5	1802.0	1794.5	1784.3	1785.4
5°	1947.3	1954.7	1957.3	1949.3	1937.2	1935.9	1924.5	1905.7	1888.3	1874.2	1864.2
7.5°	2094.5	2097.4	2090.8	2080.2	2071.2	2055.2	2034.0	2013.3	1984.2	1957.5	1937.6
10°	2205.9	2210.0	2198.6	2183.1	2170.4	2151.6	2120.8	2089.3	2051.1	2014.3	1984.8
12.5°	2290.7	2300.6	2285.9	2283.9	2262.1	2236.3	2199.7	2183.7	2130.0	2078.6	2047.0
15°	2393.6	2392.9	2394.3	2381.5	2365.4	2361.4	2322.6	2280.4	2204.6	2174.4	2122.2
17.5°	2363.8	2374.0	2378.7	2378.5	2378.1	2375.6	2363.2	2336.5	2298.6	2249.7	2189.3
20°	2293.1	2306.4	2308.5	2323.9	2332.6	2344.0	2348.6	2341.3	2317.8	2276.9	2224.7
22.5°	2183.7	2187.5	2193.7	2217.8	2236.6	2265.2	2280.1	2304.8	2295.8	2275.9	2232.2
25°	1994.2	1987.5	2010.9	2023.0	2066.6	2112.1	2145.0	2181.1	2213.3	2232.7	2220.0
27.5°	1766.7	1756.6	1791.7	1823.7	1859.1	1908.4	1959.6	2020.0	2070.3	2133.1	2154.7
30°	1574.7	1580.7	1614.3	1648.4	1702.0	1771.7	1829.4	1895.7	1967.4	2037.7	2086.7
32.5°	1367.8	1391.0	1412.2	1464.5	1511.8	1589.4	1673.9	1756.9	1846.2	1926.2	2002.0
35°	1085.5	1112.4	1141.9	1180.0	1246.4	1323.4	1405.8	1517.7	1639.7	1749.0	1838.8
37.5°	913.7	909.5	926.3	953.9	1007.6	1069.9	1164.8	1275.4	1418.9	1547.2	1673.9
40°	810.8	808.1	820.2	845.7	886.6	932.1	1015.2	1112.4	1245.7	1402.5	1553.3
42.5°	740.0	741.6	748.3	766.3	794.4	831.8	894.0	976.7	1098.8	1246.5	1408.6
45°	654.0	658.7	666.1	674.8	690.8	721.6	756.5	815.5	912.0	1035.3	1194.8
47.5°	592.1	592.2	599.8	607.3	616.9	634.3	662.7	699.7	767.8	868.2	1005.3
50°	558.9	554.2	559.6	565.5	575.6	587.6	606.4	641.3	686.8	767.9	882.5
52.5°	518.2	518.3	523.1	525.3	534.3	546.4	563.5	587.6	628.9	692.4	786.6
55°	459.7	463.0	465.7	469.7	477.8	486.5	499.9	515.9	548.2	595.7	665.4
57.5°	404.8	405.8	408.5	416.2	421.2	429.3	442.0	456.6	477.5	512.7	565.1
60°	367.2	367.2	372.5	375.9	382.6	390.6	400.7	414.8	433.5	462.3	504.6
62.5°	333.0	332.3	334.5	340.0	345.1	352.6	362.6	374.6	392.2	417.9	452.6
65°	282.8	281.4	285.5	286.8	292.2	299.5	307.6	320.3	334.4	353.1	384.0
67.5°	234.5	236.1	238.3	240.9	243.8	251.6	256.9	265.9	277.8	293.4	314.3
70°	207.7	207.7	207.7	209.7	213.8	217.8	223.2	230.6	241.9	255.3	274.1
72.5°	177.7	179.9	182.0	180.8	185.9	188.3	194.7	198.8	209.7	218.3	234.9
75°	139.4	139.4	139.4	142.7	144.7	146.7	150.8	154.8	160.2	170.9	179.6
77.5°	104.0	103.7	104.4	105.2	107.3	109.8	111.0	114.6	119.6	124.5	131.9
80°	80.4	81.8	82.4	83.7	83.7	85.1	85.7	90.5	93.8	97.1	101.9
82.5°	62.2	62.4	62.6	62.8	63.4	64.2	65.9	67.5	68.6	71.4	75.0
85°	36.2	35.5	35.5	36.9	36.2	36.2	37.6	38.9	38.9	39.5	41.5
87.5°	19.2	19.2	19.7	19.2	19.2	19.5	19.2	19.0	19.7	20.4	20.8
90°	26.1	26.1	26.1	26.1	26.1	25.2	23.7	25.2	26.1	26.9	26.1
92.5°	43.7	45.0	44.3	46.9	47.6	52.4	59.1	68.9	86.6	102.6	101.2
95°	90.0	89.2	91.6	97.9	108.2	125.5	158.6	206.8	270.7	309.4	274.0
97.5°	177.1	183.8	195.3	214.7	252.5	309.4	394.9	482.6	554.2	528.3	397.9
100°	282.6	296.8	319.7	353.7	419.2	514.7	622.9	720.7	737.3	623.6	429.4
102.5°	497.4	516.5	545.1	603.1	674.3	775.5	854.6	876.8	805.5	626.8	417.5
105°	889.7	900.7	934.6	983.6	1032.6	1058.6	1048.3	959.2	795.0	584.9	393.9
107.5°	1136.4	1151.1	1157.9	1160.6	1154.5	1116.2	1034.1	899.8	725.6	540.1	382.2
110°	1210.9	1211.7	1204.7	1189.6	1155.7	1091.0	990.0	848.6	682.1	518.7	379.7



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1209.7	1205.5	1192.0	1166.9	1119.7	1045.5	937.5	801.9	651.8	504.7	380.3
115°	1170.7	1163.6	1143.1	1106.7	1050.7	969.4	866.0	744.4	614.2	489.5	383.6
117.5°	1101.1	1095.1	1073.5	1035.1	978.0	901.7	807.9	701.1	590.5	482.0	389.3
120°	1056.2	1048.3	1025.4	988.4	933.1	861.2	777.6	679.6	577.8	477.6	393.1
122.5°	1009.5	1002.9	982.5	946.0	896.5	831.5	752.3	662.7	567.1	475.0	397.6
125°	949.7	943.3	923.6	893.6	847.8	788.6	719.1	637.8	551.8	470.5	404.1
127.5°	897.3	892.2	875.1	847.1	807.1	752.5	686.9	613.4	537.6	467.8	411.0
130°	867.6	861.2	845.5	818.6	779.9	727.8	665.5	597.5	528.2	466.6	416.1
132.5°	836.6	830.9	816.4	789.6	751.5	702.6	645.3	582.4	520.6	466.0	421.1
135°	787.1	783.9	769.7	743.7	709.6	665.5	613.4	561.3	510.0	464.9	427.1
137.5°	738.4	733.7	721.2	698.8	667.8	629.3	587.9	544.4	502.5	464.8	432.4
140°	705.0	700.2	688.3	667.8	642.6	607.8	571.6	533.6	498.2	464.1	434.9
142.5°	671.5	670.6	659.9	641.4	617.3	588.2	557.0	524.8	493.7	464.1	436.9
145°	628.3	626.0	618.1	604.7	585.7	562.9	538.4	512.3	487.9	462.6	438.9
147.5°	592.2	590.8	585.4	574.7	559.1	542.3	523.2	502.7	481.9	459.8	439.6
150°	570.8	570.0	565.2	555.7	543.9	529.7	513.1	495.7	476.8	457.9	438.9
152.5°	552.4	552.3	548.8	540.6	531.3	519.0	504.9	488.8	472.4	454.7	437.7
155°	528.2	529.7	526.5	521.0	512.3	503.6	491.8	479.2	464.1	449.2	435.8
157.5°	507.5	507.5	506.0	501.4	495.2	488.5	478.6	468.0	456.5	443.5	432.1
160°	494.1	494.1	493.4	489.5	483.9	478.4	469.7	461.0	450.8	439.7	430.2
162.5°	481.5	482.2	481.4	478.7	473.2	468.9	461.5	454.0	445.7	436.6	428.4
165°	463.4	464.1	464.1	461.0	457.9	454.7	449.2	443.6	437.4	430.2	424.7
167.5°	446.7	447.6	447.8	446.1	444.6	441.7	438.0	433.7	429.1	424.7	421.1
170°	436.6	438.1	438.9	436.6	435.8	434.1	431.0	428.7	424.7	421.5	419.2
172.5°	428.4	429.3	430.1	429.0	428.2	427.3	424.7	422.9	420.3	417.8	416.7
175°	417.6	419.2	420.0	419.2	419.2	418.4	417.6	416.8	414.4	413.6	412.8
177.5°	411.1	412.4	413.0	413.0	413.0	413.0	412.4	412.4	411.1	410.5	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1789.2	1784.8	1782.2	1772.5	1763.9	1755.3	1752.7	1753.7	1742.0	1730.7	1725.9
5°	1858.9	1845.4	1832.7	1814.6	1793.2	1769.7	1757.7	1748.3	1724.8	1699.4	1684.7
7.5°	1921.3	1902.1	1877.6	1843.6	1812.3	1775.4	1752.0	1731.2	1697.0	1661.0	1639.0
10°	1959.3	1933.2	1901.7	1860.2	1822.0	1777.1	1745.6	1714.1	1673.9	1631.0	1604.2
12.5°	1992.1	1956.8	1925.8	1872.5	1827.4	1771.2	1733.8	1689.4	1647.1	1596.2	1569.9
15°	2069.9	2004.9	1945.9	1885.6	1830.0	1751.6	1710.1	1650.4	1594.8	1531.9	1501.7
17.5°	2130.1	2057.1	1964.2	1887.5	1822.6	1735.9	1674.9	1603.4	1537.6	1465.6	1424.6
20°	2164.4	2080.6	1980.7	1889.7	1811.9	1712.7	1646.4	1573.4	1496.3	1415.2	1371.0
22.5°	2184.7	2096.7	1997.9	1881.6	1790.5	1693.9	1610.5	1530.5	1452.4	1364.8	1318.5
25°	2191.2	2110.8	2006.3	1874.9	1763.7	1654.5	1554.0	1476.2	1381.7	1300.0	1232.3
27.5°	2159.3	2101.6	2001.1	1862.3	1732.7	1605.0	1493.0	1404.9	1305.3	1216.5	1148.4
30°	2120.2	2086.7	1988.8	1849.5	1708.1	1570.7	1447.4	1347.6	1248.4	1158.6	1088.9
32.5°	2059.6	2052.3	1966.3	1831.2	1681.8	1527.3	1399.7	1298.8	1188.9	1100.7	1034.2
35°	1940.6	1972.8	1918.4	1790.5	1632.3	1465.5	1327.5	1212.2	1098.3	1013.8	951.5
37.5°	1781.1	1861.0	1846.7	1730.8	1565.6	1398.3	1245.9	1125.4	1016.8	931.6	870.4
40°	1671.2	1773.0	1787.8	1685.3	1518.4	1346.3	1184.8	1064.8	958.9	881.2	819.5
42.5°	1553.3	1672.2	1712.7	1630.6	1466.9	1291.5	1130.0	1005.8	901.0	825.5	770.7
45°	1355.6	1513.1	1586.1	1539.2	1381.1	1201.4	1035.3	909.3	814.2	743.2	700.9
47.5°	1170.7	1342.8	1441.1	1424.5	1285.5	1107.6	943.3	822.4	729.8	673.2	635.4
50°	1040.0	1216.9	1335.4	1340.9	1216.9	1040.7	875.9	761.9	676.8	623.9	593.0
52.5°	926.3	1095.2	1224.6	1252.9	1140.2	971.0	815.3	701.9	626.9	578.2	550.7
55°	778.0	920.7	1064.1	1116.4	1025.9	865.1	721.0	621.2	550.8	517.4	493.2
57.5°	646.8	765.8	898.2	955.9	900.2	762.5	627.4	540.8	483.6	454.3	435.9
60°	577.6	671.5	789.4	858.4	810.1	687.5	569.6	487.2	440.3	414.1	396.7
62.5°	513.3	596.4	696.1	759.2	733.0	617.3	511.7	438.9	398.4	374.0	361.3
65°	423.5	489.2	566.2	624.5	607.1	519.3	432.9	370.5	338.4	318.9	308.9
67.5°	348.7	396.2	449.6	500.7	486.7	424.4	355.0	306.5	282.6	265.8	259.7
70°	301.5	337.7	385.3	426.2	414.8	363.9	308.9	267.4	246.6	232.6	226.5
72.5°	256.5	286.3	322.6	356.0	348.3	306.0	260.1	228.7	212.8	199.9	194.9
75°	193.7	216.4	238.5	260.6	258.6	225.8	199.0	174.9	162.2	152.1	150.1
77.5°	143.0	155.7	170.8	183.9	180.3	161.5	140.5	126.6	117.2	110.6	109.5
80°	109.3	116.6	127.3	136.7	132.0	124.0	107.2	97.1	90.5	83.7	81.1
82.5°	79.2	86.5	93.0	98.1	94.5	86.9	76.6	69.8	65.8	61.2	60.2
85°	41.5	45.5	48.3	49.6	48.3	43.5	38.9	36.2	32.8	30.8	30.2
87.5°	20.3	19.3	18.5	19.1	17.2	16.8	14.0	11.9	11.9	12.0	11.2
90°	21.3	15.8	11.8	9.5	7.9	6.4	3.1	0.8	3.1	6.4	7.9
92.5°	78.8	53.7	35.9	28.4	23.0	19.6	13.9	9.6	13.9	19.6	23.0
95°	182.4	113.7	77.4	58.4	45.7	38.7	30.8	27.7	30.8	38.7	45.7
97.5°	245.7	150.0	104.3	82.9	68.4	57.7	49.3	45.0	49.3	57.7	68.4
100°	258.9	162.6	120.8	98.7	82.9	70.3	63.1	60.8	63.1	70.3	82.9
102.5°	259.5	174.0	135.3	113.2	96.7	84.1	77.1	75.3	77.1	84.1	96.7
105°	263.7	193.4	156.3	134.2	116.8	105.0	99.5	96.3	99.5	105.0	116.8
107.5°	274.6	213.3	177.3	155.0	137.8	126.9	121.6	119.1	121.6	126.9	137.8
110°	283.4	226.5	191.9	169.0	152.4	142.1	137.3	134.2	137.3	142.1	152.4





TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	292.9	239.2	205.7	182.2	166.2	156.6	151.3	148.0	151.3	156.6	166.2
115°	307.1	258.9	225.0	203.7	187.8	178.4	173.7	169.8	173.7	178.4	187.8
117.5°	322.2	277.1	245.7	223.6	208.4	200.1	195.3	192.2	195.3	200.1	208.4
120°	332.3	289.7	258.9	236.8	221.1	213.9	209.2	206.0	209.2	213.9	221.1
122.5°	341.2	301.7	272.9	250.0	234.3	226.5	221.9	219.3	221.9	226.5	234.3
125°	355.3	319.7	291.2	269.2	253.4	243.9	239.2	236.8	239.2	243.9	253.4
127.5°	368.3	336.5	308.8	286.1	270.9	260.5	253.9	250.7	253.9	260.5	270.9
130°	376.6	346.6	318.9	296.8	281.0	269.9	262.1	258.9	262.1	269.9	281.0
132.5°	384.8	355.4	329.0	306.9	290.5	278.8	270.3	266.5	270.3	278.8	290.5
135°	395.5	367.9	342.6	320.5	302.4	290.5	281.0	277.9	281.0	290.5	302.4
137.5°	403.7	378.0	353.0	332.5	314.5	301.8	292.4	288.6	292.4	301.8	314.5
140°	408.1	383.6	360.0	339.4	322.0	309.4	299.9	296.8	299.9	309.4	322.0
142.5°	411.9	388.1	365.1	345.8	329.0	316.4	307.6	305.0	307.6	316.4	329.0
145°	416.8	394.8	373.3	356.0	340.2	328.4	320.5	317.3	320.5	328.4	340.2
147.5°	419.5	400.1	380.0	364.6	351.4	340.5	333.0	330.6	333.0	340.5	351.4
150°	420.7	402.6	384.5	370.2	358.4	348.1	341.8	339.4	341.8	348.1	358.4
152.5°	421.4	405.2	388.9	375.9	364.7	355.7	349.4	348.3	349.4	355.7	364.7
155°	422.3	408.9	395.5	383.6	375.0	366.3	361.5	360.7	361.5	366.3	375.0
157.5°	422.3	411.6	400.2	390.3	383.3	375.8	371.9	371.2	371.9	375.8	383.3
160°	422.3	412.8	403.3	394.8	388.4	382.0	378.9	378.1	378.9	382.0	388.4
162.5°	421.7	413.5	405.3	398.5	392.8	387.8	384.6	385.1	384.6	387.8	392.8
165°	420.0	414.4	407.4	402.6	398.7	393.9	392.3	393.1	392.3	393.9	398.7
167.5°	418.9	414.2	409.1	406.1	403.2	400.2	398.8	399.8	398.8	400.2	403.2
170°	417.6	413.6	409.7	407.4	405.8	403.3	402.6	404.1	402.6	403.3	405.8
172.5°	415.7	413.0	410.3	408.6	407.7	405.3	405.8	406.7	405.8	405.3	407.7
175°	413.6	412.0	410.5	409.7	409.7	408.1	408.9	409.7	408.9	408.1	409.7
177.5°	412.4	411.1	410.5	410.5	410.5	409.2	409.9	411.1	409.9	409.2	410.5
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1720.5	1717.3	1706.1	1700.2	1690.5	1681.4	1675.5	1678.2	1680.3	1679.2	1677.7
5°	1671.2	1658.5	1639.0	1622.2	1610.2	1588.1	1578.7	1574.1	1570.0	1565.3	1560.6
7.5°	1612.6	1592.5	1564.5	1540.7	1518.1	1490.7	1475.0	1465.6	1456.0	1445.4	1436.0
10°	1570.7	1542.6	1513.1	1479.6	1452.8	1427.9	1405.8	1391.1	1377.8	1364.9	1355.6
12.5°	1526.7	1494.3	1457.8	1412.0	1382.5	1347.1	1343.6	1317.7	1296.8	1288.9	1277.9
15°	1456.8	1411.2	1364.9	1310.7	1287.3	1255.1	1235.0	1214.9	1196.8	1184.1	1180.7
17.5°	1377.4	1318.4	1272.3	1233.3	1194.9	1162.0	1143.5	1127.4	1112.5	1095.5	1093.2
20°	1316.8	1265.8	1215.6	1181.3	1141.9	1108.3	1085.5	1069.4	1056.7	1046.7	1037.9
22.5°	1259.4	1203.7	1157.6	1120.2	1081.3	1054.2	1036.2	1020.7	1010.1	999.0	990.8
25°	1167.3	1123.8	1073.5	1031.3	999.1	981.7	966.9	953.5	946.8	939.5	930.1
27.5°	1086.7	1038.3	991.4	958.7	930.4	914.9	904.5	895.3	889.1	884.7	879.4
30°	1030.0	981.0	944.1	912.0	888.6	873.1	866.5	861.1	853.7	851.0	848.4
32.5°	975.2	931.2	899.7	871.8	849.4	839.4	833.2	828.4	822.6	819.9	814.6
35°	898.0	861.1	830.2	814.9	796.8	788.0	783.4	776.7	771.2	768.6	767.9
37.5°	825.2	793.1	772.8	753.1	745.4	740.0	733.7	729.0	727.4	727.0	726.4
40°	778.0	751.8	733.8	717.7	714.3	706.3	700.9	696.9	696.9	697.6	696.9
42.5°	735.1	711.7	695.7	681.8	677.8	673.1	667.7	667.4	668.5	670.8	668.5
45°	670.0	653.4	642.0	635.2	627.8	623.2	622.5	624.5	625.2	625.9	627.8
47.5°	610.4	599.2	588.9	581.5	578.2	577.4	576.6	580.2	583.4	584.6	587.6
50°	574.9	562.2	553.5	548.8	546.1	544.8	546.1	550.2	552.8	556.1	558.2
52.5°	535.2	526.2	520.3	516.6	515.5	516.3	516.6	521.2	525.5	526.6	527.7
55°	480.5	473.7	472.4	466.4	469.1	468.4	471.7	474.4	478.5	482.5	483.1
57.5°	425.8	420.4	416.8	417.4	418.2	421.1	423.9	428.6	432.9	437.2	437.6
60°	389.3	386.7	384.7	384.7	386.0	390.0	393.3	398.0	400.7	403.4	405.4
62.5°	356.1	353.5	351.4	352.4	356.0	358.4	362.2	364.8	367.5	370.1	371.1
65°	303.6	302.3	304.3	305.6	306.2	309.6	314.3	316.3	318.9	320.3	325.0
67.5°	255.2	255.4	255.2	257.0	260.9	261.8	266.2	270.8	271.4	274.0	277.0
70°	222.5	223.8	225.2	226.5	229.8	231.2	234.5	236.5	239.2	241.3	243.3
72.5°	192.5	192.7	194.1	193.8	196.6	199.5	202.4	204.4	207.0	209.6	211.6
75°	148.0	148.0	149.5	150.1	153.5	156.8	156.1	157.4	160.2	162.8	164.2
77.5°	108.2	106.6	108.2	108.9	109.9	112.7	113.2	115.1	118.2	117.2	118.8
80°	82.4	80.4	82.4	83.1	83.1	86.4	86.4	87.8	89.8	87.8	89.8
82.5°	58.9	57.9	59.4	59.5	60.6	60.7	61.8	62.0	64.0	63.1	64.0
85°	29.5	28.8	29.5	28.8	29.5	30.2	30.2	29.5	29.5	30.8	28.8
87.5°	11.0	10.9	11.2	12.3	12.7	12.3	11.6	11.5	11.2	10.4	10.6
90°	9.5	11.8	15.8	21.3	26.1	26.9	26.1	25.2	23.7	25.2	26.1
92.5°	28.4	35.9	53.7	78.8	101.2	102.6	86.6	68.9	59.1	52.4	47.6
95°	58.4	77.4	113.7	182.4	274.0	309.4	270.7	206.8	158.6	125.5	108.2
97.5°	82.9	104.3	150.0	245.7	397.9	528.3	554.2	482.6	394.9	309.4	252.5
100°	98.7	120.8	162.6	258.9	429.4	623.6	737.3	720.7	622.9	514.7	419.2
102.5°	113.2	135.3	174.0	259.5	417.5	626.8	805.5	876.8	854.6	775.5	674.3
105°	134.2	156.3	193.4	263.7	393.9	584.9	795.0	959.2	1048.3	1058.6	1032.6
107.5°	155.0	177.3	213.3	274.6	382.2	540.1	725.6	899.8	1034.1	1116.2	1154.5
110°	169.0	191.9	226.5	283.4	379.7	518.7	682.1	848.6	990.0	1091.0	1155.7



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	182.2	205.7	239.2	292.9	380.3	504.7	651.8	801.9	937.5	1045.5	1119.7
115°	203.7	225.0	258.9	307.1	383.6	489.5	614.2	744.4	866.0	969.4	1050.7
117.5°	223.6	245.7	277.1	322.2	389.3	482.0	590.5	701.1	807.9	901.7	978.0
120°	236.8	258.9	289.7	332.3	393.1	477.6	577.8	679.6	777.6	861.2	933.1
122.5°	250.0	272.9	301.7	341.2	397.6	475.0	567.1	662.7	752.3	831.5	896.5
125°	269.2	291.2	319.7	355.3	404.1	470.5	551.8	637.8	719.1	788.6	847.8
127.5°	286.1	308.8	336.5	368.3	411.0	467.8	537.6	613.4	686.9	752.5	807.1
130°	296.8	318.9	346.6	376.6	416.1	466.6	528.2	597.5	665.5	727.8	779.9
132.5°	306.9	329.0	355.4	384.8	421.1	466.0	520.6	582.4	645.3	702.6	751.5
135°	320.5	342.6	367.9	395.5	427.1	464.9	510.0	561.3	613.4	665.5	709.6
137.5°	332.5	353.0	378.0	403.7	432.4	464.8	502.5	544.4	587.9	629.3	667.8
140°	339.4	360.0	383.6	408.1	434.9	464.1	498.2	533.6	571.6	607.8	642.6
142.5°	345.8	365.1	388.1	411.9	436.9	464.1	493.7	524.8	557.0	588.2	617.3
145°	356.0	373.3	394.8	416.8	438.9	462.6	487.9	512.3	538.4	562.9	585.7
147.5°	364.6	380.0	400.1	419.5	439.6	459.8	481.9	502.7	523.2	542.3	559.1
150°	370.2	384.5	402.6	420.7	438.9	457.9	476.8	495.7	513.1	529.7	543.9
152.5°	375.9	388.9	405.2	421.4	437.7	454.7	472.4	488.8	504.9	519.0	531.3
155°	383.6	395.5	408.9	422.3	435.8	449.2	464.1	479.2	491.8	503.6	512.3
157.5°	390.3	400.2	411.6	422.3	432.1	443.5	456.5	468.0	478.6	488.5	495.2
160°	394.8	403.3	412.8	422.3	430.2	439.7	450.8	461.0	469.7	478.4	483.9
162.5°	398.5	405.3	413.5	421.7	428.4	436.6	445.7	454.0	461.5	468.9	473.2
165°	402.6	407.4	414.4	420.0	424.7	430.2	437.4	443.6	449.2	454.7	457.9
167.5°	406.1	409.1	414.2	418.9	421.1	424.7	429.1	433.7	438.0	441.7	444.6
170°	407.4	409.7	413.6	417.6	419.2	421.5	424.7	428.7	431.0	434.1	435.8
172.5°	408.6	410.3	413.0	415.7	416.7	417.8	420.3	422.9	424.7	427.3	428.2
175°	409.7	410.5	412.0	413.6	412.8	413.6	414.4	416.8	417.6	418.4	419.2
177.5°	410.5	410.5	411.1	412.4	411.1	410.5	411.1	412.4	412.4	413.0	413.0
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1672.2	1671.2	1671.2	1666.4	1671.2	1671.2	1672.2	1677.7	1679.2	1680.3	1678.2
5°	1551.3	1549.2	1545.9	1549.2	1545.9	1549.2	1551.3	1560.6	1565.3	1570.0	1574.1
7.5°	1431.6	1423.5	1422.3	1414.4	1422.3	1423.5	1431.6	1436.0	1445.4	1456.0	1465.6
10°	1344.2	1338.9	1338.2	1325.4	1338.2	1338.9	1344.2	1355.6	1364.9	1377.8	1391.1
12.5°	1277.8	1264.9	1267.4	1260.0	1267.4	1264.9	1277.8	1277.9	1288.9	1296.8	1317.7
15°	1162.7	1162.7	1159.9	1148.5	1159.9	1162.7	1162.7	1180.7	1184.1	1196.8	1214.9
17.5°	1079.9	1078.5	1072.2	1075.4	1072.2	1078.5	1079.9	1093.2	1095.5	1112.5	1127.4
20°	1030.6	1026.6	1018.5	1018.5	1018.5	1026.6	1030.6	1037.9	1046.7	1056.7	1069.4
22.5°	984.0	983.7	975.1	977.8	975.1	983.7	984.0	990.8	999.0	1010.1	1020.7
25°	929.4	924.0	920.1	922.0	920.1	924.0	929.4	930.1	939.5	946.8	953.5
27.5°	877.7	874.7	874.4	869.0	874.4	874.7	877.7	879.4	884.7	889.1	895.3
30°	847.7	841.0	842.3	839.0	842.3	841.0	847.7	848.4	851.0	853.7	861.1
32.5°	813.3	810.9	809.6	806.8	809.6	810.9	813.3	814.6	819.9	822.6	828.4
35°	766.6	767.3	763.9	765.3	763.9	767.3	766.6	767.9	768.6	771.2	776.7
37.5°	725.7	727.8	726.3	726.7	726.3	727.8	725.7	726.4	727.0	727.4	729.0
40°	698.9	698.9	698.9	700.9	698.9	698.9	698.9	696.9	697.6	696.9	696.9
42.5°	673.2	672.1	671.1	670.9	671.1	672.1	673.2	668.5	670.8	668.5	667.4
45°	629.2	631.3	631.9	628.5	631.9	631.3	629.2	627.8	625.9	625.2	624.5
47.5°	589.5	589.7	589.5	592.4	589.5	589.7	589.5	587.6	584.6	583.4	580.2
50°	561.6	560.2	561.6	560.2	561.6	560.2	561.6	558.2	556.1	552.8	550.2
52.5°	532.1	532.3	531.5	531.3	531.5	532.3	532.1	527.7	526.6	525.5	521.2
55°	485.8	487.2	486.5	486.5	486.5	487.2	485.8	483.1	482.5	478.5	474.4
57.5°	438.0	439.2	440.1	437.2	440.1	439.2	438.0	437.6	437.2	432.9	428.6
60°	404.8	408.1	407.4	406.1	407.4	408.1	404.8	405.4	403.4	400.7	398.0
62.5°	374.2	375.4	375.3	375.0	375.3	375.4	374.2	371.1	370.1	367.5	364.8
65°	327.0	328.3	326.3	328.3	326.3	328.3	327.0	325.0	320.3	318.9	316.3
67.5°	276.2	276.6	278.1	279.0	278.1	276.6	276.2	277.0	274.0	271.4	270.8
70°	244.6	243.9	245.9	247.9	245.9	243.9	244.6	243.3	241.3	239.2	236.5
72.5°	211.4	212.8	212.2	213.6	212.2	212.8	211.4	211.6	209.6	207.0	204.4
75°	162.8	164.8	164.2	166.2	164.2	164.8	162.8	164.2	162.8	160.2	157.4
77.5°	117.6	118.0	117.6	118.8	117.6	118.0	117.6	118.8	117.2	118.2	115.1
80°	89.8	88.5	87.2	89.8	87.2	88.5	89.8	89.8	87.8	89.8	87.8
82.5°	62.4	63.2	61.9	61.9	61.9	63.2	62.4	64.0	63.1	64.0	62.0
85°	28.8	28.2	26.8	26.8	26.8	28.2	28.8	28.8	30.8	29.5	29.5
87.5°	10.6	10.0	10.0	9.5	10.0	10.0	10.6	10.6	10.4	11.2	11.5
90°	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	25.2	23.7	25.2
92.5°	46.9	44.3	45.0	43.7	45.0	44.3	46.9	47.6	52.4	59.1	68.9
95°	97.9	91.6	89.2	90.0	89.2	91.6	97.9	108.2	125.5	158.6	206.8
97.5°	214.7	195.3	183.8	177.1	183.8	195.3	214.7	252.5	309.4	394.9	482.6
100°	353.7	319.7	296.8	282.6	296.8	319.7	353.7	419.2	514.7	622.9	720.7
102.5°	603.1	545.1	516.5	497.4	516.5	545.1	603.1	674.3	775.5	854.6	876.8
105°	983.6	934.6	900.7	889.7	900.7	934.6	983.6	1032.6	1058.6	1048.3	959.2
107.5°	1160.6	1157.9	1151.1	1136.4	1151.1	1157.9	1160.6	1154.5	1116.2	1034.1	899.8
110°	1189.6	1204.7	1211.7	1210.9	1211.7	1204.7	1189.6	1155.7	1091.0	990.0	848.6



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1166.9	1192.0	1205.5	1209.7	1205.5	1192.0	1166.9	1119.7	1045.5	937.5	801.9
115°	1106.7	1143.1	1163.6	1170.7	1163.6	1143.1	1106.7	1050.7	969.4	866.0	744.4
117.5°	1035.1	1073.5	1095.1	1101.1	1095.1	1073.5	1035.1	978.0	901.7	807.9	701.1
120°	988.4	1025.4	1048.3	1056.2	1048.3	1025.4	988.4	933.1	861.2	777.6	679.6
122.5°	946.0	982.5	1002.9	1009.5	1002.9	982.5	946.0	896.5	831.5	752.3	662.7
125°	893.6	923.6	943.3	949.7	943.3	923.6	893.6	847.8	788.6	719.1	637.8
127.5°	847.1	875.1	892.2	897.3	892.2	875.1	847.1	807.1	752.5	686.9	613.4
130°	818.6	845.5	861.2	867.6	861.2	845.5	818.6	779.9	727.8	665.5	597.5
132.5°	789.6	816.4	830.9	836.6	830.9	816.4	789.6	751.5	702.6	645.3	582.4
135°	743.7	769.7	783.9	787.1	783.9	769.7	743.7	709.6	665.5	613.4	561.3
137.5°	698.8	721.2	733.7	738.4	733.7	721.2	698.8	667.8	629.3	587.9	544.4
140°	667.8	688.3	700.2	705.0	700.2	688.3	667.8	642.6	607.8	571.6	533.6
142.5°	641.4	659.9	670.6	671.5	670.6	659.9	641.4	617.3	588.2	557.0	524.8
145°	604.7	618.1	626.0	628.3	626.0	618.1	604.7	585.7	562.9	538.4	512.3
147.5°	574.7	585.4	590.8	592.2	590.8	585.4	574.7	559.1	542.3	523.2	502.7
150°	555.7	565.2	570.0	570.8	570.0	565.2	555.7	543.9	529.7	513.1	495.7
152.5°	540.6	548.8	552.3	552.4	552.3	548.8	540.6	531.3	519.0	504.9	488.8
155°	521.0	526.5	529.7	528.2	529.7	526.5	521.0	512.3	503.6	491.8	479.2
157.5°	501.4	506.0	507.5	507.5	507.5	506.0	501.4	495.2	488.5	478.6	468.0
160°	489.5	493.4	494.1	494.1	494.1	493.4	489.5	483.9	478.4	469.7	461.0
162.5°	478.7	481.4	482.2	481.5	482.2	481.4	478.7	473.2	468.9	461.5	454.0
165°	461.0	464.1	464.1	463.4	464.1	464.1	461.0	457.9	454.7	449.2	443.6
167.5°	446.1	447.8	447.6	446.7	447.6	447.8	446.1	444.6	441.7	438.0	433.7
170°	436.6	438.9	438.1	436.6	438.1	438.9	436.6	435.8	434.1	431.0	428.7
172.5°	429.0	430.1	429.3	428.4	429.3	430.1	429.0	428.2	427.3	424.7	422.9
175°	419.2	420.0	419.2	417.6	419.2	420.0	419.2	419.2	418.4	417.6	416.8
177.5°	413.0	413.0	412.4	411.1	412.4	413.0	413.0	413.0	413.0	412.4	412.4
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1675.5	1681.4	1690.5	1700.2	1706.1	1717.3	1720.5	1725.9	1730.7	1742.0	1753.7
5°	1578.7	1588.1	1610.2	1622.2	1639.0	1658.5	1671.2	1684.7	1699.4	1724.8	1748.3
7.5°	1475.0	1490.7	1518.1	1540.7	1564.5	1592.5	1612.6	1639.0	1661.0	1697.0	1731.2
10°	1405.8	1427.9	1452.8	1479.6	1513.1	1542.6	1570.7	1604.2	1631.0	1673.9	1714.1
12.5°	1343.6	1347.1	1382.5	1412.0	1457.8	1494.3	1526.7	1569.9	1596.2	1647.1	1689.4
15°	1235.0	1255.1	1287.3	1310.7	1364.9	1411.2	1456.8	1501.7	1531.9	1594.8	1650.4
17.5°	1143.5	1162.0	1194.9	1233.3	1272.3	1318.4	1377.4	1424.6	1465.6	1537.6	1603.4
20°	1085.5	1108.3	1141.9	1181.3	1215.6	1265.8	1316.8	1371.0	1415.2	1496.3	1573.4
22.5°	1036.2	1054.2	1081.3	1120.2	1157.6	1203.7	1259.4	1318.5	1364.8	1452.4	1530.5
25°	966.9	981.7	999.1	1031.3	1073.5	1123.8	1167.3	1232.3	1300.0	1381.7	1476.2
27.5°	904.5	914.9	930.4	958.7	991.4	1038.3	1086.7	1148.4	1216.5	1305.3	1404.9
30°	866.5	873.1	888.6	912.0	944.1	981.0	1030.0	1088.9	1158.6	1248.4	1347.6
32.5°	833.2	839.4	849.4	871.8	899.7	931.2	975.2	1034.2	1100.7	1188.9	1298.8
35°	783.4	788.0	796.8	814.9	830.2	861.1	898.0	951.5	1013.8	1098.3	1212.2
37.5°	733.7	740.0	745.4	753.1	772.8	793.1	825.2	870.4	931.6	1016.8	1125.4
40°	700.9	706.3	714.3	717.7	733.8	751.8	778.0	819.5	881.2	958.9	1064.8
42.5°	667.7	673.1	677.8	681.8	695.7	711.7	735.1	770.7	825.5	901.0	1005.8
45°	622.5	623.2	627.8	635.2	642.0	653.4	670.0	700.9	743.2	814.2	909.3
47.5°	576.6	577.4	578.2	581.5	588.9	599.2	610.4	635.4	673.2	729.8	822.4
50°	546.1	544.8	546.1	548.8	553.5	562.2	574.9	593.0	623.9	676.8	761.9
52.5°	516.6	516.3	515.5	516.6	520.3	526.2	535.2	550.7	578.2	626.9	701.9
55°	471.7	468.4	469.1	466.4	472.4	473.7	480.5	493.2	517.4	550.8	621.2
57.5°	423.9	421.1	418.2	417.4	416.8	420.4	425.8	435.9	454.3	483.6	540.8
60°	393.3	390.0	386.0	384.7	384.7	386.7	389.3	396.7	414.1	440.3	487.2
62.5°	362.2	358.4	356.0	352.4	351.4	353.5	356.1	361.3	374.0	398.4	438.9
65°	314.3	309.6	306.2	305.6	304.3	302.3	303.6	308.9	318.9	338.4	370.5
67.5°	266.2	261.8	260.9	257.0	255.2	255.4	255.2	259.7	265.8	282.6	306.5
70°	234.5	231.2	229.8	226.5	225.2	223.8	222.5	226.5	232.6	246.6	267.4
72.5°	202.4	199.5	196.6	193.8	194.1	192.7	192.5	194.9	199.9	212.8	228.7
75°	156.1	156.8	153.5	150.1	149.5	148.0	148.0	150.1	152.1	162.2	174.9
77.5°	113.2	112.7	109.9	108.9	108.2	106.6	108.2	109.5	110.6	117.2	126.6
80°	86.4	86.4	83.1	83.1	82.4	80.4	82.4	81.1	83.7	90.5	97.1
82.5°	61.8	60.7	60.6	59.5	59.4	57.9	58.9	60.2	61.2	65.8	69.8
85°	30.2	30.2	29.5	28.8	29.5	28.8	29.5	30.2	30.8	32.8	36.2
87.5°	11.6	12.3	12.7	12.3	11.2	10.9	11.0	11.2	12.0	11.9	11.9
90°	26.1	26.9	26.1	21.3	15.8	11.8	9.5	7.9	6.4	3.1	0.8
92.5°	86.6	102.6	101.2	78.8	53.7	35.9	28.4	23.0	19.6	13.9	9.6
95°	270.7	309.4	274.0	182.4	113.7	77.4	58.4	45.7	38.7	30.8	27.7
97.5°	554.2	528.3	397.9	245.7	150.0	104.3	82.9	68.4	57.7	49.3	45.0
100°	737.3	623.6	429.4	258.9	162.6	120.8	98.7	82.9	70.3	63.1	60.8
102.5°	805.5	626.8	417.5	259.5	174.0	135.3	113.2	96.7	84.1	77.1	75.3
105°	795.0	584.9	393.9	263.7	193.4	156.3	134.2	116.8	105.0	99.5	96.3
107.5°	725.6	540.1	382.2	274.6	213.3	177.3	155.0	137.8	126.9	121.6	119.1
110°	682.1	518.7	379.7	283.4	226.5	191.9	169.0	152.4	142.1	137.3	134.2



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	651.8	504.7	380.3	292.9	239.2	205.7	182.2	166.2	156.6	151.3	148.0
115°	614.2	489.5	383.6	307.1	258.9	225.0	203.7	187.8	178.4	173.7	169.8
117.5°	590.5	482.0	389.3	322.2	277.1	245.7	223.6	208.4	200.1	195.3	192.2
120°	577.8	477.6	393.1	332.3	289.7	258.9	236.8	221.1	213.9	209.2	206.0
122.5°	567.1	475.0	397.6	341.2	301.7	272.9	250.0	234.3	226.5	221.9	219.3
125°	551.8	470.5	404.1	355.3	319.7	291.2	269.2	253.4	243.9	239.2	236.8
127.5°	537.6	467.8	411.0	368.3	336.5	308.8	286.1	270.9	260.5	253.9	250.7
130°	528.2	466.6	416.1	376.6	346.6	318.9	296.8	281.0	269.9	262.1	258.9
132.5°	520.6	466.0	421.1	384.8	355.4	329.0	306.9	290.5	278.8	270.3	266.5
135°	510.0	464.9	427.1	395.5	367.9	342.6	320.5	302.4	290.5	281.0	277.9
137.5°	502.5	464.8	432.4	403.7	378.0	353.0	332.5	314.5	301.8	292.4	288.6
140°	498.2	464.1	434.9	408.1	383.6	360.0	339.4	322.0	309.4	299.9	296.8
142.5°	493.7	464.1	436.9	411.9	388.1	365.1	345.8	329.0	316.4	307.6	305.0
145°	487.9	462.6	438.9	416.8	394.8	373.3	356.0	340.2	328.4	320.5	317.3
147.5°	481.9	459.8	439.6	419.5	400.1	380.0	364.6	351.4	340.5	333.0	330.6
150°	476.8	457.9	438.9	420.7	402.6	384.5	370.2	358.4	348.1	341.8	339.4
152.5°	472.4	454.7	437.7	421.4	405.2	388.9	375.9	364.7	355.7	349.4	348.3
155°	464.1	449.2	435.8	422.3	408.9	395.5	383.6	375.0	366.3	361.5	360.7
157.5°	456.5	443.5	432.1	422.3	411.6	400.2	390.3	383.3	375.8	371.9	371.2
160°	450.8	439.7	430.2	422.3	412.8	403.3	394.8	388.4	382.0	378.9	378.1
162.5°	445.7	436.6	428.4	421.7	413.5	405.3	398.5	392.8	387.8	384.6	385.1
165°	437.4	430.2	424.7	420.0	414.4	407.4	402.6	398.7	393.9	392.3	393.1
167.5°	429.1	424.7	421.1	418.9	414.2	409.1	406.1	403.2	400.2	398.8	399.8
170°	424.7	421.5	419.2	417.6	413.6	409.7	407.4	405.8	403.3	402.6	404.1
172.5°	420.3	417.8	416.7	415.7	413.0	410.3	408.6	407.7	405.3	405.8	406.7
175°	414.4	413.6	412.8	413.6	412.0	410.5	409.7	409.7	408.1	408.9	409.7
177.5°	411.1	410.5	411.1	412.4	411.1	410.5	410.5	410.5	409.2	409.9	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1752.7	1755.3	1763.9	1772.5	1782.2	1784.8	1789.2	1785.4	1784.3	1794.5	1802.0
5°	1757.7	1769.7	1793.2	1814.6	1832.7	1845.4	1858.9	1864.2	1874.2	1888.3	1905.7
7.5°	1752.0	1775.4	1812.3	1843.6	1877.6	1902.1	1921.3	1937.6	1957.5	1984.2	2013.3
10°	1745.6	1777.1	1822.0	1860.2	1901.7	1933.2	1959.3	1984.8	2014.3	2051.1	2089.3
12.5°	1733.8	1771.2	1827.4	1872.5	1925.8	1956.8	1992.1	2047.0	2078.6	2130.0	2183.7
15°	1710.1	1751.6	1830.0	1885.6	1945.9	2004.9	2069.9	2122.2	2174.4	2204.6	2280.4
17.5°	1674.9	1735.9	1822.6	1887.5	1964.2	2057.1	2130.1	2189.3	2249.7	2298.6	2336.5
20°	1646.4	1712.7	1811.9	1889.7	1980.7	2080.6	2164.4	2224.7	2276.9	2317.8	2341.3
22.5°	1610.5	1693.9	1790.5	1881.6	1997.9	2096.7	2184.7	2232.2	2275.9	2295.8	2304.8
25°	1554.0	1654.5	1763.7	1874.9	2006.3	2110.8	2191.2	2220.0	2232.7	2213.3	2181.1
27.5°	1493.0	1605.0	1732.7	1862.3	2001.1	2101.6	2159.3	2154.7	2133.1	2070.3	2020.0
30°	1447.4	1570.7	1708.1	1849.5	1988.8	2086.7	2120.2	2086.7	2037.7	1967.4	1895.7
32.5°	1399.7	1527.3	1681.8	1831.2	1966.3	2052.3	2059.6	2002.0	1926.2	1846.2	1756.9
35°	1327.5	1465.5	1632.3	1790.5	1918.4	1972.8	1940.6	1838.8	1749.0	1639.7	1517.7
37.5°	1245.9	1398.3	1565.6	1730.8	1846.7	1861.0	1781.1	1673.9	1547.2	1418.9	1275.4
40°	1184.8	1346.3	1518.4	1685.3	1787.8	1773.0	1671.2	1553.3	1402.5	1245.7	1112.4
42.5°	1130.0	1291.5	1466.9	1630.6	1712.7	1672.2	1553.3	1408.6	1246.5	1098.8	976.7
45°	1035.3	1201.4	1381.1	1539.2	1586.1	1513.1	1355.6	1194.8	1035.3	912.0	815.5
47.5°	943.3	1107.6	1285.5	1424.5	1441.1	1342.8	1170.7	1005.3	868.2	767.8	699.7
50°	875.9	1040.7	1216.9	1340.9	1335.4	1216.9	1040.0	882.5	767.9	686.8	641.3
52.5°	815.3	971.0	1140.2	1252.9	1224.6	1095.2	926.3	786.6	692.4	628.9	587.6
55°	721.0	865.1	1025.9	1116.4	1064.1	920.7	778.0	665.4	595.7	548.2	515.9
57.5°	627.4	762.5	900.2	955.9	898.2	765.8	646.8	565.1	512.7	477.5	456.6
60°	569.6	687.5	810.1	858.4	789.4	671.5	577.6	504.6	462.3	433.5	414.8
62.5°	511.7	617.3	733.0	759.2	696.1	596.4	513.3	452.6	417.9	392.2	374.6
65°	432.9	519.3	607.1	624.5	566.2	489.2	423.5	384.0	353.1	334.4	320.3
67.5°	355.0	424.4	486.7	500.7	449.6	396.2	348.7	314.3	293.4	277.8	265.9
70°	308.9	363.9	414.8	426.2	385.3	337.7	301.5	274.1	255.3	241.9	230.6
72.5°	260.1	306.0	348.3	356.0	322.6	286.3	256.5	234.9	218.3	209.7	198.8
75°	199.0	225.8	258.6	260.6	238.5	216.4	193.7	179.6	170.9	160.2	154.8
77.5°	140.5	161.5	180.3	183.9	170.8	155.7	143.0	131.9	124.5	119.6	114.6
80°	107.2	124.0	132.0	136.7	127.3	116.6	109.3	101.9	97.1	93.8	90.5
82.5°	76.6	86.9	94.5	98.1	93.0	86.5	79.2	75.0	71.4	68.6	67.5
85°	38.9	43.5	48.3	49.6	48.3	45.5	41.5	41.5	39.5	38.9	38.9
87.5°	14.0	16.8	17.2	19.1	18.5	19.3	20.3	20.8	20.4	19.7	19.0
90°	3.1	6.4	7.9	9.5	11.8	15.8	21.3	26.1	26.9	26.1	25.2
92.5°	13.9	19.6	23.0	28.4	35.9	53.7	78.8	101.2	102.6	86.6	68.9
95°	30.8	38.7	45.7	58.4	77.4	113.7	182.4	274.0	309.4	270.7	206.8
97.5°	49.3	57.7	68.4	82.9	104.3	150.0	245.7	397.9	528.3	554.2	482.6
100°	63.1	70.3	82.9	98.7	120.8	162.6	258.9	429.4	623.6	737.3	720.7
102.5°	77.1	84.1	96.7	113.2	135.3	174.0	259.5	417.5	626.8	805.5	876.8
105°	99.5	105.0	116.8	134.2	156.3	193.4	263.7	393.9	584.9	795.0	959.2
107.5°	121.6	126.9	137.8	155.0	177.3	213.3	274.6	382.2	540.1	725.6	899.8
110°	137.3	142.1	152.4	169.0	191.9	226.5	283.4	379.7	518.7	682.1	848.6





TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	151.3	156.6	166.2	182.2	205.7	239.2	292.9	380.3	504.7	651.8	801.9
115°	173.7	178.4	187.8	203.7	225.0	258.9	307.1	383.6	489.5	614.2	744.4
117.5°	195.3	200.1	208.4	223.6	245.7	277.1	322.2	389.3	482.0	590.5	701.1
120°	209.2	213.9	221.1	236.8	258.9	289.7	332.3	393.1	477.6	577.8	679.6
122.5°	221.9	226.5	234.3	250.0	272.9	301.7	341.2	397.6	475.0	567.1	662.7
125°	239.2	243.9	253.4	269.2	291.2	319.7	355.3	404.1	470.5	551.8	637.8
127.5°	253.9	260.5	270.9	286.1	308.8	336.5	368.3	411.0	467.8	537.6	613.4
130°	262.1	269.9	281.0	296.8	318.9	346.6	376.6	416.1	466.6	528.2	597.5
132.5°	270.3	278.8	290.5	306.9	329.0	355.4	384.8	421.1	466.0	520.6	582.4
135°	281.0	290.5	302.4	320.5	342.6	367.9	395.5	427.1	464.9	510.0	561.3
137.5°	292.4	301.8	314.5	332.5	353.0	378.0	403.7	432.4	464.8	502.5	544.4
140°	299.9	309.4	322.0	339.4	360.0	383.6	408.1	434.9	464.1	498.2	533.6
142.5°	307.6	316.4	329.0	345.8	365.1	388.1	411.9	436.9	464.1	493.7	524.8
145°	320.5	328.4	340.2	356.0	373.3	394.8	416.8	438.9	462.6	487.9	512.3
147.5°	333.0	340.5	351.4	364.6	380.0	400.1	419.5	439.6	459.8	481.9	502.7
150°	341.8	348.1	358.4	370.2	384.5	402.6	420.7	438.9	457.9	476.8	495.7
152.5°	349.4	355.7	364.7	375.9	388.9	405.2	421.4	437.7	454.7	472.4	488.8
155°	361.5	366.3	375.0	383.6	395.5	408.9	422.3	435.8	449.2	464.1	479.2
157.5°	371.9	375.8	383.3	390.3	400.2	411.6	422.3	432.1	443.5	456.5	468.0
160°	378.9	382.0	388.4	394.8	403.3	412.8	422.3	430.2	439.7	450.8	461.0
162.5°	384.6	387.8	392.8	398.5	405.3	413.5	421.7	428.4	436.6	445.7	454.0
165°	392.3	393.9	398.7	402.6	407.4	414.4	420.0	424.7	430.2	437.4	443.6
167.5°	398.8	400.2	403.2	406.1	409.1	414.2	418.9	421.1	424.7	429.1	433.7
170°	402.6	403.3	405.8	407.4	409.7	413.6	417.6	419.2	421.5	424.7	428.7
172.5°	405.8	405.3	407.7	408.6	410.3	413.0	415.7	416.7	417.8	420.3	422.9
175°	408.9	408.1	409.7	409.7	410.5	412.0	413.6	412.8	413.6	414.4	416.8
177.5°	409.9	409.2	410.5	410.5	410.5	411.1	412.4	411.1	410.5	411.1	412.4
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5	410.5



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5	1743.5
2.5°	1808.5	1815.9	1815.9	1817.1	1825.6	1824.5	1824.0
5°	1924.5	1935.9	1937.2	1949.3	1957.3	1954.7	1947.3
7.5°	2034.0	2055.2	2071.2	2080.2	2090.8	2097.4	2094.5
10°	2120.8	2151.6	2170.4	2183.1	2198.6	2210.0	2205.9
12.5°	2199.7	2236.3	2262.1	2283.9	2285.9	2300.6	2290.7
15°	2322.6	2361.4	2365.4	2381.5	2394.3	2392.9	2393.6
17.5°	2363.2	2375.6	2378.1	2378.5	2378.7	2374.0	2363.8
20°	2348.6	2344.0	2332.6	2323.9	2308.5	2306.4	2293.1
22.5°	2280.1	2265.2	2236.6	2217.8	2193.7	2187.5	2183.7
25°	2145.0	2112.1	2066.6	2023.0	2010.9	1987.5	1994.2
27.5°	1959.6	1908.4	1859.1	1823.7	1791.7	1756.6	1766.7
30°	1829.4	1771.7	1702.0	1648.4	1614.3	1580.7	1574.7
32.5°	1673.9	1589.4	1511.8	1464.5	1412.2	1391.0	1367.8
35°	1405.8	1323.4	1246.4	1180.0	1141.9	1112.4	1085.5
37.5°	1164.8	1069.9	1007.6	953.9	926.3	909.5	913.7
40°	1015.2	932.1	886.6	845.7	820.2	808.1	810.8
42.5°	894.0	831.8	794.4	766.3	748.3	741.6	740.0
45°	756.5	721.6	690.8	674.8	666.1	658.7	654.0
47.5°	662.7	634.3	616.9	607.3	599.8	592.2	592.1
50°	606.4	587.6	575.6	565.5	559.6	554.2	558.9
52.5°	563.5	546.4	534.3	525.3	523.1	518.3	518.2
55°	499.9	486.5	477.8	469.7	465.7	463.0	459.7
57.5°	442.0	429.3	421.2	416.2	408.5	405.8	404.8
60°	400.7	390.6	382.6	375.9	372.5	367.2	367.2
62.5°	362.6	352.6	345.1	340.0	334.5	332.3	333.0
65°	307.6	299.5	292.2	286.8	285.5	281.4	282.8
67.5°	256.9	251.6	243.8	240.9	238.3	236.1	234.5
70°	223.2	217.8	213.8	209.7	207.7	207.7	207.7
72.5°	194.7	188.3	185.9	180.8	182.0	179.9	177.7
75°	150.8	146.7	144.7	142.7	139.4	139.4	139.4
77.5°	111.0	109.8	107.3	105.2	104.4	103.7	104.0
80°	85.7	85.1	83.7	83.7	82.4	81.8	80.4
82.5°	65.9	64.2	63.4	62.8	62.6	62.4	62.2
85°	37.6	36.2	36.2	36.9	35.5	35.5	36.2
87.5°	19.2	19.5	19.2	19.2	19.7	19.2	19.2
90°	23.7	25.2	26.1	26.1	26.1	26.1	26.1
92.5°	59.1	52.4	47.6	46.9	44.3	45.0	43.7
95°	158.6	125.5	108.2	97.9	91.6	89.2	90.0
97.5°	394.9	309.4	252.5	214.7	195.3	183.8	177.1
100°	622.9	514.7	419.2	353.7	319.7	296.8	282.6
102.5°	854.6	775.5	674.3	603.1	545.1	516.5	497.4
105°	1048.3	1058.6	1032.6	983.6	934.6	900.7	889.7
107.5°	1034.1	1116.2	1154.5	1160.6	1157.9	1151.1	1136.4
110°	990.0	1091.0	1155.7	1189.6	1204.7	1211.7	1210.9



TEST NUMBER: P331395-840

CATALOG NUMBER: S122DIP-S865D725U840-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	937.5	1045.5	1119.7	1166.9	1192.0	1205.5	1209.7
115°	866.0	969.4	1050.7	1106.7	1143.1	1163.6	1170.7
117.5°	807.9	901.7	978.0	1035.1	1073.5	1095.1	1101.1
120°	777.6	861.2	933.1	988.4	1025.4	1048.3	1056.2
122.5°	752.3	831.5	896.5	946.0	982.5	1002.9	1009.5
125°	719.1	788.6	847.8	893.6	923.6	943.3	949.7
127.5°	686.9	752.5	807.1	847.1	875.1	892.2	897.3
130°	665.5	727.8	779.9	818.6	845.5	861.2	867.6
132.5°	645.3	702.6	751.5	789.6	816.4	830.9	836.6
135°	613.4	665.5	709.6	743.7	769.7	783.9	787.1
137.5°	587.9	629.3	667.8	698.8	721.2	733.7	738.4
140°	571.6	607.8	642.6	667.8	688.3	700.2	705.0
142.5°	557.0	588.2	617.3	641.4	659.9	670.6	671.5
145°	538.4	562.9	585.7	604.7	618.1	626.0	628.3
147.5°	523.2	542.3	559.1	574.7	585.4	590.8	592.2
150°	513.1	529.7	543.9	555.7	565.2	570.0	570.8
152.5°	504.9	519.0	531.3	540.6	548.8	552.3	552.4
155°	491.8	503.6	512.3	521.0	526.5	529.7	528.2
157.5°	478.6	488.5	495.2	501.4	506.0	507.5	507.5
160°	469.7	478.4	483.9	489.5	493.4	494.1	494.1
162.5°	461.5	468.9	473.2	478.7	481.4	482.2	481.5
165°	449.2	454.7	457.9	461.0	464.1	464.1	463.4
167.5°	438.0	441.7	444.6	446.1	447.8	447.6	446.7
170°	431.0	434.1	435.8	436.6	438.9	438.1	436.6
172.5°	424.7	427.3	428.2	429.0	430.1	429.3	428.4
175°	417.6	418.4	419.2	419.2	420.0	419.2	417.6
177.5°	412.4	413.0	413.0	413.0	413.0	412.4	411.1
180°	410.5	410.5	410.5	410.5	410.5	410.5	410.5

(END OF REPORT)