

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331346-927

Luminaire Tested: **S122DIP-S675D530U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331346-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIP-S675D530U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3638.7 lumens  
Efficiency: N/A  
Efficacy: 90.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331346-927

CATALOG NUMBER: S122DIP-S675D530U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331346-927

CATALOG NUMBER: S122DIP-S675D530U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	55	54	50
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	50	44	65	54	47	41	48	42	37	41	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13580	13580	13580
5°	13632	13434	13514
10°	13550	13298	13365
15°	13382	13125	13112
20°	13144	12866	12854
25°	12909	12549	12549
30°	12603	12258	12152
35°	12321	11907	11732
40°	11965	11556	11335
45°	11615	11209	10930
50°	11233	10846	10462
55°	10835	10427	10038
60°	10395	9923	9558
65°	9918	9425	8993
70°	9314	8818	8398
75°	8478	8122	7923
80°	7522	7290	6918
85°	6150	5835	5243



TEST NUMBER: P331346-927

CATALOG NUMBER: S122DIP-S675D530U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.1	2.2
10°-20°	222.5	6.1
20°-30°	327.1	9.0
30°-40°	379.9	10.4
40°-50°	379.5	10.4
50°-60°	331.0	9.1
60°-70°	244.7	6.7
70°-80°	138.6	3.8
80°-90°	39.4	1.1
90°-100°	33.9	0.9
100°-110°	105.4	2.9
110°-120°	180.1	4.9
120°-130°	236.8	6.5
130°-140°	265.8	7.3
140°-150°	260.6	7.2
150°-160°	218.6	6.0
160°-170°	145.0	4.0
170°-180°	50.7	1.4
0°-30°	628.7	17.3
0°-40°	1008.6	27.7
0°-60°	1719.1	47.2
0°-90°	2141.9	58.9
90°-120°	319.4	8.8
90°-150°	1082.6	29.8
90°-180°	1497.0	41.1
0°-180°	3638.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	841	841	841	841	841	
5°	841	838	829	835	834	80
15°	801	795	785	788	784	225
25°	725	718	704	706	704	333
35°	625	617	604	599	595	390
45°	509	503	491	482	479	392
55°	385	380	370	361	357	344
65°	260	254	247	240	235	257
75°	136	134	130	126	127	145
85°	33	32	32	29	28	38
90°	0	6	16	15	15	3
95°	24	28	29	29	28	27
105°	97	98	99	100	100	103
115°	181	183	182	182	181	179
125°	263	267	266	264	264	235
135°	340	345	346	346	344	263
145°	413	416	419	419	417	258
155°	472	473	475	477	476	217
165°	514	513	513	516	514	145
175°	534	533	532	535	533	51
180°	535	535	535	535	535	



TEST NUMBER: P331346-927

CATALOG NUMBER: S122DIP-S675D530U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	844.9	844.2	843.5	842.8	842.1	840.9	839.3	837.7	836.1	834.6	836.0
5°	841.1	840.3	839.6	838.9	838.2	836.9	834.9	832.9	830.9	828.9	830.4
7.5°	833.6	832.5	831.4	830.3	829.2	827.6	825.6	823.6	821.6	819.5	820.9
10°	826.5	825.2	823.9	822.7	821.5	819.8	817.6	815.5	813.3	811.1	812.5
12.5°	816.8	815.7	814.5	813.4	812.3	810.7	808.5	806.4	804.2	802.1	803.1
15°	800.6	799.5	798.4	797.4	796.3	794.6	792.3	789.9	787.6	785.2	786.0
17.5°	779.9	778.8	777.8	776.7	775.6	773.9	771.5	769.1	766.8	764.4	765.2
20°	765.0	764.0	762.9	761.8	760.7	758.9	756.4	753.9	751.4	748.8	749.4
22.5°	750.1	748.6	747.1	745.6	744.1	742.2	739.8	737.4	735.1	732.7	732.8
25°	724.6	723.2	721.8	720.3	718.8	716.6	713.5	710.5	707.4	704.4	704.7
27.5°	695.5	694.2	692.9	691.6	690.3	688.5	686.0	683.7	681.2	678.8	678.3
30°	676.0	674.6	673.2	671.8	670.3	668.3	665.6	662.9	660.2	657.5	657.0
32.5°	655.4	654.2	653.1	651.9	650.8	648.8	645.9	643.1	640.2	637.4	636.4
35°	625.1	623.4	621.5	619.7	617.9	615.6	612.8	609.8	607.0	604.1	603.0
37.5°	591.0	589.4	587.8	586.2	584.7	582.4	579.6	576.7	573.9	570.9	569.6
40°	567.7	566.3	564.8	563.4	562.0	559.8	556.9	554.1	551.2	548.3	546.7
42.5°	545.1	543.6	542.2	540.7	539.3	537.2	534.2	531.4	528.5	525.7	523.9
45°	508.7	507.4	506.1	504.9	503.7	501.7	499.0	496.3	493.6	490.9	488.9
47.5°	472.5	471.3	470.1	468.9	467.7	465.7	462.9	460.1	457.3	454.5	452.4
50°	447.2	446.3	445.4	444.5	443.6	441.9	439.4	436.9	434.4	431.8	429.4
52.5°	422.6	421.4	420.3	419.1	417.9	416.1	413.8	411.4	409.0	406.6	404.6
55°	384.9	383.9	382.8	381.7	380.6	379.0	376.8	374.7	372.6	370.4	368.2
57.5°	347.1	346.3	345.4	344.5	343.6	342.1	339.7	337.3	334.9	332.6	330.4
60°	321.9	321.2	320.4	319.7	319.0	317.3	314.9	312.4	309.8	307.3	305.3
62.5°	297.3	296.1	295.0	293.8	292.7	291.1	289.2	287.2	285.3	283.4	281.5
65°	259.6	258.5	257.5	256.4	255.2	253.8	252.1	250.3	248.4	246.7	245.0
67.5°	221.3	220.4	219.5	218.6	217.8	216.6	214.9	213.3	211.8	210.1	208.8
70°	197.3	196.6	195.9	195.2	194.5	193.3	191.6	190.0	188.5	186.8	185.5
72.5°	172.8	172.0	171.3	170.6	169.8	169.0	167.9	166.9	165.9	164.8	163.6
75°	135.9	135.5	135.1	134.8	134.4	133.8	132.9	132.0	131.1	130.2	129.1
77.5°	102.9	102.3	101.6	101.0	100.4	100.0	99.6	99.2	98.9	98.5	98.0
80°	80.9	80.7	80.5	80.3	80.2	79.9	79.5	79.1	78.8	78.4	77.9
82.5°	60.2	60.1	60.1	60.0	60.0	59.9	59.7	59.5	59.3	59.0	58.4
85°	33.2	33.0	32.8	32.6	32.4	32.2	32.1	31.9	31.7	31.5	31.0
87.5°	11.7	11.7	11.6	11.6	11.6	11.6	11.7	11.9	12.0	12.2	11.7
90°	0.5	1.7	2.9	4.0	5.3	7.0	9.2	11.4	13.6	15.8	15.6
92.5°	8.1	9.0	9.8	10.7	11.6	12.3	12.8	13.3	13.9	14.3	14.4
95°	23.5	24.5	25.5	26.5	27.5	28.1	28.3	28.5	28.7	28.9	28.9
97.5°	42.9	43.8	44.7	45.6	46.4	47.1	47.5	47.8	48.2	48.6	48.6
100°	57.4	58.1	58.9	59.8	60.6	61.2	61.5	61.7	62.0	62.3	62.3
102.5°	72.6	73.2	73.8	74.5	75.1	75.7	76.0	76.4	76.8	77.2	77.2
105°	97.1	97.4	97.8	98.0	98.3	98.5	98.8	98.9	99.2	99.4	99.6
107.5°	121.9	122.3	122.8	123.2	123.7	123.9	123.9	123.9	123.9	123.9	124.0
110°	137.8	138.4	138.9	139.6	140.2	140.5	140.5	140.5	140.5	140.5	140.5



TEST NUMBER: P331346-927

CATALOG NUMBER: S122DIP-S675D530U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.1	155.7	156.3	156.9	157.6	157.8	157.7	157.6	157.6	157.5	157.2
115°	180.7	181.3	181.9	182.5	183.1	183.3	183.1	182.9	182.7	182.5	182.4
117.5°	206.2	207.0	207.8	208.6	209.4	209.5	209.0	208.3	207.8	207.2	207.0
120°	223.2	223.9	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2	223.2
122.5°	238.7	239.6	240.7	241.6	242.6	242.7	242.2	241.6	241.1	240.5	240.3
125°	262.9	263.8	264.7	265.6	266.5	266.8	266.5	266.3	265.9	265.6	265.3
127.5°	286.5	287.6	288.8	289.9	291.0	291.4	291.1	290.7	290.4	290.0	289.6
130°	301.3	302.6	303.9	305.2	306.5	307.0	306.9	306.7	306.5	306.3	306.1
132.5°	317.9	319.0	320.0	321.2	322.2	322.7	322.8	322.8	322.9	322.9	322.5
135°	340.2	341.3	342.4	343.5	344.6	345.2	345.4	345.6	345.9	346.0	345.9
137.5°	363.5	364.5	365.4	366.3	367.2	367.7	368.0	368.3	368.5	368.8	368.7
140°	377.6	378.6	379.5	380.3	381.3	382.0	382.5	382.9	383.5	384.0	384.0
142.5°	392.1	393.0	394.0	394.8	395.7	396.3	396.7	397.0	397.4	397.7	397.8
145°	412.9	413.6	414.3	415.0	415.7	416.4	416.9	417.6	418.2	418.7	418.8
147.5°	431.4	432.2	433.1	434.0	434.7	435.4	435.8	436.2	436.6	437.0	437.2
150°	444.1	444.7	445.3	445.8	446.5	446.9	447.3	447.7	448.1	448.6	448.9
152.5°	455.3	455.9	456.5	457.1	457.6	458.2	458.7	459.1	459.6	460.2	460.5
155°	472.1	472.4	472.7	472.9	473.2	473.6	473.9	474.2	474.4	474.8	475.3
157.5°	486.4	486.6	486.8	487.0	487.3	487.4	487.6	487.8	488.0	488.1	488.9
160°	495.1	495.3	495.5	495.7	495.9	496.1	496.1	496.2	496.4	496.5	497.1
162.5°	503.0	503.1	503.1	503.2	503.2	503.3	503.4	503.5	503.6	503.7	504.4
165°	513.7	513.5	513.4	513.3	513.3	513.2	513.2	513.2	513.2	513.2	513.9
167.5°	522.4	522.2	521.9	521.6	521.3	521.1	521.1	521.1	521.0	521.0	521.7
170°	527.2	526.9	526.6	526.2	526.0	525.8	525.7	525.5	525.5	525.4	526.1
172.5°	530.4	530.1	529.8	529.5	529.3	529.0	528.9	528.9	528.7	528.6	529.3
175°	534.4	534.1	533.8	533.5	533.2	533.0	532.7	532.6	532.3	532.1	532.8
177.5°	536.1	535.8	535.5	535.3	535.0	534.9	534.7	534.6	534.4	534.2	534.7
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331346-927

CATALOG NUMBER: S122DIP-S675D530U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1
2.5°	837.4	838.9	840.3	840.9	840.6	840.3	840.0	839.8
5°	831.8	833.2	834.6	835.2	834.9	834.5	834.2	833.8
7.5°	822.4	823.9	825.3	825.8	825.4	825.1	824.7	824.3
10°	814.0	815.5	816.9	817.3	816.8	816.3	815.7	815.2
12.5°	804.1	805.1	806.1	806.4	806.0	805.6	805.3	804.9
15°	786.7	787.4	788.1	788.1	787.1	786.2	785.4	784.4
17.5°	766.0	766.8	767.7	767.7	766.8	766.0	765.1	764.2
20°	750.0	750.5	751.0	750.9	750.2	749.5	748.8	748.1
22.5°	732.9	733.0	733.1	732.9	732.5	732.1	731.7	731.3
25°	705.1	705.4	705.8	705.8	705.4	705.1	704.7	704.4
27.5°	677.7	677.2	676.7	676.0	675.1	674.2	673.4	672.5
30°	656.4	655.8	655.3	654.7	653.9	653.2	652.5	651.8
32.5°	635.5	634.5	633.5	632.7	632.0	631.3	630.5	629.8
35°	602.0	600.9	599.8	598.8	597.9	597.0	596.1	595.2
37.5°	568.3	567.0	565.6	564.5	563.6	562.8	562.0	561.1
40°	545.1	543.4	541.9	540.7	540.0	539.2	538.5	537.8
42.5°	522.1	520.4	518.6	517.2	516.2	515.2	514.2	513.2
45°	487.0	485.0	483.0	481.6	480.9	480.2	479.5	478.7
47.5°	450.4	448.2	446.2	444.6	443.5	442.5	441.5	440.5
50°	426.8	424.3	421.8	420.1	419.1	418.3	417.4	416.5
52.5°	402.4	400.4	398.3	396.6	395.5	394.3	393.1	391.9
55°	366.1	363.9	361.8	360.2	359.3	358.5	357.5	356.6
57.5°	328.3	326.1	324.1	322.7	321.9	321.3	320.6	319.9
60°	303.3	301.3	299.4	298.2	297.6	297.1	296.5	296.0
62.5°	279.7	277.9	276.1	274.8	274.1	273.4	272.7	272.0
65°	243.4	241.8	240.2	238.9	238.1	237.1	236.2	235.4
67.5°	207.6	206.4	205.1	204.1	203.4	202.6	201.9	201.2
70°	184.3	183.1	181.8	180.8	180.1	179.4	178.6	177.9
72.5°	162.3	161.1	159.8	158.8	158.3	157.7	157.2	156.5
75°	128.0	127.0	125.9	125.6	125.9	126.3	126.6	127.0
77.5°	97.4	96.9	96.3	95.9	95.3	94.8	94.3	93.8
80°	77.4	76.8	76.3	75.8	75.5	75.1	74.8	74.4
82.5°	57.7	57.0	56.3	55.9	55.8	55.8	55.7	55.6
85°	30.5	29.9	29.4	29.0	28.8	28.7	28.5	28.3
87.5°	11.2	10.8	10.3	10.1	9.9	9.8	9.7	9.5
90°	15.4	15.2	15.0	15.0	15.1	15.1	15.3	15.4
92.5°	14.4	14.5	14.5	14.6	14.6	14.6	14.7	14.7
95°	28.9	28.9	28.9	28.8	28.6	28.4	28.2	28.0
97.5°	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.5
100°	62.3	62.3	62.3	62.3	62.2	62.1	62.0	61.9
102.5°	77.3	77.4	77.5	77.5	77.4	77.2	77.2	77.1
105°	99.8	100.0	100.2	100.3	100.3	100.3	100.3	100.3
107.5°	124.1	124.1	124.2	124.0	123.5	123.1	122.6	122.2
110°	140.5	140.5	140.5	140.4	140.1	139.7	139.4	139.1





TEST NUMBER: P331346-927

CATALOG NUMBER: S122DIP-S675D530U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	157.0	156.8	156.5	156.3	156.1	155.8	155.6	155.4
115°	182.3	182.2	182.1	181.9	181.6	181.3	181.0	180.7
117.5°	206.8	206.5	206.3	206.0	205.7	205.4	205.1	204.8
120°	223.2	223.2	223.2	223.0	222.7	222.4	222.1	221.8
122.5°	240.0	239.8	239.6	239.3	239.1	238.8	238.7	238.4
125°	265.0	264.7	264.4	264.2	264.1	264.0	263.9	263.8
127.5°	289.3	288.9	288.6	288.2	287.9	287.6	287.2	286.9
130°	305.9	305.7	305.5	305.1	304.8	304.4	304.0	303.6
132.5°	322.0	321.5	321.2	320.8	320.4	320.1	319.8	319.5
135°	345.9	345.7	345.6	345.4	345.2	344.8	344.5	344.2
137.5°	368.6	368.5	368.4	368.2	367.8	367.4	367.0	366.6
140°	384.0	384.0	384.0	383.8	383.3	382.9	382.5	382.1
142.5°	397.8	397.9	398.0	397.8	397.4	397.0	396.6	396.2
145°	419.0	419.1	419.1	419.0	418.6	418.2	417.8	417.4
147.5°	437.4	437.7	437.9	437.8	437.4	437.0	436.7	436.3
150°	449.2	449.5	449.8	449.8	449.5	449.2	448.9	448.6
152.5°	460.9	461.3	461.7	461.7	461.3	460.9	460.5	460.2
155°	475.8	476.3	476.8	476.9	476.6	476.3	475.9	475.7
157.5°	489.5	490.2	490.9	491.0	490.5	490.0	489.6	489.0
160°	497.6	498.3	498.8	499.0	498.6	498.2	497.7	497.3
162.5°	505.0	505.7	506.4	506.5	506.0	505.6	505.1	504.6
165°	514.6	515.3	515.9	516.1	515.6	515.1	514.6	514.0
167.5°	522.4	523.2	523.9	523.9	523.4	522.9	522.4	521.8
170°	526.8	527.5	528.1	528.2	527.6	527.0	526.4	525.9
172.5°	530.0	530.8	531.4	531.5	530.9	530.3	529.7	529.1
175°	533.5	534.2	535.0	535.0	534.4	533.8	533.2	532.6
177.5°	535.2	535.7	536.1	536.1	535.7	535.2	534.7	534.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3

(END OF REPORT)