

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331381-927

Luminaire Tested: **S122DIP-S865D330U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020


Test Information

Test Method: LM-79-08
Report Number: P331381-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIP-S865D330U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3819.5 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331381-927

CATALOG NUMBER: S122DIP-S865D330U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331381-927

CATALOG NUMBER: S122DIP-S865D330U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65	61
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35	32
6	67	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17651	17651	17651
5°	17718	17462	17566
10°	17613	17285	17372
15°	17396	17061	17043
20°	17086	16725	16706
25°	16778	16311	16311
30°	16384	15933	15795
35°	16015	15477	15248
40°	15553	15022	14733
45°	15098	14570	14209
50°	14601	14099	13599
55°	14083	13551	13050
60°	13511	12897	12426
65°	12894	12248	11687
70°	12109	11462	10914
75°	11017	10555	10293
80°	9772	9484	8991
85°	7984	7595	6817



TEST NUMBER: P331381-927

CATALOG NUMBER: S122DIP-S865D330U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.8	2.7
10°-20°	289.3	7.6
20°-30°	425.2	11.1
30°-40°	493.9	12.9
40°-50°	493.3	12.9
50°-60°	430.2	11.3
60°-70°	318.1	8.3
70°-80°	180.2	4.7
80°-90°	49.3	1.3
90°-100°	11.8	0.3
100°-110°	43.3	1.1
110°-120°	115.7	3.0
120°-130°	191.1	5.0
130°-140°	203.2	5.3
140°-150°	188.9	4.9
150°-160°	151.8	4.0
160°-170°	97.8	2.6
170°-180°	33.7	0.9
0°-30°	817.2	21.4
0°-40°	1311.1	34.3
0°-60°	2234.6	58.5
0°-90°	2782.2	72.8
90°-120°	170.8	4.5
90°-150°	754.0	19.7
90°-180°	1037.0	27.1
0°-180°	3819.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1093	1093	1093	1093	1093	
5°	1093	1089	1077	1085	1084	104
15°	1041	1034	1021	1024	1020	293
25°	942	933	916	917	916	433
35°	812	802	785	779	774	507
45°	661	653	638	627	622	510
55°	500	494	481	469	464	447
65°	338	331	321	311	306	334
75°	177	174	169	163	165	189
85°	43	42	41	38	37	49
90°	0	3	5	6	7	3
95°	17	9	10	11	11	20
105°	78	81	16	18	20	83
115°	147	152	158	45	21	145
125°	208	212	216	218	219	186
135°	258	262	264	266	266	199
145°	299	299	303	305	304	187
155°	329	327	330	331	329	152
165°	347	345	346	348	346	98
175°	355	353	354	355	353	34
180°	354	354	354	354	354	



TEST NUMBER: P331381-927

CATALOG NUMBER: S122DIP-S865D330U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2
2.5°	1098.3	1097.3	1096.4	1095.5	1094.6	1093.1	1091.0	1088.9	1086.9	1084.8	1086.7
5°	1093.2	1092.3	1091.4	1090.4	1089.5	1087.7	1085.2	1082.6	1080.1	1077.4	1079.3
7.5°	1083.5	1082.1	1080.7	1079.2	1077.8	1075.7	1073.1	1070.5	1067.9	1065.2	1067.1
10°	1074.3	1072.7	1071.0	1069.4	1067.8	1065.6	1062.7	1059.9	1057.2	1054.3	1056.2
12.5°	1061.7	1060.3	1058.8	1057.3	1055.9	1053.8	1051.0	1048.1	1045.4	1042.6	1043.9
15°	1040.7	1039.3	1037.8	1036.5	1035.1	1032.8	1029.8	1026.7	1023.7	1020.7	1021.6
17.5°	1013.8	1012.3	1011.0	1009.6	1008.1	1005.9	1002.8	999.7	996.6	993.6	994.7
20°	994.4	993.0	991.7	990.2	988.8	986.5	983.2	979.9	976.7	973.4	974.1
22.5°	975.1	973.1	971.1	969.2	967.3	964.7	961.6	958.5	955.5	952.4	952.5
25°	941.8	940.0	938.1	936.3	934.4	931.4	927.5	923.5	919.6	915.6	916.1
27.5°	904.0	902.4	900.6	899.0	897.3	894.8	891.8	888.6	885.5	882.3	881.7
30°	878.8	876.9	875.0	873.2	871.3	868.6	865.1	861.7	858.1	854.6	853.9
32.5°	851.9	850.4	848.9	847.4	845.9	843.3	839.6	835.9	832.3	828.5	827.3
35°	812.5	810.2	807.9	805.6	803.2	800.2	796.5	792.7	788.9	785.2	783.9
37.5°	768.2	766.1	764.1	762.0	760.0	757.1	753.4	749.6	745.8	742.1	740.4
40°	737.9	736.1	734.2	732.3	730.5	727.6	723.9	720.2	716.4	712.7	710.6
42.5°	708.5	706.6	704.7	702.9	701.0	698.2	694.5	690.8	687.0	683.3	681.0
45°	661.2	659.6	657.9	656.3	654.7	652.0	648.6	645.1	641.6	638.1	635.5
47.5°	614.1	612.6	611.0	609.5	607.9	605.3	601.7	598.0	594.4	590.7	588.0
50°	581.3	580.1	579.0	577.8	576.6	574.4	571.2	567.8	564.6	561.3	558.1
52.5°	549.4	547.8	546.3	544.7	543.2	540.9	537.8	534.7	531.6	528.5	525.9
55°	500.3	499.0	497.6	496.1	494.7	492.7	489.9	487.0	484.3	481.4	478.6
57.5°	451.1	450.0	448.9	447.8	446.7	444.6	441.5	438.4	435.3	432.2	429.5
60°	418.4	417.4	416.5	415.6	414.6	412.6	409.2	406.0	402.7	399.4	396.9
62.5°	386.4	384.9	383.4	381.9	380.4	378.4	375.9	373.4	370.8	368.4	366.0
65°	337.5	336.0	334.6	333.2	331.8	329.9	327.6	325.3	323.0	320.6	318.5
67.5°	287.6	286.5	285.3	284.2	283.1	281.5	279.4	277.3	275.2	273.1	271.5
70°	256.5	255.6	254.6	253.7	252.8	251.2	249.1	247.0	244.9	242.8	241.2
72.5°	224.5	223.6	222.7	221.7	220.8	219.7	218.3	217.0	215.6	214.2	212.6
75°	176.6	176.1	175.6	175.2	174.8	173.9	172.8	171.6	170.4	169.2	167.9
77.5°	133.7	132.9	132.1	131.3	130.6	129.9	129.4	129.0	128.5	128.0	127.3
80°	105.1	104.9	104.6	104.4	104.2	103.9	103.4	102.9	102.4	102.0	101.2
82.5°	78.2	78.2	78.1	78.0	78.0	77.9	77.6	77.3	77.0	76.8	75.8
85°	43.1	42.9	42.6	42.4	42.1	41.9	41.7	41.4	41.2	41.0	40.3
87.5°	15.2	15.0	14.7	14.4	14.2	13.9	13.6	13.4	13.1	12.8	12.3
90°	0.2	0.9	1.5	2.1	2.8	3.3	3.7	4.2	4.7	5.1	5.4
92.5°	5.1	5.1	5.1	5.0	4.9	5.1	5.2	5.5	5.7	5.9	6.1
95°	16.6	14.7	12.9	11.0	9.1	8.4	8.8	9.2	9.6	10.0	10.3
97.5°	33.0	27.7	22.4	17.2	11.9	9.7	10.6	11.5	12.4	13.4	13.6
100°	45.3	37.5	29.7	21.9	14.2	10.7	11.7	12.7	13.6	14.6	15.1
102.5°	58.9	57.2	55.5	53.9	52.3	47.4	39.3	31.2	23.1	15.0	15.6
105°	77.9	79.5	81.3	83.0	84.7	77.8	62.3	46.7	31.1	15.6	16.2
107.5°	99.5	100.9	102.3	103.7	105.0	96.4	77.8	59.2	40.5	21.9	21.2
110°	113.4	114.6	115.9	117.1	118.3	110.6	94.2	77.7	61.2	44.8	39.1



TEST NUMBER: P331381-927

CATALOG NUMBER: S122DIP-S865D330U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.6	127.6	128.7	129.8	130.8	129.3	125.2	121.2	117.1	113.0	92.3
115°	147.3	148.2	149.2	150.2	151.1	152.3	153.8	155.2	156.6	158.0	131.7
117.5°	165.8	166.8	167.9	169.1	170.1	171.1	172.1	173.1	174.0	175.1	168.7
120°	179.3	180.1	181.0	181.9	182.7	183.6	184.7	185.7	186.7	187.7	188.5
122.5°	190.8	191.7	192.6	193.5	194.4	195.4	196.5	197.6	198.8	199.9	200.3
125°	208.3	209.0	209.7	210.5	211.2	212.1	213.2	214.3	215.3	216.4	216.8
127.5°	224.0	224.9	225.7	226.6	227.4	228.1	228.9	229.8	230.6	231.4	232.0
130°	234.1	235.0	235.9	236.9	237.7	238.5	239.2	239.8	240.4	241.1	241.6
132.5°	244.4	245.1	245.9	246.7	247.5	248.1	248.7	249.4	250.0	250.6	251.2
135°	257.7	258.6	259.5	260.4	261.3	262.1	262.5	263.1	263.6	264.1	264.7
137.5°	271.2	271.8	272.4	273.1	273.7	274.3	274.9	275.4	276.1	276.6	277.2
140°	280.0	280.4	280.8	281.3	281.8	282.3	283.0	283.6	284.2	284.8	285.3
142.5°	287.3	287.7	288.1	288.6	289.0	289.5	290.3	291.0	291.7	292.4	292.9
145°	298.9	298.9	298.8	298.7	298.7	299.1	300.1	301.1	302.1	303.0	303.4
147.5°	309.0	308.8	308.6	308.3	308.2	308.5	309.4	310.5	311.4	312.4	312.6
150°	315.5	315.1	314.7	314.3	313.9	314.3	315.1	316.1	317.0	317.9	318.2
152.5°	321.1	320.7	320.2	319.7	319.3	319.5	320.4	321.2	322.1	323.0	323.3
155°	329.2	328.6	328.1	327.6	327.1	327.2	327.9	328.5	329.2	329.9	330.3
157.5°	335.4	335.0	334.5	334.1	333.7	333.7	334.2	334.7	335.2	335.6	336.0
160°	339.1	338.8	338.4	338.1	337.8	337.8	338.1	338.4	338.8	339.1	339.5
162.5°	342.4	342.1	341.7	341.4	341.0	341.0	341.3	341.6	341.9	342.2	342.6
165°	346.8	346.5	346.1	345.8	345.5	345.4	345.5	345.7	345.9	346.0	346.4
167.5°	350.1	349.7	349.4	349.0	348.7	348.6	348.8	349.0	349.1	349.3	349.7
170°	352.0	351.6	351.3	350.9	350.5	350.5	350.5	350.7	350.8	350.9	351.3
172.5°	353.2	352.8	352.4	352.1	351.8	351.6	351.8	351.9	352.0	352.1	352.5
175°	354.7	354.3	353.9	353.6	353.2	353.0	353.2	353.2	353.4	353.5	353.9
177.5°	355.0	354.7	354.3	354.0	353.7	353.6	353.6	353.7	353.7	353.8	354.1
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9



TEST NUMBER: P331381-927

CATALOG NUMBER: S122DIP-S865D330U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2
2.5°	1088.5	1090.4	1092.3	1093.1	1092.7	1092.3	1091.9	1091.5
5°	1081.2	1083.1	1085.0	1085.6	1085.2	1084.7	1084.3	1083.8
7.5°	1069.0	1070.9	1072.8	1073.4	1072.9	1072.4	1071.9	1071.3
10°	1058.0	1059.9	1061.8	1062.4	1061.7	1061.0	1060.3	1059.6
12.5°	1045.2	1046.5	1047.8	1048.2	1047.7	1047.2	1046.6	1046.2
15°	1022.5	1023.5	1024.5	1024.3	1023.2	1022.0	1020.8	1019.6
17.5°	995.7	996.8	997.9	997.8	996.7	995.6	994.5	993.4
20°	974.8	975.5	976.2	976.0	975.2	974.2	973.3	972.3
22.5°	952.7	952.8	952.9	952.8	952.1	951.6	951.0	950.5
25°	916.6	917.0	917.4	917.4	917.0	916.6	916.1	915.6
27.5°	881.0	880.3	879.6	878.7	877.5	876.4	875.3	874.2
30°	853.2	852.5	851.8	851.0	850.1	849.1	848.2	847.2
32.5°	826.0	824.7	823.5	822.4	821.5	820.5	819.6	818.6
35°	782.4	781.0	779.7	778.3	777.2	776.0	774.8	773.6
37.5°	738.7	737.0	735.2	733.8	732.7	731.6	730.5	729.3
40°	708.5	706.4	704.3	702.7	701.9	700.9	700.0	699.0
42.5°	678.7	676.4	674.1	672.3	671.0	669.7	668.4	667.1
45°	633.0	630.3	627.8	626.1	625.1	624.2	623.2	622.3
47.5°	585.3	582.7	580.0	577.9	576.6	575.2	573.9	572.5
50°	554.8	551.5	548.3	546.1	544.9	543.7	542.6	541.4
52.5°	523.1	520.4	517.7	515.6	514.0	512.5	511.0	509.4
55°	475.9	473.0	470.2	468.3	467.1	465.9	464.8	463.6
57.5°	426.7	424.0	421.2	419.4	418.5	417.6	416.8	415.8
60°	394.3	391.7	389.2	387.5	386.8	386.1	385.4	384.8
62.5°	363.5	361.2	358.8	357.2	356.2	355.4	354.5	353.6
65°	316.4	314.3	312.2	310.5	309.4	308.2	307.0	305.9
67.5°	269.8	268.2	266.6	265.3	264.4	263.4	262.4	261.5
70°	239.6	237.9	236.3	235.0	234.1	233.1	232.2	231.2
72.5°	211.0	209.3	207.7	206.5	205.7	205.0	204.2	203.5
75°	166.4	165.0	163.7	163.2	163.7	164.1	164.5	165.0
77.5°	126.7	126.0	125.2	124.5	123.9	123.3	122.6	121.9
80°	100.5	99.9	99.2	98.5	98.1	97.7	97.2	96.7
82.5°	74.9	74.1	73.2	72.7	72.6	72.5	72.4	72.3
85°	39.6	38.9	38.2	37.7	37.5	37.2	37.0	36.8
87.5°	11.8	11.2	10.8	10.5	10.3	10.1	10.0	9.8
90°	5.7	5.9	6.3	6.5	6.6	6.7	6.8	6.9
92.5°	6.3	6.4	6.5	6.7	6.7	6.8	6.8	6.9
95°	10.5	10.9	11.1	11.2	11.2	11.1	11.1	11.0
97.5°	13.9	14.0	14.3	14.4	14.5	14.6	14.7	14.7
100°	15.5	16.0	16.4	16.7	16.8	17.0	17.0	17.2
102.5°	16.2	16.8	17.3	17.7	17.9	18.1	18.2	18.4
105°	16.9	17.5	18.1	18.5	18.8	19.0	19.3	19.5
107.5°	20.6	20.0	19.3	19.1	19.3	19.6	19.8	20.0
110°	33.4	27.7	22.0	19.3	19.6	19.8	20.0	20.2



TEST NUMBER: P331381-927

CATALOG NUMBER: S122DIP-S865D330U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	71.5	50.8	30.0	19.7	19.9	20.0	20.3	20.4
115°	105.4	79.0	52.6	37.4	33.3	29.2	25.1	21.0
117.5°	162.3	155.9	149.6	139.7	126.2	112.7	99.3	85.8
120°	189.1	189.8	190.4	187.0	179.3	171.6	163.9	156.2
122.5°	200.7	201.1	201.5	200.9	199.5	198.0	196.5	195.0
125°	217.2	217.6	218.0	218.3	218.5	218.6	218.8	219.0
127.5°	232.6	233.1	233.7	234.0	234.1	234.1	234.1	234.2
130°	242.2	242.9	243.5	243.8	243.8	243.7	243.7	243.6
132.5°	251.8	252.2	252.8	253.0	252.9	252.9	252.9	252.8
135°	265.2	265.8	266.3	266.6	266.5	266.3	266.3	266.1
137.5°	277.7	278.3	278.8	279.0	278.8	278.7	278.5	278.3
140°	285.8	286.4	286.8	287.0	286.7	286.5	286.1	285.8
142.5°	293.3	293.8	294.3	294.4	294.1	293.8	293.5	293.2
145°	303.8	304.2	304.6	304.7	304.4	304.1	303.8	303.5
147.5°	312.9	313.2	313.5	313.5	313.3	313.1	312.8	312.6
150°	318.5	318.9	319.2	319.2	319.0	318.7	318.4	318.1
152.5°	323.7	324.0	324.3	324.3	323.9	323.6	323.2	322.8
155°	330.6	330.9	331.3	331.2	330.7	330.3	329.9	329.4
157.5°	336.4	336.8	337.2	337.2	336.7	336.3	335.8	335.4
160°	339.8	340.2	340.5	340.5	340.1	339.7	339.3	338.9
162.5°	342.9	343.3	343.7	343.7	343.2	342.7	342.2	341.7
165°	346.8	347.2	347.6	347.6	347.2	346.8	346.4	346.0
167.5°	350.1	350.5	350.9	350.8	350.3	349.7	349.3	348.7
170°	351.7	352.1	352.5	352.4	352.0	351.4	350.9	350.4
172.5°	352.9	353.3	353.7	353.7	353.2	352.7	352.1	351.6
175°	354.3	354.7	355.1	355.0	354.4	353.9	353.2	352.7
177.5°	354.4	354.7	355.1	355.0	354.6	354.2	353.8	353.4
180°	353.9	353.9	353.9	353.9	353.9	353.9	353.9	353.9

(END OF REPORT)