

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331672-840

Luminaire Tested: **S122RDIP-S485D1080U840-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331672-840  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S485D1080U840-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6065.5 lumens  
Efficiency: N/A  
Efficacy: 122.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331672-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331672-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18
4	71	61	53	48	63	55	49	44	44	39	36	33	30	28	23	21	20	16
5	65	54	47	41	58	49	42	37	39	34	31	30	26	24	21	19	17	14
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	15	12
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	17	15	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13454	13454	13454
5°	13506	13287	13361
10°	13404	13070	12959
15°	13249	12682	12318
20°	13036	12129	11519
25°	12818	11501	10750
30°	12515	10856	9758
35°	12220	10153	8889
40°	11921	9428	7885
45°	11574	8611	6976
50°	11215	7784	6081
55°	10849	6899	5222
60°	10424	5968	4334
65°	9941	5012	3947
70°	9361	4131	3635
75°	8659	3762	3387
80°	7643	3366	3087
85°	6002	2649	2649



TEST NUMBER: P331672-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.0	1.3
10°-20°	214.2	3.5
20°-30°	300.8	5.0
30°-40°	328.0	5.4
40°-50°	301.6	5.0
50°-60°	236.8	3.9
60°-70°	154.4	2.5
70°-80°	79.6	1.3
80°-90°	24.3	0.4
90°-100°	49.5	0.8
100°-110°	181.5	3.0
110°-120°	485.1	8.0
120°-130°	800.8	13.2
130°-140°	851.6	14.0
140°-150°	791.6	13.1
150°-160°	636.4	10.5
160°-170°	410.1	6.8
170°-180°	141.2	2.3
0°-30°	593.0	9.8
0°-40°	921.0	15.2
0°-60°	1459.4	24.1
0°-90°	1717.7	28.3
90°-120°	716.1	11.8
90°-150°	3160.1	52.1
90°-180°	4348.0	71.7
0°-180°	6065.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	833	829	820	826	824	79
15°	793	783	759	745	737	223
25°	720	694	646	616	603	331
35°	620	580	515	469	451	388
45°	507	455	377	326	306	391
55°	385	325	245	202	186	344
65°	260	199	131	107	103	258
75°	139	87	60	55	54	147
85°	32	17	14	14	14	38
90°	1	13	22	27	29	5
95°	70	37	42	47	46	85
105°	326	340	65	77	82	349
115°	617	636	662	189	88	608
125°	873	887	907	914	918	778
135°	1080	1097	1107	1117	1115	834
145°	1253	1253	1270	1277	1272	783
155°	1380	1371	1383	1388	1381	635
165°	1454	1448	1450	1457	1450	410
175°	1487	1480	1482	1488	1478	141
180°	1484	1484	1484	1484	1484	



TEST NUMBER: P331672-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	836.4	835.8	835.1	834.4	833.7	832.6	831.2	829.7	828.2	826.8	828.1
5°	833.3	832.5	831.7	830.9	830.0	828.5	826.4	824.2	822.0	819.8	821.3
7.5°	824.8	823.7	822.7	821.6	820.6	818.8	816.3	813.7	811.2	808.7	809.1
10°	817.6	816.4	815.2	814.1	812.8	810.6	807.3	803.9	800.5	797.2	796.7
12.5°	808.5	807.1	805.6	804.2	802.7	799.9	795.6	791.3	787.0	782.7	781.8
15°	792.6	790.8	789.0	787.1	785.3	781.5	775.8	770.1	764.5	758.7	755.6
17.5°	773.3	770.4	767.6	764.8	761.9	756.9	749.6	742.3	735.0	727.6	723.9
20°	758.7	755.4	752.0	748.7	745.3	739.4	731.0	722.7	714.3	705.9	701.8
22.5°	743.1	739.3	735.5	731.7	728.0	721.4	712.0	702.5	693.1	683.6	678.2
25°	719.5	714.2	708.8	703.4	698.0	689.8	678.7	667.7	656.6	645.6	638.7
27.5°	691.2	685.3	679.4	673.7	667.8	658.6	646.2	633.7	621.3	608.7	600.8
30°	671.3	664.9	658.5	652.2	645.8	635.9	622.5	609.0	595.6	582.3	573.7
32.5°	652.0	644.5	637.0	629.7	622.2	611.6	597.9	584.2	570.6	556.9	547.1
35°	620.0	611.4	602.9	594.3	585.7	574.1	559.4	544.6	529.9	515.1	504.5
37.5°	587.9	578.6	569.2	559.8	550.5	537.9	522.2	506.4	490.7	475.0	463.3
40°	565.6	555.6	545.5	535.5	525.4	512.3	496.0	479.8	463.5	447.3	435.4
42.5°	542.7	532.1	521.5	511.0	500.4	486.7	469.9	453.0	436.3	419.5	407.2
45°	506.9	495.6	484.3	473.1	461.9	447.5	429.9	412.3	394.7	377.1	365.2
47.5°	471.8	459.9	448.1	436.2	424.2	409.2	391.0	372.8	354.7	336.5	324.7
50°	446.5	434.5	422.7	410.8	398.9	383.7	365.3	346.9	328.4	309.9	298.4
52.5°	421.7	409.3	396.9	384.5	372.0	356.8	338.7	320.7	302.7	284.7	273.5
55°	385.4	372.3	359.2	346.2	333.2	317.5	299.4	281.3	263.2	245.1	235.1
57.5°	348.1	334.8	321.3	307.9	294.5	279.1	261.8	244.3	226.9	209.5	200.3
60°	322.8	309.4	296.0	282.6	269.1	253.9	236.6	219.3	202.1	184.8	176.2
62.5°	298.0	284.7	271.2	257.8	244.4	229.5	213.1	196.6	180.2	163.7	155.5
65°	260.2	246.6	233.1	219.4	205.9	191.6	176.5	161.4	146.3	131.2	125.5
67.5°	223.7	210.3	196.7	183.3	169.8	156.2	142.7	129.2	115.5	102.0	99.4
70°	198.3	185.3	172.2	159.2	146.0	133.7	122.2	110.6	99.1	87.5	85.8
72.5°	174.2	161.7	149.2	136.6	124.1	113.2	103.9	94.6	85.3	76.0	74.6
75°	138.8	127.0	115.3	103.6	91.8	83.1	77.5	71.7	66.0	60.3	59.2
77.5°	103.9	93.6	83.3	73.0	62.8	56.2	53.5	50.8	48.0	45.2	44.5
80°	82.2	73.6	65.1	56.6	48.0	42.9	41.2	39.6	37.9	36.2	35.5
82.5°	62.3	55.6	49.0	42.3	35.6	31.7	30.6	29.4	28.3	27.2	26.8
85°	32.4	28.9	25.3	21.9	18.4	16.4	15.9	15.3	14.8	14.3	14.3
87.5°	9.9	9.3	8.8	8.2	7.7	7.6	8.0	8.4	8.8	9.1	9.2
90°	1.1	3.7	6.4	9.0	11.6	13.8	15.8	17.7	19.6	21.5	22.6
92.5°	21.7	21.4	21.2	21.0	20.7	21.1	22.0	23.0	23.9	24.9	25.5
95°	69.8	61.9	54.0	46.2	38.3	35.1	36.9	38.6	40.2	41.9	43.0
97.5°	138.5	116.3	94.1	71.9	49.8	40.6	44.4	48.3	52.2	56.0	57.0
100°	190.1	157.3	124.6	92.0	59.3	44.9	49.0	53.1	57.2	61.2	63.1
102.5°	246.7	239.7	232.9	225.9	219.0	198.6	164.7	130.8	96.8	62.9	65.4
105°	326.4	333.6	340.6	347.8	355.0	326.0	260.8	195.7	130.6	65.4	68.1
107.5°	417.2	422.9	428.7	434.4	440.3	404.1	326.0	247.9	169.8	91.7	89.0
110°	475.5	480.6	485.6	490.6	495.6	463.6	394.7	325.8	256.8	187.8	164.0



TEST NUMBER: P331672-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	530.6	535.0	539.4	543.8	548.3	542.0	524.9	508.0	490.9	473.8	386.9
115°	617.3	621.4	625.4	629.4	633.5	638.5	644.5	650.5	656.4	662.4	551.9
117.5°	694.8	699.3	703.9	708.4	713.0	717.2	721.3	725.5	729.5	733.7	706.9
120°	751.4	755.1	758.6	762.2	765.8	769.7	774.1	778.3	782.6	786.9	789.7
122.5°	799.6	803.3	807.1	810.9	814.7	818.9	823.5	828.2	832.9	837.6	839.3
125°	872.8	875.9	879.0	882.1	885.1	889.0	893.5	898.1	902.6	907.2	908.8
127.5°	939.2	942.6	946.0	949.5	952.9	956.2	959.7	963.0	966.4	969.9	972.3
130°	981.2	985.0	988.9	992.7	996.4	999.7	1002.3	1004.9	1007.5	1010.2	1012.8
132.5°	1024.1	1027.4	1030.7	1033.9	1037.1	1040.1	1042.7	1045.3	1047.9	1050.6	1052.8
135°	1079.9	1083.8	1087.6	1091.5	1095.2	1098.2	1100.3	1102.5	1104.7	1106.8	1109.2
137.5°	1136.4	1139.1	1141.8	1144.5	1147.1	1149.6	1152.2	1154.6	1157.0	1159.4	1161.7
140°	1173.4	1175.3	1177.2	1179.1	1181.0	1183.3	1185.9	1188.5	1191.1	1193.8	1195.9
142.5°	1204.3	1206.0	1207.7	1209.4	1211.1	1213.6	1216.5	1219.5	1222.5	1225.6	1227.5
145°	1252.8	1252.5	1252.3	1252.1	1251.8	1253.7	1257.8	1261.8	1266.0	1270.0	1271.6
147.5°	1295.2	1294.2	1293.3	1292.4	1291.5	1293.0	1297.1	1301.0	1305.0	1309.1	1310.3
150°	1322.6	1320.9	1319.3	1317.6	1316.0	1317.0	1320.8	1324.6	1328.5	1332.2	1333.7
152.5°	1345.7	1343.9	1342.0	1340.2	1338.4	1339.2	1342.8	1346.5	1350.1	1353.7	1355.1
155°	1379.5	1377.4	1375.2	1373.0	1370.9	1371.3	1374.1	1377.0	1379.9	1382.7	1384.1
157.5°	1405.9	1404.1	1402.3	1400.5	1398.7	1398.8	1400.8	1402.7	1404.7	1406.7	1408.4
160°	1421.4	1420.0	1418.5	1417.0	1415.6	1415.6	1417.0	1418.5	1420.0	1421.4	1422.8
162.5°	1435.1	1433.7	1432.2	1430.8	1429.4	1429.3	1430.5	1431.8	1433.0	1434.2	1435.8
165°	1453.6	1452.1	1450.7	1449.3	1447.8	1447.4	1448.1	1449.0	1449.7	1450.4	1452.0
167.5°	1467.3	1465.9	1464.4	1463.0	1461.6	1461.2	1461.9	1462.5	1463.2	1463.9	1465.5
170°	1475.0	1473.6	1472.2	1470.8	1469.4	1468.8	1469.4	1469.8	1470.3	1470.8	1472.4
172.5°	1480.2	1478.7	1477.3	1475.9	1474.5	1474.0	1474.5	1474.9	1475.4	1475.9	1477.5
175°	1486.8	1485.2	1483.5	1481.9	1480.2	1479.6	1480.1	1480.6	1481.0	1481.5	1483.2
177.5°	1487.9	1486.6	1485.2	1483.9	1482.6	1482.0	1482.2	1482.4	1482.6	1482.8	1484.1
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6



TEST NUMBER: P331672-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	833.3	833.3	833.3	833.3	833.3	833.3	833.3	833.3
2.5°	829.4	830.8	832.1	832.6	832.4	832.1	831.8	831.6
5°	822.8	824.4	825.9	826.4	825.9	825.4	824.9	824.4
7.5°	809.5	809.9	810.4	810.2	809.3	808.4	807.6	806.7
10°	796.2	795.7	795.2	794.5	793.5	792.4	791.4	790.4
12.5°	780.9	780.0	779.1	777.8	776.1	774.5	772.7	771.1
15°	752.3	749.2	746.0	743.6	741.8	740.2	738.5	736.9
17.5°	720.0	716.3	712.5	709.1	706.3	703.4	700.5	697.6
20°	697.5	693.4	689.1	685.2	681.6	677.8	674.2	670.4
22.5°	672.8	667.4	662.1	657.9	655.2	652.5	649.7	646.9
25°	631.9	625.0	618.1	613.4	610.9	608.3	605.9	603.4
27.5°	592.8	584.7	576.7	570.8	566.7	562.8	558.8	554.8
30°	565.1	556.6	548.1	541.5	536.9	532.5	528.0	523.4
32.5°	537.3	527.7	517.9	510.9	506.6	502.4	498.1	493.8
35°	494.0	483.4	472.9	465.7	462.1	458.4	454.7	451.0
37.5°	451.7	440.1	428.5	420.5	416.4	412.1	407.9	403.6
40°	423.4	411.5	399.6	391.5	387.2	382.8	378.4	374.1
42.5°	394.9	382.5	370.3	362.0	357.8	353.6	349.3	345.1
45°	353.3	341.4	329.5	321.5	317.5	313.5	309.4	305.5
47.5°	312.9	301.0	289.2	281.4	277.8	274.2	270.4	266.8
50°	286.8	275.3	263.7	256.2	252.7	249.1	245.6	242.1
52.5°	262.3	251.2	239.9	232.8	229.5	226.3	223.0	219.7
55°	225.0	214.9	204.9	198.2	195.1	191.9	188.7	185.5
57.5°	191.1	181.9	172.7	166.7	164.0	161.4	158.6	155.9
60°	167.6	159.2	150.6	145.0	142.3	139.6	136.9	134.2
62.5°	147.3	139.3	131.1	126.2	124.6	123.0	121.4	119.8
65°	119.9	114.1	108.5	105.3	104.8	104.3	103.8	103.3
67.5°	96.7	94.1	91.5	90.0	89.4	88.9	88.4	87.8
70°	84.1	82.5	80.8	79.6	79.0	78.3	77.6	77.0
72.5°	73.2	71.8	70.4	69.5	69.1	68.7	68.3	67.9
75°	58.0	56.9	55.6	54.9	54.8	54.6	54.4	54.3
77.5°	43.9	43.2	42.6	42.1	41.8	41.6	41.3	41.0
80°	34.8	34.2	33.5	33.2	33.2	33.2	33.2	33.2
82.5°	26.4	26.0	25.5	25.3	25.3	25.3	25.3	25.3
85°	14.3	14.3	14.3	14.3	14.3	14.3	14.3	14.3
87.5°	9.3	9.4	9.5	9.6	9.7	9.8	9.9	10.0
90°	23.8	25.0	26.3	27.1	27.6	28.1	28.5	29.0
92.5°	26.2	26.8	27.4	27.9	28.2	28.4	28.7	29.0
95°	44.2	45.4	46.7	47.2	46.9	46.7	46.4	46.2
97.5°	58.0	58.9	59.9	60.5	60.8	61.1	61.3	61.6
100°	65.0	67.0	68.9	70.0	70.5	71.0	71.5	71.9
102.5°	67.9	70.4	72.8	74.4	75.0	75.7	76.4	77.1
105°	70.7	73.3	75.9	77.8	78.8	79.7	80.6	81.6
107.5°	86.3	83.6	81.0	80.2	81.1	82.0	83.0	83.9
110°	140.2	116.3	92.4	81.0	81.9	82.9	83.8	84.8





TEST NUMBER: P331672-840

CATALOG NUMBER: S122RDIP-S485D1080U840-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	299.8	212.8	125.7	82.6	83.4	84.1	84.9	85.6
115°	441.4	331.0	220.6	156.7	139.6	122.4	105.2	88.1
117.5°	680.2	653.5	626.8	585.2	528.8	472.3	415.9	359.4
120°	792.6	795.5	798.4	783.7	751.4	719.2	687.0	654.9
122.5°	841.0	842.7	844.4	842.1	836.0	829.7	823.4	817.2
125°	910.5	912.1	913.8	915.0	915.7	916.5	917.2	917.9
127.5°	974.7	977.1	979.6	980.9	981.0	981.2	981.3	981.4
130°	1015.4	1018.0	1020.7	1021.9	1021.7	1021.4	1021.2	1021.0
132.5°	1055.0	1057.3	1059.6	1060.6	1060.3	1060.1	1059.9	1059.6
135°	1111.6	1114.0	1116.3	1117.3	1116.8	1116.3	1115.9	1115.4
137.5°	1164.1	1166.4	1168.7	1169.5	1168.7	1167.9	1167.1	1166.3
140°	1198.1	1200.2	1202.3	1202.9	1201.6	1200.4	1199.2	1198.1
142.5°	1229.4	1231.4	1233.3	1233.8	1232.5	1231.3	1230.2	1229.0
145°	1273.3	1275.0	1276.7	1276.9	1275.8	1274.6	1273.3	1272.1
147.5°	1311.5	1312.8	1314.0	1314.1	1313.1	1312.1	1311.1	1310.1
150°	1335.1	1336.6	1338.0	1338.1	1336.9	1335.7	1334.5	1333.3
152.5°	1356.6	1358.1	1359.5	1359.4	1357.8	1356.2	1354.6	1353.1
155°	1385.5	1387.0	1388.5	1388.2	1386.2	1384.4	1382.5	1380.6
157.5°	1410.0	1411.6	1413.2	1413.1	1411.3	1409.4	1407.5	1405.6
160°	1424.2	1425.6	1427.0	1426.9	1425.3	1423.6	1422.0	1420.3
162.5°	1437.4	1439.1	1440.8	1440.5	1438.5	1436.4	1434.3	1432.3
165°	1453.7	1455.3	1457.0	1457.0	1455.3	1453.7	1452.0	1450.4
167.5°	1467.2	1468.8	1470.6	1470.3	1468.1	1466.0	1463.9	1461.7
170°	1474.1	1475.7	1477.4	1477.1	1475.0	1472.9	1470.8	1468.5
172.5°	1479.3	1480.9	1482.6	1482.4	1480.2	1478.0	1475.9	1473.7
175°	1484.8	1486.5	1488.1	1487.8	1485.4	1483.0	1480.7	1478.2
177.5°	1485.4	1486.7	1488.1	1487.9	1486.2	1484.5	1482.8	1481.1
180°	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6	1483.6

(END OF REPORT)