

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331744-927

Luminaire Tested: **S122RDIP-S1005D530U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331744-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIP-S1005D530U927-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4434.9 lumens  
Efficiency: N/A  
Efficacy: 80.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331744-927

CATALOG NUMBER: S122RDIP-S1005D530U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331744-927

CATALOG NUMBER: S122RDIP-S1005D530U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	101	97	93	90	95	91	88	85	80	78	75	70	68	66	60	59	58	54
2	93	85	79	74	87	80	75	71	71	67	63	62	59	56	54	52	50	46
3	85	76	68	63	79	71	65	60	63	58	54	55	52	48	48	46	43	40
4	78	67	60	54	73	64	57	51	56	51	47	50	46	42	44	40	38	34
5	72	60	52	47	67	57	50	45	51	45	41	45	40	37	40	36	33	30
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	30	27
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	27	24
8	57	45	37	32	54	43	36	31	39	33	29	34	30	26	31	27	24	22
9	54	41	34	29	50	39	33	28	36	30	26	32	27	24	28	25	22	20
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	26	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	21660	21660	21660
5°	21742	21389	21507
10°	21577	21040	20859
15°	21329	20415	19826
20°	20984	19524	18545
25°	20633	18513	17302
30°	20144	17473	15709
35°	19669	16344	14310
40°	19191	15173	12690
45°	18630	13860	11227
50°	18053	12534	9789
55°	17464	11108	8408
60°	16779	9607	6978
65°	16000	8073	6357
70°	15073	6652	5844
75°	13936	6057	5452
80°	12301	5421	4965
85°	9670	4279	4279



TEST NUMBER: P331744-927

CATALOG NUMBER: S122RDIP-S1005D530U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.6	2.8
10°-20°	344.8	7.8
20°-30°	484.2	10.9
30°-40°	528.0	11.9
40°-50°	485.4	10.9
50°-60°	381.3	8.6
60°-70°	248.6	5.6
70°-80°	128.2	2.9
80°-90°	34.7	0.8
90°-100°	19.1	0.4
100°-110°	69.9	1.6
110°-120°	186.8	4.2
120°-130°	308.4	7.0
130°-140°	328.0	7.4
140°-150°	304.8	6.9
150°-160°	245.1	5.5
160°-170°	157.9	3.6
170°-180°	54.4	1.2
0°-30°	954.5	21.5
0°-40°	1482.5	33.4
0°-60°	2349.2	53.0
0°-90°	2760.6	62.2
90°-120°	275.8	6.2
90°-150°	1217.0	27.4
90°-180°	1674.0	37.7
0°-180°	4434.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1342	1342	1342	1342	1342	
5°	1342	1335	1320	1330	1327	127
15°	1276	1261	1221	1199	1186	359
25°	1158	1117	1039	991	971	532
35°	998	934	829	755	726	624
45°	816	732	607	524	492	630
55°	620	524	395	324	299	554
65°	419	320	211	172	166	415
75°	223	141	97	89	87	236
85°	52	28	23	23	23	62
90°	0	5	8	10	11	3
95°	27	14	16	18	18	33
105°	126	131	25	30	31	134
115°	238	245	255	73	34	234
125°	336	342	349	352	354	300
135°	416	422	426	430	430	321
145°	482	482	489	492	490	302
155°	531	528	532	535	532	245
165°	560	558	558	561	558	158
175°	573	570	570	573	569	54
180°	571	571	571	571	571	



TEST NUMBER: P331744-927

CATALOG NUMBER: S122RDIP-S1005D530U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1346.4	1345.3	1344.2	1343.1	1342.0	1340.3	1337.9	1335.6	1333.2	1330.9	1333.0
5°	1341.5	1340.1	1338.8	1337.4	1336.1	1333.7	1330.2	1326.7	1323.2	1319.7	1322.1
7.5°	1327.7	1326.0	1324.4	1322.6	1321.0	1318.1	1314.0	1309.9	1305.8	1301.7	1302.4
10°	1316.1	1314.2	1312.2	1310.3	1308.4	1304.8	1299.4	1294.0	1288.6	1283.3	1282.5
12.5°	1301.5	1299.1	1296.8	1294.5	1292.2	1287.5	1280.6	1273.7	1266.9	1260.0	1258.5
15°	1276.0	1273.0	1270.0	1267.0	1264.1	1258.0	1248.9	1239.7	1230.5	1221.3	1216.2
17.5°	1244.6	1240.1	1235.6	1231.1	1226.5	1218.4	1206.6	1194.8	1183.0	1171.3	1165.2
20°	1221.3	1215.9	1210.5	1205.1	1199.8	1190.3	1176.8	1163.3	1149.9	1136.3	1129.6
22.5°	1196.0	1190.0	1184.0	1178.0	1171.9	1161.3	1146.1	1130.8	1115.6	1100.4	1091.7
25°	1158.2	1149.5	1140.9	1132.3	1123.6	1110.5	1092.7	1074.8	1057.0	1039.2	1028.2
27.5°	1112.5	1103.2	1093.8	1084.4	1075.0	1060.3	1040.2	1020.1	1000.1	980.0	967.1
30°	1080.5	1070.2	1060.0	1049.7	1039.5	1023.6	1002.0	980.4	958.9	937.2	923.4
32.5°	1049.4	1037.4	1025.5	1013.5	1001.5	984.5	962.5	940.5	918.5	896.4	880.7
35°	997.9	984.2	970.4	956.6	942.9	924.2	900.4	876.7	852.9	829.2	812.2
37.5°	946.5	931.4	916.2	901.1	886.1	865.9	840.5	815.2	789.9	764.6	745.9
40°	910.5	894.4	878.1	862.0	845.8	824.6	798.4	772.3	746.1	719.9	700.8
42.5°	873.6	856.6	839.6	822.4	805.4	783.4	756.4	729.3	702.3	675.3	655.5
45°	815.9	797.7	779.7	761.6	743.5	720.3	692.0	663.7	635.3	607.0	587.9
47.5°	759.5	740.4	721.2	702.0	682.9	658.7	629.5	600.2	570.9	541.7	522.7
50°	718.7	699.6	680.4	661.2	642.1	617.7	588.0	558.3	528.6	499.0	480.4
52.5°	678.9	658.9	638.9	618.9	598.8	574.3	545.3	516.3	487.2	458.2	440.2
55°	620.4	599.4	578.3	557.2	536.2	511.1	482.0	452.8	423.7	394.6	378.3
57.5°	560.4	538.8	517.2	495.7	474.0	449.2	421.3	393.2	365.3	337.2	322.4
60°	519.6	498.0	476.4	454.9	433.2	408.6	380.8	353.0	325.2	297.5	283.7
62.5°	479.8	458.2	436.7	415.0	393.5	369.4	342.9	316.4	289.9	263.5	250.3
65°	418.8	397.0	375.2	353.3	331.4	308.4	284.1	259.8	235.5	211.3	202.1
67.5°	360.0	338.4	316.7	295.0	273.3	251.5	229.7	207.9	186.0	164.1	159.9
70°	319.3	298.3	277.2	256.2	235.1	215.3	196.7	178.1	159.5	140.9	138.2
72.5°	280.4	260.2	240.1	219.9	199.7	182.1	167.2	152.3	137.3	122.4	120.1
75°	223.4	204.5	185.6	166.8	147.8	133.8	124.6	115.5	106.3	97.1	95.2
77.5°	167.3	150.8	134.2	117.6	101.0	90.5	86.1	81.7	77.2	72.9	71.8
80°	132.3	118.6	104.8	91.0	77.3	69.1	66.4	63.7	61.0	58.3	57.2
82.5°	100.3	89.5	78.8	68.0	57.4	51.0	49.2	47.4	45.6	43.7	43.1
85°	52.2	46.5	40.9	35.2	29.5	26.3	25.5	24.7	23.8	23.1	23.1
87.5°	15.6	14.1	12.6	11.0	9.5	8.9	9.0	9.1	9.3	9.4	9.3
90°	0.4	1.4	2.5	3.4	4.4	5.3	6.1	6.8	7.5	8.2	8.7
92.5°	8.3	8.2	8.2	8.1	8.0	8.2	8.5	8.9	9.2	9.6	9.8
95°	26.9	23.8	20.8	17.7	14.7	13.5	14.2	14.8	15.4	16.2	16.6
97.5°	53.3	44.8	36.3	27.7	19.2	15.6	17.1	18.6	20.1	21.5	21.9
100°	73.2	60.6	48.0	35.4	22.8	17.3	18.9	20.4	22.0	23.5	24.3
102.5°	95.0	92.4	89.7	87.0	84.4	76.4	63.5	50.4	37.3	24.2	25.2
105°	125.6	128.4	131.2	134.0	136.7	125.6	100.4	75.4	50.3	25.2	26.2
107.5°	160.7	162.9	165.1	167.3	169.5	155.6	125.6	95.5	65.4	35.3	34.3
110°	183.2	185.1	187.0	188.9	190.8	178.6	152.0	125.5	98.9	72.3	63.1



TEST NUMBER: P331744-927

CATALOG NUMBER: S122RDIP-S1005D530U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	204.3	206.0	207.7	209.5	211.1	208.7	202.2	195.6	189.0	182.5	148.9
115°	237.7	239.2	240.8	242.4	244.0	245.9	248.2	250.5	252.8	255.1	212.5
117.5°	267.6	269.3	271.1	272.8	274.6	276.2	277.8	279.4	281.0	282.5	272.3
120°	289.4	290.7	292.2	293.5	294.9	296.4	298.1	299.8	301.3	303.0	304.1
122.5°	307.9	309.3	310.9	312.3	313.7	315.4	317.1	318.9	320.8	322.6	323.2
125°	336.1	337.3	338.5	339.7	340.9	342.4	344.1	345.9	347.6	349.4	350.0
127.5°	361.6	363.0	364.3	365.6	366.9	368.3	369.6	370.9	372.2	373.5	374.4
130°	377.9	379.3	380.8	382.3	383.7	385.0	386.0	387.0	388.0	389.0	390.1
132.5°	394.4	395.6	396.9	398.2	399.4	400.5	401.6	402.6	403.5	404.6	405.4
135°	415.9	417.4	418.8	420.3	421.8	422.9	423.7	424.6	425.4	426.2	427.1
137.5°	437.7	438.6	439.7	440.7	441.7	442.8	443.7	444.7	445.5	446.5	447.4
140°	451.9	452.6	453.4	454.1	454.8	455.7	456.7	457.7	458.7	459.7	460.6
142.5°	463.7	464.5	465.1	465.7	466.4	467.3	468.5	469.6	470.8	472.0	472.7
145°	482.4	482.4	482.3	482.2	482.1	482.8	484.4	485.9	487.5	489.1	489.7
147.5°	498.8	498.4	498.0	497.7	497.3	498.0	499.5	501.1	502.6	504.1	504.6
150°	509.3	508.7	508.0	507.4	506.8	507.2	508.7	510.1	511.6	513.0	513.6
152.5°	518.2	517.5	516.8	516.1	515.4	515.7	517.1	518.6	519.9	521.3	521.9
155°	531.2	530.4	529.6	528.8	527.9	528.1	529.2	530.3	531.4	532.5	533.1
157.5°	541.4	540.7	540.0	539.3	538.6	538.7	539.4	540.2	541.0	541.8	542.3
160°	547.4	546.8	546.3	545.7	545.2	545.2	545.7	546.3	546.8	547.4	548.0
162.5°	552.6	552.1	551.5	551.0	550.5	550.4	550.9	551.4	551.8	552.3	552.9
165°	559.8	559.2	558.6	558.1	557.5	557.5	557.7	557.9	558.3	558.5	559.2
167.5°	565.1	564.5	564.0	563.4	562.8	562.7	562.9	563.2	563.5	563.7	564.4
170°	568.0	567.5	567.0	566.4	565.9	565.6	565.9	566.0	566.2	566.4	567.0
172.5°	570.1	569.5	568.9	568.4	567.8	567.6	567.8	568.0	568.2	568.4	569.0
175°	572.6	572.0	571.3	570.7	570.0	569.8	570.0	570.1	570.3	570.5	571.2
177.5°	573.0	572.5	572.0	571.5	570.9	570.7	570.8	570.8	570.9	571.0	571.6
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331744-927

CATALOG NUMBER: S122RDIP-S1005D530U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5	1341.5
2.5°	1335.1	1337.3	1339.5	1340.3	1339.9	1339.5	1339.0	1338.6
5°	1324.5	1327.0	1329.4	1330.2	1329.4	1328.6	1327.8	1327.0
7.5°	1303.1	1303.8	1304.5	1304.2	1302.7	1301.3	1300.0	1298.5
10°	1281.6	1280.8	1280.0	1278.8	1277.2	1275.6	1273.9	1272.3
12.5°	1257.0	1255.5	1254.1	1252.0	1249.4	1246.7	1244.0	1241.3
15°	1211.1	1205.9	1200.8	1196.9	1194.2	1191.5	1188.8	1186.1
17.5°	1159.1	1153.0	1146.9	1141.5	1136.9	1132.3	1127.6	1123.0
20°	1122.8	1116.1	1109.4	1103.0	1097.1	1091.2	1085.2	1079.3
22.5°	1083.1	1074.4	1065.6	1059.1	1054.7	1050.3	1045.8	1041.4
25°	1017.1	1006.1	995.0	987.5	983.3	979.3	975.3	971.2
27.5°	954.2	941.3	928.4	918.7	912.3	905.9	899.4	893.0
30°	909.7	896.0	882.2	871.7	864.4	857.1	849.9	842.6
32.5°	865.1	849.4	833.6	822.4	815.6	808.7	801.8	795.0
35°	795.2	778.2	761.2	749.7	743.8	737.8	731.9	726.0
37.5°	727.1	708.4	689.7	676.9	670.2	663.4	656.6	649.7
40°	681.6	662.4	643.3	630.3	623.2	616.2	609.2	602.1
42.5°	635.6	615.8	596.0	582.7	575.9	569.1	562.4	555.6
45°	568.7	549.5	530.4	517.6	511.1	504.6	498.1	491.7
47.5°	503.6	484.6	465.5	453.0	447.2	441.3	435.4	429.5
50°	461.8	443.1	424.5	412.3	406.7	401.0	395.4	389.7
52.5°	422.2	404.3	386.3	374.7	369.5	364.2	359.0	353.8
55°	362.2	346.0	329.8	319.2	314.0	308.9	303.8	298.7
57.5°	307.6	292.7	277.9	268.3	264.0	259.7	255.4	251.0
60°	269.9	256.2	242.4	233.4	229.0	224.7	220.4	216.1
62.5°	237.3	224.1	211.0	203.1	200.6	198.0	195.4	192.8
65°	192.9	183.7	174.5	169.5	168.7	167.9	167.2	166.4
67.5°	155.7	151.5	147.3	144.7	143.9	143.1	142.2	141.3
70°	135.5	132.8	130.1	128.2	127.1	126.0	124.9	123.8
72.5°	117.9	115.6	113.3	111.9	111.2	110.6	109.9	109.2
75°	93.3	91.5	89.6	88.5	88.2	87.9	87.7	87.4
77.5°	70.7	69.6	68.5	67.7	67.3	66.9	66.5	66.1
80°	56.1	55.1	53.9	53.4	53.4	53.4	53.4	53.4
82.5°	42.4	41.7	41.1	40.8	40.8	40.8	40.8	40.8
85°	23.1	23.1	23.1	23.1	23.1	23.1	23.1	23.1
87.5°	9.2	9.0	9.0	8.9	9.0	9.0	9.0	9.0
90°	9.2	9.7	10.1	10.5	10.6	10.8	11.0	11.2
92.5°	10.1	10.3	10.5	10.7	10.9	10.9	11.1	11.2
95°	17.0	17.5	18.0	18.1	18.1	18.0	17.9	17.7
97.5°	22.3	22.7	23.1	23.3	23.4	23.5	23.6	23.8
100°	25.0	25.7	26.5	26.9	27.2	27.3	27.5	27.7
102.5°	26.1	27.1	28.0	28.7	28.9	29.2	29.4	29.7
105°	27.3	28.3	29.2	29.9	30.3	30.7	31.1	31.4
107.5°	33.3	32.2	31.2	30.9	31.2	31.6	31.9	32.3
110°	53.9	44.8	35.6	31.2	31.5	31.9	32.3	32.6





TEST NUMBER: P331744-927

CATALOG NUMBER: S122RDIP-S1005D530U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	115.4	81.9	48.4	31.8	32.1	32.4	32.7	33.0
115°	170.0	127.5	84.9	60.4	53.7	47.1	40.5	33.9
117.5°	262.0	251.7	241.4	225.4	203.6	181.9	160.2	138.4
120°	305.2	306.3	307.4	301.8	289.4	277.0	264.6	252.2
122.5°	323.8	324.6	325.2	324.3	321.9	319.5	317.1	314.7
125°	350.6	351.3	351.9	352.4	352.7	352.9	353.2	353.5
127.5°	375.3	376.3	377.2	377.7	377.8	377.9	377.9	378.0
130°	391.0	392.1	393.1	393.6	393.4	393.3	393.2	393.2
132.5°	406.3	407.2	408.1	408.4	408.3	408.2	408.1	408.1
135°	428.1	429.0	429.9	430.3	430.1	429.9	429.8	429.5
137.5°	448.3	449.2	450.1	450.4	450.0	449.7	449.5	449.2
140°	461.4	462.2	463.0	463.2	462.7	462.3	461.8	461.4
142.5°	473.5	474.2	475.0	475.2	474.7	474.2	473.7	473.2
145°	490.4	491.0	491.6	491.7	491.3	490.8	490.4	489.9
147.5°	505.1	505.6	506.0	506.0	505.7	505.3	504.9	504.5
150°	514.1	514.7	515.2	515.3	514.8	514.4	513.9	513.5
152.5°	522.4	523.0	523.6	523.5	522.9	522.3	521.7	521.1
155°	533.6	534.2	534.7	534.6	533.9	533.1	532.4	531.6
157.5°	543.0	543.6	544.2	544.2	543.4	542.7	542.0	541.3
160°	548.4	549.0	549.5	549.5	548.9	548.3	547.6	546.9
162.5°	553.6	554.2	554.8	554.8	554.0	553.2	552.4	551.6
165°	559.8	560.5	561.1	561.1	560.5	559.8	559.2	558.5
167.5°	565.0	565.7	566.3	566.3	565.4	564.6	563.7	562.9
170°	567.7	568.3	568.9	568.9	568.0	567.2	566.4	565.5
172.5°	569.7	570.3	570.9	570.8	570.1	569.2	568.4	567.5
175°	571.8	572.4	573.1	573.0	572.0	571.1	570.2	569.3
177.5°	572.0	572.6	573.1	573.0	572.4	571.6	571.0	570.4
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3

(END OF REPORT)